

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P321128

Luminaire Tested: **GLEON-SA4C-830-U-AFL**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P321128
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-29)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GLEON-SA4C-830-U-AFL
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(4) 80 CRI, 3000K, 1050mA LIGHTSQUARES WITH 16 LEDS EACH AND AUTOMOTIVE
FRONTLINE OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 23261 lumens
Efficiency: N/A
Efficacy: 103.4 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B3 - U0 - G2


Input Watts (W): 225
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P321128
 CATALOG NUMBER: GLEON-SA4C-830-U-AFL

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 11.4 fc
 Type II - Short - N/A

REPORT NUMBER: P321128
CATALOG NUMBER: GLEON-SA4C-830-U-AFL

Luminous Intensity Polar Plot



REPORT NUMBER: P321128

CATALOG NUMBER: GLEON-SA4C-830-U-AFL

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4009.7	0.0	4009.7
	% Fixture	17.2	0.0	17.2
Street Side	Lumens	19251.3	0.0	19251.3
	% Fixture	82.8	0.0	82.8
Total	Lumens	23261.0	0.0	23261.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	492.8	2.1
10°-20°	1393.4	6.0
20°-30°	2269.6	9.8
30°-40°	3392.7	14.6
40°-50°	5146.1	22.1
50°-60°	5767.8	24.8
60°-70°	3406.7	14.6
70°-80°	1116.2	4.8
80°-90°	275.8	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	23261.0	100.0
0°-180°	23261.0	100.0

Coefficient of Utilization



REPORT NUMBER: P321128


CATALOG NUMBER: GLEON-SA4C-830-U-AFL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	2996.4	12.9			
FM	(30°-60°)	12526.8	53.9			
FH	(60°-80°)	3606.7	15.5			G2/5000
FVH	(80°-90°)	121.4	0.5			G2/225
BL	(0°-30°)	1159.4	5.0	B3/2500		
BM	(30°-60°)	1779.8	7.7	B2/2500		
BH	(60°-80°)	916.2	3.9	B2/1000		G2/1000
BVH	(80°-90°)	154.3	0.7			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G2

Type II Short





REPORT NUMBER: P321128

CATALOG NUMBER: GLEON-SA4C-830-U-AFL

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	56°	65°	75°	85°
0°	5159.3	5159.3	5159.3	5159.3	5159.3	5159.3	5159.3	5159.3	5159.3	5159.3	5159.3
2.5°	5924.3	5978.7	5954.7	5871.6	5807.6	5717.3	5616.6	5586.2	5479.9	5360.8	5217.7
5°	6862.0	6834.8	6795.7	6666.2	6529.5	6370.4	6117.8	6077.8	5841.2	5571.8	5287.2
7.5°	7396.0	7393.6	7370.4	7294.5	7169.8	6962.0	6657.4	6610.2	6252.9	5819.6	5378.3
10°	7318.5	7312.9	7351.3	7430.4	7468.0	7424.8	7168.2	7121.0	6682.2	6093.8	5483.9
12.5°	6878.0	6881.2	6942.8	7109.0	7335.3	7607.1	7565.5	7542.3	7127.4	6404.0	5611.8
15°	6535.1	6542.3	6591.0	6735.7	7002.7	7495.9	7806.9	7814.9	7558.3	6746.1	5761.3
17.5°	6384.8	6400.0	6422.4	6523.9	6768.5	7274.5	7864.5	7907.6	7935.6	7101.0	5905.1
20°	6432.8	6447.1	6453.5	6518.3	6718.9	7140.2	7824.5	7902.0	8225.0	7435.2	6049.0
22.5°	6647.8	6656.6	6660.6	6677.4	6833.2	7178.6	7798.1	7879.7	8434.4	7735.0	6157.8
25°	7004.3	6997.9	6972.3	6950.8	7055.5	7330.5	7858.9	7936.4	8604.7	8006.8	6228.9
27.5°	7431.2	7423.2	7373.6	7314.5	7374.4	7567.1	8033.9	8095.5	8757.4	8261.0	6264.9
30°	7943.6	7922.8	7829.3	7759.0	7782.1	7922.0	8322.5	8378.5	8993.2	8549.6	6300.1
32.5°	8536.0	8513.6	8378.5	8261.8	8261.8	8378.5	8619.9	8666.3	9193.1	8875.7	6356.8
35°	9277.8	9249.8	9074.0	8878.1	8822.9	8882.1	9025.2	9058.0	9552.8	9286.6	6459.9
37.5°	10152.3	10114.8	9886.9	9624.7	9504.0	9500.8	9604.0	9671.1	10127.6	9826.2	6635.0
40°	11029.3	11002.9	10803.9	10597.6	10361.0	10285.0	10444.1	10464.9	10879.0	10496.1	6858.8
42.5°	11707.2	11702.4	11665.6	11692.8	11450.6	11297.1	11421.8	11438.6	11796.7	11221.1	7097.1
45°	12065.3	12073.3	12251.6	12646.5	12736.0	12624.1	12685.6	12690.4	12845.5	11952.6	7315.3
47.5°	11778.3	11819.9	12270.8	13154.1	13887.1	14258.9	14156.5	14215.7	13862.4	12580.9	7486.4
50°	10660.0	10711.1	11478.5	12927.9	14424.3	15840.9	15787.3	15773.7	14682.5	13041.4	7579.1
52.5°	9274.6	9314.6	9947.7	11751.9	14030.2	16715.4	17207.0	17136.7	15411.6	13385.9	7596.7
55°	7165.0	7227.4	7834.1	9404.9	12436.2	16381.3	18251.0	18187.9	16075.9	13566.6	7575.9
57°	5093.8	5159.3	5762.1	7177.8	10461.7	15224.5	18355.0	18422.1	16434.8	13597.0	7599.1
57.5°	4545.4	4612.5	5209.7	6584.6	9846.2	14806.4	18265.4	18377.3	16499.6	13592.2	7611.9
60°	2288.7	2314.3	2694.8	3675.6	6224.1	11970.2	17097.5	17386.1	16557.9	13357.1	7667.0
62.5°	1422.9	1404.5	1392.6	1693.1	3028.1	7938.0	14687.3	15242.9	15441.2	12788.0	7533.5
65°	1251.1	1216.7	1084.8	1060.8	1337.4	3855.5	11060.5	11751.9	13055.0	11891.0	7215.4
67.5°	1175.1	1141.5	992.9	903.3	904.1	1528.4	6866.8	7645.4	10169.9	10374.6	6464.7
70°	1096.8	1066.4	927.3	821.8	769.8	846.6	3159.2	3750.0	6629.4	8154.7	5403.1
72.5°	996.0	975.3	843.4	734.6	679.5	633.9	1209.5	1428.5	3837.9	5476.7	3752.4
75°	890.5	871.3	758.6	654.7	587.6	498.8	681.1	733.8	1949.7	2801.9	1847.4
77.5°	774.6	763.4	674.7	578.8	525.2	413.3	482.0	507.6	836.2	1201.5	926.5
80°	616.3	637.9	590.0	515.6	466.0	331.0	341.3	358.1	486.8	586.8	526.0
82.5°	401.3	438.9	462.1	418.9	383.7	260.6	245.4	252.6	317.4	358.1	228.6
85°	167.1	187.9	303.8	274.2	255.0	190.3	164.7	167.9	196.7	203.8	93.5
87.5°	74.3	79.1	133.5	125.5	107.9	65.6	70.3	76.7	104.7	99.1	36.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P321128

CATALOG NUMBER: GLEON-SA4C-830-U-AFL

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	5159.3	5159.3	5159.3	5159.3	5159.3	5159.3	5159.3	5159.3	5159.3	5159.3	5159.3
2.5°	5164.1	5097.0	4981.8	4854.7	4750.8	4667.7	4583.7	4526.2	4459.0	4423.1	4404.7
5°	5168.1	5036.2	4794.0	4545.4	4323.1	4120.1	3926.6	3778.0	3638.9	3563.7	3542.9
7.5°	5184.9	4986.6	4594.9	4185.6	3790.7	3430.2	3152.0	2977.8	2852.3	2796.3	2780.3
10°	5198.5	4928.3	4348.7	3742.8	3205.6	2840.3	2624.4	2526.9	2483.7	2476.5	2469.3
12.5°	5230.5	4868.3	4089.7	3280.7	2750.7	2498.1	2423.0	2416.6	2428.6	2446.2	2446.2
15°	5280.8	4809.2	3793.9	2884.2	2461.3	2372.6	2387.8	2423.0	2455.7	2482.9	2486.9
17.5°	5317.6	4736.4	3475.8	2566.9	2307.1	2331.0	2385.4	2435.0	2468.5	2494.9	2497.3
20°	5344.0	4623.7	3136.0	2324.6	2218.3	2292.7	2360.6	2404.6	2427.8	2454.2	2458.1
22.5°	5330.4	4472.6	2834.7	2151.2	2146.4	2236.7	2301.5	2354.2	2336.6	2311.1	2327.8
25°	5264.8	4264.8	2524.5	2021.7	2070.4	2161.6	2241.5	2206.3	2147.2	2136.0	2142.4
27.5°	5148.1	3999.4	2237.5	1901.8	1982.5	2092.0	2087.2	2052.1	2031.3	2016.9	2025.7
30°	5022.6	3711.6	1986.5	1797.0	1885.0	1975.3	1956.9	1956.1	1935.3	1912.2	1923.4
32.5°	4898.7	3422.2	1787.5	1710.7	1811.4	1823.4	1863.4	1875.4	1834.6	1785.9	1782.7
35°	4790.8	3148.8	1636.4	1632.4	1722.7	1724.3	1782.7	1765.9	1664.3	1614.0	1614.0
37.5°	4710.0	2876.2	1521.3	1562.0	1606.0	1647.6	1677.1	1607.6	1590.8	1562.8	1562.0
40°	4674.9	2636.4	1449.3	1508.5	1523.7	1576.4	1500.5	1527.6	1535.6	1521.3	1521.3
42.5°	4638.1	2427.8	1387.0	1467.7	1465.3	1458.1	1419.7	1454.9	1486.9	1487.7	1485.3
45°	4601.3	2247.9	1331.8	1380.6	1414.1	1336.6	1343.8	1381.4	1426.1	1442.1	1442.1
47.5°	4560.6	2105.6	1281.4	1288.6	1340.6	1288.6	1283.0	1311.8	1364.6	1390.2	1395.7
50°	4471.0	1977.7	1223.9	1207.9	1222.3	1239.9	1244.7	1258.3	1316.6	1357.4	1367.0
52.5°	4347.1	1863.4	1150.3	1133.5	1133.5	1199.9	1222.3	1226.3	1275.8	1324.6	1334.2
55°	4244.0	1790.7	1074.4	1071.2	1068.0	1157.5	1195.9	1202.3	1236.7	1275.0	1279.8
57°	4251.2	1785.1	1016.0	1019.2	1018.4	1114.4	1171.1	1184.7	1202.3	1235.1	1240.7
57.5°	4255.2	1789.1	1003.2	1004.8	1004.0	1102.4	1163.9	1179.1	1192.7	1227.1	1232.7
60°	4315.1	1799.4	951.3	933.7	937.7	1038.4	1123.2	1142.3	1151.1	1196.7	1203.9
62.5°	4226.4	1753.1	909.7	867.3	867.3	971.3	1066.4	1096.8	1110.4	1171.9	1183.9
65°	3969.0	1622.8	861.0	792.2	800.2	904.1	998.4	1048.0	1068.8	1145.5	1158.3
67.5°	3571.7	1471.7	809.0	725.1	733.0	833.8	928.1	981.7	1014.4	1116.8	1127.2
70°	3054.5	1287.0	738.6	653.9	663.5	757.0	845.0	905.7	954.5	1089.6	1092.8
72.5°	2251.9	1055.2	640.3	575.6	586.0	667.5	761.0	831.4	896.9	1021.6	1020.0
75°	1339.0	825.0	531.6	496.4	503.6	579.6	685.1	770.6	868.9	995.2	1010.4
77.5°	812.2	621.1	433.3	415.7	424.5	502.0	630.7	721.9	857.0	938.5	933.7
80°	490.8	443.7	346.1	334.9	343.7	429.3	583.6	685.1	749.0	801.8	801.8
82.5°	256.6	271.0	254.2	245.4	257.4	348.5	530.8	597.9	661.9	568.4	530.8
85°	104.7	141.5	154.3	153.5	160.7	241.4	458.1	511.6	426.9	405.3	414.9
87.5°	35.2	60.0	75.1	64.8	67.9	151.9	317.4	247.0	293.4	204.6	194.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW EDISON

Report Number: SP1-2408-195-9

Test Date: 08/07/2024

Luminaire Tested: GALN-SB1A-830-U-5WQ

Data in this report applies to families of products including GALN-SB1A-830-U-5WQ.

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2408-195-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/07/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: MCGRAW EDISON
 Catalog Number: **GALN-SB1A-830-U-5WQ**
 Description: GALLEON AREA AND ROADWAY LUMINAIRE. (1) 80 CRI, 3000K, 350MA HIGH DENSITY LIGHTSQUARE WITH 26 LEDS AND TYPE V WIDE OPTICS

Spectral Parameters

CCT (K): 3050
 CIE u' : 0.2476
 CIE v' : 0.5251
 Duv: 0.0034
 CIE x: 0.4383
 CIE y: 0.4131
 CIE z: 0.1487
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 581
 Purity: 55.55201
 R_f: 81.5
 R_g: 99.2

CRI (Ra): 81.0
 R1: 79.6
 R2: 85.6
 R3: 92.0
 R4: 82.6
 R5: 78.9
 R6: 81.7
 R7: 85.2
 R8: 62.0
 R9: 7.1
 R10: 67.0
 R11: 82.7
 R12: 63.2
 R13: 80.3
 R14: 95.0
 R15: 71.7



Test Conditions

Stabilization Time: 20M
 Operation Time: 1H 20M
 Sphere Temperature (°C): 24.2

REPORT NUMBER: SP1-2408-195-9

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2408-195-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2408-195-9

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	168	NR	620	940	NR	750	35	NR	880	1	NR
365	0	NR	495	233	NR	625	897	NR	755	30	NR	885	1	NR
370	0	NR	500	300	NR	630	847	NR	760	26	NR	890	1	NR
375	0	NR	505	372	NR	635	790	NR	765	22	NR	895	1	NR
380	0	NR	510	430	NR	640	730	NR	770	19	NR	900	1	NR
385	0	NR	515	483	NR	645	668	NR	775	16	NR	905	1	NR
390	0	NR	520	524	NR	650	605	NR	780	14	NR	910	0	NR
395	2	NR	525	555	NR	655	545	NR	785	12	NR	915	0	NR
400	4	NR	530	581	NR	660	485	NR	790	10	NR	920	0	NR
405	7	NR	535	604	NR	665	430	NR	795	9	NR	925	0	NR
410	17	NR	540	623	NR	670	378	NR	800	8	NR	930	0	NR
415	34	NR	545	645	NR	675	331	NR	805	7	NR	935	0	NR
420	68	NR	550	667	NR	680	290	NR	810	6	NR	940	0	NR
425	128	NR	555	693	NR	685	251	NR	815	5	NR	945	0	NR
430	214	NR	560	719	NR	690	218	NR	820	4	NR	950	0	NR
435	339	NR	565	754	NR	695	188	NR	825	4	NR	955	0	NR
440	507	NR	570	791	NR	700	162	NR	830	3	NR	960	0	NR
445	573	NR	575	830	NR	705	139	NR	835	3	NR	965	0	NR
450	356	NR	580	873	NR	710	119	NR	840	3	NR	970	0	NR
455	217	NR	585	913	NR	715	102	NR	845	2	NR	975	0	NR
460	168	NR	590	948	NR	720	88	NR	850	2	NR	980	0	NR
465	113	NR	595	974	NR	725	76	NR	855	2	NR	985	0	NR
470	85	NR	600	994	NR	730	65	NR	860	1	NR	990	0	NR
475	85	NR	605	998	NR	735	55	NR	865	1	NR	995	0	NR
480	94	NR	610	994	NR	740	47	NR	870	1	NR	1000	0	NR
485	120	NR	615	973	NR	745	41	NR	875	1	NR			

REPORT NUMBER: SP1-2408-195-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.27

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	168	NR	620	940	NR	750	35	NR	880	1	NR
365	0	NR	495	233	NR	625	897	NR	755	30	NR	885	1	NR
370	0	NR	500	300	NR	630	847	NR	760	26	NR	890	1	NR
375	0	NR	505	372	NR	635	790	NR	765	22	NR	895	1	NR
380	0	NR	510	430	NR	640	730	NR	770	19	NR	900	1	NR
385	0	NR	515	483	NR	645	668	NR	775	16	NR	905	1	NR
390	0	NR	520	524	NR	650	605	NR	780	14	NR	910	0	NR
395	2	NR	525	555	NR	655	545	NR	785	12	NR	915	0	NR
400	4	NR	530	581	NR	660	485	NR	790	10	NR	920	0	NR
405	7	NR	535	604	NR	665	430	NR	795	9	NR	925	0	NR
410	17	NR	540	623	NR	670	378	NR	800	8	NR	930	0	NR
415	34	NR	545	645	NR	675	331	NR	805	7	NR	935	0	NR
420	68	NR	550	667	NR	680	290	NR	810	6	NR	940	0	NR
425	128	NR	555	693	NR	685	251	NR	815	5	NR	945	0	NR
430	214	NR	560	719	NR	690	218	NR	820	4	NR	950	0	NR
435	339	NR	565	754	NR	695	188	NR	825	4	NR	955	0	NR
440	507	NR	570	791	NR	700	162	NR	830	3	NR	960	0	NR
445	573	NR	575	830	NR	705	139	NR	835	3	NR	965	0	NR
450	356	NR	580	873	NR	710	119	NR	840	3	NR	970	0	NR
455	217	NR	585	913	NR	715	102	NR	845	2	NR	975	0	NR
460	168	NR	590	948	NR	720	88	NR	850	2	NR	980	0	NR
465	113	NR	595	974	NR	725	76	NR	855	2	NR	985	0	NR
470	85	NR	600	994	NR	730	65	NR	860	1	NR	990	0	NR
475	85	NR	605	998	NR	735	55	NR	865	1	NR	995	0	NR
480	94	NR	610	994	NR	740	47	NR	870	1	NR	1000	0	NR
485	120	NR	615	973	NR	745	41	NR	875	1	NR			

REPORT NUMBER: SP1-2408-195-9

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 2.32

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	168	NR	620	940	NR	750	35	NR	880	1	NR
365	0	NR	495	233	NR	625	897	NR	755	30	NR	885	1	NR
370	0	NR	500	300	NR	630	847	NR	760	26	NR	890	1	NR
375	0	NR	505	372	NR	635	790	NR	765	22	NR	895	1	NR
380	0	NR	510	430	NR	640	730	NR	770	19	NR	900	1	NR
385	0	NR	515	483	NR	645	668	NR	775	16	NR	905	1	NR
390	0	NR	520	524	NR	650	605	NR	780	14	NR	910	0	NR
395	2	NR	525	555	NR	655	545	NR	785	12	NR	915	0	NR
400	4	NR	530	581	NR	660	485	NR	790	10	NR	920	0	NR
405	7	NR	535	604	NR	665	430	NR	795	9	NR	925	0	NR
410	17	NR	540	623	NR	670	378	NR	800	8	NR	930	0	NR
415	34	NR	545	645	NR	675	331	NR	805	7	NR	935	0	NR
420	68	NR	550	667	NR	680	290	NR	810	6	NR	940	0	NR
425	128	NR	555	693	NR	685	251	NR	815	5	NR	945	0	NR
430	214	NR	560	719	NR	690	218	NR	820	4	NR	950	0	NR
435	339	NR	565	754	NR	695	188	NR	825	4	NR	955	0	NR
440	507	NR	570	791	NR	700	162	NR	830	3	NR	960	0	NR
445	573	NR	575	830	NR	705	139	NR	835	3	NR	965	0	NR
450	356	NR	580	873	NR	710	119	NR	840	3	NR	970	0	NR
455	217	NR	585	913	NR	715	102	NR	845	2	NR	975	0	NR
460	168	NR	590	948	NR	720	88	NR	850	2	NR	980	0	NR
465	113	NR	595	974	NR	725	76	NR	855	2	NR	985	0	NR
470	85	NR	600	994	NR	730	65	NR	860	1	NR	990	0	NR
475	85	NR	605	998	NR	735	55	NR	865	1	NR	995	0	NR
480	94	NR	610	994	NR	740	47	NR	870	1	NR	1000	0	NR
485	120	NR	615	973	NR	745	41	NR	875	1	NR			

REPORT NUMBER: SP1-2408-195-9

TM-30-18

Summary

$R_f = 81.5$
 $R_g = 99.2$
 $CIE R_a = 81.0$
 $R_9 = 7.1$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 74	CES51 = 89	CES76 = 70
CES02 = 63	CES27 = 88	CES52 = 92	CES77 = 86
CES03 = 31	CES28 = 89	CES53 = 81	CES78 = 72
CES04 = 70	CES29 = 67	CES54 = 87	CES79 = 90
CES05 = 50	CES30 = 68	CES55 = 85	CES80 = 88
CES06 = 51	CES31 = 71	CES56 = 78	CES81 = 78
CES07 = 42	CES32 = 70	CES57 = 76	CES82 = 95
CES08 = 41	CES33 = 71	CES58 = 78	CES83 = 90
CES09 = 29	CES34 = 82	CES59 = 92	CES84 = 94
CES10 = 76	CES35 = 90	CES60 = 95	CES85 = 86
CES11 = 59	CES36 = 93	CES61 = 93	CES86 = 72
CES12 = 65	CES37 = 87	CES62 = 83	CES87 = 85
CES13 = 43	CES38 = 75	CES63 = 77	CES88 = 83
CES14 = 74	CES39 = 94	CES64 = 83	CES89 = 75
CES15 = 71	CES40 = 89	CES65 = 77	CES90 = 81
CES16 = 47	CES41 = 85	CES66 = 80	CES91 = 96
CES17 = 50	CES42 = 86	CES67 = 79	CES92 = 73
CES18 = 56	CES43 = 81	CES68 = 84	CES93 = 84
CES19 = 72	CES44 = 99	CES69 = 91	CES94 = 64
CES20 = 66	CES45 = 87	CES70 = 78	CES95 = 80
CES21 = 87	CES46 = 82	CES71 = 76	CES96 = 84
CES22 = 79	CES47 = 77	CES72 = 92	CES97 = 87
CES23 = 92	CES48 = 71	CES73 = 71	CES98 = 81
CES24 = 91	CES49 = 81	CES74 = 93	CES99 = 74
CES25 = 72	CES50 = 89	CES75 = 74	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)