

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P319167

Luminaire Tested: **GLEON-SA3C-827-U-T4W**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P319167
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GLEON-SA3C-827-U-T4W
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(3) 80 CRI, 2700K, 1050mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV WIDE OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15762 lumens
Efficiency: N/A
Efficacy: 95.0 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B3 - U0 - G3


Input Watts (W): 166
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P319167
 CATALOG NUMBER: GLEON-SA3C-827-U-T4W

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 3.2 fc
 Type IV - Short - N/A

REPORT NUMBER: P319167
CATALOG NUMBER: GLEON-SA3C-827-U-T4W

Luminous Intensity Polar Plot



— Vertical Plane Through 46-Deg Lateral - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P319167
 CATALOG NUMBER: GLEON-SA3C-827-U-T4W


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 3612.6 | 0.0 | 3612.6 |
| | % Fixture | 22.9 | 0.0 | 22.9 |
| Street Side | Lumens | 12149.4 | 0.0 | 12149.4 |
| | % Fixture | 77.1 | 0.0 | 77.1 |
| Total | Lumens | 15762.0 | 0.0 | 15762.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 163.7 | 1.0 |
| 10°-20° | 545.4 | 3.5 |
| 20°-30° | 909.4 | 5.8 |
| 30°-40° | 1290.5 | 8.2 |
| 40°-50° | 1898.3 | 12.0 |
| 50°-60° | 3214.7 | 20.4 |
| 60°-70° | 4563.2 | 29.0 |
| 70°-80° | 2772.2 | 17.6 |
| 80°-90° | 404.6 | 2.6 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 15762.0 | 100.0 |
| 0°-180° | 15762.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P319167
 CATALOG NUMBER: GLEON-SA3C-827-U-T4W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 860.0 | 5.5 | | | |
| FM (30°-60°) | 4740.5 | 30.1 | | | |
| FH (60°-80°) | 6296.8 | 39.9 | | | G3/7500 |
| FVH (80°-90°) | 252.0 | 1.6 | | | G3/500 |
| BL (0°-30°) | 758.5 | 4.8 | B2/1000 | | |
| BM (30°-60°) | 1663.0 | 10.6 | B2/2500 | | |
| BH (60°-80°) | 1038.6 | 6.6 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 152.6 | 1.0 | | | G2/225 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G3

Type IV Short





REPORT NUMBER: P319167
 CATALOG NUMBER: GLEON-SA3C-827-U-T4W

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 46° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|---------|---------|--------|--------|--------|--------|
| 0° | 1605.8 | 1605.8 | 1605.8 | 1605.8 | 1605.8 | 1605.8 | 1605.8 | 1605.8 | 1605.8 | 1605.8 | 1605.8 |
| 2.5° | 1686.2 | 1687.3 | 1689.4 | 1684.1 | 1669.0 | 1664.6 | 1663.0 | 1647.4 | 1637.1 | 1622.0 | 1609.1 |
| 5° | 1821.1 | 1822.1 | 1818.9 | 1803.8 | 1770.4 | 1745.5 | 1743.4 | 1707.8 | 1675.4 | 1640.9 | 1615.0 |
| 7.5° | 1961.9 | 1963.5 | 1953.2 | 1924.6 | 1877.7 | 1834.6 | 1831.9 | 1783.3 | 1734.2 | 1681.9 | 1643.1 |
| 10° | 2086.5 | 2080.0 | 2063.3 | 2023.3 | 1967.8 | 1914.9 | 1912.8 | 1862.1 | 1805.4 | 1742.3 | 1690.5 |
| 12.5° | 2169.5 | 2164.1 | 2142.6 | 2094.0 | 2033.1 | 1984.5 | 1980.2 | 1933.3 | 1878.2 | 1809.2 | 1747.2 |
| 15° | 2215.4 | 2219.2 | 2190.0 | 2135.0 | 2075.7 | 2034.7 | 2030.9 | 1997.5 | 1948.4 | 1878.8 | 1807.6 |
| 17.5° | 2221.3 | 2224.5 | 2196.5 | 2142.0 | 2093.5 | 2065.4 | 2063.8 | 2041.7 | 2006.1 | 1939.2 | 1864.8 |
| 20° | 2186.8 | 2188.9 | 2165.8 | 2121.0 | 2089.2 | 2080.5 | 2080.0 | 2070.3 | 2043.8 | 1984.5 | 1912.2 |
| 22.5° | 2136.6 | 2138.2 | 2121.5 | 2089.2 | 2078.4 | 2091.9 | 2095.6 | 2091.9 | 2073.0 | 2017.4 | 1949.4 |
| 25° | 2124.2 | 2123.1 | 2105.9 | 2073.0 | 2082.1 | 2110.7 | 2115.6 | 2117.2 | 2104.3 | 2055.7 | 1996.9 |
| 27.5° | 2184.1 | 2180.3 | 2147.4 | 2094.5 | 2100.5 | 2135.0 | 2141.5 | 2157.1 | 2149.0 | 2106.4 | 2050.9 |
| 30° | 2357.2 | 2350.8 | 2283.3 | 2176.5 | 2147.4 | 2165.2 | 2173.3 | 2198.1 | 2199.7 | 2164.1 | 2122.6 |
| 32.5° | 2649.6 | 2641.5 | 2520.7 | 2329.7 | 2226.7 | 2196.0 | 2203.5 | 2240.7 | 2260.7 | 2233.2 | 2188.4 |
| 35° | 3019.1 | 3009.9 | 2851.3 | 2590.3 | 2359.4 | 2254.8 | 2260.2 | 2289.8 | 2329.7 | 2290.9 | 2231.6 |
| 37.5° | 3404.2 | 3382.1 | 3229.5 | 2896.7 | 2570.3 | 2380.4 | 2380.4 | 2384.2 | 2403.1 | 2322.2 | 2282.3 |
| 40° | 3787.2 | 3765.1 | 3627.0 | 3257.0 | 2843.3 | 2578.4 | 2566.0 | 2482.4 | 2467.3 | 2397.7 | 2384.2 |
| 42.5° | 4143.2 | 4136.8 | 4055.3 | 3664.2 | 3163.7 | 2773.1 | 2755.9 | 2614.0 | 2617.2 | 2574.1 | 2574.6 |
| 45° | 4521.9 | 4521.9 | 4455.6 | 4075.3 | 3536.9 | 3086.0 | 3068.7 | 2860.0 | 2892.3 | 2872.4 | 2920.4 |
| 47.5° | 4831.0 | 4840.7 | 4831.5 | 4503.6 | 3971.2 | 3483.5 | 3452.3 | 3200.9 | 3291.5 | 3360.0 | 3499.7 |
| 50° | 5146.6 | 5161.7 | 5163.3 | 4973.4 | 4496.0 | 3956.1 | 3920.5 | 3653.5 | 3855.7 | 4052.1 | 4326.6 |
| 52.5° | 5604.5 | 5638.5 | 5503.1 | 5442.2 | 5139.0 | 4517.1 | 4482.0 | 4235.5 | 4573.2 | 4848.8 | 5321.9 |
| 55° | 6029.0 | 5999.4 | 5902.8 | 5940.6 | 5827.3 | 5155.7 | 5129.3 | 4913.0 | 5372.6 | 5730.7 | 6345.1 |
| 57.5° | 6258.8 | 6256.7 | 6353.8 | 6515.6 | 6569.5 | 5943.3 | 5921.2 | 5710.8 | 6273.9 | 6543.1 | 7305.8 |
| 60° | 6528.5 | 6532.3 | 6772.9 | 7140.2 | 7362.5 | 6923.9 | 6914.2 | 6754.6 | 7149.4 | 7301.5 | 8059.4 |
| 62.5° | 6566.3 | 6634.3 | 7048.5 | 7680.7 | 8104.7 | 8069.7 | 8091.2 | 7694.8 | 7932.6 | 7906.7 | 8622.0 |
| 65° | 6132.1 | 6221.6 | 6971.4 | 7844.2 | 8842.6 | 9322.7 | 9342.7 | 8640.4 | 8550.3 | 8424.0 | 8823.2 |
| 67.5° | 5242.0 | 5374.7 | 6189.3 | 7488.7 | 9085.9 | 10248.9 | 10276.9 | 9373.4 | 9062.7 | 8599.4 | 8338.8 |
| 70° | 3814.7 | 3962.0 | 4781.9 | 6395.8 | 8652.2 | 10545.0 | 10576.9 | 9697.6 | 9082.1 | 8100.4 | 7118.7 |
| 72.5° | 2304.4 | 2419.8 | 3095.7 | 4708.6 | 7302.6 | 10005.6 | 10062.3 | 9286.6 | 8291.9 | 6861.4 | 5256.6 |
| 75° | 1011.9 | 1087.5 | 1496.9 | 2713.3 | 5228.0 | 8278.4 | 8349.1 | 7948.8 | 6737.3 | 4986.4 | 3107.0 |
| 77.5° | 431.0 | 452.6 | 613.9 | 1178.6 | 2955.5 | 5656.8 | 5753.9 | 5807.9 | 4571.0 | 2713.3 | 1312.9 |
| 80° | 268.6 | 277.3 | 347.4 | 533.5 | 1383.1 | 3177.2 | 3281.8 | 3417.2 | 2269.9 | 997.4 | 458.5 |
| 82.5° | 163.4 | 173.2 | 230.9 | 322.6 | 720.1 | 1440.2 | 1490.4 | 1585.9 | 880.9 | 431.0 | 237.3 |
| 85° | 98.2 | 105.2 | 141.3 | 203.9 | 410.0 | 566.4 | 565.8 | 625.7 | 414.8 | 277.3 | 125.1 |
| 87.5° | 46.9 | 52.3 | 75.5 | 105.7 | 206.6 | 212.5 | 199.0 | 225.5 | 251.9 | 181.8 | 63.1 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P319167
 CATALOG NUMBER: GLEON-SA3C-827-U-T4W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1605.8 | 1605.8 | 1605.8 | 1605.8 | 1605.8 | 1605.8 | 1605.8 | 1605.8 | 1605.8 | 1605.8 | 1605.8 |
| 2.5° | 1604.8 | 1602.6 | 1595.6 | 1590.2 | 1589.1 | 1585.9 | 1583.2 | 1584.8 | 1587.0 | 1587.5 | 1587.5 |
| 5° | 1604.2 | 1598.3 | 1589.1 | 1585.3 | 1590.2 | 1596.7 | 1604.8 | 1615.5 | 1622.0 | 1626.9 | 1630.1 |
| 7.5° | 1630.1 | 1618.8 | 1608.5 | 1606.4 | 1616.1 | 1633.3 | 1651.7 | 1674.3 | 1690.0 | 1700.8 | 1702.9 |
| 10° | 1673.3 | 1659.2 | 1649.0 | 1651.2 | 1668.4 | 1693.2 | 1719.1 | 1748.2 | 1772.0 | 1786.5 | 1787.6 |
| 12.5° | 1722.9 | 1709.4 | 1699.7 | 1708.9 | 1737.5 | 1767.7 | 1794.6 | 1820.0 | 1841.6 | 1856.1 | 1856.1 |
| 15° | 1780.1 | 1770.4 | 1759.0 | 1780.1 | 1818.9 | 1845.9 | 1857.2 | 1869.6 | 1881.5 | 1892.3 | 1890.1 |
| 17.5° | 1835.1 | 1825.9 | 1820.0 | 1844.8 | 1885.3 | 1897.7 | 1890.1 | 1880.9 | 1880.9 | 1886.9 | 1888.0 |
| 20° | 1882.6 | 1874.5 | 1878.2 | 1902.5 | 1923.6 | 1910.6 | 1882.6 | 1853.4 | 1841.6 | 1844.8 | 1848.0 |
| 22.5° | 1924.1 | 1920.3 | 1931.6 | 1943.0 | 1927.9 | 1882.6 | 1830.8 | 1791.4 | 1776.8 | 1775.8 | 1776.8 |
| 25° | 1972.6 | 1972.1 | 1986.1 | 1965.6 | 1898.7 | 1815.1 | 1745.5 | 1707.2 | 1699.2 | 1705.6 | 1716.4 |
| 27.5° | 2033.1 | 2039.0 | 2046.0 | 1971.0 | 1839.4 | 1713.2 | 1642.5 | 1616.1 | 1624.2 | 1639.8 | 1650.1 |
| 30° | 2110.2 | 2126.4 | 2111.3 | 1957.5 | 1754.2 | 1596.7 | 1529.2 | 1521.7 | 1543.8 | 1565.9 | 1576.7 |
| 32.5° | 2185.2 | 2210.5 | 2173.8 | 1922.5 | 1644.1 | 1473.1 | 1420.8 | 1418.7 | 1445.6 | 1467.2 | 1482.3 |
| 35° | 2245.6 | 2295.8 | 2220.8 | 1852.9 | 1516.8 | 1359.3 | 1321.0 | 1306.5 | 1316.2 | 1341.5 | 1358.8 |
| 37.5° | 2324.3 | 2407.9 | 2253.1 | 1746.6 | 1378.7 | 1265.5 | 1220.7 | 1187.3 | 1178.6 | 1188.9 | 1197.5 |
| 40° | 2468.4 | 2578.9 | 2268.2 | 1598.3 | 1243.9 | 1171.6 | 1126.3 | 1077.2 | 1043.2 | 1018.4 | 1019.0 |
| 42.5° | 2703.5 | 2801.7 | 2258.5 | 1418.1 | 1119.3 | 1079.9 | 1028.7 | 972.0 | 917.0 | 860.9 | 856.6 |
| 45° | 3085.5 | 3132.9 | 2229.4 | 1227.2 | 1009.8 | 983.9 | 935.9 | 879.2 | 805.9 | 742.2 | 736.3 |
| 47.5° | 3696.6 | 3591.4 | 2184.1 | 1060.5 | 913.2 | 902.4 | 858.2 | 792.9 | 715.3 | 664.0 | 659.7 |
| 50° | 4530.0 | 4253.3 | 2162.0 | 927.8 | 828.0 | 831.2 | 795.1 | 726.1 | 652.7 | 614.9 | 610.6 |
| 52.5° | 5526.8 | 5024.1 | 2204.6 | 825.3 | 759.5 | 770.8 | 743.9 | 679.1 | 617.6 | 588.0 | 583.6 |
| 55° | 6560.9 | 5822.4 | 2250.4 | 750.9 | 694.8 | 716.9 | 707.7 | 654.3 | 598.8 | 571.2 | 567.5 |
| 57.5° | 7446.1 | 6418.5 | 2158.7 | 690.5 | 637.0 | 671.6 | 679.7 | 638.7 | 589.0 | 564.2 | 559.9 |
| 60° | 8003.3 | 6658.5 | 1918.2 | 633.8 | 591.2 | 635.4 | 663.5 | 634.4 | 592.8 | 590.7 | 587.4 |
| 62.5° | 8267.6 | 6637.5 | 1557.3 | 589.0 | 562.6 | 619.8 | 675.3 | 658.6 | 636.0 | 655.4 | 657.0 |
| 65° | 8148.9 | 6320.3 | 1159.7 | 559.4 | 542.1 | 625.7 | 710.9 | 704.5 | 648.4 | 667.8 | 670.5 |
| 67.5° | 7367.9 | 5563.5 | 858.7 | 533.5 | 519.5 | 642.4 | 775.7 | 719.6 | 624.1 | 638.1 | 629.5 |
| 70° | 5955.1 | 4410.8 | 662.4 | 504.4 | 496.3 | 640.3 | 804.8 | 710.4 | 597.7 | 600.9 | 577.7 |
| 72.5° | 4106.6 | 3007.8 | 538.9 | 477.4 | 462.8 | 583.6 | 784.3 | 687.8 | 575.6 | 550.7 | 520.0 |
| 75° | 2233.2 | 1614.5 | 458.0 | 449.3 | 404.0 | 512.4 | 746.6 | 671.6 | 555.6 | 522.7 | 505.4 |
| 77.5° | 878.7 | 670.0 | 397.5 | 411.0 | 353.3 | 452.6 | 704.5 | 640.8 | 528.1 | 484.9 | 476.3 |
| 80° | 358.7 | 342.0 | 329.6 | 355.5 | 303.7 | 395.9 | 653.8 | 604.7 | 495.2 | 449.9 | 432.6 |
| 82.5° | 203.4 | 212.5 | 256.2 | 280.5 | 246.5 | 364.6 | 629.5 | 575.6 | 455.8 | 402.9 | 382.4 |
| 85° | 104.1 | 124.6 | 178.5 | 201.2 | 181.2 | 310.2 | 579.9 | 503.8 | 365.7 | 308.5 | 310.2 |
| 87.5° | 50.2 | 69.6 | 112.7 | 126.2 | 117.6 | 224.4 | 433.2 | 365.2 | 284.8 | 225.5 | 218.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_g = -1.5$



Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)