

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P316617

Luminaire Tested: **GLEON-SA3D-827-U-5MQ**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P316617  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-6)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: GLEON-SA3D-827-U-5MQ  
Description: GALLEON AREA AND ROADWAY LUMINAIRE  
(3) 80 CRI, 2700K, 1200mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE V  
MEDIUM OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 18293 lumens  
Efficiency: N/A  
Efficacy: 95.8 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B4 - U0 - G2


Input Watts (W): 191  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P316617  
 CATALOG NUMBER: GLEON-SA3D-827-U-5MQ

## Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 3.2 fc  
 Type V - Short - N/A

REPORT NUMBER: P316617  
CATALOG NUMBER: GLEON-SA3D-827-U-5MQ

## Luminous Intensity Polar Plot



REPORT NUMBER: P316617

CATALOG NUMBER: GLEON-SA3D-827-U-5MQ

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 9146.5   | 0.0    | 9146.5  |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Street Side</b> | Lumens    | 9146.5   | 0.0    | 9146.5  |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Total</b>       | Lumens    | 18293.0  | 0.0    | 18293.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 189.2   | 1.0       |
| 10°-20°   | 555.5   | 3.0       |
| 20°-30°   | 945.6   | 5.2       |
| 30°-40°   | 1499.8  | 8.2       |
| 40°-50°   | 2440.6  | 13.3      |
| 50°-60°   | 4024.1  | 22.0      |
| 60°-70°   | 5907.5  | 32.3      |
| 70°-80°   | 2612.3  | 14.3      |
| 80°-90°   | 118.3   | 0.6       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 18293.0 | 100.0     |
| 0°-180°   | 18293.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P316617


CATALOG NUMBER: GLEON-SA3D-827-U-5MQ

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 845.2  | 4.6       |                         |      |         |
| FM   | (30°-60°)   | 3982.3 | 21.8      |                         |      |         |
| FH   | (60°-80°)   | 4259.9 | 23.3      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 59.2   | 0.3       |                         |      | G1/100  |
| BL   | (0°-30°)    | 845.2  | 4.6       | B2/1000                 |      |         |
| BM   | (30°-60°)   | 3982.3 | 21.8      | B3/5000                 |      |         |
| BH   | (60°-80°)   | 4259.9 | 23.3      | B4/5000                 |      | G2/5000 |
| BVH  | (80°-90°)   | 59.2   | 0.3       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B4-U0-G2**

Type V Short





REPORT NUMBER: P316617

CATALOG NUMBER: GLEON-SA3D-827-U-5MQ

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1997.9 | 1997.9 | 1997.9 | 1997.9 | 1997.9 | 1997.9 | 1997.9 | 1997.9 | 1997.9 | 1997.9 | 1997.9 |
| 2.5°  | 1994.9 | 1993.0 | 1997.3 | 1996.7 | 1993.0 | 1993.6 | 1993.6 | 1995.5 | 1995.5 | 1994.2 | 1994.2 |
| 5°    | 1987.6 | 1986.4 | 1991.2 | 1991.2 | 1987.6 | 1988.8 | 1990.0 | 1991.8 | 1991.2 | 1990.0 | 1989.4 |
| 7.5°  | 1978.5 | 1977.9 | 1982.7 | 1982.7 | 1980.3 | 1981.5 | 1980.3 | 1980.9 | 1979.7 | 1978.5 | 1976.7 |
| 10°   | 1963.4 | 1964.6 | 1968.8 | 1970.0 | 1970.0 | 1970.6 | 1969.4 | 1966.4 | 1964.6 | 1962.8 | 1960.9 |
| 12.5° | 1949.4 | 1948.8 | 1954.9 | 1957.9 | 1962.8 | 1968.2 | 1964.6 | 1956.1 | 1952.5 | 1948.8 | 1947.6 |
| 15°   | 1940.4 | 1941.0 | 1947.0 | 1952.5 | 1960.9 | 1972.5 | 1968.2 | 1954.9 | 1947.6 | 1943.4 | 1942.2 |
| 17.5° | 1938.5 | 1939.8 | 1947.6 | 1957.3 | 1966.4 | 1979.1 | 1976.7 | 1963.4 | 1951.3 | 1943.4 | 1941.6 |
| 20°   | 1942.8 | 1943.4 | 1955.5 | 1969.4 | 1985.2 | 1997.3 | 1991.8 | 1977.3 | 1960.9 | 1948.8 | 1945.8 |
| 22.5° | 1950.7 | 1953.1 | 1968.2 | 1990.0 | 2014.2 | 2030.6 | 2023.9 | 1999.1 | 1973.7 | 1958.5 | 1954.3 |
| 25°   | 1975.5 | 1976.1 | 1996.7 | 2026.3 | 2055.4 | 2074.2 | 2066.3 | 2031.2 | 1998.5 | 1981.5 | 1976.1 |
| 27.5° | 2026.9 | 2028.8 | 2049.3 | 2083.8 | 2108.7 | 2120.8 | 2115.9 | 2087.5 | 2059.6 | 2041.5 | 2043.3 |
| 30°   | 2101.4 | 2103.8 | 2126.8 | 2165.0 | 2180.1 | 2183.1 | 2181.9 | 2168.6 | 2143.2 | 2119.0 | 2120.8 |
| 32.5° | 2192.2 | 2193.4 | 2224.3 | 2258.8 | 2270.9 | 2273.3 | 2270.9 | 2258.8 | 2228.5 | 2195.9 | 2197.7 |
| 35°   | 2309.1 | 2312.7 | 2342.4 | 2375.7 | 2385.3 | 2390.2 | 2386.0 | 2370.2 | 2338.7 | 2306.6 | 2305.4 |
| 37.5° | 2453.2 | 2453.8 | 2484.6 | 2519.1 | 2531.3 | 2532.5 | 2527.6 | 2517.3 | 2478.0 | 2448.9 | 2447.1 |
| 40°   | 2620.3 | 2622.7 | 2659.0 | 2695.9 | 2700.8 | 2695.3 | 2702.0 | 2695.9 | 2655.4 | 2622.1 | 2627.5 |
| 42.5° | 2823.7 | 2829.1 | 2872.7 | 2909.0 | 2895.1 | 2892.1 | 2896.3 | 2898.1 | 2865.4 | 2824.9 | 2821.2 |
| 45°   | 3060.4 | 3065.2 | 3119.7 | 3148.8 | 3139.7 | 3119.7 | 3128.2 | 3142.7 | 3097.3 | 3047.1 | 3051.9 |
| 47.5° | 3330.4 | 3342.5 | 3400.6 | 3427.9 | 3405.5 | 3378.2 | 3394.6 | 3416.4 | 3363.1 | 3300.7 | 3297.7 |
| 50°   | 3630.7 | 3645.8 | 3723.3 | 3761.5 | 3739.1 | 3688.8 | 3716.1 | 3730.6 | 3653.7 | 3573.2 | 3566.5 |
| 52.5° | 3951.0 | 3966.1 | 4063.6 | 4142.3 | 4127.7 | 4049.6 | 4087.8 | 4072.6 | 3984.3 | 3875.9 | 3867.4 |
| 55°   | 4313.6 | 4319.7 | 4425.0 | 4552.1 | 4566.7 | 4509.2 | 4506.7 | 4481.9 | 4351.1 | 4225.8 | 4219.8 |
| 57.5° | 4686.5 | 4690.8 | 4827.0 | 4977.1 | 5045.6 | 5045.6 | 4977.7 | 4925.1 | 4751.3 | 4606.0 | 4590.9 |
| 60°   | 5089.1 | 5104.3 | 5255.0 | 5459.1 | 5618.9 | 5666.1 | 5546.2 | 5402.8 | 5213.9 | 5036.5 | 5018.9 |
| 62.5° | 5447.6 | 5465.1 | 5695.8 | 5999.7 | 6256.4 | 6428.3 | 6135.3 | 5901.6 | 5557.7 | 5273.2 | 5239.9 |
| 65°   | 5493.0 | 5540.2 | 5876.2 | 6426.5 | 7001.1 | 7344.3 | 6782.5 | 6206.7 | 5580.1 | 5184.8 | 5150.9 |
| 67.5° | 5016.5 | 5096.4 | 5550.5 | 6407.1 | 7594.4 | 8331.2 | 7196.0 | 6032.4 | 5178.1 | 4741.0 | 4703.5 |
| 70°   | 3854.7 | 3970.9 | 4494.6 | 5604.4 | 7492.1 | 8649.0 | 6936.9 | 5281.1 | 4317.2 | 3846.8 | 3794.2 |
| 72.5° | 2114.7 | 2162.6 | 2633.6 | 3837.7 | 6006.4 | 7349.8 | 5786.0 | 3904.9 | 2863.0 | 2329.6 | 2241.3 |
| 75°   | 670.8  | 687.8  | 927.5  | 1570.5 | 3397.6 | 4868.2 | 3675.5 | 1916.8 | 1055.2 | 778.0  | 768.9  |
| 77.5° | 297.9  | 299.7  | 335.4  | 458.3  | 1170.3 | 2466.5 | 1405.8 | 521.9  | 359.6  | 314.2  | 324.5  |
| 80°   | 188.3  | 188.3  | 207.7  | 227.0  | 318.5  | 716.2  | 380.2  | 248.2  | 211.9  | 196.8  | 201.0  |
| 82.5° | 90.2   | 99.9   | 135.0  | 145.3  | 175.0  | 241.0  | 194.9  | 162.3  | 141.7  | 105.3  | 98.1   |
| 85°   | 59.3   | 49.6   | 85.4   | 96.3   | 101.7  | 115.6  | 113.2  | 107.2  | 92.6   | 52.7   | 58.7   |
| 87.5° | 26.6   | 25.4   | 44.2   | 40.6   | 38.1   | 29.1   | 43.6   | 53.9   | 52.1   | 26.0   | 26.0   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-157-9  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/03/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Invue  
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**  
 Description: Epic Modern Light Square 40W 5WQ Optic

### Spectral Parameters

CCT (K): 2764  
 CIE  $u'$ : 0.2591  
 CIE  $v'$ : 0.5290  
 Duv: 0.0020  
 CIE x: 0.4581  
 CIE y: 0.4156  
 CIE z: 0.1263  
 Peak Wavelength (nm): 603  
 Dominant Wavelength (nm): 583  
 Purity: 62.2537  
 R<sub>f</sub>: 84.7  
 R<sub>g</sub>: 94.6

CRI (Ra): 80.9  
 R1: 78.8  
 R2: 89.9  
 R3: 96.2  
 R4: 79.1  
 R5: 79.1  
 R6: 88.8  
 R7: 81.3  
 R8: 54.3  
 R9: -1.5  
 R10: 77.9  
 R11: 78.9  
 R12: 71.6  
 R13: 81.2  
 R14: 98.5  
 R15: 69.9



### Test Conditions

Stabilization Time: 81M  
 Operation Time: 2H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-157-9

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



REPORT NUMBER: SP1-2407-157-9

### Photopic Flux vs. Wavelength


**Photopic Lumens: 4337.9**

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 0                | 0.0              | 490       | 18018            | 2.6              | 620       | 87426            | 22.8             | 750       | 2680             | 0.0              | 880       | 58               | 0.0              |
| 365       | 0                | 0.0              | 495       | 22295            | 3.9              | 625       | 83013            | 18.2             | 755       | 2287             | 0.0              | 885       | 46               | 0.0              |
| 370       | 0                | 0.0              | 500       | 26478            | 5.8              | 630       | 78077            | 14.1             | 760       | 1944             | 0.0              | 890       | 45               | 0.0              |
| 375       | 0                | 0.0              | 505       | 30524            | 8.5              | 635       | 72080            | 10.7             | 765       | 1653             | 0.0              | 895       | 41               | 0.0              |
| 380       | 0                | 0.0              | 510       | 33611            | 11.5             | 640       | 66249            | 7.9              | 770       | 1413             | 0.0              | 900       | 38               | 0.0              |
| 385       | 0                | 0.0              | 515       | 36490            | 15.2             | 645       | 59973            | 5.7              | 775       | 1198             | 0.0              | 905       | 33               | 0.0              |
| 390       | 0                | 0.0              | 520       | 38610            | 18.7             | 650       | 53972            | 3.9              | 780       | 1025             | 0.0              | 910       | 30               | 0.0              |
| 395       | 0                | 0.0              | 525       | 40511            | 21.9             | 655       | 48369            | 2.7              | 785       | 874              | 0.0              | 915       | 23               | 0.0              |
| 400       | 48               | 0.0              | 530       | 42223            | 24.9             | 660       | 42641            | 1.8              | 790       | 747              | 0.0              | 920       | 24               | 0.0              |
| 405       | 201              | 0.0              | 535       | 44137            | 27.6             | 665       | 37602            | 1.1              | 795       | 639              | 0.0              | 925       | 22               | 0.0              |
| 410       | 457              | 0.0              | 540       | 46032            | 30.0             | 670       | 32798            | 0.7              | 800       | 547              | 0.0              | 930       | 22               | 0.0              |
| 415       | 925              | 0.0              | 545       | 48553            | 32.5             | 675       | 28558            | 0.5              | 805       | 473              | 0.0              | 935       | 17               | 0.0              |
| 420       | 1816             | 0.0              | 550       | 51408            | 34.9             | 680       | 24782            | 0.3              | 810       | 401              | 0.0              | 940       | 13               | 0.0              |
| 425       | 3217             | 0.0              | 555       | 54711            | 37.4             | 685       | 21386            | 0.2              | 815       | 351              | 0.0              | 945       | 6                | 0.0              |
| 430       | 5520             | 0.0              | 560       | 58847            | 40.0             | 690       | 18413            | 0.1              | 820       | 307              | 0.0              | 950       | 10               | 0.0              |
| 435       | 9225             | 0.1              | 565       | 63386            | 42.4             | 695       | 15721            | 0.1              | 825       | 261              | 0.0              | 955       | 11               | 0.0              |
| 440       | 15522            | 0.2              | 570       | 68196            | 44.3             | 700       | 13432            | 0.0              | 830       | 228              | 0.0              | 960       | 8                | 0.0              |
| 445       | 27642            | 0.6              | 575       | 73613            | 46.0             | 705       | 11513            | 0.0              | 835       | 193              | 0.0              | 965       | 12               | 0.0              |
| 450       | 36602            | 0.9              | 580       | 79207            | 47.1             | 710       | 9780             | 0.0              | 840       | 174              | 0.0              | 970       | 3                | 0.0              |
| 455       | 28292            | 0.9              | 585       | 84248            | 47.0             | 715       | 8356             | 0.0              | 845       | 151              | 0.0              | 975       | 8                | 0.0              |
| 460       | 21166            | 0.9              | 590       | 88397            | 45.7             | 720       | 7161             | 0.0              | 850       | 123              | 0.0              | 980       | 2                | 0.0              |
| 465       | 19092            | 1.0              | 595       | 91428            | 43.4             | 725       | 6067             | 0.0              | 855       | 106              | 0.0              | 985       | 13               | 0.0              |
| 470       | 14951            | 0.9              | 600       | 93452            | 40.3             | 730       | 5164             | 0.0              | 860       | 95               | 0.0              | 990       | 16               | 0.0              |
| 475       | 12606            | 1.0              | 605       | 93959            | 36.4             | 735       | 4393             | 0.0              | 865       | 82               | 0.0              | 995       | 20               | 0.0              |
| 480       | 13323            | 1.3              | 610       | 93079            | 32.0             | 740       | 3694             | 0.0              | 870       | 77               | 0.0              | 1000      | 0                | 0.0              |
| 485       | 15164            | 1.8              | 615       | 90707            | 27.3             | 745       | 3157             | 0.0              | 875       | 65               | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2407-157-9

### Scotopic Flux vs. Wavelength


**Scotopic Lumens: 5286.7**
**S/P: 1.22**

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | 0.0                            | 490               | 18018                                | 75.9                           | 620               | 87426                                | 0.4                            | 750               | 2680                                 | 0.0                            | 880               | 58                                   | 0.0                            |
| 365               | 0                                    | 0.0                            | 495               | 22295                                | 93.2                           | 625               | 83013                                | 0.2                            | 755               | 2287                                 | 0.0                            | 885               | 46                                   | 0.0                            |
| 370               | 0                                    | 0.0                            | 500               | 26478                                | 107.8                          | 630               | 78077                                | 0.1                            | 760               | 1944                                 | 0.0                            | 890               | 45                                   | 0.0                            |
| 375               | 0                                    | 0.0                            | 505               | 30524                                | 118.7                          | 635               | 72080                                | 0.1                            | 765               | 1653                                 | 0.0                            | 895               | 41                                   | 0.0                            |
| 380               | 0                                    | 0.0                            | 510               | 33611                                | 122.2                          | 640               | 66249                                | 0.1                            | 770               | 1413                                 | 0.0                            | 900               | 38                                   | 0.0                            |
| 385               | 0                                    | 0.0                            | 515               | 36490                                | 120.8                          | 645               | 59973                                | 0.0                            | 775               | 1198                                 | 0.0                            | 905               | 33                                   | 0.0                            |
| 390               | 0                                    | 0.0                            | 520               | 38610                                | 113.9                          | 650               | 53972                                | 0.0                            | 780               | 1025                                 | 0.0                            | 910               | 30                                   | 0.0                            |
| 395               | 0                                    | 0.0                            | 525               | 40511                                | 104.1                          | 655               | 48369                                | 0.0                            | 785               | 874                                  | 0.0                            | 915               | 23                                   | 0.0                            |
| 400               | 48                                   | 0.0                            | 530               | 42223                                | 92.4                           | 660               | 42641                                | 0.0                            | 790               | 747                                  | 0.0                            | 920               | 24                                   | 0.0                            |
| 405               | 201                                  | 0.0                            | 535               | 44137                                | 80.5                           | 665               | 37602                                | 0.0                            | 795               | 639                                  | 0.0                            | 925               | 22                                   | 0.0                            |
| 410               | 457                                  | 0.1                            | 540               | 46032                                | 68.2                           | 670               | 32798                                | 0.0                            | 800               | 547                                  | 0.0                            | 930               | 22                                   | 0.0                            |
| 415               | 925                                  | 0.3                            | 545               | 48553                                | 57.1                           | 675               | 28558                                | 0.0                            | 805               | 473                                  | 0.0                            | 935               | 17                                   | 0.0                            |
| 420               | 1816                                 | 1.1                            | 550               | 51408                                | 46.7                           | 680               | 24782                                | 0.0                            | 810               | 401                                  | 0.0                            | 940               | 13                                   | 0.0                            |
| 425               | 3217                                 | 2.5                            | 555               | 54711                                | 37.4                           | 685               | 21386                                | 0.0                            | 815               | 351                                  | 0.0                            | 945               | 6                                    | 0.0                            |
| 430               | 5520                                 | 5.9                            | 560               | 58847                                | 29.4                           | 690               | 18413                                | 0.0                            | 820               | 307                                  | 0.0                            | 950               | 10                                   | 0.0                            |
| 435               | 9225                                 | 12.5                           | 565               | 63386                                | 22.5                           | 695               | 15721                                | 0.0                            | 825               | 261                                  | 0.0                            | 955               | 11                                   | 0.0                            |
| 440               | 15522                                | 26.3                           | 570               | 68196                                | 16.9                           | 700               | 13432                                | 0.0                            | 830               | 228                                  | 0.0                            | 960               | 8                                    | 0.0                            |
| 445               | 27642                                | 55.2                           | 575               | 73613                                | 12.4                           | 705               | 11513                                | 0.0                            | 835               | 193                                  | 0.0                            | 965               | 12                                   | 0.0                            |
| 450               | 36602                                | 85.4                           | 580               | 79207                                | 9.0                            | 710               | 9780                                 | 0.0                            | 840               | 174                                  | 0.0                            | 970               | 3                                    | 0.0                            |
| 455               | 28292                                | 75.1                           | 585               | 84248                                | 6.3                            | 715               | 8356                                 | 0.0                            | 845               | 151                                  | 0.0                            | 975               | 8                                    | 0.0                            |
| 460               | 21166                                | 63.2                           | 590               | 88397                                | 4.4                            | 720               | 7161                                 | 0.0                            | 850               | 123                                  | 0.0                            | 980               | 2                                    | 0.0                            |
| 465               | 19092                                | 63.2                           | 595               | 91428                                | 3.0                            | 725               | 6067                                 | 0.0                            | 855               | 106                                  | 0.0                            | 985               | 13                                   | 0.0                            |
| 470               | 14951                                | 54.2                           | 600               | 93452                                | 2.0                            | 730               | 5164                                 | 0.0                            | 860               | 95                                   | 0.0                            | 990               | 16                                   | 0.0                            |
| 475               | 12606                                | 48.8                           | 605               | 93959                                | 1.3                            | 735               | 4393                                 | 0.0                            | 865               | 82                                   | 0.0                            | 995               | 20                                   | 0.0                            |
| 480               | 13323                                | 54.2                           | 610               | 93079                                | 0.9                            | 740               | 3694                                 | 0.0                            | 870               | 77                                   | 0.0                            | 1000              | 0                                    | 0.0                            |
| 485               | 15164                                | 63.3                           | 615               | 90707                                | 0.5                            | 745               | 3157                                 | 0.0                            | 875               | 65                                   | 0.0                            |                   |                                      |                                |

REPORT NUMBER: SP1-2407-157-9

### Melanopic Flux vs. Wavelength



**Melanopic Lumens: 9797**

**M/P: 2.26**

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 0                | 0.0              | 490       | 18018            | 27.7             | 620       | 87426            | 1.1              | 750       | 2680             | 0.0              | 880       | 58               | 0.0              |
| 365       | 0                | 0.0              | 495       | 22295            | 36.0             | 625       | 83013            | 0.7              | 755       | 2287             | 0.0              | 885       | 46               | 0.0              |
| 370       | 0                | 0.0              | 500       | 26478            | 44.2             | 630       | 78077            | 0.4              | 760       | 1944             | 0.0              | 890       | 45               | 0.0              |
| 375       | 0                | 0.0              | 505       | 30524            | 51.8             | 635       | 72080            | 0.3              | 765       | 1653             | 0.0              | 895       | 41               | 0.0              |
| 380       | 0                | 0.0              | 510       | 33611            | 57.0             | 640       | 66249            | 0.2              | 770       | 1413             | 0.0              | 900       | 38               | 0.0              |
| 385       | 0                | 0.0              | 515       | 36490            | 60.5             | 645       | 59973            | 0.1              | 775       | 1198             | 0.0              | 905       | 33               | 0.0              |
| 390       | 0                | 0.0              | 520       | 38610            | 61.4             | 650       | 53972            | 0.1              | 780       | 1025             | 0.0              | 910       | 30               | 0.0              |
| 395       | 0                | 0.0              | 525       | 40511            | 60.6             | 655       | 48369            | 0.0              | 785       | 874              | 0.0              | 915       | 23               | 0.0              |
| 400       | 48               | 0.0              | 530       | 42223            | 58.2             | 660       | 42641            | 0.0              | 790       | 747              | 0.0              | 920       | 24               | 0.0              |
| 405       | 201              | 0.0              | 535       | 44137            | 55.0             | 665       | 37602            | 0.0              | 795       | 639              | 0.0              | 925       | 22               | 0.0              |
| 410       | 457              | 0.0              | 540       | 46032            | 50.9             | 670       | 32798            | 0.0              | 800       | 547              | 0.0              | 930       | 22               | 0.0              |
| 415       | 925              | 0.1              | 545       | 48553            | 46.6             | 675       | 28558            | 0.0              | 805       | 473              | 0.0              | 935       | 17               | 0.0              |
| 420       | 1816             | 0.3              | 550       | 51408            | 42.0             | 680       | 24782            | 0.0              | 810       | 401              | 0.0              | 940       | 13               | 0.0              |
| 425       | 3217             | 0.8              | 555       | 54711            | 37.4             | 685       | 21386            | 0.0              | 815       | 351              | 0.0              | 945       | 6                | 0.0              |
| 430       | 5520             | 1.9              | 560       | 58847            | 32.9             | 690       | 18413            | 0.0              | 820       | 307              | 0.0              | 950       | 10               | 0.0              |
| 435       | 9225             | 4.1              | 565       | 63386            | 28.4             | 695       | 15721            | 0.0              | 825       | 261              | 0.0              | 955       | 11               | 0.0              |
| 440       | 15522            | 8.7              | 570       | 68196            | 24.1             | 700       | 13432            | 0.0              | 830       | 228              | 0.0              | 960       | 8                | 0.0              |
| 445       | 27642            | 18.5             | 575       | 73613            | 20.0             | 705       | 11513            | 0.0              | 835       | 193              | 0.0              | 965       | 12               | 0.0              |
| 450       | 36602            | 28.3             | 580       | 79207            | 16.3             | 710       | 9780             | 0.0              | 840       | 174              | 0.0              | 970       | 3                | 0.0              |
| 455       | 28292            | 24.7             | 585       | 84248            | 12.9             | 715       | 8356             | 0.0              | 845       | 151              | 0.0              | 975       | 8                | 0.0              |
| 460       | 21166            | 20.4             | 590       | 88397            | 9.8              | 720       | 7161             | 0.0              | 850       | 123              | 0.0              | 980       | 2                | 0.0              |
| 465       | 19092            | 20.1             | 595       | 91428            | 7.3              | 725       | 6067             | 0.0              | 855       | 106              | 0.0              | 985       | 13               | 0.0              |
| 470       | 14951            | 17.2             | 600       | 93452            | 5.3              | 730       | 5164             | 0.0              | 860       | 95               | 0.0              | 990       | 16               | 0.0              |
| 475       | 12606            | 15.7             | 605       | 93959            | 3.7              | 735       | 4393             | 0.0              | 865       | 82               | 0.0              | 995       | 20               | 0.0              |
| 480       | 13323            | 18.0             | 610       | 93079            | 2.5              | 740       | 3694             | 0.0              | 870       | 77               | 0.0              | 1000      | 0                | 0.0              |
| 485       | 15164            | 21.9             | 615       | 90707            | 1.7              | 745       | 3157             | 0.0              | 875       | 65               | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2407-157-9



TM-30-18

### Summary

$R_f = 84.7$   
 $R_g = 94.6$   
 $CIE R_a = 80.9$   
 $R_g = -1.5$



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)