

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P320457

Luminaire Tested: **GLEON-SA3D-827-U-SLL**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P320457  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-26)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: GLEON-SA3D-827-U-SLL  
Description: GALLEON AREA AND ROADWAY LUMINAIRE  
(3) 80 CRI, 2700K, 1200mA LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT  
ELIMINATOR LEFT OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 15303 lumens  
Efficiency: N/A  
Efficacy: 80.1 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type III - Medium  
BUG Rating: B2 - U0 - G4


Input Watts (W): 191  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P320457  
 CATALOG NUMBER: GLEON-SA3D-827-U-SLL

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 9.4 fc  
 Type III - Medium - N/A

REPORT NUMBER: P320457  
CATALOG NUMBER: GLEON-SA3D-827-U-SLL

### Luminous Intensity Polar Plot



— Vertical Plane Through 75-Deg Lateral      - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P320457  
 CATALOG NUMBER: GLEON-SA3D-827-U-SLL


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 2695.2   | 0.0    | 2695.2  |
|                    | % Fixture | 17.6     | 0.0    | 17.6    |
| <b>Street Side</b> | Lumens    | 12607.8  | 0.0    | 12607.8 |
|                    | % Fixture | 82.4     | 0.0    | 82.4    |
| <b>Total</b>       | Lumens    | 15303.0  | 0.0    | 15303.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 359.8   | 2.4       |
| 10°-20°   | 747.5   | 4.9       |
| 20°-30°   | 1063.1  | 6.9       |
| 30°-40°   | 1531.9  | 10.0      |
| 40°-50°   | 2158.9  | 14.1      |
| 50°-60°   | 3001.2  | 19.6      |
| 60°-70°   | 3629.3  | 23.7      |
| 70°-80°   | 2230.9  | 14.6      |
| 80°-90°   | 580.5   | 3.8       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 15303.0 | 100.0     |
| 0°-180°   | 15303.0 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P320457  
 CATALOG NUMBER: GLEON-SA3D-827-U-SLL

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 1519.4 | 9.9       |                         |      |         |
| FM (30°-60°)   | 5468.5 | 35.7      |                         |      |         |
| FH (60°-80°)   | 5104.6 | 33.4      |                         |      | G3/7500 |
| FVH (80°-90°)  | 515.3  | 3.4       |                         |      | G4/750  |
| BL (0°-30°)    | 650.9  | 4.3       | B2/1000                 |      |         |
| BM (30°-60°)   | 1223.4 | 8.0       | B2/2500                 |      |         |
| BH (60°-80°)   | 755.6  | 4.9       | B2/1000                 |      | G2/1000 |
| BVH (80°-90°)  | 65.2   | 0.4       |                         |      | G1/100  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B2-U0-G4**  
 Type III Medium





REPORT NUMBER: P320457

CATALOG NUMBER: GLEON-SA3D-827-U-SLL

**CANDELA DISTRIBUTION (FULL):**

|        | 0°      | 5°      | 10°     | 15°     | 20°     | 25°     | 30°     | 35°     | 40°     | 45°     | 50°     |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°     | 4662.1  | 4662.1  | 4662.1  | 4662.1  | 4662.1  | 4662.1  | 4662.1  | 4662.1  | 4662.1  | 4662.1  | 4662.1  |
| 2.5°   | 4969.3  | 5034.7  | 5080.0  | 5124.7  | 5159.5  | 5193.8  | 5244.0  | 5294.1  | 5303.9  | 5313.1  | 5293.5  |
| 5°     | 4939.9  | 5099.6  | 5235.4  | 5370.6  | 5496.1  | 5621.5  | 5696.7  | 5772.0  | 5787.3  | 5802.6  | 5755.5  |
| 7.5°   | 4623.6  | 4859.1  | 5094.7  | 5330.2  | 5546.2  | 5762.2  | 5893.7  | 6024.7  | 6054.7  | 6084.0  | 6006.9  |
| 10°    | 4263.8  | 4537.9  | 4827.3  | 5116.7  | 5401.2  | 5685.7  | 5876.0  | 6066.3  | 6104.2  | 6142.1  | 6046.1  |
| 12.5°  | 3990.3  | 4289.5  | 4598.5  | 4907.5  | 5207.9  | 5507.7  | 5704.7  | 5901.7  | 5948.8  | 5995.9  | 5926.2  |
| 15°    | 3885.1  | 4213.0  | 4503.7  | 4794.3  | 5056.1  | 5317.4  | 5478.9  | 5639.8  | 5659.4  | 5678.4  | 5667.4  |
| 17.5°  | 3990.3  | 4351.9  | 4615.0  | 4877.5  | 5020.1  | 5162.0  | 5226.8  | 5291.1  | 5312.5  | 5333.3  | 5361.5  |
| 20°    | 4298.1  | 4688.4  | 4873.8  | 5058.6  | 5052.5  | 5045.7  | 5014.5  | 4982.7  | 4977.2  | 4971.7  | 5051.3  |
| 22.5°  | 4737.4  | 5190.8  | 5264.8  | 5338.2  | 5166.3  | 4994.4  | 4889.7  | 4784.5  | 4763.7  | 4742.3  | 4826.7  |
| 25°    | 5253.2  | 5735.9  | 5722.4  | 5708.4  | 5381.0  | 5053.1  | 4853.6  | 4654.2  | 4630.9  | 4607.7  | 4679.9  |
| 27.5°  | 5814.2  | 6275.5  | 6187.4  | 6099.3  | 5654.5  | 5209.7  | 4920.3  | 4630.9  | 4607.7  | 4584.4  | 4648.1  |
| 30°    | 6252.9  | 6671.4  | 6530.0  | 6388.7  | 5885.2  | 5381.6  | 5037.8  | 4693.9  | 4656.0  | 4617.5  | 4695.8  |
| 32.5°  | 6624.3  | 6980.3  | 6790.7  | 6601.0  | 6072.4  | 5543.8  | 5171.8  | 4799.8  | 4740.4  | 4681.1  | 4785.7  |
| 35°    | 7010.9  | 7288.7  | 7022.0  | 6754.6  | 6239.4  | 5723.7  | 5330.2  | 4936.2  | 4863.4  | 4790.6  | 4934.4  |
| 37.5°  | 7445.9  | 7676.6  | 7293.6  | 6910.0  | 6427.3  | 5944.5  | 5567.6  | 5190.1  | 5115.5  | 5040.9  | 5224.4  |
| 40°    | 7905.4  | 8097.5  | 7586.7  | 7075.8  | 6632.8  | 6189.9  | 5896.2  | 5601.9  | 5530.9  | 5459.3  | 5682.0  |
| 42.5°  | 8307.4  | 8447.5  | 7859.5  | 7271.6  | 6880.6  | 6489.0  | 6282.3  | 6074.8  | 6074.2  | 6073.0  | 6298.8  |
| 45°    | 8610.3  | 8732.0  | 8087.1  | 7441.7  | 7122.3  | 6802.3  | 6694.6  | 6586.9  | 6673.2  | 6759.5  | 6963.8  |
| 47.5°  | 8861.7  | 8944.3  | 8278.0  | 7611.1  | 7398.8  | 7186.5  | 7202.4  | 7218.3  | 7393.9  | 7569.5  | 7701.1  |
| 50°    | 9149.3  | 9082.6  | 8451.2  | 7819.2  | 7753.7  | 7688.2  | 7831.4  | 7974.0  | 8175.9  | 8377.2  | 8466.5  |
| 52.5°  | 9460.7  | 9283.9  | 8686.1  | 8087.8  | 8161.2  | 8234.6  | 8525.8  | 8817.1  | 9020.8  | 9224.5  | 9258.2  |
| 55°    | 10020.5 | 9749.5  | 9118.1  | 8486.1  | 8627.4  | 8768.1  | 9195.8  | 9622.8  | 9781.9  | 9941.0  | 9953.2  |
| 57.5°  | 10651.3 | 10410.9 | 9723.2  | 9035.5  | 9187.2  | 9338.9  | 9832.7  | 10325.8 | 10497.7 | 10669.1 | 10645.2 |
| 60°    | 10894.2 | 10905.8 | 10297.7 | 9688.9  | 9841.9  | 9994.8  | 10475.7 | 10956.6 | 11154.2 | 11351.2 | 11298.6 |
| 62.5°  | 10649.5 | 10936.4 | 10611.5 | 10286.1 | 10424.9 | 10563.2 | 11034.3 | 11505.4 | 11707.9 | 11910.5 | 11818.7 |
| 65°    | 10165.5 | 10450.0 | 10595.6 | 10741.3 | 10787.1 | 10833.0 | 11272.9 | 11712.2 | 11867.6 | 12022.4 | 11975.9 |
| 67.5°  | 9550.0  | 9780.1  | 10317.3 | 10853.8 | 10761.4 | 10669.1 | 10875.2 | 11081.4 | 11241.1 | 11400.8 | 11374.5 |
| 70°    | 8837.2  | 9111.3  | 9827.8  | 10544.2 | 10090.3 | 9635.7  | 9550.6  | 9465.6  | 9638.1  | 9810.1  | 9703.6  |
| 72.5°  | 7559.1  | 7972.7  | 8736.9  | 9500.5  | 8664.1  | 7827.7  | 7537.1  | 7246.5  | 7464.9  | 7683.3  | 7513.9  |
| 75°    | 5709.6  | 6258.4  | 7102.7  | 7946.4  | 6948.5  | 5950.6  | 5562.7  | 5174.8  | 5362.7  | 5550.5  | 5434.3  |
| 77.5°  | 3970.8  | 4659.1  | 5490.5  | 6322.0  | 5307.6  | 4292.6  | 4004.4  | 3715.6  | 3771.9  | 3827.6  | 3808.0  |
| 80°    | 2707.3  | 3160.1  | 3740.1  | 4319.5  | 3644.0  | 2968.6  | 2991.2  | 3013.3  | 2986.9  | 2960.0  | 2999.2  |
| 82.5°  | 1697.8  | 2016.6  | 2464.4  | 2911.7  | 2553.2  | 2194.6  | 2400.2  | 2605.8  | 2504.8  | 2403.3  | 2441.2  |
| 85°    | 956.3   | 1150.8  | 1588.9  | 2026.4  | 1888.7  | 1750.4  | 1871.0  | 1990.9  | 1834.3  | 1677.6  | 1746.8  |
| 87.5°  | 182.3   | 303.5   | 879.2   | 1454.3  | 1320.3  | 1186.3  | 1030.9  | 875.5   | 668.1   | 460.7   | 673.0   |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P320457  
 CATALOG NUMBER: GLEON-SA3D-827-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 0°  | 5°  | 10° | 15° | 20° | 25° | 30° | 35° | 40° | 45° | 50° |
|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |





REPORT NUMBER: P320457

CATALOG NUMBER: GLEON-SA3D-827-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 55°     | 60°     | 65°     | 70°     | 75°     | 80°     | 85°     | 90°     | 95°     | 100°   | 105°   |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|--------|--------|
| 0°     | 4662.1  | 4662.1  | 4662.1  | 4662.1  | 4662.1  | 4662.1  | 4662.1  | 4662.1  | 4662.1  | 4662.1 | 4662.1 |
| 2.5°   | 5274.0  | 5263.6  | 5253.2  | 5215.8  | 5177.9  | 5121.6  | 5075.1  | 4994.4  | 4950.3  | 4883.6 | 4816.9 |
| 5°     | 5707.7  | 5641.7  | 5575.6  | 5461.8  | 5347.4  | 5220.1  | 5073.9  | 4911.8  | 4789.4  | 4630.3 | 4471.2 |
| 7.5°   | 5929.8  | 5775.7  | 5620.9  | 5402.4  | 5183.4  | 4986.4  | 4755.1  | 4539.8  | 4356.2  | 4149.4 | 3942.6 |
| 10°    | 5950.0  | 5718.8  | 5486.9  | 5203.0  | 4918.5  | 4679.3  | 4413.1  | 4173.9  | 3953.6  | 3716.2 | 3478.2 |
| 12.5°  | 5855.8  | 5609.9  | 5363.3  | 5050.6  | 4737.4  | 4465.7  | 4179.4  | 3911.4  | 3667.3  | 3406.0 | 3144.2 |
| 15°    | 5656.4  | 5460.0  | 5262.9  | 4969.9  | 4676.8  | 4402.7  | 4124.9  | 3807.4  | 3531.5  | 3264.1 | 2996.1 |
| 17.5°  | 5389.0  | 5296.0  | 5202.4  | 4990.7  | 4778.4  | 4541.0  | 4271.8  | 3899.2  | 3576.1  | 3285.5 | 2994.9 |
| 20°    | 5130.2  | 5164.4  | 5198.1  | 5113.7  | 5029.2  | 4838.9  | 4604.0  | 4185.5  | 3773.1  | 3393.2 | 3012.6 |
| 22.5°  | 4910.5  | 5075.1  | 5239.1  | 5304.6  | 5369.4  | 5255.0  | 5071.4  | 4587.5  | 4041.7  | 3545.5 | 3049.4 |
| 25°    | 4751.5  | 5024.3  | 5297.2  | 5515.0  | 5732.2  | 5681.4  | 5540.1  | 5075.7  | 4397.8  | 3765.2 | 3131.9 |
| 27.5°  | 4711.7  | 5046.4  | 5381.0  | 5718.8  | 6055.9  | 6103.0  | 6063.8  | 5590.3  | 4822.4  | 4038.1 | 3253.1 |
| 30°    | 4774.1  | 5113.0  | 5451.4  | 5862.5  | 6273.1  | 6460.9  | 6513.5  | 6019.2  | 5307.6  | 4356.2 | 3404.2 |
| 32.5°  | 4890.3  | 5222.6  | 5554.8  | 6002.6  | 6449.9  | 6733.8  | 6901.4  | 6411.3  | 5646.0  | 4596.1 | 3545.5 |
| 35°    | 5078.2  | 5389.0  | 5699.8  | 6166.0  | 6632.2  | 6999.3  | 7305.2  | 6816.4  | 5946.4  | 4763.7 | 3580.4 |
| 37.5°  | 5407.3  | 5674.7  | 5942.1  | 6372.8  | 6802.9  | 7278.9  | 7738.4  | 7262.4  | 6271.2  | 4925.2 | 3578.6 |
| 40°    | 5904.8  | 6093.8  | 6282.3  | 6646.3  | 7009.7  | 7608.7  | 8229.1  | 7759.8  | 6630.4  | 5100.2 | 3570.0 |
| 42.5°  | 6524.5  | 6621.8  | 6718.5  | 7006.7  | 7294.8  | 7953.2  | 8674.5  | 8246.2  | 6973.0  | 5262.9 | 3552.9 |
| 45°    | 7167.6  | 7193.3  | 7219.0  | 7400.7  | 7581.8  | 8226.0  | 8978.0  | 8611.5  | 7272.2  | 5404.3 | 3535.8 |
| 47.5°  | 7832.0  | 7743.9  | 7655.8  | 7728.0  | 7800.2  | 8435.3  | 9194.6  | 8888.6  | 7572.6  | 5560.9 | 3548.6 |
| 50°    | 8555.8  | 8310.5  | 8065.1  | 8027.2  | 7989.3  | 8644.5  | 9449.7  | 9241.1  | 7933.6  | 5789.1 | 3644.7 |
| 52.5°  | 9291.2  | 8886.8  | 8482.4  | 8332.5  | 8182.0  | 8894.1  | 9788.0  | 9679.7  | 8448.7  | 6142.8 | 3836.2 |
| 55°    | 9965.5  | 9450.9  | 8936.4  | 8734.5  | 8532.6  | 9275.9  | 10201.0 | 10324.0 | 9108.9  | 6594.9 | 4080.3 |
| 57.5°  | 10620.7 | 10037.7 | 9454.6  | 9267.4  | 9080.1  | 9837.0  | 10724.1 | 10902.2 | 9775.8  | 7028.7 | 4281.0 |
| 60°    | 11246.0 | 10669.1 | 10091.5 | 9941.6  | 9791.1  | 10534.5 | 11289.5 | 11159.7 | 10119.6 | 7231.8 | 4343.4 |
| 62.5°  | 11726.9 | 11268.0 | 10809.2 | 10730.2 | 10650.7 | 11239.9 | 11723.9 | 11059.4 | 9901.2  | 7031.7 | 4162.3 |
| 65°    | 11929.4 | 11668.2 | 11406.3 | 11480.3 | 11553.8 | 11773.4 | 11832.1 | 10765.7 | 9214.7  | 6471.3 | 3727.9 |
| 67.5°  | 11347.6 | 11400.8 | 11454.0 | 11764.8 | 12075.0 | 11923.9 | 11510.3 | 10186.9 | 8237.7  | 5677.2 | 3116.7 |
| 70°    | 9596.5  | 9915.9  | 10234.7 | 10970.1 | 11704.9 | 11369.6 | 10648.3 | 9148.1  | 7061.7  | 4762.5 | 2462.6 |
| 72.5°  | 7343.8  | 7702.9  | 8061.4  | 9152.9  | 10243.8 | 9934.9  | 9051.4  | 7513.9  | 5661.9  | 3803.1 | 1943.8 |
| 75°    | 5317.4  | 5723.0  | 6128.1  | 7332.1  | 8536.2  | 8107.3  | 6770.5  | 5379.8  | 4300.5  | 2903.1 | 1505.1 |
| 77.5°  | 3787.8  | 4059.5  | 4331.1  | 5520.5  | 6709.3  | 6010.6  | 4506.7  | 3620.2  | 2976.5  | 2017.8 | 1058.5 |
| 80°    | 3038.3  | 2955.1  | 2871.9  | 3534.5  | 4197.1  | 4080.9  | 2980.8  | 2324.9  | 2060.0  | 1352.1 | 644.3  |
| 82.5°  | 2478.5  | 2275.4  | 2072.3  | 2384.3  | 2696.3  | 2679.2  | 2068.6  | 1705.8  | 1533.2  | 939.8  | 346.3  |
| 85°    | 1815.3  | 1733.9  | 1652.5  | 1928.5  | 2204.4  | 1968.9  | 1401.1  | 1084.2  | 1195.5  | 692.0  | 188.4  |
| 87.5°  | 885.3   | 1011.4  | 1136.8  | 1462.3  | 1787.2  | 1341.7  | 425.2   | 210.5   | 291.2   | 191.5  | 91.2   |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    |



REPORT NUMBER: P320457  
 CATALOG NUMBER: GLEON-SA3D-827-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 55° | 60° | 65° | 70° | 75° | 80° | 85° | 90° | 95° | 100° | 105° |
|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 115°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 120°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 125°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 130°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 135°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 140°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 145°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 150°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 155°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 160°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 165°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 170°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 175°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 180°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |



REPORT NUMBER: P320457  
 CATALOG NUMBER: GLEON-SA3D-827-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 110°   | 115°   | 120°   | 125°   | 130°   | 135°   | 140°   | 145°   | 150°   | 155°   | 160°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 |
| 2.5°   | 4767.4 | 4717.2 | 4660.3 | 4603.4 | 4538.5 | 4473.1 | 4434.5 | 4395.4 | 4353.2 | 4310.9 | 4263.2 |
| 5°     | 4366.0 | 4260.8 | 4141.5 | 4022.2 | 3904.1 | 3786.0 | 3722.4 | 3658.7 | 3591.4 | 3523.5 | 3464.8 |
| 7.5°   | 3789.7 | 3636.1 | 3470.9 | 3305.1 | 3158.3 | 3010.8 | 2919.6 | 2827.9 | 2744.7 | 2660.8 | 2590.5 |
| 10°    | 3282.5 | 3086.7 | 2920.9 | 2754.5 | 2643.7 | 2533.0 | 2449.1 | 2365.3 | 2284.6 | 2203.2 | 2125.5 |
| 12.5°  | 2948.4 | 2752.6 | 2647.4 | 2542.1 | 2450.4 | 2358.6 | 2261.9 | 2164.6 | 2053.9 | 1942.6 | 1861.2 |
| 15°    | 2818.1 | 2640.0 | 2523.2 | 2405.7 | 2282.7 | 2159.1 | 2040.4 | 1921.8 | 1790.8 | 1659.9 | 1567.5 |
| 17.5°  | 2761.8 | 2528.7 | 2365.3 | 2201.4 | 2039.2 | 1877.1 | 1739.4 | 1601.8 | 1458.6 | 1315.4 | 1221.8 |
| 20°    | 2702.4 | 2392.2 | 2173.2 | 1953.6 | 1745.5 | 1537.5 | 1381.5 | 1225.5 | 1097.6 | 969.7  | 898.2  |
| 22.5°  | 2648.6 | 2247.2 | 1972.5 | 1697.2 | 1451.3 | 1205.3 | 1052.3 | 898.8  | 820.5  | 742.1  | 713.4  |
| 25°    | 2626.6 | 2120.6 | 1782.9 | 1445.1 | 1185.7 | 925.7  | 816.8  | 707.9  | 677.9  | 647.3  | 632.6  |
| 27.5°  | 2630.2 | 2007.4 | 1623.2 | 1238.3 | 1004.6 | 770.9  | 696.3  | 621.6  | 603.3  | 584.3  | 575.1  |
| 30°    | 2644.3 | 1884.4 | 1472.7 | 1060.9 | 868.2  | 675.5  | 627.1  | 578.2  | 558.6  | 539.0  | 527.4  |
| 32.5°  | 2660.2 | 1774.3 | 1356.4 | 937.9  | 780.7  | 622.8  | 583.1  | 542.7  | 523.7  | 504.8  | 493.1  |
| 35°    | 2632.7 | 1684.4 | 1276.9 | 869.4  | 724.4  | 578.8  | 545.1  | 510.9  | 490.1  | 469.3  | 458.3  |
| 37.5°  | 2586.2 | 1593.8 | 1215.1 | 835.8  | 687.7  | 539.0  | 514.5  | 489.5  | 468.0  | 446.0  | 435.6  |
| 40°    | 2544.0 | 1517.3 | 1169.2 | 820.5  | 667.5  | 513.9  | 493.1  | 472.3  | 450.3  | 427.7  | 415.4  |
| 42.5°  | 2509.7 | 1465.9 | 1123.9 | 781.9  | 649.1  | 515.8  | 486.4  | 456.4  | 435.0  | 413.6  | 400.1  |
| 45°    | 2484.0 | 1432.3 | 1088.4 | 744.6  | 632.0  | 519.4  | 482.1  | 444.8  | 423.4  | 401.4  | 385.5  |
| 47.5°  | 2481.6 | 1414.5 | 1063.4 | 712.2  | 599.6  | 486.4  | 471.1  | 455.8  | 424.6  | 392.8  | 374.4  |
| 50°    | 2515.2 | 1385.8 | 1034.0 | 681.6  | 568.4  | 455.2  | 476.0  | 496.2  | 443.0  | 389.1  | 365.9  |
| 52.5°  | 2585.6 | 1335.0 | 987.5  | 640.0  | 530.5  | 420.3  | 452.8  | 484.6  | 438.7  | 392.2  | 362.2  |
| 55°    | 2670.6 | 1260.4 | 917.1  | 573.3  | 480.3  | 386.7  | 415.4  | 443.6  | 414.8  | 385.5  | 349.4  |
| 57.5°  | 2723.9 | 1166.1 | 828.4  | 490.7  | 424.0  | 357.3  | 373.8  | 389.7  | 378.1  | 366.5  | 329.8  |
| 60°    | 2692.0 | 1040.7 | 728.7  | 416.0  | 374.4  | 332.8  | 329.8  | 326.1  | 343.2  | 360.4  | 318.2  |
| 62.5°  | 2536.6 | 911.0  | 640.6  | 370.2  | 339.0  | 307.1  | 300.4  | 293.1  | 321.2  | 348.7  | 304.1  |
| 65°    | 2274.2 | 820.5  | 584.9  | 349.4  | 314.5  | 279.6  | 272.3  | 264.9  | 273.5  | 282.1  | 261.3  |
| 67.5°  | 1940.7 | 764.8  | 553.1  | 341.4  | 299.2  | 256.4  | 247.8  | 239.2  | 237.4  | 235.6  | 228.2  |
| 70°    | 1596.9 | 730.5  | 532.3  | 334.1  | 282.7  | 230.7  | 222.7  | 214.8  | 212.3  | 209.2  | 203.7  |
| 72.5°  | 1335.0 | 726.2  | 529.8  | 333.4  | 269.2  | 205.0  | 197.6  | 190.3  | 187.2  | 183.5  | 179.3  |
| 75°    | 1093.3 | 681.6  | 502.9  | 324.3  | 250.8  | 176.8  | 170.1  | 163.4  | 160.9  | 157.9  | 154.2  |
| 77.5°  | 811.3  | 564.1  | 422.8  | 281.4  | 214.8  | 148.1  | 141.3  | 134.0  | 133.4  | 132.2  | 129.1  |
| 80°    | 526.2  | 408.1  | 302.2  | 196.4  | 156.6  | 116.2  | 110.7  | 104.6  | 105.2  | 105.8  | 103.4  |
| 82.5°  | 292.5  | 238.0  | 184.8  | 131.5  | 107.1  | 82.6   | 80.1   | 77.1   | 78.9   | 80.1   | 77.1   |
| 85°    | 154.2  | 119.9  | 99.1   | 78.3   | 61.8   | 45.3   | 45.3   | 44.7   | 47.1   | 49.6   | 47.1   |
| 87.5°  | 66.7   | 42.2   | 36.1   | 29.4   | 16.5   | 3.1    | 3.7    | 3.7    | 4.9    | 6.1    | 5.5    |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P320457  
 CATALOG NUMBER: GLEON-SA3D-827-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 110° | 115° | 120° | 125° | 130° | 135° | 140° | 145° | 150° | 155° | 160° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 115°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 117.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 120°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 122.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 125°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 127.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 130°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 132.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 135°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 137.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 140°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 142.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 145°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 147.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 150°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 152.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 155°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 157.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 160°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 162.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 165°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 167.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 170°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 172.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 175°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 177.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 180°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |



REPORT NUMBER: P320457  
 CATALOG NUMBER: GLEON-SA3D-827-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 165°   | 170°   | 175°   | 180°   | 185°   | 190°   | 195°   | 200°   | 205°   | 210°   | 215°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 |
| 2.5°   | 4214.9 | 4170.2 | 4124.9 | 4075.4 | 4084.6 | 4046.6 | 4008.7 | 3984.8 | 3961.0 | 3953.6 | 3946.3 |
| 5°     | 3406.0 | 3355.3 | 3303.9 | 3258.0 | 3297.8 | 3270.8 | 3243.9 | 3240.2 | 3236.0 | 3236.0 | 3235.3 |
| 7.5°   | 2520.1 | 2465.7 | 2410.6 | 2372.7 | 2411.8 | 2406.9 | 2402.0 | 2428.3 | 2454.7 | 2476.1 | 2496.9 |
| 10°    | 2047.8 | 1981.7 | 1915.0 | 1858.7 | 1848.9 | 1820.8 | 1792.0 | 1798.2 | 1803.7 | 1826.9 | 1850.2 |
| 12.5°  | 1779.8 | 1700.9 | 1622.0 | 1555.9 | 1525.9 | 1479.4 | 1432.3 | 1402.9 | 1373.6 | 1376.6 | 1379.1 |
| 15°    | 1474.5 | 1398.0 | 1320.9 | 1264.0 | 1245.1 | 1209.0 | 1172.9 | 1136.2 | 1098.8 | 1083.5 | 1067.6 |
| 17.5°  | 1127.6 | 1066.4 | 1004.6 | 966.7  | 966.7  | 956.3  | 945.9  | 927.5  | 908.6  | 893.3  | 877.4  |
| 20°    | 826.6  | 794.2  | 761.1  | 745.2  | 750.1  | 750.7  | 750.7  | 759.9  | 769.1  | 764.2  | 759.3  |
| 22.5°  | 684.0  | 672.4  | 660.8  | 654.0  | 656.5  | 657.1  | 657.7  | 666.3  | 674.2  | 680.4  | 685.9  |
| 25°    | 617.3  | 610.0  | 602.7  | 600.2  | 605.7  | 606.3  | 606.3  | 611.8  | 617.3  | 623.5  | 629.6  |
| 27.5°  | 565.3  | 562.3  | 559.2  | 554.9  | 560.4  | 560.4  | 559.8  | 565.9  | 571.4  | 577.0  | 581.8  |
| 30°    | 515.8  | 517.0  | 517.6  | 516.4  | 520.1  | 522.5  | 524.3  | 528.6  | 532.3  | 536.6  | 540.9  |
| 32.5°  | 480.9  | 479.1  | 477.2  | 476.0  | 484.0  | 488.2  | 492.5  | 496.8  | 500.5  | 502.3  | 504.1  |
| 35°    | 447.2  | 443.0  | 438.7  | 435.6  | 443.0  | 448.5  | 454.0  | 461.9  | 469.3  | 470.5  | 471.7  |
| 37.5°  | 424.6  | 419.1  | 413.6  | 409.9  | 413.0  | 415.4  | 417.9  | 426.4  | 435.0  | 439.9  | 444.2  |
| 40°    | 403.2  | 397.7  | 392.2  | 389.1  | 391.0  | 391.6  | 392.2  | 396.5  | 400.1  | 409.3  | 417.9  |
| 42.5°  | 386.1  | 379.3  | 372.6  | 368.9  | 370.2  | 371.4  | 372.0  | 371.4  | 370.8  | 379.3  | 387.9  |
| 45°    | 368.9  | 361.6  | 354.2  | 350.0  | 350.6  | 350.6  | 350.6  | 349.4  | 347.5  | 351.8  | 356.1  |
| 47.5°  | 355.5  | 346.9  | 338.3  | 334.1  | 332.8  | 331.6  | 330.4  | 329.8  | 328.6  | 331.6  | 334.1  |
| 50°    | 342.0  | 332.8  | 323.0  | 318.2  | 315.1  | 313.9  | 312.6  | 312.0  | 310.8  | 313.9  | 316.3  |
| 52.5°  | 331.6  | 320.6  | 309.6  | 301.6  | 298.6  | 296.7  | 294.9  | 295.5  | 295.5  | 296.7  | 297.3  |
| 55°    | 313.3  | 303.5  | 293.1  | 287.6  | 282.1  | 280.8  | 279.6  | 281.4  | 282.7  | 282.7  | 282.7  |
| 57.5°  | 293.1  | 283.9  | 274.1  | 270.4  | 265.5  | 265.5  | 264.9  | 267.4  | 269.2  | 270.4  | 271.7  |
| 60°    | 275.3  | 264.9  | 254.5  | 251.5  | 249.6  | 249.0  | 248.4  | 251.5  | 253.9  | 256.4  | 258.8  |
| 62.5°  | 258.8  | 247.8  | 236.8  | 233.1  | 232.5  | 233.1  | 233.1  | 236.2  | 238.6  | 241.1  | 243.5  |
| 65°    | 240.4  | 229.4  | 217.8  | 214.1  | 215.4  | 217.2  | 219.0  | 221.5  | 223.3  | 225.8  | 228.2  |
| 67.5°  | 220.3  | 211.1  | 201.3  | 197.6  | 198.2  | 200.7  | 203.1  | 205.0  | 206.2  | 208.6  | 211.1  |
| 70°    | 198.2  | 190.3  | 182.3  | 179.9  | 179.3  | 182.3  | 184.8  | 186.0  | 187.2  | 190.3  | 192.7  |
| 72.5°  | 174.4  | 167.6  | 160.9  | 159.1  | 159.7  | 161.5  | 163.4  | 165.2  | 166.4  | 169.5  | 171.9  |
| 75°    | 149.9  | 143.8  | 137.7  | 136.4  | 137.7  | 139.5  | 141.3  | 142.6  | 143.8  | 147.5  | 150.5  |
| 77.5°  | 126.0  | 119.3  | 112.0  | 111.4  | 113.2  | 115.0  | 116.2  | 118.1  | 119.9  | 124.8  | 129.7  |
| 80°    | 101.0  | 93.6   | 85.7   | 85.0   | 86.9   | 88.7   | 90.6   | 92.4   | 94.2   | 100.3  | 105.8  |
| 82.5°  | 74.0   | 65.5   | 56.9   | 55.7   | 61.8   | 63.6   | 65.5   | 68.5   | 71.0   | 76.5   | 82.0   |
| 85°    | 44.7   | 36.1   | 27.5   | 26.9   | 32.4   | 35.5   | 38.5   | 42.2   | 45.3   | 50.2   | 55.1   |
| 87.5°  | 4.9    | 2.4    | 0.0    | 0.0    | 0.6    | 3.1    | 5.5    | 8.6    | 11.6   | 16.5   | 20.8   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P320457  
 CATALOG NUMBER: GLEON-SA3D-827-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 165° | 170° | 175° | 180° | 185° | 190° | 195° | 200° | 205° | 210° | 215° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 115°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 117.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 120°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 122.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 125°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 127.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 130°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 132.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 135°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 137.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 140°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 142.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 145°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 147.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 150°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 152.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 155°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 157.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 160°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 162.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 165°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 167.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 170°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 172.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 175°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 177.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 180°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |



REPORT NUMBER: P320457  
 CATALOG NUMBER: GLEON-SA3D-827-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 220°   | 225°   | 230°   | 235°   | 240°   | 245°   | 250°   | 255°   | 260°   | 265°   | 270°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 |
| 2.5°   | 3919.4 | 3891.8 | 3920.0 | 3947.5 | 3959.1 | 3970.8 | 3940.8 | 3910.2 | 3957.9 | 4005.0 | 4017.3 |
| 5°     | 3210.9 | 3185.8 | 3204.8 | 3223.1 | 3182.1 | 3141.1 | 3136.8 | 3131.9 | 3167.4 | 3202.9 | 3208.4 |
| 7.5°   | 2488.9 | 2481.0 | 2498.7 | 2516.4 | 2464.4 | 2411.8 | 2386.1 | 2360.4 | 2369.0 | 2377.6 | 2376.3 |
| 10°    | 1855.7 | 1860.6 | 1882.6 | 1904.0 | 1863.6 | 1823.2 | 1805.5 | 1787.8 | 1807.3 | 1826.3 | 1844.1 |
| 12.5°  | 1390.1 | 1400.5 | 1423.7 | 1446.4 | 1429.8 | 1412.7 | 1414.5 | 1416.4 | 1439.0 | 1461.0 | 1480.6 |
| 15°    | 1079.9 | 1092.1 | 1108.6 | 1124.5 | 1125.2 | 1125.2 | 1141.1 | 1156.4 | 1154.5 | 1152.7 | 1166.1 |
| 17.5°  | 893.9  | 909.8  | 911.6  | 913.5  | 914.1  | 914.7  | 913.5  | 912.2  | 903.1  | 893.9  | 904.3  |
| 20°    | 765.4  | 770.9  | 775.8  | 780.1  | 774.6  | 768.5  | 753.2  | 737.9  | 731.7  | 725.6  | 735.4  |
| 22.5°  | 696.3  | 706.0  | 701.2  | 695.6  | 684.6  | 673.0  | 661.4  | 649.1  | 648.5  | 647.3  | 652.8  |
| 25°    | 638.1  | 646.1  | 637.5  | 629.0  | 621.0  | 613.1  | 605.1  | 597.1  | 596.5  | 595.9  | 598.4  |
| 27.5°  | 589.8  | 597.1  | 589.2  | 581.2  | 574.5  | 567.8  | 561.7  | 555.5  | 554.3  | 553.1  | 553.7  |
| 30°    | 548.2  | 554.9  | 548.2  | 540.9  | 536.0  | 530.5  | 526.2  | 521.9  | 521.3  | 520.7  | 520.7  |
| 32.5°  | 510.9  | 517.6  | 512.7  | 507.8  | 503.5  | 499.3  | 496.2  | 493.1  | 490.1  | 487.0  | 480.3  |
| 35°    | 478.4  | 485.2  | 482.1  | 478.4  | 473.6  | 468.7  | 463.2  | 457.0  | 449.1  | 440.5  | 436.8  |
| 37.5°  | 450.9  | 457.6  | 454.6  | 451.5  | 444.8  | 438.1  | 428.3  | 417.9  | 415.4  | 412.4  | 411.8  |
| 40°    | 428.9  | 439.3  | 433.2  | 426.4  | 416.0  | 405.6  | 400.7  | 395.9  | 394.6  | 393.4  | 392.2  |
| 42.5°  | 404.4  | 420.3  | 409.3  | 398.3  | 388.5  | 378.7  | 377.5  | 376.3  | 375.7  | 375.1  | 375.1  |
| 45°    | 373.8  | 391.0  | 379.9  | 368.3  | 362.8  | 357.3  | 357.3  | 357.3  | 357.9  | 357.9  | 359.1  |
| 47.5°  | 345.1  | 355.5  | 350.0  | 344.5  | 341.4  | 338.3  | 339.0  | 339.6  | 341.4  | 342.6  | 345.7  |
| 50°    | 320.6  | 324.3  | 325.5  | 326.1  | 324.3  | 322.4  | 323.7  | 324.3  | 326.1  | 327.3  | 329.8  |
| 52.5°  | 302.9  | 308.4  | 308.4  | 307.7  | 307.7  | 307.7  | 309.0  | 310.2  | 312.0  | 313.9  | 316.3  |
| 55°    | 291.2  | 299.2  | 296.7  | 294.3  | 294.9  | 294.9  | 296.1  | 297.3  | 299.2  | 300.4  | 304.1  |
| 57.5°  | 280.2  | 288.8  | 286.3  | 283.9  | 283.9  | 283.9  | 284.5  | 285.1  | 286.9  | 288.2  | 290.6  |
| 60°    | 267.4  | 275.9  | 273.5  | 270.4  | 271.0  | 271.7  | 272.3  | 272.3  | 273.5  | 274.1  | 274.1  |
| 62.5°  | 252.1  | 260.6  | 258.2  | 255.1  | 257.0  | 258.2  | 258.2  | 258.2  | 259.4  | 260.0  | 258.2  |
| 65°    | 236.2  | 244.1  | 241.7  | 239.2  | 241.7  | 243.5  | 244.7  | 245.3  | 244.7  | 244.1  | 242.3  |
| 67.5°  | 219.0  | 227.0  | 224.5  | 221.5  | 224.5  | 227.0  | 229.4  | 231.3  | 229.4  | 227.6  | 225.2  |
| 70°    | 200.7  | 208.6  | 205.6  | 202.5  | 205.6  | 208.6  | 211.1  | 213.5  | 211.1  | 208.6  | 208.0  |
| 72.5°  | 181.1  | 190.3  | 186.6  | 182.9  | 186.6  | 190.3  | 191.5  | 192.7  | 190.9  | 189.1  | 187.8  |
| 75°    | 159.7  | 168.9  | 165.8  | 162.1  | 165.2  | 168.3  | 168.9  | 169.5  | 169.5  | 168.9  | 165.2  |
| 77.5°  | 137.0  | 144.4  | 142.6  | 140.7  | 142.6  | 144.4  | 144.4  | 144.4  | 145.0  | 145.0  | 140.1  |
| 80°    | 110.1  | 114.4  | 115.0  | 115.6  | 116.2  | 116.9  | 116.2  | 115.6  | 114.4  | 113.2  | 110.1  |
| 82.5°  | 82.0   | 82.0   | 86.9   | 91.2   | 91.2   | 90.6   | 89.9   | 88.7   | 86.3   | 83.2   | 76.5   |
| 85°    | 52.0   | 48.9   | 56.9   | 64.2   | 64.2   | 63.6   | 62.4   | 60.6   | 55.7   | 50.2   | 44.7   |
| 87.5°  | 17.7   | 14.7   | 22.6   | 30.6   | 31.2   | 31.2   | 30.0   | 28.8   | 23.9   | 18.4   | 14.1   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P320457  
 CATALOG NUMBER: GLEON-SA3D-827-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 220° | 225° | 230° | 235° | 240° | 245° | 250° | 255° | 260° | 265° | 270° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 115°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 117.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 120°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 122.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 125°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 127.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 130°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 132.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 135°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 137.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 140°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 142.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 145°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 147.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 150°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 152.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 155°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 157.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 160°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 162.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 165°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 167.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 170°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 172.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 175°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 177.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 180°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |





REPORT NUMBER: P320457  
 CATALOG NUMBER: GLEON-SA3D-827-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 275°   | 280°   | 285°   | 290°   | 295°   | 300°   | 305°   | 310°   | 315°   | 320°   | 325°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 |
| 2.5°   | 4035.6 | 4043.6 | 4050.9 | 4110.9 | 4170.2 | 4240.0 | 4309.7 | 4362.9 | 4415.6 | 4470.0 | 4524.5 |
| 5°     | 3227.4 | 3237.2 | 3247.0 | 3319.8 | 3392.0 | 3489.3 | 3586.5 | 3670.4 | 3754.2 | 3852.7 | 3951.2 |
| 7.5°   | 2392.2 | 2413.7 | 2434.5 | 2512.2 | 2589.3 | 2693.9 | 2797.9 | 2907.4 | 3016.3 | 3144.8 | 3273.3 |
| 10°    | 1878.9 | 1919.3 | 1959.1 | 2038.6 | 2118.1 | 2221.5 | 2324.3 | 2438.7 | 2553.2 | 2679.8 | 2805.8 |
| 12.5°  | 1521.0 | 1574.8 | 1628.1 | 1723.5 | 1819.0 | 1942.6 | 2065.5 | 2192.8 | 2319.4 | 2430.8 | 2542.1 |
| 15°    | 1201.6 | 1260.4 | 1318.5 | 1419.4 | 1520.4 | 1656.2 | 1791.4 | 1930.3 | 2068.6 | 2202.0 | 2335.3 |
| 17.5°  | 937.3  | 985.7  | 1033.4 | 1119.0 | 1204.1 | 1335.6 | 1467.2 | 1612.8 | 1758.4 | 1921.1 | 2083.3 |
| 20°    | 756.2  | 776.4  | 796.6  | 858.4  | 919.6  | 1026.6 | 1133.1 | 1281.8 | 1430.5 | 1625.0 | 1819.6 |
| 22.5°  | 662.6  | 673.0  | 682.8  | 712.8  | 742.1  | 811.3  | 879.8  | 1011.4 | 1142.3 | 1354.6 | 1566.3 |
| 25°    | 606.3  | 614.3  | 622.2  | 641.8  | 661.4  | 694.4  | 727.5  | 819.8  | 912.2  | 1120.9 | 1328.9 |
| 27.5°  | 555.5  | 567.8  | 579.4  | 588.6  | 597.1  | 619.8  | 641.8  | 702.4  | 762.9  | 957.5  | 1151.5 |
| 30°    | 518.8  | 523.1  | 527.4  | 541.5  | 554.9  | 578.2  | 601.4  | 643.6  | 685.9  | 850.4  | 1014.4 |
| 32.5°  | 476.0  | 482.1  | 488.2  | 502.9  | 517.6  | 539.0  | 560.4  | 594.7  | 628.3  | 769.1  | 909.2  |
| 35°    | 437.5  | 443.6  | 449.7  | 464.4  | 478.4  | 501.7  | 524.3  | 553.1  | 581.2  | 703.6  | 826.0  |
| 37.5°  | 413.6  | 419.7  | 425.8  | 438.7  | 450.9  | 474.2  | 496.8  | 519.4  | 541.5  | 654.7  | 767.8  |
| 40°    | 393.4  | 399.5  | 405.6  | 417.9  | 429.5  | 452.1  | 474.2  | 493.1  | 512.1  | 617.9  | 723.8  |
| 42.5°  | 375.7  | 382.4  | 389.1  | 401.4  | 413.0  | 433.2  | 453.4  | 478.4  | 502.9  | 586.1  | 668.7  |
| 45°    | 361.0  | 367.7  | 373.8  | 387.3  | 400.7  | 420.3  | 439.9  | 474.8  | 509.7  | 569.6  | 629.6  |
| 47.5°  | 347.5  | 354.9  | 361.6  | 376.3  | 391.0  | 415.4  | 439.3  | 468.7  | 497.4  | 556.8  | 616.1  |
| 50°    | 334.7  | 343.2  | 351.8  | 369.5  | 386.7  | 427.7  | 468.0  | 472.3  | 476.0  | 546.4  | 616.1  |
| 52.5°  | 322.4  | 332.2  | 342.0  | 364.0  | 385.5  | 433.2  | 480.9  | 465.6  | 449.7  | 526.8  | 603.9  |
| 55°    | 310.2  | 318.8  | 326.7  | 353.6  | 380.6  | 415.4  | 450.3  | 430.1  | 409.3  | 490.1  | 570.8  |
| 57.5°  | 293.7  | 302.9  | 311.4  | 340.2  | 368.9  | 393.4  | 417.3  | 398.9  | 379.9  | 448.5  | 516.4  |
| 60°    | 276.5  | 286.9  | 297.3  | 334.1  | 370.2  | 365.9  | 361.0  | 357.3  | 353.0  | 402.0  | 450.9  |
| 62.5°  | 261.3  | 272.3  | 283.3  | 331.0  | 378.7  | 349.4  | 320.0  | 323.0  | 325.5  | 361.6  | 397.7  |
| 65°    | 246.0  | 257.0  | 267.4  | 291.2  | 315.1  | 303.5  | 291.8  | 296.7  | 301.0  | 336.5  | 372.0  |
| 67.5°  | 228.8  | 238.6  | 247.8  | 255.7  | 263.7  | 264.9  | 266.1  | 271.0  | 275.9  | 318.2  | 359.8  |
| 70°    | 209.9  | 217.8  | 225.8  | 231.3  | 236.2  | 238.6  | 240.4  | 246.6  | 252.7  | 298.6  | 344.5  |
| 72.5°  | 188.4  | 195.2  | 201.3  | 206.2  | 211.1  | 212.9  | 214.1  | 220.3  | 226.4  | 275.3  | 324.3  |
| 75°    | 165.2  | 170.7  | 175.6  | 179.9  | 184.2  | 186.6  | 189.1  | 193.3  | 197.6  | 250.8  | 303.5  |
| 77.5°  | 139.5  | 145.0  | 149.9  | 153.6  | 156.6  | 159.1  | 160.9  | 166.4  | 171.9  | 216.6  | 260.6  |
| 80°    | 108.9  | 115.6  | 121.8  | 124.8  | 127.3  | 127.9  | 127.9  | 132.8  | 137.7  | 169.5  | 200.7  |
| 82.5°  | 77.1   | 84.4   | 91.2   | 93.6   | 96.1   | 96.1   | 96.1   | 101.6  | 107.1  | 128.5  | 149.3  |
| 85°    | 45.3   | 53.2   | 60.6   | 63.0   | 65.5   | 66.7   | 67.3   | 69.7   | 71.6   | 86.9   | 101.6  |
| 87.5°  | 14.1   | 20.8   | 26.9   | 28.1   | 29.4   | 31.8   | 34.3   | 34.9   | 34.9   | 45.3   | 55.7   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P320457  
 CATALOG NUMBER: GLEON-SA3D-827-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 275° | 280° | 285° | 290° | 295° | 300° | 305° | 310° | 315° | 320° | 325° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 115°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 117.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 120°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 122.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 125°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 127.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 130°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 132.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 135°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 137.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 140°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 142.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 145°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 147.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 150°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 152.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 155°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 157.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 160°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 162.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 165°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 167.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 170°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 172.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 175°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 177.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 180°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |



REPORT NUMBER: P320457

CATALOG NUMBER: GLEON-SA3D-827-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 330°   | 335°   | 340°   | 345°   | 350°   | 355°   | 360°    |
|--------|--------|--------|--------|--------|--------|--------|---------|
| 0°     | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1 | 4662.1  |
| 2.5°   | 4586.9 | 4649.3 | 4722.1 | 4794.3 | 4856.1 | 4917.9 | 4969.3  |
| 5°     | 4076.6 | 4202.0 | 4355.6 | 4508.6 | 4645.0 | 4781.4 | 4939.9  |
| 7.5°   | 3435.4 | 3597.5 | 3796.4 | 3995.2 | 4188.0 | 4380.1 | 4623.6  |
| 10°    | 2971.0 | 3135.6 | 3346.1 | 3555.9 | 3772.5 | 3988.5 | 4263.8  |
| 12.5°  | 2676.1 | 2809.5 | 3013.3 | 3217.0 | 3471.5 | 3725.4 | 3990.3  |
| 15°    | 2481.6 | 2627.2 | 2825.4 | 3023.7 | 3302.0 | 3580.4 | 3885.1  |
| 17.5°  | 2274.2 | 2464.4 | 2718.4 | 2972.3 | 3302.0 | 3631.2 | 3990.3  |
| 20°    | 2057.0 | 2293.7 | 2622.9 | 2952.1 | 3396.3 | 3839.8 | 4298.1  |
| 22.5°  | 1840.4 | 2114.5 | 2536.6 | 2958.2 | 3538.8 | 4118.8 | 4737.4  |
| 25°    | 1645.2 | 1961.5 | 2484.0 | 3005.9 | 3746.2 | 4485.9 | 5253.2  |
| 27.5°  | 1497.1 | 1842.2 | 2462.6 | 3082.4 | 4009.3 | 4936.2 | 5814.2  |
| 30°    | 1365.6 | 1716.8 | 2436.9 | 3157.0 | 4262.6 | 5367.6 | 6252.9  |
| 32.5°  | 1251.8 | 1594.4 | 2387.4 | 3179.7 | 4439.4 | 5699.2 | 6624.3  |
| 35°    | 1162.5 | 1499.0 | 2304.1 | 3109.3 | 4550.2 | 5991.0 | 7010.9  |
| 37.5°  | 1085.4 | 1402.9 | 2209.3 | 3015.7 | 4648.7 | 6281.6 | 7445.9  |
| 40°    | 1012.0 | 1300.1 | 2127.9 | 2955.1 | 4784.5 | 6613.9 | 7905.4  |
| 42.5°  | 942.2  | 1215.7 | 2062.5 | 2909.2 | 4910.5 | 6911.2 | 8307.4  |
| 45°    | 890.2  | 1150.8 | 2004.3 | 2857.2 | 4991.9 | 7126.6 | 8610.3  |
| 47.5°  | 864.5  | 1112.3 | 1973.1 | 2833.4 | 5073.3 | 7312.6 | 8861.7  |
| 50°    | 860.8  | 1105.6 | 2008.6 | 2911.7 | 5249.5 | 7586.7 | 9149.3  |
| 52.5°  | 860.2  | 1116.6 | 2110.8 | 3105.0 | 5576.8 | 8048.0 | 9460.7  |
| 55°    | 847.4  | 1123.3 | 2232.6 | 3341.2 | 6016.1 | 8690.4 | 10020.5 |
| 57.5°  | 808.2  | 1100.1 | 2358.0 | 3615.3 | 6480.5 | 9345.1 | 10651.3 |
| 60°    | 747.7  | 1043.8 | 2461.4 | 3878.4 | 6792.5 | 9706.0 | 10894.2 |
| 62.5°  | 671.8  | 945.3  | 2495.6 | 4045.4 | 6784.0 | 9522.5 | 10649.5 |
| 65°    | 606.9  | 841.9  | 2383.1 | 3923.7 | 6440.7 | 8957.2 | 10165.5 |
| 67.5°  | 549.4  | 738.5  | 2101.6 | 3464.2 | 5823.4 | 8182.0 | 9550.0  |
| 70°    | 507.8  | 670.6  | 1738.8 | 2807.1 | 5050.6 | 7293.6 | 8837.2  |
| 72.5°  | 481.5  | 638.1  | 1417.6 | 2196.5 | 4098.6 | 6000.2 | 7559.1  |
| 75°    | 445.4  | 587.4  | 1112.3 | 1636.6 | 3136.8 | 4637.0 | 5709.6  |
| 77.5°  | 378.1  | 495.0  | 838.2  | 1181.4 | 2301.7 | 3421.3 | 3970.8  |
| 80°    | 291.8  | 382.4  | 576.3  | 770.3  | 1584.0 | 2397.8 | 2707.3  |
| 82.5°  | 208.0  | 266.8  | 349.4  | 432.0  | 1052.3 | 1672.1 | 1697.8  |
| 85°    | 128.5  | 155.4  | 200.1  | 244.7  | 696.3  | 1147.8 | 956.3   |
| 87.5°  | 69.1   | 82.6   | 105.8  | 128.5  | 222.7  | 316.9  | 182.3   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     |



REPORT NUMBER: P320457  
CATALOG NUMBER: GLEON-SA3D-827-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 330° | 335° | 340° | 345° | 350° | 355° | 360° |
|--------|------|------|------|------|------|------|------|
| 112.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 115°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 117.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 120°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 122.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 125°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 127.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 130°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 132.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 135°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 137.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 140°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 142.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 145°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 147.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 150°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 152.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 155°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 157.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 160°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 162.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 165°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 167.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 170°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 172.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 175°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 177.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 180°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |

(END OF REPORT)