

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P324959

Luminaire Tested: **GLEON-SA5B-830-U-AFL-HSS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P324959
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-30)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GLEON-SA5B-830-U-AFL-HSS
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(5) 80 CRI, 3000K, 800mA LIGHTSQUARES WITH 16 LEDS EACH AND AUTOMOTIVE
FRONTLINE OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 18580 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 210
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P324959
 CATALOG NUMBER: GLEON-SA5B-830-U-AFL-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 10.2 fc
 Type II - Short - N/A

REPORT NUMBER: P324959
CATALOG NUMBER: GLEON-SA5B-830-U-AFL-HSS

Luminous Intensity Polar Plot



REPORT NUMBER: P324959
 CATALOG NUMBER: GLEON-SA5B-830-U-AFL-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	927.0	0.0	927.0
	% Fixture	5.0	0.0	5.0
Street Side	Lumens	17653.0	0.0	17653.0
	% Fixture	95.0	0.0	95.0
Total	Lumens	18580.0	0.0	18580.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	383.2	2.1
10°-20°	1050.9	5.7
20°-30°	1794.3	9.7
30°-40°	2879.5	15.5
40°-50°	4601.5	24.8
50°-60°	4930.6	26.5
60°-70°	2531.5	13.6
70°-80°	383.5	2.1
80°-90°	25.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	18580.0	100.0
0°-180°	18580.0	100.0

Coefficient of Utilization



REPORT NUMBER: P324959


CATALOG NUMBER: GLEON-SA5B-830-U-AFL-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	2777.4	14.9			
FM	(30°-60°)	12022.1	64.7			
FH	(60°-80°)	2829.6	15.2			G2/5000
FVH	(80°-90°)	24.0	0.1			G1/100
BL	(0°-30°)	451.0	2.4	B1/500		
BM	(30°-60°)	389.5	2.1	B1/1000		
BH	(60°-80°)	85.4	0.5	B0/110		G0/110
BVH	(80°-90°)	1.0	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type II Short





REPORT NUMBER: P324959

CATALOG NUMBER: GLEON-SA5B-830-U-AFL-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	54°	55°	65°	75°	85°
0°	4161.2	4161.2	4161.2	4161.2	4161.2	4161.2	4161.2	4161.2	4161.2	4161.2	4161.2
2.5°	5221.9	5144.1	5146.5	5111.2	4982.0	4880.9	4775.8	4750.9	4587.2	4415.5	4250.2
5°	6124.6	6067.6	6054.0	5985.8	5806.1	5615.9	5412.1	5364.8	5044.6	4693.2	4347.3
7.5°	6588.4	6589.2	6578.0	6553.1	6440.8	6256.2	6007.5	5957.7	5522.0	4994.9	4448.4
10°	6453.6	6484.1	6546.7	6629.3	6715.2	6691.9	6504.9	6460.0	5986.6	5314.2	4560.8
12.5°	6139.1	6143.1	6212.9	6348.5	6595.6	6849.2	6852.4	6837.1	6430.3	5648.0	4684.3
15°	5982.6	5997.8	6023.5	6111.0	6345.3	6751.3	7041.7	7063.4	6837.1	6002.7	4815.9
17.5°	6085.3	6107.0	6085.3	6095.7	6231.3	6596.4	7074.6	7130.0	7192.6	6353.3	4940.3
20°	6363.7	6383.8	6345.3	6302.7	6329.2	6551.5	7051.4	7126.0	7471.0	6664.6	5044.6
22.5°	6739.2	6747.3	6688.7	6618.9	6599.6	6703.9	7070.6	7147.7	7694.1	6946.3	5110.4
25°	7152.5	7159.7	7086.7	7006.4	6960.7	7003.2	7228.7	7286.5	7890.7	7215.1	5148.1
27.5°	7602.6	7609.0	7517.6	7418.9	7365.9	7367.5	7489.5	7551.3	8100.1	7521.6	5178.6
30°	8078.4	8075.2	7991.0	7853.8	7786.4	7784.7	7865.0	7927.6	8403.4	7914.7	5220.3
32.5°	8612.8	8606.4	8486.8	8316.7	8240.5	8251.7	8323.2	8359.3	8779.7	8333.6	5294.9
35°	9316.5	9298.1	9117.5	8906.5	8766.1	8762.1	8822.2	8851.1	9259.5	8840.7	5419.3
37.5°	10229.6	10212.8	9968.0	9661.5	9464.1	9390.3	9461.7	9498.6	9944.0	9491.4	5619.1
40°	11129.9	11113.0	10967.8	10687.0	10382.9	10205.5	10261.7	10301.0	10798.5	10281.0	5871.1
42.5°	11750.9	11765.4	11815.9	11839.2	11554.4	11182.1	11207.7	11248.7	11696.4	11125.1	6159.1
45°	11914.6	11945.9	12231.6	12792.4	12899.2	12608.7	12339.9	12362.4	12608.7	11969.2	6447.2
47.5°	11422.8	11480.5	12031.8	13074.9	13978.4	14183.8	13675.1	13645.4	13484.1	12652.0	6651.8
50°	10305.0	10358.0	11072.1	12615.1	14305.7	15687.5	15275.0	15187.6	14252.0	13060.4	6724.0
52.5°	8687.4	8751.6	9331.8	11167.6	13688.7	16358.2	16789.9	16716.9	14815.3	13092.5	6736.0
55°	6135.0	6212.9	6826.7	8559.1	11733.3	15824.7	17326.7	17305.1	15283.0	13007.5	6761.7
57.5°	3447.9	3504.0	4166.0	5486.7	8593.6	13783.4	16765.9	16909.5	15565.5	12859.8	6800.2
60°	1531.0	1546.2	1888.8	2731.3	5031.0	10533.7	15160.3	15402.6	15323.2	12662.5	6865.2
62.5°	848.9	836.1	836.1	1135.4	2186.5	6521.0	12362.4	12762.8	14288.9	12429.0	6868.4
65°	665.2	653.1	618.6	623.5	832.9	2894.2	8560.7	9272.4	12324.7	11744.5	6637.3
67.5°	564.1	553.6	519.1	505.5	517.5	954.8	4703.6	5442.6	9351.8	9965.6	5749.1
70°	476.6	469.4	451.7	434.9	404.4	471.8	1799.8	2302.0	5762.7	6629.3	3924.5
72.5°	383.5	380.3	386.8	372.3	335.4	314.5	615.4	745.4	2588.5	2958.4	1616.8
75°	330.6	329.0	332.2	317.7	276.0	219.1	312.9	341.8	730.2	723.8	327.4
77.5°	215.0	217.4	275.2	268.8	237.5	146.0	162.1	174.9	221.5	166.1	99.5
80°	137.2	135.6	139.6	223.1	213.4	111.5	81.0	85.1	106.7	81.8	48.1
82.5°	83.4	81.8	91.5	104.3	107.5	77.8	49.7	50.6	66.6	53.0	25.7
85°	7.2	9.6	55.4	51.4	36.9	24.1	24.1	25.7	35.3	31.3	14.4
87.5°	0.0	0.0	9.6	14.4	8.0	8.8	8.8	9.6	13.6	13.6	7.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P324959

CATALOG NUMBER: GLEON-SA5B-830-U-AFL-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	4161.2	4161.2	4161.2	4161.2	4161.2	4161.2	4161.2	4161.2	4161.2	4161.2	4161.2
2.5°	4164.4	4080.9	3912.4	3750.4	3613.1	3480.8	3329.9	3180.7	3110.9	3082.8	3053.9
5°	4171.6	3999.9	3652.5	3302.6	2939.9	2613.4	2334.9	2049.3	1906.5	1843.9	1815.0
7.5°	4181.2	3919.7	3358.0	2770.6	2186.5	1743.6	1356.8	1108.1	1000.6	983.7	942.0
10°	4182.8	3822.6	3016.2	2183.3	1466.0	1051.1	808.8	680.4	633.1	625.1	611.4
12.5°	4186.0	3707.8	2636.6	1616.8	977.3	702.9	584.9	542.4	529.6	528.8	528.8
15°	4195.7	3587.5	2242.7	1165.1	702.1	556.9	513.5	496.7	491.9	494.3	493.5
17.5°	4195.7	3445.4	1855.9	868.2	567.3	500.7	476.6	465.4	463.8	466.2	467.0
20°	4165.2	3272.9	1501.3	675.6	503.1	464.6	442.9	432.5	428.5	430.1	430.9
22.5°	4092.2	3061.1	1212.4	559.3	460.6	431.7	408.4	392.4	385.9	386.8	386.8
25°	3978.2	2810.0	948.4	483.8	426.1	396.4	369.1	350.6	346.6	345.8	347.4
27.5°	3832.2	2532.3	755.0	426.1	385.1	357.1	329.8	314.5	311.3	312.1	312.9
30°	3688.6	2244.3	595.4	377.1	339.4	312.9	292.1	284.8	284.8	287.3	288.1
32.5°	3557.0	1967.5	471.0	334.6	298.5	274.4	262.4	261.6	265.6	267.2	268.0
35°	3443.8	1711.5	390.0	301.7	266.4	245.5	241.5	244.7	249.5	252.8	253.6
37.5°	3363.6	1482.8	341.0	274.4	241.5	224.7	223.9	230.3	236.7	243.9	245.5
40°	3329.9	1289.4	307.3	250.3	221.5	208.6	206.2	215.0	227.1	237.5	239.1
42.5°	3301.8	1131.4	278.4	227.1	205.4	187.0	186.2	197.4	211.8	222.3	224.7
45°	3277.7	1004.6	251.9	202.2	184.5	160.5	162.9	177.3	188.6	199.8	202.2
47.5°	3228.0	900.3	223.1	175.7	152.5	137.2	142.0	154.9	163.7	180.5	182.9
50°	3138.9	815.2	193.4	143.6	124.4	118.8	126.0	134.8	146.0	160.5	162.1
52.5°	3078.8	751.0	167.7	120.4	102.7	104.3	111.5	114.7	121.2	126.8	125.2
55°	3044.3	715.7	146.8	104.3	87.5	92.3	93.9	89.9	86.7	81.0	78.6
57.5°	3040.2	683.6	130.8	90.7	77.0	79.4	73.8	60.2	48.9	42.5	40.9
60°	3033.8	644.3	118.0	76.2	68.2	65.0	53.0	32.9	23.3	21.7	21.7
62.5°	2964.0	583.3	108.3	64.2	57.8	48.9	30.5	15.2	12.8	13.6	13.6
65°	2741.8	498.3	98.7	52.2	45.7	35.3	15.2	8.8	4.8	5.6	5.6
67.5°	2330.9	397.2	88.3	40.1	34.5	22.5	8.8	4.0	0.0	0.0	0.0
70°	1560.6	246.3	74.6	28.1	22.5	13.6	6.4	0.8	0.0	0.0	0.0
72.5°	598.6	133.2	60.2	16.9	14.4	9.6	4.0	0.0	0.0	0.0	0.0
75°	134.8	87.5	41.7	12.0	10.4	6.4	1.6	0.0	0.0	0.0	0.0
77.5°	51.4	63.4	24.1	8.0	7.2	4.0	0.0	0.0	0.0	0.0	0.0
80°	24.9	37.7	11.2	4.8	4.0	1.6	0.0	0.0	0.0	0.0	0.0
82.5°	12.8	14.4	4.8	2.4	1.6	0.0	0.0	0.0	0.0	0.0	0.0
85°	7.2	7.2	2.4	1.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	4.0	2.4	0.8	0.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW EDISON

Report Number: SP1-2408-195-9

Test Date: 08/07/2024

Luminaire Tested: GALN-SB1A-830-U-5WQ

Data in this report applies to families of products including GALN-SB1A-830-U-5WQ.

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2408-195-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/07/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: MCGRAW EDISON
 Catalog Number: **GALN-SB1A-830-U-5WQ**
 Description: GALLEON AREA AND ROADWAY LUMINAIRE. (1) 80 CRI, 3000K, 350MA HIGH DENSITY LIGHTSQUARE WITH 26 LEDS AND TYPE V WIDE OPTICS

Spectral Parameters

CCT (K): 3050
 CIE u' : 0.2476
 CIE v' : 0.5251
 Duv: 0.0034
 CIE x: 0.4383
 CIE y: 0.4131
 CIE z: 0.1487
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 581
 Purity: 55.55201
 R_f: 81.5
 R_g: 99.2

CRI (Ra): 81.0
 R1: 79.6
 R2: 85.6
 R3: 92.0
 R4: 82.6
 R5: 78.9
 R6: 81.7
 R7: 85.2
 R8: 62.0
 R9: 7.1
 R10: 67.0
 R11: 82.7
 R12: 63.2
 R13: 80.3
 R14: 95.0
 R15: 71.7



Test Conditions

Stabilization Time: 20M
 Operation Time: 1H 20M
 Sphere Temperature (°C): 24.2

REPORT NUMBER: SP1-2408-195-9

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2408-195-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2408-195-9

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	168	NR	620	940	NR	750	35	NR	880	1	NR
365	0	NR	495	233	NR	625	897	NR	755	30	NR	885	1	NR
370	0	NR	500	300	NR	630	847	NR	760	26	NR	890	1	NR
375	0	NR	505	372	NR	635	790	NR	765	22	NR	895	1	NR
380	0	NR	510	430	NR	640	730	NR	770	19	NR	900	1	NR
385	0	NR	515	483	NR	645	668	NR	775	16	NR	905	1	NR
390	0	NR	520	524	NR	650	605	NR	780	14	NR	910	0	NR
395	2	NR	525	555	NR	655	545	NR	785	12	NR	915	0	NR
400	4	NR	530	581	NR	660	485	NR	790	10	NR	920	0	NR
405	7	NR	535	604	NR	665	430	NR	795	9	NR	925	0	NR
410	17	NR	540	623	NR	670	378	NR	800	8	NR	930	0	NR
415	34	NR	545	645	NR	675	331	NR	805	7	NR	935	0	NR
420	68	NR	550	667	NR	680	290	NR	810	6	NR	940	0	NR
425	128	NR	555	693	NR	685	251	NR	815	5	NR	945	0	NR
430	214	NR	560	719	NR	690	218	NR	820	4	NR	950	0	NR
435	339	NR	565	754	NR	695	188	NR	825	4	NR	955	0	NR
440	507	NR	570	791	NR	700	162	NR	830	3	NR	960	0	NR
445	573	NR	575	830	NR	705	139	NR	835	3	NR	965	0	NR
450	356	NR	580	873	NR	710	119	NR	840	3	NR	970	0	NR
455	217	NR	585	913	NR	715	102	NR	845	2	NR	975	0	NR
460	168	NR	590	948	NR	720	88	NR	850	2	NR	980	0	NR
465	113	NR	595	974	NR	725	76	NR	855	2	NR	985	0	NR
470	85	NR	600	994	NR	730	65	NR	860	1	NR	990	0	NR
475	85	NR	605	998	NR	735	55	NR	865	1	NR	995	0	NR
480	94	NR	610	994	NR	740	47	NR	870	1	NR	1000	0	NR
485	120	NR	615	973	NR	745	41	NR	875	1	NR			

REPORT NUMBER: SP1-2408-195-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.27

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	168	NR	620	940	NR	750	35	NR	880	1	NR
365	0	NR	495	233	NR	625	897	NR	755	30	NR	885	1	NR
370	0	NR	500	300	NR	630	847	NR	760	26	NR	890	1	NR
375	0	NR	505	372	NR	635	790	NR	765	22	NR	895	1	NR
380	0	NR	510	430	NR	640	730	NR	770	19	NR	900	1	NR
385	0	NR	515	483	NR	645	668	NR	775	16	NR	905	1	NR
390	0	NR	520	524	NR	650	605	NR	780	14	NR	910	0	NR
395	2	NR	525	555	NR	655	545	NR	785	12	NR	915	0	NR
400	4	NR	530	581	NR	660	485	NR	790	10	NR	920	0	NR
405	7	NR	535	604	NR	665	430	NR	795	9	NR	925	0	NR
410	17	NR	540	623	NR	670	378	NR	800	8	NR	930	0	NR
415	34	NR	545	645	NR	675	331	NR	805	7	NR	935	0	NR
420	68	NR	550	667	NR	680	290	NR	810	6	NR	940	0	NR
425	128	NR	555	693	NR	685	251	NR	815	5	NR	945	0	NR
430	214	NR	560	719	NR	690	218	NR	820	4	NR	950	0	NR
435	339	NR	565	754	NR	695	188	NR	825	4	NR	955	0	NR
440	507	NR	570	791	NR	700	162	NR	830	3	NR	960	0	NR
445	573	NR	575	830	NR	705	139	NR	835	3	NR	965	0	NR
450	356	NR	580	873	NR	710	119	NR	840	3	NR	970	0	NR
455	217	NR	585	913	NR	715	102	NR	845	2	NR	975	0	NR
460	168	NR	590	948	NR	720	88	NR	850	2	NR	980	0	NR
465	113	NR	595	974	NR	725	76	NR	855	2	NR	985	0	NR
470	85	NR	600	994	NR	730	65	NR	860	1	NR	990	0	NR
475	85	NR	605	998	NR	735	55	NR	865	1	NR	995	0	NR
480	94	NR	610	994	NR	740	47	NR	870	1	NR	1000	0	NR
485	120	NR	615	973	NR	745	41	NR	875	1	NR			

REPORT NUMBER: SP1-2408-195-9

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 2.32

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	168	NR	620	940	NR	750	35	NR	880	1	NR
365	0	NR	495	233	NR	625	897	NR	755	30	NR	885	1	NR
370	0	NR	500	300	NR	630	847	NR	760	26	NR	890	1	NR
375	0	NR	505	372	NR	635	790	NR	765	22	NR	895	1	NR
380	0	NR	510	430	NR	640	730	NR	770	19	NR	900	1	NR
385	0	NR	515	483	NR	645	668	NR	775	16	NR	905	1	NR
390	0	NR	520	524	NR	650	605	NR	780	14	NR	910	0	NR
395	2	NR	525	555	NR	655	545	NR	785	12	NR	915	0	NR
400	4	NR	530	581	NR	660	485	NR	790	10	NR	920	0	NR
405	7	NR	535	604	NR	665	430	NR	795	9	NR	925	0	NR
410	17	NR	540	623	NR	670	378	NR	800	8	NR	930	0	NR
415	34	NR	545	645	NR	675	331	NR	805	7	NR	935	0	NR
420	68	NR	550	667	NR	680	290	NR	810	6	NR	940	0	NR
425	128	NR	555	693	NR	685	251	NR	815	5	NR	945	0	NR
430	214	NR	560	719	NR	690	218	NR	820	4	NR	950	0	NR
435	339	NR	565	754	NR	695	188	NR	825	4	NR	955	0	NR
440	507	NR	570	791	NR	700	162	NR	830	3	NR	960	0	NR
445	573	NR	575	830	NR	705	139	NR	835	3	NR	965	0	NR
450	356	NR	580	873	NR	710	119	NR	840	3	NR	970	0	NR
455	217	NR	585	913	NR	715	102	NR	845	2	NR	975	0	NR
460	168	NR	590	948	NR	720	88	NR	850	2	NR	980	0	NR
465	113	NR	595	974	NR	725	76	NR	855	2	NR	985	0	NR
470	85	NR	600	994	NR	730	65	NR	860	1	NR	990	0	NR
475	85	NR	605	998	NR	735	55	NR	865	1	NR	995	0	NR
480	94	NR	610	994	NR	740	47	NR	870	1	NR	1000	0	NR
485	120	NR	615	973	NR	745	41	NR	875	1	NR			

REPORT NUMBER: SP1-2408-195-9

TM-30-18

Summary

$R_f = 81.5$
 $R_g = 99.2$
 $CIE R_a = 81.0$
 $R_9 = 7.1$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 74	CES51 = 89	CES76 = 70
CES02 = 63	CES27 = 88	CES52 = 92	CES77 = 86
CES03 = 31	CES28 = 89	CES53 = 81	CES78 = 72
CES04 = 70	CES29 = 67	CES54 = 87	CES79 = 90
CES05 = 50	CES30 = 68	CES55 = 85	CES80 = 88
CES06 = 51	CES31 = 71	CES56 = 78	CES81 = 78
CES07 = 42	CES32 = 70	CES57 = 76	CES82 = 95
CES08 = 41	CES33 = 71	CES58 = 78	CES83 = 90
CES09 = 29	CES34 = 82	CES59 = 92	CES84 = 94
CES10 = 76	CES35 = 90	CES60 = 95	CES85 = 86
CES11 = 59	CES36 = 93	CES61 = 93	CES86 = 72
CES12 = 65	CES37 = 87	CES62 = 83	CES87 = 85
CES13 = 43	CES38 = 75	CES63 = 77	CES88 = 83
CES14 = 74	CES39 = 94	CES64 = 83	CES89 = 75
CES15 = 71	CES40 = 89	CES65 = 77	CES90 = 81
CES16 = 47	CES41 = 85	CES66 = 80	CES91 = 96
CES17 = 50	CES42 = 86	CES67 = 79	CES92 = 73
CES18 = 56	CES43 = 81	CES68 = 84	CES93 = 84
CES19 = 72	CES44 = 99	CES69 = 91	CES94 = 64
CES20 = 66	CES45 = 87	CES70 = 78	CES95 = 80
CES21 = 87	CES46 = 82	CES71 = 76	CES96 = 84
CES22 = 79	CES47 = 77	CES72 = 92	CES97 = 87
CES23 = 92	CES48 = 71	CES73 = 71	CES98 = 81
CES24 = 91	CES49 = 81	CES74 = 93	CES99 = 74
CES25 = 72	CES50 = 89	CES75 = 74	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)