

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P320150

Luminaire Tested: **GLEON-SA6A-830-U-SL4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P320150
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-24)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GLEON-SA6A-830-U-SL4
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(6) 80 CRI, 3000K, 615mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV SPILL
LIGHT ELIMINATOR OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 21047 lumens
Efficiency: N/A
Efficacy: 109.1 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B2 - U0 - G5


Input Watts (W): 193
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P320150
 CATALOG NUMBER: GLEON-SA6A-830-U-SL4

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 6 fc
 Type IV - Short - N/A

REPORT NUMBER: P320150
CATALOG NUMBER: GLEON-SA6A-830-U-SL4

Luminous Intensity Polar Plot



REPORT NUMBER: P320150

CATALOG NUMBER: GLEON-SA6A-830-U-SL4

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2895.9	0.0	2895.9
	% Fixture	13.8	0.0	13.8
Street Side	Lumens	18151.1	0.0	18151.1
	% Fixture	86.2	0.0	86.2
Total	Lumens	21047.0	0.0	21047.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	326.6	1.6
10°-20°	837.1	4.0
20°-30°	1289.8	6.1
30°-40°	1875.5	8.9
40°-50°	2760.4	13.1
50°-60°	3876.5	18.4
60°-70°	4906.5	23.3
70°-80°	4320.4	20.5
80°-90°	854.2	4.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	21047.0	100.0
0°-180°	21047.0	100.0

Coefficient of Utilization



REPORT NUMBER: P320150


CATALOG NUMBER: GLEON-SA6A-830-U-SL4

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1637.7	7.8			
FM	(30°-60°)	7126.7	33.9			
FH	(60°-80°)	8590.3	40.8			G4/12000
FVH	(80°-90°)	796.4	3.8			G5
BL	(0°-30°)	815.7	3.9	B2/1000		
BM	(30°-60°)	1385.8	6.6	B2/2500		
BH	(60°-80°)	636.6	3.0	B2/1000		G2/1000
BVH	(80°-90°)	57.8	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G5

Type IV Short





REPORT NUMBER: P320150

CATALOG NUMBER: GLEON-SA6A-830-U-SL4

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	37°	45°	55°	65°	75°	85°
0°	3708.4	3708.4	3708.4	3708.4	3708.4	3708.4	3708.4	3708.4	3708.4	3708.4	3708.4
2.5°	3835.2	3835.9	3835.2	3829.2	3815.2	3803.3	3793.7	3779.6	3748.4	3724.7	3689.1
5°	3871.5	3867.1	3864.1	3853.0	3830.7	3817.4	3798.8	3772.2	3721.0	3673.6	3615.7
7.5°	3854.5	3849.3	3842.6	3829.2	3804.0	3792.9	3767.0	3732.1	3670.6	3608.3	3525.3
10°	3801.8	3800.3	3797.4	3794.4	3772.9	3764.0	3740.3	3703.2	3642.4	3566.8	3469.7
12.5°	3743.2	3747.0	3758.8	3774.4	3764.7	3760.3	3745.5	3720.3	3658.0	3576.4	3459.3
15°	3706.2	3716.6	3748.4	3789.2	3797.4	3795.9	3792.2	3775.9	3709.9	3619.4	3483.0
17.5°	3693.6	3710.6	3771.4	3838.9	3862.6	3867.8	3869.3	3841.1	3767.7	3672.1	3507.5
20°	3716.6	3738.1	3827.0	3919.7	3957.5	3960.5	3953.8	3904.9	3822.6	3717.3	3520.8
22.5°	3786.2	3805.5	3916.7	4021.3	4064.3	4068.7	4048.7	3974.6	3880.4	3770.7	3539.4
25°	3920.4	3944.2	4055.4	4159.9	4182.1	4182.9	4154.0	4062.0	3956.0	3845.6	3579.4
27.5°	4095.4	4119.1	4219.2	4321.5	4309.7	4303.0	4263.7	4171.8	4054.6	3948.6	3650.6
30°	4290.4	4316.3	4411.2	4483.9	4455.7	4442.4	4410.5	4291.9	4191.8	4089.5	3759.6
32.5°	4492.0	4515.8	4598.8	4648.5	4612.9	4607.0	4558.8	4450.5	4370.5	4304.5	3936.0
35°	4698.9	4715.9	4797.5	4825.7	4778.2	4776.7	4763.4	4664.0	4613.6	4644.8	4192.5
37.5°	4910.2	4914.6	4984.3	4985.8	4971.7	4977.6	4991.7	4929.5	4943.5	5040.7	4526.1
40°	5098.5	5110.4	5160.8	5176.3	5200.8	5221.6	5292.0	5251.2	5360.2	5532.2	4941.3
42.5°	5237.9	5260.9	5341.7	5381.7	5461.0	5493.7	5593.0	5630.8	5850.3	6108.3	5435.1
45°	5355.8	5391.3	5521.1	5603.4	5737.6	5794.7	5937.0	6063.8	6404.1	6733.2	5954.8
47.5°	5483.3	5528.5	5690.9	5848.0	6030.4	6094.9	6353.7	6543.4	6995.0	7361.9	6444.8
50°	5670.8	5705.7	5864.3	6111.2	6338.8	6421.9	6780.0	7052.0	7595.5	7961.0	6869.7
52.5°	5932.6	5919.2	6053.4	6399.6	6705.1	6807.4	7235.2	7593.2	8204.1	8502.9	7228.5
55°	6195.7	6173.5	6267.7	6701.4	7132.1	7239.6	7736.3	8136.7	8783.2	8990.8	7503.5
57.5°	6488.6	6446.3	6525.7	7041.7	7618.5	7746.7	8297.6	8714.2	9352.6	9385.2	7678.5
60°	6790.3	6733.2	6822.2	7463.5	8236.0	8387.3	8954.4	9277.7	9889.3	9701.0	7734.9
62.5°	7054.3	7014.2	7151.4	7934.3	8932.2	9098.3	9599.4	9876.7	10418.7	9832.2	7531.7
65°	7284.8	7291.5	7528.7	8463.6	9708.4	9885.6	10339.3	10615.1	10835.3	9754.4	7056.5
67.5°	7559.9	7597.7	8002.5	9160.5	10685.6	10879.8	11415.8	11420.3	11068.1	9297.7	6120.9
70°	7961.0	8038.8	8654.2	10127.3	12074.9	12341.8	12755.5	11893.3	10741.2	8059.6	4816.0
72.5°	8316.8	8462.2	9347.4	11233.4	13768.2	13970.6	13539.1	11620.4	9374.8	6040.1	3000.4
74°	8172.3	8352.4	9473.4	11778.4	14405.8	14502.9	13274.5	10824.2	7816.4	4182.9	1743.7
75°	7860.9	8056.6	9289.5	11773.2	14325.0	14270.9	12635.4	9914.5	6437.4	2852.8	1160.3
77.5°	6344.0	6550.9	7827.5	10090.2	11745.7	11694.6	9706.2	6651.0	2819.5	935.6	589.4
80°	3688.4	3846.3	4859.0	6407.8	7920.2	8012.9	6383.3	3291.0	1109.1	525.6	399.6
82.5°	1638.5	1747.4	2347.2	3271.0	4779.7	4899.1	3342.9	1724.5	685.0	319.5	240.2
85°	1075.0	1155.8	1424.9	1557.6	2276.0	2357.6	1636.2	1342.6	452.2	175.7	176.4
87.5°	773.3	851.1	1058.7	924.5	1044.6	989.0	890.4	1242.6	181.6	100.1	59.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320150

CATALOG NUMBER: GLEON-SA6A-830-U-SL4

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	3708.4	3708.4	3708.4	3708.4	3708.4	3708.4	3708.4	3708.4	3708.4	3708.4	3708.4
2.5°	3673.6	3661.7	3635.0	3584.6	3556.4	3532.7	3493.4	3470.4	3460.0	3459.3	3463.7
5°	3582.4	3554.9	3486.0	3401.5	3334.0	3272.5	3196.1	3150.1	3117.5	3098.2	3103.4
7.5°	3476.3	3433.3	3325.1	3190.2	3081.9	2962.6	2844.7	2774.3	2719.4	2678.6	2686.0
10°	3403.7	3344.4	3186.5	2992.2	2812.1	2638.6	2476.2	2379.1	2302.0	2242.7	2247.1
12.5°	3379.2	3299.2	3080.4	2821.0	2568.2	2330.9	2118.9	1969.9	1890.5	1823.1	1828.3
15°	3382.9	3275.4	2991.5	2666.8	2348.7	2049.9	1792.7	1618.4	1510.9	1464.2	1465.0
17.5°	3385.9	3248.0	2898.1	2501.4	2131.5	1787.5	1508.0	1331.5	1230.0	1187.0	1187.7
20°	3376.3	3203.5	2782.4	2311.6	1904.6	1546.5	1275.9	1126.2	1049.1	1015.7	1015.7
22.5°	3363.7	3150.9	2651.9	2121.1	1680.7	1337.5	1109.9	995.7	951.2	929.0	928.2
25°	3369.6	3111.6	2518.5	1925.4	1474.6	1170.6	999.4	923.8	894.1	880.0	879.3
27.5°	3401.5	3093.1	2395.4	1730.4	1294.5	1045.4	925.2	871.9	852.6	843.7	843.7
30°	3459.3	3093.1	2267.2	1564.3	1144.7	952.7	868.2	831.8	818.5	812.6	812.6
32.5°	3560.1	3110.1	2143.3	1399.7	1025.3	880.0	820.7	796.2	785.9	782.9	782.9
35°	3733.6	3167.9	2022.5	1244.0	929.0	820.7	775.5	761.4	754.0	753.2	755.5
37.5°	3977.5	3285.8	1909.1	1129.1	860.7	772.5	737.7	726.6	722.1	725.8	728.8
40°	4284.5	3446.0	1806.0	1025.3	808.8	734.0	702.8	695.4	693.2	698.4	702.8
42.5°	4655.1	3662.4	1721.5	950.5	768.8	701.3	673.2	664.3	662.1	668.0	673.9
45°	5056.2	3895.2	1662.2	894.8	737.7	676.9	647.2	637.6	633.1	636.1	642.8
47.5°	5421.0	4115.4	1638.5	855.6	708.0	656.1	624.2	612.4	605.0	603.5	608.7
50°	5728.7	4279.3	1649.6	831.8	684.3	633.1	602.0	588.7	577.5	570.9	574.6
52.5°	5952.6	4382.3	1660.0	821.5	665.8	607.9	577.5	564.9	550.1	539.0	539.0
55°	6114.9	4406.0	1637.0	813.3	651.7	580.5	550.1	538.2	523.4	510.8	509.3
57.5°	6178.7	4339.3	1551.7	801.4	642.0	554.6	521.2	512.3	499.7	484.9	484.1
60°	6092.7	4133.2	1387.1	776.2	629.4	533.1	492.3	486.3	480.4	466.3	465.6
62.5°	5747.2	3681.0	1174.4	725.1	604.2	510.1	465.6	468.6	469.3	459.7	458.2
65°	5120.7	3059.7	966.8	658.3	566.4	482.6	438.2	452.2	460.4	458.9	456.7
67.5°	4210.3	2381.3	819.2	587.9	516.7	444.8	408.5	424.8	431.5	436.7	435.2
70°	3124.9	1679.2	677.6	513.8	456.7	400.3	370.0	378.1	373.7	379.6	381.8
72.5°	1742.3	1007.5	552.3	439.6	394.4	348.5	327.0	325.5	315.8	315.8	315.8
74°	1045.4	739.2	485.6	393.7	356.6	314.3	295.8	289.1	280.2	281.0	280.2
75°	840.7	635.4	445.6	363.3	329.9	294.3	275.8	266.9	260.2	260.2	259.5
77.5°	530.8	482.6	358.8	289.1	263.9	242.4	229.8	218.0	218.0	217.2	216.5
80°	401.1	384.0	279.5	218.7	202.4	186.1	177.9	172.7	172.7	175.0	174.2
82.5°	275.1	289.1	196.5	152.7	144.6	132.7	131.2	132.0	129.7	126.8	126.0
85°	200.9	217.2	132.7	96.4	88.2	80.8	86.7	89.7	86.0	79.3	76.4
87.5°	77.1	142.3	71.2	40.0	37.1	31.9	37.1	38.6	41.5	32.6	33.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW EDISON

Report Number: SP1-2408-195-9

Test Date: 08/07/2024

Luminaire Tested: GALN-SB1A-830-U-5WQ

Data in this report applies to families of products including GALN-SB1A-830-U-5WQ.

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2408-195-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/07/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: MCGRAW EDISON
 Catalog Number: **GALN-SB1A-830-U-5WQ**
 Description: GALLEON AREA AND ROADWAY LUMINAIRE. (1) 80 CRI, 3000K, 350MA HIGH DENSITY LIGHTSQUARE WITH 26 LEDS AND TYPE V WIDE OPTICS

Spectral Parameters

CCT (K): 3050
 CIE u' : 0.2476
 CIE v' : 0.5251
 Duv: 0.0034
 CIE x: 0.4383
 CIE y: 0.4131
 CIE z: 0.1487
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 581
 Purity: 55.55201
 R_f: 81.5
 R_g: 99.2

CRI (Ra): 81.0
 R1: 79.6
 R2: 85.6
 R3: 92.0
 R4: 82.6
 R5: 78.9
 R6: 81.7
 R7: 85.2
 R8: 62.0
 R9: 7.1
 R10: 67.0
 R11: 82.7
 R12: 63.2
 R13: 80.3
 R14: 95.0
 R15: 71.7



Test Conditions

Stabilization Time: 20M
 Operation Time: 1H 20M
 Sphere Temperature (°C): 24.2

REPORT NUMBER: SP1-2408-195-9

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2408-195-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2408-195-9

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	168	NR	620	940	NR	750	35	NR	880	1	NR
365	0	NR	495	233	NR	625	897	NR	755	30	NR	885	1	NR
370	0	NR	500	300	NR	630	847	NR	760	26	NR	890	1	NR
375	0	NR	505	372	NR	635	790	NR	765	22	NR	895	1	NR
380	0	NR	510	430	NR	640	730	NR	770	19	NR	900	1	NR
385	0	NR	515	483	NR	645	668	NR	775	16	NR	905	1	NR
390	0	NR	520	524	NR	650	605	NR	780	14	NR	910	0	NR
395	2	NR	525	555	NR	655	545	NR	785	12	NR	915	0	NR
400	4	NR	530	581	NR	660	485	NR	790	10	NR	920	0	NR
405	7	NR	535	604	NR	665	430	NR	795	9	NR	925	0	NR
410	17	NR	540	623	NR	670	378	NR	800	8	NR	930	0	NR
415	34	NR	545	645	NR	675	331	NR	805	7	NR	935	0	NR
420	68	NR	550	667	NR	680	290	NR	810	6	NR	940	0	NR
425	128	NR	555	693	NR	685	251	NR	815	5	NR	945	0	NR
430	214	NR	560	719	NR	690	218	NR	820	4	NR	950	0	NR
435	339	NR	565	754	NR	695	188	NR	825	4	NR	955	0	NR
440	507	NR	570	791	NR	700	162	NR	830	3	NR	960	0	NR
445	573	NR	575	830	NR	705	139	NR	835	3	NR	965	0	NR
450	356	NR	580	873	NR	710	119	NR	840	3	NR	970	0	NR
455	217	NR	585	913	NR	715	102	NR	845	2	NR	975	0	NR
460	168	NR	590	948	NR	720	88	NR	850	2	NR	980	0	NR
465	113	NR	595	974	NR	725	76	NR	855	2	NR	985	0	NR
470	85	NR	600	994	NR	730	65	NR	860	1	NR	990	0	NR
475	85	NR	605	998	NR	735	55	NR	865	1	NR	995	0	NR
480	94	NR	610	994	NR	740	47	NR	870	1	NR	1000	0	NR
485	120	NR	615	973	NR	745	41	NR	875	1	NR			

REPORT NUMBER: SP1-2408-195-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.27

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	168	NR	620	940	NR	750	35	NR	880	1	NR
365	0	NR	495	233	NR	625	897	NR	755	30	NR	885	1	NR
370	0	NR	500	300	NR	630	847	NR	760	26	NR	890	1	NR
375	0	NR	505	372	NR	635	790	NR	765	22	NR	895	1	NR
380	0	NR	510	430	NR	640	730	NR	770	19	NR	900	1	NR
385	0	NR	515	483	NR	645	668	NR	775	16	NR	905	1	NR
390	0	NR	520	524	NR	650	605	NR	780	14	NR	910	0	NR
395	2	NR	525	555	NR	655	545	NR	785	12	NR	915	0	NR
400	4	NR	530	581	NR	660	485	NR	790	10	NR	920	0	NR
405	7	NR	535	604	NR	665	430	NR	795	9	NR	925	0	NR
410	17	NR	540	623	NR	670	378	NR	800	8	NR	930	0	NR
415	34	NR	545	645	NR	675	331	NR	805	7	NR	935	0	NR
420	68	NR	550	667	NR	680	290	NR	810	6	NR	940	0	NR
425	128	NR	555	693	NR	685	251	NR	815	5	NR	945	0	NR
430	214	NR	560	719	NR	690	218	NR	820	4	NR	950	0	NR
435	339	NR	565	754	NR	695	188	NR	825	4	NR	955	0	NR
440	507	NR	570	791	NR	700	162	NR	830	3	NR	960	0	NR
445	573	NR	575	830	NR	705	139	NR	835	3	NR	965	0	NR
450	356	NR	580	873	NR	710	119	NR	840	3	NR	970	0	NR
455	217	NR	585	913	NR	715	102	NR	845	2	NR	975	0	NR
460	168	NR	590	948	NR	720	88	NR	850	2	NR	980	0	NR
465	113	NR	595	974	NR	725	76	NR	855	2	NR	985	0	NR
470	85	NR	600	994	NR	730	65	NR	860	1	NR	990	0	NR
475	85	NR	605	998	NR	735	55	NR	865	1	NR	995	0	NR
480	94	NR	610	994	NR	740	47	NR	870	1	NR	1000	0	NR
485	120	NR	615	973	NR	745	41	NR	875	1	NR			

REPORT NUMBER: SP1-2408-195-9

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 2.32

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	168	NR	620	940	NR	750	35	NR	880	1	NR
365	0	NR	495	233	NR	625	897	NR	755	30	NR	885	1	NR
370	0	NR	500	300	NR	630	847	NR	760	26	NR	890	1	NR
375	0	NR	505	372	NR	635	790	NR	765	22	NR	895	1	NR
380	0	NR	510	430	NR	640	730	NR	770	19	NR	900	1	NR
385	0	NR	515	483	NR	645	668	NR	775	16	NR	905	1	NR
390	0	NR	520	524	NR	650	605	NR	780	14	NR	910	0	NR
395	2	NR	525	555	NR	655	545	NR	785	12	NR	915	0	NR
400	4	NR	530	581	NR	660	485	NR	790	10	NR	920	0	NR
405	7	NR	535	604	NR	665	430	NR	795	9	NR	925	0	NR
410	17	NR	540	623	NR	670	378	NR	800	8	NR	930	0	NR
415	34	NR	545	645	NR	675	331	NR	805	7	NR	935	0	NR
420	68	NR	550	667	NR	680	290	NR	810	6	NR	940	0	NR
425	128	NR	555	693	NR	685	251	NR	815	5	NR	945	0	NR
430	214	NR	560	719	NR	690	218	NR	820	4	NR	950	0	NR
435	339	NR	565	754	NR	695	188	NR	825	4	NR	955	0	NR
440	507	NR	570	791	NR	700	162	NR	830	3	NR	960	0	NR
445	573	NR	575	830	NR	705	139	NR	835	3	NR	965	0	NR
450	356	NR	580	873	NR	710	119	NR	840	3	NR	970	0	NR
455	217	NR	585	913	NR	715	102	NR	845	2	NR	975	0	NR
460	168	NR	590	948	NR	720	88	NR	850	2	NR	980	0	NR
465	113	NR	595	974	NR	725	76	NR	855	2	NR	985	0	NR
470	85	NR	600	994	NR	730	65	NR	860	1	NR	990	0	NR
475	85	NR	605	998	NR	735	55	NR	865	1	NR	995	0	NR
480	94	NR	610	994	NR	740	47	NR	870	1	NR	1000	0	NR
485	120	NR	615	973	NR	745	41	NR	875	1	NR			

REPORT NUMBER: SP1-2408-195-9

TM-30-18

Summary

$R_f = 81.5$
 $R_g = 99.2$
 $CIE R_a = 81.0$
 $R_g = 7.1$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 74	CES51 = 89	CES76 = 70
CES02 = 63	CES27 = 88	CES52 = 92	CES77 = 86
CES03 = 31	CES28 = 89	CES53 = 81	CES78 = 72
CES04 = 70	CES29 = 67	CES54 = 87	CES79 = 90
CES05 = 50	CES30 = 68	CES55 = 85	CES80 = 88
CES06 = 51	CES31 = 71	CES56 = 78	CES81 = 78
CES07 = 42	CES32 = 70	CES57 = 76	CES82 = 95
CES08 = 41	CES33 = 71	CES58 = 78	CES83 = 90
CES09 = 29	CES34 = 82	CES59 = 92	CES84 = 94
CES10 = 76	CES35 = 90	CES60 = 95	CES85 = 86
CES11 = 59	CES36 = 93	CES61 = 93	CES86 = 72
CES12 = 65	CES37 = 87	CES62 = 83	CES87 = 85
CES13 = 43	CES38 = 75	CES63 = 77	CES88 = 83
CES14 = 74	CES39 = 94	CES64 = 83	CES89 = 75
CES15 = 71	CES40 = 89	CES65 = 77	CES90 = 81
CES16 = 47	CES41 = 85	CES66 = 80	CES91 = 96
CES17 = 50	CES42 = 86	CES67 = 79	CES92 = 73
CES18 = 56	CES43 = 81	CES68 = 84	CES93 = 84
CES19 = 72	CES44 = 99	CES69 = 91	CES94 = 64
CES20 = 66	CES45 = 87	CES70 = 78	CES95 = 80
CES21 = 87	CES46 = 82	CES71 = 76	CES96 = 84
CES22 = 79	CES47 = 77	CES72 = 92	CES97 = 87
CES23 = 92	CES48 = 71	CES73 = 71	CES98 = 81
CES24 = 91	CES49 = 81	CES74 = 93	CES99 = 74
CES25 = 72	CES50 = 89	CES75 = 74	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)