

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P316334

Luminaire Tested: **GLEON-SA0C-830-U-5WQ**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P316334  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: GLEON-SA0C-830-U-5WQ  
Description: GALLEON AREA AND ROADWAY LUMINAIRE  
(10) 80 CRI, 3000K, 1050mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE V WIDE OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 58599 lumens  
Efficiency: N/A  
Efficacy: 105.0 lumens/watt  
Luminous Opening: Rectangular (W 2.5' x L: 1' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B5 - U0 - G5


Input Watts (W): 558  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P316334  
 CATALOG NUMBER: GLEON-SA0C-830-U-5WQ

## Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 7.7 fc  
 Type V - Short - N/A

REPORT NUMBER: P316334  
CATALOG NUMBER: GLEON-SA0C-830-U-5WQ

## Luminous Intensity Polar Plot



REPORT NUMBER: P316334

CATALOG NUMBER: GLEON-SA0C-830-U-5WQ

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 29299.5  | 0.0    | 29299.5 |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Street Side</b> | Lumens    | 29299.5  | 0.0    | 29299.5 |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Total</b>       | Lumens    | 58599.0  | 0.0    | 58599.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 450.1   | 0.8       |
| 10°-20°   | 1314.8  | 2.2       |
| 20°-30°   | 2241.7  | 3.8       |
| 30°-40°   | 3502.7  | 6.0       |
| 40°-50°   | 5936.3  | 10.1      |
| 50°-60°   | 10825.4 | 18.5      |
| 60°-70°   | 18636.6 | 31.8      |
| 70°-80°   | 14608.1 | 24.9      |
| 80°-90°   | 1083.2  | 1.8       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 58599.0 | 100.0     |
| 0°-180°   | 58599.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P316334


CATALOG NUMBER: GLEON-SA0C-830-U-5WQ

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |        |
|------|-------------|---------|-----------|-------------------------|------|--------|
|      |             |         |           | B                       | U    | G      |
| FL   | (0°-30°)    | 2003.3  | 3.4       |                         |      |        |
| FM   | (30°-60°)   | 10132.2 | 17.3      |                         |      |        |
| FH   | (60°-80°)   | 16622.4 | 28.4      |                         |      | G5     |
| FVH  | (80°-90°)   | 541.6   | 0.9       |                         |      | G4/750 |
| BL   | (0°-30°)    | 2003.3  | 3.4       | B3/2500                 |      |        |
| BM   | (30°-60°)   | 10132.2 | 17.3      | B5                      |      |        |
| BH   | (60°-80°)   | 16622.4 | 28.4      | B5                      |      | G5     |
| BVH  | (80°-90°)   | 541.6   | 0.9       |                         |      | G4/750 |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |        |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |        |

**BUG Rating: B5-U0-G5**

Type V Short



REPORT NUMBER: P316334

CATALOG NUMBER: GLEON-SA0C-830-U-5WQ

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 15°     | 25°     | 35°     | 45°     | 55°     | 65°     | 75°     | 85°     | 90°     |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 4822.7  | 4822.7  | 4822.7  | 4822.7  | 4822.7  | 4822.7  | 4822.7  | 4822.7  | 4822.7  | 4822.7  | 4822.7  |
| 2.5°  | 4801.4  | 4807.2  | 4801.4  | 4805.3  | 4795.6  | 4799.4  | 4799.4  | 4799.4  | 4797.5  | 4799.4  | 4795.6  |
| 5°    | 4758.7  | 4762.6  | 4754.9  | 4758.7  | 4752.9  | 4758.7  | 4760.7  | 4758.7  | 4754.9  | 4756.8  | 4749.0  |
| 7.5°  | 4694.8  | 4698.6  | 4692.8  | 4698.6  | 4690.9  | 4700.6  | 4698.6  | 4692.8  | 4687.0  | 4687.0  | 4679.3  |
| 10°   | 4659.9  | 4661.8  | 4646.3  | 4640.5  | 4623.1  | 4626.9  | 4632.7  | 4638.6  | 4644.4  | 4656.0  | 4654.1  |
| 12.5° | 4661.8  | 4661.8  | 4638.6  | 4613.4  | 4588.2  | 4594.0  | 4603.7  | 4625.0  | 4648.3  | 4669.6  | 4671.5  |
| 15°   | 4681.2  | 4679.3  | 4644.4  | 4603.7  | 4586.2  | 4603.7  | 4609.5  | 4623.1  | 4659.9  | 4696.7  | 4698.6  |
| 17.5° | 4694.8  | 4694.8  | 4640.5  | 4594.0  | 4592.0  | 4619.2  | 4617.2  | 4623.1  | 4663.8  | 4718.0  | 4720.0  |
| 20°   | 4720.0  | 4720.0  | 4650.2  | 4599.8  | 4599.8  | 4628.9  | 4630.8  | 4640.5  | 4681.2  | 4741.3  | 4751.0  |
| 22.5° | 4776.2  | 4778.1  | 4704.5  | 4663.8  | 4667.6  | 4685.1  | 4690.9  | 4706.4  | 4743.2  | 4809.1  | 4820.8  |
| 25°   | 4855.7  | 4859.5  | 4783.9  | 4760.7  | 4774.2  | 4807.2  | 4803.3  | 4815.0  | 4855.7  | 4919.6  | 4931.3  |
| 27.5° | 4966.1  | 4956.5  | 4886.7  | 4877.0  | 4890.5  | 4913.8  | 4911.9  | 4913.8  | 4946.8  | 5004.9  | 5018.5  |
| 30°   | 5109.6  | 5105.7  | 5055.3  | 5061.1  | 5055.3  | 5047.6  | 5049.5  | 5065.0  | 5082.4  | 5129.0  | 5142.5  |
| 32.5° | 5249.2  | 5253.0  | 5222.0  | 5251.1  | 5293.7  | 5322.8  | 5278.2  | 5235.6  | 5216.2  | 5241.4  | 5253.0  |
| 35°   | 5501.1  | 5510.8  | 5462.4  | 5443.0  | 5501.1  | 5586.4  | 5460.4  | 5390.7  | 5429.4  | 5462.4  | 5472.1  |
| 37.5° | 5929.5  | 5935.3  | 5853.9  | 5776.4  | 5733.7  | 5815.2  | 5689.2  | 5695.0  | 5830.7  | 5892.7  | 5890.8  |
| 40°   | 6418.0  | 6419.9  | 6365.7  | 6297.8  | 6224.2  | 6243.5  | 6193.1  | 6208.7  | 6297.8  | 6354.0  | 6369.5  |
| 42.5° | 6999.5  | 6993.7  | 6908.4  | 6811.5  | 6790.2  | 6809.6  | 6724.3  | 6712.6  | 6815.4  | 6916.2  | 6918.1  |
| 45°   | 7753.5  | 7740.0  | 7629.5  | 7522.9  | 7420.1  | 7377.5  | 7356.2  | 7412.4  | 7553.9  | 7646.9  | 7648.9  |
| 47.5° | 8565.7  | 8528.9  | 8470.7  | 8385.5  | 8296.3  | 8253.6  | 8218.8  | 8245.9  | 8348.6  | 8385.5  | 8389.3  |
| 50°   | 9401.2  | 9408.9  | 9420.6  | 9387.6  | 9354.7  | 9341.1  | 9250.0  | 9197.6  | 9228.7  | 9160.8  | 9151.1  |
| 52.5° | 10391.7 | 10407.2 | 10519.6 | 10614.6 | 10670.8 | 10699.9 | 10527.4 | 10347.1 | 10246.3 | 10114.5 | 10075.7 |
| 55°   | 11560.5 | 11585.7 | 11750.5 | 12014.1 | 12285.5 | 12428.9 | 12116.9 | 11779.6 | 11467.5 | 11221.3 | 11141.8 |
| 57.5° | 12863.1 | 12907.7 | 13134.5 | 13640.4 | 14196.7 | 14536.0 | 14008.7 | 13396.2 | 12793.4 | 12438.6 | 12376.6 |
| 60°   | 14390.6 | 14433.2 | 14747.2 | 15472.2 | 16373.6 | 16883.3 | 16084.7 | 15082.6 | 14332.4 | 13993.2 | 13878.8 |
| 62.5° | 16208.8 | 16212.7 | 16598.4 | 17445.5 | 18635.6 | 19345.1 | 18263.5 | 16924.1 | 16150.6 | 15741.6 | 15631.1 |
| 65°   | 18164.6 | 18174.3 | 18573.6 | 19488.5 | 20719.4 | 21490.9 | 20269.7 | 18874.1 | 17928.1 | 17325.3 | 17240.0 |
| 67.5° | 19546.7 | 19587.4 | 20008.0 | 21109.0 | 22260.4 | 22956.3 | 21692.5 | 20114.6 | 19021.4 | 18302.2 | 18230.5 |
| 70°   | 19325.7 | 19484.7 | 19979.0 | 21264.1 | 22865.2 | 23857.7 | 21923.2 | 19967.3 | 18525.2 | 17676.1 | 17616.1 |
| 72.5° | 16854.3 | 17158.6 | 17817.6 | 19504.0 | 22064.7 | 23431.2 | 20665.1 | 17883.6 | 16251.4 | 15528.4 | 15419.9 |
| 75°   | 11477.2 | 11971.5 | 12965.9 | 15398.5 | 18850.8 | 20287.2 | 17397.0 | 14258.8 | 12723.6 | 11723.4 | 11649.7 |
| 77.5° | 5117.3  | 5229.8  | 6489.7  | 9290.7  | 13008.5 | 14568.9 | 12640.2 | 9327.5  | 7001.5  | 5584.5  | 5286.0  |
| 80°   | 1426.7  | 1444.1  | 1926.8  | 3460.0  | 6511.0  | 8559.9  | 6989.8  | 3634.5  | 2043.1  | 1440.2  | 1356.9  |
| 82.5° | 453.6   | 492.4   | 600.9   | 897.5   | 2188.4  | 3905.8  | 2246.6  | 969.2   | 690.1   | 550.5   | 496.2   |
| 85°   | 221.0   | 219.0   | 304.3   | 364.4   | 558.3   | 864.5   | 595.1   | 449.7   | 393.5   | 261.7   | 236.5   |
| 87.5° | 93.0    | 95.0    | 141.5   | 127.9   | 162.8   | 139.6   | 191.9   | 201.6   | 211.3   | 116.3   | 100.8   |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW EDISON

Report Number: SP1-2408-195-9

Test Date: 08/07/2024

Luminaire Tested: GALN-SB1A-830-U-5WQ

Data in this report applies to families of products including GALN-SB1A-830-U-5WQ.

### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2408-195-9  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 08/07/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: MCGRAW EDISON  
 Catalog Number: **GALN-SB1A-830-U-5WQ**  
 Description: GALLEON AREA AND ROADWAY LUMINAIRE. (1) 80 CRI, 3000K, 350MA HIGH DENSITY LIGHTSQUARE WITH 26 LEDS AND TYPE V WIDE OPTICS

### Spectral Parameters

CCT (K): 3050  
 CIE  $u'$ : 0.2476  
 CIE  $v'$ : 0.5251  
 Duv: 0.0034  
 CIE x: 0.4383  
 CIE y: 0.4131  
 CIE z: 0.1487  
 Peak Wavelength (nm): 603  
 Dominant Wavelength (nm): 581  
 Purity: 55.55201  
 R<sub>f</sub>: 81.5  
 R<sub>g</sub>: 99.2

CRI (Ra): 81.0  
 R1: 79.6  
 R2: 85.6  
 R3: 92.0  
 R4: 82.6  
 R5: 78.9  
 R6: 81.7  
 R7: 85.2  
 R8: 62.0  
 R9: 7.1  
 R10: 67.0  
 R11: 82.7  
 R12: 63.2  
 R13: 80.3  
 R14: 95.0  
 R15: 71.7



### Test Conditions

Stabilization Time: 20M  
 Operation Time: 1H 20M  
 Sphere Temperature (°C): 24.2

REPORT NUMBER: SP1-2408-195-9

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2408-195-9

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2408-195-9

### Photopic Flux vs. Wavelength



### Photopic Lumens: NR

| $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|
| 360               | 0                                      | NR                             | 490               | 168                                    | NR                             | 620               | 940                                    | NR                             | 750               | 35                                     | NR                             | 880               | 1                                      | NR                             |
| 365               | 0                                      | NR                             | 495               | 233                                    | NR                             | 625               | 897                                    | NR                             | 755               | 30                                     | NR                             | 885               | 1                                      | NR                             |
| 370               | 0                                      | NR                             | 500               | 300                                    | NR                             | 630               | 847                                    | NR                             | 760               | 26                                     | NR                             | 890               | 1                                      | NR                             |
| 375               | 0                                      | NR                             | 505               | 372                                    | NR                             | 635               | 790                                    | NR                             | 765               | 22                                     | NR                             | 895               | 1                                      | NR                             |
| 380               | 0                                      | NR                             | 510               | 430                                    | NR                             | 640               | 730                                    | NR                             | 770               | 19                                     | NR                             | 900               | 1                                      | NR                             |
| 385               | 0                                      | NR                             | 515               | 483                                    | NR                             | 645               | 668                                    | NR                             | 775               | 16                                     | NR                             | 905               | 1                                      | NR                             |
| 390               | 0                                      | NR                             | 520               | 524                                    | NR                             | 650               | 605                                    | NR                             | 780               | 14                                     | NR                             | 910               | 0                                      | NR                             |
| 395               | 2                                      | NR                             | 525               | 555                                    | NR                             | 655               | 545                                    | NR                             | 785               | 12                                     | NR                             | 915               | 0                                      | NR                             |
| 400               | 4                                      | NR                             | 530               | 581                                    | NR                             | 660               | 485                                    | NR                             | 790               | 10                                     | NR                             | 920               | 0                                      | NR                             |
| 405               | 7                                      | NR                             | 535               | 604                                    | NR                             | 665               | 430                                    | NR                             | 795               | 9                                      | NR                             | 925               | 0                                      | NR                             |
| 410               | 17                                     | NR                             | 540               | 623                                    | NR                             | 670               | 378                                    | NR                             | 800               | 8                                      | NR                             | 930               | 0                                      | NR                             |
| 415               | 34                                     | NR                             | 545               | 645                                    | NR                             | 675               | 331                                    | NR                             | 805               | 7                                      | NR                             | 935               | 0                                      | NR                             |
| 420               | 68                                     | NR                             | 550               | 667                                    | NR                             | 680               | 290                                    | NR                             | 810               | 6                                      | NR                             | 940               | 0                                      | NR                             |
| 425               | 128                                    | NR                             | 555               | 693                                    | NR                             | 685               | 251                                    | NR                             | 815               | 5                                      | NR                             | 945               | 0                                      | NR                             |
| 430               | 214                                    | NR                             | 560               | 719                                    | NR                             | 690               | 218                                    | NR                             | 820               | 4                                      | NR                             | 950               | 0                                      | NR                             |
| 435               | 339                                    | NR                             | 565               | 754                                    | NR                             | 695               | 188                                    | NR                             | 825               | 4                                      | NR                             | 955               | 0                                      | NR                             |
| 440               | 507                                    | NR                             | 570               | 791                                    | NR                             | 700               | 162                                    | NR                             | 830               | 3                                      | NR                             | 960               | 0                                      | NR                             |
| 445               | 573                                    | NR                             | 575               | 830                                    | NR                             | 705               | 139                                    | NR                             | 835               | 3                                      | NR                             | 965               | 0                                      | NR                             |
| 450               | 356                                    | NR                             | 580               | 873                                    | NR                             | 710               | 119                                    | NR                             | 840               | 3                                      | NR                             | 970               | 0                                      | NR                             |
| 455               | 217                                    | NR                             | 585               | 913                                    | NR                             | 715               | 102                                    | NR                             | 845               | 2                                      | NR                             | 975               | 0                                      | NR                             |
| 460               | 168                                    | NR                             | 590               | 948                                    | NR                             | 720               | 88                                     | NR                             | 850               | 2                                      | NR                             | 980               | 0                                      | NR                             |
| 465               | 113                                    | NR                             | 595               | 974                                    | NR                             | 725               | 76                                     | NR                             | 855               | 2                                      | NR                             | 985               | 0                                      | NR                             |
| 470               | 85                                     | NR                             | 600               | 994                                    | NR                             | 730               | 65                                     | NR                             | 860               | 1                                      | NR                             | 990               | 0                                      | NR                             |
| 475               | 85                                     | NR                             | 605               | 998                                    | NR                             | 735               | 55                                     | NR                             | 865               | 1                                      | NR                             | 995               | 0                                      | NR                             |
| 480               | 94                                     | NR                             | 610               | 994                                    | NR                             | 740               | 47                                     | NR                             | 870               | 1                                      | NR                             | 1000              | 0                                      | NR                             |
| 485               | 120                                    | NR                             | 615               | 973                                    | NR                             | 745               | 41                                     | NR                             | 875               | 1                                      | NR                             |                   |                                        |                                |

REPORT NUMBER: SP1-2408-195-9

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.27

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 168                                  | NR                             | 620               | 940                                  | NR                             | 750               | 35                                   | NR                             | 880               | 1                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 233                                  | NR                             | 625               | 897                                  | NR                             | 755               | 30                                   | NR                             | 885               | 1                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 300                                  | NR                             | 630               | 847                                  | NR                             | 760               | 26                                   | NR                             | 890               | 1                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 372                                  | NR                             | 635               | 790                                  | NR                             | 765               | 22                                   | NR                             | 895               | 1                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 430                                  | NR                             | 640               | 730                                  | NR                             | 770               | 19                                   | NR                             | 900               | 1                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 483                                  | NR                             | 645               | 668                                  | NR                             | 775               | 16                                   | NR                             | 905               | 1                                    | NR                             |
| 390               | 0                                    | NR                             | 520               | 524                                  | NR                             | 650               | 605                                  | NR                             | 780               | 14                                   | NR                             | 910               | 0                                    | NR                             |
| 395               | 2                                    | NR                             | 525               | 555                                  | NR                             | 655               | 545                                  | NR                             | 785               | 12                                   | NR                             | 915               | 0                                    | NR                             |
| 400               | 4                                    | NR                             | 530               | 581                                  | NR                             | 660               | 485                                  | NR                             | 790               | 10                                   | NR                             | 920               | 0                                    | NR                             |
| 405               | 7                                    | NR                             | 535               | 604                                  | NR                             | 665               | 430                                  | NR                             | 795               | 9                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 17                                   | NR                             | 540               | 623                                  | NR                             | 670               | 378                                  | NR                             | 800               | 8                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 34                                   | NR                             | 545               | 645                                  | NR                             | 675               | 331                                  | NR                             | 805               | 7                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 68                                   | NR                             | 550               | 667                                  | NR                             | 680               | 290                                  | NR                             | 810               | 6                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 128                                  | NR                             | 555               | 693                                  | NR                             | 685               | 251                                  | NR                             | 815               | 5                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 214                                  | NR                             | 560               | 719                                  | NR                             | 690               | 218                                  | NR                             | 820               | 4                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 339                                  | NR                             | 565               | 754                                  | NR                             | 695               | 188                                  | NR                             | 825               | 4                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 507                                  | NR                             | 570               | 791                                  | NR                             | 700               | 162                                  | NR                             | 830               | 3                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 573                                  | NR                             | 575               | 830                                  | NR                             | 705               | 139                                  | NR                             | 835               | 3                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 356                                  | NR                             | 580               | 873                                  | NR                             | 710               | 119                                  | NR                             | 840               | 3                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 217                                  | NR                             | 585               | 913                                  | NR                             | 715               | 102                                  | NR                             | 845               | 2                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 168                                  | NR                             | 590               | 948                                  | NR                             | 720               | 88                                   | NR                             | 850               | 2                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 113                                  | NR                             | 595               | 974                                  | NR                             | 725               | 76                                   | NR                             | 855               | 2                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 85                                   | NR                             | 600               | 994                                  | NR                             | 730               | 65                                   | NR                             | 860               | 1                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 85                                   | NR                             | 605               | 998                                  | NR                             | 735               | 55                                   | NR                             | 865               | 1                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 94                                   | NR                             | 610               | 994                                  | NR                             | 740               | 47                                   | NR                             | 870               | 1                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 120                                  | NR                             | 615               | 973                                  | NR                             | 745               | 41                                   | NR                             | 875               | 1                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2408-195-9

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.32

| $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|
| 360               | 0                                      | NR                             | 490               | 168                                    | NR                             | 620               | 940                                    | NR                             | 750               | 35                                     | NR                             | 880               | 1                                      | NR                             |
| 365               | 0                                      | NR                             | 495               | 233                                    | NR                             | 625               | 897                                    | NR                             | 755               | 30                                     | NR                             | 885               | 1                                      | NR                             |
| 370               | 0                                      | NR                             | 500               | 300                                    | NR                             | 630               | 847                                    | NR                             | 760               | 26                                     | NR                             | 890               | 1                                      | NR                             |
| 375               | 0                                      | NR                             | 505               | 372                                    | NR                             | 635               | 790                                    | NR                             | 765               | 22                                     | NR                             | 895               | 1                                      | NR                             |
| 380               | 0                                      | NR                             | 510               | 430                                    | NR                             | 640               | 730                                    | NR                             | 770               | 19                                     | NR                             | 900               | 1                                      | NR                             |
| 385               | 0                                      | NR                             | 515               | 483                                    | NR                             | 645               | 668                                    | NR                             | 775               | 16                                     | NR                             | 905               | 1                                      | NR                             |
| 390               | 0                                      | NR                             | 520               | 524                                    | NR                             | 650               | 605                                    | NR                             | 780               | 14                                     | NR                             | 910               | 0                                      | NR                             |
| 395               | 2                                      | NR                             | 525               | 555                                    | NR                             | 655               | 545                                    | NR                             | 785               | 12                                     | NR                             | 915               | 0                                      | NR                             |
| 400               | 4                                      | NR                             | 530               | 581                                    | NR                             | 660               | 485                                    | NR                             | 790               | 10                                     | NR                             | 920               | 0                                      | NR                             |
| 405               | 7                                      | NR                             | 535               | 604                                    | NR                             | 665               | 430                                    | NR                             | 795               | 9                                      | NR                             | 925               | 0                                      | NR                             |
| 410               | 17                                     | NR                             | 540               | 623                                    | NR                             | 670               | 378                                    | NR                             | 800               | 8                                      | NR                             | 930               | 0                                      | NR                             |
| 415               | 34                                     | NR                             | 545               | 645                                    | NR                             | 675               | 331                                    | NR                             | 805               | 7                                      | NR                             | 935               | 0                                      | NR                             |
| 420               | 68                                     | NR                             | 550               | 667                                    | NR                             | 680               | 290                                    | NR                             | 810               | 6                                      | NR                             | 940               | 0                                      | NR                             |
| 425               | 128                                    | NR                             | 555               | 693                                    | NR                             | 685               | 251                                    | NR                             | 815               | 5                                      | NR                             | 945               | 0                                      | NR                             |
| 430               | 214                                    | NR                             | 560               | 719                                    | NR                             | 690               | 218                                    | NR                             | 820               | 4                                      | NR                             | 950               | 0                                      | NR                             |
| 435               | 339                                    | NR                             | 565               | 754                                    | NR                             | 695               | 188                                    | NR                             | 825               | 4                                      | NR                             | 955               | 0                                      | NR                             |
| 440               | 507                                    | NR                             | 570               | 791                                    | NR                             | 700               | 162                                    | NR                             | 830               | 3                                      | NR                             | 960               | 0                                      | NR                             |
| 445               | 573                                    | NR                             | 575               | 830                                    | NR                             | 705               | 139                                    | NR                             | 835               | 3                                      | NR                             | 965               | 0                                      | NR                             |
| 450               | 356                                    | NR                             | 580               | 873                                    | NR                             | 710               | 119                                    | NR                             | 840               | 3                                      | NR                             | 970               | 0                                      | NR                             |
| 455               | 217                                    | NR                             | 585               | 913                                    | NR                             | 715               | 102                                    | NR                             | 845               | 2                                      | NR                             | 975               | 0                                      | NR                             |
| 460               | 168                                    | NR                             | 590               | 948                                    | NR                             | 720               | 88                                     | NR                             | 850               | 2                                      | NR                             | 980               | 0                                      | NR                             |
| 465               | 113                                    | NR                             | 595               | 974                                    | NR                             | 725               | 76                                     | NR                             | 855               | 2                                      | NR                             | 985               | 0                                      | NR                             |
| 470               | 85                                     | NR                             | 600               | 994                                    | NR                             | 730               | 65                                     | NR                             | 860               | 1                                      | NR                             | 990               | 0                                      | NR                             |
| 475               | 85                                     | NR                             | 605               | 998                                    | NR                             | 735               | 55                                     | NR                             | 865               | 1                                      | NR                             | 995               | 0                                      | NR                             |
| 480               | 94                                     | NR                             | 610               | 994                                    | NR                             | 740               | 47                                     | NR                             | 870               | 1                                      | NR                             | 1000              | 0                                      | NR                             |
| 485               | 120                                    | NR                             | 615               | 973                                    | NR                             | 745               | 41                                     | NR                             | 875               | 1                                      | NR                             |                   |                                        |                                |

REPORT NUMBER: SP1-2408-195-9

TM-30-18

### Summary

$R_f = 81.5$   
 $R_g = 99.2$   
 $CIE R_a = 81.0$   
 $R_9 = 7.1$



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 74 | CES51 = 89 | CES76 = 70 |
| CES02 = 63 | CES27 = 88 | CES52 = 92 | CES77 = 86 |
| CES03 = 31 | CES28 = 89 | CES53 = 81 | CES78 = 72 |
| CES04 = 70 | CES29 = 67 | CES54 = 87 | CES79 = 90 |
| CES05 = 50 | CES30 = 68 | CES55 = 85 | CES80 = 88 |
| CES06 = 51 | CES31 = 71 | CES56 = 78 | CES81 = 78 |
| CES07 = 42 | CES32 = 70 | CES57 = 76 | CES82 = 95 |
| CES08 = 41 | CES33 = 71 | CES58 = 78 | CES83 = 90 |
| CES09 = 29 | CES34 = 82 | CES59 = 92 | CES84 = 94 |
| CES10 = 76 | CES35 = 90 | CES60 = 95 | CES85 = 86 |
| CES11 = 59 | CES36 = 93 | CES61 = 93 | CES86 = 72 |
| CES12 = 65 | CES37 = 87 | CES62 = 83 | CES87 = 85 |
| CES13 = 43 | CES38 = 75 | CES63 = 77 | CES88 = 83 |
| CES14 = 74 | CES39 = 94 | CES64 = 83 | CES89 = 75 |
| CES15 = 71 | CES40 = 89 | CES65 = 77 | CES90 = 81 |
| CES16 = 47 | CES41 = 85 | CES66 = 80 | CES91 = 96 |
| CES17 = 50 | CES42 = 86 | CES67 = 79 | CES92 = 73 |
| CES18 = 56 | CES43 = 81 | CES68 = 84 | CES93 = 84 |
| CES19 = 72 | CES44 = 99 | CES69 = 91 | CES94 = 64 |
| CES20 = 66 | CES45 = 87 | CES70 = 78 | CES95 = 80 |
| CES21 = 87 | CES46 = 82 | CES71 = 76 | CES96 = 84 |
| CES22 = 79 | CES47 = 77 | CES72 = 92 | CES97 = 87 |
| CES23 = 92 | CES48 = 71 | CES73 = 71 | CES98 = 81 |
| CES24 = 91 | CES49 = 81 | CES74 = 93 | CES99 = 74 |
| CES25 = 72 | CES50 = 89 | CES75 = 74 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**


(END OF REPORT)