

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P318879

Luminaire Tested: **GLEON-SA5B-830-U-T4FT**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P318879
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-16)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GLEON-SA5B-830-U-T4FT
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(5) 80 CRI, 3000K, 800mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV
FORWARD THROW OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 22833 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B3 - U0 - G4


Input Watts (W): 210
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P318879
 CATALOG NUMBER: GLEON-SA5B-830-U-T4FT

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 5.7 fc
 Type IV - Short - N/A

REPORT NUMBER: P318879
CATALOG NUMBER: GLEON-SA5B-830-U-T4FT

Luminous Intensity Polar Plot



REPORT NUMBER: P318879

CATALOG NUMBER: GLEON-SA5B-830-U-T4FT

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4902.8	0.0	4902.8
	% Fixture	21.5	0.0	21.5
Street Side	Lumens	17930.2	0.0	17930.2
	% Fixture	78.5	0.0	78.5
Total	Lumens	22833.0	0.0	22833.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	322.8	1.4
10°-20°	874.2	3.8
20°-30°	1427.7	6.3
30°-40°	2126.1	9.3
40°-50°	3049.4	13.4
50°-60°	4186.4	18.3
60°-70°	5241.2	23.0
70°-80°	4741.5	20.8
80°-90°	863.7	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	22833.0	100.0
0°-180°	22833.0	100.0

Coefficient of Utilization



REPORT NUMBER: P318879


CATALOG NUMBER: GLEON-SA5B-830-U-T4FT

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1311.4	5.7			
FM	(30°-60°)	7002.4	30.7			
FH	(60°-80°)	8928.5	39.1			G4/12000
FVH	(80°-90°)	687.8	3.0			G4/750
BL	(0°-30°)	1313.2	5.8	B3/2500		
BM	(30°-60°)	2359.6	10.3	B2/2500		
BH	(60°-80°)	1054.2	4.6	B3/2500		G3/2500
BVH	(80°-90°)	175.8	0.8			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G4

Type IV Short





REPORT NUMBER: P318879

CATALOG NUMBER: GLEON-SA5B-830-U-T4FT

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	33°	35°	45°	55°	65°	75°	85°
0°	3568.9	3568.9	3568.9	3568.9	3568.9	3568.9	3568.9	3568.9	3568.9	3568.9	3568.9
2.5°	3314.2	3301.6	3325.2	3328.4	3348.9	3356.8	3385.2	3429.3	3465.6	3507.4	3545.3
5°	3013.7	3005.0	3038.1	3061.8	3106.7	3125.7	3192.7	3286.6	3370.2	3464.8	3550.8
7.5°	2728.2	2723.4	2760.5	2814.1	2866.2	2892.2	3008.2	3144.6	3284.2	3437.2	3568.9
10°	2487.6	2486.0	2521.5	2574.4	2650.9	2680.0	2829.9	3009.7	3205.3	3415.9	3599.7
12.5°	2352.7	2358.3	2374.8	2419.0	2490.0	2519.1	2685.6	2896.9	3139.1	3408.8	3644.6
15°	2385.9	2394.5	2366.1	2364.6	2415.0	2437.9	2594.1	2816.5	3091.8	3420.6	3710.1
17.5°	2527.0	2528.6	2453.7	2406.4	2437.1	2449.0	2565.7	2770.7	3064.1	3447.5	3792.1
20°	2725.8	2721.8	2589.3	2510.5	2527.0	2530.2	2605.9	2771.5	3061.8	3494.0	3898.6
22.5°	2989.2	2960.0	2781.8	2674.5	2670.6	2665.8	2709.2	2829.9	3096.5	3569.7	4025.6
25°	3333.1	3305.5	3060.2	2913.5	2882.0	2870.1	2876.4	2954.5	3165.1	3651.0	4167.6
27.5°	3715.6	3667.5	3430.9	3223.5	3158.0	3141.4	3103.6	3130.4	3240.0	3729.0	4336.3
30°	4035.8	4009.8	3803.2	3557.1	3479.8	3456.1	3356.8	3327.6	3348.1	3835.5	4549.3
32.5°	4214.9	4197.5	4072.1	3873.4	3801.6	3768.5	3628.1	3569.7	3521.6	4003.5	4838.0
35°	4431.8	4420.7	4345.0	4200.7	4094.2	4059.5	3950.7	3889.9	3766.1	4234.6	5211.0
37.5°	4707.8	4696.0	4697.6	4580.8	4453.9	4421.5	4349.8	4285.9	4083.2	4538.3	5616.4
40°	5020.2	4997.3	4988.6	4983.1	4902.6	4884.5	4846.6	4759.9	4480.7	4901.1	6016.3
42.5°	5490.2	5409.0	5235.5	5300.9	5380.6	5371.1	5401.9	5277.3	4922.4	5330.1	6406.7
45°	5943.7	5810.4	5510.7	5524.9	5699.2	5752.1	5982.4	5894.1	5401.1	5800.2	6810.5
47.5°	6150.4	6049.4	5794.7	5795.5	5968.2	6077.8	6582.6	6519.5	5904.3	6334.2	7303.5
50°	6381.5	6280.5	6051.8	6137.8	6288.4	6405.1	7162.3	7130.0	6383.1	6918.6	7894.2
52.5°	6633.9	6462.7	6317.6	6471.4	6682.8	6818.4	7742.8	7654.5	6822.4	7507.0	8573.3
55°	6637.0	6590.5	6700.9	6813.7	7130.0	7296.4	8350.9	8117.4	7180.4	8085.1	9126.2
57.5°	7014.8	6939.1	7173.3	7225.4	7638.7	7826.4	8955.8	8520.5	7544.8	8528.4	9424.3
60°	7514.9	7450.2	7641.8	7779.1	8268.1	8518.9	9601.8	8934.5	7831.1	8862.8	9410.1
62.5°	8378.5	8305.1	8302.8	8495.2	9153.8	9445.6	10326.6	9340.7	7944.7	8929.0	9008.7
65°	9642.8	9526.1	9306.0	9397.5	10377.1	10668.1	11136.6	9634.9	7794.8	8574.1	7974.7
67.5°	10873.2	10869.3	10598.7	10786.4	11992.4	12225.8	12059.4	9664.1	7327.1	7338.2	6140.1
70°	12099.6	12115.4	12069.7	12722.7	14174.7	14417.7	13042.2	9272.1	6275.8	5299.4	3678.6
72.5°	13071.3	13067.4	13297.7	14981.6	17007.0	16952.6	13870.3	8084.3	4505.9	2860.7	1758.0
75°	12441.9	12304.7	12990.9	16100.0	18657.8	18392.0	13166.0	5639.3	2338.5	1302.2	946.5
77.5°	8115.1	8245.2	9252.4	13300.1	16320.0	15996.7	9659.4	2631.1	1101.8	854.2	686.2
80°	2938.7	3076.0	4332.4	7533.8	11243.9	11191.0	4756.7	1081.3	745.3	645.2	500.0
82.5°	1011.1	1061.6	1709.1	3345.7	6348.4	6585.0	1789.6	614.4	541.8	457.5	342.3
85°	396.7	454.3	781.6	1609.8	3202.2	3225.8	724.8	367.5	377.0	299.7	187.7
87.5°	150.6	183.0	373.8	747.7	1462.3	1343.2	259.5	175.1	214.5	178.2	89.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P318879

CATALOG NUMBER: GLEON-SA5B-830-U-T4FT

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	3568.9	3568.9	3568.9	3568.9	3568.9	3568.9	3568.9	3568.9	3568.9	3568.9	3568.9
2.5°	3574.4	3591.0	3625.7	3649.4	3674.6	3681.7	3684.9	3691.2	3697.5	3695.1	3695.9
5°	3596.5	3628.9	3684.9	3708.5	3719.6	3707.0	3682.5	3662.8	3648.6	3640.7	3638.3
7.5°	3632.8	3678.6	3738.5	3734.6	3709.3	3653.3	3590.2	3542.9	3503.5	3489.3	3481.4
10°	3680.9	3734.6	3776.4	3731.4	3658.1	3561.0	3466.4	3393.0	3333.9	3311.0	3307.1
12.5°	3742.4	3796.9	3804.8	3709.3	3587.9	3455.4	3326.8	3229.8	3141.4	3113.0	3106.7
15°	3822.1	3873.4	3824.5	3670.7	3501.1	3322.8	3156.4	3024.7	2931.6	2896.9	2884.3
17.5°	3905.7	3954.6	3828.4	3606.8	3387.5	3165.9	2956.9	2822.0	2715.5	2675.3	2670.6
20°	4005.9	4028.0	3811.8	3515.3	3231.4	2962.4	2742.4	2615.4	2558.6	2530.2	2527.0
22.5°	4129.7	4106.0	3774.0	3391.5	3033.4	2727.4	2548.3	2489.2	2475.0	2468.7	2471.0
25°	4260.6	4188.1	3718.0	3229.8	2783.4	2492.3	2406.4	2422.9	2441.9	2439.5	2439.5
27.5°	4405.0	4271.7	3632.0	3015.2	2506.5	2299.9	2310.1	2370.9	2399.3	2398.5	2397.7
30°	4590.3	4366.3	3522.4	2757.3	2247.8	2164.2	2226.5	2300.7	2339.3	2337.7	2338.5
32.5°	4818.2	4470.4	3373.3	2469.5	2060.9	2064.1	2135.8	2209.2	2254.1	2250.2	2251.0
35°	5084.8	4587.2	3171.4	2185.5	1937.1	1984.4	2041.2	2092.5	2135.0	2129.5	2124.0
37.5°	5375.1	4701.5	2903.3	1931.6	1836.1	1910.3	1957.6	1966.3	1986.0	1971.8	1961.5
40°	5651.1	4789.1	2557.8	1723.3	1734.4	1847.2	1877.9	1843.2	1807.7	1803.0	1788.8
42.5°	5891.7	4818.2	2208.4	1556.9	1627.1	1780.9	1799.8	1727.3	1663.4	1633.4	1620.8
45°	6145.7	4828.5	1882.7	1417.3	1523.8	1721.8	1742.3	1645.3	1555.3	1490.7	1469.4
47.5°	6477.7	4902.6	1629.5	1314.0	1444.9	1682.3	1711.5	1579.8	1463.1	1370.8	1351.1
50°	6912.3	5049.3	1423.6	1235.1	1393.7	1656.3	1689.4	1515.9	1387.3	1276.1	1256.4
52.5°	7395.0	5184.2	1257.2	1171.2	1344.0	1610.6	1661.0	1470.2	1316.4	1188.6	1167.3
55°	7732.5	5080.9	1123.1	1105.0	1279.3	1545.1	1621.6	1431.5	1214.6	1103.4	1084.5
57.5°	7797.2	4727.5	1021.4	1036.4	1201.2	1463.1	1560.9	1345.5	1159.4	1066.3	1046.6
60°	7620.5	4235.4	945.7	973.3	1117.6	1359.7	1447.3	1284.8	1106.6	1026.9	1010.3
62.5°	7176.5	3731.4	889.7	916.5	1039.5	1254.8	1376.3	1220.9	1052.9	981.9	965.4
65°	6279.7	3132.8	836.0	866.0	967.0	1164.1	1312.4	1161.8	1000.1	945.7	929.9
67.5°	4740.2	2346.4	785.6	812.4	902.3	1085.3	1243.0	1103.4	948.8	914.1	895.2
70°	2791.3	1469.4	728.0	756.4	834.5	1003.2	1168.9	1039.5	884.9	869.2	844.7
72.5°	1299.0	884.1	662.5	690.1	749.3	893.6	1073.4	955.9	809.2	774.5	741.4
75°	775.3	646.7	585.2	609.7	651.5	776.9	953.6	870.7	737.4	691.7	657.0
77.5°	579.7	494.5	500.0	526.1	560.0	679.9	844.7	803.7	682.2	646.7	623.1
80°	417.2	375.4	407.8	436.2	471.7	618.4	809.2	743.0	616.8	569.5	547.4
82.5°	278.4	269.7	306.8	336.0	370.7	541.1	760.3	650.7	526.9	466.9	418.0
85°	153.8	162.5	206.6	219.3	249.2	380.9	623.1	522.9	396.7	319.4	305.2
87.5°	63.9	74.9	111.2	107.3	132.5	227.1	410.1	315.5	252.4	188.5	146.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW EDISON

Report Number: SP1-2408-195-9

Test Date: 08/07/2024

Luminaire Tested: GALN-SB1A-830-U-5WQ

Data in this report applies to families of products including GALN-SB1A-830-U-5WQ.

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2408-195-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/07/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: MCGRAW EDISON
 Catalog Number: **GALN-SB1A-830-U-5WQ**
 Description: GALLEON AREA AND ROADWAY LUMINAIRE. (1) 80 CRI, 3000K, 350MA HIGH DENSITY LIGHTSQUARE WITH 26 LEDS AND TYPE V WIDE OPTICS

Spectral Parameters

CCT (K): 3050
 CIE u' : 0.2476
 CIE v' : 0.5251
 Duv: 0.0034
 CIE x: 0.4383
 CIE y: 0.4131
 CIE z: 0.1487
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 581
 Purity: 55.55201
 R_f: 81.5
 R_g: 99.2

CRI (Ra): 81.0
 R1: 79.6
 R2: 85.6
 R3: 92.0
 R4: 82.6
 R5: 78.9
 R6: 81.7
 R7: 85.2
 R8: 62.0
 R9: 7.1
 R10: 67.0
 R11: 82.7
 R12: 63.2
 R13: 80.3
 R14: 95.0
 R15: 71.7



Test Conditions

Stabilization Time: 20M
 Operation Time: 1H 20M
 Sphere Temperature (°C): 24.2

REPORT NUMBER: SP1-2408-195-9

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2408-195-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2408-195-9

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	168	NR	620	940	NR	750	35	NR	880	1	NR
365	0	NR	495	233	NR	625	897	NR	755	30	NR	885	1	NR
370	0	NR	500	300	NR	630	847	NR	760	26	NR	890	1	NR
375	0	NR	505	372	NR	635	790	NR	765	22	NR	895	1	NR
380	0	NR	510	430	NR	640	730	NR	770	19	NR	900	1	NR
385	0	NR	515	483	NR	645	668	NR	775	16	NR	905	1	NR
390	0	NR	520	524	NR	650	605	NR	780	14	NR	910	0	NR
395	2	NR	525	555	NR	655	545	NR	785	12	NR	915	0	NR
400	4	NR	530	581	NR	660	485	NR	790	10	NR	920	0	NR
405	7	NR	535	604	NR	665	430	NR	795	9	NR	925	0	NR
410	17	NR	540	623	NR	670	378	NR	800	8	NR	930	0	NR
415	34	NR	545	645	NR	675	331	NR	805	7	NR	935	0	NR
420	68	NR	550	667	NR	680	290	NR	810	6	NR	940	0	NR
425	128	NR	555	693	NR	685	251	NR	815	5	NR	945	0	NR
430	214	NR	560	719	NR	690	218	NR	820	4	NR	950	0	NR
435	339	NR	565	754	NR	695	188	NR	825	4	NR	955	0	NR
440	507	NR	570	791	NR	700	162	NR	830	3	NR	960	0	NR
445	573	NR	575	830	NR	705	139	NR	835	3	NR	965	0	NR
450	356	NR	580	873	NR	710	119	NR	840	3	NR	970	0	NR
455	217	NR	585	913	NR	715	102	NR	845	2	NR	975	0	NR
460	168	NR	590	948	NR	720	88	NR	850	2	NR	980	0	NR
465	113	NR	595	974	NR	725	76	NR	855	2	NR	985	0	NR
470	85	NR	600	994	NR	730	65	NR	860	1	NR	990	0	NR
475	85	NR	605	998	NR	735	55	NR	865	1	NR	995	0	NR
480	94	NR	610	994	NR	740	47	NR	870	1	NR	1000	0	NR
485	120	NR	615	973	NR	745	41	NR	875	1	NR			

REPORT NUMBER: SP1-2408-195-9

Scotopic Flux vs. Wavelength


Scotopic Lumens: NR
S/P: 1.27

λ (nm)	Power W ^Λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^Λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^Λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^Λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^Λ /nm	Lumens (Φ/nm)
360	0	NR	490	168	NR	620	940	NR	750	35	NR	880	1	NR
365	0	NR	495	233	NR	625	897	NR	755	30	NR	885	1	NR
370	0	NR	500	300	NR	630	847	NR	760	26	NR	890	1	NR
375	0	NR	505	372	NR	635	790	NR	765	22	NR	895	1	NR
380	0	NR	510	430	NR	640	730	NR	770	19	NR	900	1	NR
385	0	NR	515	483	NR	645	668	NR	775	16	NR	905	1	NR
390	0	NR	520	524	NR	650	605	NR	780	14	NR	910	0	NR
395	2	NR	525	555	NR	655	545	NR	785	12	NR	915	0	NR
400	4	NR	530	581	NR	660	485	NR	790	10	NR	920	0	NR
405	7	NR	535	604	NR	665	430	NR	795	9	NR	925	0	NR
410	17	NR	540	623	NR	670	378	NR	800	8	NR	930	0	NR
415	34	NR	545	645	NR	675	331	NR	805	7	NR	935	0	NR
420	68	NR	550	667	NR	680	290	NR	810	6	NR	940	0	NR
425	128	NR	555	693	NR	685	251	NR	815	5	NR	945	0	NR
430	214	NR	560	719	NR	690	218	NR	820	4	NR	950	0	NR
435	339	NR	565	754	NR	695	188	NR	825	4	NR	955	0	NR
440	507	NR	570	791	NR	700	162	NR	830	3	NR	960	0	NR
445	573	NR	575	830	NR	705	139	NR	835	3	NR	965	0	NR
450	356	NR	580	873	NR	710	119	NR	840	3	NR	970	0	NR
455	217	NR	585	913	NR	715	102	NR	845	2	NR	975	0	NR
460	168	NR	590	948	NR	720	88	NR	850	2	NR	980	0	NR
465	113	NR	595	974	NR	725	76	NR	855	2	NR	985	0	NR
470	85	NR	600	994	NR	730	65	NR	860	1	NR	990	0	NR
475	85	NR	605	998	NR	735	55	NR	865	1	NR	995	0	NR
480	94	NR	610	994	NR	740	47	NR	870	1	NR	1000	0	NR
485	120	NR	615	973	NR	745	41	NR	875	1	NR			

REPORT NUMBER: SP1-2408-195-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.32

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	168	NR	620	940	NR	750	35	NR	880	1	NR
365	0	NR	495	233	NR	625	897	NR	755	30	NR	885	1	NR
370	0	NR	500	300	NR	630	847	NR	760	26	NR	890	1	NR
375	0	NR	505	372	NR	635	790	NR	765	22	NR	895	1	NR
380	0	NR	510	430	NR	640	730	NR	770	19	NR	900	1	NR
385	0	NR	515	483	NR	645	668	NR	775	16	NR	905	1	NR
390	0	NR	520	524	NR	650	605	NR	780	14	NR	910	0	NR
395	2	NR	525	555	NR	655	545	NR	785	12	NR	915	0	NR
400	4	NR	530	581	NR	660	485	NR	790	10	NR	920	0	NR
405	7	NR	535	604	NR	665	430	NR	795	9	NR	925	0	NR
410	17	NR	540	623	NR	670	378	NR	800	8	NR	930	0	NR
415	34	NR	545	645	NR	675	331	NR	805	7	NR	935	0	NR
420	68	NR	550	667	NR	680	290	NR	810	6	NR	940	0	NR
425	128	NR	555	693	NR	685	251	NR	815	5	NR	945	0	NR
430	214	NR	560	719	NR	690	218	NR	820	4	NR	950	0	NR
435	339	NR	565	754	NR	695	188	NR	825	4	NR	955	0	NR
440	507	NR	570	791	NR	700	162	NR	830	3	NR	960	0	NR
445	573	NR	575	830	NR	705	139	NR	835	3	NR	965	0	NR
450	356	NR	580	873	NR	710	119	NR	840	3	NR	970	0	NR
455	217	NR	585	913	NR	715	102	NR	845	2	NR	975	0	NR
460	168	NR	590	948	NR	720	88	NR	850	2	NR	980	0	NR
465	113	NR	595	974	NR	725	76	NR	855	2	NR	985	0	NR
470	85	NR	600	994	NR	730	65	NR	860	1	NR	990	0	NR
475	85	NR	605	998	NR	735	55	NR	865	1	NR	995	0	NR
480	94	NR	610	994	NR	740	47	NR	870	1	NR	1000	0	NR
485	120	NR	615	973	NR	745	41	NR	875	1	NR			

REPORT NUMBER: SP1-2408-195-9

TM-30-18

Summary

$R_f = 81.5$
 $R_g = 99.2$
 $CIE R_a = 81.0$
 $R_9 = 7.1$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 74	CES51 = 89	CES76 = 70
CES02 = 63	CES27 = 88	CES52 = 92	CES77 = 86
CES03 = 31	CES28 = 89	CES53 = 81	CES78 = 72
CES04 = 70	CES29 = 67	CES54 = 87	CES79 = 90
CES05 = 50	CES30 = 68	CES55 = 85	CES80 = 88
CES06 = 51	CES31 = 71	CES56 = 78	CES81 = 78
CES07 = 42	CES32 = 70	CES57 = 76	CES82 = 95
CES08 = 41	CES33 = 71	CES58 = 78	CES83 = 90
CES09 = 29	CES34 = 82	CES59 = 92	CES84 = 94
CES10 = 76	CES35 = 90	CES60 = 95	CES85 = 86
CES11 = 59	CES36 = 93	CES61 = 93	CES86 = 72
CES12 = 65	CES37 = 87	CES62 = 83	CES87 = 85
CES13 = 43	CES38 = 75	CES63 = 77	CES88 = 83
CES14 = 74	CES39 = 94	CES64 = 83	CES89 = 75
CES15 = 71	CES40 = 89	CES65 = 77	CES90 = 81
CES16 = 47	CES41 = 85	CES66 = 80	CES91 = 96
CES17 = 50	CES42 = 86	CES67 = 79	CES92 = 73
CES18 = 56	CES43 = 81	CES68 = 84	CES93 = 84
CES19 = 72	CES44 = 99	CES69 = 91	CES94 = 64
CES20 = 66	CES45 = 87	CES70 = 78	CES95 = 80
CES21 = 87	CES46 = 82	CES71 = 76	CES96 = 84
CES22 = 79	CES47 = 77	CES72 = 92	CES97 = 87
CES23 = 92	CES48 = 71	CES73 = 71	CES98 = 81
CES24 = 91	CES49 = 81	CES74 = 93	CES99 = 74
CES25 = 72	CES50 = 89	CES75 = 74	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)