

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P151225

Luminaire Tested: **TLM-F02-LED-E1-SL3**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P151225  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33679)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TLM-F02-LED-E1-SL3  
Description: TALON MEDIUM LED SITE LUMINAIRE  
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 3 W/ SPILL LIGHT CONTROL  
Light Source: (14) 4000K CCT, 70 CRI LEDs  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5012.9 lumens  
Efficiency: N/A  
Efficacy: 91.1 lumens/watt  
Spacing Criteria (0/90/45): 1.44 / 3.92 / 2.51  
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')  
CIE Type: Direct

Input Watts (W): 55  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P151225  
CATALOG NUMBER: TLM-F02-LED-E1-SL3

### Luminous Intensity Polar Plot





TEST NUMBER: P151225

CATALOG NUMBER: TLM-F02-LED-E1-SL3

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	106	100	94	89	103	97	92	88	93	89	85	89	85	82	85	82	80	77					77			
2	93	82	74	66	90	80	72	65	77	70	64	73	67	62	70	65	61	58					58			
3	82	69	59	50	79	67	58	50	64	56	49	61	54	48	58	52	47	44					44			
4	73	59	48	39	71	57	47	39	54	46	38	52	44	38	49	43	37	35					35			
5	66	51	40	32	64	49	39	31	47	38	31	45	37	31	43	36	30	28					28			
6	60	44	34	26	58	43	33	26	41	32	26	39	31	25	38	31	25	23					23			
7	55	39	29	22	53	38	29	22	37	28	22	35	27	21	34	27	21	19					19			
8	51	35	25	19	49	35	25	19	33	25	18	32	24	18	30	23	18	16					16			
9	47	32	23	16	46	31	22	16	30	22	16	29	21	16	28	21	16	14					14			
10	44	29	20	14	43	29	20	14	28	20	14	27	19	14	26	19	14	12					12			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	17862	17862	17862
5°	19839	18202	17010
10°	22930	19541	17534
15°	26518	21912	19457
20°	29341	24395	19258
25°	31138	27809	16876
30°	32316	33393	12874
35°	33396	41834	7844
40°	35665	56192	5718
45°	43080	73243	5508
50°	56276	93279	5557
55°	70294	124654	5761
60°	81675	180736	6139
65°	84019	221092	6838
70°	74788	203488	7563
75°	35930	114999	8809
80°	12397	15929	8997
85°	5576	9880	9057



TEST NUMBER: P151225

CATALOG NUMBER: TLM-F02-LED-E1-SL3

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	54.5	1.1
10°-20°	186.9	3.7
20°-30°	330.1	6.6
30°-40°	473.8	9.5
40°-50°	719.6	14.4
50°-60°	1059.5	21.1
60°-70°	1408.1	28.1
70°-80°	688.9	13.7
80°-90°	91.5	1.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	571.6	11.4
0°-40°	1045.4	20.9
0°-60°	2824.5	56.3
0°-90°	5012.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5012.9	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	548	548	548	548	548	
5°	606	589	556	528	520	60
15°	785	715	649	588	576	223
25°	865	771	773	644	469	398
35°	839	916	1051	497	197	529
45°	934	1464	1588	179	119	738
55°	1236	1937	2192	108	101	1091
65°	1089	2470	2865	121	89	1057
75°	285	850	912	140	70	355
85°	15	47	26	34	24	22
90°	0	0	0	0	0	



TEST NUMBER: P151225

CATALOG NUMBER: TLM-F02-LED-E1-SL3

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	60°	61°	62°	64°
0°	547.6	547.6	547.6	547.6	547.6	547.6	547.6	547.6	547.6	547.6	547.6
2.5°	573.5	574.0	572.9	572.4	569.1	565.8	563.6	560.8	560.8	560.8	559.7
5°	605.9	603.7	605.4	601.5	594.9	588.9	582.8	577.9	576.8	576.8	574.6
7.5°	645.0	642.3	641.2	635.7	625.7	616.9	604.8	599.9	597.1	596.0	594.9
10°	692.3	692.3	685.2	675.8	662.6	647.2	634.0	625.2	624.6	624.6	619.7
12.5°	740.8	741.9	732.5	723.2	701.7	681.3	665.9	656.0	655.5	653.3	650.5
15°	785.3	782.6	776.5	762.8	739.1	714.9	695.6	685.7	683.5	681.3	679.7
17.5°	822.2	819.5	811.8	794.2	769.4	740.8	717.1	706.6	705.5	704.4	702.2
20°	845.3	843.1	832.1	811.8	785.9	756.7	731.4	724.3	722.1	722.1	721.0
22.5°	858.5	855.2	839.3	812.3	787.0	765.5	744.6	740.2	738.6	739.1	739.1
25°	865.2	862.4	839.8	801.3	777.1	771.0	762.2	759.5	760.0	760.6	761.7
27.5°	866.3	862.4	836.0	787.0	764.4	781.5	787.6	792.0	792.0	794.2	798.0
30°	858.0	853.6	828.3	776.0	758.9	802.4	826.6	838.2	842.6	841.5	850.3
32.5°	843.7	840.9	820.6	776.0	774.3	843.7	886.6	903.1	905.3	906.4	916.3
35°	838.7	838.2	829.4	802.4	822.2	916.3	981.8	994.5	997.2	997.2	1004.4
37.5°	837.6	840.4	850.3	851.9	906.4	1024.2	1110.1	1129.3	1129.3	1134.8	1134.8
40°	837.6	843.7	881.1	925.7	1009.3	1164.5	1283.4	1305.4	1305.4	1311.5	1308.2
42.5°	870.1	878.9	940.5	1025.3	1139.2	1309.3	1445.8	1470.5	1472.2	1470.5	1475.5
45°	933.9	941.6	1016.5	1138.1	1273.0	1464.5	1601.0	1630.7	1624.6	1628.5	1630.1
47.5°	1018.7	1030.8	1116.1	1261.4	1403.4	1608.1	1774.9	1801.8	1799.6	1801.3	1794.1
50°	1109.0	1121.6	1216.8	1383.6	1533.3	1723.7	1914.7	1954.8	1951.0	1953.7	1957.6
52.5°	1188.8	1196.5	1288.4	1475.5	1631.8	1831.6	2022.0	2072.1	2080.9	2082.0	2084.7
55°	1236.1	1245.4	1329.6	1521.2	1703.3	1937.2	2144.7	2220.7	2237.7	2242.1	2254.2
57.5°	1252.6	1262.5	1339.0	1527.8	1742.4	2036.3	2315.9	2449.6	2463.9	2487.6	2526.1
60°	1252.0	1262.5	1329.1	1512.9	1782.0	2159.0	2582.2	2806.2	2878.9	2903.1	2958.1
62.5°	1200.9	1213.0	1280.7	1467.8	1832.7	2315.9	2978.5	3323.0	3416.6	3460.6	3520.0
65°	1088.6	1097.4	1160.7	1353.3	1818.4	2470.5	3309.8	3739.6	3824.9	3889.3	3995.5
67°	989.0	994.5	1044.0	1217.9	1678.6	2476.0	3414.4	3843.1	3917.4	3985.6	4095.2
67.5°	963.7	975.2	1013.7	1176.6	1626.3	2444.7	3407.2	3827.1	3903.1	3974.1	4089.7
70°	784.2	800.8	820.0	929.5	1278.5	2056.7	3154.6	3550.9	3617.5	3683.5	3844.7
72.5°	483.8	513.5	517.3	586.7	832.1	1421.6	2552.5	2994.5	3044.5	3091.9	3257.0
75°	285.1	289.5	303.2	359.4	488.2	849.7	1712.7	2224.5	2270.7	2293.9	2423.2
77.5°	159.1	163.5	175.0	223.4	375.3	572.4	997.2	1307.1	1335.1	1364.3	1343.4
80°	66.0	72.1	77.6	90.3	175.6	451.8	685.7	831.0	849.2	866.3	887.7
82.5°	31.9	34.1	41.8	47.9	63.8	185.5	537.7	720.4	741.9	766.6	816.7
85°	14.9	16.5	23.1	27.5	30.8	46.8	180.0	350.6	380.3	385.8	395.7
87.5°	1.1	1.1	2.8	3.9	5.5	6.1	18.7	26.4	29.7	27.0	34.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P151225

CATALOG NUMBER: TLM-F02-LED-E1-SL3

**CANDELA DISTRIBUTION (continued):**

	65°	66°	67°	68°	69°	70°	71°	72°	73°	74°	75°
0°	547.6	547.6	547.6	547.6	547.6	547.6	547.6	547.6	547.6	547.6	547.6
2.5°	559.2	558.6	557.5	557.5	557.0	557.0	557.0	555.9	555.9	555.9	555.3
5°	574.0	573.5	571.8	571.8	570.7	570.7	569.1	568.5	567.4	567.4	566.9
7.5°	593.3	592.7	590.5	590.5	588.9	588.3	587.2	585.6	585.6	584.5	583.4
10°	619.7	618.0	617.5	614.7	615.3	614.2	613.1	611.4	610.3	609.2	608.1
12.5°	649.4	649.4	646.7	645.0	646.1	645.0	642.8	642.3	640.6	640.6	639.0
15°	677.5	677.5	676.4	674.2	674.7	673.1	672.5	671.4	669.2	669.8	669.2
17.5°	701.7	701.7	700.0	698.9	698.9	697.3	697.8	696.7	695.6	695.1	693.4
20°	721.0	721.0	719.9	718.8	719.3	719.3	717.7	717.7	717.7	716.6	716.6
22.5°	739.7	740.2	740.2	740.2	740.8	741.3	740.8	741.9	741.3	742.4	742.4
25°	764.4	766.1	767.2	767.2	769.9	770.5	771.0	772.7	772.7	774.3	774.9
27.5°	801.3	802.4	806.8	807.9	808.5	812.9	813.4	815.6	817.8	818.4	818.9
30°	851.9	854.7	858.0	860.2	860.2	865.7	867.9	866.8	872.9	874.5	876.7
32.5°	919.6	921.8	925.1	927.3	929.5	932.3	932.8	935.6	940.5	945.0	942.2
35°	1004.9	1010.4	1004.9	1011.0	1012.6	1016.5	1015.4	1018.7	1020.9	1022.6	1022.0
37.5°	1128.8	1126.0	1124.9	1122.7	1118.9	1132.1	1125.5	1124.9	1121.6	1131.0	1124.9
40°	1291.7	1293.3	1295.0	1286.2	1281.2	1281.2	1279.6	1273.5	1270.8	1279.0	1277.9
42.5°	1461.7	1463.4	1455.7	1450.2	1437.5	1435.9	1428.2	1426.5	1423.8	1428.2	1423.8
45°	1616.4	1617.5	1600.4	1603.2	1593.3	1594.9	1582.8	1587.8	1581.2	1585.6	1593.8
47.5°	1789.2	1791.4	1776.5	1782.6	1772.7	1766.6	1766.1	1769.4	1762.2	1766.6	1768.8
50°	1946.0	1943.3	1935.6	1937.2	1932.8	1933.9	1927.3	1933.4	1925.1	1933.9	1932.8
52.5°	2085.3	2082.0	2080.3	2085.8	2082.0	2082.0	2078.1	2080.9	2082.0	2095.2	2097.9
55°	2254.2	2257.0	2259.7	2269.6	2274.0	2266.9	2274.0	2287.8	2288.4	2319.7	2336.8
57.5°	2525.6	2544.8	2554.7	2560.8	2586.6	2583.9	2600.4	2633.4	2636.7	2709.4	2751.7
60°	2998.9	3033.0	3065.4	3047.8	3100.1	3116.1	3126.0	3187.6	3206.9	3275.7	3312.6
62.5°	3596.5	3600.4	3651.0	3635.1	3664.8	3657.6	3669.7	3697.8	3723.1	3779.8	3814.5
65°	4013.7	4031.9	4051.7	4031.3	4030.8	4006.5	3991.1	3990.6	4006.0	4018.1	4056.6
67°	4127.1	4145.2	4150.2	4135.3	4113.9	4083.0	4054.4	4039.6	4029.7	4035.2	4059.4
67.5°	4126.0	4143.0	4149.1	4134.8	4105.1	4079.2	4048.9	4031.9	4018.7	4021.4	4041.8
70°	3891.5	3928.4	3948.2	3952.6	3948.8	3903.6	3877.8	3862.4	3851.3	3824.4	3822.7
72.5°	3297.1	3341.7	3357.1	3381.9	3392.9	3326.3	3298.2	3315.3	3276.8	3191.5	3195.3
75°	2421.0	2424.3	2372.6	2362.7	2325.8	2175.0	2129.9	2088.6	2022.5	1919.6	1822.8
77.5°	1262.0	1261.4	1202.0	1171.7	1127.7	1036.9	1032.5	958.7	907.0	812.9	778.7
80°	896.5	910.8	930.6	940.5	925.1	889.9	841.5	789.2	729.2	670.3	599.9
82.5°	833.8	842.6	853.0	814.5	793.1	743.5	706.6	630.7	588.3	521.2	450.2
85°	405.6	432.6	411.7	387.4	379.2	296.6	286.7	239.4	217.4	178.9	166.8
87.5°	25.9	31.9	28.6	25.9	22.6	12.7	17.1	12.1	12.7	9.4	8.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P151225

CATALOG NUMBER: TLM-F02-LED-E1-SL3

**CANDELA DISTRIBUTION (continued):**

	76°	77°	78°	79°	80°	81°	82°	83°	84°	85°	86°
0°	547.6	547.6	547.6	547.6	547.6	547.6	547.6	547.6	547.6	547.6	547.6
2.5°	555.3	554.8	554.2	553.7	553.1	553.1	552.6	552.0	551.5	550.3	550.3
5°	565.8	565.8	565.2	564.1	564.1	563.0	561.4	560.8	560.8	559.7	558.6
7.5°	582.8	582.3	581.2	580.6	579.5	578.4	577.3	576.2	575.7	574.0	573.5
10°	608.7	607.6	604.8	603.7	603.2	602.1	601.0	599.9	598.2	597.1	596.6
12.5°	637.9	637.3	635.1	636.2	633.5	632.4	631.3	628.5	629.6	627.4	626.3
15°	667.0	667.6	666.5	666.5	664.3	662.6	661.5	659.3	658.8	657.7	656.6
17.5°	692.9	694.0	692.3	691.2	690.1	689.0	686.8	684.6	684.6	682.4	681.3
20°	716.6	717.7	717.1	716.0	714.4	713.8	712.7	711.1	711.1	710.0	708.3
22.5°	743.5	744.1	744.1	743.5	741.9	742.4	741.3	739.7	740.2	738.0	738.0
25°	776.0	777.1	778.2	778.7	777.6	778.2	777.1	776.0	775.4	776.0	775.4
27.5°	820.6	821.7	825.0	822.2	825.0	825.5	823.9	821.7	823.3	826.1	824.4
30°	879.5	878.4	882.8	883.3	882.8	883.3	882.2	880.6	881.7	886.6	883.9
32.5°	945.5	947.7	948.8	949.9	951.6	953.8	952.1	950.5	953.2	951.6	955.4
35°	1025.3	1030.3	1031.9	1030.3	1031.4	1035.2	1034.7	1035.2	1040.7	1035.2	1042.4
37.5°	1126.0	1131.0	1134.8	1132.6	1135.4	1135.4	1139.8	1151.9	1144.2	1154.1	1161.8
40°	1272.4	1280.1	1280.7	1280.1	1282.9	1286.2	1290.6	1303.8	1295.0	1305.4	1312.6
42.5°	1423.2	1432.6	1435.9	1430.4	1436.4	1443.6	1444.1	1455.7	1456.2	1457.9	1461.7
45°	1593.3	1601.5	1608.1	1605.4	1605.9	1615.3	1613.1	1624.1	1615.8	1615.8	1618.0
47.5°	1774.3	1782.0	1786.4	1790.8	1785.3	1793.6	1797.4	1795.2	1785.3	1783.1	1769.9
50°	1939.4	1946.0	1952.6	1964.7	1964.2	1968.1	1970.8	1960.9	1958.7	1946.6	1931.7
52.5°	2114.4	2131.5	2146.4	2171.7	2175.5	2188.7	2183.8	2167.3	2164.5	2144.7	2124.9
55°	2358.2	2407.2	2428.7	2467.8	2494.2	2493.6	2482.6	2479.9	2459.0	2419.3	2395.7
57.5°	2782.6	2859.1	2895.9	2946.6	2954.8	2949.9	2935.6	2910.3	2873.9	2807.3	2764.4
60°	3395.1	3442.4	3485.4	3497.5	3503.5	3494.2	3444.1	3388.0	3317.0	3225.1	3148.6
62.5°	3858.0	3906.4	3938.3	3933.4	3895.4	3847.5	3774.3	3680.2	3580.6	3477.7	3363.2
65°	4093.5	4113.9	4108.9	4070.4	4005.4	3921.8	3815.0	3698.9	3581.7	3460.1	3341.2
67°	4080.8	4081.4	4047.8	3973.0	3889.9	3784.8	3654.3	3527.7	3390.2	3262.5	3121.0
67.5°	4058.3	4056.1	4009.3	3927.3	3837.6	3729.2	3593.8	3462.8	3320.3	3191.5	3045.1
70°	3802.9	3772.1	3666.4	3535.4	3410.5	3264.1	3122.1	2971.9	2811.2	2700.6	2532.2
72.5°	3124.9	3020.9	2838.7	2701.7	2567.9	2376.4	2287.8	2101.2	1988.4	1918.0	1790.8
75°	1809.6	1722.6	1581.7	1453.5	1388.5	1275.2	1221.2	1084.2	1055.6	1054.5	1010.4
77.5°	690.7	602.6	511.8	412.2	350.6	278.5	245.5	219.6	199.8	213.5	193.7
80°	517.9	426.0	333.0	242.2	172.8	127.7	109.5	101.3	96.3	92.5	89.7
82.5°	385.8	304.3	236.1	154.1	107.9	81.5	70.4	66.0	63.8	60.0	56.7
85°	130.4	104.6	82.6	57.2	45.1	36.9	34.1	33.0	31.4	28.6	27.0
87.5°	7.2	6.6	7.2	5.5	6.6	5.5	6.1	6.1	6.1	5.5	5.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





TEST NUMBER: P151225

CATALOG NUMBER: TLM-F02-LED-E1-SL3

**CANDELA DISTRIBUTION (continued):**

	87°	88°	89°	90°	95°	105°	115°	125°	135°	145°	155°
0°	547.6	547.6	547.6	547.6	547.6	547.6	547.6	547.6	547.6	547.6	547.6
2.5°	549.8	549.8	549.8	548.7	547.0	543.7	540.4	537.7	534.9	533.3	532.2
5°	558.1	557.0	556.4	555.9	552.0	545.4	539.3	533.8	528.3	523.9	522.3
7.5°	572.9	570.7	570.2	568.5	563.6	553.7	544.8	536.0	528.3	522.3	519.5
10°	595.5	595.5	592.2	590.0	584.5	571.3	558.6	547.0	536.6	530.0	528.3
12.5°	624.1	624.1	621.3	619.7	613.1	596.0	580.6	566.9	557.0	550.3	549.8
15°	653.8	653.3	651.1	648.9	641.7	623.5	608.1	596.0	587.8	580.1	577.9
17.5°	680.2	680.2	677.5	675.3	668.1	652.7	639.0	630.2	620.8	604.8	592.7
20°	706.6	707.2	705.0	702.8	696.7	683.5	677.5	668.7	647.8	613.1	584.5
22.5°	735.8	738.0	735.3	733.1	728.1	722.6	720.4	699.5	655.5	599.9	558.1
25°	773.2	777.1	773.8	772.7	769.9	771.6	765.0	716.6	644.5	571.3	519.0
27.5°	824.4	824.4	825.0	825.0	823.9	829.9	805.7	717.1	620.2	534.4	472.2
30°	884.4	887.7	886.6	886.6	891.0	894.9	828.3	705.0	589.4	488.7	415.0
32.5°	956.5	959.3	960.4	955.4	973.0	953.2	836.5	683.0	551.5	432.0	346.7
35°	1043.5	1047.3	1050.1	1050.6	1062.2	1003.8	832.1	650.5	497.0	361.0	271.9
37.5°	1156.8	1164.5	1170.6	1173.3	1173.9	1046.8	820.0	607.6	426.0	281.8	202.5
40°	1307.6	1315.9	1314.2	1319.7	1288.4	1072.1	792.5	545.4	337.9	206.9	156.3
42.5°	1452.9	1454.0	1456.2	1451.3	1387.4	1085.3	754.0	469.4	253.2	154.6	133.7
45°	1615.3	1605.9	1595.5	1587.8	1478.8	1090.2	701.1	377.0	178.9	129.9	123.8
47.5°	1767.7	1755.1	1733.6	1711.6	1560.2	1082.5	633.5	282.3	135.9	118.9	117.2
50°	1917.4	1893.8	1863.5	1838.2	1638.4	1071.0	558.6	203.6	118.9	113.4	111.7
52.5°	2102.9	2063.3	2023.6	1990.6	1740.2	1052.8	479.9	154.6	111.7	109.0	106.8
55°	2357.1	2302.1	2238.3	2192.0	1878.3	1025.3	397.4	131.0	108.4	106.2	102.9
57.5°	2709.4	2626.8	2554.7	2479.3	2067.1	997.2	326.4	121.6	107.9	104.6	100.2
60°	3069.3	2970.2	2878.3	2770.5	2259.7	969.2	276.8	120.5	109.5	104.6	98.0
62.5°	3256.4	3154.1	3043.4	2933.9	2342.8	903.1	242.7	122.2	113.4	106.2	98.0
65°	3213.5	3088.6	2976.3	2864.6	2246.5	778.2	205.3	124.4	121.1	112.8	99.6
67°	2997.8	2867.3	2759.5	2652.7	2031.9	651.6	176.1	126.6	129.3	120.5	102.9
67.5°	2921.8	2791.4	2685.2	2581.1	1968.6	625.2	169.0	127.7	131.0	122.7	104.0
70°	2422.6	2326.9	2214.1	2133.7	1593.8	462.8	138.7	129.9	140.9	135.4	109.0
72.5°	1743.5	1652.2	1567.4	1522.8	1173.9	323.6	116.7	127.7	146.9	142.5	111.2
75°	926.8	921.3	890.5	912.5	726.5	211.3	102.9	119.4	140.3	130.4	103.5
77.5°	187.1	192.6	226.2	222.9	234.4	117.8	88.1	102.4	108.4	95.8	84.2
80°	87.0	85.3	83.7	84.8	83.1	75.4	71.5	80.4	75.4	61.6	56.1
82.5°	53.9	52.8	51.2	50.6	56.1	60.0	62.7	63.3	50.1	42.9	41.3
85°	25.9	25.9	25.3	26.4	33.0	49.0	52.8	46.8	33.6	30.8	29.2
87.5°	5.0	5.0	5.5	5.0	6.6	11.6	13.2	15.4	12.7	13.2	14.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P151225

CATALOG NUMBER: TLM-F02-LED-E1-SL3

**CANDELA DISTRIBUTION (continued):**

	165°	175°	180°
0°	547.6	547.6	547.6
2.5°	531.1	530.0	530.0
5°	520.1	519.5	519.5
7.5°	517.3	517.9	517.3
10°	527.8	527.2	529.4
12.5°	550.9	552.6	552.0
15°	575.1	576.2	576.2
17.5°	582.3	578.4	577.9
20°	563.6	556.4	554.8
22.5°	528.3	515.1	515.7
25°	483.8	467.8	468.9
27.5°	432.0	415.0	414.4
30°	369.8	351.1	341.8
32.5°	295.0	272.4	272.4
35°	221.8	203.6	197.0
37.5°	168.4	158.0	154.6
40°	140.3	135.4	134.3
42.5°	127.7	126.0	125.5
45°	121.1	120.0	119.4
47.5°	115.0	114.5	113.9
50°	110.6	110.1	109.5
52.5°	106.8	105.7	105.1
55°	101.3	101.3	101.3
57.5°	98.0	98.0	97.4
60°	94.7	94.1	94.1
62.5°	91.9	90.8	91.4
65°	90.3	88.6	88.6
67°	89.2	85.9	85.9
67.5°	89.2	84.8	84.8
70°	87.5	80.4	79.3
72.5°	85.9	75.4	73.7
75°	81.5	71.5	69.9
77.5°	69.9	63.8	62.7
80°	53.9	46.8	47.9
82.5°	39.1	33.6	33.0
85°	28.1	24.2	24.2
87.5°	14.9	12.7	13.2
90°	0.0	0.0	0.0

(END OF REPORT)