

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P154553

Luminaire Tested: **TLM-F03-LED-E1-T2-8030**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P154553  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33671)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TLM-F03-LED-E1-T2-8030  
Description: TALON MEDIUM LED SITE LUMINAIRE  
(3) LIGHTBARS WITH AccuLED OPTICS - TYPE 2  
Light Source: (21) 3000K CCT, 80 CRI LEDs  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6404.1 lumens  
Efficiency: N/A  
Efficacy: 81.8 lumens/watt  
Spacing Criteria (0/90/45): 2.21 / 4.51 / 2.52  
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')  
CIE Type: Direct

Input Watts (W): 78.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P154553  
CATALOG NUMBER: TLM-F03-LED-E1-T2-8030

### Luminous Intensity Polar Plot





TEST NUMBER: P154553

CATALOG NUMBER: TLM-F03-LED-E1-T2-8030

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	107	101	96	91	104	98	94	90	94	90	87	90	87	84	86	84	81	79
2	94	84	76	69	91	82	75	68	78	72	66	75	70	65	72	67	63	61
3	84	71	61	53	81	69	60	53	66	58	51	63	56	50	60	54	50	47
4	75	60	50	42	72	59	49	41	56	48	41	54	46	40	51	45	39	37
5	67	52	42	34	65	51	41	33	49	40	33	46	39	33	44	38	32	30
6	61	46	35	28	59	45	35	27	43	34	27	41	33	27	39	32	27	24
7	56	40	30	23	54	40	30	23	38	29	23	36	28	23	35	28	22	20
8	52	36	26	20	50	35	26	20	34	26	19	33	25	19	31	24	19	17
9	48	33	23	17	46	32	23	17	31	23	17	30	22	17	28	22	17	15
10	45	30	21	15	43	29	21	15	28	20	15	27	20	15	26	19	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	13784	13784	13784
5°	15071	14122	13400
10°	16861	15276	13997
15°	19100	17065	15046
20°	21182	19984	16121
25°	22559	23749	17178
30°	24905	28075	18012
35°	30835	33876	18255
40°	39141	39729	16623
45°	50125	48066	14020
50°	59712	59551	10945
55°	67600	84647	7792
60°	69208	178819	6118
65°	50893	251421	5145
70°	24164	252956	5086
75°	13159	93940	6205
80°	6223	15026	7947
85°	2915	9287	9287



TEST NUMBER: P154553

CATALOG NUMBER: TLM-F03-LED-E1-T2-8030

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	64.1	1.0
10°-20°	220.2	3.4
20°-30°	432.7	6.8
30°-40°	718.9	11.2
40°-50°	1056.4	16.5
50°-60°	1462.5	22.8
60°-70°	1745.7	27.3
70°-80°	617.3	9.6
80°-90°	86.3	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	717.0	11.2
0°-40°	1435.9	22.4
0°-60°	3954.8	61.8
0°-90°	6404.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6404.1	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	640	640	640	640	640	
5°	697	684	654	628	620	69
15°	857	803	766	735	675	244
25°	950	921	1000	940	723	443
35°	1173	1213	1289	1098	695	750
45°	1646	1797	1579	995	460	1260
55°	1801	2159	2255	680	208	1578
65°	999	1489	4936	210	101	974
75°	158	448	1129	84	75	195
85°	12	24	38	64	38	17
90°	0	0	0	0	0	



TEST NUMBER: P154553

CATALOG NUMBER: TLM-F03-LED-E1-T2-8030

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	60°	61°	62°	64°
0°	640.3	640.3	640.3	640.3	640.3	640.3	640.3	640.3	640.3	640.3	640.3
2.5°	668.2	668.9	667.5	666.8	664.7	661.2	658.4	655.6	655.6	655.6	653.5
5°	697.4	698.8	696.0	693.9	687.7	684.2	679.3	675.8	674.4	673.7	671.7
7.5°	734.4	732.3	728.1	726.7	721.8	714.2	705.1	698.1	698.1	697.4	698.1
10°	771.3	765.7	763.6	761.5	753.9	744.1	733.7	726.0	725.3	724.6	722.5
12.5°	808.2	806.1	804.0	796.4	788.7	773.4	761.5	753.9	753.2	753.9	751.1
15°	857.0	852.1	850.0	836.8	820.1	803.3	788.7	781.7	779.6	780.3	778.3
17.5°	894.6	894.6	889.7	875.1	853.5	830.5	815.2	811.0	810.3	810.3	811.0
20°	924.6	923.9	919.0	907.1	881.4	858.4	850.7	849.3	848.6	848.6	850.7
22.5°	941.3	939.9	937.8	924.6	904.4	889.0	889.7	893.9	895.3	896.7	899.5
25°	949.7	947.6	946.9	937.8	923.2	921.1	933.6	944.8	947.6	950.3	953.8
27.5°	963.6	960.1	961.5	958.0	954.5	960.8	986.6	998.4	1000.5	1004.0	1006.1
30°	1001.9	1000.5	1006.1	1007.5	1010.3	1019.3	1043.0	1054.2	1059.0	1059.0	1068.8
32.5°	1075.1	1075.8	1077.2	1091.8	1096.7	1102.9	1115.5	1124.5	1125.2	1125.9	1135.0
35°	1173.3	1177.5	1189.3	1201.9	1213.7	1213.0	1205.4	1210.2	1206.7	1210.9	1211.6
37.5°	1297.3	1291.7	1309.2	1337.7	1355.8	1351.0	1316.8	1294.5	1300.8	1298.0	1295.9
40°	1392.8	1399.0	1432.5	1470.1	1484.0	1499.4	1454.8	1416.5	1410.9	1400.4	1394.2
42.5°	1524.5	1525.2	1552.3	1580.2	1620.6	1654.1	1625.5	1570.4	1553.7	1541.2	1514.0
45°	1646.4	1644.3	1666.6	1700.7	1748.8	1796.9	1807.3	1747.4	1741.1	1718.8	1683.3
47.5°	1727.9	1725.1	1740.4	1785.0	1863.1	1941.8	1985.0	1966.9	1955.0	1946.0	1890.2
50°	1782.9	1777.4	1794.8	1842.2	1929.3	2050.5	2163.4	2178.7	2173.8	2173.8	2138.3
52.5°	1824.1	1824.1	1836.6	1874.9	1963.4	2114.6	2316.6	2394.0	2400.3	2407.2	2405.1
55°	1801.1	1804.5	1835.9	1891.6	1985.0	2159.2	2443.5	2612.8	2647.6	2676.9	2710.3
57.5°	1722.3	1734.2	1776.0	1867.3	1990.6	2192.6	2584.2	2919.3	3017.6	3102.6	3234.9
60°	1607.4	1622.7	1683.3	1799.7	1949.5	2138.3	2633.7	3178.5	3334.6	3519.9	3865.5
62.5°	1410.2	1425.5	1484.7	1601.1	1729.3	1930.0	2428.8	3216.8	3466.3	3728.9	4251.5
65°	999.1	974.7	1043.0	1147.5	1294.5	1488.9	1962.7	2959.7	3318.6	3674.6	4319.8
67.5°	556.7	554.6	596.4	674.4	815.2	1024.2	1352.4	2270.0	2600.2	3003.6	3795.8
70°	383.9	388.1	414.6	498.9	615.2	795.7	963.6	1425.5	1663.1	1936.9	2715.9
72.5°	269.6	278.7	293.3	343.5	462.6	670.3	984.5	852.1	970.6	1157.3	1633.1
75°	158.2	164.4	174.9	199.3	263.4	448.0	1019.3	749.0	749.0	792.9	988.0
77.5°	97.5	97.5	103.8	113.6	140.0	219.5	726.0	841.7	818.0	792.9	795.0
80°	50.2	53.6	62.7	67.6	78.0	100.3	326.1	785.2	861.2	912.0	876.5
82.5°	23.0	25.8	38.3	41.1	45.3	53.0	112.2	446.6	598.5	788.0	984.5
85°	11.8	11.8	20.2	25.1	27.2	24.4	41.1	180.5	273.1	416.6	652.1
87.5°	2.1	2.1	3.5	4.2	6.3	5.6	7.0	10.5	17.4	18.8	19.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P154553

CATALOG NUMBER: TLM-F03-LED-E1-T2-8030

**CANDELA DISTRIBUTION (continued):**

	65°	66°	67°	68°	69°	70°	71°	72°	73°	74°	75°
0°	640.3	640.3	640.3	640.3	640.3	640.3	640.3	640.3	640.3	640.3	640.3
2.5°	652.8	653.5	652.8	652.1	650.8	650.8	650.8	650.1	650.1	650.1	649.4
5°	671.7	668.9	669.6	668.2	667.5	666.8	667.5	666.1	664.7	665.4	664.7
7.5°	695.3	693.9	691.2	691.2	690.5	689.1	689.1	687.0	686.3	684.9	684.2
10°	721.8	718.3	719.7	718.3	719.0	716.2	714.9	713.5	712.1	712.1	712.8
12.5°	749.0	748.3	746.2	744.8	744.8	742.7	743.4	742.7	740.6	739.9	737.8
15°	776.9	776.9	774.8	775.5	774.8	773.4	772.0	772.0	770.6	769.2	769.9
17.5°	809.6	809.6	809.6	809.6	810.3	808.2	808.9	807.5	806.1	808.9	808.9
20°	852.1	854.9	854.9	854.2	857.7	855.6	854.9	858.4	854.9	859.8	859.1
22.5°	900.9	903.7	903.7	906.5	907.1	909.2	910.6	909.2	912.0	914.8	914.8
25°	955.2	958.0	960.1	964.3	966.4	965.0	965.7	969.2	970.6	973.3	976.1
27.5°	1012.4	1013.1	1015.8	1020.7	1024.2	1025.6	1026.3	1031.9	1032.6	1034.0	1036.7
30°	1068.1	1075.1	1073.7	1079.9	1082.0	1084.1	1088.3	1090.4	1095.3	1098.1	1098.1
32.5°	1133.6	1132.2	1137.8	1142.6	1146.1	1149.6	1153.1	1155.9	1158.7	1160.1	1167.0
35°	1215.1	1217.9	1217.9	1218.6	1227.0	1227.6	1230.4	1236.7	1238.8	1243.0	1245.8
37.5°	1295.9	1291.1	1290.4	1290.4	1287.6	1289.7	1290.4	1291.1	1293.8	1294.5	1297.3
40°	1386.5	1380.2	1374.7	1371.2	1365.6	1357.9	1356.5	1353.1	1355.2	1354.5	1355.2
42.5°	1510.5	1493.1	1479.9	1470.1	1459.0	1450.6	1444.3	1435.3	1429.0	1421.3	1419.9
45°	1668.7	1635.9	1613.6	1597.6	1581.6	1558.6	1545.4	1531.4	1518.9	1506.3	1495.9
47.5°	1876.3	1841.5	1805.9	1776.7	1751.6	1714.7	1677.0	1656.1	1631.8	1610.2	1594.8
50°	2120.9	2079.1	2062.3	2021.2	1989.9	1934.1	1887.5	1853.3	1804.5	1771.8	1743.2
52.5°	2371.0	2360.5	2351.5	2316.6	2279.7	2247.7	2206.6	2146.6	2097.2	2059.6	2001.0
55°	2711.7	2716.6	2713.1	2694.3	2681.0	2650.4	2633.7	2581.4	2559.1	2504.8	2443.5
57.5°	3285.1	3324.1	3373.6	3393.1	3419.6	3394.5	3423.8	3459.3	3370.8	3401.5	3346.4
60°	4017.4	4196.4	4303.0	4434.0	4519.7	4639.6	4661.2	4692.5	4683.5	4700.9	4736.4
62.5°	4464.7	4677.2	4881.3	5029.7	5188.6	5276.4	5382.3	5456.1	5532.8	5584.3	5569.7
65°	4596.4	4815.1	5000.5	5162.8	5304.9	5412.2	5510.5	5603.1	5673.5	5723.0	5752.2
67.5°	4112.8	4398.5	4593.6	4783.8	4967.0	5079.9	5162.1	5252.0	5355.1	5440.8	5457.5
70°	3094.9	3523.4	3800.0	4027.8	4243.1	4395.0	4510.0	4593.6	4673.7	4735.0	4801.9
72.5°	1935.5	2310.4	2626.7	2922.1	3150.6	3359.7	3456.5	3641.8	3617.5	3664.1	3714.3
75°	1160.1	1342.6	1516.8	1725.1	1845.0	2019.1	2050.5	2081.1	2065.1	2012.9	2051.9
77.5°	806.1	836.1	834.7	822.8	810.3	779.6	739.9	718.3	703.7	682.8	691.2
80°	811.0	746.2	647.3	544.2	449.4	386.7	361.6	361.6	387.4	424.3	461.2
82.5°	969.2	900.2	802.6	671.7	532.3	433.4	367.2	340.7	345.6	383.2	430.6
85°	653.5	668.9	586.7	536.5	425.0	330.9	277.3	225.0	199.3	205.5	232.7
87.5°	23.7	28.6	10.5	13.9	9.8	8.4	8.4	9.1	6.3	7.7	7.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P154553

CATALOG NUMBER: TLM-F03-LED-E1-T2-8030

**CANDELA DISTRIBUTION (continued):**

	76°	77°	78°	79°	80°	81°	82°	83°	84°	85°	86°
0°	640.3	640.3	640.3	640.3	640.3	640.3	640.3	640.3	640.3	640.3	640.3
2.5°	648.7	648.0	648.0	646.6	646.6	645.9	645.9	645.2	644.5	644.5	643.8
5°	664.0	663.3	661.9	661.2	659.8	659.8	659.1	657.7	657.7	656.3	655.6
7.5°	685.6	684.2	682.8	682.1	681.4	679.3	679.3	677.9	677.9	676.5	675.8
10°	711.4	710.0	708.6	709.3	707.2	706.5	705.1	705.1	703.0	702.3	702.3
12.5°	739.2	738.5	738.5	736.4	735.8	735.1	732.3	732.3	732.3	730.9	731.6
15°	769.2	769.9	767.8	769.9	769.2	767.1	767.1	767.1	764.3	767.8	765.0
17.5°	809.6	811.7	810.3	811.0	809.6	809.6	810.3	809.6	811.0	811.0	815.2
20°	859.8	860.5	864.0	862.6	862.6	861.9	863.3	864.0	866.7	865.3	868.1
22.5°	914.8	918.3	919.0	921.8	921.8	921.1	922.5	925.3	926.7	928.7	928.1
25°	977.5	979.6	982.4	978.9	984.5	984.5	985.9	989.4	990.1	990.1	994.9
27.5°	1036.0	1041.6	1042.3	1045.8	1043.7	1045.1	1050.0	1052.1	1054.9	1054.9	1056.3
30°	1102.2	1104.3	1105.7	1109.9	1109.2	1109.9	1110.6	1114.1	1114.1	1117.6	1121.0
32.5°	1170.5	1171.9	1173.3	1177.5	1178.9	1181.7	1180.3	1183.1	1186.5	1187.2	1189.3
35°	1252.0	1253.4	1254.8	1261.1	1261.8	1266.7	1268.1	1266.7	1272.2	1268.8	1272.2
37.5°	1299.4	1305.7	1307.1	1311.3	1309.9	1313.3	1315.4	1318.2	1319.6	1322.4	1328.0
40°	1357.2	1359.3	1363.5	1365.6	1368.4	1369.1	1371.9	1374.0	1376.1	1382.3	1388.6
42.5°	1416.5	1419.3	1421.3	1424.1	1427.6	1430.4	1432.5	1438.8	1440.2	1444.3	1456.2
45°	1488.2	1486.8	1487.5	1488.2	1489.6	1493.1	1499.4	1505.6	1509.8	1519.6	1529.3
47.5°	1577.4	1568.4	1564.9	1559.3	1560.7	1568.4	1569.7	1580.2	1588.6	1597.6	1609.5
50°	1712.6	1688.2	1673.6	1658.9	1657.5	1661.7	1667.3	1678.4	1688.2	1700.0	1716.8
52.5°	1939.7	1893.0	1863.8	1823.4	1812.2	1810.1	1805.9	1812.2	1815.0	1831.0	1862.4
55°	2399.6	2313.2	2257.4	2194.7	2136.2	2118.8	2085.3	2092.3	2085.3	2095.1	2141.8
57.5°	3359.7	3290.7	3236.3	3156.2	3055.9	2949.3	2922.8	2813.4	2835.0	2897.7	2857.3
60°	4753.8	4728.7	4689.7	4651.4	4514.1	4436.8	4310.7	4296.8	4208.3	4209.0	4151.2
62.5°	5534.2	5566.2	5542.5	5531.4	5523.7	5499.3	5436.6	5361.4	5248.5	5167.0	5047.2
65°	5757.1	5730.0	5704.2	5700.7	5698.6	5738.3	5747.4	5694.4	5592.0	5465.2	5327.2
67.5°	5497.2	5481.9	5483.3	5454.0	5472.2	5541.1	5589.2	5574.6	5480.5	5327.2	5151.7
70°	4878.5	4848.6	4879.2	4917.6	4944.7	4984.4	5032.5	5044.4	4958.7	4801.2	4622.1
72.5°	3653.0	3657.9	3687.1	3697.6	3807.0	3795.8	3839.0	3698.3	3636.3	3486.5	3394.5
75°	1922.3	1890.9	1972.5	1799.7	1728.6	1778.1	1639.4	1506.3	1534.2	1557.2	1391.4
77.5°	679.3	635.4	560.9	530.9	441.7	374.1	305.9	275.9	259.9	251.5	241.1
80°	487.7	501.6	486.3	450.1	382.5	306.6	241.8	190.9	163.7	149.1	139.3
82.5°	493.3	548.3	572.7	562.3	501.0	379.0	250.1	159.6	118.4	98.9	92.0
85°	264.8	289.8	278.7	234.8	211.1	126.1	86.4	57.8	48.8	44.6	41.1
87.5°	10.5	8.4	7.0	7.0	7.7	8.4	7.0	7.7	7.0	7.0	7.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





TEST NUMBER: P154553

CATALOG NUMBER: TLM-F03-LED-E1-T2-8030

**CANDELA DISTRIBUTION (continued):**

	87°	88°	89°	90°	95°	105°	115°	125°	135°	145°	155°
0°	640.3	640.3	640.3	640.3	640.3	640.3	640.3	640.3	640.3	640.3	640.3
2.5°	642.4	642.4	642.4	641.7	640.3	636.8	633.3	630.5	628.5	626.4	623.6
5°	654.9	653.5	653.5	653.5	648.0	642.4	637.5	632.6	628.5	625.0	622.2
7.5°	675.8	675.1	672.3	671.7	667.5	658.4	652.8	644.5	639.6	634.7	633.3
10°	700.9	700.2	699.5	698.8	693.3	684.2	677.2	669.6	662.6	655.6	648.7
12.5°	730.2	729.5	728.8	726.7	724.6	719.7	712.1	703.7	695.3	680.7	673.0
15°	766.4	767.8	766.4	765.7	764.3	765.0	760.1	748.3	735.1	716.2	700.2
17.5°	814.5	813.1	812.4	815.2	814.5	818.0	816.6	801.2	781.0	751.1	723.2
20°	867.4	867.4	870.2	872.3	878.6	887.6	883.5	864.6	827.7	785.9	749.7
22.5°	930.8	932.2	935.0	933.6	943.4	958.0	959.4	932.9	884.9	827.0	776.2
25°	997.0	998.4	995.6	999.8	1015.8	1036.7	1040.9	1003.3	939.9	864.6	798.5
27.5°	1059.7	1061.1	1061.1	1066.7	1082.0	1117.6	1121.7	1079.9	995.6	897.4	814.5
30°	1121.0	1126.6	1128.0	1129.4	1152.4	1201.9	1210.9	1150.3	1044.4	921.8	825.6
32.5°	1198.4	1200.5	1203.3	1206.7	1233.2	1293.8	1293.8	1210.9	1075.8	937.1	827.7
35°	1281.3	1282.0	1288.3	1289.0	1326.6	1387.2	1375.4	1261.1	1098.1	933.6	812.4
37.5°	1331.5	1334.2	1340.5	1348.9	1388.6	1474.3	1447.1	1304.3	1102.2	910.6	777.6
40°	1393.5	1399.0	1405.3	1413.7	1472.9	1562.8	1507.7	1331.5	1084.8	865.3	725.3
42.5°	1460.4	1468.0	1477.8	1493.1	1563.5	1640.8	1553.7	1335.6	1045.1	814.5	663.3
45°	1535.6	1549.5	1560.7	1578.8	1658.2	1708.4	1581.6	1311.3	994.9	747.6	597.1
47.5°	1622.7	1633.8	1653.4	1672.9	1752.3	1754.4	1584.4	1263.9	926.7	680.7	526.7
50°	1730.0	1737.0	1766.2	1778.1	1852.6	1802.5	1564.2	1199.8	854.9	605.5	448.7
52.5°	1872.8	1882.6	1920.2	1938.3	1991.3	1867.9	1535.6	1130.1	772.7	521.2	368.6
55°	2155.0	2197.5	2224.0	2255.3	2289.5	2016.4	1523.1	1055.6	680.0	423.6	291.9
57.5°	2947.2	2933.3	2991.8	3062.8	3062.2	2355.7	1598.3	991.5	570.6	324.0	224.3
60°	4127.5	4140.7	4110.7	4153.2	4018.1	2776.5	1701.4	923.9	447.3	241.1	171.4
62.5°	5004.7	4928.0	4885.5	4835.3	4537.8	2822.5	1626.2	785.2	325.4	169.3	131.7
65°	5212.3	5122.4	5031.1	4935.7	4487.0	2544.5	1334.2	576.2	210.4	116.4	104.5
67.5°	5007.4	4863.2	4746.9	4648.6	4111.4	2109.0	975.4	353.9	120.5	94.1	89.2
70°	4476.5	4317.0	4128.9	4018.8	3462.1	1554.4	625.0	190.9	92.7	83.6	81.5
72.5°	3276.7	3145.8	2940.2	2814.1	2486.0	944.8	349.1	107.3	86.4	80.1	77.3
75°	1276.4	1208.1	1122.4	1129.4	1008.2	418.0	158.2	92.7	84.3	78.7	75.9
77.5°	219.5	213.9	197.9	197.9	225.0	152.6	105.2	93.4	83.6	77.3	72.5
80°	131.7	128.9	122.6	121.2	117.1	107.3	101.0	94.8	82.2	73.2	66.9
82.5°	86.4	82.9	80.8	80.1	87.1	94.1	94.8	94.1	78.0	63.4	54.3
85°	36.9	36.9	36.9	37.6	50.2	75.9	78.0	83.6	64.1	49.5	39.0
87.5°	6.3	7.7	7.7	8.4	9.1	16.7	20.9	27.2	21.6	20.9	18.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P154553

CATALOG NUMBER: TLM-F03-LED-E1-T2-8030

**CANDELA DISTRIBUTION (continued):**

	165°	175°	180°
0°	640.3	640.3	640.3
2.5°	622.9	621.5	621.5
5°	620.8	619.4	620.1
7.5°	629.2	626.4	627.1
10°	644.5	641.7	640.3
12.5°	664.0	660.5	660.5
15°	684.2	675.8	675.1
17.5°	700.9	690.5	689.1
20°	719.7	705.8	703.7
22.5°	737.1	718.3	715.5
25°	749.7	726.7	723.2
27.5°	755.3	728.1	725.3
30°	759.4	728.8	724.6
32.5°	755.3	722.5	719.0
35°	732.3	696.7	694.6
37.5°	692.6	652.8	650.1
40°	640.3	598.5	591.5
42.5°	573.4	534.4	526.7
45°	508.6	464.0	460.5
47.5°	438.9	396.4	398.5
50°	365.8	327.5	326.8
52.5°	296.1	262.7	260.6
55°	233.4	209.7	207.6
57.5°	184.6	172.1	170.0
60°	150.5	144.2	142.1
62.5°	121.2	119.1	118.4
65°	101.0	101.0	101.0
67.5°	87.8	88.5	88.5
70°	80.8	81.5	80.8
72.5°	78.0	80.1	80.1
75°	75.9	77.3	74.6
77.5°	74.6	75.2	70.4
80°	73.9	73.2	64.1
82.5°	64.1	62.0	54.3
85°	58.5	44.6	37.6
87.5°	30.0	20.9	16.0
90°	0.0	0.0	0.0

(END OF REPORT)