

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P197581

Luminaire Tested: **TT-C1-LED-E1-5MQ-PM-LWR-LW-8030**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P197581  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P115393)  
Test Lab: INNOVATION CENTER P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TT-C1-LED-E1-5MQ-PM-LWR-LW-8030  
Description: TOPTIER LED AREA/SITE LUMINAIRE  
MEDIUM DISTRIBUTION WITH LumaWatt WIRELESS SENSOR  
Light Source: (168) 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2986.2 lumens  
Efficiency: N/A  
Efficacy: 106.6 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type V - Short - Full Cutoff  
BUG Rating: B1 - U0 - G1


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



REPORT NUMBER: P197581  
 CATALOG NUMBER: TT-C1-LED-E1-5MQ-PM-LWR-LW-8030

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 6.2 fc  
 Type V - Short - Full Cutoff

REPORT NUMBER: P197581  
CATALOG NUMBER: TT-C1-LED-E1-5MQ-PM-LWR-LW-8030

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral    - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P197581

CATALOG NUMBER: TT-C1-LED-E1-5MQ-PM-LWR-LW-8030


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1493.1	0.0	1493.1
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	1493.1	0.0	1493.1
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	2986.2	0.0	2986.2
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	58.7	2.0
10°-20°	173.1	5.8
20°-30°	277.3	9.3
30°-40°	365.0	12.2
40°-50°	454.7	15.2
50°-60°	535.6	17.9
60°-70°	569.4	19.1
70°-80°	427.0	14.3
80°-90°	125.4	4.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2986.2	100.0
0°-180°	2986.2	100.0



REPORT NUMBER: P197581


CATALOG NUMBER: TT-C1-LED-E1-5MQ-PM-LWR-LW-8030

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	254.6	8.5			
FM	(30°-60°)	677.6	22.7			
FH	(60°-80°)	498.2	16.7			G0/660
FVH	(80°-90°)	62.7	2.1			G1/100
BL	(0°-30°)	254.6	8.5	B1/500		
BM	(30°-60°)	677.6	22.7	B1/1000		
BH	(60°-80°)	498.2	16.7	B1/500		G0/660
BVH	(80°-90°)	62.7	2.1			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B1-U0-G1**

Type V Short





REPORT NUMBER: P197581

CATALOG NUMBER: TT-C1-LED-E1-5MQ-PM-LWR-LW-8030

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	616.0	616.0	616.0	616.0	616.0	616.0	616.0	616.0	616.0	616.0	616.0
2.5°	615.3	615.3	615.3	616.0	616.0	616.0	616.0	616.0	616.0	616.0	616.0
5°	615.3	615.3	615.3	615.3	615.3	615.3	616.0	616.0	616.0	616.0	616.0
7.5°	614.1	614.1	614.1	614.1	614.1	614.7	614.7	614.7	614.7	614.7	614.7
10°	612.8	612.8	612.8	612.8	613.5	613.5	613.5	613.5	613.5	613.5	613.5
12.5°	611.6	611.6	611.0	611.6	611.6	611.6	612.2	612.2	612.2	612.2	612.2
15°	609.1	609.1	609.7	609.7	610.3	610.3	610.3	610.3	611.0	611.0	611.0
17.5°	607.8	607.8	608.5	609.1	609.1	609.7	610.3	610.3	611.0	611.0	611.0
20°	609.7	609.7	609.7	610.3	611.0	611.6	612.2	612.8	612.8	613.5	612.8
22.5°	606.0	606.0	606.0	606.6	606.6	606.6	607.2	607.8	607.8	608.5	607.8
25°	599.1	599.1	599.7	599.7	600.3	600.3	601.0	601.0	601.0	601.6	601.6
27.5°	592.2	591.6	592.8	592.8	593.5	593.5	594.1	594.7	594.7	594.7	595.3
30°	584.7	584.7	585.3	585.3	586.0	586.6	587.2	587.8	587.8	588.5	588.5
32.5°	576.6	577.2	577.8	578.5	579.1	580.3	581.0	581.6	582.2	582.8	582.2
35°	570.9	571.6	572.2	573.4	575.3	576.6	577.8	579.1	579.7	579.7	579.7
37.5°	572.2	572.8	574.1	576.6	579.7	581.6	584.1	586.0	586.6	587.2	587.2
40°	579.1	580.3	582.2	585.3	589.1	592.2	596.0	597.8	599.1	599.7	599.1
42.5°	578.5	580.3	582.2	586.0	590.3	593.5	597.2	599.1	600.3	601.0	600.3
45°	576.6	577.8	579.7	583.5	586.6	591.0	594.7	596.6	598.5	599.1	598.5
47.5°	572.2	572.2	572.8	576.6	581.0	586.6	589.7	592.8	594.7	594.7	594.7
50°	566.6	569.1	570.3	575.3	579.7	584.7	590.3	594.7	595.3	596.0	595.3
52.5°	566.6	567.2	571.6	574.7	583.5	591.0	596.6	601.0	604.7	605.3	605.3
55°	576.6	577.8	580.3	587.8	594.7	606.0	615.3	619.1	621.6	624.1	621.6
57.5°	577.2	581.6	586.0	594.7	605.3	614.7	622.8	629.7	631.6	636.0	631.0
60°	569.7	570.9	575.3	586.0	599.7	609.7	617.2	623.5	629.7	627.2	629.7
62.5°	557.8	560.9	567.2	575.3	586.6	598.5	609.7	611.6	621.0	618.5	622.2
65°	548.4	550.9	557.2	569.1	582.8	590.3	602.8	610.3	609.7	614.7	609.1
67.5°	525.3	527.2	532.8	544.7	557.8	569.1	572.8	584.7	586.0	592.8	586.6
70°	487.1	491.5	499.7	510.9	521.5	530.9	537.8	544.1	547.8	549.1	547.8
72.5°	439.6	446.5	452.8	463.4	474.0	480.3	484.6	493.4	495.9	499.7	498.4
75°	390.8	390.8	397.1	405.2	413.4	417.1	419.6	425.2	428.4	432.7	429.0
77.5°	323.9	327.7	333.3	340.2	338.9	340.8	340.8	343.9	342.7	345.8	348.3
80°	253.9	257.6	262.6	267.7	267.0	262.6	265.8	262.0	260.8	261.4	263.3
82.5°	181.4	183.9	188.2	191.4	191.4	188.2	189.5	185.7	187.0	183.9	186.4
85°	103.8	106.9	110.1	113.2	113.2	111.3	113.2	108.2	108.8	108.8	108.8
87.5°	25.6	28.1	29.4	31.3	30.0	33.1	35.0	31.9	32.5	31.3	33.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P197581

CATALOG NUMBER: TT-C1-LED-E1-5MQ-PM-LWR-LW-8030

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	616.0	616.0	616.0	616.0	616.0	616.0	616.0	616.0
2.5°	616.0	615.3	616.0	616.0	616.0	616.0	615.3	615.3
5°	616.0	616.0	616.0	615.3	615.3	615.3	615.3	615.3
7.5°	614.7	614.7	614.7	614.1	614.1	614.1	614.1	614.1
10°	613.5	613.5	612.8	612.8	612.8	612.8	612.8	612.8
12.5°	612.2	612.2	611.6	611.6	611.6	611.6	611.6	611.0
15°	611.0	611.0	610.3	610.3	609.7	609.7	609.1	609.1
17.5°	611.0	610.3	609.7	609.1	609.1	608.5	607.8	607.8
20°	612.8	612.2	611.6	611.0	610.3	609.7	609.7	609.1
22.5°	607.8	607.2	606.6	606.6	606.0	606.0	606.0	605.3
25°	601.6	601.0	601.0	599.7	599.7	599.1	599.1	598.5
27.5°	594.7	594.1	594.1	593.5	592.8	592.2	591.6	591.6
30°	587.8	587.2	587.2	586.6	585.3	585.3	584.7	584.1
32.5°	581.6	581.6	581.0	579.7	578.5	577.8	576.6	576.6
35°	579.7	578.5	577.2	575.3	573.4	572.2	571.6	570.9
37.5°	586.6	584.7	581.6	579.7	577.2	574.7	573.4	572.2
40°	598.5	595.3	592.2	589.1	585.3	582.2	579.7	579.1
42.5°	599.1	597.2	594.1	590.3	586.0	582.2	579.7	579.1
45°	597.2	594.7	591.0	586.6	583.5	579.1	577.2	576.6
47.5°	592.8	590.3	586.6	580.3	575.9	572.8	572.2	572.2
50°	595.3	590.3	584.1	580.3	575.9	570.9	569.1	567.8
52.5°	601.0	596.0	592.2	584.1	574.7	570.3	567.8	565.9
55°	619.1	616.6	605.3	594.1	587.2	581.6	579.1	577.8
57.5°	631.0	622.2	612.8	605.3	597.2	587.8	581.6	578.5
60°	624.7	615.3	611.0	601.0	584.1	574.1	570.3	568.4
62.5°	611.0	611.0	599.1	583.5	577.2	568.4	561.6	559.1
65°	610.3	602.2	590.3	584.7	569.7	556.6	549.7	548.4
67.5°	584.1	572.8	569.7	557.2	544.7	532.8	527.8	525.3
70°	544.1	540.3	530.9	522.8	511.5	499.0	492.2	489.7
72.5°	493.4	487.1	482.8	475.9	465.3	449.6	444.0	440.9
75°	424.6	421.5	421.5	414.0	404.0	394.6	394.0	392.7
77.5°	341.4	342.7	345.8	337.7	340.8	335.8	331.4	328.3
80°	259.5	265.1	265.8	267.7	269.5	262.6	259.5	255.8
82.5°	184.5	187.6	191.4	192.0	193.2	188.2	185.7	182.0
85°	108.8	110.7	113.8	113.8	113.8	109.4	108.2	105.1
87.5°	31.9	31.9	33.8	31.9	31.9	31.9	28.8	30.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)