

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P197965

Luminaire Tested: **TT-C1-LED-E1-RW-PM-MS/DIM-8030**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P197965  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P34692)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TT-C1-LED-E1-RW-PM-MS/DIM-8030  
Description: TOPTIER LED AREA/SITE LUMINAIRE  
RECTANGULAR DISTRIBUTION WITH DIMMING OCCUPANCY SENSOR  
Light Source: (168) 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2548.2 lumens  
Efficiency: N/A  
Efficacy: 91.0 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type IV - Short - Semi-Cutoff  
BUG Rating: B2 - U0 - G2

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT




REPORT NUMBER: P197965

CATALOG NUMBER: TT-C1-LED-E1-RW-PM-MS/DIM-8030

### Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 1.7 fc  
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P197965

CATALOG NUMBER: TT-C1-LED-E1-RW-PM-MS/DIM-8030

### Luminous Intensity Polar Plot



— Vertical Plane Through 88-Deg Lateral    - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P197965

CATALOG NUMBER: TT-C1-LED-E1-RW-PM-MS/DIM-8030


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1274.1	0.0	1274.1
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	1274.1	0.0	1274.1
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	2548.2	0.0	2548.2
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	11.9	0.5
10°-20°	40.6	1.6
20°-30°	86.3	3.4
30°-40°	164.8	6.5
40°-50°	303.0	11.9
50°-60°	524.7	20.6
60°-70°	682.6	26.8
70°-80°	559.4	22.0
80°-90°	174.9	6.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2548.2	100.0
0°-180°	2548.2	100.0



REPORT NUMBER: P197965


CATALOG NUMBER: TT-C1-LED-E1-RW-PM-MS/DIM-8030

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	69.4	2.7			
FM	(30°-60°)	496.2	19.5			
FH	(60°-80°)	621.0	24.4			G0/660
FVH	(80°-90°)	87.4	3.4			G1/100
BL	(0°-30°)	69.4	2.7	B0/110		
BM	(30°-60°)	496.2	19.5	B1/1000		
BH	(60°-80°)	621.0	24.4	B2/1000		G2/1000
BVH	(80°-90°)	87.4	3.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G2**

Type IV Short





REPORT NUMBER: P197965

CATALOG NUMBER: TT-C1-LED-E1-RW-PM-MS/DIM-8030

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	88°
0°	119.1	119.1	119.1	119.1	119.1	119.1	119.1	119.1	119.1	119.1	119.1
2.5°	120.1	120.1	120.1	120.1	120.1	120.1	120.1	120.1	120.1	120.1	120.1
5°	122.3	122.3	122.3	122.8	122.8	122.8	122.8	122.8	122.3	122.3	122.3
7.5°	125.0	125.0	125.5	125.5	125.5	125.5	125.0	125.0	124.4	124.4	124.4
10°	129.3	129.3	129.8	129.8	129.3	128.7	128.7	128.7	128.2	128.2	128.2
12.5°	135.2	135.2	135.7	135.2	134.6	134.1	134.1	133.6	133.0	133.0	133.0
15°	143.2	143.2	142.7	141.6	140.5	140.5	138.9	138.9	138.9	138.9	138.4
17.5°	153.9	153.4	151.3	150.7	149.1	148.0	147.0	146.4	145.9	145.9	146.4
20°	165.7	164.7	162.0	162.0	159.3	157.7	156.6	155.5	155.5	155.0	154.5
22.5°	179.7	178.6	175.4	174.3	171.6	169.0	167.9	165.2	164.7	164.7	165.2
25°	193.6	194.2	191.5	189.3	185.6	182.9	179.1	177.5	175.9	175.9	174.9
27.5°	209.7	210.2	207.0	204.4	201.1	195.8	193.6	191.5	189.9	190.9	189.9
30°	226.9	227.9	225.3	222.0	217.2	211.9	209.2	208.6	207.0	208.1	207.6
32.5°	246.7	246.2	244.6	241.4	234.9	230.6	228.5	227.9	229.0	229.6	229.0
35°	269.8	267.6	266.0	261.2	255.3	252.1	249.9	252.1	256.9	260.1	259.1
37.5°	293.9	290.7	289.1	283.7	278.4	276.8	279.4	283.7	288.6	292.8	292.8
40°	313.8	314.8	311.1	306.3	302.0	303.6	308.4	315.9	325.6	329.9	329.3
42.5°	333.6	336.8	333.1	328.2	328.8	333.6	340.6	354.5	376.0	382.4	381.9
45°	351.3	358.3	355.1	351.8	356.7	364.7	383.5	414.6	444.1	466.1	467.7
47.5°	374.4	378.1	376.5	376.5	384.0	402.8	431.2	474.7	505.8	526.7	529.9
50°	400.7	396.9	397.4	402.3	421.0	448.9	487.5	528.3	584.1	593.7	596.4
52.5°	422.6	416.2	420.0	429.1	456.4	491.8	540.1	623.8	695.1	759.5	768.6
55°	445.2	437.7	445.2	459.7	499.9	549.2	620.0	717.1	792.2	832.4	837.2
57.5°	462.3	461.3	472.0	492.9	542.3	608.2	688.1	771.3	821.7	850.1	854.4
60°	483.8	484.9	497.2	525.1	584.1	647.4	706.9	783.1	833.0	849.6	854.4
62.5°	504.2	508.5	522.9	554.6	606.1	654.3	711.7	804.0	867.3	903.2	900.0
65°	523.5	527.8	544.9	566.4	613.6	666.7	762.7	846.4	902.1	941.8	946.1
67.5°	542.8	548.2	555.1	572.3	617.9	667.8	750.9	821.2	866.2	893.6	895.2
70°	559.4	558.9	557.3	562.1	590.5	629.1	706.4	762.2	804.5	827.1	832.4
72.5°	561.6	560.0	541.2	527.2	536.4	566.9	640.9	685.5	717.6	736.4	740.2
75°	543.9	534.7	497.7	467.7	466.1	496.7	558.9	591.1	610.4	634.5	636.1
77.5°	486.5	476.3	435.0	394.2	394.2	414.1	466.1	483.3	507.4	525.6	530.5
80°	392.1	391.0	348.1	315.9	304.1	320.7	363.1	369.5	387.8	403.3	408.2
82.5°	283.7	275.7	252.1	224.7	215.1	225.8	254.8	261.2	268.2	282.1	288.0
85°	171.6	172.2	156.1	140.5	128.2	131.9	154.5	163.6	172.7	181.8	185.0
87.5°	61.7	71.3	55.8	49.3	42.9	40.8	47.7	59.0	69.2	82.1	89.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P197965

CATALOG NUMBER: TT-C1-LED-E1-RW-PM-MS/DIM-8030

**CANDELA DISTRIBUTION (continued):**

	90°
0°	119.1
2.5°	120.1
5°	121.8
7.5°	124.4
10°	128.2
12.5°	133.0
15°	138.4
17.5°	145.4
20°	154.5
22.5°	164.1
25°	175.4
27.5°	190.9
30°	207.0
32.5°	229.0
35°	261.7
37.5°	292.8
40°	330.9
42.5°	384.0
45°	469.8
47.5°	529.4
50°	601.3
52.5°	761.1
55°	838.9
57.5°	855.5
60°	854.4
62.5°	908.6
65°	945.6
67.5°	896.2
70°	834.6
72.5°	738.6
75°	639.9
77.5°	533.1
80°	410.3
82.5°	285.9
85°	192.6
87.5°	79.4
90°	0.0

(END OF REPORT)