

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P198110

Luminaire Tested: **TT-C1-LED-E1-RW-PM-SG-MS/DIM**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P198110  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P34700)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TT-C1-LED-E1-RW-PM-SG-MS/DIM  
Description: TOPTIER LED AREA/SITE LUMINAIRE  
RECTANGULAR DISTRIBUTION WITH SOFTENING GLASS LENS AND DIMMING OCCUPANCY  
SENSOR  
Light Source: (168) 4000K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2887.3 lumens  
Efficiency: N/A  
Efficacy: 103.1 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type III - Short - Full Cutoff  
BUG Rating: B2 - U0 - G2

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT




REPORT NUMBER: P198110

CATALOG NUMBER: TT-C1-LED-E1-RW-PM-SG-MS/DIM

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 2.7 fc  
 Type III - Short - Full Cutoff

REPORT NUMBER: P198110  
CATALOG NUMBER: TT-C1-LED-E1-RW-PM-SG-MS/DIM

### Luminous Intensity Polar Plot



— Vertical Plane Through 90-Deg Lateral    - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P198110

CATALOG NUMBER: TT-C1-LED-E1-RW-PM-SG-MS/DIM


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1443.7	0.0	1443.7
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	1443.7	0.0	1443.7
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	2887.3	0.0	2887.3
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	17.0	0.6
10°-20°	59.0	2.0
20°-30°	128.6	4.5
30°-40°	258.2	8.9
40°-50°	482.1	16.7
50°-60°	710.1	24.6
60°-70°	715.3	24.8
70°-80°	427.0	14.8
80°-90°	90.0	3.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2887.3	100.0
0°-180°	2887.3	100.0



REPORT NUMBER: P198110


CATALOG NUMBER: TT-C1-LED-E1-RW-PM-SG-MS/DIM

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	102.3	3.5			
FM	(30°-60°)	725.2	25.1			
FH	(60°-80°)	571.2	19.8			G0/660
FVH	(80°-90°)	45.0	1.6			G1/100
BL	(0°-30°)	102.3	3.5	B0/110		
BM	(30°-60°)	725.2	25.1	B1/1000		
BH	(60°-80°)	571.2	19.8	B2/1000		G2/1000
BVH	(80°-90°)	45.0	1.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G2**

Type III Short





REPORT NUMBER: P198110

CATALOG NUMBER: TT-C1-LED-E1-RW-PM-SG-MS/DIM

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	171.7	171.7	171.7	171.7	171.7	171.7	171.7	171.7	171.7	171.7	171.7
2.5°	173.0	173.0	173.0	173.0	173.0	172.3	173.0	172.3	172.3	172.3	172.3
5°	174.8	174.8	174.8	175.5	175.5	175.5	175.5	174.8	175.5	174.8	175.5
7.5°	179.2	179.2	179.2	179.2	179.2	179.2	179.9	179.2	179.9	179.2	179.2
10°	184.9	184.9	184.9	184.9	185.5	185.5	185.5	186.1	186.1	186.1	186.1
12.5°	193.0	193.0	193.0	193.0	193.0	193.0	193.6	193.6	194.3	194.3	194.3
15°	203.7	203.7	203.0	203.0	203.0	203.7	203.7	204.9	204.3	204.3	204.3
17.5°	216.8	216.2	216.2	216.2	216.2	216.2	216.2	217.5	217.5	217.5	218.1
20°	231.2	232.5	231.9	230.6	230.6	230.6	231.2	232.5	232.5	234.4	235.0
22.5°	251.3	251.9	250.7	250.0	248.2	248.2	250.0	250.7	253.2	252.5	253.2
25°	272.6	272.0	271.3	270.1	270.1	270.1	271.3	273.2	275.1	277.0	277.0
27.5°	296.4	295.8	295.2	294.5	293.3	295.2	296.4	300.8	302.1	306.4	305.2
30°	322.7	323.4	322.1	321.5	320.9	321.5	326.5	332.8	337.8	340.9	341.5
32.5°	352.2	352.8	352.2	350.9	352.2	355.3	361.6	369.7	379.8	385.4	387.3
35°	384.8	386.0	384.8	386.0	387.3	392.9	404.2	416.7	434.3	439.3	442.4
37.5°	419.9	418.6	418.0	419.9	425.5	437.4	453.1	475.0	493.2	508.2	508.2
40°	455.0	455.6	456.2	456.2	466.9	483.2	508.9	538.3	565.3	584.7	585.3
42.5°	492.6	492.6	492.6	498.2	511.4	537.1	570.3	613.5	650.5	668.6	671.2
45°	530.8	533.3	534.5	542.1	561.5	594.1	637.9	690.0	737.0	761.4	760.1
47.5°	568.4	571.5	574.0	585.3	611.6	646.7	701.2	763.9	817.2	844.7	847.2
50°	607.2	605.4	610.4	624.2	653.6	698.7	757.0	829.1	889.9	923.7	926.2
52.5°	632.9	632.3	637.3	651.7	686.2	737.0	804.0	886.1	951.9	987.0	997.0
55°	651.1	650.5	656.1	673.0	710.6	764.5	837.2	923.7	990.1	1026.5	1031.5
57.5°	659.2	659.9	664.9	682.4	721.3	777.7	852.9	936.2	999.5	1033.4	1037.8
60°	658.0	658.6	663.0	679.9	718.2	772.7	845.4	923.7	983.9	1015.2	1020.2
62.5°	644.8	644.2	648.0	662.4	696.2	747.0	816.5	890.5	947.5	976.3	982.0
65°	617.3	616.6	616.6	629.2	658.0	701.2	767.0	832.8	886.1	913.7	914.9
67.5°	572.1	572.1	570.9	578.4	599.7	641.7	698.1	758.3	801.5	827.2	831.0
70°	511.4	512.6	508.2	512.6	530.2	563.4	613.5	661.8	695.6	725.0	726.9
72.5°	444.9	439.9	438.0	439.3	452.5	473.8	517.0	557.7	589.1	609.1	612.9
75°	359.1	359.1	357.8	355.9	363.5	384.8	413.6	446.8	473.1	486.9	491.9
77.5°	275.1	277.6	273.9	273.9	279.5	295.8	320.9	339.0	357.8	367.2	364.7
80°	195.5	194.9	193.0	191.8	198.0	207.4	227.5	238.1	243.8	252.5	256.3
82.5°	120.9	122.2	124.1	118.4	120.9	129.7	140.4	146.0	148.5	152.3	151.7
85°	59.5	60.2	60.8	61.4	61.4	64.5	70.8	73.3	75.2	77.1	75.8
87.5°	21.9	20.7	20.1	20.1	20.1	20.7	23.8	23.2	24.4	24.4	25.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)