

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P197809

Luminaire Tested: **TT-C4-LED-E1-5WQ-PM-CG-LWR-LW-8030**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P197809  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P115528)  
Test Lab: INNOVATION CENTER P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TT-C4-LED-E1-5WQ-PM-CG-LWR-LW-8030  
Description: TOPTIER LED AREA/SITE LUMINAIRE  
WIDE DISTRIBUTION WITH CLEAR GLASS LENS AND LumaWatt WIRELESS SENSOR  
Light Source: (160) 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4513.3 lumens  
Efficiency: N/A  
Efficacy: 77.8 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type V - Short - Full Cutoff  
BUG Rating: B2 - U0 - G1

Input Watts (W): 58  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT




REPORT NUMBER: P197809

CATALOG NUMBER: TT-C4-LED-E1-5WQ-PM-CG-LWR-LW-8030

### Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd  
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 4.1 fc  
 Type V - Short - Full Cutoff

REPORT NUMBER: P197809

CATALOG NUMBER: TT-C4-LED-E1-5WQ-PM-CG-LWR-LW-8030

### Luminous Intensity Polar Plot



— Vertical Plane Through 50-Deg Lateral    - - - Horizontal Cone Through 59-Deg Vertical

REPORT NUMBER: P197809

CATALOG NUMBER: TT-C4-LED-E1-5WQ-PM-CG-LWR-LW-8030


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	2256.6	0.0	2256.6
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	2256.6	0.0	2256.6
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	4513.3	0.0	4513.3
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	37.3	0.8
10°-20°	126.0	2.8
20°-30°	253.7	5.6
30°-40°	436.5	9.7
40°-50°	720.7	16.0
50°-60°	1014.8	22.5
60°-70°	1085.6	24.1
70°-80°	689.6	15.3
80°-90°	149.0	3.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4513.3	100.0
0°-180°	4513.3	100.0



REPORT NUMBER: P197809


CATALOG NUMBER: TT-C4-LED-E1-5WQ-PM-CG-LWR-LW-8030

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	208.5	4.6			
FM	(30°-60°)	1086.0	24.1			
FH	(60°-80°)	887.6	19.7			G1/1800
FVH	(80°-90°)	74.5	1.7			G1/100
BL	(0°-30°)	208.5	4.6	B1/500		
BM	(30°-60°)	1086.0	24.1	B2/2500		
BH	(60°-80°)	887.6	19.7	B2/1000		G1/1800
BVH	(80°-90°)	74.5	1.7			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G1**

Type V Short





REPORT NUMBER: P197809

CATALOG NUMBER: TT-C4-LED-E1-5WQ-PM-CG-LWR-LW-8030

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	375.6	375.6	375.6	375.6	375.6	375.6	375.6	375.6	375.6	375.6	375.6
2.5°	383.6	382.6	382.6	382.6	382.6	382.6	382.6	382.6	382.6	382.6	382.6
5°	385.6	385.6	386.6	386.6	387.6	387.6	387.6	388.6	388.6	388.6	389.6
7.5°	389.6	388.6	389.6	389.6	389.6	390.6	390.6	390.6	391.6	392.6	392.6
10°	402.6	401.6	402.6	402.6	402.6	400.6	400.6	401.6	400.6	400.6	400.6
12.5°	417.6	417.6	418.6	419.6	419.6	418.6	417.6	416.6	415.6	415.6	415.6
15°	431.6	432.6	433.6	435.6	436.6	436.6	437.6	438.6	437.6	437.6	436.6
17.5°	453.5	455.5	456.5	457.5	457.5	457.5	459.5	462.5	465.5	467.5	465.5
20°	490.5	491.5	493.5	493.5	492.5	493.5	495.5	496.5	498.5	500.5	501.5
22.5°	515.5	517.5	520.5	520.5	519.5	520.5	522.5	522.5	520.5	521.5	523.5
25°	536.5	537.5	539.5	540.5	541.5	546.4	550.4	549.4	545.4	546.4	545.4
27.5°	561.4	563.4	565.4	565.4	565.4	568.4	572.4	574.4	577.4	576.4	573.4
30°	594.4	597.4	598.4	597.4	599.4	602.4	601.4	603.4	608.4	613.4	607.4
32.5°	620.4	623.4	626.4	630.4	637.4	641.3	639.4	640.4	643.3	647.3	647.3
35°	659.3	664.3	666.3	667.3	674.3	682.3	688.3	693.3	692.3	689.3	694.3
37.5°	718.3	723.3	725.3	729.3	738.3	740.2	749.2	761.2	765.2	761.2	761.2
40°	781.2	786.2	796.2	805.2	819.2	822.2	833.2	838.2	848.1	849.1	843.1
42.5°	833.2	839.1	841.1	856.1	875.1	889.1	901.1	902.1	909.1	915.1	908.1
45°	889.1	894.1	897.1	911.1	921.1	938.0	957.0	965.0	968.0	967.0	971.0
47.5°	941.0	948.0	951.0	962.0	974.0	988.0	999.0	1022.0	1027.0	1017.0	1026.0
50°	973.0	981.0	988.0	1012.0	1033.0	1043.9	1052.9	1071.9	1082.9	1073.9	1076.9
52.5°	1023.0	1025.0	1031.0	1040.9	1071.9	1108.9	1118.9	1124.9	1140.8	1145.8	1131.9
55°	1090.9	1097.9	1102.9	1115.9	1128.9	1154.8	1198.8	1206.8	1202.8	1226.8	1201.8
57.5°	1100.9	1113.9	1128.9	1157.8	1183.8	1191.8	1217.8	1248.7	1245.7	1248.7	1250.7
59°	1094.9	1105.9	1118.9	1148.8	1193.8	1204.8	1217.8	1245.7	1258.7	1241.7	1261.7
60°	1096.9	1104.9	1111.9	1135.8	1183.8	1208.8	1216.8	1233.7	1258.7	1235.7	1259.7
62.5°	1088.9	1098.9	1106.9	1120.9	1143.8	1178.8	1209.8	1201.8	1237.7	1219.8	1232.8
65°	1045.9	1056.9	1072.9	1092.9	1119.9	1129.9	1160.8	1177.8	1169.8	1189.8	1168.8
67.5°	974.0	984.0	994.0	1018.0	1047.9	1060.9	1068.9	1099.9	1088.9	1111.9	1087.9
70°	878.1	889.1	903.1	916.1	943.0	954.0	963.0	977.0	981.0	981.0	979.0
72.5°	763.2	772.2	781.2	794.2	810.2	820.2	824.2	827.2	843.1	837.2	838.2
75°	633.4	642.3	646.3	651.3	662.3	661.3	665.3	663.3	673.3	669.3	667.3
77.5°	495.5	498.5	509.5	509.5	506.5	511.5	506.5	503.5	501.5	503.5	503.5
80°	343.7	352.6	359.6	364.6	366.6	364.6	365.6	361.6	361.6	358.6	359.6
82.5°	211.8	220.8	223.8	228.8	229.8	229.8	229.8	226.8	227.8	224.8	226.8
85°	103.9	103.9	107.9	112.9	113.9	115.9	115.9	115.9	115.9	115.9	116.9
87.5°	26.0	26.0	28.0	31.0	31.0	32.0	33.0	34.0	34.0	35.0	35.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P197809

CATALOG NUMBER: TT-C4-LED-E1-5WQ-PM-CG-LWR-LW-8030

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	375.6	375.6	375.6	375.6	375.6	375.6	375.6	375.6
2.5°	382.6	382.6	382.6	382.6	382.6	382.6	382.6	382.6
5°	389.6	388.6	388.6	387.6	387.6	386.6	386.6	386.6
7.5°	393.6	393.6	392.6	391.6	390.6	390.6	391.6	391.6
10°	401.6	403.6	404.6	404.6	403.6	403.6	402.6	402.6
12.5°	414.6	416.6	418.6	420.6	420.6	419.6	417.6	416.6
15°	434.6	434.6	435.6	436.6	436.6	434.6	430.6	430.6
17.5°	461.5	459.5	456.5	457.5	458.5	457.5	453.5	455.5
20°	498.5	494.5	492.5	490.5	494.5	494.5	488.5	488.5
22.5°	525.5	522.5	517.5	516.5	519.5	521.5	516.5	513.5
25°	548.4	549.4	543.4	540.5	541.5	542.5	535.5	536.5
27.5°	573.4	574.4	571.4	566.4	564.4	567.4	562.4	560.4
30°	603.4	602.4	604.4	598.4	593.4	596.4	596.4	591.4
32.5°	642.3	639.4	640.4	633.4	627.4	626.4	622.4	616.4
35°	695.3	687.3	681.3	677.3	666.3	664.3	664.3	657.3
37.5°	764.2	752.2	741.2	741.2	724.3	719.3	722.3	713.3
40°	841.1	837.2	820.2	817.2	799.2	787.2	787.2	776.2
42.5°	897.1	902.1	882.1	870.1	858.1	839.1	841.1	827.2
45°	958.0	955.0	938.0	917.1	913.1	893.1	895.1	881.1
47.5°	1016.0	998.0	990.0	969.0	960.0	937.1	944.0	933.1
50°	1071.9	1051.9	1043.9	1019.0	1007.0	982.0	983.0	963.0
52.5°	1129.9	1111.9	1099.9	1067.9	1046.9	1029.0	1025.0	1016.0
55°	1204.8	1185.8	1156.8	1126.9	1110.9	1084.9	1087.9	1073.9
57.5°	1233.7	1221.8	1190.8	1172.8	1142.8	1116.9	1110.9	1085.9
59°	1232.8	1225.8	1194.8	1182.8	1139.8	1117.9	1106.9	1086.9
60°	1225.8	1223.8	1192.8	1177.8	1132.9	1112.9	1102.9	1089.9
62.5°	1204.8	1203.8	1168.8	1150.8	1113.9	1097.9	1091.9	1074.9
65°	1173.8	1156.8	1129.9	1117.9	1079.9	1067.9	1050.9	1034.0
67.5°	1099.9	1061.9	1057.9	1042.9	1010.0	995.0	984.0	968.0
70°	978.0	953.0	953.0	934.1	911.1	904.1	889.1	871.1
72.5°	826.2	820.2	823.2	801.2	790.2	786.2	773.2	757.2
75°	660.3	661.3	658.3	653.3	650.3	651.3	637.4	630.4
77.5°	500.5	509.5	507.5	500.5	507.5	506.5	494.5	491.5
80°	356.6	360.6	362.6	358.6	362.6	359.6	349.6	348.6
82.5°	224.8	225.8	227.8	223.8	224.8	223.8	216.8	216.8
85°	114.9	118.9	113.9	109.9	109.9	105.9	103.9	104.9
87.5°	34.0	36.0	32.0	32.0	30.0	28.0	27.0	27.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)