

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P198026

Luminaire Tested: **TT-C4-LED-E1-RW-PM-CG-LWR-LW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P198026
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P34697)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TT-C4-LED-E1-RW-PM-CG-LWR-LW
Description: TOPTIER LED AREA/SITE LUMINAIRE
RECTANGULAR DISTRIBUTION WITH CLEAR GLASS LENS AND LumaWatt WIRELESS
SENSOR
Light Source: (160) 4000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5059.8 lumens
Efficiency: N/A
Efficacy: 87.2 lumens/watt
Luminous Opening: Circular (Dia: 1.12' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B3 - U0 - G3

Input Watts (W): 58
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P198026

CATALOG NUMBER: TT-C4-LED-E1-RW-PM-CG-LWR-LW

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 3.8 fc
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P198026
CATALOG NUMBER: TT-C4-LED-E1-RW-PM-CG-LWR-LW

Luminous Intensity Polar Plot



— Vertical Plane Through 90-Deg Lateral - - - Horizontal Cone Through 62.5-Deg Vertical

REPORT NUMBER: P198026

CATALOG NUMBER: TT-C4-LED-E1-RW-PM-CG-LWR-LW


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2529.9	0.0	2529.9
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	2529.9	0.0	2529.9
	% Fixture	50.0	0.0	50.0
Total	Lumens	5059.8	0.0	5059.8
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.5	0.5
10°-20°	87.1	1.7
20°-30°	186.1	3.7
30°-40°	361.9	7.2
40°-50°	682.3	13.5
50°-60°	1166.0	23.0
60°-70°	1404.1	27.7
70°-80°	944.9	18.7
80°-90°	202.1	4.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5059.8	100.0
0°-180°	5059.8	100.0



REPORT NUMBER: P198026


CATALOG NUMBER: TT-C4-LED-E1-RW-PM-CG-LWR-LW

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	149.3	3.0			
FM	(30°-60°)	1105.1	21.8			
FH	(60°-80°)	1174.5	23.2			G1/1800
FVH	(80°-90°)	101.1	2.0			G2/225
BL	(0°-30°)	149.3	3.0	B1/500		
BM	(30°-60°)	1105.1	21.8	B2/2500		
BH	(60°-80°)	1174.5	23.2	B3/2500		G3/2500
BVH	(80°-90°)	101.1	2.0			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3

Type IV Short





REPORT NUMBER: P198026

CATALOG NUMBER: TT-C4-LED-E1-RW-PM-CG-LWR-LW

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	255.8	255.8	255.8	255.8	255.8	255.8	255.8	255.8	255.8	255.8	255.8
2.5°	258.2	258.2	258.2	258.2	258.2	258.2	259.4	259.4	259.4	259.4	259.4
5°	261.8	261.8	262.9	262.9	264.1	264.1	264.1	264.1	262.9	262.9	262.9
7.5°	267.7	267.7	268.9	270.0	270.0	268.9	268.9	267.7	267.7	267.7	267.7
10°	277.2	277.2	278.3	278.3	277.2	277.2	277.2	276.0	276.0	276.0	276.0
12.5°	287.8	289.0	290.2	289.0	287.8	286.6	286.6	285.4	285.4	285.4	285.4
15°	303.2	305.6	304.4	304.4	303.2	300.8	299.7	298.5	298.5	298.5	298.5
17.5°	326.9	326.9	323.3	321.0	318.6	317.4	316.2	315.1	315.1	315.1	315.1
20°	351.8	350.6	347.0	343.5	339.9	338.7	335.2	334.0	335.2	334.0	334.0
22.5°	381.4	380.2	375.5	371.9	367.2	362.4	361.2	357.7	356.5	355.3	356.5
25°	411.0	412.2	408.6	405.1	398.0	393.2	388.5	386.1	383.7	382.6	382.6
27.5°	445.3	447.7	445.3	438.2	431.1	427.6	420.5	418.1	416.9	418.1	418.1
30°	482.1	483.2	479.7	476.1	469.0	460.7	456.0	457.2	457.2	460.7	459.6
32.5°	527.1	525.9	521.1	518.8	511.7	504.6	502.2	503.4	508.1	510.5	510.5
35°	576.8	573.3	568.5	563.8	557.9	553.1	554.3	563.8	578.0	581.5	583.9
37.5°	626.6	620.6	620.6	613.5	608.8	612.3	619.4	637.2	647.9	664.5	660.9
40°	672.7	673.9	671.6	665.6	664.5	676.3	691.7	714.2	741.4	758.0	756.8
42.5°	715.4	726.0	718.9	720.1	726.0	745.0	769.9	813.7	868.2	889.5	889.5
45°	762.8	775.8	769.9	773.4	790.0	819.6	872.9	959.4	1034.0	1084.9	1084.9
47.5°	811.3	823.2	820.8	827.9	857.5	909.6	991.4	1099.1	1173.8	1223.5	1230.6
50°	872.9	868.2	869.4	887.1	938.1	1013.9	1118.1	1224.7	1347.9	1377.5	1391.7
52.5°	926.2	912.0	920.3	949.9	1023.3	1112.2	1241.3	1429.6	1600.1	1718.6	1728.1
55°	970.0	959.4	976.0	1017.4	1112.2	1229.4	1397.6	1628.6	1769.5	1841.8	1854.8
57.5°	1007.9	1003.2	1030.4	1083.7	1204.5	1347.9	1518.4	1705.6	1803.9	1859.5	1869.0
60°	1042.3	1045.8	1075.4	1146.5	1276.8	1408.3	1545.7	1703.2	1801.5	1845.3	1854.8
62.5°	1069.5	1075.4	1114.5	1188.0	1300.5	1405.9	1538.6	1719.8	1847.7	1916.4	1923.5
65°	1087.3	1093.2	1137.0	1188.0	1293.4	1395.2	1582.4	1736.3	1831.1	1901.0	1914.0
67.5°	1089.7	1097.9	1124.0	1166.6	1255.5	1345.5	1506.6	1617.9	1693.7	1736.3	1748.2
70°	1075.4	1073.1	1082.6	1100.3	1153.6	1215.2	1351.4	1434.3	1488.8	1532.6	1543.3
72.5°	1021.0	1017.4	994.9	974.8	994.9	1043.5	1160.7	1216.4	1253.1	1288.6	1295.7
75°	916.7	900.2	844.5	816.1	810.1	852.8	942.8	978.3	992.5	1032.8	1037.5
77.5°	733.2	726.0	678.7	628.9	624.2	650.2	718.9	734.3	722.5	766.3	779.3
80°	535.4	525.9	480.9	444.2	434.7	452.4	492.7	496.3	488.0	509.3	509.3
82.5°	342.3	332.8	313.9	286.6	266.5	277.2	307.9	307.9	307.9	313.9	317.4
85°	176.5	172.9	158.7	145.7	138.6	140.9	151.6	152.8	158.7	162.3	157.5
87.5°	49.7	52.1	49.7	43.8	42.6	41.5	46.2	47.4	50.9	53.3	55.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)