

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P386224

Luminaire Tested: **GPC-SA1D-760-U-SLR-HSS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P386224
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-28)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GPC-SA1D-760-U-SLR-HSS
Description: GALLEON PEDESTRIAN LUMINAIRE
(1) 70 CRI, 5700K, 1200mA LIGHTSQUARE WITH 16 LEDS AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6143 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type IV - Medium
BUG Rating: B1 - U0 - G2


Input Watts (W): 67
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P386224
 CATALOG NUMBER: GPC-SA1D-760-U-SLR-HSS

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 3.2 fc
 Type IV - Medium - N/A

REPORT NUMBER: P386224
CATALOG NUMBER: GPC-SA1D-760-U-SLR-HSS

Luminous Intensity Polar Plot



REPORT NUMBER: P386224

CATALOG NUMBER: GPC-SA1D-760-U-SLR-HSS


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 743.5 | 0.0 | 743.5 |
| | % Fixture | 12.1 | 0.0 | 12.1 |
| Street Side | Lumens | 5399.5 | 0.0 | 5399.5 |
| | % Fixture | 87.9 | 0.0 | 87.9 |
| Total | Lumens | 6143.0 | 0.0 | 6143.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 153.6 | 2.5 |
| 10°-20° | 305.7 | 5.0 |
| 20°-30° | 434.1 | 7.1 |
| 30°-40° | 641.2 | 10.4 |
| 40°-50° | 924.7 | 15.1 |
| 50°-60° | 1298.1 | 21.1 |
| 60°-70° | 1513.2 | 24.6 |
| 70°-80° | 773.6 | 12.6 |
| 80°-90° | 98.8 | 1.6 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 6143.0 | 100.0 |
| 0°-180° | 6143.0 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P386224


CATALOG NUMBER: GPC-SA1D-760-U-SLR-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 673.8 | 11.0 | | | |
| FM (30°-60°) | 2527.3 | 41.1 | | | |
| FH (60°-80°) | 2105.6 | 34.3 | | | G2/5000 |
| FVH (80°-90°) | 92.8 | 1.5 | | | G1/100 |
| BL (0°-30°) | 219.6 | 3.6 | B1/500 | | |
| BM (30°-60°) | 336.7 | 5.5 | B1/1000 | | |
| BH (60°-80°) | 181.2 | 2.9 | B1/500 | | G1/500 |
| BVH (80°-90°) | 6.0 | 0.1 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G2

Type IV Medium





REPORT NUMBER: P386224

CATALOG NUMBER: GPC-SA1D-760-U-SLR-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 1° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2001.1 | 2001.1 | 2001.1 | 2001.1 | 2001.1 | 2001.1 | 2001.1 | 2001.1 | 2001.1 | 2001.1 | 2001.1 |
| 2.5° | 2191.1 | 2174.2 | 2155.6 | 2094.8 | 2038.3 | 1973.7 | 1921.0 | 1884.4 | 1838.4 | 1778.7 | 1763.6 |
| 5° | 2175.4 | 2157.3 | 2098.9 | 1963.5 | 1845.1 | 1729.8 | 1618.7 | 1553.5 | 1472.6 | 1390.5 | 1370.1 |
| 7.5° | 2017.4 | 1998.5 | 1914.1 | 1728.7 | 1569.2 | 1402.7 | 1258.4 | 1169.0 | 1077.7 | 1002.6 | 962.7 |
| 10° | 1852.9 | 1832.3 | 1737.4 | 1512.4 | 1316.0 | 1165.5 | 1059.6 | 974.3 | 887.9 | 807.6 | 743.6 |
| 12.5° | 1739.7 | 1712.7 | 1609.6 | 1354.7 | 1183.6 | 1081.4 | 982.5 | 880.3 | 763.4 | 677.2 | 606.8 |
| 15° | 1692.3 | 1661.4 | 1552.6 | 1293.9 | 1136.7 | 1016.8 | 887.9 | 762.5 | 625.4 | 526.8 | 462.1 |
| 17.5° | 1729.0 | 1688.8 | 1572.1 | 1289.8 | 1077.9 | 914.7 | 751.7 | 604.5 | 455.7 | 355.9 | 309.9 |
| 20° | 1853.5 | 1800.8 | 1652.7 | 1288.6 | 1006.6 | 793.3 | 586.7 | 420.2 | 300.3 | 241.5 | 217.4 |
| 22.5° | 2049.7 | 1980.1 | 1768.5 | 1298.0 | 933.0 | 665.9 | 423.7 | 285.5 | 225.5 | 195.0 | 180.7 |
| 25° | 2286.6 | 2206.0 | 1935.3 | 1330.8 | 868.4 | 541.9 | 307.9 | 225.5 | 190.3 | 167.9 | 156.0 |
| 27.5° | 2511.8 | 2446.3 | 2146.0 | 1378.3 | 818.4 | 441.8 | 250.0 | 191.2 | 162.7 | 147.8 | 138.2 |
| 30° | 2736.8 | 2654.4 | 2362.2 | 1434.7 | 758.1 | 374.0 | 219.7 | 174.3 | 145.8 | 130.1 | 124.0 |
| 32.5° | 2900.3 | 2831.9 | 2531.6 | 1475.5 | 693.8 | 329.7 | 196.4 | 159.5 | 136.2 | 120.2 | 111.2 |
| 35° | 3092.7 | 3015.3 | 2676.8 | 1484.5 | 652.5 | 301.8 | 176.7 | 143.5 | 118.2 | 103.9 | 94.3 |
| 37.5° | 3300.5 | 3204.2 | 2844.5 | 1464.7 | 620.2 | 288.1 | 161.8 | 136.2 | 110.3 | 95.7 | 85.6 |
| 40° | 3530.4 | 3421.6 | 3005.4 | 1436.2 | 588.4 | 283.5 | 150.5 | 130.7 | 104.2 | 89.3 | 78.9 |
| 42.5° | 3772.5 | 3644.2 | 3144.8 | 1406.2 | 568.4 | 267.4 | 149.3 | 125.1 | 99.5 | 83.5 | 73.0 |
| 45° | 3975.9 | 3845.9 | 3288.0 | 1396.3 | 554.1 | 250.0 | 154.2 | 121.4 | 96.3 | 78.9 | 68.7 |
| 47.5° | 4138.0 | 4014.9 | 3434.6 | 1418.4 | 546.0 | 234.0 | 140.6 | 126.3 | 94.6 | 74.8 | 64.9 |
| 50° | 4331.6 | 4192.2 | 3641.3 | 1484.5 | 534.0 | 218.0 | 127.2 | 144.6 | 94.6 | 72.2 | 61.7 |
| 52.5° | 4574.3 | 4436.3 | 3871.8 | 1586.9 | 510.2 | 195.9 | 114.4 | 144.9 | 95.5 | 68.7 | 57.6 |
| 55° | 4879.6 | 4779.5 | 4200.9 | 1699.3 | 472.0 | 163.3 | 98.9 | 124.6 | 92.0 | 62.3 | 53.8 |
| 57.5° | 5172.3 | 5090.6 | 4501.0 | 1776.1 | 421.1 | 127.5 | 86.1 | 100.4 | 84.1 | 54.7 | 48.0 |
| 59° | 5252.4 | 5163.0 | 4611.0 | 1779.6 | 383.0 | 111.2 | 79.7 | 82.9 | 82.4 | 51.2 | 44.5 |
| 60° | 5252.4 | 5157.5 | 4642.7 | 1761.0 | 355.3 | 102.1 | 75.7 | 73.9 | 85.9 | 48.9 | 42.5 |
| 62.5° | 5157.2 | 5023.9 | 4539.7 | 1635.0 | 289.9 | 87.0 | 66.1 | 61.1 | 77.1 | 43.9 | 37.5 |
| 65° | 4959.3 | 4765.2 | 4188.7 | 1407.1 | 258.4 | 79.7 | 57.0 | 50.1 | 53.5 | 38.7 | 32.9 |
| 67.5° | 4629.3 | 4366.2 | 3682.6 | 1136.7 | 245.9 | 77.7 | 49.2 | 42.5 | 40.5 | 33.2 | 28.8 |
| 70° | 4048.1 | 3756.2 | 3068.3 | 893.7 | 235.1 | 76.8 | 41.3 | 35.8 | 32.6 | 27.9 | 24.4 |
| 72.5° | 2946.3 | 2641.9 | 2178.3 | 698.7 | 228.7 | 78.6 | 33.2 | 30.0 | 26.8 | 21.8 | 18.9 |
| 75° | 1685.3 | 1486.0 | 1224.3 | 461.6 | 195.0 | 75.1 | 25.6 | 25.0 | 19.2 | 15.7 | 13.1 |
| 77.5° | 870.7 | 844.3 | 733.7 | 177.2 | 93.4 | 32.9 | 16.9 | 14.6 | 11.3 | 9.6 | 7.9 |
| 80° | 375.7 | 371.6 | 321.6 | 51.2 | 24.7 | 18.3 | 9.6 | 6.1 | 5.2 | 4.1 | 3.2 |
| 82.5° | 129.8 | 129.8 | 114.4 | 17.2 | 11.1 | 9.0 | 1.2 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 26.2 | 29.4 | 20.7 | 0.0 | 3.8 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386224
 CATALOG NUMBER: GPC-SA1D-760-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2001.1 | 2001.1 | 2001.1 | 2001.1 | 2001.1 | 2001.1 | 2001.1 | 2001.1 | 2001.1 | 2001.1 | 2001.1 |
| 2.5° | 1745.3 | 1710.0 | 1707.7 | 1685.6 | 1658.0 | 1645.4 | 1638.2 | 1651.0 | 1666.7 | 1668.4 | 1692.0 |
| 5° | 1354.7 | 1317.7 | 1333.2 | 1293.9 | 1301.7 | 1293.9 | 1281.1 | 1283.4 | 1290.4 | 1268.6 | 1295.6 |
| 7.5° | 951.4 | 923.4 | 941.2 | 930.7 | 944.7 | 950.2 | 942.3 | 930.7 | 896.3 | 892.3 | 915.8 |
| 10° | 717.1 | 685.4 | 666.4 | 646.7 | 651.0 | 660.0 | 657.1 | 648.7 | 626.9 | 628.0 | 650.7 |
| 12.5° | 576.2 | 540.7 | 503.2 | 454.6 | 442.6 | 449.3 | 442.6 | 437.7 | 416.7 | 418.5 | 438.6 |
| 15° | 437.1 | 408.0 | 368.7 | 329.7 | 308.5 | 310.5 | 291.9 | 278.8 | 265.7 | 250.0 | 262.2 |
| 17.5° | 295.1 | 277.3 | 265.7 | 254.1 | 228.7 | 222.9 | 199.4 | 174.0 | 164.1 | 156.9 | 162.1 |
| 20° | 209.0 | 199.4 | 194.7 | 194.1 | 179.6 | 172.3 | 149.3 | 133.6 | 128.6 | 127.2 | 130.4 |
| 22.5° | 174.6 | 167.6 | 160.9 | 157.2 | 149.9 | 141.4 | 124.0 | 116.1 | 112.6 | 110.9 | 113.2 |
| 25° | 151.9 | 146.7 | 139.7 | 133.3 | 130.4 | 121.4 | 108.8 | 103.0 | 100.7 | 98.9 | 100.1 |
| 27.5° | 135.0 | 130.4 | 122.2 | 118.2 | 115.8 | 108.0 | 97.2 | 92.5 | 90.5 | 89.9 | 89.6 |
| 30° | 121.6 | 117.3 | 109.7 | 105.1 | 101.0 | 94.0 | 87.6 | 82.9 | 80.9 | 80.3 | 79.7 |
| 32.5° | 108.3 | 104.8 | 99.8 | 95.2 | 90.8 | 84.4 | 78.9 | 75.1 | 71.9 | 71.3 | 71.0 |
| 35° | 91.4 | 87.9 | 85.3 | 85.0 | 80.9 | 74.8 | 70.7 | 65.8 | 63.2 | 62.3 | 62.6 |
| 37.5° | 81.2 | 76.5 | 70.7 | 72.8 | 71.6 | 67.2 | 61.7 | 56.7 | 54.1 | 53.5 | 53.5 |
| 40° | 74.8 | 69.8 | 63.2 | 59.7 | 63.2 | 62.3 | 53.5 | 48.6 | 46.0 | 45.7 | 45.1 |
| 42.5° | 68.7 | 63.7 | 56.2 | 50.3 | 52.1 | 54.7 | 46.3 | 41.6 | 39.0 | 38.4 | 37.5 |
| 45° | 64.3 | 59.1 | 50.6 | 43.9 | 40.5 | 46.0 | 39.6 | 33.8 | 32.3 | 31.1 | 30.6 |
| 47.5° | 60.2 | 55.3 | 45.7 | 38.1 | 32.3 | 33.2 | 31.7 | 27.6 | 25.9 | 24.7 | 24.4 |
| 50° | 56.7 | 51.5 | 41.3 | 32.6 | 26.8 | 24.4 | 25.6 | 21.8 | 20.4 | 19.2 | 18.6 |
| 52.5° | 52.7 | 47.7 | 36.7 | 28.2 | 22.4 | 19.2 | 19.5 | 17.2 | 15.7 | 14.8 | 14.6 |
| 55° | 49.5 | 44.5 | 32.9 | 24.7 | 19.8 | 15.7 | 14.0 | 13.4 | 12.5 | 11.9 | 11.6 |
| 57.5° | 45.1 | 40.5 | 29.1 | 21.0 | 16.9 | 12.8 | 10.8 | 10.8 | 10.5 | 9.9 | 9.6 |
| 59° | 42.5 | 38.4 | 26.8 | 18.9 | 15.4 | 11.1 | 9.6 | 9.9 | 9.6 | 9.0 | 8.7 |
| 60° | 40.5 | 36.7 | 25.0 | 17.5 | 14.6 | 10.2 | 8.7 | 9.3 | 9.0 | 8.4 | 8.1 |
| 62.5° | 35.8 | 33.2 | 21.5 | 14.6 | 12.8 | 8.1 | 7.3 | 7.9 | 7.9 | 7.6 | 7.3 |
| 65° | 31.4 | 28.5 | 18.3 | 12.2 | 11.9 | 7.0 | 5.8 | 7.0 | 7.3 | 6.7 | 6.1 |
| 67.5° | 27.4 | 24.4 | 16.0 | 9.9 | 11.1 | 5.5 | 4.4 | 5.8 | 7.9 | 6.1 | 5.5 |
| 70° | 23.3 | 20.4 | 12.5 | 7.9 | 11.6 | 3.8 | 3.5 | 5.2 | 9.3 | 6.7 | 5.2 |
| 72.5° | 18.0 | 15.7 | 8.7 | 5.8 | 12.5 | 2.6 | 2.6 | 4.4 | 10.5 | 7.3 | 4.9 |
| 75° | 12.5 | 10.2 | 5.2 | 3.5 | 10.2 | 1.7 | 1.7 | 4.1 | 9.9 | 6.7 | 4.7 |
| 77.5° | 7.3 | 5.5 | 1.7 | 0.3 | 5.2 | 0.0 | 0.3 | 2.9 | 7.0 | 4.1 | 2.0 |
| 80° | 2.6 | 1.2 | 0.0 | 0.0 | 3.2 | 0.0 | 0.0 | 0.0 | 0.6 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386224
 CATALOG NUMBER: GPC-SA1D-760-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2001.1 | 2001.1 | 2001.1 | 2001.1 | 2001.1 | 2001.1 | 2001.1 | 2001.1 | 2001.1 | 2001.1 | 2001.1 |
| 2.5° | 1698.1 | 1737.4 | 1772.6 | 1825.9 | 1889.0 | 1961.8 | 2024.4 | 2091.6 | 2154.7 | 2180.9 | 2199.0 |
| 5° | 1301.2 | 1349.8 | 1406.5 | 1484.8 | 1589.0 | 1717.3 | 1837.5 | 1973.4 | 2119.5 | 2192.6 | 2261.2 |
| 7.5° | 919.9 | 969.4 | 1039.8 | 1123.1 | 1249.1 | 1401.9 | 1559.0 | 1746.7 | 1944.6 | 2060.1 | 2173.9 |
| 10° | 661.5 | 722.3 | 788.1 | 901.9 | 1029.9 | 1174.9 | 1336.7 | 1546.2 | 1766.8 | 1894.8 | 2031.9 |
| 12.5° | 450.2 | 519.5 | 619.0 | 746.5 | 896.9 | 1039.0 | 1179.5 | 1379.4 | 1635.5 | 1762.4 | 1909.4 |
| 15° | 270.1 | 308.5 | 413.8 | 561.4 | 745.9 | 922.8 | 1076.8 | 1277.3 | 1550.3 | 1705.7 | 1858.5 |
| 17.5° | 166.5 | 184.2 | 241.5 | 362.6 | 556.4 | 780.2 | 991.2 | 1242.7 | 1562.5 | 1751.7 | 1915.2 |
| 20° | 132.7 | 139.7 | 158.0 | 214.2 | 368.7 | 623.1 | 894.9 | 1235.7 | 1662.3 | 1895.1 | 2070.6 |
| 22.5° | 115.2 | 121.9 | 134.2 | 155.7 | 231.9 | 466.5 | 803.5 | 1242.1 | 1805.5 | 2110.2 | 2315.1 |
| 25° | 101.6 | 107.4 | 119.0 | 136.8 | 170.0 | 328.6 | 705.7 | 1270.6 | 1992.0 | 2377.1 | 2594.8 |
| 27.5° | 90.8 | 95.7 | 106.5 | 122.8 | 145.8 | 229.3 | 594.9 | 1305.2 | 2213.2 | 2650.1 | 2864.8 |
| 30° | 80.9 | 85.3 | 94.9 | 110.0 | 126.6 | 176.4 | 473.2 | 1328.8 | 2434.7 | 2864.8 | 3057.8 |
| 32.5° | 72.5 | 75.7 | 84.4 | 97.2 | 110.0 | 140.6 | 359.7 | 1325.0 | 2599.1 | 3043.5 | 3196.6 |
| 35° | 63.7 | 66.9 | 74.5 | 85.6 | 95.7 | 116.1 | 282.9 | 1254.3 | 2742.3 | 3228.9 | 3355.5 |
| 37.5° | 54.1 | 58.2 | 65.5 | 75.4 | 82.4 | 102.1 | 228.7 | 1169.0 | 2887.5 | 3440.8 | 3532.7 |
| 40° | 46.0 | 50.1 | 56.5 | 67.2 | 71.6 | 96.9 | 175.8 | 1065.1 | 3050.8 | 3677.7 | 3727.1 |
| 42.5° | 38.1 | 41.9 | 48.6 | 57.9 | 67.5 | 83.5 | 130.1 | 946.4 | 3207.7 | 3880.2 | 3904.4 |
| 45° | 30.8 | 34.6 | 41.6 | 50.9 | 72.2 | 69.3 | 100.7 | 819.2 | 3334.2 | 4048.7 | 4056.6 |
| 47.5° | 24.4 | 27.9 | 35.2 | 48.0 | 67.2 | 55.3 | 71.9 | 719.4 | 3440.5 | 4180.2 | 4159.6 |
| 50° | 18.9 | 21.8 | 29.4 | 55.0 | 58.8 | 45.7 | 54.4 | 686.2 | 3535.6 | 4261.7 | 4208.2 |
| 52.5° | 14.8 | 17.5 | 24.2 | 51.5 | 45.7 | 37.8 | 45.7 | 717.4 | 3666.0 | 4329.3 | 4235.5 |
| 55° | 11.9 | 14.6 | 18.9 | 29.4 | 31.1 | 32.0 | 39.0 | 746.5 | 3891.0 | 4487.6 | 4397.1 |
| 57.5° | 9.9 | 12.5 | 15.4 | 20.7 | 23.6 | 27.1 | 34.6 | 749.7 | 4156.1 | 4750.7 | 4665.1 |
| 59° | 9.0 | 11.3 | 14.0 | 18.3 | 20.7 | 24.7 | 32.6 | 732.2 | 4249.5 | 4846.4 | 4803.6 |
| 60° | 8.4 | 10.8 | 13.1 | 16.9 | 19.2 | 23.3 | 31.4 | 715.6 | 4253.6 | 4842.9 | 4862.7 |
| 62.5° | 7.3 | 9.6 | 11.6 | 14.3 | 16.3 | 19.8 | 28.2 | 654.2 | 4081.3 | 4684.3 | 4827.2 |
| 65° | 6.4 | 8.4 | 10.5 | 12.2 | 14.0 | 17.8 | 25.6 | 542.2 | 3787.1 | 4428.5 | 4584.2 |
| 67.5° | 5.8 | 7.3 | 9.6 | 10.8 | 12.5 | 15.7 | 22.7 | 386.5 | 3419.5 | 4115.6 | 4216.6 |
| 70° | 5.2 | 7.0 | 8.7 | 9.9 | 11.3 | 13.7 | 19.5 | 222.1 | 2887.5 | 3657.6 | 3729.5 |
| 72.5° | 4.9 | 6.7 | 7.9 | 9.3 | 10.2 | 12.2 | 17.8 | 104.5 | 2114.3 | 2930.0 | 3117.7 |
| 75° | 4.4 | 6.1 | 7.3 | 8.7 | 9.6 | 11.1 | 15.1 | 50.1 | 1406.2 | 2120.4 | 2333.7 |
| 77.5° | 2.6 | 4.9 | 6.7 | 7.9 | 8.4 | 9.6 | 12.5 | 28.8 | 897.5 | 1467.6 | 1728.7 |
| 80° | 0.0 | 1.7 | 4.9 | 6.7 | 7.3 | 8.1 | 9.6 | 22.7 | 480.2 | 838.4 | 1006.4 |
| 82.5° | 0.0 | 0.0 | 3.5 | 5.2 | 4.9 | 5.5 | 7.3 | 14.3 | 216.5 | 548.0 | 617.5 |
| 85° | 0.0 | 0.0 | 1.2 | 4.1 | 3.5 | 2.6 | 4.9 | 4.9 | 47.4 | 277.3 | 346.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.3 | 1.7 | 1.2 | 2.0 | 0.6 | 0.3 | 20.7 | 83.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386224

CATALOG NUMBER: GPC-SA1D-760-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 359° | 360° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2001.1 | 2001.1 | 2001.1 | 2001.1 | 2001.1 | 2001.1 | 2001.1 | 2001.1 | 2001.1 | 2001.1 |
| 2.5° | 2262.1 | 2283.7 | 2320.0 | 2337.2 | 2328.8 | 2293.0 | 2250.2 | 2206.5 | 2180.9 | 2191.1 |
| 5° | 2401.2 | 2512.1 | 2576.1 | 2597.4 | 2561.9 | 2481.5 | 2376.5 | 2238.0 | 2188.8 | 2175.4 |
| 7.5° | 2401.2 | 2609.9 | 2742.0 | 2765.3 | 2686.1 | 2528.7 | 2331.7 | 2115.4 | 2043.6 | 2017.4 |
| 10° | 2316.8 | 2600.9 | 2785.1 | 2822.0 | 2711.5 | 2476.0 | 2212.1 | 1965.3 | 1880.0 | 1852.9 |
| 12.5° | 2221.7 | 2527.5 | 2721.6 | 2772.6 | 2681.8 | 2423.6 | 2129.1 | 1863.7 | 1763.3 | 1739.7 |
| 15° | 2163.2 | 2437.3 | 2598.0 | 2634.9 | 2596.5 | 2393.1 | 2109.3 | 1833.2 | 1715.0 | 1692.3 |
| 17.5° | 2184.1 | 2367.5 | 2425.4 | 2446.9 | 2472.8 | 2382.3 | 2163.2 | 1900.1 | 1750.5 | 1729.0 |
| 20° | 2263.0 | 2293.8 | 2263.9 | 2290.9 | 2360.8 | 2392.8 | 2291.5 | 2061.9 | 1882.3 | 1853.5 |
| 22.5° | 2396.9 | 2255.7 | 2171.6 | 2182.4 | 2267.4 | 2427.4 | 2487.7 | 2293.0 | 2085.8 | 2049.7 |
| 25° | 2552.8 | 2286.6 | 2120.4 | 2110.8 | 2198.1 | 2473.1 | 2666.9 | 2544.4 | 2326.4 | 2286.6 |
| 27.5° | 2749.0 | 2355.8 | 2109.9 | 2100.3 | 2173.9 | 2515.9 | 2815.9 | 2792.9 | 2579.9 | 2511.8 |
| 30° | 2900.3 | 2423.9 | 2141.1 | 2118.9 | 2198.1 | 2545.6 | 2935.5 | 3003.9 | 2781.9 | 2736.8 |
| 32.5° | 3008.9 | 2504.2 | 2191.7 | 2159.7 | 2266.2 | 2596.8 | 3027.8 | 3197.2 | 2968.7 | 2900.3 |
| 35° | 3091.5 | 2591.6 | 2273.5 | 2220.8 | 2359.9 | 2674.5 | 3114.2 | 3402.9 | 3167.5 | 3092.7 |
| 37.5° | 3168.9 | 2714.1 | 2401.2 | 2338.4 | 2506.9 | 2799.6 | 3205.6 | 3636.3 | 3389.8 | 3300.5 |
| 40° | 3276.9 | 2852.9 | 2598.2 | 2542.4 | 2753.9 | 2970.2 | 3319.7 | 3879.6 | 3642.7 | 3530.4 |
| 42.5° | 3384.9 | 3001.9 | 2799.9 | 2815.1 | 3062.1 | 3177.4 | 3467.0 | 4136.9 | 3892.4 | 3772.5 |
| 45° | 3483.5 | 3155.6 | 3087.2 | 3157.0 | 3348.2 | 3404.7 | 3613.3 | 4285.6 | 4091.8 | 3975.9 |
| 47.5° | 3571.4 | 3347.6 | 3372.7 | 3558.6 | 3673.6 | 3610.4 | 3722.8 | 4413.9 | 4240.2 | 4138.0 |
| 50° | 3673.6 | 3596.2 | 3749.0 | 4012.0 | 4048.1 | 3796.7 | 3822.3 | 4565.9 | 4413.6 | 4331.6 |
| 52.5° | 3785.3 | 3858.1 | 4165.7 | 4397.6 | 4386.0 | 3998.9 | 3922.4 | 4736.1 | 4651.4 | 4574.3 |
| 55° | 3912.2 | 4069.7 | 4532.7 | 4758.5 | 4748.6 | 4224.8 | 4088.3 | 4946.5 | 4949.4 | 4879.6 |
| 57.5° | 4100.5 | 4251.8 | 4781.8 | 5050.4 | 5067.0 | 4485.5 | 4369.4 | 5182.2 | 5218.9 | 5172.3 |
| 59° | 4235.5 | 4370.0 | 4880.4 | 5172.3 | 5239.9 | 4687.2 | 4574.9 | 5319.0 | 5294.9 | 5252.4 |
| 60° | 4335.7 | 4445.1 | 4929.3 | 5236.1 | 5340.3 | 4824.0 | 4726.5 | 5399.3 | 5303.9 | 5252.4 |
| 62.5° | 4583.3 | 4608.6 | 5017.5 | 5308.3 | 5455.8 | 5127.8 | 5153.1 | 5536.1 | 5241.3 | 5157.2 |
| 65° | 4698.8 | 4711.9 | 5016.4 | 5179.0 | 5344.0 | 5364.4 | 5540.2 | 5540.2 | 5088.5 | 4959.3 |
| 67.5° | 4650.5 | 4587.4 | 4767.5 | 4750.7 | 4915.4 | 5223.9 | 5685.7 | 5337.1 | 4796.3 | 4629.3 |
| 70° | 4257.7 | 4014.7 | 3934.6 | 3941.9 | 4067.9 | 4543.7 | 5397.6 | 4739.3 | 4243.4 | 4048.1 |
| 72.5° | 3542.6 | 2959.7 | 2762.1 | 2987.6 | 3020.5 | 3492.0 | 4599.9 | 3569.1 | 3129.4 | 2946.3 |
| 75° | 2849.4 | 2086.3 | 1765.1 | 2003.1 | 2059.0 | 2555.5 | 3558.3 | 2222.8 | 1827.9 | 1685.3 |
| 77.5° | 2047.1 | 1497.6 | 1266.5 | 1249.9 | 1322.1 | 1620.7 | 2524.9 | 1118.7 | 933.0 | 870.7 |
| 80° | 1162.9 | 985.7 | 1061.4 | 1001.4 | 1037.8 | 1013.3 | 1199.6 | 490.7 | 401.9 | 375.7 |
| 82.5° | 701.9 | 582.6 | 630.9 | 525.3 | 664.7 | 578.8 | 462.1 | 157.2 | 136.5 | 129.8 |
| 85° | 456.6 | 318.4 | 165.9 | 111.2 | 229.0 | 369.9 | 103.3 | 42.8 | 32.9 | 26.2 |
| 87.5° | 157.4 | 81.2 | 8.1 | 3.5 | 24.4 | 69.0 | 3.8 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-9-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-760-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 5474 | CRI (Ra): | 71.7 | R9: | -27.1 |
| CIE u': | 0.2052 | R1: | 70.6 | R10: | 40.8 |
| CIE v': | 0.4804 | R2: | 74.6 | R11: | 74.6 |
| Duv: | 0.0025 | R3: | 78.3 | R12: | 50.4 |
| CIE x: | 0.3330 | R4: | 73.8 | R13: | 70.0 |
| CIE y: | 0.3466 | R5: | 72.4 | R14: | 87.8 |
| CIE z: | 0.3204 | R6: | 67.5 | | |
| Peak Wavelength (nm): | 442 | R7: | 77.5 | | |
| Dominant Wavelength (nm): | 554 | R8: | 58.9 | | |
| Purity: | 4.1 | | | | |
| Rf: | 72.1 | | | | |
| Rg: | 97.2 | | | | |



Test Conditions

Stabilization Time: 240M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.6/31%
 Sphere Temperature (°C): 25.9

REPORT NUMBER: SP1-1908-441-9-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-9-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-9-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 13759.3 S/P: 1.85

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 5527.6 M/P: 0.74

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Summary

$R_f = 72.1$
 $R_g = 97.2$
 CIE $R_a = 71.7$
 $R_g = -27.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 54 | CES51 = 88 | CES76 = 43 |
| CES02 = 59 | CES27 = 79 | CES52 = 90 | CES77 = 64 |
| CES03 = 30 | CES28 = 77 | CES53 = 77 | CES78 = 46 |
| CES04 = 69 | CES29 = 50 | CES54 = 81 | CES79 = 74 |
| CES05 = 46 | CES30 = 59 | CES55 = 80 | CES80 = 70 |
| CES06 = 50 | CES31 = 55 | CES56 = 70 | CES81 = 71 |
| CES07 = 38 | CES32 = 52 | CES57 = 68 | CES82 = 88 |
| CES08 = 38 | CES33 = 63 | CES58 = 70 | CES83 = 82 |
| CES09 = 29 | CES34 = 63 | CES59 = 88 | CES84 = 87 |
| CES10 = 72 | CES35 = 79 | CES60 = 92 | CES85 = 84 |
| CES11 = 55 | CES36 = 90 | CES61 = 88 | CES86 = 76 |
| CES12 = 61 | CES37 = 72 | CES62 = 81 | CES87 = 75 |
| CES13 = 41 | CES38 = 68 | CES63 = 75 | CES88 = 77 |
| CES14 = 74 | CES39 = 91 | CES64 = 72 | CES89 = 76 |
| CES15 = 70 | CES40 = 83 | CES65 = 65 | CES90 = 76 |
| CES16 = 46 | CES41 = 84 | CES66 = 66 | CES91 = 92 |
| CES17 = 48 | CES42 = 70 | CES67 = 64 | CES92 = 70 |
| CES18 = 55 | CES43 = 69 | CES68 = 71 | CES93 = 83 |
| CES19 = 70 | CES44 = 98 | CES69 = 80 | CES94 = 60 |
| CES20 = 64 | CES45 = 79 | CES70 = 58 | CES95 = 73 |
| CES21 = 85 | CES46 = 78 | CES71 = 55 | CES96 = 79 |
| CES22 = 77 | CES47 = 76 | CES72 = 84 | CES97 = 84 |
| CES23 = 91 | CES48 = 68 | CES73 = 47 | CES98 = 73 |
| CES24 = 90 | CES49 = 78 | CES74 = 94 | CES99 = 62 |
| CES25 = 71 | CES50 = 87 | CES75 = 51 | |



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Measure Comparisons



(END OF REPORT)