

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P386446

Luminaire Tested: **GPC-SA2A-760-U-SLL-HSS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P386446
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-27)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GPC-SA2A-760-U-SLL-HSS
Description: GALLEON PEDESTRIAN LUMINAIRE
(2) 70 CRI, 5700K, 615mA LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT
ELIMINATOR LEFT OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7210 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B1 - U0 - G2


Input Watts (W): 66
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P386446
 CATALOG NUMBER: GPC-SA2A-760-U-SLL-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 5 fc
 Type III - Medium - N/A

REPORT NUMBER: P386446
CATALOG NUMBER: GPC-SA2A-760-U-SLL-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 75-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P386446

CATALOG NUMBER: GPC-SA2A-760-U-SLL-HSS


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 1081.9 | 0.0 | 1081.9 |
| | % Fixture | 15.0 | 0.0 | 15.0 |
| Street Side | Lumens | 6128.1 | 0.0 | 6128.1 |
| | % Fixture | 85.0 | 0.0 | 85.0 |
| Total | Lumens | 7210.0 | 0.0 | 7210.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 183.5 | 2.5 |
| 10°-20° | 361.3 | 5.0 |
| 20°-30° | 511.1 | 7.1 |
| 30°-40° | 751.5 | 10.4 |
| 40°-50° | 1080.1 | 15.0 |
| 50°-60° | 1520.5 | 21.1 |
| 60°-70° | 1775.8 | 24.6 |
| 70°-80° | 906.0 | 12.6 |
| 80°-90° | 120.3 | 1.7 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 7210.0 | 100.0 |
| 0°-180° | 7210.0 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P386446


CATALOG NUMBER: GPC-SA2A-760-U-SLL-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 772.9 | 10.7 | | | |
| FM (30°-60°) | 2837.7 | 39.4 | | | |
| FH (60°-80°) | 2400.7 | 33.3 | | | G2/5000 |
| FVH (80°-90°) | 116.7 | 1.6 | | | G2/225 |
| BL (0°-30°) | 282.9 | 3.9 | B1/500 | | |
| BM (30°-60°) | 514.3 | 7.1 | B1/1000 | | |
| BH (60°-80°) | 281.0 | 3.9 | B1/500 | | G1/500 |
| BVH (80°-90°) | 3.6 | 0.1 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G2

Type III Medium





REPORT NUMBER: P386446
 CATALOG NUMBER: GPC-SA2A-760-U-SLL-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 1° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2418.8 | 2418.8 | 2418.8 | 2418.8 | 2418.8 | 2418.8 | 2418.8 | 2418.8 | 2418.8 | 2418.8 | 2418.8 |
| 2.5° | 2622.1 | 2626.2 | 2647.3 | 2696.5 | 2750.1 | 2754.2 | 2790.4 | 2753.2 | 2740.6 | 2680.5 | 2618.3 |
| 5° | 2641.9 | 2657.6 | 2730.3 | 2874.8 | 3000.1 | 3040.4 | 3069.1 | 2996.0 | 2919.2 | 2772.3 | 2615.6 |
| 7.5° | 2482.4 | 2508.7 | 2623.1 | 2894.3 | 3118.3 | 3217.4 | 3236.2 | 3121.7 | 2933.5 | 2691.7 | 2456.1 |
| 10° | 2278.1 | 2308.2 | 2446.2 | 2779.5 | 3087.2 | 3257.0 | 3282.9 | 3133.0 | 2862.5 | 2561.3 | 2283.6 |
| 12.5° | 2112.8 | 2148.0 | 2289.0 | 2650.4 | 2980.3 | 3168.2 | 3219.4 | 3095.1 | 2801.0 | 2468.7 | 2165.7 |
| 15° | 2036.6 | 2076.9 | 2225.2 | 2567.1 | 2861.8 | 3009.7 | 3052.1 | 2998.4 | 2766.9 | 2454.0 | 2138.4 |
| 17.5° | 2080.4 | 2124.1 | 2277.1 | 2574.2 | 2750.5 | 2813.7 | 2847.8 | 2869.7 | 2766.9 | 2542.5 | 2218.3 |
| 20° | 2259.7 | 2306.8 | 2468.7 | 2647.0 | 2658.3 | 2634.7 | 2671.2 | 2748.1 | 2799.0 | 2710.5 | 2410.3 |
| 22.5° | 2507.6 | 2563.0 | 2745.7 | 2771.6 | 2613.2 | 2524.0 | 2528.8 | 2649.4 | 2857.4 | 2923.6 | 2676.7 |
| 25° | 2809.9 | 2877.5 | 3063.3 | 2957.5 | 2632.0 | 2458.1 | 2456.4 | 2568.1 | 2914.4 | 3137.1 | 2973.5 |
| 27.5° | 3110.1 | 3184.6 | 3347.8 | 3184.2 | 2709.5 | 2446.2 | 2442.7 | 2543.5 | 2970.1 | 3327.0 | 3297.6 |
| 30° | 3361.8 | 3434.2 | 3575.0 | 3348.5 | 2793.2 | 2474.2 | 2457.8 | 2569.8 | 3003.2 | 3450.3 | 3534.0 |
| 32.5° | 3566.8 | 3624.8 | 3738.6 | 3461.6 | 2882.7 | 2528.5 | 2492.9 | 2640.2 | 3059.6 | 3554.5 | 3751.2 |
| 35° | 3792.2 | 3853.3 | 3898.8 | 3569.2 | 2983.1 | 2606.7 | 2555.8 | 2751.8 | 3146.3 | 3660.4 | 3989.3 |
| 37.5° | 4049.4 | 4110.2 | 4104.7 | 3667.5 | 3110.5 | 2736.1 | 2703.7 | 2928.8 | 3281.2 | 3765.2 | 4255.0 |
| 40° | 4301.1 | 4363.3 | 4318.9 | 3775.1 | 3260.1 | 2949.6 | 2925.7 | 3194.5 | 3461.9 | 3899.4 | 4566.5 |
| 42.5° | 4536.8 | 4604.0 | 4509.1 | 3876.9 | 3438.3 | 3218.7 | 3259.7 | 3536.7 | 3688.0 | 4064.7 | 4834.9 |
| 45° | 4726.7 | 4795.3 | 4668.6 | 3975.9 | 3626.2 | 3545.3 | 3668.6 | 3915.8 | 3959.9 | 4204.4 | 5016.3 |
| 47.5° | 4864.6 | 4929.5 | 4779.3 | 4075.0 | 3866.6 | 3944.5 | 4159.4 | 4313.4 | 4205.5 | 4325.7 | 5145.1 |
| 50° | 4952.8 | 5003.3 | 4811.7 | 4199.0 | 4182.2 | 4410.4 | 4670.6 | 4745.8 | 4436.7 | 4435.0 | 5301.5 |
| 52.5° | 5008.8 | 5031.7 | 4835.6 | 4328.4 | 4511.5 | 4917.6 | 5171.4 | 5194.9 | 4674.7 | 4555.2 | 5512.2 |
| 55° | 5201.8 | 5220.2 | 5005.0 | 4485.2 | 4783.7 | 5361.9 | 5624.2 | 5602.4 | 4944.2 | 4790.5 | 5760.9 |
| 57.5° | 5531.0 | 5550.5 | 5355.1 | 4710.6 | 5004.0 | 5636.5 | 5952.5 | 5991.7 | 5260.2 | 5121.1 | 6027.3 |
| 60° | 5696.3 | 5732.5 | 5662.8 | 4996.1 | 5217.5 | 5812.1 | 6176.2 | 6301.5 | 5655.0 | 5557.0 | 6285.5 |
| 62.5° | 5546.4 | 5599.0 | 5700.1 | 5312.8 | 5429.6 | 5908.8 | 6245.9 | 6412.5 | 6059.4 | 6064.8 | 6444.6 |
| 65° | 5247.2 | 5289.2 | 5460.6 | 5486.3 | 5552.5 | 5896.8 | 6073.7 | 6257.5 | 6307.0 | 6531.4 | 6436.1 |
| 67.5° | 4885.8 | 4901.5 | 5047.0 | 5499.9 | 5374.2 | 5537.5 | 5556.6 | 5692.6 | 6111.3 | 6696.7 | 6177.5 |
| 70° | 4365.6 | 4374.2 | 4501.2 | 5042.6 | 4618.4 | 4654.3 | 4625.9 | 4653.6 | 5254.0 | 6294.0 | 5524.9 |
| 72.5° | 3513.5 | 3535.0 | 3715.7 | 4187.7 | 3364.6 | 3261.1 | 3483.8 | 3471.5 | 4046.3 | 5317.5 | 4103.3 |
| 75° | 2586.9 | 2624.1 | 2897.0 | 3373.1 | 2361.5 | 2136.0 | 2298.6 | 2342.0 | 2876.5 | 4113.2 | 2566.0 |
| 77.5° | 1811.2 | 1838.9 | 2103.2 | 2479.6 | 1709.1 | 1527.4 | 1468.6 | 1520.2 | 1898.7 | 2975.6 | 1292.8 |
| 80° | 1043.4 | 1053.7 | 1222.4 | 1431.8 | 1151.7 | 1317.7 | 1193.7 | 1229.2 | 1137.7 | 1323.8 | 556.0 |
| 82.5° | 682.8 | 684.5 | 750.4 | 852.2 | 717.2 | 833.4 | 616.8 | 788.6 | 699.8 | 531.8 | 181.0 |
| 85° | 368.9 | 370.9 | 435.1 | 604.9 | 406.1 | 229.5 | 134.9 | 277.0 | 432.7 | 121.9 | 49.5 |
| 87.5° | 40.6 | 37.2 | 131.2 | 220.0 | 112.7 | 20.8 | 7.2 | 31.1 | 69.3 | 7.9 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386446
 CATALOG NUMBER: GPC-SA2A-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2418.8 | 2418.8 | 2418.8 | 2418.8 | 2418.8 | 2418.8 | 2418.8 | 2418.8 | 2418.8 | 2418.8 | 2418.8 |
| 2.5° | 2586.5 | 2558.2 | 2487.5 | 2412.7 | 2352.6 | 2296.2 | 2239.5 | 2170.2 | 2116.6 | 2105.6 | 2087.9 |
| 5° | 2531.2 | 2441.4 | 2293.1 | 2144.2 | 2024.3 | 1873.0 | 1777.1 | 1702.3 | 1629.2 | 1624.7 | 1610.0 |
| 7.5° | 2337.9 | 2219.7 | 2011.0 | 1805.1 | 1636.3 | 1492.2 | 1346.7 | 1249.4 | 1172.9 | 1145.9 | 1129.8 |
| 10° | 2152.1 | 2019.2 | 1758.6 | 1523.6 | 1373.0 | 1245.6 | 1143.2 | 1041.4 | 949.2 | 885.6 | 856.9 |
| 12.5° | 2022.3 | 1875.4 | 1588.2 | 1385.7 | 1277.7 | 1156.8 | 1031.8 | 904.8 | 798.5 | 722.0 | 675.2 |
| 15° | 1972.1 | 1815.3 | 1531.2 | 1331.0 | 1197.8 | 1044.8 | 884.9 | 739.8 | 622.0 | 552.6 | 510.6 |
| 17.5° | 2031.9 | 1849.5 | 1526.7 | 1264.4 | 1078.3 | 888.0 | 711.4 | 540.0 | 429.0 | 376.4 | 349.4 |
| 20° | 2183.5 | 1958.1 | 1525.0 | 1182.8 | 936.2 | 702.2 | 481.9 | 355.2 | 287.9 | 258.6 | 245.9 |
| 22.5° | 2398.0 | 2096.8 | 1538.7 | 1102.2 | 788.3 | 501.7 | 332.7 | 260.9 | 226.4 | 210.7 | 203.6 |
| 25° | 2674.0 | 2291.4 | 1577.3 | 1029.1 | 649.3 | 374.3 | 259.2 | 218.6 | 194.3 | 182.0 | 176.9 |
| 27.5° | 2968.0 | 2515.5 | 1637.4 | 965.6 | 536.2 | 298.5 | 222.0 | 187.2 | 169.7 | 161.2 | 156.4 |
| 30° | 3210.5 | 2775.1 | 1698.2 | 894.9 | 454.3 | 260.3 | 203.2 | 170.8 | 150.6 | 145.2 | 140.7 |
| 32.5° | 3422.6 | 2971.5 | 1741.2 | 831.0 | 400.6 | 231.2 | 183.8 | 152.7 | 139.0 | 128.4 | 123.6 |
| 35° | 3642.3 | 3135.1 | 1739.8 | 786.2 | 363.7 | 209.4 | 167.4 | 136.6 | 120.2 | 107.9 | 104.2 |
| 37.5° | 3880.0 | 3319.8 | 1710.1 | 748.0 | 347.7 | 191.9 | 158.1 | 128.1 | 111.7 | 99.4 | 94.6 |
| 40° | 4158.3 | 3513.8 | 1679.7 | 712.1 | 343.3 | 177.9 | 151.6 | 121.2 | 103.8 | 91.9 | 87.1 |
| 42.5° | 4429.5 | 3688.7 | 1653.1 | 685.5 | 324.1 | 177.6 | 145.8 | 116.1 | 97.7 | 86.1 | 80.6 |
| 45° | 4646.4 | 3851.6 | 1648.0 | 669.4 | 304.0 | 183.8 | 142.8 | 112.7 | 92.9 | 81.3 | 76.2 |
| 47.5° | 4826.7 | 4028.5 | 1680.7 | 658.2 | 284.8 | 167.7 | 150.3 | 110.3 | 88.5 | 77.2 | 71.4 |
| 50° | 5041.2 | 4245.8 | 1757.9 | 639.7 | 264.7 | 151.0 | 172.1 | 111.0 | 84.7 | 73.1 | 66.9 |
| 52.5° | 5340.4 | 4546.3 | 1871.3 | 608.6 | 237.0 | 135.6 | 169.4 | 111.7 | 80.6 | 68.7 | 62.5 |
| 55° | 5675.8 | 4921.7 | 1993.3 | 557.1 | 198.4 | 115.4 | 145.2 | 106.9 | 72.7 | 63.9 | 58.1 |
| 57.5° | 6028.3 | 5262.2 | 2065.7 | 495.6 | 157.8 | 99.7 | 116.1 | 97.3 | 64.2 | 57.4 | 53.6 |
| 60° | 6083.6 | 5391.7 | 2032.5 | 420.1 | 125.3 | 86.8 | 86.1 | 99.0 | 57.4 | 50.5 | 47.8 |
| 62.5° | 5946.0 | 5229.1 | 1872.4 | 352.8 | 104.9 | 76.2 | 70.7 | 86.4 | 51.9 | 45.1 | 42.4 |
| 65° | 5681.3 | 4789.5 | 1612.8 | 318.0 | 97.3 | 65.2 | 58.7 | 60.8 | 45.4 | 39.3 | 36.9 |
| 67.5° | 5313.1 | 4202.7 | 1324.2 | 298.2 | 96.3 | 56.0 | 50.2 | 46.1 | 39.3 | 34.2 | 32.1 |
| 70° | 4560.3 | 3501.2 | 1056.4 | 287.2 | 93.6 | 47.1 | 42.4 | 37.6 | 32.8 | 29.0 | 27.3 |
| 72.5° | 3356.4 | 2481.0 | 821.8 | 275.3 | 94.3 | 37.6 | 36.9 | 31.1 | 26.3 | 22.5 | 21.9 |
| 75° | 1939.3 | 1417.4 | 539.0 | 223.0 | 89.8 | 29.0 | 30.7 | 21.9 | 18.4 | 15.7 | 15.7 |
| 77.5° | 1033.5 | 864.5 | 205.3 | 92.9 | 32.8 | 18.4 | 17.4 | 13.0 | 11.6 | 9.6 | 9.2 |
| 80° | 450.5 | 380.5 | 61.8 | 26.0 | 18.1 | 9.9 | 6.5 | 5.8 | 5.1 | 4.1 | 3.8 |
| 82.5° | 159.5 | 137.6 | 20.2 | 12.6 | 7.9 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 36.2 | 26.0 | 0.0 | 3.1 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386446
 CATALOG NUMBER: GPC-SA2A-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2418.8 | 2418.8 | 2418.8 | 2418.8 | 2418.8 | 2418.8 | 2418.8 | 2418.8 | 2418.8 | 2418.8 | 2418.8 |
| 2.5° | 2051.7 | 2044.2 | 1999.8 | 2001.5 | 2009.3 | 2020.6 | 1993.9 | 2006.2 | 2039.4 | 2071.1 | 2083.1 |
| 5° | 1586.5 | 1588.2 | 1561.2 | 1577.9 | 1593.0 | 1603.2 | 1560.2 | 1560.9 | 1587.2 | 1623.0 | 1641.8 |
| 7.5° | 1117.9 | 1115.1 | 1116.5 | 1156.5 | 1184.8 | 1164.3 | 1180.4 | 1124.7 | 1128.1 | 1153.7 | 1134.6 |
| 10° | 831.0 | 793.4 | 772.2 | 802.3 | 833.4 | 822.1 | 794.4 | 776.3 | 789.0 | 817.3 | 815.3 |
| 12.5° | 653.0 | 599.1 | 567.3 | 545.8 | 571.4 | 550.2 | 549.5 | 533.8 | 516.8 | 519.8 | 565.3 |
| 15° | 491.1 | 451.9 | 414.3 | 379.8 | 379.1 | 371.9 | 335.4 | 294.4 | 291.0 | 293.0 | 316.6 |
| 17.5° | 337.8 | 324.5 | 309.1 | 279.4 | 271.5 | 241.5 | 206.0 | 189.6 | 181.4 | 185.1 | 193.0 |
| 20° | 237.4 | 232.3 | 234.0 | 217.9 | 206.6 | 177.9 | 157.1 | 150.6 | 149.3 | 153.0 | 156.8 |
| 22.5° | 196.7 | 187.5 | 186.5 | 179.3 | 168.0 | 147.2 | 135.9 | 132.2 | 130.5 | 133.9 | 136.6 |
| 25° | 172.1 | 162.9 | 159.2 | 154.7 | 142.8 | 128.4 | 121.6 | 118.2 | 116.5 | 118.5 | 120.2 |
| 27.5° | 151.6 | 143.1 | 139.7 | 136.6 | 125.0 | 114.8 | 109.3 | 106.2 | 104.9 | 105.5 | 107.2 |
| 30° | 136.3 | 128.8 | 124.3 | 120.6 | 110.7 | 103.5 | 98.7 | 95.6 | 94.3 | 94.3 | 96.0 |
| 32.5° | 120.2 | 116.1 | 112.0 | 107.2 | 98.0 | 93.2 | 88.5 | 85.0 | 83.7 | 84.0 | 85.4 |
| 35° | 100.1 | 98.7 | 99.7 | 95.3 | 87.4 | 83.3 | 78.6 | 74.8 | 73.8 | 74.1 | 75.5 |
| 37.5° | 88.8 | 82.7 | 86.4 | 84.0 | 79.6 | 74.1 | 68.0 | 64.6 | 62.8 | 63.9 | 64.6 |
| 40° | 81.6 | 74.1 | 71.4 | 73.8 | 73.1 | 64.2 | 58.7 | 55.3 | 54.0 | 54.3 | 55.0 |
| 42.5° | 75.5 | 66.6 | 60.5 | 60.1 | 64.2 | 56.0 | 50.2 | 47.1 | 45.4 | 45.4 | 46.1 |
| 45° | 69.7 | 60.1 | 52.6 | 46.8 | 54.0 | 47.5 | 42.0 | 39.3 | 37.2 | 37.2 | 37.6 |
| 47.5° | 65.2 | 54.6 | 45.8 | 38.3 | 40.6 | 38.9 | 34.5 | 31.8 | 29.7 | 29.7 | 30.1 |
| 50° | 61.1 | 49.2 | 39.6 | 32.1 | 30.4 | 32.1 | 28.0 | 24.9 | 23.6 | 23.2 | 23.9 |
| 52.5° | 56.7 | 43.7 | 33.8 | 27.3 | 23.9 | 24.2 | 21.9 | 19.8 | 18.1 | 18.1 | 18.8 |
| 55° | 52.3 | 39.3 | 29.4 | 23.2 | 19.8 | 18.1 | 17.4 | 16.1 | 14.7 | 14.7 | 15.4 |
| 57.5° | 47.8 | 34.5 | 24.9 | 19.1 | 15.7 | 14.3 | 14.3 | 13.3 | 12.3 | 12.3 | 13.0 |
| 60° | 43.7 | 29.7 | 20.5 | 15.7 | 12.3 | 12.0 | 12.3 | 11.3 | 10.6 | 10.6 | 11.3 |
| 62.5° | 38.9 | 25.3 | 16.7 | 13.0 | 9.9 | 9.6 | 10.6 | 9.9 | 9.2 | 9.2 | 9.9 |
| 65° | 33.1 | 21.5 | 13.3 | 9.9 | 7.5 | 7.5 | 8.9 | 8.2 | 7.5 | 7.5 | 8.2 |
| 67.5° | 28.0 | 18.1 | 10.2 | 7.2 | 5.5 | 5.8 | 7.5 | 6.8 | 6.5 | 6.5 | 7.2 |
| 70° | 23.2 | 14.0 | 7.2 | 4.4 | 3.1 | 4.4 | 5.8 | 5.8 | 5.8 | 5.8 | 6.5 |
| 72.5° | 17.4 | 9.6 | 4.1 | 1.7 | 1.4 | 3.1 | 4.8 | 5.5 | 5.1 | 5.1 | 6.1 |
| 75° | 11.3 | 5.5 | 1.4 | 0.0 | 0.0 | 1.7 | 3.8 | 4.4 | 4.4 | 4.1 | 5.1 |
| 77.5° | 6.5 | 1.7 | 0.0 | 0.0 | 0.0 | 0.0 | 2.4 | 2.0 | 1.7 | 1.4 | 2.4 |
| 80° | 1.7 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386446
 CATALOG NUMBER: GPC-SA2A-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 359° | 360° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2418.8 | 2418.8 | 2418.8 | 2418.8 | 2418.8 | 2418.8 | 2418.8 | 2418.8 | 2418.8 | 2418.8 |
| 2.5° | 2131.2 | 2171.6 | 2228.2 | 2288.4 | 2380.9 | 2454.4 | 2526.4 | 2588.2 | 2612.1 | 2622.1 |
| 5° | 1686.9 | 1746.0 | 1829.0 | 1935.5 | 2102.6 | 2252.8 | 2405.2 | 2558.5 | 2625.1 | 2641.9 |
| 7.5° | 1210.4 | 1285.9 | 1391.5 | 1525.0 | 1720.7 | 1915.4 | 2128.2 | 2353.3 | 2456.4 | 2482.4 |
| 10° | 895.9 | 988.1 | 1109.0 | 1249.7 | 1436.5 | 1636.7 | 1868.6 | 2125.8 | 2243.6 | 2278.1 |
| 12.5° | 635.6 | 760.3 | 922.2 | 1093.3 | 1255.2 | 1433.8 | 1668.5 | 1951.9 | 2075.6 | 2112.8 |
| 15° | 373.3 | 493.9 | 685.5 | 914.7 | 1122.0 | 1303.0 | 1541.4 | 1862.8 | 1999.1 | 2036.6 |
| 17.5° | 214.1 | 274.3 | 419.1 | 674.6 | 956.0 | 1206.7 | 1501.4 | 1885.0 | 2045.5 | 2080.4 |
| 20° | 163.6 | 182.7 | 241.5 | 434.4 | 762.0 | 1112.1 | 1501.4 | 2010.7 | 2208.4 | 2259.7 |
| 22.5° | 143.1 | 157.1 | 181.0 | 259.2 | 560.8 | 1010.6 | 1518.9 | 2192.4 | 2450.9 | 2507.6 |
| 25° | 127.1 | 139.7 | 160.2 | 195.0 | 382.5 | 890.1 | 1560.2 | 2415.4 | 2736.5 | 2809.9 |
| 27.5° | 113.7 | 125.7 | 144.1 | 170.8 | 261.6 | 744.6 | 1615.9 | 2677.0 | 3051.4 | 3110.1 |
| 30° | 101.8 | 113.1 | 129.8 | 148.6 | 201.9 | 579.6 | 1663.3 | 2923.6 | 3298.7 | 3361.8 |
| 32.5° | 90.5 | 100.8 | 115.8 | 129.8 | 165.3 | 428.6 | 1668.5 | 3119.0 | 3503.9 | 3566.8 |
| 35° | 79.9 | 89.1 | 102.8 | 113.7 | 137.0 | 338.5 | 1588.9 | 3288.4 | 3709.2 | 3792.2 |
| 37.5° | 69.7 | 78.6 | 90.5 | 98.7 | 120.6 | 276.0 | 1467.3 | 3477.3 | 3972.5 | 4049.4 |
| 40° | 60.1 | 68.0 | 80.3 | 85.7 | 114.1 | 212.1 | 1335.1 | 3675.4 | 4230.7 | 4301.1 |
| 42.5° | 51.2 | 58.7 | 70.7 | 81.3 | 100.1 | 158.5 | 1192.3 | 3861.2 | 4463.0 | 4536.8 |
| 45° | 42.7 | 50.5 | 62.5 | 86.1 | 83.0 | 118.5 | 1039.7 | 3984.5 | 4646.4 | 4726.7 |
| 47.5° | 34.5 | 43.4 | 59.8 | 82.0 | 66.3 | 87.1 | 918.8 | 4101.3 | 4785.4 | 4864.6 |
| 50° | 27.7 | 36.5 | 67.3 | 73.1 | 54.3 | 66.6 | 868.2 | 4205.8 | 4876.6 | 4952.8 |
| 52.5° | 22.5 | 30.7 | 63.5 | 56.0 | 45.4 | 55.0 | 895.5 | 4375.2 | 4961.0 | 5008.8 |
| 55° | 18.8 | 24.2 | 38.3 | 38.9 | 38.6 | 46.8 | 929.3 | 4618.4 | 5179.2 | 5201.8 |
| 57.5° | 16.4 | 19.5 | 26.6 | 30.1 | 32.4 | 41.7 | 930.0 | 4967.5 | 5517.0 | 5531.0 |
| 60° | 14.0 | 17.1 | 22.2 | 24.2 | 28.0 | 37.2 | 896.2 | 5089.4 | 5649.9 | 5696.3 |
| 62.5° | 12.3 | 15.0 | 18.4 | 20.2 | 23.6 | 33.5 | 817.0 | 4912.8 | 5467.5 | 5546.4 |
| 65° | 10.9 | 13.7 | 15.4 | 17.1 | 20.8 | 30.1 | 686.5 | 4559.6 | 5164.9 | 5247.2 |
| 67.5° | 9.6 | 12.0 | 13.7 | 15.4 | 18.8 | 26.6 | 505.5 | 4149.4 | 4817.5 | 4885.8 |
| 70° | 8.5 | 10.6 | 12.3 | 13.7 | 16.4 | 22.5 | 306.7 | 3521.0 | 4337.3 | 4365.6 |
| 72.5° | 8.2 | 9.6 | 11.3 | 12.3 | 14.3 | 19.8 | 155.4 | 2587.6 | 3467.4 | 3513.5 |
| 75° | 7.2 | 8.5 | 10.2 | 10.9 | 12.6 | 17.1 | 63.2 | 1699.5 | 2512.8 | 2586.9 |
| 77.5° | 5.8 | 7.9 | 9.2 | 9.9 | 10.9 | 14.0 | 32.1 | 1086.1 | 1763.4 | 1811.2 |
| 80° | 2.0 | 5.8 | 7.9 | 8.2 | 9.2 | 10.2 | 21.2 | 594.6 | 1022.9 | 1043.4 |
| 82.5° | 0.0 | 3.8 | 6.1 | 5.8 | 6.5 | 7.9 | 13.7 | 282.8 | 675.2 | 682.8 |
| 85° | 0.0 | 1.7 | 4.8 | 3.8 | 2.7 | 5.5 | 4.8 | 61.8 | 354.2 | 368.9 |
| 87.5° | 0.0 | 0.0 | 0.3 | 1.7 | 1.4 | 2.0 | 0.7 | 0.3 | 32.1 | 40.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-9-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-760-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 5474 | CRI (Ra): | 71.7 | R9: | -27.1 |
| CIE u': | 0.2052 | R1: | 70.6 | R10: | 40.8 |
| CIE v': | 0.4804 | R2: | 74.6 | R11: | 74.6 |
| Duv: | 0.0025 | R3: | 78.3 | R12: | 50.4 |
| CIE x: | 0.3330 | R4: | 73.8 | R13: | 70.0 |
| CIE y: | 0.3466 | R5: | 72.4 | R14: | 87.8 |
| CIE z: | 0.3204 | R6: | 67.5 | | |
| Peak Wavelength (nm): | 442 | R7: | 77.5 | | |
| Dominant Wavelength (nm): | 554 | R8: | 58.9 | | |
| Purity: | 4.1 | | | | |
| Rf: | 72.1 | | | | |
| Rg: | 97.2 | | | | |



Test Conditions
 Stabilization Time: 240M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.6/31%
 Sphere Temperature (°C): 25.9

REPORT NUMBER: SP1-1908-441-9-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-9-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-9-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 13759.3 S/P: 1.85

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 5527.6 M/P: 0.74

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Summary

$R_f = 72.1$
 $R_g = 97.2$
 CIE $R_a = 71.7$
 $R_g = -27.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 54 | CES51 = 88 | CES76 = 43 |
| CES02 = 59 | CES27 = 79 | CES52 = 90 | CES77 = 64 |
| CES03 = 30 | CES28 = 77 | CES53 = 77 | CES78 = 46 |
| CES04 = 69 | CES29 = 50 | CES54 = 81 | CES79 = 74 |
| CES05 = 46 | CES30 = 59 | CES55 = 80 | CES80 = 70 |
| CES06 = 50 | CES31 = 55 | CES56 = 70 | CES81 = 71 |
| CES07 = 38 | CES32 = 52 | CES57 = 68 | CES82 = 88 |
| CES08 = 38 | CES33 = 63 | CES58 = 70 | CES83 = 82 |
| CES09 = 29 | CES34 = 63 | CES59 = 88 | CES84 = 87 |
| CES10 = 72 | CES35 = 79 | CES60 = 92 | CES85 = 84 |
| CES11 = 55 | CES36 = 90 | CES61 = 88 | CES86 = 76 |
| CES12 = 61 | CES37 = 72 | CES62 = 81 | CES87 = 75 |
| CES13 = 41 | CES38 = 68 | CES63 = 75 | CES88 = 77 |
| CES14 = 74 | CES39 = 91 | CES64 = 72 | CES89 = 76 |
| CES15 = 70 | CES40 = 83 | CES65 = 65 | CES90 = 76 |
| CES16 = 46 | CES41 = 84 | CES66 = 66 | CES91 = 92 |
| CES17 = 48 | CES42 = 70 | CES67 = 64 | CES92 = 70 |
| CES18 = 55 | CES43 = 69 | CES68 = 71 | CES93 = 83 |
| CES19 = 70 | CES44 = 98 | CES69 = 80 | CES94 = 60 |
| CES20 = 64 | CES45 = 79 | CES70 = 58 | CES95 = 73 |
| CES21 = 85 | CES46 = 78 | CES71 = 55 | CES96 = 79 |
| CES22 = 77 | CES47 = 76 | CES72 = 84 | CES97 = 84 |
| CES23 = 91 | CES48 = 68 | CES73 = 47 | CES98 = 73 |
| CES24 = 90 | CES49 = 78 | CES74 = 94 | CES99 = 62 |
| CES25 = 71 | CES50 = 87 | CES75 = 51 | |



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Measure Comparisons



(END OF REPORT)