

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P149525

Luminaire Tested: **TLM-F03-LED-E1-SL2-HSS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P149525
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33726)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TLM-F03-LED-E1-SL2-HSS
Description: TALON MEDIUM LED SITE LUMINAIRE
(3) LIGHTBARS WITH AccuLED OPTICS - TYPE 2 W/ SPILL LIGHT CONTROL AND
HOUSE SIDE SHIELD
Light Source: (21) 4000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4541.0 lumens
Efficiency: N/A
Efficacy: 58.0 lumens/watt
Spacing Criteria (0/90/45): 3.84 / 3.85 / 3.8
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
CIE Type: Direct


Input Watts (W): 78.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P149525

CATALOG NUMBER: TLM-F03-LED-E1-SL2-HSS

Luminous Intensity Polar Plot





TEST NUMBER: P149525

CATALOG NUMBER: TLM-F03-LED-E1-SL2-HSS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	106	100	94	89	103	97	92	88	93	89	85	89	86	82	85	82	80
2	93	82	73	66	90	80	72	65	76	69	63	73	67	62	70	65	60
3	82	68	58	49	79	66	57	49	63	55	48	60	53	47	57	51	46
4	72	57	46	38	70	56	45	37	53	44	37	50	42	36	48	41	35
5	65	49	38	29	62	47	37	29	45	36	29	43	35	28	41	34	28
6	58	42	31	23	56	41	31	23	39	30	23	37	29	23	35	28	22
7	53	37	26	19	51	36	26	19	34	25	19	33	24	18	31	24	18
8	49	33	23	16	47	32	22	16	30	22	15	29	21	15	28	20	15
9	45	29	20	13	43	29	19	13	27	19	13	26	18	13	25	18	13
10	42	26	17	11	40	26	17	11	25	17	11	24	16	11	23	16	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	3750	3750	3750
5°	6457	3836	2193
10°	9601	4059	1607
15°	11351	4489	1324
20°	12577	4841	1097
25°	15570	5157	843
30°	22223	5663	656
35°	38596	6770	478
40°	51504	7796	256
45°	60044	10077	76
50°	62317	13742	27
55°	63051	19115	0
60°	77483	34406	0
65°	79771	45585	0
70°	26084	49467	0
75°	4467	16344	0
80°	1128	2256	0
85°	0	1235	0



TEST NUMBER: P149525

CATALOG NUMBER: TLM-F03-LED-E1-SL2-HSS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.3	0.4
10°-20°	74.7	1.6
20°-30°	151.7	3.3
30°-40°	370.5	8.2
40°-50°	828.7	18.2
50°-60°	1165.2	25.7
60°-70°	1370.1	30.2
70°-80°	494.8	10.9
80°-90°	66.2	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	245.6	5.4
0°-40°	616.1	13.6
0°-60°	2609.9	57.5
0°-90°	4541.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4541.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	174	174	174	174	174	
5°	299	263	178	114	102	33
15°	509	504	201	65	59	144
25°	656	621	217	44	36	320
35°	1469	1021	258	26	18	901
45°	1972	2686	331	10	2	1493
55°	1680	2796	509	1	0	1557
65°	1566	2407	895	0	0	1383
75°	54	639	196	0	0	111
85°	0	10	5	0	0	1
90°	0	0	0	0	0	



TEST NUMBER: P149525

CATALOG NUMBER: TLM-F03-LED-E1-SL2-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	56°	57°	58°	59°
0°	174.2	174.2	174.2	174.2	174.2	174.2	174.2	174.2	174.2	174.2	174.2
2.5°	227.8	230.3	228.7	224.5	219.6	213.0	207.2	207.2	206.4	203.9	204.7
5°	298.8	299.7	296.4	286.5	277.4	263.3	247.7	246.0	244.4	241.9	241.1
7.5°	368.2	371.5	368.2	357.5	339.3	317.8	293.1	290.6	285.6	285.6	282.3
10°	439.2	439.2	435.9	423.5	407.0	376.4	345.1	340.9	335.2	333.5	328.6
12.5°	489.5	489.5	487.9	481.3	468.1	440.8	402.9	398.7	391.3	388.8	383.0
15°	509.3	509.3	510.2	516.0	516.8	504.4	464.8	461.5	454.0	447.4	445.0
17.5°	521.7	520.9	520.9	529.2	544.0	552.3	526.7	523.4	515.1	511.8	503.6
20°	549.0	547.3	542.4	542.4	556.4	585.3	585.3	584.5	575.4	572.9	568.8
22.5°	589.4	587.8	572.9	560.5	567.1	603.5	637.3	635.7	632.4	629.0	626.6
25°	655.5	649.7	624.1	587.8	582.0	620.8	676.9	681.1	683.5	683.5	685.2
27.5°	755.4	747.9	702.5	634.8	609.2	648.9	720.7	728.9	736.4	738.0	745.4
30°	894.0	880.8	815.6	716.6	657.9	690.1	785.1	794.2	804.9	808.2	819.7
32.5°	1121.9	1114.5	1051.7	903.1	777.6	771.0	875.1	886.6	900.6	906.4	920.5
35°	1468.6	1470.3	1419.1	1285.3	1112.0	1021.2	1036.0	1045.9	1050.9	1068.2	1075.7
37.5°	1703.9	1708.0	1719.6	1666.7	1542.9	1450.4	1334.0	1344.8	1319.2	1321.7	1322.5
40°	1832.7	1845.9	1913.6	1964.7	1954.8	1901.2	1807.9	1813.7	1765.8	1755.1	1703.1
42.5°	1918.5	1935.9	2044.0	2202.5	2283.4	2332.1	2310.6	2308.2	2271.0	2257.0	2213.2
45°	1972.2	1987.9	2124.1	2357.7	2544.3	2686.3	2744.9	2751.5	2720.1	2706.1	2669.7
47.5°	1969.7	1987.9	2134.0	2415.5	2690.4	2917.4	3082.5	3090.8	3109.8	3097.4	3099.8
50°	1860.7	1878.1	2025.0	2317.2	2647.5	3023.1	3325.2	3351.6	3382.2	3402.8	3412.7
52.5°	1728.6	1741.0	1871.5	2148.8	2464.2	2979.3	3468.9	3514.3	3559.7	3598.5	3625.7
55°	1679.9	1694.0	1796.3	2026.7	2317.2	2796.1	3535.7	3602.6	3667.0	3730.5	3782.6
57.5°	1705.5	1718.7	1792.2	1968.9	2229.7	2602.9	3554.7	3658.7	3764.4	3867.6	3969.9
60°	1799.6	1813.7	1876.4	2022.5	2206.6	2491.4	3480.4	3652.9	3828.8	4008.7	4178.0
62.5°	1762.5	1768.3	1860.7	2116.6	2371.7	2396.5	3210.5	3451.5	3719.8	3997.2	4270.4
63°	1727.0	1733.6	1827.7	2091.1	2422.1	2382.5	3127.1	3381.4	3664.5	3963.3	4260.5
65°	1566.0	1566.8	1638.7	1846.7	2366.0	2407.2	2755.6	2998.3	3323.6	3681.8	4057.5
67.5°	1168.9	1163.2	1232.5	1391.0	1857.4	2408.1	2365.1	2501.3	2727.5	3045.4	3382.2
70°	414.4	405.3	517.6	737.2	1157.4	1969.7	2032.4	2041.5	2104.3	2276.0	2487.3
72.5°	134.6	137.0	165.1	269.9	533.3	1325.8	1840.1	1812.0	1795.5	1794.7	1822.8
75°	53.7	54.5	66.0	119.7	239.4	639.0	1611.4	1627.1	1632.9	1641.1	1650.2
77.5°	25.6	28.1	37.1	66.9	118.9	316.2	1153.3	1286.2	1362.1	1420.7	1456.2
80°	9.1	10.7	20.6	41.3	55.3	145.3	607.6	733.1	844.5	988.2	1112.0
82.5°	0.0	0.0	4.1	28.9	30.5	58.6	249.3	292.2	334.3	433.4	556.4
85°	0.0	0.0	0.0	8.3	9.1	9.9	84.2	101.5	113.9	132.9	153.5
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.8	2.5	5.0	12.4	19.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P149525

CATALOG NUMBER: TLM-F03-LED-E1-SL2-HSS

CANDELA DISTRIBUTION (continued):

	60°	61°	62°	64°	65°	66°	67°	68°	69°	70°	71°
0°	174.2	174.2	174.2	174.2	174.2	174.2	174.2	174.2	174.2	174.2	174.2
2.5°	203.1	202.3	202.3	200.6	199.8	198.1	197.3	194.8	194.0	194.0	194.0
5°	240.2	236.9	235.3	231.1	228.7	227.8	223.7	222.1	219.6	220.4	216.3
7.5°	281.5	275.7	273.2	267.5	265.8	260.0	258.4	254.3	251.8	246.8	245.2
10°	326.9	319.5	315.4	306.3	303.8	299.7	294.7	289.8	285.6	280.7	278.2
12.5°	378.9	372.3	369.0	356.6	350.8	345.1	338.5	331.9	325.3	321.1	315.4
15°	440.0	429.3	426.0	414.4	404.5	397.1	388.0	379.7	374.8	366.5	360.8
17.5°	500.3	489.5	487.1	469.7	459.0	454.0	444.1	433.4	424.3	416.1	407.0
20°	560.5	553.1	546.5	530.0	518.4	510.2	497.0	486.2	478.8	467.2	455.7
22.5°	620.8	613.4	608.4	591.1	580.3	568.8	557.2	545.7	534.9	520.9	507.7
25°	682.7	677.8	675.3	659.6	649.7	639.0	627.4	614.2	601.0	585.3	571.3
27.5°	747.1	748.8	743.8	740.5	729.8	722.3	704.2	695.1	685.2	666.2	648.9
30°	828.8	833.8	832.1	834.6	828.0	823.0	809.0	797.5	785.9	767.7	747.9
32.5°	932.0	938.6	941.9	951.0	947.7	946.1	941.9	925.4	917.2	885.8	877.5
35°	1091.3	1088.0	1102.1	1109.5	1106.2	1104.6	1099.6	1090.5	1080.6	1058.3	1037.7
37.5°	1298.6	1301.9	1306.8	1291.9	1282.0	1281.2	1266.4	1257.3	1243.2	1218.5	1193.7
40°	1678.3	1657.7	1634.5	1571.8	1544.6	1528.9	1485.1	1472.7	1448.8	1414.9	1389.4
42.5°	2172.0	2151.3	2082.0	1977.1	1921.0	1843.4	1807.9	1764.1	1730.3	1675.0	1645.3
45°	2662.3	2602.9	2594.6	2472.4	2403.1	2300.7	2237.2	2163.7	2086.9	2014.3	1961.4
47.5°	3075.9	3062.7	3022.2	2947.9	2883.6	2797.7	2716.0	2602.9	2523.6	2420.4	2325.5
50°	3406.9	3406.1	3391.3	3348.3	3294.7	3225.3	3153.5	3057.7	2967.8	2841.5	2739.9
52.5°	3654.6	3667.8	3672.8	3659.6	3638.9	3577.8	3541.5	3461.4	3385.5	3278.2	3168.4
55°	3836.2	3884.9	3909.7	3937.8	3932.0	3910.5	3908.9	3856.9	3822.2	3737.2	3659.6
57.5°	4060.8	4140.8	4217.6	4353.8	4358.8	4406.7	4431.4	4456.2	4462.8	4428.9	4403.3
60°	4346.4	4509.8	4655.1	4939.9	5014.2	5131.5	5207.4	5290.0	5360.1	5365.9	5364.3
62.5°	4547.8	4799.6	5034.1	5456.7	5601.2	5736.6	5838.1	5918.2	5966.9	6016.4	6039.5
63°	4553.6	4829.3	5078.6	5514.5	5666.4	5795.2	5891.8	5966.1	6017.3	6047.0	6061.8
65°	4414.1	4748.4	5045.6	5479.8	5622.7	5752.3	5802.6	5851.3	5876.1	5887.6	5843.9
67.5°	3741.3	4068.2	4414.9	4900.3	5022.5	5177.7	5219.0	5243.7	5255.3	5252.8	5215.7
70°	2797.7	3071.8	3457.3	4012.1	4173.9	4325.8	4419.9	4460.3	4473.5	4469.4	4414.1
72.5°	1953.2	2114.2	2432.0	3049.5	3269.9	3464.7	3581.1	3641.4	3653.8	3629.0	3577.8
75°	1640.3	1648.6	1720.4	2058.0	2264.4	2472.4	2603.7	2641.7	2616.9	2541.8	2411.4
77.5°	1464.5	1482.6	1482.6	1533.0	1573.5	1631.2	1643.6	1551.2	1443.8	1305.2	1192.9
80°	1228.4	1291.9	1336.5	1373.7	1377.8	1366.2	1335.7	1283.7	1201.1	1095.5	978.2
82.5°	746.3	871.8	922.9	1114.5	1208.6	1272.1	1267.2	1197.8	1135.1	1025.3	925.4
85°	188.2	203.1	220.4	286.5	321.1	392.1	436.7	457.3	464.8	426.8	386.3
87.5°	18.2	12.4	20.6	15.7	22.3	16.5	22.3	20.6	25.6	27.2	29.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P149525

CATALOG NUMBER: TLM-F03-LED-E1-SL2-HSS

CANDELA DISTRIBUTION (continued):

	72°	73°	74°	75°	76°	77°	78°	79°	80°	81°	82°
0°	174.2	174.2	174.2	174.2	174.2	174.2	174.2	174.2	174.2	174.2	174.2
2.5°	192.3	191.5	190.7	189.9	189.0	188.2	186.6	186.6	184.9	184.1	183.3
5°	213.8	212.2	211.3	209.7	207.2	205.6	203.1	199.8	197.3	196.5	194.8
7.5°	241.1	236.9	235.3	232.8	229.5	224.5	221.2	218.8	214.6	212.2	207.2
10°	271.6	267.5	262.5	257.6	252.6	246.8	242.7	239.4	232.8	229.5	223.7
12.5°	310.4	303.0	297.2	290.6	284.0	277.4	272.4	262.5	256.7	249.3	244.4
15°	350.0	343.4	336.8	328.6	318.7	307.9	303.0	293.9	286.5	274.9	268.3
17.5°	397.9	385.5	375.6	365.7	356.6	346.7	336.8	322.8	312.0	302.1	288.9
20°	445.0	430.1	419.4	406.2	392.9	377.3	365.7	355.8	340.9	327.7	313.7
22.5°	495.3	480.5	463.1	449.9	431.7	419.4	403.7	387.2	372.3	355.0	337.6
25°	556.4	540.7	520.9	503.6	482.9	465.6	446.6	427.6	409.5	389.6	367.4
27.5°	631.5	615.0	593.6	572.9	545.7	524.2	506.0	480.5	457.3	432.6	407.0
30°	726.5	708.3	681.9	652.2	624.9	601.0	575.4	541.5	516.0	486.2	453.2
32.5°	850.3	828.8	793.3	765.3	731.4	700.0	664.5	630.7	594.4	555.6	517.6
35°	1006.3	986.5	945.2	903.9	866.8	829.7	785.1	746.3	695.1	648.0	599.3
37.5°	1168.1	1132.6	1094.6	1050.1	1003.8	959.3	904.8	851.1	792.5	741.3	680.2
40°	1353.0	1310.1	1278.7	1230.9	1165.6	1102.1	1051.7	984.9	911.4	842.9	771.0
42.5°	1606.5	1558.6	1502.5	1429.8	1382.8	1308.5	1243.2	1164.0	1067.4	990.6	903.9
45°	1899.5	1834.3	1779.8	1709.7	1652.7	1560.2	1484.3	1378.6	1282.0	1181.3	1075.7
47.5°	2233.9	2153.0	2073.7	2004.4	1913.6	1822.8	1726.2	1613.9	1490.1	1379.5	1254.0
50°	2617.7	2503.0	2393.2	2304.0	2179.4	2074.5	1969.7	1843.4	1706.4	1579.2	1436.4
52.5°	3044.5	2911.6	2766.3	2629.3	2484.8	2350.3	2224.0	2078.7	1925.9	1770.8	1611.4
55°	3559.7	3459.8	3288.9	3114.7	2921.5	2741.6	2578.9	2399.0	2213.2	2009.3	1841.7
57.5°	4366.2	4317.5	4174.7	4000.5	3748.7	3529.9	3254.2	3033.8	2764.7	2484.0	2267.7
60°	5459.2	5398.9	5318.9	5177.7	4977.9	4680.7	4376.9	4034.3	3624.9	3236.1	2867.0
62.5°	6042.0	6020.6	5955.3	5857.9	5671.4	5436.9	5130.6	4754.2	4291.9	3819.7	3349.2
63°	6059.4	6032.1	5976.0	5876.9	5712.6	5485.6	5185.1	4819.4	4367.0	3885.7	3405.3
65°	5824.9	5814.2	5757.2	5649.1	5536.8	5363.4	5130.6	4816.1	4436.4	3981.5	3503.5
67.5°	5166.1	5133.9	5046.4	5013.4	4935.0	4814.5	4637.0	4420.7	4149.1	3791.6	3378.9
70°	4369.5	4321.6	4211.8	4153.2	4057.5	3981.5	3873.4	3719.0	3551.4	3302.1	2994.2
72.5°	3525.0	3425.9	3325.2	3172.5	3038.8	2903.4	2783.7	2674.7	2490.6	2389.9	2156.3
75°	2289.2	2109.2	1936.7	1705.5	1497.5	1313.4	1134.3	1043.5	854.4	777.6	667.8
77.5°	1086.4	985.7	850.3	745.4	611.7	499.4	407.8	306.3	240.2	188.2	143.6
80°	876.7	791.7	710.0	615.0	514.3	410.3	314.5	235.3	166.8	115.6	81.7
82.5°	781.8	689.3	588.6	523.4	454.9	372.3	305.4	249.3	184.1	134.6	91.6
85°	303.8	255.9	197.3	161.0	125.5	103.2	93.3	64.4	50.4	39.6	30.5
87.5°	26.4	21.5	17.3	11.6	12.4	6.6	7.4	5.0	4.1	4.1	3.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P149525

CATALOG NUMBER: TLM-F03-LED-E1-SL2-HSS

CANDELA DISTRIBUTION (continued):

	83°	84°	85°	86°	87°	88°	89°	90°	95°	105°	115°
0°	174.2	174.2	174.2	174.2	174.2	174.2	174.2	174.2	174.2	174.2	174.2
2.5°	182.4	181.6	180.8	179.1	179.1	177.5	176.7	175.8	171.7	162.6	155.2
5°	191.5	189.9	188.2	185.7	184.1	181.6	180.0	177.5	168.4	151.1	136.2
7.5°	204.7	201.4	199.0	194.0	191.5	188.2	185.7	181.6	166.8	140.3	119.7
10°	220.4	214.6	210.5	204.7	199.8	195.6	191.5	185.7	165.1	128.8	104.8
12.5°	239.4	232.8	224.5	217.9	211.3	205.6	199.8	192.3	162.6	118.9	93.3
15°	258.4	248.5	242.7	233.6	224.5	216.3	208.0	201.4	163.5	108.1	83.4
17.5°	279.9	269.9	257.6	247.7	237.8	227.0	217.1	203.9	159.3	99.9	75.9
20°	300.5	286.5	274.9	262.5	248.5	235.3	222.9	211.3	156.0	91.6	69.3
22.5°	322.8	306.3	291.4	275.7	258.4	243.5	228.7	213.8	150.2	84.2	63.6
25°	350.0	331.0	309.6	290.6	272.4	254.3	235.3	217.1	144.5	77.6	59.4
27.5°	383.0	358.3	336.8	312.9	287.3	264.2	243.5	223.7	138.7	72.6	55.3
30°	425.1	396.3	365.7	335.2	307.9	281.5	252.6	227.8	132.9	67.7	51.2
32.5°	481.3	445.0	407.8	372.3	336.0	302.1	271.6	239.4	129.6	63.6	47.1
35°	555.6	508.5	463.1	418.5	374.8	333.5	293.9	257.6	129.6	58.6	42.1
37.5°	625.7	571.3	513.5	458.2	406.2	358.3	311.2	267.5	123.0	54.5	38.0
40°	701.7	636.5	568.8	503.6	440.8	381.4	327.7	277.4	117.2	49.5	33.8
42.5°	818.1	735.5	647.2	571.3	496.1	422.7	355.8	296.4	109.8	44.6	29.7
45°	970.8	866.0	762.0	669.5	573.7	483.8	404.5	331.0	108.1	40.5	25.6
47.5°	1134.3	1010.4	888.3	770.2	657.9	553.1	458.2	369.8	108.1	36.3	22.3
50°	1296.9	1141.7	1011.3	874.2	747.9	624.1	511.0	410.3	109.0	33.0	18.2
52.5°	1443.8	1277.9	1131.8	973.3	833.8	690.1	567.1	449.9	107.3	28.9	14.9
55°	1647.7	1452.9	1283.7	1108.7	945.2	783.4	643.9	509.3	108.1	25.6	12.4
57.5°	2023.4	1794.7	1590.8	1361.3	1173.1	964.2	795.0	631.5	118.1	21.5	9.1
60°	2562.4	2265.2	1978.8	1698.9	1459.5	1211.0	991.5	799.1	138.7	17.3	6.6
62.5°	2924.8	2536.0	2194.2	1885.5	1607.3	1347.3	1107.9	889.1	152.7	14.0	4.1
63°	2962.0	2560.0	2216.5	1897.9	1613.9	1353.9	1112.8	895.7	153.5	13.2	4.1
65°	3032.2	2601.2	2228.9	1900.4	1607.3	1344.8	1109.5	894.9	155.2	10.7	3.3
67.5°	2952.1	2537.7	2157.1	1829.4	1549.5	1291.1	1068.2	861.8	154.4	7.4	2.5
70°	2640.0	2296.6	1962.3	1656.8	1402.6	1168.9	972.5	785.9	142.0	5.0	1.7
72.5°	1938.3	1704.7	1445.5	1225.1	1056.7	877.5	748.8	590.3	109.8	3.3	0.8
75°	574.6	523.4	440.0	388.0	342.6	283.2	251.8	196.5	56.1	1.7	0.0
77.5°	114.7	104.0	93.3	85.0	80.1	68.5	65.2	53.7	23.1	0.8	0.0
80°	60.3	49.5	42.1	37.1	32.2	26.4	22.3	18.2	4.1	0.0	0.0
82.5°	57.8	38.8	28.1	23.1	19.8	15.7	12.4	9.1	2.5	0.0	0.0
85°	21.5	16.5	12.4	9.9	8.3	7.4	5.8	5.0	0.0	0.0	0.0
87.5°	3.3	2.5	2.5	1.7	1.7	0.8	0.8	0.8	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P149525

CATALOG NUMBER: TLM-F03-LED-E1-SL2-HSS

CANDELA DISTRIBUTION (continued):

	125°	135°	145°	155°	165°	175°	180°
0°	174.2	174.2	174.2	174.2	174.2	174.2	174.2
2.5°	147.8	141.2	137.9	133.7	133.7	132.9	134.6
5°	123.0	113.9	107.3	102.4	103.2	100.7	101.5
7.5°	104.0	94.9	89.2	85.9	85.0	84.2	84.2
10°	90.0	81.7	76.8	74.3	73.5	73.5	73.5
12.5°	80.1	71.8	67.7	66.0	66.0	65.2	65.2
15°	71.8	65.2	61.1	59.4	59.4	58.6	59.4
17.5°	65.2	58.6	55.3	53.7	53.7	52.8	52.8
20°	59.4	53.7	50.4	47.9	47.9	47.1	47.9
22.5°	54.5	48.7	44.6	42.9	42.1	41.3	42.1
25°	49.5	43.8	39.6	37.1	36.3	36.3	35.5
27.5°	45.4	39.6	34.7	32.2	31.4	31.4	30.5
30°	41.3	34.7	29.7	27.2	26.4	26.4	26.4
32.5°	37.1	29.7	25.6	23.1	22.3	22.3	22.3
35°	33.0	25.6	21.5	19.0	18.2	18.2	18.2
37.5°	28.1	21.5	16.5	14.9	14.0	13.2	13.2
40°	23.9	16.5	12.4	10.7	9.1	9.1	9.1
42.5°	19.8	13.2	9.1	6.6	5.8	5.0	5.8
45°	16.5	9.9	5.8	3.3	2.5	2.5	2.5
47.5°	13.2	6.6	2.5	0.8	0.8	0.8	0.8
50°	9.9	4.1	0.8	0.0	0.0	0.8	0.8
52.5°	7.4	2.5	0.0	0.0	0.0	0.0	0.0
55°	4.1	0.8	0.0	0.0	0.0	0.0	0.0
57.5°	2.5	0.0	0.0	0.0	0.0	0.0	0.0
60°	1.7	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	0.8	0.0	0.0	0.0	0.0	0.0	0.0
63°	0.8	0.0	0.0	0.0	0.0	0.0	0.0
65°	0.8	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)