

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P154555

Luminaire Tested: **TLM-F03-LED-E1-T2**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P154555
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33671)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TLM-F03-LED-E1-T2
Description: TALON MEDIUM LED SITE LUMINAIRE
(3) LIGHTBARS WITH AccuLED OPTICS - TYPE 2
Light Source: (21) 4000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7587.9 lumens
Efficiency: N/A
Efficacy: 96.9 lumens/watt
Spacing Criteria (0/90/45): 2.21 / 4.51 / 2.52
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
CIE Type: Direct

Input Watts (W): 78.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P154555
CATALOG NUMBER: TLM-F03-LED-E1-T2

Luminous Intensity Polar Plot





TEST NUMBER: P154555

CATALOG NUMBER: TLM-F03-LED-E1-T2

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	107	101	96	91	104	98	94	90	94	90	87	90	87	84	86	84	81	79
2	94	84	76	69	91	82	75	68	78	72	66	75	70	65	72	67	63	61
3	84	71	61	53	81	69	60	53	66	58	51	63	56	50	60	54	50	47
4	75	60	50	42	72	59	49	41	56	48	41	54	46	40	51	45	39	37
5	67	52	42	34	65	51	41	33	49	40	33	46	39	33	44	38	32	30
6	61	46	35	28	59	45	35	27	43	34	27	41	33	27	39	32	27	24
7	56	40	30	23	54	40	30	23	38	29	23	36	28	23	35	28	22	20
8	52	36	26	20	50	35	26	20	34	26	19	33	25	19	31	24	19	17
9	48	33	23	17	46	32	23	17	31	23	17	30	22	17	28	22	17	15
10	45	30	21	15	43	29	21	15	28	20	15	27	20	15	26	19	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	16333	16333	16333
5°	17859	16733	15877
10°	19978	18100	16585
15°	22630	20221	17828
20°	25097	23679	19102
25°	26727	28138	20354
30°	29509	33265	21341
35°	36535	40136	21629
40°	46375	47072	19697
45°	59389	56950	16614
50°	70750	70556	12968
55°	80095	100295	9233
60°	82000	211877	7251
65°	60302	297892	6097
70°	28633	299710	6030
75°	15587	111308	7345
80°	7364	17803	9410
85°	3458	11016	11016



TEST NUMBER: P154555

CATALOG NUMBER: TLM-F03-LED-E1-T2

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.0	1.0
10°-20°	260.9	3.4
20°-30°	512.6	6.8
30°-40°	851.8	11.2
40°-50°	1251.6	16.5
50°-60°	1732.9	22.8
60°-70°	2068.3	27.3
70°-80°	731.5	9.6
80°-90°	102.2	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	849.6	11.2
0°-40°	1701.4	22.4
0°-60°	4685.9	61.8
0°-90°	7587.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7587.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	759	759	759	759	759	
5°	826	811	774	745	735	82
15°	1015	952	907	871	800	289
25°	1125	1091	1185	1114	857	524
35°	1390	1437	1527	1301	823	889
45°	1951	2129	1871	1179	546	1493
55°	2134	2558	2672	806	246	1870
65°	1184	1764	5848	249	120	1154
75°	187	531	1338	100	88	231
85°	14	29	45	76	45	20
90°	0	0	0	0	0	



TEST NUMBER: P154555

CATALOG NUMBER: TLM-F03-LED-E1-T2

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	60°	61°	62°	64°
0°	758.7	758.7	758.7	758.7	758.7	758.7	758.7	758.7	758.7	758.7	758.7
2.5°	791.7	792.5	790.9	790.0	787.6	783.4	780.1	776.8	776.8	776.8	774.3
5°	826.4	828.0	824.7	822.2	814.8	810.7	804.9	800.8	799.1	798.3	795.8
7.5°	870.1	867.6	862.7	861.0	855.2	846.2	835.4	827.2	827.2	826.4	827.2
10°	913.9	907.3	904.8	902.3	893.2	881.7	869.3	860.2	859.4	858.5	856.1
12.5°	957.6	955.1	952.7	943.6	934.5	916.3	902.3	893.2	892.4	893.2	889.9
15°	1015.4	1009.6	1007.1	991.5	971.6	951.8	934.5	926.2	923.8	924.6	922.1
17.5°	1060.0	1060.0	1054.2	1036.9	1011.3	984.0	965.9	960.9	960.1	960.1	960.9
20°	1095.5	1094.6	1088.9	1074.8	1044.3	1017.0	1008.0	1006.3	1005.5	1005.5	1008.0
22.5°	1115.3	1113.6	1111.2	1095.5	1071.5	1053.4	1054.2	1059.1	1060.8	1062.5	1065.8
25°	1125.2	1122.7	1121.9	1111.2	1093.8	1091.3	1106.2	1119.4	1122.7	1126.0	1130.1
27.5°	1141.7	1137.6	1139.2	1135.1	1131.0	1138.4	1168.9	1183.0	1185.5	1189.6	1192.1
30°	1187.1	1185.5	1192.1	1193.7	1197.0	1207.7	1235.8	1249.0	1254.8	1254.8	1266.4
32.5°	1273.8	1274.6	1276.3	1293.6	1299.4	1306.8	1321.7	1332.4	1333.2	1334.0	1344.8
35°	1390.2	1395.1	1409.2	1424.0	1438.1	1437.2	1428.2	1433.9	1429.8	1434.8	1435.6
37.5°	1537.1	1530.5	1551.2	1585.0	1606.5	1600.7	1560.2	1533.8	1541.3	1538.0	1535.5
40°	1650.2	1657.7	1697.3	1741.9	1758.4	1776.5	1723.7	1678.3	1671.7	1659.3	1651.9
42.5°	1806.2	1807.1	1839.3	1872.3	1920.2	1959.8	1925.9	1860.7	1840.9	1826.1	1793.9
45°	1950.7	1948.2	1974.7	2015.1	2072.1	2129.0	2141.4	2070.4	2063.0	2036.6	1994.5
47.5°	2047.3	2044.0	2062.2	2115.0	2207.5	2300.7	2351.9	2330.5	2316.4	2305.7	2239.6
50°	2112.5	2105.9	2126.6	2182.7	2285.9	2429.5	2563.3	2581.4	2575.6	2575.6	2533.5
52.5°	2161.2	2161.2	2176.1	2221.5	2326.3	2505.5	2744.9	2836.5	2843.9	2852.2	2849.7
55°	2134.0	2138.1	2175.3	2241.3	2351.9	2558.3	2895.1	3095.7	3137.0	3171.7	3211.3
57.5°	2040.7	2054.7	2104.3	2212.4	2358.5	2597.9	3061.9	3458.9	3575.3	3676.1	3832.9
60°	1904.5	1922.6	1994.5	2132.3	2309.8	2533.5	3120.5	3766.0	3951.0	4170.6	4580.0
62.5°	1670.9	1689.0	1759.2	1897.1	2049.0	2286.7	2877.8	3811.4	4107.0	4418.2	5037.4
65°	1183.8	1154.9	1235.8	1359.6	1533.8	1764.1	2325.5	3506.8	3932.0	4353.8	5118.3
67.5°	659.6	657.1	706.6	799.1	965.9	1213.5	1602.3	2689.6	3080.9	3558.8	4497.5
70°	454.9	459.8	491.2	591.1	728.9	942.7	1141.7	1689.0	1970.5	2295.0	3217.9
72.5°	319.5	330.2	347.5	407.0	548.1	794.2	1166.5	1009.6	1150.0	1371.2	1935.0
75°	187.4	194.8	207.2	236.1	312.0	530.8	1207.7	887.4	887.4	939.4	1170.6
77.5°	115.6	115.6	123.0	134.6	165.9	260.0	860.2	997.2	969.2	939.4	941.9
80°	59.4	63.6	74.3	80.1	92.5	118.9	386.3	930.4	1020.3	1080.6	1038.5
82.5°	27.2	30.5	45.4	48.7	53.7	62.7	132.9	529.2	709.1	933.7	1166.5
85°	14.0	14.0	23.9	29.7	32.2	28.9	48.7	213.8	323.6	493.7	772.7
87.5°	2.5	2.5	4.1	5.0	7.4	6.6	8.3	12.4	20.6	22.3	23.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P154555

CATALOG NUMBER: TLM-F03-LED-E1-T2

CANDELA DISTRIBUTION (continued):

	65°	66°	67°	68°	69°	70°	71°	72°	73°	74°	75°
0°	758.7	758.7	758.7	758.7	758.7	758.7	758.7	758.7	758.7	758.7	758.7
2.5°	773.5	774.3	773.5	772.7	771.0	771.0	771.0	770.2	770.2	770.2	769.4
5°	795.8	792.5	793.3	791.7	790.9	790.0	790.9	789.2	787.6	788.4	787.6
7.5°	823.9	822.2	818.9	818.9	818.1	816.4	816.4	814.0	813.1	811.5	810.7
10°	855.2	851.1	852.8	851.1	851.9	848.6	847.0	845.3	843.7	843.7	844.5
12.5°	887.4	886.6	884.1	882.5	882.5	880.0	880.8	880.0	877.5	876.7	874.2
15°	920.5	920.5	918.0	918.8	918.0	916.3	914.7	914.7	913.0	911.4	912.2
17.5°	959.3	959.3	959.3	959.3	960.1	957.6	958.4	956.8	955.1	958.4	958.4
20°	1009.6	1012.9	1012.9	1012.1	1016.2	1013.7	1012.9	1017.0	1012.9	1018.7	1017.9
22.5°	1067.4	1070.7	1070.7	1074.0	1074.8	1077.3	1079.0	1077.3	1080.6	1083.9	1083.9
25°	1131.8	1135.1	1137.6	1142.5	1145.0	1143.4	1144.2	1148.3	1150.0	1153.3	1156.6
27.5°	1199.5	1200.3	1203.6	1209.4	1213.5	1215.2	1216.0	1222.6	1223.4	1225.1	1228.4
30°	1265.5	1273.8	1272.1	1279.6	1282.0	1284.5	1289.5	1291.9	1297.7	1301.0	1301.0
32.5°	1343.1	1341.5	1348.1	1353.9	1358.0	1362.1	1366.2	1369.5	1372.8	1374.5	1382.8
35°	1439.7	1443.0	1443.0	1443.8	1453.7	1454.6	1457.9	1465.3	1467.8	1472.7	1476.0
37.5°	1535.5	1529.7	1528.9	1528.9	1525.6	1528.0	1528.9	1529.7	1533.0	1533.8	1537.1
40°	1642.8	1635.4	1628.8	1624.6	1618.0	1608.9	1607.3	1603.2	1605.6	1604.8	1605.6
42.5°	1789.7	1769.1	1753.4	1741.9	1728.6	1718.7	1711.3	1700.6	1693.2	1684.1	1682.4
45°	1977.1	1938.3	1911.9	1892.9	1873.9	1846.7	1831.0	1814.5	1799.6	1784.8	1772.4
47.5°	2223.1	2181.9	2139.8	2105.1	2075.4	2031.6	1987.0	1962.3	1933.4	1907.8	1889.6
50°	2512.9	2463.4	2443.6	2394.8	2357.7	2291.7	2236.3	2195.9	2138.1	2099.3	2065.5
52.5°	2809.3	2796.9	2786.1	2744.9	2701.1	2663.1	2614.4	2543.4	2484.8	2440.3	2370.9
55°	3212.9	3218.7	3214.6	3192.3	3176.6	3140.3	3120.5	3058.6	3032.2	2967.8	2895.1
57.5°	3892.4	3938.6	3997.2	4020.3	4051.7	4022.0	4056.6	4098.7	3993.9	4030.2	3965.0
60°	4760.0	4972.1	5098.4	5253.6	5355.2	5497.2	5522.8	5559.9	5549.2	5569.8	5611.9
62.5°	5290.0	5541.7	5783.6	5959.5	6147.7	6251.7	6377.2	6464.7	6555.5	6616.6	6599.2
65°	5446.0	5705.2	5924.8	6117.1	6285.5	6412.7	6529.1	6638.9	6722.2	6780.9	6815.5
67.5°	4873.1	5211.5	5442.7	5668.1	5885.2	6018.9	6116.3	6222.8	6345.0	6446.5	6466.3
70°	3667.0	4174.7	4502.4	4772.4	5027.4	5207.4	5343.6	5442.7	5537.6	5610.3	5689.5
72.5°	2293.3	2737.4	3112.2	3462.3	3733.0	3980.7	4095.4	4315.0	4286.1	4341.4	4400.9
75°	1374.5	1590.8	1797.2	2044.0	2186.0	2392.4	2429.5	2465.8	2446.9	2384.9	2431.2
77.5°	955.1	990.6	989.0	974.9	960.1	923.8	876.7	851.1	833.8	809.0	818.9
80°	960.9	884.1	766.9	644.7	532.5	458.2	428.4	428.4	459.0	502.7	546.5
82.5°	1148.3	1066.6	951.0	795.8	630.7	513.5	435.1	403.7	409.5	454.0	510.2
85°	774.3	792.5	695.1	635.7	503.6	392.1	328.6	266.6	236.1	243.5	275.7
87.5°	28.1	33.8	12.4	16.5	11.6	9.9	9.9	10.7	7.4	9.1	8.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P154555

CATALOG NUMBER: TLM-F03-LED-E1-T2

CANDELA DISTRIBUTION (continued):

	76°	77°	78°	79°	80°	81°	82°	83°	84°	85°	86°
0°	758.7	758.7	758.7	758.7	758.7	758.7	758.7	758.7	758.7	758.7	758.7
2.5°	768.6	767.7	767.7	766.1	766.1	765.3	765.3	764.4	763.6	763.6	762.8
5°	786.7	785.9	784.2	783.4	781.8	781.8	780.9	779.3	779.3	777.6	776.8
7.5°	812.3	810.7	809.0	808.2	807.4	804.9	804.9	803.2	803.2	801.6	800.8
10°	842.9	841.2	839.6	840.4	837.9	837.1	835.4	835.4	833.0	832.1	832.1
12.5°	875.9	875.1	875.1	872.6	871.8	870.9	867.6	867.6	867.6	866.0	866.8
15°	911.4	912.2	909.7	912.2	911.4	908.9	908.9	908.9	905.6	909.7	906.4
17.5°	959.3	961.7	960.1	960.9	959.3	959.3	960.1	959.3	960.9	960.9	965.9
20°	1018.7	1019.5	1023.7	1022.0	1022.0	1021.2	1022.8	1023.7	1027.0	1025.3	1028.6
22.5°	1083.9	1088.0	1088.9	1092.2	1092.2	1091.3	1093.0	1096.3	1097.9	1100.4	1099.6
25°	1158.2	1160.7	1164.0	1159.9	1166.5	1166.5	1168.1	1172.2	1173.1	1173.1	1178.8
27.5°	1227.6	1234.2	1235.0	1239.1	1236.6	1238.3	1244.1	1246.5	1249.8	1249.8	1251.5
30°	1306.0	1308.5	1310.1	1315.1	1314.2	1315.1	1315.9	1320.0	1320.0	1324.1	1328.3
32.5°	1386.9	1388.5	1390.2	1395.1	1396.8	1400.1	1398.4	1401.7	1405.9	1406.7	1409.2
35°	1483.5	1485.1	1486.8	1494.2	1495.0	1500.8	1502.5	1500.8	1507.4	1503.3	1507.4
37.5°	1539.6	1547.0	1548.7	1553.6	1552.0	1556.1	1558.6	1561.9	1563.5	1566.8	1573.5
40°	1608.1	1610.6	1615.6	1618.0	1621.3	1622.2	1625.5	1627.9	1630.4	1637.8	1645.3
42.5°	1678.3	1681.6	1684.1	1687.4	1691.5	1694.8	1697.3	1704.7	1706.4	1711.3	1725.3
45°	1763.3	1761.7	1762.5	1763.3	1765.0	1769.1	1776.5	1784.0	1788.9	1800.5	1812.0
47.5°	1869.0	1858.3	1854.1	1847.5	1849.2	1858.3	1859.9	1872.3	1882.2	1892.9	1907.0
50°	2029.1	2000.2	1982.9	1965.6	1963.9	1968.9	1975.5	1988.7	2000.2	2014.3	2034.1
52.5°	2298.3	2243.0	2208.3	2160.4	2147.2	2144.7	2139.8	2147.2	2150.5	2169.5	2206.6
55°	2843.1	2740.7	2674.7	2600.4	2531.1	2510.4	2470.8	2479.1	2470.8	2482.4	2537.7
57.5°	3980.7	3899.0	3834.6	3739.6	3620.8	3494.4	3463.1	3333.5	3359.1	3433.4	3385.5
60°	5632.6	5602.8	5556.6	5511.2	5348.6	5256.9	5107.5	5091.0	4986.2	4987.0	4918.5
62.5°	6557.1	6595.1	6567.1	6553.8	6544.8	6515.9	6441.6	6352.4	6218.7	6122.1	5980.1
65°	6821.3	6789.1	6758.6	6754.4	6752.0	6799.0	6809.8	6747.0	6625.7	6475.4	6312.0
67.5°	6513.4	6495.2	6496.9	6462.2	6483.7	6565.4	6622.4	6605.0	6493.6	6312.0	6103.9
70°	5780.3	5744.8	5781.2	5826.6	5858.8	5905.8	5962.8	5976.8	5875.3	5688.7	5476.5
72.5°	4328.2	4334.0	4368.7	4381.1	4510.7	4497.5	4548.6	4381.9	4308.4	4130.9	4022.0
75°	2277.6	2240.5	2337.1	2132.3	2048.1	2106.7	1942.5	1784.8	1817.8	1845.0	1648.6
77.5°	804.9	752.9	664.5	629.0	523.4	443.3	362.4	326.9	307.9	298.0	285.6
80°	577.9	594.4	576.2	533.3	453.2	363.2	286.5	226.2	194.0	176.7	165.1
82.5°	584.5	649.7	678.6	666.2	593.6	449.1	296.4	189.0	140.3	117.2	109.0
85°	313.7	343.4	330.2	278.2	250.1	149.4	102.4	68.5	57.8	52.8	48.7
87.5°	12.4	9.9	8.3	8.3	9.1	9.9	8.3	9.1	8.3	8.3	8.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P154555

CATALOG NUMBER: TLM-F03-LED-E1-T2

CANDELA DISTRIBUTION (continued):

	87°	88°	89°	90°	95°	105°	115°	125°	135°	145°	155°
0°	758.7	758.7	758.7	758.7	758.7	758.7	758.7	758.7	758.7	758.7	758.7
2.5°	761.1	761.1	761.1	760.3	758.7	754.5	750.4	747.1	744.6	742.1	738.8
5°	776.0	774.3	774.3	774.3	767.7	761.1	755.4	749.6	744.6	740.5	737.2
7.5°	800.8	799.9	796.6	795.8	790.9	780.1	773.5	763.6	757.8	752.1	750.4
10°	830.5	829.7	828.8	828.0	821.4	810.7	802.4	793.3	785.1	776.8	768.6
12.5°	865.2	864.3	863.5	861.0	858.5	852.8	843.7	833.8	823.9	806.5	797.5
15°	908.1	909.7	908.1	907.3	905.6	906.4	900.6	886.6	870.9	848.6	829.7
17.5°	965.0	963.4	962.6	965.9	965.0	969.2	967.5	949.4	925.4	889.9	856.9
20°	1027.8	1027.8	1031.1	1033.6	1041.0	1051.7	1046.8	1024.5	980.7	931.2	888.3
22.5°	1102.9	1104.6	1107.9	1106.2	1117.8	1135.1	1136.7	1105.4	1048.4	979.9	919.6
25°	1181.3	1183.0	1179.7	1184.6	1203.6	1228.4	1233.3	1188.8	1113.6	1024.5	946.1
27.5°	1255.6	1257.3	1257.3	1263.9	1282.0	1324.1	1329.1	1279.6	1179.7	1063.3	965.0
30°	1328.3	1334.9	1336.5	1338.2	1365.4	1424.0	1434.8	1362.9	1237.5	1092.2	978.2
32.5°	1419.9	1422.4	1425.7	1429.8	1461.2	1533.0	1533.0	1434.8	1274.6	1110.3	980.7
35°	1518.1	1519.0	1526.4	1527.2	1571.8	1643.6	1629.6	1494.2	1301.0	1106.2	962.6
37.5°	1577.6	1580.9	1588.3	1598.2	1645.3	1746.8	1714.6	1545.4	1306.0	1079.0	921.3
40°	1651.0	1657.7	1665.1	1675.0	1745.2	1851.7	1786.4	1577.6	1285.3	1025.3	859.4
42.5°	1730.3	1739.4	1750.9	1769.1	1852.5	1944.1	1840.9	1582.5	1238.3	965.0	785.9
45°	1819.5	1836.0	1849.2	1870.6	1964.7	2024.2	1873.9	1553.6	1178.8	885.8	707.5
47.5°	1922.6	1935.9	1959.0	1982.1	2076.2	2078.7	1877.2	1497.5	1097.9	806.5	624.1
50°	2049.8	2058.0	2092.7	2106.7	2195.1	2135.6	1853.3	1421.6	1012.9	717.4	531.6
52.5°	2219.0	2230.6	2275.1	2296.6	2359.4	2213.2	1819.5	1339.0	915.5	617.5	436.7
55°	2553.3	2603.7	2635.1	2672.2	2712.7	2389.1	1804.6	1250.7	805.7	501.9	345.9
57.5°	3492.0	3475.5	3544.8	3629.0	3628.2	2791.1	1893.8	1174.7	676.1	383.9	265.8
60°	4890.4	4906.1	4870.6	4921.0	4760.8	3289.7	2015.9	1094.6	530.0	285.6	203.1
62.5°	5929.7	5838.9	5788.6	5729.1	5376.6	3344.2	1926.8	930.4	385.5	200.6	156.0
65°	6175.8	6069.3	5961.1	5848.0	5316.4	3014.8	1580.9	682.7	249.3	137.9	123.8
67.5°	5933.0	5762.2	5624.3	5507.9	4871.4	2498.9	1155.7	419.4	142.8	111.4	105.7
70°	5304.0	5115.0	4892.1	4761.6	4102.0	1841.7	740.5	226.2	109.8	99.1	96.6
72.5°	3882.4	3727.2	3483.7	3334.3	2945.5	1119.4	413.6	127.1	102.4	94.9	91.6
75°	1512.4	1431.5	1329.9	1338.2	1194.5	495.3	187.4	109.8	99.9	93.3	90.0
77.5°	260.0	253.4	234.4	234.4	266.6	180.8	124.7	110.6	99.1	91.6	85.9
80°	156.0	152.7	145.3	143.6	138.7	127.1	119.7	112.3	97.4	86.7	79.3
82.5°	102.4	98.2	95.8	94.9	103.2	111.4	112.3	111.4	92.5	75.1	64.4
85°	43.8	43.8	43.8	44.6	59.4	90.0	92.5	99.1	75.9	58.6	46.2
87.5°	7.4	9.1	9.1	9.9	10.7	19.8	24.8	32.2	25.6	24.8	22.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P154555

CATALOG NUMBER: TLM-F03-LED-E1-T2

CANDELA DISTRIBUTION (continued):

	165°	175°	180°
0°	758.7	758.7	758.7
2.5°	738.0	736.4	736.4
5°	735.5	733.9	734.7
7.5°	745.4	742.1	743.0
10°	763.6	760.3	758.7
12.5°	786.7	782.6	782.6
15°	810.7	800.8	799.9
17.5°	830.5	818.1	816.4
20°	852.8	836.3	833.8
22.5°	873.4	851.1	847.8
25°	888.3	861.0	856.9
27.5°	894.9	862.7	859.4
30°	899.8	863.5	858.5
32.5°	894.9	856.1	851.9
35°	867.6	825.5	823.0
37.5°	820.6	773.5	770.2
40°	758.7	709.1	700.9
42.5°	679.4	633.2	624.1
45°	602.6	549.8	545.7
47.5°	520.1	469.7	472.2
50°	433.4	388.0	387.2
52.5°	350.8	311.2	308.7
55°	276.6	248.5	246.0
57.5°	218.8	203.9	201.4
60°	178.3	170.9	168.4
62.5°	143.6	141.2	140.3
65°	119.7	119.7	119.7
67.5°	104.0	104.8	104.8
70°	95.8	96.6	95.8
72.5°	92.5	94.9	94.9
75°	90.0	91.6	88.3
77.5°	88.3	89.2	83.4
80°	87.5	86.7	75.9
82.5°	75.9	73.5	64.4
85°	69.3	52.8	44.6
87.5°	35.5	24.8	19.0
90°	0.0	0.0	0.0

(END OF REPORT)