

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P150082

Luminaire Tested: **TLM-E02-LED-E1-SL2-7060**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P150082
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33678)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TLM-E02-LED-E1-SL2-7060
Description: TALON MEDIUM LED SITE LUMINAIRE
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 2 W/ SPILL LIGHT CONTROL
Light Source: (42) 5700K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6269.7 lumens
Efficiency: N/A
Efficacy: 120.3 lumens/watt
Spacing Criteria (0/90/45): 1.99 / 4.45 / 2.31
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')
CIE Type: Direct

Input Watts (W): 52.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P150082
CATALOG NUMBER: TLM-E02-LED-E1-SL2-7060

Luminous Intensity Polar Plot





TEST NUMBER: P150082

CATALOG NUMBER: TLM-E02-LED-E1-SL2-7060

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	106	100	94	90	103	98	93	88	93	89	85	89	86	83	85	83	80	78					78			
2	93	83	74	67	90	81	73	66	77	70	64	74	68	63	70	66	61	59					59			
3	82	69	59	51	80	68	58	51	64	56	50	61	54	49	59	53	48	45					45			
4	74	59	48	40	71	57	47	40	55	46	39	52	45	38	50	43	38	35					35			
5	66	51	40	32	64	50	39	32	47	38	31	45	37	31	43	36	30	28					28			
6	60	44	34	26	58	43	33	26	41	32	26	40	32	25	38	31	25	23					23			
7	55	39	29	22	53	38	29	22	37	28	22	35	27	21	34	27	21	19					19			
8	51	35	25	19	49	34	25	19	33	24	18	32	24	18	30	23	18	16					16			
9	47	32	22	16	46	31	22	16	30	22	16	29	21	16	28	21	16	14					14			
10	44	29	20	14	42	28	20	14	27	19	14	26	19	14	25	19	14	12					12			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	21286	21286	21286
5°	21302	22085	21725
10°	22794	24765	21456
15°	24972	28599	19957
20°	27377	32271	17238
25°	31930	36411	14256
30°	37461	42899	11258
35°	53417	54098	9397
40°	67199	69992	8737
45°	76458	94633	8299
50°	78766	119828	7845
55°	79905	152803	7626
60°	98310	268824	7587
65°	100420	373168	7973
70°	48142	386280	9070
75°	13271	159057	11040
80°	11176	22221	10913
85°	7410	13810	11789



TEST NUMBER: P150082

CATALOG NUMBER: TLM-E02-LED-E1-SL2-7060

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.9	1.0
10°-20°	212.1	3.4
20°-30°	366.4	5.8
30°-40°	606.5	9.7
40°-50°	1028.6	16.4
50°-60°	1366.6	21.8
60°-70°	1765.4	28.2
70°-80°	740.4	11.8
80°-90°	118.9	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	643.4	10.3
0°-40°	1249.9	19.9
0°-60°	3645.0	58.1
0°-90°	6269.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6269.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	653	653	653	653	653	
5°	651	662	674	670	664	63
15°	740	748	847	738	591	211
25°	887	806	1012	676	396	414
35°	1342	1119	1359	479	236	830
45°	1658	2366	2052	246	180	1259
55°	1405	2357	2687	167	134	1301
65°	1301	2044	4835	133	103	1176
75°	105	588	1262	138	88	170
85°	20	49	37	42	32	26
90°	0	0	0	0	0	



TEST NUMBER: P150082

CATALOG NUMBER: TLM-E02-LED-E1-SL2-7060

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	60°	61°	62°	64°
0°	652.6	652.6	652.6	652.6	652.6	652.6	652.6	652.6	652.6	652.6	652.6
2.5°	650.6	652.6	651.2	652.6	654.0	654.7	656.0	655.3	655.3	656.0	654.7
5°	650.6	650.6	652.6	656.0	657.4	661.5	666.3	665.6	666.3	665.6	667.0
7.5°	664.2	663.5	665.6	669.7	671.1	677.2	685.4	686.8	688.2	688.2	690.2
10°	688.2	687.5	689.5	691.6	693.6	698.4	710.1	714.9	715.5	716.2	719.0
12.5°	718.3	717.6	714.9	714.9	714.2	723.1	738.8	747.7	749.1	751.8	753.8
15°	739.5	737.4	733.3	730.6	734.0	748.4	771.6	781.9	783.3	785.3	790.8
17.5°	760.0	757.9	749.1	742.2	747.0	770.3	801.7	812.7	815.4	817.5	823.6
20°	788.7	787.4	774.4	757.9	756.6	786.7	825.0	839.4	841.4	844.1	850.3
22.5°	832.5	826.4	811.3	780.5	765.5	796.3	841.4	861.2	864.0	866.7	874.9
25°	887.2	884.5	858.5	811.3	779.8	805.8	859.2	883.8	887.9	891.3	902.3
27.5°	944.0	939.9	911.9	850.3	805.2	825.0	887.2	915.3	920.8	926.2	936.5
30°	994.6	993.3	970.0	903.0	846.2	861.2	932.4	966.6	972.7	979.6	989.2
32.5°	1113.7	1114.4	1090.4	1022.0	945.4	926.9	997.4	1048.7	1051.4	1059.6	1076.7
35°	1341.5	1344.2	1335.3	1281.3	1195.1	1119.1	1126.0	1176.6	1179.3	1186.2	1202.6
37.5°	1494.0	1499.5	1526.8	1543.9	1500.2	1465.3	1378.4	1358.6	1360.6	1356.5	1353.1
40°	1578.2	1586.4	1658.2	1747.1	1795.0	1795.7	1758.1	1670.5	1637.0	1627.4	1586.4
42.5°	1626.0	1639.7	1741.6	1893.5	2031.0	2125.4	2148.7	2051.5	2026.9	1983.1	1904.5
45°	1657.5	1673.9	1794.3	2002.3	2204.8	2365.5	2486.6	2443.5	2427.1	2400.4	2327.9
47.5°	1652.0	1665.0	1790.2	2039.2	2295.7	2524.2	2739.0	2783.5	2763.6	2756.8	2707.6
50°	1552.2	1563.8	1691.0	1947.5	2245.8	2584.4	2899.1	3025.0	3025.0	3038.0	3022.9
52.5°	1445.4	1455.0	1570.6	1801.2	2084.4	2525.6	2988.0	3196.7	3224.0	3246.6	3282.2
55°	1405.1	1416.7	1504.3	1701.3	1946.9	2357.3	3018.1	3325.3	3375.9	3414.2	3494.9
57.5°	1424.2	1435.9	1498.1	1647.2	1866.1	2185.6	3019.5	3498.3	3596.2	3674.8	3838.3
60°	1507.0	1518.0	1569.9	1697.2	1844.9	2086.4	2961.3	3774.0	3930.0	4077.7	4350.0
62.5°	1468.7	1482.4	1558.3	1780.0	2003.0	2011.2	2751.3	3987.4	4238.5	4456.7	4889.7
65°	1301.1	1315.5	1375.0	1582.3	2012.5	2044.0	2440.1	3991.6	4303.5	4598.3	5065.5
67.5°	987.8	993.3	1040.5	1206.7	1609.6	2080.3	2119.9	3518.9	3815.7	4144.8	4627.1
70°	504.8	514.4	528.1	666.3	1036.4	1719.1	1821.7	2593.3	2971.6	3311.6	3891.0
72.5°	175.1	178.5	192.2	254.5	504.8	1128.0	1594.6	1777.2	2005.7	2323.8	2994.9
75°	105.3	105.3	110.1	128.6	230.5	587.6	1418.8	1451.6	1482.4	1589.1	2028.3
77.5°	83.5	84.8	84.8	88.2	127.9	301.7	1077.4	1349.7	1353.8	1364.0	1437.9
80°	59.5	62.3	67.7	70.5	82.8	165.5	604.7	1184.8	1265.5	1304.5	1358.6
82.5°	44.5	47.2	57.5	60.9	64.3	92.3	271.6	817.5	964.5	1042.5	1232.7
85°	19.8	23.3	39.0	43.1	45.1	49.3	127.2	232.6	267.5	300.3	396.1
87.5°	3.4	3.4	6.2	8.9	13.0	12.3	28.0	39.7	40.4	47.2	52.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P150082

CATALOG NUMBER: TLM-E02-LED-E1-SL2-7060

CANDELA DISTRIBUTION (continued):

	65°	66°	67°	68°	69°	70°	71°	72°	73°	74°	75°
0°	652.6	652.6	652.6	652.6	652.6	652.6	652.6	652.6	652.6	652.6	652.6
2.5°	654.7	654.7	654.7	654.0	654.7	654.7	654.7	654.7	655.3	655.3	655.3
5°	669.0	667.7	668.3	668.3	668.3	667.7	669.0	668.3	669.0	671.1	670.4
7.5°	690.2	691.6	692.3	693.0	693.0	693.0	693.6	695.0	695.0	697.1	696.4
10°	721.7	721.0	721.7	723.7	725.8	726.5	728.5	727.9	729.2	732.0	734.7
12.5°	755.2	756.6	758.6	760.7	764.1	764.8	766.8	767.5	771.6	771.6	774.4
15°	792.8	793.5	797.6	798.3	802.4	803.8	807.2	808.6	813.4	814.0	816.8
17.5°	827.0	828.4	830.5	832.5	837.3	839.4	842.1	844.8	848.9	850.3	855.1
20°	854.4	857.1	857.8	861.9	866.0	868.8	871.5	874.2	878.3	880.4	885.2
22.5°	879.0	881.8	883.8	887.2	890.0	894.1	895.4	900.2	904.3	907.8	911.9
25°	905.7	909.8	911.9	918.0	920.1	924.2	927.6	932.4	937.9	942.0	947.4
27.5°	943.3	949.5	952.2	959.1	963.9	965.9	971.4	978.2	983.0	987.8	993.3
30°	995.3	1007.0	1009.0	1013.8	1022.7	1024.1	1030.9	1036.4	1043.9	1048.7	1053.5
32.5°	1076.0	1090.4	1091.8	1097.2	1104.8	1107.5	1113.0	1119.1	1130.8	1132.8	1140.3
35°	1199.9	1206.0	1211.5	1213.5	1219.7	1223.1	1227.2	1234.1	1245.7	1244.3	1252.5
37.5°	1348.3	1350.4	1351.0	1344.2	1345.6	1339.4	1346.9	1348.3	1352.4	1355.8	1364.0
40°	1560.4	1539.2	1536.4	1520.0	1503.6	1494.7	1491.3	1477.6	1481.0	1482.4	1489.2
42.5°	1870.2	1829.2	1795.0	1771.7	1731.4	1711.5	1684.9	1663.7	1647.2	1653.4	1656.1
45°	2262.9	2204.1	2149.3	2078.2	2025.5	1987.9	1940.7	1898.3	1879.1	1870.2	1881.2
47.5°	2654.9	2602.9	2538.6	2465.4	2381.9	2319.7	2241.0	2171.9	2124.0	2106.3	2115.8
50°	2993.5	2945.6	2897.0	2853.9	2756.8	2689.1	2581.7	2492.1	2416.8	2378.5	2368.3
52.5°	3274.6	3249.3	3223.3	3187.1	3109.1	3041.4	2955.9	2867.6	2767.7	2689.8	2663.1
55°	3525.7	3540.7	3527.8	3528.4	3497.7	3454.6	3382.0	3316.4	3246.6	3158.4	3121.4
57.5°	3891.7	3980.6	3998.4	4042.9	4064.7	4088.0	4108.5	4069.5	4051.7	3986.1	3986.8
60°	4468.3	4598.3	4711.2	4813.8	4897.9	4980.0	5066.2	5104.5	5146.9	5166.8	5234.5
62.5°	5082.0	5205.8	5374.1	5511.6	5588.9	5695.6	5789.3	5850.2	5924.7	6004.1	6107.4
65°	5233.8	5382.9	5489.0	5580.6	5657.3	5714.0	5765.3	5837.9	5900.1	6026.0	6147.7
67.5°	4844.6	4963.6	5060.8	5151.0	5210.6	5258.4	5304.3	5352.2	5458.9	5573.1	5695.6
70°	4158.5	4302.1	4462.9	4579.9	4609.3	4650.3	4694.1	4756.3	4809.7	4929.4	5022.4
72.5°	3341.0	3547.6	3683.7	3845.8	3880.7	3943.0	3967.6	4016.2	4025.8	4090.7	4115.4
75°	2328.6	2565.3	2702.1	2821.1	2844.4	2810.2	2823.8	2652.1	2608.4	2572.8	2544.1
77.5°	1537.1	1600.7	1622.6	1603.5	1511.8	1440.0	1363.4	1288.1	1296.3	1235.4	1128.7
80°	1366.8	1381.1	1361.3	1342.1	1289.5	1214.2	1145.1	1074.7	1039.8	1002.8	948.1
82.5°	1329.8	1385.2	1391.4	1368.1	1326.4	1244.3	1160.9	1056.2	967.3	885.2	801.7
85°	444.6	541.1	584.2	624.6	636.9	651.2	602.0	534.9	454.2	400.2	313.3
87.5°	56.8	70.5	81.4	69.8	81.4	95.8	69.1	77.3	78.0	48.6	36.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P150082

CATALOG NUMBER: TLM-E02-LED-E1-SL2-7060

CANDELA DISTRIBUTION (continued):

	76°	77°	78°	79°	80°	81°	82°	83°	84°	85°	86°
0°	652.6	652.6	652.6	652.6	652.6	652.6	652.6	652.6	652.6	652.6	652.6
2.5°	656.0	655.3	655.3	655.3	654.7	655.3	655.3	655.3	655.3	655.3	654.7
5°	671.1	671.1	673.1	673.8	672.4	671.8	672.4	673.1	673.1	672.4	673.1
7.5°	699.1	699.8	701.2	703.2	701.9	702.5	703.2	702.5	704.6	705.3	704.6
10°	734.7	736.1	739.5	740.2	739.5	742.2	742.9	741.5	742.9	742.9	745.6
12.5°	775.7	777.1	781.2	782.6	783.9	784.6	786.7	787.4	789.4	790.8	792.8
15°	820.2	821.6	824.3	829.1	830.5	831.8	833.2	837.3	838.0	840.7	842.8
17.5°	857.8	859.9	864.0	867.4	869.5	872.9	874.2	879.0	880.4	884.5	887.9
20°	887.9	891.3	894.8	898.9	902.3	906.4	907.8	912.5	915.3	917.3	921.4
22.5°	915.3	919.4	924.2	929.0	931.7	937.2	939.2	941.3	947.4	950.2	954.3
25°	950.9	955.0	960.4	966.6	969.3	976.2	978.2	981.6	988.5	991.2	997.4
27.5°	999.4	1004.9	1009.0	1015.2	1018.6	1023.4	1028.2	1032.3	1038.4	1042.5	1049.4
30°	1060.3	1064.4	1071.3	1076.0	1081.5	1088.4	1093.8	1097.9	1101.4	1107.5	1115.0
32.5°	1149.9	1150.6	1152.7	1164.3	1169.8	1175.2	1182.8	1186.2	1191.7	1197.8	1206.0
35°	1261.4	1267.6	1272.4	1277.8	1284.0	1290.2	1292.9	1303.2	1307.9	1316.2	1324.4
37.5°	1372.2	1372.9	1383.9	1387.3	1392.8	1398.9	1408.5	1418.8	1431.1	1439.3	1452.3
40°	1491.3	1496.7	1510.4	1517.3	1524.1	1539.2	1546.7	1563.1	1583.6	1595.3	1617.1
42.5°	1663.7	1671.9	1696.5	1707.4	1723.9	1748.5	1764.2	1786.8	1795.0	1823.0	1833.3
45°	1889.4	1914.7	1950.3	1973.5	2003.0	2029.6	2043.3	2053.6	2065.9	2087.8	2085.0
47.5°	2133.6	2166.5	2206.1	2254.0	2273.2	2304.6	2322.4	2342.3	2331.3	2325.8	2320.4
50°	2384.0	2422.3	2475.0	2518.1	2547.5	2566.6	2581.7	2578.9	2555.7	2543.4	2509.2
52.5°	2662.4	2685.0	2734.9	2771.9	2789.6	2793.7	2790.3	2769.8	2747.9	2708.9	2668.6
55°	3089.3	3079.0	3098.8	3115.9	3110.5	3129.6	3080.4	3061.2	3007.2	2956.6	2902.5
57.5°	3956.7	3970.3	3859.5	3809.6	3800.7	3818.5	3731.6	3720.7	3590.0	3573.6	3482.6
60°	5224.9	5292.0	5205.1	5156.5	5025.2	4982.1	4884.9	4844.6	4719.4	4618.2	4490.2
62.5°	6178.5	6239.4	6275.7	6206.6	6130.0	6017.1	5870.0	5707.2	5574.5	5419.2	5283.8
65°	6264.7	6387.8	6471.3	6503.5	6449.4	6325.6	6144.3	5939.1	5735.9	5541.0	5370.0
67.5°	5861.8	5971.9	6101.2	6216.8	6223.7	6143.0	5988.4	5779.7	5545.1	5304.3	5103.8
70°	5169.5	5307.7	5420.6	5542.3	5627.2	5580.6	5503.3	5311.8	5068.3	4880.8	4650.3
72.5°	4204.3	4262.4	4289.8	4409.5	4410.9	4326.1	4271.3	4165.3	3969.0	3836.3	3660.5
75°	2455.1	2327.2	2191.1	2072.7	1976.3	1935.9	1756.7	1726.6	1606.2	1531.6	1422.2
77.5°	1012.4	898.2	751.1	628.7	507.6	452.9	373.5	338.6	293.5	273.6	260.6
80°	868.1	760.0	649.2	543.2	448.8	354.3	275.7	214.1	168.3	143.0	132.7
82.5°	708.7	643.7	566.4	508.9	435.1	364.6	307.8	238.7	178.5	131.3	100.6
85°	255.8	210.0	169.0	155.3	123.8	101.9	85.5	73.2	60.2	47.9	42.4
87.5°	28.7	27.4	15.7	15.0	17.1	12.3	14.4	13.0	10.9	9.6	10.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P150082

CATALOG NUMBER: TLM-E02-LED-E1-SL2-7060

CANDELA DISTRIBUTION (continued):

	87°	88°	89°	90°	95°	105°	115°	125°	135°	145°	155°
0°	652.6	652.6	652.6	652.6	652.6	652.6	652.6	652.6	652.6	652.6	652.6
2.5°	654.7	654.7	655.3	655.3	656.0	656.7	658.1	657.4	657.4	658.1	658.1
5°	673.1	675.2	674.5	674.5	674.5	675.2	675.9	673.1	670.4	667.7	666.3
7.5°	705.3	706.6	708.0	706.6	708.0	707.3	706.0	698.4	689.5	678.6	671.1
10°	747.0	747.0	748.4	747.7	750.4	748.4	744.3	727.2	708.0	684.8	667.7
12.5°	792.2	796.9	794.9	795.6	801.0	795.6	786.0	760.7	726.5	688.9	658.8
15°	845.5	847.6	848.9	846.9	850.3	845.5	828.4	788.0	738.1	685.4	641.0
17.5°	889.3	890.0	890.7	892.0	896.8	891.3	861.9	807.2	740.8	669.7	610.9
20°	923.5	926.9	929.7	929.7	936.5	928.3	889.3	816.8	732.0	643.7	572.6
22.5°	959.1	961.8	965.2	965.9	974.8	966.6	911.9	814.7	708.7	606.8	528.1
25°	1002.8	1005.6	1008.3	1011.7	1024.1	1012.4	934.4	806.5	676.5	563.0	480.2
27.5°	1053.5	1059.6	1061.7	1067.1	1081.5	1063.7	953.6	794.2	641.0	512.4	429.6
30°	1121.2	1128.7	1131.5	1139.0	1158.8	1119.8	964.5	773.0	595.8	461.1	375.6
32.5°	1212.2	1222.4	1230.6	1238.9	1261.4	1175.9	965.9	742.2	543.2	403.6	323.6
35°	1331.2	1346.9	1353.1	1358.6	1379.8	1236.8	959.8	696.4	478.8	344.8	282.5
37.5°	1464.6	1480.3	1484.4	1487.2	1491.3	1288.8	944.7	626.6	406.3	293.5	249.7
40°	1628.8	1642.5	1647.9	1643.8	1621.9	1329.1	911.2	545.2	335.9	258.6	229.2
42.5°	1829.2	1849.7	1851.8	1833.3	1760.8	1351.7	844.1	449.4	280.5	233.3	213.4
45°	2077.5	2076.2	2064.5	2051.5	1912.0	1342.8	750.4	366.0	245.6	213.4	199.1
47.5°	2300.5	2277.3	2259.5	2221.2	2045.4	1290.8	629.3	303.0	224.4	198.4	186.8
50°	2483.2	2440.8	2403.1	2361.4	2144.6	1198.5	508.9	257.2	204.5	185.4	175.1
52.5°	2627.5	2576.2	2532.4	2491.4	2240.3	1095.9	417.3	223.7	185.4	172.4	162.1
55°	2853.3	2802.0	2732.2	2687.0	2386.7	1001.5	357.8	197.0	166.9	158.7	148.4
57.5°	3424.5	3379.3	3295.9	3178.9	2763.0	965.9	324.2	176.5	151.9	147.1	138.9
60°	4421.8	4348.6	4239.9	4120.8	3527.8	989.8	297.6	162.1	141.6	137.5	131.3
62.5°	5174.3	5045.7	4922.6	4812.4	4139.3	989.2	262.7	151.2	134.1	132.0	125.9
65°	5205.1	5074.4	4950.6	4835.0	4153.0	880.4	221.6	141.6	132.7	132.0	121.8
67.5°	4928.7	4787.1	4667.4	4521.7	3844.5	688.2	177.9	135.4	138.2	136.8	120.4
70°	4477.2	4292.5	4194.0	4050.4	3383.4	481.6	146.4	137.5	149.8	145.7	122.4
72.5°	3514.1	3374.5	3224.7	3124.8	2648.7	304.4	123.1	138.9	154.6	147.8	127.9
75°	1307.9	1345.6	1284.0	1262.1	1345.6	178.5	109.5	129.3	138.2	127.9	116.3
77.5°	264.1	252.4	239.4	236.7	305.8	110.1	100.6	112.2	106.0	93.7	94.4
80°	126.6	123.1	119.0	118.3	113.6	91.7	93.0	95.8	80.0	72.5	77.3
82.5°	84.1	79.4	78.0	75.2	76.6	82.1	88.2	82.1	61.6	57.5	69.8
85°	39.0	37.6	36.9	36.9	41.0	73.9	73.2	60.2	42.4	41.0	69.8
87.5°	9.6	9.6	10.3	9.6	10.9	21.9	19.2	18.5	15.7	17.8	32.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P150082

CATALOG NUMBER: TLM-E02-LED-E1-SL2-7060

CANDELA DISTRIBUTION (continued):

	165°	175°	180°
0°	652.6	652.6	652.6
2.5°	657.4	658.1	657.4
5°	663.5	663.5	663.5
7.5°	663.5	661.5	660.8
10°	654.0	647.8	647.8
12.5°	637.6	627.3	625.9
15°	606.8	593.1	591.0
17.5°	567.8	549.3	545.9
20°	524.0	500.7	496.6
22.5°	476.1	449.4	447.4
25°	428.9	401.5	396.1
27.5°	376.2	349.6	346.8
30°	323.6	300.3	298.9
32.5°	279.1	264.7	262.0
35°	247.6	239.4	236.0
37.5°	227.1	221.0	220.3
40°	211.4	205.9	205.2
42.5°	198.4	193.6	192.9
45°	185.4	181.3	179.9
47.5°	172.4	168.3	167.6
50°	160.8	155.3	154.6
52.5°	149.8	144.3	143.0
55°	139.6	134.1	134.1
57.5°	130.7	125.2	124.5
60°	122.4	117.0	116.3
62.5°	116.3	109.5	108.8
65°	111.5	104.7	103.3
67.5°	108.8	100.6	98.5
70°	113.6	98.5	95.1
72.5°	114.2	96.5	91.7
75°	110.1	91.0	87.6
77.5°	96.5	81.4	78.0
80°	83.5	62.9	58.1
82.5°	79.4	51.3	44.5
85°	61.6	33.5	31.5
87.5°	34.9	18.5	15.0
90°	0.0	0.0	0.0

(END OF REPORT)