

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P197656

Luminaire Tested: **TT-C1-LED-E1-5MQ-PM-CG-LWR-LW-7060**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P197656  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P115378)  
Test Lab: INNOVATION CENTER P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TT-C1-LED-E1-5MQ-PM-CG-LWR-LW-7060  
Description: TOPTIER LED AREA/SITE LUMINAIRE  
MEDIUM DISTRIBUTION WITH CLEAR GLASS LENS AND LumaWatt WIRELESS SENSOR  
Light Source: (168) 5700K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2878.4 lumens  
Efficiency: N/A  
Efficacy: 102.8 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type V - Short - Semi-Cutoff  
BUG Rating: B1 - U0 - G1

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT




REPORT NUMBER: P197656

CATALOG NUMBER: TT-C1-LED-E1-5MQ-PM-CG-LWR-LW-7060

### Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd  
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 5.6 fc  
 Type V - Short - Semi-Cutoff

REPORT NUMBER: P197656

CATALOG NUMBER: TT-C1-LED-E1-5MQ-PM-CG-LWR-LW-7060

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral      - - - Horizontal Cone Through 61-Deg Vertical

REPORT NUMBER: P197656

CATALOG NUMBER: TT-C1-LED-E1-5MQ-PM-CG-LWR-LW-7060

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1439.2	0.0	1439.2
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	1439.2	0.0	1439.2
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	2878.4	0.0	2878.4
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	53.2	1.8
10°-20°	157.3	5.5
20°-30°	253.1	8.8
30°-40°	335.3	11.6
40°-50°	423.4	14.7
50°-60°	507.3	17.6
60°-70°	554.7	19.3
70°-80°	444.0	15.4
80°-90°	150.2	5.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2878.4	100.0
0°-180°	2878.4	100.0



REPORT NUMBER: P197656


CATALOG NUMBER: TT-C1-LED-E1-5MQ-PM-CG-LWR-LW-7060

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	231.8	8.1			
FM	(30°-60°)	633.0	22.0			
FH	(60°-80°)	499.3	17.3			G0/660
FVH	(80°-90°)	75.1	2.6			G1/100
BL	(0°-30°)	231.8	8.1	B1/500		
BM	(30°-60°)	633.0	22.0	B1/1000		
BH	(60°-80°)	499.3	17.3	B1/500		G0/660
BVH	(80°-90°)	75.1	2.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B1-U0-G1**

Type V Short





REPORT NUMBER: P197656

CATALOG NUMBER: TT-C1-LED-E1-5MQ-PM-CG-LWR-LW-7060

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	557.7	557.7	557.7	557.7	557.7	557.7	557.7	557.7	557.7	557.7	557.7
2.5°	558.2	557.7	558.2	558.2	558.2	558.2	558.2	558.2	558.2	558.2	558.2
5°	557.7	557.7	557.7	557.7	557.7	557.7	557.7	557.7	557.7	557.7	557.7
7.5°	557.2	557.2	557.2	557.2	557.2	557.2	557.2	557.2	557.7	557.2	557.7
10°	556.1	556.1	556.1	556.1	556.6	556.6	556.6	556.6	556.6	556.6	556.6
12.5°	555.0	555.0	555.0	555.0	555.5	555.5	555.5	555.5	556.1	556.1	555.5
15°	553.9	553.4	553.4	553.9	553.9	554.4	554.4	554.4	555.0	554.4	554.4
17.5°	552.8	552.3	552.8	553.4	553.4	553.9	554.4	554.4	555.0	555.0	555.0
20°	554.4	553.9	554.4	555.0	555.5	556.6	557.2	557.7	558.2	558.7	558.7
22.5°	551.2	550.7	551.2	551.2	551.7	552.3	553.4	553.9	554.4	554.4	554.4
25°	546.4	546.4	546.9	546.9	547.5	548.0	548.6	549.1	549.1	549.6	549.1
27.5°	541.1	541.1	541.6	541.6	542.7	542.7	543.2	543.7	544.2	544.2	544.2
30°	534.6	534.6	535.2	535.7	536.7	537.3	537.8	538.3	538.9	538.9	538.9
32.5°	528.7	528.2	528.7	529.8	531.4	532.5	533.5	534.1	534.1	534.1	534.6
35°	523.9	524.4	525.5	526.6	528.7	529.8	530.8	532.5	533.0	533.0	533.0
37.5°	525.0	525.5	527.1	529.2	531.9	535.2	537.3	539.4	541.1	540.5	540.0
40°	531.9	533.0	535.7	538.9	543.2	547.5	550.7	553.4	555.0	555.5	555.0
42.5°	533.0	534.1	536.2	541.1	545.9	550.7	555.0	557.7	559.8	560.3	559.8
45°	532.5	532.5	535.7	541.1	545.9	550.7	556.1	559.8	562.0	562.0	562.0
47.5°	528.7	530.3	532.5	537.8	544.2	549.1	554.4	558.2	560.9	562.5	560.9
50°	528.7	528.7	532.5	536.2	542.1	550.7	558.2	562.0	564.7	564.1	564.7
52.5°	527.7	530.8	533.0	538.3	549.1	557.7	563.6	568.9	572.6	573.2	572.2
55°	537.3	537.8	542.7	552.8	563.0	572.6	583.4	591.5	597.9	601.7	596.3
57.5°	544.8	542.1	551.7	560.3	572.2	586.7	602.7	609.1	614.0	612.9	614.5
60°	534.6	538.3	545.3	554.4	573.2	587.7	596.3	603.2	609.1	610.7	608.6
61°	529.8	536.2	539.4	551.7	571.6	582.3	591.5	601.1	611.8	615.6	610.7
62.5°	521.7	531.9	530.8	550.7	563.0	575.4	592.5	603.8	611.3	612.4	611.3
65°	522.2	520.7	533.0	547.5	559.8	581.8	596.3	603.2	607.6	609.7	608.6
67.5°	505.1	499.7	514.7	525.0	545.9	563.0	577.0	587.1	593.6	595.7	593.1
70°	465.4	469.2	479.9	495.5	512.6	533.5	546.4	559.8	565.2	565.7	565.7
72.5°	427.3	429.5	440.3	454.7	474.6	492.8	505.7	516.4	521.2	521.7	522.8
75°	376.9	379.1	391.4	404.8	424.7	440.3	449.3	462.2	469.2	475.1	470.3
77.5°	318.5	322.3	331.9	346.4	364.6	373.2	389.3	404.3	409.1	410.8	409.1
80°	252.5	257.4	266.0	285.3	293.3	307.3	322.8	329.2	333.5	334.6	335.1
82.5°	181.8	185.6	194.6	208.0	217.2	228.5	239.1	247.2	252.0	251.0	250.4
85°	107.2	108.3	118.0	127.1	134.1	141.0	149.6	155.5	156.6	158.7	158.2
87.5°	32.2	32.7	37.0	41.8	45.1	48.2	53.6	60.6	62.2	57.9	58.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P197656

CATALOG NUMBER: TT-C1-LED-E1-5MQ-PM-CG-LWR-LW-7060

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	557.7	557.7	557.7	557.7	557.7	557.7	557.7	557.7
2.5°	558.2	558.2	558.2	558.2	558.2	558.2	557.7	558.2
5°	557.7	557.7	557.7	557.7	557.7	557.7	557.7	557.7
7.5°	557.7	557.2	557.2	557.2	557.2	557.2	557.2	557.2
10°	556.6	556.6	556.6	556.6	556.1	556.1	556.1	556.1
12.5°	555.5	555.5	555.5	555.5	555.0	555.0	555.0	555.0
15°	554.4	554.4	554.4	554.4	553.9	553.9	553.9	553.9
17.5°	555.0	554.4	553.9	553.9	553.4	552.8	552.8	552.8
20°	558.2	557.7	556.6	555.5	555.0	554.4	554.4	554.4
22.5°	553.9	553.4	552.3	551.7	551.7	551.2	550.7	550.7
25°	549.1	548.0	548.0	547.5	547.5	546.4	546.4	545.9
27.5°	543.7	543.2	542.7	542.1	542.1	541.6	541.1	540.5
30°	538.9	537.8	536.7	536.2	535.7	535.2	535.2	535.2
32.5°	534.1	533.0	532.5	530.8	529.8	529.2	528.7	528.7
35°	532.5	530.8	529.8	528.2	526.6	525.5	525.0	523.9
37.5°	538.9	536.7	535.2	532.5	528.7	527.1	525.5	525.0
40°	552.8	550.7	547.5	543.2	538.9	535.7	533.0	531.9
42.5°	557.7	555.0	550.7	546.4	541.1	536.2	534.1	533.0
45°	559.3	556.6	550.7	545.3	540.5	536.2	533.0	531.9
47.5°	557.7	553.9	548.6	544.2	537.3	531.9	529.8	528.2
50°	561.4	558.2	551.2	541.6	535.7	532.5	528.7	528.2
52.5°	568.9	563.0	556.6	549.6	538.3	531.9	529.8	527.1
55°	591.5	583.4	572.2	560.9	553.9	543.7	537.3	537.3
57.5°	608.6	602.1	587.7	572.6	559.8	552.3	542.7	543.2
60°	603.8	595.2	588.2	573.2	555.0	544.8	541.1	534.1
61°	603.2	591.5	581.8	570.0	554.4	538.3	537.3	528.2
62.5°	604.3	593.6	575.4	563.0	551.2	530.3	529.8	521.2
65°	603.2	593.1	583.9	560.9	544.8	536.2	518.0	525.0
67.5°	586.7	577.5	560.9	548.0	523.3	512.6	502.4	502.4
70°	560.3	546.9	530.8	514.7	498.2	479.9	470.8	465.4
72.5°	516.4	505.1	492.3	475.1	454.7	438.1	429.5	425.8
75°	461.2	448.8	437.6	424.7	403.3	389.3	380.2	377.5
77.5°	403.3	392.5	372.7	360.4	345.9	329.8	321.7	318.5
80°	329.2	323.4	309.4	289.5	282.6	262.7	257.4	252.5
82.5°	247.2	240.8	227.9	214.0	205.4	194.1	184.5	183.4
85°	155.5	151.2	143.1	133.0	122.2	115.8	107.2	109.4
87.5°	57.9	55.2	50.4	44.0	39.2	34.8	30.6	32.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)