

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P197582

Luminaire Tested: **TT-C1-LED-E1-5MQ-PM-LWR-LW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P197582
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P115393)
Test Lab: INNOVATION CENTER P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TT-C1-LED-E1-5MQ-PM-LWR-LW
Description: TOPTIER LED AREA/SITE LUMINAIRE
MEDIUM DISTRIBUTION WITH LumaWatt WIRELESS SENSOR
Light Source: (168) 4000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3489 lumens
Efficiency: N/A
Efficacy: 124.6 lumens/watt
Luminous Opening: Circular (Dia: 1.12' x H: 0')
IES Classification: Type V - Short - Full Cutoff
BUG Rating: B2 - U0 - G1

Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P197582

CATALOG NUMBER: TT-C1-LED-E1-5MQ-PM-LWR-LW

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 7.2 fc
 Type V - Short - Full Cutoff

REPORT NUMBER: P197582
CATALOG NUMBER: TT-C1-LED-E1-5MQ-PM-LWR-LW

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P197582

CATALOG NUMBER: TT-C1-LED-E1-5MQ-PM-LWR-LW


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1744.5	0.0	1744.5
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	1744.5	0.0	1744.5
	% Fixture	50.0	0.0	50.0
Total	Lumens	3489.0	0.0	3489.0
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.6	2.0
10°-20°	202.3	5.8
20°-30°	324.0	9.3
30°-40°	426.5	12.2
40°-50°	531.2	15.2
50°-60°	625.8	17.9
60°-70°	665.3	19.1
70°-80°	498.9	14.3
80°-90°	146.5	4.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3489.0	100.0
0°-180°	3489.0	100.0



REPORT NUMBER: P197582


CATALOG NUMBER: TT-C1-LED-E1-5MQ-PM-LWR-LW

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	297.4	8.5			
FM (30°-60°)	791.7	22.7			
FH (60°-80°)	582.1	16.7			G0/660
FVH (80°-90°)	73.2	2.1			G1/100
BL (0°-30°)	297.4	8.5	B1/500		
BM (30°-60°)	791.7	22.7	B1/1000		
BH (60°-80°)	582.1	16.7	B2/1000		G0/660
BVH (80°-90°)	73.2	2.1			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G1

Type V Short





REPORT NUMBER: P197582

CATALOG NUMBER: TT-C1-LED-E1-5MQ-PM-LWR-LW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	719.7	719.7	719.7	719.7	719.7	719.7	719.7	719.7	719.7	719.7	719.7
2.5°	719.0	719.0	719.0	719.7	719.7	719.7	719.7	719.7	719.7	719.7	719.7
5°	719.0	719.0	719.0	719.0	719.0	719.0	719.7	719.7	719.7	719.7	719.7
7.5°	717.5	717.5	717.5	717.5	717.5	718.2	718.2	718.2	718.2	718.2	718.2
10°	716.0	716.0	716.0	716.0	716.8	716.8	716.8	716.8	716.8	716.8	716.8
12.5°	714.6	714.6	713.8	714.6	714.6	714.6	715.3	715.3	715.3	715.3	715.3
15°	711.7	711.7	712.4	712.4	713.1	713.1	713.1	713.1	713.8	713.8	713.8
17.5°	710.2	710.2	710.9	711.7	711.7	712.4	713.1	713.1	713.8	713.8	713.8
20°	712.4	712.4	712.4	713.1	713.8	714.6	715.3	716.0	716.0	716.8	716.0
22.5°	708.0	708.0	708.0	708.7	708.7	708.7	709.5	710.2	710.2	710.9	710.2
25°	700.0	700.0	700.7	700.7	701.4	701.4	702.2	702.2	702.2	702.9	702.9
27.5°	691.9	691.2	692.7	692.7	693.4	693.4	694.1	694.8	694.8	694.8	695.6
30°	683.2	683.2	683.9	683.9	684.6	685.3	686.1	686.8	686.8	687.5	687.5
32.5°	673.7	674.4	675.1	675.9	676.6	678.0	678.8	679.5	680.2	681.0	680.2
35°	667.1	667.8	668.5	670.0	672.2	673.7	675.1	676.6	677.3	677.3	677.3
37.5°	668.5	669.3	670.7	673.7	677.3	679.5	682.4	684.6	685.3	686.1	686.1
40°	676.6	678.0	680.2	683.9	688.3	691.9	696.3	698.5	700.0	700.7	700.0
42.5°	675.9	678.0	680.2	684.6	689.7	693.4	697.8	700.0	701.4	702.2	701.4
45°	673.7	675.1	677.3	681.7	685.3	690.5	694.8	697.0	699.2	700.0	699.2
47.5°	668.5	668.5	669.3	673.7	678.8	685.3	689.0	692.7	694.8	694.8	694.8
50°	662.0	664.9	666.4	672.2	677.3	683.2	689.7	694.8	695.6	696.3	695.6
52.5°	662.0	662.7	667.8	671.5	681.7	690.5	697.0	702.2	706.5	707.3	707.3
55°	673.7	675.1	678.0	686.8	694.8	708.0	719.0	723.3	726.3	729.2	726.3
57.5°	674.4	679.5	684.6	694.8	707.3	718.2	727.7	735.8	738.0	743.1	737.2
60°	665.6	667.1	672.2	684.6	700.7	712.4	721.2	728.5	735.8	732.8	735.8
62.5°	651.7	655.4	662.7	672.2	685.3	699.2	712.4	714.6	725.5	722.6	727.0
65°	640.8	643.7	651.0	664.9	681.0	689.7	704.3	713.1	712.4	718.2	711.7
67.5°	613.7	615.9	622.5	636.4	651.7	664.9	669.3	683.2	684.6	692.7	685.3
70°	569.2	574.3	583.8	596.9	609.4	620.3	628.4	635.7	640.0	641.5	640.0
72.5°	513.6	521.7	529.0	541.4	553.8	561.1	566.3	576.5	579.4	583.8	582.3
75°	456.7	456.7	464.0	473.5	483.0	487.3	490.3	496.8	500.5	505.6	501.2
77.5°	378.5	382.9	389.4	397.5	396.0	398.2	398.2	401.9	400.4	404.0	407.0
80°	296.6	301.0	306.9	312.7	312.0	306.9	310.5	306.1	304.7	305.4	307.6
82.5°	211.9	214.8	219.9	223.6	223.6	219.9	221.4	217.0	218.5	214.8	217.7
85°	121.3	124.9	128.6	132.2	132.2	130.1	132.2	126.4	127.1	127.1	127.1
87.5°	30.0	32.9	34.3	36.5	35.1	38.7	40.9	37.3	38.0	36.5	38.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P197582

CATALOG NUMBER: TT-C1-LED-E1-5MQ-PM-LWR-LW

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	719.7	719.7	719.7	719.7	719.7	719.7	719.7	719.7
2.5°	719.7	719.0	719.7	719.7	719.7	719.7	719.0	719.0
5°	719.7	719.7	719.7	719.0	719.0	719.0	719.0	719.0
7.5°	718.2	718.2	718.2	717.5	717.5	717.5	717.5	717.5
10°	716.8	716.8	716.0	716.0	716.0	716.0	716.0	716.0
12.5°	715.3	715.3	714.6	714.6	714.6	714.6	714.6	713.8
15°	713.8	713.8	713.1	713.1	712.4	712.4	711.7	711.7
17.5°	713.8	713.1	712.4	711.7	711.7	710.9	710.2	710.2
20°	716.0	715.3	714.6	713.8	713.1	712.4	712.4	711.7
22.5°	710.2	709.5	708.7	708.7	708.0	708.0	708.0	707.3
25°	702.9	702.2	702.2	700.7	700.7	700.0	700.0	699.2
27.5°	694.8	694.1	694.1	693.4	692.7	691.9	691.2	691.2
30°	686.8	686.1	686.1	685.3	683.9	683.9	683.2	682.4
32.5°	679.5	679.5	678.8	677.3	675.9	675.1	673.7	673.7
35°	677.3	675.9	674.4	672.2	670.0	668.5	667.8	667.1
37.5°	685.3	683.2	679.5	677.3	674.4	671.5	670.0	668.5
40°	699.2	695.6	691.9	688.3	683.9	680.2	677.3	676.6
42.5°	700.0	697.8	694.1	689.7	684.6	680.2	677.3	676.6
45°	697.8	694.8	690.5	685.3	681.7	676.6	674.4	673.7
47.5°	692.7	689.7	685.3	678.0	672.9	669.3	668.5	668.5
50°	695.6	689.7	682.4	678.0	672.9	667.1	664.9	663.4
52.5°	702.2	696.3	691.9	682.4	671.5	666.4	663.4	661.2
55°	723.3	720.4	707.3	694.1	686.1	679.5	676.6	675.1
57.5°	737.2	727.0	716.0	707.3	697.8	686.8	679.5	675.9
60°	729.9	719.0	713.8	702.2	682.4	670.7	666.4	664.2
62.5°	713.8	713.8	700.0	681.7	674.4	664.2	656.1	653.2
65°	713.1	703.6	689.7	683.2	665.6	650.3	642.2	640.8
67.5°	682.4	669.3	665.6	651.0	636.4	622.5	616.7	613.7
70°	635.7	631.3	620.3	610.8	597.7	583.1	575.0	572.1
72.5°	576.5	569.2	564.1	556.0	543.6	525.3	518.8	515.1
75°	496.1	492.5	492.5	483.7	472.0	461.0	460.3	458.8
77.5°	398.9	400.4	404.0	394.6	398.2	392.4	387.2	383.6
80°	303.2	309.8	310.5	312.7	314.9	306.9	303.2	298.8
82.5°	215.5	219.2	223.6	224.3	225.8	219.9	217.0	212.6
85°	127.1	129.3	133.0	133.0	133.0	127.9	126.4	122.7
87.5°	37.3	37.3	39.5	37.3	37.3	37.3	33.6	35.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)