

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P588382

Luminaire Tested: **GAT-CA6-LED-110-730-U-55-5-X-X**

Issue Date: 11/30/2021

Test Information

Test Method: LM-79-08
Report Number: P588382
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2107-308-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GAT-CA6-LED-110-730-U-55-5-X-X
Description: GENERATIONS SERIES AVENUE WITH NO CAGE AND TYPE V REFRACTOR
Light Source: (6) 3000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14238 lumens
Efficiency: N/A
Efficacy: 126.9 lumens/watt
Luminous Opening: Vertical Cylinder (Dia: 1.33' x H: 1.25')
IES Classification: Type V - Short - Non-Cutoff
BUG Rating: B4 - U5 - G5


Input Watts (W): 112.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P588382
 CATALOG NUMBER: GAT-CA6-LED-110-730-U-55-5-X-X

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 1.1 fc
 Type V - Short - Non-Cutoff

REPORT NUMBER: P588382
CATALOG NUMBER: GAT-CA6-LED-110-730-U-55-5-X-X

Luminous Intensity Polar Plot



— Vertical Plane Through 0-Deg Lateral - - - Horizontal Cone Through 62.5-Deg Vertical

REPORT NUMBER: P588382
 CATALOG NUMBER: GAT-CA6-LED-110-730-U-55-5-X-X


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	6180.4	938.6	7119.0
	% Fixture	43.4	6.6	50.0
Street Side	Lumens	6180.4	938.6	7119.0
	% Fixture	43.4	6.6	50.0
Total	Lumens	12360.8	1877.3	14238.0
	% Fixture	86.8	13.2	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	11.7	0.1
10°-20°	54.0	0.4
20°-30°	140.3	1.0
30°-40°	315.5	2.2
40°-50°	637.4	4.5
50°-60°	1941.1	13.6
60°-70°	3776.6	26.5
70°-80°	3136.1	22.0
80°-90°	2347.9	16.5
90°-100°	859.9	6.0
100°-110°	323.7	2.3
110°-120°	269.9	1.9
120°-130°	190.1	1.3
130°-140°	123.2	0.9
140°-150°	71.4	0.5
150°-160°	30.8	0.2
160°-170°	7.8	0.1
170°-180°	0.6	0.0
0°-90°	12360.8	86.8
0°-180°	14238.0	100.0

Coefficient of Utilization




REPORT NUMBER: P588382
 CATALOG NUMBER: GAT-CA6-LED-110-730-U-55-5-X-X

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	103.0	0.7			
FM (30°-60°)	1447.0	10.2			
FH (60°-80°)	3456.4	24.3			G2/5000
FVH (80°-90°)	1174.0	8.2			G5
BL (0°-30°)	103.0	0.7	B0/110		
BM (30°-60°)	1447.0	10.2	B2/2500		
BH (60°-80°)	3456.4	24.3	B4/5000		G2/5000
BVH (80°-90°)	1174.0	8.2			G5
UL (90°-100°)	859.9	6.0		U4/1000	
UH (100°-180°)	938.6	6.6		U4/1000	

BUG Rating: B4-U5-G5
 Type V Short





REPORT NUMBER: P588382
CATALOG NUMBER: GAT-CA6-LED-110-730-U-55-5-X-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	94.9
2.5°	96.8
5°	108.2
7.5°	129.1
10°	148.0
12.5°	167.0
15°	186.0
17.5°	205.0
20°	227.7
22.5°	244.8
25°	280.9
27.5°	345.4
30°	409.9
32.5°	453.6
35°	472.6
37.5°	542.8
40°	637.7
42.5°	736.4
45°	831.3
47.5°	892.0
50°	990.7
52.5°	1358.9
55°	2015.6
57.5°	2854.4
60°	3647.8
62.5°	4090.0
65°	3979.9
67.5°	3659.2
70°	3357.4
72.5°	3103.1
75°	2955.0
77.5°	2805.1
80°	2651.4
82.5°	2486.3
85°	2220.5
87.5°	1867.5
90°	1427.2
92.5°	1017.3
95°	707.9
97.5°	512.4
100°	392.9
102.5°	326.4
105°	292.3
107.5°	273.3
110°	267.6



REPORT NUMBER: P588382
CATALOG NUMBER: GAT-CA6-LED-110-730-U-55-5-X-X

CANDELA DISTRIBUTION (continued):

	0°
112.5°	271.4
115°	279.0
117.5°	275.2
120°	256.2
122.5°	227.7
125°	206.9
127.5°	191.7
130°	180.3
132.5°	168.9
135°	159.4
137.5°	148.0
140°	134.8
142.5°	123.4
145°	113.9
147.5°	102.5
150°	87.3
152.5°	75.9
155°	64.5
157.5°	55.0
160°	43.7
162.5°	34.2
165°	24.7
167.5°	17.1
170°	11.4
172.5°	5.7
175°	3.8
177.5°	5.7
180°	5.7

(END OF REPORT)