

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P198085

Luminaire Tested: **TT-C1-LED-E1-RW-PM-SG-LWR-LW-8030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P198085
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P34701)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TT-C1-LED-E1-RW-PM-SG-LWR-LW-8030
Description: TOPTIER LED AREA/SITE LUMINAIRE
RECTANGULAR DISTRIBUTION WITH SOFTENING GLASS LENS AND LumaWatt WIRELESS SENSOR
Light Source: (168) 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2320.8 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Luminous Opening: Circular (Dia: 1.12' x H: 0')
IES Classification: Type III - Short - Full Cutoff
BUG Rating: B1 - U0 - G1

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P198085

CATALOG NUMBER: TT-C1-LED-E1-RW-PM-SG-LWR-LW-8030

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 2.2 fc
 Type III - Short - Full Cutoff

REPORT NUMBER: P198085
CATALOG NUMBER: TT-C1-LED-E1-RW-PM-SG-LWR-LW-8030

Luminous Intensity Polar Plot



— Vertical Plane Through 90-Deg Lateral - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P198085

CATALOG NUMBER: TT-C1-LED-E1-RW-PM-SG-LWR-LW-8030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1160.4	0.0	1160.4
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	1160.4	0.0	1160.4
	% Fixture	50.0	0.0	50.0
Total	Lumens	2320.8	0.0	2320.8
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	13.7	0.6
10°-20°	47.4	2.0
20°-30°	103.5	4.5
30°-40°	208.1	9.0
40°-50°	393.3	16.9
50°-60°	580.2	25.0
60°-70°	571.4	24.6
70°-80°	332.8	14.3
80°-90°	70.4	3.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2320.8	100.0
0°-180°	2320.8	100.0



REPORT NUMBER: P198085


CATALOG NUMBER: TT-C1-LED-E1-RW-PM-SG-LWR-LW-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	82.3	3.5			
FM	(30°-60°)	590.8	25.5			
FH	(60°-80°)	452.1	19.5			G0/660
FVH	(80°-90°)	35.2	1.5			G1/100
BL	(0°-30°)	82.3	3.5	B0/110		
BM	(30°-60°)	590.8	25.5	B1/1000		
BH	(60°-80°)	452.1	19.5	B1/500		G1/500
BVH	(80°-90°)	35.2	1.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type III Short





REPORT NUMBER: P198085

CATALOG NUMBER: TT-C1-LED-E1-RW-PM-SG-LWR-LW-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	137.8	137.8	137.8	137.8	137.8	137.8	137.8	137.8	137.8	137.8	137.8
2.5°	138.9	138.9	138.9	138.9	138.4	138.9	138.4	138.4	138.4	138.4	138.4
5°	140.5	141.1	140.5	140.5	140.5	140.5	140.5	140.5	140.0	140.0	140.5
7.5°	144.3	144.3	144.3	144.3	143.7	144.3	143.7	143.7	143.7	143.7	143.7
10°	149.6	149.6	149.6	149.6	149.1	149.1	149.1	148.6	148.6	148.6	148.6
12.5°	156.1	156.6	156.6	156.1	155.5	155.5	155.0	155.0	155.0	155.0	154.5
15°	165.7	165.2	165.2	164.1	164.1	163.1	163.6	163.1	162.5	162.0	162.5
17.5°	175.4	175.9	175.9	174.9	174.3	173.8	172.7	172.7	172.2	172.7	172.7
20°	190.4	190.4	189.3	188.3	186.7	186.1	185.0	185.0	184.0	185.0	185.0
22.5°	205.4	205.4	204.4	203.8	201.7	200.1	199.5	199.0	198.5	199.5	198.5
25°	224.2	224.2	223.1	221.0	218.8	218.3	216.7	216.7	217.2	217.8	215.6
27.5°	243.5	244.0	243.0	241.4	239.2	237.1	237.1	237.6	238.1	240.3	239.7
30°	267.1	266.6	265.0	262.8	261.7	260.1	260.7	262.8	265.0	267.1	267.1
32.5°	291.2	290.7	290.2	288.0	287.5	286.9	289.6	293.9	298.2	299.8	302.5
35°	317.0	317.0	316.4	314.8	315.9	318.6	322.9	330.9	337.4	344.9	344.9
37.5°	345.4	344.3	344.9	344.9	347.6	352.4	362.6	378.1	391.5	399.0	399.0
40°	374.9	373.3	373.8	376.5	381.3	393.1	410.8	432.3	453.8	463.4	466.6
42.5°	403.3	401.7	403.9	406.6	418.4	436.6	462.9	495.6	526.2	541.2	540.6
45°	429.6	430.7	433.4	439.8	457.0	483.8	521.3	565.3	605.0	622.7	629.1
47.5°	455.9	456.4	460.2	471.5	495.6	529.4	575.0	633.4	677.4	698.3	706.4
50°	480.6	481.6	488.1	504.2	532.6	573.4	629.7	691.9	740.2	764.8	771.8
52.5°	502.6	503.6	511.1	531.0	564.8	612.0	671.0	734.8	785.8	814.2	818.5
55°	520.8	521.9	529.4	550.3	586.8	635.6	695.6	758.9	806.7	831.9	835.1
57.5°	531.5	532.1	540.1	561.6	597.5	643.1	701.0	762.2	804.0	826.5	829.2
60°	532.1	533.1	540.6	560.0	593.2	635.0	690.3	745.0	783.1	803.5	806.7
62.5°	522.4	522.9	529.4	544.4	572.8	609.3	660.2	709.6	743.9	763.8	767.5
65°	500.4	500.4	503.6	514.9	536.9	568.0	611.4	657.0	688.7	706.9	709.1
67.5°	463.9	463.9	464.5	472.0	487.0	511.7	548.7	586.8	615.2	633.4	636.1
70°	417.3	416.7	412.5	417.3	426.9	447.9	480.6	509.5	532.6	547.1	556.7
72.5°	358.3	356.1	352.9	351.8	361.5	379.7	406.6	426.4	439.3	454.8	455.9
75°	289.6	288.6	284.3	284.3	293.9	308.4	329.9	343.3	349.7	359.9	362.0
77.5°	216.1	215.6	217.2	217.8	223.1	238.7	251.0	260.7	259.1	265.5	267.6
80°	151.3	152.3	152.3	151.8	157.2	163.1	176.5	179.1	177.0	179.1	179.1
82.5°	96.0	95.5	94.4	96.0	100.3	105.1	110.5	111.0	112.6	111.0	112.1
85°	48.3	47.7	48.8	49.3	51.5	54.2	59.0	60.1	57.4	57.4	56.3
87.5°	16.6	17.7	16.6	17.2	17.2	19.8	19.3	19.3	19.3	19.3	20.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)