

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P198086

Luminaire Tested: **TT-C1-LED-E1-RW-PM-SG-LWR-LW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P198086  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P34701)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TT-C1-LED-E1-RW-PM-SG-LWR-LW  
Description: TOPTIER LED AREA/SITE LUMINAIRE  
RECTANGULAR DISTRIBUTION WITH SOFTENING GLASS LENS AND LumaWatt WIRELESS  
SENSOR  
Light Source: (168) 4000K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2711.6 lumens  
Efficiency: N/A  
Efficacy: 96.8 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type III - Short - Full Cutoff  
BUG Rating: B2 - U0 - G2

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT




REPORT NUMBER: P198086

CATALOG NUMBER: TT-C1-LED-E1-RW-PM-SG-LWR-LW

### Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd  
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 2.6 fc  
 Type III - Short - Full Cutoff

REPORT NUMBER: P198086

CATALOG NUMBER: TT-C1-LED-E1-RW-PM-SG-LWR-LW

### Luminous Intensity Polar Plot



— Vertical Plane Through 90-Deg Lateral    - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P198086

CATALOG NUMBER: TT-C1-LED-E1-RW-PM-SG-LWR-LW


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1355.8	0.0	1355.8
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	1355.8	0.0	1355.8
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	2711.6	0.0	2711.6
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	16.0	0.6
10°-20°	55.4	2.0
20°-30°	120.9	4.5
30°-40°	243.1	9.0
40°-50°	459.5	16.9
50°-60°	677.8	25.0
60°-70°	667.7	24.6
70°-80°	388.8	14.3
80°-90°	82.3	3.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2711.6	100.0
0°-180°	2711.6	100.0



REPORT NUMBER: P198086


CATALOG NUMBER: TT-C1-LED-E1-RW-PM-SG-LWR-LW

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	96.1	3.5			
FM	(30°-60°)	690.3	25.5			
FH	(60°-80°)	528.2	19.5			G0/660
FVH	(80°-90°)	41.2	1.5			G1/100
BL	(0°-30°)	96.1	3.5	B0/110		
BM	(30°-60°)	690.3	25.5	B1/1000		
BH	(60°-80°)	528.2	19.5	B2/1000		G2/1000
BVH	(80°-90°)	41.2	1.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G2**

Type III Short





REPORT NUMBER: P198086

CATALOG NUMBER: TT-C1-LED-E1-RW-PM-SG-LWR-LW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	161.1	161.1	161.1	161.1	161.1	161.1	161.1	161.1	161.1	161.1	161.1
2.5°	162.3	162.3	162.3	162.3	161.7	162.3	161.7	161.7	161.7	161.7	161.7
5°	164.2	164.8	164.2	164.2	164.2	164.2	164.2	164.2	163.6	163.6	164.2
7.5°	168.6	168.6	168.6	168.6	167.9	168.6	167.9	167.9	167.9	167.9	167.9
10°	174.8	174.8	174.8	174.8	174.2	174.2	174.2	173.6	173.6	173.6	173.6
12.5°	182.4	183.0	183.0	182.4	181.7	181.7	181.1	181.1	181.1	181.1	180.5
15°	193.6	193.0	193.0	191.8	191.8	190.5	191.1	190.5	189.9	189.3	189.9
17.5°	204.9	205.5	205.5	204.3	203.7	203.0	201.8	201.8	201.2	201.8	201.8
20°	222.5	222.5	221.2	220.0	218.1	217.5	216.2	216.2	214.9	216.2	216.2
22.5°	240.0	240.0	238.8	238.1	235.6	233.7	233.1	232.5	231.9	233.1	231.9
25°	261.9	261.9	260.7	258.2	255.7	255.1	253.2	253.2	253.8	254.4	251.9
27.5°	284.5	285.1	283.9	282.0	279.5	277.0	277.0	277.6	278.2	280.7	280.1
30°	312.1	311.5	309.6	307.1	305.8	303.9	304.6	307.1	309.6	312.1	312.1
32.5°	340.3	339.7	339.0	336.5	335.9	335.3	338.4	343.4	348.4	350.3	353.4
35°	370.4	370.4	369.7	367.9	369.1	372.2	377.3	386.7	394.2	402.9	402.9
37.5°	403.6	402.3	402.9	402.9	406.1	411.7	423.6	441.8	457.5	466.2	466.2
40°	438.0	436.2	436.8	439.9	445.6	459.3	480.0	505.1	530.2	541.4	545.2
42.5°	471.3	469.4	471.9	475.0	488.8	510.1	540.8	579.0	614.8	632.3	631.7
45°	502.0	503.2	506.3	513.9	533.9	565.3	609.1	660.5	706.9	727.6	735.1
47.5°	532.7	533.3	537.7	550.8	579.0	618.5	671.8	740.1	791.5	815.9	825.3
50°	561.5	562.7	570.3	589.1	622.3	669.9	735.7	808.4	864.8	893.6	901.8
52.5°	587.2	588.4	597.2	620.4	659.9	715.0	784.0	858.5	918.1	951.3	956.3
55°	608.5	609.7	618.5	643.0	685.6	742.6	812.8	886.7	942.5	972.0	975.7
57.5°	621.0	621.7	631.0	656.1	698.1	751.4	819.0	890.5	939.4	965.7	968.8
60°	621.7	622.9	631.7	654.2	693.1	742.0	806.5	870.4	914.9	938.7	942.5
62.5°	610.4	611.0	618.5	636.1	669.3	711.9	771.4	829.1	869.2	892.4	896.8
65°	584.7	584.7	588.4	601.6	627.3	663.6	714.4	767.7	804.6	825.9	828.4
67.5°	542.1	542.1	542.7	551.5	569.0	597.8	641.1	685.6	718.8	740.1	743.2
70°	487.5	486.9	481.9	487.5	498.8	523.3	561.5	595.3	622.3	639.2	650.5
72.5°	418.6	416.1	412.3	411.1	422.4	443.7	475.0	498.2	513.2	531.4	532.7
75°	338.4	337.1	332.1	332.1	343.4	360.3	385.4	401.1	408.6	420.5	423.0
77.5°	252.5	251.9	253.8	254.4	260.7	278.9	293.3	304.6	302.7	310.2	312.7
80°	176.7	178.0	178.0	177.3	183.6	190.5	206.2	209.3	206.8	209.3	209.3
82.5°	112.2	111.5	110.3	112.2	117.2	122.8	129.1	129.7	131.6	129.7	131.0
85°	56.4	55.8	57.0	57.7	60.2	63.3	68.9	70.2	67.1	67.1	65.8
87.5°	19.4	20.7	19.4	20.1	20.1	23.2	22.6	22.6	22.6	22.6	23.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)