

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P197929

Luminaire Tested: **TT-C4-LED-E1-5WQ-PM-SG-8030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P197929
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P115543)
Test Lab: INNOVATION CENTER P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TT-C4-LED-E1-5WQ-PM-SG-8030
Description: TOPTIER LED AREA/SITE LUMINAIRE
WIDE DISTRIBUTION WITH SOFTENING GLASS LENS
Light Source: (160) 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4883.9 lumens
Efficiency: N/A
Efficacy: 84.2 lumens/watt
Luminous Opening: Circular (Dia: 1.12' x H: 0')
IES Classification: Type V - Short - Full Cutoff
BUG Rating: B2 - U0 - G1


Input Watts (W): 58
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



REPORT NUMBER: P197929
 CATALOG NUMBER: TT-C4-LED-E1-5WQ-PM-SG-8030

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 5 fc
 Type V - Short - Full Cutoff

REPORT NUMBER: P197929
CATALOG NUMBER: TT-C4-LED-E1-5WQ-PM-SG-8030

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P197929

CATALOG NUMBER: TT-C4-LED-E1-5WQ-PM-SG-8030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2442.0	0.0	2442.0
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	2442.0	0.0	2442.0
	% Fixture	50.0	0.0	50.0
Total	Lumens	4883.9	0.0	4883.9
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.7	0.9
10°-20°	151.6	3.1
20°-30°	308.7	6.3
30°-40°	563.8	11.5
40°-50°	957.3	19.6
50°-60°	1246.7	25.5
60°-70°	1008.3	20.6
70°-80°	495.5	10.1
80°-90°	107.2	2.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4883.9	100.0
0°-180°	4883.9	100.0



REPORT NUMBER: P197929


CATALOG NUMBER: TT-C4-LED-E1-5WQ-PM-SG-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	252.5	5.2			
FM	(30°-60°)	1383.9	28.3			
FH	(60°-80°)	751.9	15.4			G1/1800
FVH	(80°-90°)	53.6	1.1			G1/100
BL	(0°-30°)	252.5	5.2	B1/500		
BM	(30°-60°)	1383.9	28.3	B2/2500		
BH	(60°-80°)	751.9	15.4	B2/1000		G1/1800
BVH	(80°-90°)	53.6	1.1			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G1

Type V Short





REPORT NUMBER: P197929

CATALOG NUMBER: TT-C4-LED-E1-5WQ-PM-SG-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	452.5	452.5	452.5	452.5	452.5	452.5	452.5	452.5	452.5	452.5	452.5
2.5°	454.5	454.5	454.5	454.5	454.5	454.5	455.5	455.5	455.5	455.5	455.5
5°	460.5	460.5	460.5	461.5	461.5	461.5	461.5	461.5	461.5	461.5	461.5
7.5°	469.5	468.5	469.5	469.5	469.5	470.5	470.5	469.5	470.5	470.5	470.5
10°	482.5	481.5	482.5	482.5	482.5	483.5	483.5	483.5	483.5	484.5	484.5
12.5°	501.5	500.5	501.5	502.5	501.5	502.5	502.5	502.5	502.5	502.5	502.5
15°	525.5	524.5	525.5	526.5	525.5	527.5	527.5	526.5	526.5	527.5	527.5
17.5°	554.4	552.4	553.4	554.4	554.4	556.4	556.4	555.4	556.4	557.4	556.4
20°	584.4	582.4	583.4	586.4	586.4	587.4	589.4	588.4	589.4	590.4	589.4
22.5°	617.4	616.4	617.4	620.4	620.4	621.4	624.4	624.4	624.4	625.4	624.4
25°	653.3	652.3	653.3	656.3	656.3	658.3	662.3	662.3	663.3	664.3	663.3
27.5°	695.3	694.3	696.3	699.3	700.3	703.3	708.3	709.3	710.3	711.3	709.3
30°	744.2	742.2	745.2	750.2	752.2	756.2	762.2	764.2	765.2	768.2	766.2
32.5°	800.2	798.2	802.2	808.2	811.2	817.2	825.2	827.2	830.2	832.2	829.2
35°	866.1	865.1	869.1	878.1	883.1	890.1	901.1	904.1	906.1	910.1	906.1
37.5°	939.0	938.0	945.0	955.0	964.0	975.0	987.0	992.0	995.0	1000.0	995.0
40°	1020.0	1019.0	1028.0	1039.9	1050.9	1064.9	1079.9	1086.9	1092.9	1097.9	1091.9
42.5°	1102.9	1102.9	1113.9	1126.9	1142.8	1159.8	1176.8	1184.8	1194.8	1197.8	1190.8
45°	1182.8	1183.8	1194.8	1210.8	1233.7	1255.7	1274.7	1284.7	1295.7	1298.7	1289.7
47.5°	1258.7	1259.7	1269.7	1290.7	1316.7	1341.6	1364.6	1378.6	1389.6	1390.6	1383.6
50°	1320.7	1324.7	1337.6	1356.6	1383.6	1409.6	1437.5	1455.5	1466.5	1469.5	1462.5
52.5°	1344.6	1351.6	1366.6	1390.6	1421.6	1448.5	1479.5	1502.5	1515.5	1520.5	1514.5
55°	1322.7	1330.7	1348.6	1375.6	1409.6	1443.5	1475.5	1502.5	1520.5	1527.5	1521.5
57.5°	1273.7	1274.7	1292.7	1319.7	1350.6	1385.6	1416.6	1441.5	1458.5	1465.5	1464.5
60°	1188.8	1188.8	1205.8	1231.8	1255.7	1291.7	1317.7	1336.6	1348.6	1356.6	1354.6
62.5°	1074.9	1074.9	1089.9	1116.9	1140.8	1171.8	1196.8	1216.8	1224.8	1233.7	1235.7
65°	948.0	948.0	962.0	989.0	1011.0	1038.9	1062.9	1081.9	1089.9	1100.9	1098.9
67.5°	813.2	812.2	825.2	848.1	869.1	895.1	918.1	936.1	945.0	958.0	949.0
70°	674.3	674.3	685.3	703.3	718.3	744.2	766.2	784.2	791.2	802.2	797.2
72.5°	542.5	541.5	550.4	564.4	576.4	599.4	612.4	632.4	638.4	653.3	645.3
75°	423.6	421.6	428.6	438.6	446.5	461.5	471.5	487.5	492.5	502.5	498.5
77.5°	318.7	317.7	320.7	327.7	333.7	345.6	349.6	357.6	361.6	371.6	363.6
80°	228.8	225.8	228.8	232.8	234.8	243.8	244.8	247.7	249.7	256.7	248.7
82.5°	153.8	149.8	151.8	154.8	154.8	159.8	160.8	159.8	163.8	165.8	161.8
85°	87.9	84.9	85.9	87.9	86.9	89.9	89.9	88.9	91.9	91.9	89.9
87.5°	29.0	27.0	28.0	29.0	29.0	30.0	31.0	30.0	32.0	32.0	30.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P197929

CATALOG NUMBER: TT-C4-LED-E1-5WQ-PM-SG-8030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	452.5	452.5	452.5	452.5	452.5	452.5	452.5	452.5
2.5°	455.5	455.5	455.5	455.5	455.5	455.5	455.5	455.5
5°	461.5	461.5	461.5	461.5	461.5	460.5	460.5	460.5
7.5°	470.5	470.5	470.5	470.5	470.5	469.5	469.5	469.5
10°	484.5	483.5	483.5	483.5	483.5	482.5	483.5	482.5
12.5°	502.5	503.5	503.5	502.5	503.5	501.5	501.5	501.5
15°	527.5	526.5	526.5	526.5	526.5	525.5	525.5	525.5
17.5°	555.4	555.4	554.4	554.4	553.4	552.4	552.4	552.4
20°	588.4	587.4	586.4	585.4	584.4	582.4	581.4	581.4
22.5°	622.4	621.4	620.4	619.4	618.4	616.4	614.4	614.4
25°	660.3	658.3	657.3	655.3	653.3	651.3	650.3	649.3
27.5°	706.3	704.3	701.3	698.3	694.3	693.3	691.3	691.3
30°	761.2	758.2	754.2	749.2	745.2	741.2	739.3	738.3
32.5°	825.2	821.2	814.2	808.2	801.2	797.2	794.2	792.2
35°	900.1	894.1	886.1	877.1	868.1	861.1	856.1	856.1
37.5°	988.0	979.0	967.0	956.0	943.0	935.1	929.1	925.1
40°	1083.9	1070.9	1055.9	1041.9	1027.0	1016.0	1007.0	1008.0
42.5°	1178.8	1167.8	1149.8	1132.9	1113.9	1098.9	1087.9	1086.9
45°	1278.7	1264.7	1242.7	1220.8	1198.8	1180.8	1167.8	1165.8
47.5°	1371.6	1356.6	1330.7	1303.7	1279.7	1259.7	1245.7	1243.7
50°	1447.5	1429.6	1402.6	1373.6	1347.6	1325.7	1310.7	1306.7
52.5°	1496.5	1476.5	1447.5	1412.6	1384.6	1359.6	1341.6	1336.6
55°	1504.5	1478.5	1447.5	1408.6	1377.6	1349.6	1329.7	1323.7
57.5°	1449.5	1421.6	1393.6	1359.6	1328.7	1298.7	1282.7	1274.7
60°	1342.6	1320.7	1297.7	1266.7	1241.7	1213.8	1200.8	1196.8
62.5°	1219.8	1200.8	1179.8	1147.8	1126.9	1101.9	1089.9	1084.9
65°	1087.9	1065.9	1045.9	1020.0	997.0	976.0	959.0	957.0
67.5°	942.0	919.1	902.1	879.1	856.1	836.2	825.2	819.2
70°	788.2	769.2	752.2	727.3	712.3	693.3	685.3	679.3
72.5°	635.4	624.4	603.4	587.4	570.4	555.4	550.4	544.4
75°	491.5	478.5	462.5	452.5	439.6	431.6	427.6	423.6
77.5°	360.6	349.6	340.7	336.7	330.7	322.7	319.7	316.7
80°	249.7	244.8	238.8	237.8	233.8	227.8	226.8	225.8
82.5°	161.8	158.8	156.8	156.8	154.8	150.8	149.8	149.8
85°	89.9	88.9	89.9	88.9	86.9	84.9	84.9	84.9
87.5°	30.0	30.0	31.0	32.0	29.0	29.0	28.0	28.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)