

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P198025

Luminaire Tested: **TT-C4-LED-E1-RW-PM-CG-LWR-LW-8030**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P198025  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P34697)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TT-C4-LED-E1-RW-PM-CG-LWR-LW-8030  
Description: TOPTIER LED AREA/SITE LUMINAIRE  
RECTANGULAR DISTRIBUTION WITH CLEAR GLASS LENS AND LumaWatt WIRELESS  
SENSOR  
Light Source: (160) 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3816 lumens  
Efficiency: N/A  
Efficacy: 65.8 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type IV - Short - Semi-Cutoff  
BUG Rating: B2 - U0 - G2

Input Watts (W): 58  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT




REPORT NUMBER: P198025

CATALOG NUMBER: TT-C4-LED-E1-RW-PM-CG-LWR-LW-8030

### Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 2.9 fc  
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P198025

CATALOG NUMBER: TT-C4-LED-E1-RW-PM-CG-LWR-LW-8030

### Luminous Intensity Polar Plot



— Vertical Plane Through 90-Deg Lateral    - - - Horizontal Cone Through 62.5-Deg Vertical

REPORT NUMBER: P198025

CATALOG NUMBER: TT-C4-LED-E1-RW-PM-CG-LWR-LW-8030


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1908.0	0.0	1908.0
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	1908.0	0.0	1908.0
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	3816.0	0.0	3816.0
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	19.3	0.5
10°-20°	65.7	1.7
20°-30°	140.3	3.7
30°-40°	272.9	7.2
40°-50°	514.6	13.5
50°-60°	879.3	23.0
60°-70°	1058.9	27.7
70°-80°	712.6	18.7
80°-90°	152.4	4.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3816.0	100.0
0°-180°	3816.0	100.0



REPORT NUMBER: P198025


CATALOG NUMBER: TT-C4-LED-E1-RW-PM-CG-LWR-LW-8030

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	112.6	3.0			
FM	(30°-60°)	833.4	21.8			
FH	(60°-80°)	885.7	23.2			G1/1800
FVH	(80°-90°)	76.2	2.0			G1/100
BL	(0°-30°)	112.6	3.0	B1/500		
BM	(30°-60°)	833.4	21.8	B1/1000		
BH	(60°-80°)	885.7	23.2	B2/1000		G2/1000
BVH	(80°-90°)	76.2	2.0			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G2**

Type IV Short





REPORT NUMBER: P198025

CATALOG NUMBER: TT-C4-LED-E1-RW-PM-CG-LWR-LW-8030

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	192.9	192.9	192.9	192.9	192.9	192.9	192.9	192.9	192.9	192.9	192.9
2.5°	194.7	194.7	194.7	194.7	194.7	194.7	195.6	195.6	195.6	195.6	195.6
5°	197.4	197.4	198.3	198.3	199.2	199.2	199.2	199.2	198.3	198.3	198.3
7.5°	201.9	201.9	202.8	203.7	203.7	202.8	202.8	201.9	201.9	201.9	201.9
10°	209.0	209.0	209.9	209.9	209.0	209.0	209.0	208.1	208.1	208.1	208.1
12.5°	217.1	218.0	218.8	218.0	217.1	216.2	216.2	215.3	215.3	215.3	215.3
15°	228.7	230.5	229.6	229.6	228.7	226.9	226.0	225.1	225.1	225.1	225.1
17.5°	246.5	246.5	243.9	242.1	240.3	239.4	238.5	237.6	237.6	237.6	237.6
20°	265.3	264.4	261.7	259.0	256.4	255.5	252.8	251.9	252.8	251.9	251.9
22.5°	287.6	286.7	283.2	280.5	276.9	273.3	272.4	269.8	268.9	268.0	268.9
25°	310.0	310.9	308.2	305.5	300.1	296.6	293.0	291.2	289.4	288.5	288.5
27.5°	335.9	337.7	335.9	330.5	325.1	322.5	317.1	315.3	314.4	315.3	315.3
30°	363.6	364.4	361.8	359.1	353.7	347.5	343.9	344.8	344.8	347.5	346.6
32.5°	397.5	396.6	393.0	391.2	385.9	380.5	378.7	379.6	383.2	385.0	385.0
35°	435.0	432.3	428.8	425.2	420.7	417.2	418.0	425.2	435.9	438.6	440.4
37.5°	472.5	468.1	468.1	462.7	459.1	461.8	467.2	480.6	488.6	501.1	498.4
40°	507.4	508.3	506.5	502.0	501.1	510.0	521.7	538.6	559.2	571.7	570.8
42.5°	539.5	547.6	542.2	543.1	547.6	561.9	580.6	613.7	654.8	670.8	670.8
45°	575.3	585.1	580.6	583.3	595.8	618.1	658.3	723.5	779.8	818.2	818.2
47.5°	611.9	620.8	619.0	624.4	646.7	686.0	747.7	828.9	885.2	922.7	928.1
50°	658.3	654.8	655.7	669.0	707.5	764.6	843.2	923.6	1016.5	1038.9	1049.6
52.5°	698.5	687.8	694.1	716.4	771.8	838.8	936.1	1078.2	1206.8	1296.1	1303.3
55°	731.6	723.5	736.0	767.3	838.8	927.2	1054.0	1228.2	1334.5	1389.0	1398.8
57.5°	760.2	756.6	777.1	817.3	908.4	1016.5	1145.2	1286.3	1360.4	1402.4	1409.6
60°	786.1	788.7	811.1	864.7	962.9	1062.1	1165.7	1284.5	1358.6	1391.7	1398.8
62.5°	806.6	811.1	840.6	895.9	980.8	1060.3	1160.3	1297.0	1393.5	1445.3	1450.6
65°	820.0	824.5	857.5	895.9	975.4	1052.3	1193.4	1309.5	1381.0	1433.7	1443.5
67.5°	821.8	828.0	847.7	879.9	946.9	1014.7	1136.2	1220.2	1277.4	1309.5	1318.4
70°	811.1	809.3	816.4	829.8	870.0	916.5	1019.2	1081.7	1122.8	1155.9	1163.9
72.5°	770.0	767.3	750.3	735.2	750.3	787.0	875.4	917.4	945.1	971.9	977.2
75°	691.4	678.9	636.9	615.5	611.0	643.1	711.0	737.8	748.5	778.9	782.5
77.5°	552.9	547.6	511.8	474.3	470.7	490.4	542.2	553.8	544.9	577.9	587.8
80°	403.8	396.6	362.7	335.0	327.8	341.2	371.6	374.3	368.0	384.1	384.1
82.5°	258.2	251.0	236.7	216.2	201.0	209.0	232.2	232.2	232.2	236.7	239.4
85°	133.1	130.4	119.7	109.9	104.5	106.3	114.3	115.2	119.7	122.4	118.8
87.5°	37.5	39.3	37.5	33.1	32.2	31.3	34.8	35.7	38.4	40.2	42.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)