

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P197977

Luminaire Tested: **TT-C4-LED-E1-RW-PM-MS/DIM-8030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P197977
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P34692)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TT-C4-LED-E1-RW-PM-MS/DIM-8030
Description: TOPTIER LED AREA/SITE LUMINAIRE
RECTANGULAR DISTRIBUTION WITH DIMMING OCCUPANCY SENSOR
Light Source: (160) 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4243.9 lumens
Efficiency: N/A
Efficacy: 73.2 lumens/watt
Luminous Opening: Circular (Dia: 1.12' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B3 - U0 - G3

Input Watts (W): 58
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P197977

CATALOG NUMBER: TT-C4-LED-E1-RW-PM-MS/DIM-8030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 2.8 fc
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P197977

CATALOG NUMBER: TT-C4-LED-E1-RW-PM-MS/DIM-8030

Luminous Intensity Polar Plot



— Vertical Plane Through 88-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P197977

CATALOG NUMBER: TT-C4-LED-E1-RW-PM-MS/DIM-8030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2122.0	0.0	2122.0
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	2122.0	0.0	2122.0
	% Fixture	50.0	0.0	50.0
Total	Lumens	4243.9	0.0	4243.9
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.8	0.5
10°-20°	67.6	1.6
20°-30°	143.7	3.4
30°-40°	274.5	6.5
40°-50°	504.6	11.9
50°-60°	873.9	20.6
60°-70°	1136.9	26.8
70°-80°	931.7	22.0
80°-90°	291.3	6.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4243.9	100.0
0°-180°	4243.9	100.0



REPORT NUMBER: P197977


CATALOG NUMBER: TT-C4-LED-E1-RW-PM-MS/DIM-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	115.6	2.7			
FM	(30°-60°)	826.5	19.5			
FH	(60°-80°)	1034.3	24.4			G1/1800
FVH	(80°-90°)	145.6	3.4			G2/225
BL	(0°-30°)	115.6	2.7	B1/500		
BM	(30°-60°)	826.5	19.5	B1/1000		
BH	(60°-80°)	1034.3	24.4	B3/2500		G3/2500
BVH	(80°-90°)	145.6	3.4			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3

Type IV Short





REPORT NUMBER: P197977

CATALOG NUMBER: TT-C4-LED-E1-RW-PM-MS/DIM-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	88°
0°	198.3	198.3	198.3	198.3	198.3	198.3	198.3	198.3	198.3	198.3	198.3
2.5°	200.1	200.1	200.1	200.1	200.1	200.1	200.1	200.1	200.1	200.1	200.1
5°	203.7	203.7	203.7	204.6	204.6	204.6	204.6	204.6	203.7	203.7	203.7
7.5°	208.1	208.1	209.0	209.0	209.0	209.0	208.1	208.1	207.2	207.2	207.2
10°	215.3	215.3	216.2	216.2	215.3	214.4	214.4	214.4	213.5	213.5	213.5
12.5°	225.1	225.1	226.0	225.1	224.2	223.3	223.3	222.4	221.5	221.5	221.5
15°	238.5	238.5	237.6	235.8	234.0	234.0	231.4	231.4	231.4	231.4	230.5
17.5°	256.4	255.5	251.9	251.0	248.3	246.5	244.8	243.9	243.0	243.0	243.9
20°	276.0	274.2	269.8	269.8	265.3	262.6	260.8	259.0	259.0	258.2	257.3
22.5°	299.2	297.5	292.1	290.3	285.8	281.4	279.6	275.1	274.2	274.2	275.1
25°	322.5	323.4	318.9	315.3	309.1	304.6	298.3	295.7	293.0	293.0	291.2
27.5°	349.3	350.2	344.8	340.3	335.0	326.0	322.5	318.9	316.2	318.0	316.2
30°	377.8	379.6	375.2	369.8	361.8	352.8	348.4	347.5	344.8	346.6	345.7
32.5°	410.9	410.0	407.3	402.0	391.2	384.1	380.5	379.6	381.4	382.3	381.4
35°	449.3	445.7	443.1	435.0	425.2	419.8	416.3	419.8	427.9	433.2	431.4
37.5°	489.5	484.1	481.5	472.5	463.6	460.9	465.4	472.5	480.6	487.7	487.7
40°	522.6	524.3	518.1	510.0	502.9	505.6	513.6	526.1	542.2	549.4	548.5
42.5°	555.6	561.0	554.7	546.7	547.6	555.6	567.2	590.4	626.2	636.9	636.0
45°	585.1	596.7	591.3	586.0	594.0	607.4	638.7	690.5	739.6	776.2	778.9
47.5°	623.5	629.7	627.1	627.1	639.6	670.8	718.2	790.5	842.3	877.2	882.5
50°	667.3	661.0	661.9	669.9	701.2	747.7	812.0	879.9	972.8	988.8	993.3
52.5°	703.9	693.2	699.4	714.6	760.2	819.1	899.5	1038.9	1157.7	1264.9	1280.0
55°	741.4	728.9	741.4	765.5	832.5	914.7	1032.6	1194.3	1319.3	1386.3	1394.4
57.5°	770.0	768.2	786.1	820.9	903.1	1013.0	1146.0	1284.5	1368.5	1415.8	1423.0
60°	805.7	807.5	828.0	874.5	972.8	1078.2	1177.3	1304.2	1387.2	1414.9	1423.0
62.5°	839.7	846.8	870.9	923.6	1009.4	1089.8	1185.4	1339.0	1444.4	1504.2	1498.9
65°	871.8	879.0	907.5	943.3	1021.9	1110.3	1270.2	1409.6	1502.5	1568.6	1575.7
67.5°	904.0	912.9	924.5	953.1	1029.0	1112.1	1250.6	1367.6	1442.6	1488.2	1490.8
70°	931.7	930.8	928.1	936.1	983.5	1047.8	1176.4	1269.3	1339.9	1377.4	1386.3
72.5°	935.2	932.6	901.3	878.1	893.3	944.2	1067.4	1141.6	1195.2	1226.4	1232.7
75°	905.8	890.6	828.9	778.9	776.2	827.2	930.8	984.4	1016.5	1056.7	1059.4
77.5°	810.2	793.2	724.4	656.5	656.5	689.6	776.2	804.8	845.0	875.4	883.4
80°	653.0	651.2	579.7	526.1	506.5	534.2	604.7	615.5	645.8	671.7	679.8
82.5°	472.5	459.1	419.8	374.3	358.2	376.1	424.3	435.0	446.6	469.9	479.7
85°	285.8	286.7	259.9	234.0	213.5	219.7	257.3	272.4	287.6	302.8	308.2
87.5°	102.7	118.8	92.9	82.2	71.5	67.9	79.5	98.3	115.2	136.7	148.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P197977

CATALOG NUMBER: TT-C4-LED-E1-RW-PM-MS/DIM-8030

CANDELA DISTRIBUTION (continued):

	90°
0°	198.3
2.5°	200.1
5°	202.8
7.5°	207.2
10°	213.5
12.5°	221.5
15°	230.5
17.5°	242.1
20°	257.3
22.5°	273.3
25°	292.1
27.5°	318.0
30°	344.8
32.5°	381.4
35°	435.9
37.5°	487.7
40°	551.1
42.5°	639.6
45°	782.5
47.5°	881.6
50°	1001.3
52.5°	1267.5
55°	1397.1
57.5°	1424.7
60°	1423.0
62.5°	1513.2
65°	1574.8
67.5°	1492.6
70°	1389.9
72.5°	1230.0
75°	1065.7
77.5°	887.9
80°	683.3
82.5°	476.1
85°	320.7
87.5°	132.2
90°	0.0

(END OF REPORT)