

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P558683 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **GFLD-SA2C-940-U-WR-XX**

Issue Date: 7/20/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P558683 (CONVERTED FROM TYPE C PHOTOMETRY)  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2101-125-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 7/20/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: GFLD-SA2C-940-U-WR-XX  
Description: GALLEON FLOOD, TWO LIGHT SQAURE, WIDE SYMMETRICAL ROUND N6  
Light Source: (32) 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


|                   |                                      |                      |                 |
|-------------------|--------------------------------------|----------------------|-----------------|
| Lumens per Lamp:  | N/A                                  | NEMA Type:           | 6H x 6V         |
| Luminaire Lumens: | 9064.8 lumens                        | Max Intensity:       | 6697.7 candela  |
| Efficiency:       | N/A                                  | Max Intensity Angle: | 0°H x 2.5°V     |
| Efficacy:         | 109.2 lumens/watt                    |                      |                 |
| Luminous Opening: | Rectangular (W 1' x L: 0.5' x H: 0') |                      |                 |
| Beam Angle (50%): | 68°H x 68.7°V                        | Field Angle (10%):   | 114°H x 113.4°V |
| Beam Lumens:      | 5435 lumens                          | Field Lumens:        | 8659.3 lumens   |
| Beam Efficiency:  | 60.0%                                | Field Efficiency:    | 95.5%           |

Input Watts (W): 83  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



REPORT NUMBER: P558683 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: GFLD-SA2C-940-U-WR-XX


### Iso-Candela Plot






REPORT NUMBER: P558683 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: GFLD-SA2C-940-U-WR-XX

### Lumen Table



REPORT NUMBER: P558683 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: GFLD-SA2C-940-U-WR-XX


### Luminous Intensity Polar Plot



— Vertical Distribution Through 0-Deg      - - - Horizontal Distribution Through 2.5-Deg

REPORT NUMBER: P558683 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: GFLD-SA2C-940-U-WR-XX

### Luminous Intensity Plot



**Beam:**  
H Angle: 68°  
V Angle: 68.7°  
Lumens: 5435  
Efficiency: 60.0%

**Field:**  
H Angle: 114°  
V Angle: 113.4°  
Lumens: 8659.3  
Efficiency: 95.5%

**Spill:**  
Lumens: 405.5  
Efficiency: 4.5%

- Vertical Distribution through 0-Deg
- - Horizontal Distribution through 2.5-Deg



REPORT NUMBER: P558683 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: GFLD-SA2C-940-U-WR-XX

FIELD  
 BEAM

**CANDELA DISTRIBUTION:**

|        | -90° | -87.5° | -85° | -82.5° | -80° | -77.5° | -75° | -72.5° | -70°  | -67.5° | -65°  |
|--------|------|--------|------|--------|------|--------|------|--------|-------|--------|-------|
| 90°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 87.5°  | 0.0  | 0.1    | 0.2  | 0.3    | 0.5  | 0.6    | 0.7  | 0.8    | 0.9   | 1.0    | 1.1   |
| 85°    | 0.0  | 0.2    | 0.5  | 0.7    | 0.9  | 1.1    | 1.3  | 1.6    | 1.8   | 2.0    | 2.2   |
| 82.5°  | 0.0  | 0.3    | 0.7  | 1.0    | 1.4  | 1.7    | 2.0  | 2.3    | 2.8   | 3.8    | 4.9   |
| 80°    | 0.0  | 0.5    | 0.9  | 1.4    | 1.8  | 2.2    | 2.8  | 4.2    | 5.5   | 7.0    | 8.5   |
| 77.5°  | 0.0  | 0.6    | 1.1  | 1.7    | 2.2  | 3.1    | 4.7  | 6.5    | 8.3   | 10.1   | 12.6  |
| 75°    | 0.0  | 0.7    | 1.3  | 2.0    | 2.8  | 4.4    | 6.6  | 8.8    | 11.2  | 14.9   | 18.6  |
| 72.5°  | 0.0  | 0.8    | 1.6  | 2.3    | 3.7  | 5.7    | 8.4  | 11.6   | 16.0  | 20.3   | 24.6  |
| 70°    | 0.0  | 0.9    | 1.8  | 2.7    | 4.5  | 7.0    | 10.4 | 15.7   | 20.7  | 25.7   | 32.7  |
| 67.5°  | 0.0  | 1.0    | 2.0  | 3.2    | 5.3  | 8.2    | 13.5 | 19.9   | 25.4  | 32.8   | 41.1  |
| 65°    | 0.0  | 1.1    | 2.2  | 3.7    | 6.1  | 9.8    | 16.5 | 23.9   | 31.2  | 39.7   | 49.1  |
| 62.5°  | 0.0  | 1.2    | 2.4  | 4.2    | 6.9  | 11.8   | 19.3 | 28.3   | 36.7  | 46.4   | 56.7  |
| 60°    | 0.0  | 1.3    | 2.6  | 4.6    | 7.5  | 13.6   | 21.8 | 32.6   | 41.9  | 53.7   | 64.4  |
| 57.5°  | 0.0  | 1.4    | 2.9  | 5.0    | 8.6  | 15.2   | 24.4 | 36.5   | 48.3  | 61.0   | 70.8  |
| 55°    | 0.0  | 1.5    | 3.1  | 5.4    | 9.6  | 16.6   | 26.6 | 39.5   | 55.0  | 67.8   | 76.6  |
| 52.5°  | 0.0  | 1.6    | 3.3  | 5.7    | 10.4 | 17.9   | 28.5 | 44.0   | 61.7  | 73.2   | 82.4  |
| 50°    | 0.0  | 1.7    | 3.6  | 6.0    | 11.2 | 19.1   | 30.2 | 48.2   | 67.8  | 78.5   | 88.5  |
| 47.5°  | 0.0  | 1.8    | 3.8  | 6.3    | 11.8 | 20.0   | 31.7 | 51.8   | 72.5  | 83.8   | 94.3  |
| 45°    | 0.0  | 1.8    | 4.0  | 6.7    | 12.2 | 20.7   | 34.2 | 54.9   | 74.6  | 88.6   | 99.7  |
| 42.5°  | 0.0  | 1.9    | 4.2  | 7.0    | 12.6 | 21.2   | 36.4 | 56.6   | 75.9  | 93.0   | 105.6 |
| 40°    | 0.0  | 2.0    | 4.4  | 7.3    | 12.8 | 21.4   | 38.1 | 57.3   | 76.7  | 96.7   | 111.5 |
| 37.5°  | 0.0  | 2.1    | 4.6  | 7.6    | 12.9 | 21.4   | 39.4 | 57.5   | 77.5  | 98.3   | 117.1 |
| 35°    | 0.0  | 2.1    | 4.8  | 8.0    | 12.9 | 21.9   | 40.2 | 57.2   | 78.3  | 101.9  | 122.8 |
| 32.5°  | 0.0  | 2.2    | 4.9  | 8.3    | 12.7 | 22.5   | 40.4 | 56.4   | 79.1  | 106.5  | 128.4 |
| 30°    | 0.0  | 2.3    | 5.1  | 8.6    | 12.4 | 22.8   | 39.7 | 55.6   | 79.9  | 112.0  | 133.8 |
| 27.5°  | 0.0  | 2.3    | 5.2  | 8.8    | 12.7 | 22.8   | 38.6 | 55.7   | 81.9  | 118.2  | 138.8 |
| 25°    | 0.0  | 2.4    | 5.4  | 9.1    | 13.1 | 22.6   | 37.2 | 55.8   | 86.1  | 123.2  | 143.5 |
| 22.5°  | 0.0  | 2.4    | 5.5  | 9.3    | 13.4 | 22.6   | 35.5 | 55.6   | 90.6  | 127.0  | 149.6 |
| 20°    | 0.0  | 2.4    | 5.6  | 9.5    | 13.8 | 23.7   | 33.5 | 55.3   | 95.2  | 130.4  | 155.0 |
| 17.5°  | 0.0  | 2.5    | 5.7  | 9.7    | 14.1 | 24.6   | 33.2 | 54.8   | 99.8  | 133.5  | 159.7 |
| 15°    | 0.0  | 2.5    | 5.8  | 9.9    | 14.4 | 25.4   | 33.8 | 54.5   | 104.3 | 136.2  | 163.7 |
| 12.5°  | 0.0  | 2.5    | 5.8  | 10.0   | 14.6 | 26.1   | 34.4 | 54.2   | 108.3 | 138.6  | 167.0 |
| 10°    | 0.0  | 2.6    | 5.9  | 10.1   | 14.9 | 26.6   | 35.0 | 53.1   | 111.6 | 140.4  | 169.6 |
| 7.5°   | 0.0  | 2.6    | 5.9  | 10.2   | 15.1 | 27.1   | 35.4 | 51.4   | 114.3 | 141.8  | 171.0 |
| 5°     | 0.0  | 2.6    | 6.0  | 10.3   | 15.3 | 27.4   | 35.8 | 49.2   | 116.2 | 142.9  | 171.7 |
| 2.5°   | 0.0  | 2.6    | 6.0  | 10.3   | 15.5 | 27.6   | 36.2 | 43.9   | 117.1 | 143.8  | 171.3 |
| 0°     | 0.0  | 2.6    | 6.0  | 10.3   | 15.4 | 27.5   | 36.0 | 46.7   | 117.2 | 143.6  | 171.8 |
| -2.5°  | 0.0  | 2.6    | 6.0  | 10.3   | 15.3 | 27.4   | 35.8 | 49.2   | 116.2 | 142.9  | 171.7 |
| -5°    | 0.0  | 2.6    | 6.0  | 10.3   | 15.1 | 27.1   | 35.4 | 51.4   | 114.3 | 141.8  | 171.0 |
| -7.5°  | 0.0  | 2.6    | 5.9  | 10.2   | 15.1 | 27.1   | 35.4 | 51.4   | 114.3 | 141.8  | 171.0 |
| -10°   | 0.0  | 2.6    | 5.9  | 10.1   | 14.9 | 26.6   | 35.0 | 53.1   | 111.6 | 140.4  | 169.6 |
| -12.5° | 0.0  | 2.5    | 5.8  | 10.0   | 14.6 | 26.1   | 34.4 | 54.2   | 108.3 | 138.6  | 167.0 |
| -15°   | 0.0  | 2.5    | 5.8  | 9.9    | 14.4 | 25.4   | 33.8 | 54.5   | 104.3 | 136.2  | 163.7 |
| -17.5° | 0.0  | 2.5    | 5.7  | 9.7    | 14.1 | 24.6   | 33.2 | 54.8   | 99.8  | 133.5  | 159.7 |
| -20°   | 0.0  | 2.4    | 5.6  | 9.5    | 13.8 | 23.7   | 33.5 | 55.3   | 95.2  | 130.4  | 155.0 |



REPORT NUMBER: P558683 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: GFLD-SA2C-940-U-WR-XX

**CANDELA DISTRIBUTION (continued):**

|        | -90° | -87.5° | -85° | -82.5° | -80° | -77.5° | -75° | -72.5° | -70° | -67.5° | -65°  |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|-------|
| -22.5° | 0.0  | 2.4    | 5.5  | 9.3    | 13.4 | 22.6   | 35.5 | 55.6   | 90.6 | 127.0  | 149.6 |
| -25°   | 0.0  | 2.4    | 5.4  | 9.1    | 13.1 | 22.6   | 37.2 | 55.8   | 86.1 | 123.2  | 143.5 |
| -27.5° | 0.0  | 2.3    | 5.2  | 8.8    | 12.7 | 22.8   | 38.6 | 55.7   | 81.9 | 118.2  | 138.8 |
| -30°   | 0.0  | 2.3    | 5.1  | 8.6    | 12.4 | 22.8   | 39.7 | 55.6   | 79.9 | 112.0  | 133.8 |
| -32.5° | 0.0  | 2.2    | 4.9  | 8.3    | 12.7 | 22.5   | 40.4 | 56.4   | 79.1 | 106.5  | 128.4 |
| -35°   | 0.0  | 2.1    | 4.8  | 8.0    | 12.9 | 21.9   | 40.2 | 57.2   | 78.3 | 101.9  | 122.8 |
| -37.5° | 0.0  | 2.1    | 4.6  | 7.6    | 12.9 | 21.4   | 39.4 | 57.5   | 77.5 | 98.3   | 117.1 |
| -40°   | 0.0  | 2.0    | 4.4  | 7.3    | 12.8 | 21.4   | 38.1 | 57.3   | 76.7 | 96.7   | 111.5 |
| -42.5° | 0.0  | 1.9    | 4.2  | 7.0    | 12.6 | 21.2   | 36.4 | 56.6   | 75.9 | 93.0   | 105.6 |
| -45°   | 0.0  | 1.8    | 4.0  | 6.7    | 12.2 | 20.7   | 34.2 | 54.9   | 74.6 | 88.6   | 99.7  |
| -47.5° | 0.0  | 1.8    | 3.8  | 6.3    | 11.8 | 20.0   | 31.7 | 51.8   | 72.5 | 83.8   | 94.3  |
| -50°   | 0.0  | 1.7    | 3.6  | 6.0    | 11.2 | 19.1   | 30.2 | 48.2   | 67.8 | 78.5   | 88.5  |
| -52.5° | 0.0  | 1.6    | 3.3  | 5.7    | 10.4 | 17.9   | 28.5 | 44.0   | 61.7 | 73.2   | 82.4  |
| -55°   | 0.0  | 1.5    | 3.1  | 5.4    | 9.6  | 16.6   | 26.6 | 39.5   | 55.0 | 67.8   | 76.6  |
| -57.5° | 0.0  | 1.4    | 2.9  | 5.0    | 8.6  | 15.2   | 24.4 | 36.5   | 48.3 | 61.0   | 70.8  |
| -60°   | 0.0  | 1.3    | 2.6  | 4.6    | 7.5  | 13.6   | 21.8 | 32.6   | 41.9 | 53.7   | 64.4  |
| -62.5° | 0.0  | 1.2    | 2.4  | 4.2    | 6.9  | 11.8   | 19.3 | 28.3   | 36.7 | 46.4   | 56.7  |
| -65°   | 0.0  | 1.1    | 2.2  | 3.7    | 6.1  | 9.8    | 16.5 | 23.9   | 31.2 | 39.7   | 49.1  |
| -67.5° | 0.0  | 1.0    | 2.0  | 3.2    | 5.3  | 8.2    | 13.5 | 19.9   | 25.4 | 32.8   | 41.1  |
| -70°   | 0.0  | 0.9    | 1.8  | 2.7    | 4.5  | 7.0    | 10.4 | 15.7   | 20.7 | 25.7   | 32.7  |
| -72.5° | 0.0  | 0.8    | 1.6  | 2.3    | 3.7  | 5.7    | 8.4  | 11.6   | 16.0 | 20.3   | 24.6  |
| -75°   | 0.0  | 0.7    | 1.3  | 2.0    | 2.8  | 4.4    | 6.6  | 8.8    | 11.2 | 14.9   | 18.6  |
| -77.5° | 0.0  | 0.6    | 1.1  | 1.7    | 2.2  | 3.1    | 4.7  | 6.5    | 8.3  | 10.1   | 12.6  |
| -80°   | 0.0  | 0.5    | 0.9  | 1.4    | 1.8  | 2.2    | 2.8  | 4.2    | 5.5  | 7.0    | 8.5   |
| -82.5° | 0.0  | 0.3    | 0.7  | 1.0    | 1.4  | 1.7    | 2.0  | 2.3    | 2.8  | 3.8    | 4.9   |
| -85°   | 0.0  | 0.2    | 0.5  | 0.7    | 0.9  | 1.1    | 1.3  | 1.6    | 1.8  | 2.0    | 2.2   |
| -87.5° | 0.0  | 0.1    | 0.2  | 0.3    | 0.5  | 0.6    | 0.7  | 0.8    | 0.9  | 1.0    | 1.1   |
| -90°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   |





REPORT NUMBER: P558683 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: GFLD-SA2C-940-U-WR-XX

**CANDELA DISTRIBUTION (continued):**

|        | -62.5° | -60°  | -57.5° | -55°  | -52.5° | -50°   | -47.5° | -45°   | -42.5° | -40°   | -37.5° |
|--------|--------|-------|--------|-------|--------|--------|--------|--------|--------|--------|--------|
| 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5°  | 1.1    | 1.1   | 1.0    | 1.0   | 1.0    | 1.1    | 1.1    | 1.2    | 1.1    | 1.0    | 0.9    |
| 85°    | 2.2    | 2.2   | 2.4    | 2.6   | 2.9    | 3.1    | 3.2    | 3.2    | 3.5    | 4.0    | 4.6    |
| 82.5°  | 5.5    | 5.8   | 6.0    | 6.1   | 6.2    | 6.2    | 6.1    | 6.1    | 7.5    | 9.3    | 11.3   |
| 80°    | 9.2    | 9.5   | 11.0   | 12.5  | 13.3   | 13.4   | 12.7   | 11.3   | 13.4   | 16.7   | 20.8   |
| 77.5°  | 14.9   | 17.1  | 19.4   | 21.8  | 22.3   | 21.1   | 19.3   | 16.7   | 19.7   | 25.7   | 32.4   |
| 75°    | 21.7   | 24.7  | 28.1   | 30.6  | 30.6   | 28.8   | 26.4   | 25.9   | 30.9   | 38.1   | 44.0   |
| 72.5°  | 29.7   | 34.1  | 37.3   | 39.5  | 39.3   | 39.0   | 40.0   | 42.1   | 46.2   | 51.5   | 56.1   |
| 70°    | 39.3   | 43.7  | 46.1   | 47.2  | 47.7   | 50.1   | 53.7   | 56.3   | 59.3   | 64.4   | 69.2   |
| 67.5°  | 48.9   | 52.2  | 54.4   | 55.8  | 59.8   | 64.4   | 68.0   | 71.3   | 74.9   | 80.2   | 84.5   |
| 65°    | 57.4   | 60.8  | 63.8   | 68.3  | 74.1   | 78.5   | 82.7   | 87.1   | 93.4   | 99.3   | 102.9  |
| 62.5°  | 65.7   | 69.4  | 73.9   | 80.0  | 86.4   | 91.9   | 98.8   | 106.6  | 114.8  | 120.9  | 127.8  |
| 60°    | 72.2   | 77.4  | 83.8   | 91.1  | 98.6   | 107.6  | 116.5  | 125.7  | 134.1  | 142.2  | 152.4  |
| 57.5°  | 78.3   | 85.8  | 93.9   | 102.4 | 112.4  | 123.6  | 134.5  | 144.4  | 154.9  | 166.2  | 177.8  |
| 55°    | 85.0   | 94.8  | 103.8  | 113.9 | 126.1  | 140.4  | 152.5  | 164.2  | 176.7  | 195.9  | 212.6  |
| 52.5°  | 92.4   | 103.2 | 113.3  | 125.7 | 140.9  | 156.2  | 169.9  | 186.3  | 207.3  | 235.7  | 281.7  |
| 50°    | 99.3   | 110.9 | 122.8  | 138.8 | 155.3  | 171.3  | 191.2  | 214.0  | 256.2  | 309.1  | 401.7  |
| 47.5°  | 106.2  | 118.5 | 134.3  | 151.5 | 169.5  | 190.7  | 215.8  | 265.7  | 323.3  | 455.1  | 586.4  |
| 45°    | 113.1  | 127.7 | 145.1  | 164.7 | 186.1  | 212.7  | 264.9  | 326.5  | 483.0  | 634.6  | 792.5  |
| 42.5°  | 119.7  | 136.9 | 156.8  | 177.7 | 205.6  | 253.7  | 321.0  | 483.7  | 653.2  | 827.3  | 978.8  |
| 40°    | 127.3  | 145.5 | 168.5  | 195.0 | 231.9  | 305.0  | 456.0  | 639.2  | 830.2  | 994.7  | 1142.1 |
| 37.5°  | 134.5  | 156.0 | 181.0  | 211.8 | 278.1  | 400.1  | 594.7  | 797.9  | 982.9  | 1143.6 | 1301.1 |
| 35°    | 141.1  | 166.1 | 195.9  | 242.1 | 323.3  | 524.5  | 735.5  | 942.1  | 1118.9 | 1290.5 | 1462.8 |
| 32.5°  | 148.8  | 175.9 | 210.2  | 282.3 | 427.2  | 644.5  | 869.1  | 1065.9 | 1251.1 | 1434.1 | 1630.9 |
| 30°    | 157.3  | 188.1 | 230.2  | 320.7 | 530.1  | 761.2  | 983.7  | 1184.8 | 1376.7 | 1580.0 | 1790.7 |
| 27.5°  | 165.3  | 199.8 | 263.3  | 395.0 | 626.9  | 870.2  | 1087.9 | 1294.9 | 1500.9 | 1717.3 | 1944.3 |
| 25°    | 172.6  | 211.0 | 294.4  | 476.6 | 720.3  | 963.1  | 1183.8 | 1394.4 | 1616.9 | 1852.1 | 2090.9 |
| 22.5°  | 180.5  | 221.8 | 322.4  | 550.9 | 805.7  | 1045.8 | 1268.6 | 1491.8 | 1727.3 | 1976.6 | 2225.7 |
| 20°    | 189.0  | 245.0 | 368.5  | 619.4 | 883.4  | 1121.0 | 1344.6 | 1582.3 | 1830.6 | 2088.8 | 2351.9 |
| 17.5°  | 196.7  | 265.6 | 423.5  | 684.5 | 948.6  | 1186.4 | 1413.0 | 1664.3 | 1920.5 | 2190.4 | 2467.5 |
| 15°    | 203.7  | 283.3 | 472.0  | 742.0 | 1004.1 | 1241.9 | 1479.7 | 1737.0 | 2000.3 | 2281.4 | 2569.3 |
| 12.5°  | 209.8  | 298.3 | 513.7  | 791.7 | 1050.8 | 1289.4 | 1535.8 | 1798.4 | 2071.5 | 2361.0 | 2661.0 |
| 10°    | 215.0  | 310.6 | 548.4  | 833.3 | 1088.9 | 1328.6 | 1580.8 | 1849.5 | 2128.1 | 2425.1 | 2735.0 |
| 7.5°   | 218.3  | 320.6 | 575.8  | 866.5 | 1118.2 | 1359.3 | 1614.8 | 1889.7 | 2169.5 | 2475.2 | 2790.9 |
| 5°     | 220.4  | 328.9 | 595.7  | 891.1 | 1139.6 | 1382.4 | 1639.2 | 1918.6 | 2196.1 | 2510.3 | 2828.5 |
| 2.5°   | 221.4  | 334.6 | 607.8  | 906.8 | 1152.9 | 1398.6 | 1659.5 | 1944.0 | 2224.1 | 2535.3 | 2857.6 |
| 0°     | 221.3  | 337.5 | 612.2  | 913.5 | 1158.0 | 1406.0 | 1669.5 | 1957.1 | 2242.0 | 2546.0 | 2877.5 |
| -2.5°  | 221.4  | 334.6 | 607.8  | 906.8 | 1152.9 | 1398.6 | 1659.5 | 1944.0 | 2224.1 | 2535.3 | 2857.6 |
| -5°    | 220.4  | 328.9 | 595.7  | 891.1 | 1139.6 | 1382.4 | 1639.2 | 1918.6 | 2196.1 | 2510.3 | 2828.5 |
| -7.5°  | 218.3  | 320.6 | 575.8  | 866.5 | 1118.2 | 1359.3 | 1614.8 | 1889.7 | 2169.5 | 2475.2 | 2790.9 |
| -10°   | 215.0  | 310.6 | 548.4  | 833.3 | 1088.9 | 1328.6 | 1580.8 | 1849.5 | 2128.1 | 2425.1 | 2735.0 |
| -12.5° | 209.8  | 298.3 | 513.7  | 791.7 | 1050.8 | 1289.4 | 1535.8 | 1798.4 | 2071.5 | 2361.0 | 2661.0 |
| -15°   | 203.7  | 283.3 | 472.0  | 742.0 | 1004.1 | 1241.9 | 1479.7 | 1737.0 | 2000.3 | 2281.4 | 2569.3 |
| -17.5° | 196.7  | 265.6 | 423.5  | 684.5 | 948.6  | 1186.4 | 1413.0 | 1664.3 | 1920.5 | 2190.4 | 2467.5 |
| -20°   | 189.0  | 245.0 | 368.5  | 619.4 | 883.4  | 1121.0 | 1344.6 | 1582.3 | 1830.6 | 2088.8 | 2351.9 |



REPORT NUMBER: P558683 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: GFLD-SA2C-940-U-WR-XX

**CANDELA DISTRIBUTION (continued):**

|        | -62.5° | -60°  | -57.5° | -55°  | -52.5° | -50°   | -47.5° | -45°   | -42.5° | -40°   | -37.5° |
|--------|--------|-------|--------|-------|--------|--------|--------|--------|--------|--------|--------|
| -22.5° | 180.5  | 221.8 | 322.4  | 550.9 | 805.7  | 1045.8 | 1268.6 | 1491.8 | 1727.3 | 1976.6 | 2225.7 |
| -25°   | 172.6  | 211.0 | 294.4  | 476.6 | 720.3  | 963.1  | 1183.8 | 1394.4 | 1616.9 | 1852.1 | 2090.9 |
| -27.5° | 165.3  | 199.8 | 263.3  | 395.0 | 626.9  | 870.2  | 1087.9 | 1294.9 | 1500.9 | 1717.3 | 1944.3 |
| -30°   | 157.3  | 188.1 | 230.2  | 320.7 | 530.1  | 761.2  | 983.7  | 1184.8 | 1376.7 | 1580.0 | 1790.7 |
| -32.5° | 148.8  | 175.9 | 210.2  | 282.3 | 427.2  | 644.5  | 869.1  | 1065.9 | 1251.1 | 1434.1 | 1630.9 |
| -35°   | 141.1  | 166.1 | 195.9  | 242.1 | 323.3  | 524.5  | 735.5  | 942.1  | 1118.9 | 1290.5 | 1462.8 |
| -37.5° | 134.5  | 156.0 | 181.0  | 211.8 | 278.1  | 400.1  | 594.7  | 797.9  | 982.9  | 1143.6 | 1301.1 |
| -40°   | 127.3  | 145.5 | 168.5  | 195.0 | 231.9  | 305.0  | 456.0  | 639.2  | 830.2  | 994.7  | 1142.1 |
| -42.5° | 119.7  | 136.9 | 156.8  | 177.7 | 205.6  | 253.7  | 321.0  | 483.7  | 653.2  | 827.3  | 978.8  |
| -45°   | 113.1  | 127.7 | 145.1  | 164.7 | 186.1  | 212.7  | 264.9  | 326.5  | 483.0  | 634.6  | 792.5  |
| -47.5° | 106.2  | 118.5 | 134.3  | 151.5 | 169.5  | 190.7  | 215.8  | 265.7  | 323.3  | 455.1  | 586.4  |
| -50°   | 99.3   | 110.9 | 122.8  | 138.8 | 155.3  | 171.3  | 191.2  | 214.0  | 256.2  | 309.1  | 401.7  |
| -52.5° | 92.4   | 103.2 | 113.3  | 125.7 | 140.9  | 156.2  | 169.9  | 186.3  | 207.3  | 235.7  | 281.7  |
| -55°   | 85.0   | 94.8  | 103.8  | 113.9 | 126.1  | 140.4  | 152.5  | 164.2  | 176.7  | 195.9  | 212.6  |
| -57.5° | 78.3   | 85.8  | 93.9   | 102.4 | 112.4  | 123.6  | 134.5  | 144.4  | 154.9  | 166.2  | 177.8  |
| -60°   | 72.2   | 77.4  | 83.8   | 91.1  | 98.6   | 107.6  | 116.5  | 125.7  | 134.1  | 142.2  | 152.4  |
| -62.5° | 65.7   | 69.4  | 73.9   | 80.0  | 86.4   | 91.9   | 98.8   | 106.6  | 114.8  | 120.9  | 127.8  |
| -65°   | 57.4   | 60.8  | 63.8   | 68.3  | 74.1   | 78.5   | 82.7   | 87.1   | 93.4   | 99.3   | 102.9  |
| -67.5° | 48.9   | 52.2  | 54.4   | 55.8  | 59.8   | 64.4   | 68.0   | 71.3   | 74.9   | 80.2   | 84.5   |
| -70°   | 39.3   | 43.7  | 46.1   | 47.2  | 47.7   | 50.1   | 53.7   | 56.3   | 59.3   | 64.4   | 69.2   |
| -72.5° | 29.7   | 34.1  | 37.3   | 39.5  | 39.3   | 39.0   | 40.0   | 42.1   | 46.2   | 51.5   | 56.1   |
| -75°   | 21.7   | 24.7  | 28.1   | 30.6  | 30.6   | 28.8   | 26.4   | 25.9   | 30.9   | 38.1   | 44.0   |
| -77.5° | 14.9   | 17.1  | 19.4   | 21.8  | 22.3   | 21.1   | 19.3   | 16.7   | 19.7   | 25.7   | 32.4   |
| -80°   | 9.2    | 9.5   | 11.0   | 12.5  | 13.3   | 13.4   | 12.7   | 11.3   | 13.4   | 16.7   | 20.8   |
| -82.5° | 5.5    | 5.8   | 6.0    | 6.1   | 6.2    | 6.2    | 6.1    | 6.1    | 7.5    | 9.3    | 11.3   |
| -85°   | 2.2    | 2.2   | 2.4    | 2.6   | 2.9    | 3.1    | 3.2    | 3.2    | 3.5    | 4.0    | 4.6    |
| -87.5° | 1.1    | 1.1   | 1.0    | 1.0   | 1.0    | 1.1    | 1.1    | 1.2    | 1.1    | 1.0    | 0.9    |
| -90°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P558683 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: GFLD-SA2C-940-U-WR-XX

**CANDELA DISTRIBUTION (continued):**

|        | -35°   | -32.5° | -30°   | -27.5° | -25°   | -22.5° | -20°   | -17.5° | -15°   | -12.5° | -10°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5°  | 0.7    | 0.8    | 0.8    | 0.8    | 0.8    | 0.8    | 0.8    | 0.9    | 0.9    | 0.9    | 0.9    |
| 85°    | 5.2    | 5.2    | 5.0    | 4.7    | 4.4    | 4.5    | 4.7    | 4.8    | 4.9    | 4.6    | 4.2    |
| 82.5°  | 13.5   | 14.5   | 15.5   | 16.5   | 17.5   | 17.4   | 16.9   | 16.2   | 15.3   | 13.6   | 11.8   |
| 80°    | 25.3   | 27.7   | 29.3   | 30.5   | 31.5   | 30.5   | 29.1   | 27.4   | 25.5   | 22.6   | 19.5   |
| 77.5°  | 39.3   | 41.7   | 42.9   | 44.4   | 46.0   | 46.3   | 46.4   | 46.6   | 46.8   | 41.5   | 34.8   |
| 75°    | 48.8   | 51.9   | 54.5   | 56.8   | 58.8   | 59.8   | 60.5   | 61.2   | 61.8   | 54.8   | 45.6   |
| 72.5°  | 60.0   | 63.0   | 65.5   | 68.0   | 70.2   | 71.9   | 73.2   | 74.3   | 75.1   | 69.4   | 61.4   |
| 70°    | 73.0   | 76.1   | 78.9   | 81.5   | 84.0   | 86.3   | 88.4   | 90.3   | 92.0   | 92.3   | 92.7   |
| 67.5°  | 87.8   | 89.6   | 93.0   | 96.2   | 100.1  | 102.9  | 106.1  | 109.0  | 111.7  | 114.0  | 116.0  |
| 65°    | 106.1  | 112.6  | 119.2  | 122.4  | 122.6  | 126.8  | 133.2  | 136.8  | 137.8  | 138.6  | 140.7  |
| 62.5°  | 136.7  | 145.1  | 149.6  | 155.3  | 163.3  | 171.9  | 175.2  | 179.9  | 185.7  | 192.2  | 198.2  |
| 60°    | 161.1  | 168.3  | 178.9  | 189.8  | 199.4  | 208.1  | 229.4  | 248.2  | 264.3  | 278.2  | 291.6  |
| 57.5°  | 191.4  | 203.2  | 219.5  | 248.8  | 275.6  | 299.9  | 341.4  | 392.1  | 437.2  | 476.7  | 511.4  |
| 55°    | 239.6  | 273.9  | 304.8  | 374.1  | 448.1  | 512.2  | 572.2  | 636.3  | 688.5  | 729.3  | 767.1  |
| 52.5°  | 321.8  | 416.2  | 511.8  | 601.8  | 690.2  | 770.7  | 843.0  | 899.9  | 944.3  | 977.6  | 1009.1 |
| 50°    | 515.2  | 628.9  | 745.4  | 852.7  | 939.6  | 1019.0 | 1094.2 | 1150.6 | 1197.8 | 1238.4 | 1274.4 |
| 47.5°  | 726.0  | 859.1  | 969.2  | 1068.2 | 1161.9 | 1249.9 | 1332.2 | 1400.8 | 1459.0 | 1512.6 | 1557.2 |
| 45°    | 935.8  | 1054.9 | 1167.8 | 1273.9 | 1375.9 | 1474.6 | 1563.0 | 1641.1 | 1718.0 | 1781.6 | 1831.9 |
| 42.5°  | 1113.2 | 1239.2 | 1359.3 | 1480.8 | 1594.8 | 1705.5 | 1812.4 | 1907.4 | 1989.1 | 2058.6 | 2114.5 |
| 40°    | 1283.5 | 1419.3 | 1562.0 | 1696.9 | 1832.2 | 1958.6 | 2077.0 | 2185.4 | 2278.5 | 2360.7 | 2430.3 |
| 37.5°  | 1456.8 | 1615.4 | 1772.2 | 1925.9 | 2075.0 | 2212.4 | 2348.3 | 2473.4 | 2582.4 | 2678.7 | 2759.5 |
| 35°    | 1639.7 | 1814.6 | 1985.1 | 2158.3 | 2321.1 | 2480.1 | 2630.3 | 2768.0 | 2888.8 | 3002.2 | 3099.7 |
| 32.5°  | 1822.9 | 2012.4 | 2204.4 | 2391.8 | 2572.1 | 2750.2 | 2915.0 | 3070.2 | 3213.0 | 3338.5 | 3442.6 |
| 30°    | 2001.2 | 2209.9 | 2415.4 | 2619.5 | 2825.3 | 3019.4 | 3201.9 | 3372.4 | 3527.3 | 3664.0 | 3782.2 |
| 27.5°  | 2172.4 | 2396.7 | 2617.1 | 2850.6 | 3074.3 | 3285.4 | 3483.7 | 3666.9 | 3839.9 | 3995.3 | 4129.5 |
| 25°    | 2330.8 | 2569.1 | 2825.9 | 3070.8 | 3310.1 | 3544.3 | 3761.6 | 3960.7 | 4158.4 | 4329.4 | 4475.1 |
| 22.5°  | 2480.5 | 2746.4 | 3016.8 | 3273.6 | 3537.7 | 3795.1 | 4038.4 | 4269.1 | 4480.2 | 4659.4 | 4814.8 |
| 20°    | 2622.8 | 2908.9 | 3187.5 | 3471.9 | 3757.9 | 4035.6 | 4303.4 | 4550.0 | 4773.1 | 4968.4 | 5143.6 |
| 17.5°  | 2757.2 | 3053.3 | 3349.4 | 3653.0 | 3961.8 | 4253.8 | 4537.6 | 4805.9 | 5049.4 | 5266.1 | 5463.6 |
| 15°    | 2873.5 | 3179.4 | 3496.4 | 3819.2 | 4142.2 | 4452.7 | 4753.8 | 5046.0 | 5320.0 | 5555.9 | 5755.1 |
| 12.5°  | 2972.3 | 3291.0 | 3626.4 | 3965.0 | 4305.4 | 4630.9 | 4950.1 | 5262.8 | 5554.1 | 5807.6 | 6012.1 |
| 10°    | 3054.2 | 3388.1 | 3738.5 | 4091.2 | 4440.4 | 4778.6 | 5110.6 | 5434.0 | 5746.9 | 6009.7 | 6219.7 |
| 7.5°   | 3122.5 | 3469.2 | 3827.7 | 4191.0 | 4543.4 | 4894.6 | 5240.8 | 5567.6 | 5875.8 | 6153.0 | 6368.8 |
| 5°     | 3173.5 | 3526.0 | 3892.0 | 4264.4 | 4622.2 | 4985.9 | 5342.4 | 5676.9 | 5982.1 | 6233.2 | 6409.4 |
| 2.5°   | 3211.5 | 3561.4 | 3933.8 | 4308.7 | 4671.2 | 5048.1 | 5412.2 | 5747.0 | 6059.3 | 6297.0 | 6449.6 |
| 0°     | 3237.4 | 3580.9 | 3971.8 | 4339.4 | 4708.0 | 5094.5 | 5454.4 | 5792.8 | 6106.2 | 6338.7 | 6496.3 |
| -2.5°  | 3211.5 | 3561.4 | 3933.8 | 4308.7 | 4671.2 | 5048.1 | 5412.2 | 5747.0 | 6059.3 | 6297.0 | 6449.6 |
| -5°    | 3173.5 | 3526.0 | 3892.0 | 4264.4 | 4622.2 | 4985.9 | 5342.4 | 5676.9 | 5982.1 | 6233.2 | 6409.4 |
| -7.5°  | 3122.5 | 3469.2 | 3827.7 | 4191.0 | 4543.4 | 4894.6 | 5240.8 | 5567.6 | 5875.8 | 6153.0 | 6368.8 |
| -10°   | 3054.2 | 3388.1 | 3738.5 | 4091.2 | 4440.4 | 4778.6 | 5110.6 | 5434.0 | 5746.9 | 6009.7 | 6219.7 |
| -12.5° | 2972.3 | 3291.0 | 3626.4 | 3965.0 | 4305.4 | 4630.9 | 4950.1 | 5262.8 | 5554.1 | 5807.6 | 6012.1 |
| -15°   | 2873.5 | 3179.4 | 3496.4 | 3819.2 | 4142.2 | 4452.7 | 4753.8 | 5046.0 | 5320.0 | 5555.9 | 5755.1 |
| -17.5° | 2757.2 | 3053.3 | 3349.4 | 3653.0 | 3961.8 | 4253.8 | 4537.6 | 4805.9 | 5049.4 | 5266.1 | 5463.6 |
| -20°   | 2622.8 | 2908.9 | 3187.5 | 3471.9 | 3757.9 | 4035.6 | 4303.4 | 4550.0 | 4773.1 | 4968.4 | 5143.6 |



REPORT NUMBER: P558683 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: GFLD-SA2C-940-U-WR-XX

**CANDELA DISTRIBUTION (continued):**

|        | -35°   | -32.5° | -30°   | -27.5° | -25°   | -22.5° | -20°   | -17.5° | -15°   | -12.5° | -10°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| -22.5° | 2480.5 | 2746.4 | 3016.8 | 3273.6 | 3537.7 | 3795.1 | 4038.4 | 4269.1 | 4480.2 | 4659.4 | 4814.8 |
| -25°   | 2330.8 | 2569.1 | 2825.9 | 3070.8 | 3310.1 | 3544.3 | 3761.6 | 3960.7 | 4158.4 | 4329.4 | 4475.1 |
| -27.5° | 2172.4 | 2396.7 | 2617.1 | 2850.6 | 3074.3 | 3285.4 | 3483.7 | 3666.9 | 3839.9 | 3995.3 | 4129.5 |
| -30°   | 2001.2 | 2209.9 | 2415.4 | 2619.5 | 2825.3 | 3019.4 | 3201.9 | 3372.4 | 3527.3 | 3664.0 | 3782.2 |
| -32.5° | 1822.9 | 2012.4 | 2204.4 | 2391.8 | 2572.1 | 2750.2 | 2915.0 | 3070.2 | 3213.0 | 3338.5 | 3442.6 |
| -35°   | 1639.7 | 1814.6 | 1985.1 | 2158.3 | 2321.1 | 2480.1 | 2630.3 | 2768.0 | 2888.8 | 3002.2 | 3099.7 |
| -37.5° | 1456.8 | 1615.4 | 1772.2 | 1925.9 | 2075.0 | 2212.4 | 2348.3 | 2473.4 | 2582.4 | 2678.7 | 2759.5 |
| -40°   | 1283.5 | 1419.3 | 1562.0 | 1696.9 | 1832.2 | 1958.6 | 2077.0 | 2185.4 | 2278.5 | 2360.7 | 2430.3 |
| -42.5° | 1113.2 | 1239.2 | 1359.3 | 1480.8 | 1594.8 | 1705.5 | 1812.4 | 1907.4 | 1989.1 | 2058.6 | 2114.5 |
| -45°   | 935.8  | 1054.9 | 1167.8 | 1273.9 | 1375.9 | 1474.6 | 1563.0 | 1641.1 | 1718.0 | 1781.6 | 1831.9 |
| -47.5° | 726.0  | 859.1  | 969.2  | 1068.2 | 1161.9 | 1249.9 | 1332.2 | 1400.8 | 1459.0 | 1512.6 | 1557.2 |
| -50°   | 515.2  | 628.9  | 745.4  | 852.7  | 939.6  | 1019.0 | 1094.2 | 1150.6 | 1197.8 | 1238.4 | 1274.4 |
| -52.5° | 321.8  | 416.2  | 511.8  | 601.8  | 690.2  | 770.7  | 843.0  | 899.9  | 944.3  | 977.6  | 1009.1 |
| -55°   | 239.6  | 273.9  | 304.8  | 374.1  | 448.1  | 512.2  | 572.2  | 636.3  | 688.5  | 729.3  | 767.1  |
| -57.5° | 191.4  | 203.2  | 219.5  | 248.8  | 275.6  | 299.9  | 341.4  | 392.1  | 437.2  | 476.7  | 511.4  |
| -60°   | 161.1  | 168.3  | 178.9  | 189.8  | 199.4  | 208.1  | 229.4  | 248.2  | 264.3  | 278.2  | 291.6  |
| -62.5° | 136.7  | 145.1  | 149.6  | 155.3  | 163.3  | 171.9  | 175.2  | 179.9  | 185.7  | 192.2  | 198.2  |
| -65°   | 106.1  | 112.6  | 119.2  | 122.4  | 122.6  | 126.8  | 133.2  | 136.8  | 137.8  | 138.6  | 140.7  |
| -67.5° | 87.8   | 89.6   | 93.0   | 96.2   | 100.1  | 102.9  | 106.1  | 109.0  | 111.7  | 114.0  | 116.0  |
| -70°   | 73.0   | 76.1   | 78.9   | 81.5   | 84.0   | 86.3   | 88.4   | 90.3   | 92.0   | 92.3   | 92.7   |
| -72.5° | 60.0   | 63.0   | 65.5   | 68.0   | 70.2   | 71.9   | 73.2   | 74.3   | 75.1   | 69.4   | 61.4   |
| -75°   | 48.8   | 51.9   | 54.5   | 56.8   | 58.8   | 59.8   | 60.5   | 61.2   | 61.8   | 54.8   | 45.6   |
| -77.5° | 39.3   | 41.7   | 42.9   | 44.4   | 46.0   | 46.3   | 46.4   | 46.6   | 46.8   | 41.5   | 34.8   |
| -80°   | 25.3   | 27.7   | 29.3   | 30.5   | 31.5   | 30.5   | 29.1   | 27.4   | 25.5   | 22.6   | 19.5   |
| -82.5° | 13.5   | 14.5   | 15.5   | 16.5   | 17.5   | 17.4   | 16.9   | 16.2   | 15.3   | 13.6   | 11.8   |
| -85°   | 5.2    | 5.2    | 5.0    | 4.7    | 4.4    | 4.5    | 4.7    | 4.8    | 4.9    | 4.6    | 4.2    |
| -87.5° | 0.7    | 0.8    | 0.8    | 0.8    | 0.8    | 0.8    | 0.8    | 0.9    | 0.9    | 0.9    | 0.9    |
| -90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P558683 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: GFLD-SA2C-940-U-WR-XX

**CANDELA DISTRIBUTION (continued):**

|        | -7.5°  | -5°    | -2.5°  | 0°     | 2.5°   | 5°     | 7.5°   | 10°    | 12.5°  | 15°    | 17.5°  |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5°  | 0.9    | 0.9    | 0.9    | 0.9    | 0.9    | 0.9    | 0.9    | 0.9    | 0.9    | 0.9    | 0.9    |
| 85°    | 3.8    | 3.4    | 3.4    | 3.4    | 3.4    | 3.4    | 3.8    | 4.2    | 4.6    | 4.9    | 4.8    |
| 82.5°  | 9.8    | 7.7    | 8.1    | 8.6    | 8.1    | 7.7    | 9.8    | 11.8   | 13.6   | 15.3   | 16.2   |
| 80°    | 16.3   | 12.9   | 13.3   | 13.8   | 13.3   | 12.9   | 16.3   | 19.5   | 22.6   | 25.5   | 27.4   |
| 77.5°  | 27.6   | 20.0   | 19.3   | 18.9   | 19.3   | 20.0   | 27.6   | 34.8   | 41.5   | 46.8   | 46.6   |
| 75°    | 36.1   | 26.3   | 25.8   | 25.8   | 25.8   | 26.3   | 36.1   | 45.6   | 54.8   | 61.8   | 61.2   |
| 72.5°  | 53.3   | 45.1   | 39.4   | 33.6   | 39.4   | 45.1   | 53.3   | 61.4   | 69.4   | 75.1   | 74.3   |
| 70°    | 93.7   | 94.8   | 94.4   | 93.0   | 94.4   | 94.8   | 93.7   | 92.7   | 92.3   | 92.0   | 90.3   |
| 67.5°  | 117.6  | 118.8  | 119.1  | 118.8  | 119.1  | 118.8  | 117.6  | 116.0  | 114.0  | 111.7  | 109.0  |
| 65°    | 142.1  | 142.9  | 143.6  | 143.8  | 143.6  | 142.9  | 142.1  | 140.7  | 138.6  | 137.8  | 136.8  |
| 62.5°  | 202.6  | 205.6  | 208.7  | 210.9  | 208.7  | 205.6  | 202.6  | 198.2  | 192.2  | 185.7  | 179.9  |
| 60°    | 303.3  | 313.0  | 317.3  | 317.7  | 317.3  | 313.0  | 303.3  | 291.6  | 278.2  | 264.3  | 248.2  |
| 57.5°  | 539.2  | 559.9  | 578.5  | 592.4  | 578.5  | 559.9  | 539.2  | 511.4  | 476.7  | 437.2  | 392.1  |
| 55°    | 797.2  | 819.3  | 831.8  | 835.2  | 831.8  | 819.3  | 797.2  | 767.1  | 729.3  | 688.5  | 636.3  |
| 52.5°  | 1033.1 | 1047.8 | 1061.7 | 1073.7 | 1061.7 | 1047.8 | 1033.1 | 1009.1 | 977.6  | 944.3  | 899.9  |
| 50°    | 1301.6 | 1317.9 | 1331.7 | 1342.3 | 1331.7 | 1317.9 | 1301.6 | 1274.4 | 1238.4 | 1197.8 | 1150.6 |
| 47.5°  | 1588.6 | 1608.6 | 1623.4 | 1633.3 | 1623.4 | 1608.6 | 1588.6 | 1557.2 | 1512.6 | 1459.0 | 1400.8 |
| 45°    | 1875.0 | 1909.3 | 1930.1 | 1933.8 | 1930.1 | 1909.3 | 1875.0 | 1831.9 | 1781.6 | 1718.0 | 1641.1 |
| 42.5°  | 2162.8 | 2195.7 | 2217.9 | 2234.3 | 2217.9 | 2195.7 | 2162.8 | 2114.5 | 2058.6 | 1989.1 | 1907.4 |
| 40°    | 2488.3 | 2529.7 | 2548.6 | 2536.5 | 2548.6 | 2529.7 | 2488.3 | 2430.3 | 2360.7 | 2278.5 | 2185.4 |
| 37.5°  | 2821.8 | 2864.3 | 2886.2 | 2885.2 | 2886.2 | 2864.3 | 2821.8 | 2759.5 | 2678.7 | 2582.4 | 2473.4 |
| 35°    | 3175.4 | 3228.1 | 3256.6 | 3249.4 | 3256.6 | 3228.1 | 3175.4 | 3099.7 | 3002.2 | 2888.8 | 2768.0 |
| 32.5°  | 3525.7 | 3589.4 | 3630.5 | 3636.9 | 3630.5 | 3589.4 | 3525.7 | 3442.6 | 3338.5 | 3213.0 | 3070.2 |
| 30°    | 3877.0 | 3945.8 | 3986.7 | 3990.7 | 3986.7 | 3945.8 | 3877.0 | 3782.2 | 3664.0 | 3527.3 | 3372.4 |
| 27.5°  | 4242.1 | 4319.1 | 4361.9 | 4372.2 | 4361.9 | 4319.1 | 4242.1 | 4129.5 | 3995.3 | 3839.9 | 3666.9 |
| 25°    | 4599.3 | 4684.7 | 4733.9 | 4752.7 | 4733.9 | 4684.7 | 4599.3 | 4475.1 | 4329.4 | 4158.4 | 3960.7 |
| 22.5°  | 4943.7 | 5037.5 | 5101.5 | 5117.8 | 5101.5 | 5037.5 | 4943.7 | 4814.8 | 4659.4 | 4480.2 | 4269.1 |
| 20°    | 5289.2 | 5399.8 | 5481.6 | 5489.7 | 5481.6 | 5399.8 | 5289.2 | 5143.6 | 4968.4 | 4773.1 | 4550.0 |
| 17.5°  | 5621.8 | 5741.5 | 5829.1 | 5850.5 | 5829.1 | 5741.5 | 5621.8 | 5463.6 | 5266.1 | 5049.4 | 4805.9 |
| 15°    | 5919.6 | 6045.2 | 6129.8 | 6148.4 | 6129.8 | 6045.2 | 5919.6 | 5755.1 | 5555.9 | 5320.0 | 5046.0 |
| 12.5°  | 6176.5 | 6292.3 | 6371.3 | 6401.5 | 6371.3 | 6292.3 | 6176.5 | 6012.1 | 5807.6 | 5554.1 | 5262.8 |
| 10°    | 6383.5 | 6473.0 | 6543.6 | 6575.5 | 6543.6 | 6473.0 | 6383.5 | 6219.7 | 6009.7 | 5746.9 | 5434.0 |
| 7.5°   | 6499.1 | 6572.7 | 6621.6 | 6639.2 | 6621.6 | 6572.7 | 6499.1 | 6368.8 | 6153.0 | 5875.8 | 5567.6 |
| 5°     | 6544.8 | 6615.3 | 6641.8 | 6657.3 | 6641.8 | 6615.3 | 6544.8 | 6409.4 | 6233.2 | 5982.1 | 5676.9 |
| 2.5°   | 6551.0 | 6607.5 | 6661.9 | 6697.7 | 6661.9 | 6607.5 | 6551.0 | 6449.6 | 6297.0 | 6059.3 | 5747.0 |
| 0°     | 6587.5 | 6642.6 | 6672.8 | 6690.0 | 6672.8 | 6642.6 | 6587.5 | 6496.3 | 6338.7 | 6106.2 | 5792.8 |
| -2.5°  | 6551.0 | 6607.5 | 6661.9 | 6697.7 | 6661.9 | 6607.5 | 6551.0 | 6449.6 | 6297.0 | 6059.3 | 5747.0 |
| -5°    | 6544.8 | 6615.3 | 6641.8 | 6657.3 | 6641.8 | 6615.3 | 6544.8 | 6409.4 | 6233.2 | 5982.1 | 5676.9 |
| -7.5°  | 6499.1 | 6572.7 | 6621.6 | 6639.2 | 6621.6 | 6572.7 | 6499.1 | 6368.8 | 6153.0 | 5875.8 | 5567.6 |
| -10°   | 6383.5 | 6473.0 | 6543.6 | 6575.5 | 6543.6 | 6473.0 | 6383.5 | 6219.7 | 6009.7 | 5746.9 | 5434.0 |
| -12.5° | 6176.5 | 6292.3 | 6371.3 | 6401.5 | 6371.3 | 6292.3 | 6176.5 | 6012.1 | 5807.6 | 5554.1 | 5262.8 |
| -15°   | 5919.6 | 6045.2 | 6129.8 | 6148.4 | 6129.8 | 6045.2 | 5919.6 | 5755.1 | 5555.9 | 5320.0 | 5046.0 |
| -17.5° | 5621.8 | 5741.5 | 5829.1 | 5850.5 | 5829.1 | 5741.5 | 5621.8 | 5463.6 | 5266.1 | 5049.4 | 4805.9 |
| -20°   | 5289.2 | 5399.8 | 5481.6 | 5489.7 | 5481.6 | 5399.8 | 5289.2 | 5143.6 | 4968.4 | 4773.1 | 4550.0 |



REPORT NUMBER: P558683 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: GFLD-SA2C-940-U-WR-XX

**CANDELA DISTRIBUTION (continued):**

|        | -7.5°  | -5°    | -2.5°  | 0°     | 2.5°   | 5°     | 7.5°   | 10°    | 12.5°  | 15°    | 17.5°  |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| -22.5° | 4943.7 | 5037.5 | 5101.5 | 5117.8 | 5101.5 | 5037.5 | 4943.7 | 4814.8 | 4659.4 | 4480.2 | 4269.1 |
| -25°   | 4599.3 | 4684.7 | 4733.9 | 4752.7 | 4733.9 | 4684.7 | 4599.3 | 4475.1 | 4329.4 | 4158.4 | 3960.7 |
| -27.5° | 4242.1 | 4319.1 | 4361.9 | 4372.2 | 4361.9 | 4319.1 | 4242.1 | 4129.5 | 3995.3 | 3839.9 | 3666.9 |
| -30°   | 3877.0 | 3945.8 | 3986.7 | 3990.7 | 3986.7 | 3945.8 | 3877.0 | 3782.2 | 3664.0 | 3527.3 | 3372.4 |
| -32.5° | 3525.7 | 3589.4 | 3630.5 | 3636.9 | 3630.5 | 3589.4 | 3525.7 | 3442.6 | 3338.5 | 3213.0 | 3070.2 |
| -35°   | 3175.4 | 3228.1 | 3256.6 | 3249.4 | 3256.6 | 3228.1 | 3175.4 | 3099.7 | 3002.2 | 2888.8 | 2768.0 |
| -37.5° | 2821.8 | 2864.3 | 2886.2 | 2885.2 | 2886.2 | 2864.3 | 2821.8 | 2759.5 | 2678.7 | 2582.4 | 2473.4 |
| -40°   | 2488.3 | 2529.7 | 2548.6 | 2536.5 | 2548.6 | 2529.7 | 2488.3 | 2430.3 | 2360.7 | 2278.5 | 2185.4 |
| -42.5° | 2162.8 | 2195.7 | 2217.9 | 2234.3 | 2217.9 | 2195.7 | 2162.8 | 2114.5 | 2058.6 | 1989.1 | 1907.4 |
| -45°   | 1875.0 | 1909.3 | 1930.1 | 1933.8 | 1930.1 | 1909.3 | 1875.0 | 1831.9 | 1781.6 | 1718.0 | 1641.1 |
| -47.5° | 1588.6 | 1608.6 | 1623.4 | 1633.3 | 1623.4 | 1608.6 | 1588.6 | 1557.2 | 1512.6 | 1459.0 | 1400.8 |
| -50°   | 1301.6 | 1317.9 | 1331.7 | 1342.3 | 1331.7 | 1317.9 | 1301.6 | 1274.4 | 1238.4 | 1197.8 | 1150.6 |
| -52.5° | 1033.1 | 1047.8 | 1061.7 | 1073.7 | 1061.7 | 1047.8 | 1033.1 | 1009.1 | 977.6  | 944.3  | 899.9  |
| -55°   | 797.2  | 819.3  | 831.8  | 835.2  | 831.8  | 819.3  | 797.2  | 767.1  | 729.3  | 688.5  | 636.3  |
| -57.5° | 539.2  | 559.9  | 578.5  | 592.4  | 578.5  | 559.9  | 539.2  | 511.4  | 476.7  | 437.2  | 392.1  |
| -60°   | 303.3  | 313.0  | 317.3  | 317.7  | 317.3  | 313.0  | 303.3  | 291.6  | 278.2  | 264.3  | 248.2  |
| -62.5° | 202.6  | 205.6  | 208.7  | 210.9  | 208.7  | 205.6  | 202.6  | 198.2  | 192.2  | 185.7  | 179.9  |
| -65°   | 142.1  | 142.9  | 143.6  | 143.8  | 143.6  | 142.9  | 142.1  | 140.7  | 138.6  | 137.8  | 136.8  |
| -67.5° | 117.6  | 118.8  | 119.1  | 118.8  | 119.1  | 118.8  | 117.6  | 116.0  | 114.0  | 111.7  | 109.0  |
| -70°   | 93.7   | 94.8   | 94.4   | 93.0   | 94.4   | 94.8   | 93.7   | 92.7   | 92.3   | 92.0   | 90.3   |
| -72.5° | 53.3   | 45.1   | 39.4   | 33.6   | 39.4   | 45.1   | 53.3   | 61.4   | 69.4   | 75.1   | 74.3   |
| -75°   | 36.1   | 26.3   | 25.8   | 25.8   | 25.8   | 26.3   | 36.1   | 45.6   | 54.8   | 61.8   | 61.2   |
| -77.5° | 27.6   | 20.0   | 19.3   | 18.9   | 19.3   | 20.0   | 27.6   | 34.8   | 41.5   | 46.8   | 46.6   |
| -80°   | 16.3   | 12.9   | 13.3   | 13.8   | 13.3   | 12.9   | 16.3   | 19.5   | 22.6   | 25.5   | 27.4   |
| -82.5° | 9.8    | 7.7    | 8.1    | 8.6    | 8.1    | 7.7    | 9.8    | 11.8   | 13.6   | 15.3   | 16.2   |
| -85°   | 3.8    | 3.4    | 3.4    | 3.4    | 3.4    | 3.4    | 3.8    | 4.2    | 4.6    | 4.9    | 4.8    |
| -87.5° | 0.9    | 0.9    | 0.9    | 0.9    | 0.9    | 0.9    | 0.9    | 0.9    | 0.9    | 0.9    | 0.9    |
| -90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P558683 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: GFLD-SA2C-940-U-WR-XX

**CANDELA DISTRIBUTION (continued):**

|        | 20°    | 22.5°  | 25°    | 27.5°  | 30°    | 32.5°  | 35°    | 37.5°  | 40°    | 42.5°  | 45°    |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5°  | 0.8    | 0.8    | 0.8    | 0.8    | 0.8    | 0.8    | 0.7    | 0.9    | 1.0    | 1.1    | 1.2    |
| 85°    | 4.7    | 4.5    | 4.4    | 4.7    | 5.0    | 5.2    | 5.2    | 4.6    | 4.0    | 3.5    | 3.2    |
| 82.5°  | 16.9   | 17.4   | 17.5   | 16.5   | 15.5   | 14.5   | 13.5   | 11.3   | 9.3    | 7.5    | 6.1    |
| 80°    | 29.1   | 30.5   | 31.5   | 30.5   | 29.3   | 27.7   | 25.3   | 20.8   | 16.7   | 13.4   | 11.3   |
| 77.5°  | 46.4   | 46.3   | 46.0   | 44.4   | 42.9   | 41.7   | 39.3   | 32.4   | 25.7   | 19.7   | 16.7   |
| 75°    | 60.5   | 59.8   | 58.8   | 56.8   | 54.5   | 51.9   | 48.8   | 44.0   | 38.1   | 30.9   | 25.9   |
| 72.5°  | 73.2   | 71.9   | 70.2   | 68.0   | 65.5   | 63.0   | 60.0   | 56.1   | 51.5   | 46.2   | 42.1   |
| 70°    | 88.4   | 86.3   | 84.0   | 81.5   | 78.9   | 76.1   | 73.0   | 69.2   | 64.4   | 59.3   | 56.3   |
| 67.5°  | 106.1  | 102.9  | 100.1  | 96.2   | 93.0   | 89.6   | 87.8   | 84.5   | 80.2   | 74.9   | 71.3   |
| 65°    | 133.2  | 126.8  | 122.6  | 122.4  | 119.2  | 112.6  | 106.1  | 102.9  | 99.3   | 93.4   | 87.1   |
| 62.5°  | 175.2  | 171.9  | 163.3  | 155.3  | 149.6  | 145.1  | 136.7  | 127.8  | 120.9  | 114.8  | 106.6  |
| 60°    | 229.4  | 208.1  | 199.4  | 189.8  | 178.9  | 168.3  | 161.1  | 152.4  | 142.2  | 134.1  | 125.7  |
| 57.5°  | 341.4  | 299.9  | 275.6  | 248.8  | 219.5  | 203.2  | 191.4  | 177.8  | 166.2  | 154.9  | 144.4  |
| 55°    | 572.2  | 512.2  | 448.1  | 374.1  | 304.8  | 273.9  | 239.6  | 212.6  | 195.9  | 176.7  | 164.2  |
| 52.5°  | 843.0  | 770.7  | 690.2  | 601.8  | 511.8  | 416.2  | 321.8  | 281.7  | 235.7  | 207.3  | 186.3  |
| 50°    | 1094.2 | 1019.0 | 939.6  | 852.7  | 745.4  | 628.9  | 515.2  | 401.7  | 309.1  | 256.2  | 214.0  |
| 47.5°  | 1332.2 | 1249.9 | 1161.9 | 1068.2 | 969.2  | 859.1  | 726.0  | 586.4  | 455.1  | 323.3  | 265.7  |
| 45°    | 1563.0 | 1474.6 | 1375.9 | 1273.9 | 1167.8 | 1054.9 | 935.8  | 792.5  | 634.6  | 483.0  | 326.5  |
| 42.5°  | 1812.4 | 1705.5 | 1594.8 | 1480.8 | 1359.3 | 1239.2 | 1113.2 | 978.8  | 827.3  | 653.2  | 483.7  |
| 40°    | 2077.0 | 1958.6 | 1832.2 | 1696.9 | 1562.0 | 1419.3 | 1283.5 | 1142.1 | 994.7  | 830.2  | 639.2  |
| 37.5°  | 2348.3 | 2212.4 | 2075.0 | 1925.9 | 1772.2 | 1615.4 | 1456.8 | 1301.1 | 1143.6 | 982.9  | 797.9  |
| 35°    | 2630.3 | 2480.1 | 2321.1 | 2158.3 | 1985.1 | 1814.6 | 1639.7 | 1462.8 | 1290.5 | 1118.9 | 942.1  |
| 32.5°  | 2915.0 | 2750.2 | 2572.1 | 2391.8 | 2204.4 | 2012.4 | 1822.9 | 1630.9 | 1434.1 | 1251.1 | 1065.9 |
| 30°    | 3201.9 | 3019.4 | 2825.3 | 2619.5 | 2415.4 | 2209.9 | 2001.2 | 1790.7 | 1580.0 | 1376.7 | 1184.8 |
| 27.5°  | 3483.7 | 3285.4 | 3074.3 | 2850.6 | 2617.1 | 2396.7 | 2172.4 | 1944.3 | 1717.3 | 1500.9 | 1294.9 |
| 25°    | 3761.6 | 3544.3 | 3310.1 | 3070.8 | 2825.9 | 2569.1 | 2330.8 | 2090.9 | 1852.1 | 1616.9 | 1394.4 |
| 22.5°  | 4038.4 | 3795.1 | 3537.7 | 3273.6 | 3016.8 | 2746.4 | 2480.5 | 2225.7 | 1976.6 | 1727.3 | 1491.8 |
| 20°    | 4303.4 | 4035.6 | 3757.9 | 3471.9 | 3187.5 | 2908.9 | 2622.8 | 2351.9 | 2088.8 | 1830.6 | 1582.3 |
| 17.5°  | 4537.6 | 4253.8 | 3961.8 | 3653.0 | 3349.4 | 3053.3 | 2757.2 | 2467.5 | 2190.4 | 1920.5 | 1664.3 |
| 15°    | 4753.8 | 4452.7 | 4142.2 | 3819.2 | 3496.4 | 3179.4 | 2873.5 | 2569.3 | 2281.4 | 2000.3 | 1737.0 |
| 12.5°  | 4950.1 | 4630.9 | 4305.4 | 3965.0 | 3626.4 | 3291.0 | 2972.3 | 2661.0 | 2361.0 | 2071.5 | 1798.4 |
| 10°    | 5110.6 | 4778.6 | 4440.4 | 4091.2 | 3738.5 | 3388.1 | 3054.2 | 2735.0 | 2425.1 | 2128.1 | 1849.5 |
| 7.5°   | 5240.8 | 4894.6 | 4543.4 | 4191.0 | 3827.7 | 3469.2 | 3122.5 | 2790.9 | 2475.2 | 2169.5 | 1889.7 |
| 5°     | 5342.4 | 4985.9 | 4622.2 | 4264.4 | 3892.0 | 3526.0 | 3173.5 | 2828.5 | 2510.3 | 2196.1 | 1918.6 |
| 2.5°   | 5412.2 | 5048.1 | 4671.2 | 4308.7 | 3933.8 | 3561.4 | 3211.5 | 2857.6 | 2535.3 | 2224.1 | 1944.0 |
| 0°     | 5454.4 | 5094.5 | 4708.0 | 4339.4 | 3971.8 | 3580.9 | 3237.4 | 2877.5 | 2546.0 | 2242.0 | 1957.1 |
| -2.5°  | 5412.2 | 5048.1 | 4671.2 | 4308.7 | 3933.8 | 3561.4 | 3211.5 | 2857.6 | 2535.3 | 2224.1 | 1944.0 |
| -5°    | 5342.4 | 4985.9 | 4622.2 | 4264.4 | 3892.0 | 3526.0 | 3173.5 | 2828.5 | 2510.3 | 2196.1 | 1918.6 |
| -7.5°  | 5240.8 | 4894.6 | 4543.4 | 4191.0 | 3827.7 | 3469.2 | 3122.5 | 2790.9 | 2475.2 | 2169.5 | 1889.7 |
| -10°   | 5110.6 | 4778.6 | 4440.4 | 4091.2 | 3738.5 | 3388.1 | 3054.2 | 2735.0 | 2425.1 | 2128.1 | 1849.5 |
| -12.5° | 4950.1 | 4630.9 | 4305.4 | 3965.0 | 3626.4 | 3291.0 | 2972.3 | 2661.0 | 2361.0 | 2071.5 | 1798.4 |
| -15°   | 4753.8 | 4452.7 | 4142.2 | 3819.2 | 3496.4 | 3179.4 | 2873.5 | 2569.3 | 2281.4 | 2000.3 | 1737.0 |
| -17.5° | 4537.6 | 4253.8 | 3961.8 | 3653.0 | 3349.4 | 3053.3 | 2757.2 | 2467.5 | 2190.4 | 1920.5 | 1664.3 |
| -20°   | 4303.4 | 4035.6 | 3757.9 | 3471.9 | 3187.5 | 2908.9 | 2622.8 | 2351.9 | 2088.8 | 1830.6 | 1582.3 |



REPORT NUMBER: P558683 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: GFLD-SA2C-940-U-WR-XX

**CANDELA DISTRIBUTION (continued):**

|        | 20°    | 22.5°  | 25°    | 27.5°  | 30°    | 32.5°  | 35°    | 37.5°  | 40°    | 42.5°  | 45°    |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| -22.5° | 4038.4 | 3795.1 | 3537.7 | 3273.6 | 3016.8 | 2746.4 | 2480.5 | 2225.7 | 1976.6 | 1727.3 | 1491.8 |
| -25°   | 3761.6 | 3544.3 | 3310.1 | 3070.8 | 2825.9 | 2569.1 | 2330.8 | 2090.9 | 1852.1 | 1616.9 | 1394.4 |
| -27.5° | 3483.7 | 3285.4 | 3074.3 | 2850.6 | 2617.1 | 2396.7 | 2172.4 | 1944.3 | 1717.3 | 1500.9 | 1294.9 |
| -30°   | 3201.9 | 3019.4 | 2825.3 | 2619.5 | 2415.4 | 2209.9 | 2001.2 | 1790.7 | 1580.0 | 1376.7 | 1184.8 |
| -32.5° | 2915.0 | 2750.2 | 2572.1 | 2391.8 | 2204.4 | 2012.4 | 1822.9 | 1630.9 | 1434.1 | 1251.1 | 1065.9 |
| -35°   | 2630.3 | 2480.1 | 2321.1 | 2158.3 | 1985.1 | 1814.6 | 1639.7 | 1462.8 | 1290.5 | 1118.9 | 942.1  |
| -37.5° | 2348.3 | 2212.4 | 2075.0 | 1925.9 | 1772.2 | 1615.4 | 1456.8 | 1301.1 | 1143.6 | 982.9  | 797.9  |
| -40°   | 2077.0 | 1958.6 | 1832.2 | 1696.9 | 1562.0 | 1419.3 | 1283.5 | 1142.1 | 994.7  | 830.2  | 639.2  |
| -42.5° | 1812.4 | 1705.5 | 1594.8 | 1480.8 | 1359.3 | 1239.2 | 1113.2 | 978.8  | 827.3  | 653.2  | 483.7  |
| -45°   | 1563.0 | 1474.6 | 1375.9 | 1273.9 | 1167.8 | 1054.9 | 935.8  | 792.5  | 634.6  | 483.0  | 326.5  |
| -47.5° | 1332.2 | 1249.9 | 1161.9 | 1068.2 | 969.2  | 859.1  | 726.0  | 586.4  | 455.1  | 323.3  | 265.7  |
| -50°   | 1094.2 | 1019.0 | 939.6  | 852.7  | 745.4  | 628.9  | 515.2  | 401.7  | 309.1  | 256.2  | 214.0  |
| -52.5° | 843.0  | 770.7  | 690.2  | 601.8  | 511.8  | 416.2  | 321.8  | 281.7  | 235.7  | 207.3  | 186.3  |
| -55°   | 572.2  | 512.2  | 448.1  | 374.1  | 304.8  | 273.9  | 239.6  | 212.6  | 195.9  | 176.7  | 164.2  |
| -57.5° | 341.4  | 299.9  | 275.6  | 248.8  | 219.5  | 203.2  | 191.4  | 177.8  | 166.2  | 154.9  | 144.4  |
| -60°   | 229.4  | 208.1  | 199.4  | 189.8  | 178.9  | 168.3  | 161.1  | 152.4  | 142.2  | 134.1  | 125.7  |
| -62.5° | 175.2  | 171.9  | 163.3  | 155.3  | 149.6  | 145.1  | 136.7  | 127.8  | 120.9  | 114.8  | 106.6  |
| -65°   | 133.2  | 126.8  | 122.6  | 122.4  | 119.2  | 112.6  | 106.1  | 102.9  | 99.3   | 93.4   | 87.1   |
| -67.5° | 106.1  | 102.9  | 100.1  | 96.2   | 93.0   | 89.6   | 87.8   | 84.5   | 80.2   | 74.9   | 71.3   |
| -70°   | 88.4   | 86.3   | 84.0   | 81.5   | 78.9   | 76.1   | 73.0   | 69.2   | 64.4   | 59.3   | 56.3   |
| -72.5° | 73.2   | 71.9   | 70.2   | 68.0   | 65.5   | 63.0   | 60.0   | 56.1   | 51.5   | 46.2   | 42.1   |
| -75°   | 60.5   | 59.8   | 58.8   | 56.8   | 54.5   | 51.9   | 48.8   | 44.0   | 38.1   | 30.9   | 25.9   |
| -77.5° | 46.4   | 46.3   | 46.0   | 44.4   | 42.9   | 41.7   | 39.3   | 32.4   | 25.7   | 19.7   | 16.7   |
| -80°   | 29.1   | 30.5   | 31.5   | 30.5   | 29.3   | 27.7   | 25.3   | 20.8   | 16.7   | 13.4   | 11.3   |
| -82.5° | 16.9   | 17.4   | 17.5   | 16.5   | 15.5   | 14.5   | 13.5   | 11.3   | 9.3    | 7.5    | 6.1    |
| -85°   | 4.7    | 4.5    | 4.4    | 4.7    | 5.0    | 5.2    | 5.2    | 4.6    | 4.0    | 3.5    | 3.2    |
| -87.5° | 0.8    | 0.8    | 0.8    | 0.8    | 0.8    | 0.8    | 0.7    | 0.9    | 1.0    | 1.1    | 1.2    |
| -90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |





REPORT NUMBER: P558683 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: GFLD-SA2C-940-U-WR-XX

**CANDELA DISTRIBUTION (continued):**

|        | 47.5°  | 50°    | 52.5°  | 55°   | 57.5° | 60°   | 62.5° | 65°   | 67.5° | 70°   | 72.5° |
|--------|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|
| 90°    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 87.5°  | 1.1    | 1.1    | 1.0    | 1.0   | 1.0   | 1.1   | 1.1   | 1.1   | 1.0   | 0.9   | 0.8   |
| 85°    | 3.2    | 3.1    | 2.9    | 2.6   | 2.4   | 2.2   | 2.2   | 2.2   | 2.0   | 1.8   | 1.6   |
| 82.5°  | 6.1    | 6.2    | 6.2    | 6.1   | 6.0   | 5.8   | 5.5   | 4.9   | 3.8   | 2.8   | 2.3   |
| 80°    | 12.7   | 13.4   | 13.3   | 12.5  | 11.0  | 9.5   | 9.2   | 8.5   | 7.0   | 5.5   | 4.2   |
| 77.5°  | 19.3   | 21.1   | 22.3   | 21.8  | 19.4  | 17.1  | 14.9  | 12.6  | 10.1  | 8.3   | 6.5   |
| 75°    | 26.4   | 28.8   | 30.6   | 30.6  | 28.1  | 24.7  | 21.7  | 18.6  | 14.9  | 11.2  | 8.8   |
| 72.5°  | 40.0   | 39.0   | 39.3   | 39.5  | 37.3  | 34.1  | 29.7  | 24.6  | 20.3  | 16.0  | 11.6  |
| 70°    | 53.7   | 50.1   | 47.7   | 47.2  | 46.1  | 43.7  | 39.3  | 32.7  | 25.7  | 20.7  | 15.7  |
| 67.5°  | 68.0   | 64.4   | 59.8   | 55.8  | 54.4  | 52.2  | 48.9  | 41.1  | 32.8  | 25.4  | 19.9  |
| 65°    | 82.7   | 78.5   | 74.1   | 68.3  | 63.8  | 60.8  | 57.4  | 49.1  | 39.7  | 31.2  | 23.9  |
| 62.5°  | 98.8   | 91.9   | 86.4   | 80.0  | 73.9  | 69.4  | 65.7  | 56.7  | 46.4  | 36.7  | 28.3  |
| 60°    | 116.5  | 107.6  | 98.6   | 91.1  | 83.8  | 77.4  | 72.2  | 64.4  | 53.7  | 41.9  | 32.6  |
| 57.5°  | 134.5  | 123.6  | 112.4  | 102.4 | 93.9  | 85.8  | 78.3  | 70.8  | 61.0  | 48.3  | 36.5  |
| 55°    | 152.5  | 140.4  | 126.1  | 113.9 | 103.8 | 94.8  | 85.0  | 76.6  | 67.8  | 55.0  | 39.5  |
| 52.5°  | 169.9  | 156.2  | 140.9  | 125.7 | 113.3 | 103.2 | 92.4  | 82.4  | 73.2  | 61.7  | 44.0  |
| 50°    | 191.2  | 171.3  | 155.3  | 138.8 | 122.8 | 110.9 | 99.3  | 88.5  | 78.5  | 67.8  | 48.2  |
| 47.5°  | 215.8  | 190.7  | 169.5  | 151.5 | 134.3 | 118.5 | 106.2 | 94.3  | 83.8  | 72.5  | 51.8  |
| 45°    | 264.9  | 212.7  | 186.1  | 164.7 | 145.1 | 127.7 | 113.1 | 99.7  | 88.6  | 74.6  | 54.9  |
| 42.5°  | 321.0  | 253.7  | 205.6  | 177.7 | 156.8 | 136.9 | 119.7 | 105.6 | 93.0  | 75.9  | 56.6  |
| 40°    | 456.0  | 305.0  | 231.9  | 195.0 | 168.5 | 145.5 | 127.3 | 111.5 | 96.7  | 76.7  | 57.3  |
| 37.5°  | 594.7  | 400.1  | 278.1  | 211.8 | 181.0 | 156.0 | 134.5 | 117.1 | 98.3  | 77.5  | 57.5  |
| 35°    | 735.5  | 524.5  | 323.3  | 242.1 | 195.9 | 166.1 | 141.1 | 122.8 | 101.9 | 78.3  | 57.2  |
| 32.5°  | 869.1  | 644.5  | 427.2  | 282.3 | 210.2 | 175.9 | 148.8 | 128.4 | 106.5 | 79.1  | 56.4  |
| 30°    | 983.7  | 761.2  | 530.1  | 320.7 | 230.2 | 188.1 | 157.3 | 133.8 | 112.0 | 79.9  | 55.6  |
| 27.5°  | 1087.9 | 870.2  | 626.9  | 395.0 | 263.3 | 199.8 | 165.3 | 138.8 | 118.2 | 81.9  | 55.7  |
| 25°    | 1183.8 | 963.1  | 720.3  | 476.6 | 294.4 | 211.0 | 172.6 | 143.5 | 123.2 | 86.1  | 55.8  |
| 22.5°  | 1268.6 | 1045.8 | 805.7  | 550.9 | 322.4 | 221.8 | 180.5 | 149.6 | 127.0 | 90.6  | 55.6  |
| 20°    | 1344.6 | 1121.0 | 883.4  | 619.4 | 368.5 | 245.0 | 189.0 | 155.0 | 130.4 | 95.2  | 55.3  |
| 17.5°  | 1413.0 | 1186.4 | 948.6  | 684.5 | 423.5 | 265.6 | 196.7 | 159.7 | 133.5 | 99.8  | 54.8  |
| 15°    | 1479.7 | 1241.9 | 1004.1 | 742.0 | 472.0 | 283.3 | 203.7 | 163.7 | 136.2 | 104.3 | 54.5  |
| 12.5°  | 1535.8 | 1289.4 | 1050.8 | 791.7 | 513.7 | 298.3 | 209.8 | 167.0 | 138.6 | 108.3 | 54.2  |
| 10°    | 1580.8 | 1328.6 | 1088.9 | 833.3 | 548.4 | 310.6 | 215.0 | 169.6 | 140.4 | 111.6 | 53.1  |
| 7.5°   | 1614.8 | 1359.3 | 1118.2 | 866.5 | 575.8 | 320.6 | 218.3 | 171.0 | 141.8 | 114.3 | 51.4  |
| 5°     | 1639.2 | 1382.4 | 1139.6 | 891.1 | 595.7 | 328.9 | 220.4 | 171.7 | 142.9 | 116.2 | 49.2  |
| 2.5°   | 1659.5 | 1398.6 | 1152.9 | 906.8 | 607.8 | 334.6 | 221.4 | 171.8 | 143.6 | 117.2 | 46.7  |
| 0°     | 1669.5 | 1406.0 | 1158.0 | 913.5 | 612.2 | 337.5 | 221.3 | 171.3 | 143.8 | 117.1 | 43.9  |
| -2.5°  | 1659.5 | 1398.6 | 1152.9 | 906.8 | 607.8 | 334.6 | 221.4 | 171.8 | 143.6 | 117.2 | 46.7  |
| -5°    | 1639.2 | 1382.4 | 1139.6 | 891.1 | 595.7 | 328.9 | 220.4 | 171.7 | 142.9 | 116.2 | 49.2  |
| -7.5°  | 1614.8 | 1359.3 | 1118.2 | 866.5 | 575.8 | 320.6 | 218.3 | 171.0 | 141.8 | 114.3 | 51.4  |
| -10°   | 1580.8 | 1328.6 | 1088.9 | 833.3 | 548.4 | 310.6 | 215.0 | 169.6 | 140.4 | 111.6 | 53.1  |
| -12.5° | 1535.8 | 1289.4 | 1050.8 | 791.7 | 513.7 | 298.3 | 209.8 | 167.0 | 138.6 | 108.3 | 54.2  |
| -15°   | 1479.7 | 1241.9 | 1004.1 | 742.0 | 472.0 | 283.3 | 203.7 | 163.7 | 136.2 | 104.3 | 54.5  |
| -17.5° | 1413.0 | 1186.4 | 948.6  | 684.5 | 423.5 | 265.6 | 196.7 | 159.7 | 133.5 | 99.8  | 54.8  |
| -20°   | 1344.6 | 1121.0 | 883.4  | 619.4 | 368.5 | 245.0 | 189.0 | 155.0 | 130.4 | 95.2  | 55.3  |



REPORT NUMBER: P558683 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: GFLD-SA2C-940-U-WR-XX

**CANDELA DISTRIBUTION (continued):**

|        | 47.5°  | 50°    | 52.5° | 55°   | 57.5° | 60°   | 62.5° | 65°   | 67.5° | 70°  | 72.5° |
|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|------|-------|
| -22.5° | 1268.6 | 1045.8 | 805.7 | 550.9 | 322.4 | 221.8 | 180.5 | 149.6 | 127.0 | 90.6 | 55.6  |
| -25°   | 1183.8 | 963.1  | 720.3 | 476.6 | 294.4 | 211.0 | 172.6 | 143.5 | 123.2 | 86.1 | 55.8  |
| -27.5° | 1087.9 | 870.2  | 626.9 | 395.0 | 263.3 | 199.8 | 165.3 | 138.8 | 118.2 | 81.9 | 55.7  |
| -30°   | 983.7  | 761.2  | 530.1 | 320.7 | 230.2 | 188.1 | 157.3 | 133.8 | 112.0 | 79.9 | 55.6  |
| -32.5° | 869.1  | 644.5  | 427.2 | 282.3 | 210.2 | 175.9 | 148.8 | 128.4 | 106.5 | 79.1 | 56.4  |
| -35°   | 735.5  | 524.5  | 323.3 | 242.1 | 195.9 | 166.1 | 141.1 | 122.8 | 101.9 | 78.3 | 57.2  |
| -37.5° | 594.7  | 400.1  | 278.1 | 211.8 | 181.0 | 156.0 | 134.5 | 117.1 | 98.3  | 77.5 | 57.5  |
| -40°   | 456.0  | 305.0  | 231.9 | 195.0 | 168.5 | 145.5 | 127.3 | 111.5 | 96.7  | 76.7 | 57.3  |
| -42.5° | 321.0  | 253.7  | 205.6 | 177.7 | 156.8 | 136.9 | 119.7 | 105.6 | 93.0  | 75.9 | 56.6  |
| -45°   | 264.9  | 212.7  | 186.1 | 164.7 | 145.1 | 127.7 | 113.1 | 99.7  | 88.6  | 74.6 | 54.9  |
| -47.5° | 215.8  | 190.7  | 169.5 | 151.5 | 134.3 | 118.5 | 106.2 | 94.3  | 83.8  | 72.5 | 51.8  |
| -50°   | 191.2  | 171.3  | 155.3 | 138.8 | 122.8 | 110.9 | 99.3  | 88.5  | 78.5  | 67.8 | 48.2  |
| -52.5° | 169.9  | 156.2  | 140.9 | 125.7 | 113.3 | 103.2 | 92.4  | 82.4  | 73.2  | 61.7 | 44.0  |
| -55°   | 152.5  | 140.4  | 126.1 | 113.9 | 103.8 | 94.8  | 85.0  | 76.6  | 67.8  | 55.0 | 39.5  |
| -57.5° | 134.5  | 123.6  | 112.4 | 102.4 | 93.9  | 85.8  | 78.3  | 70.8  | 61.0  | 48.3 | 36.5  |
| -60°   | 116.5  | 107.6  | 98.6  | 91.1  | 83.8  | 77.4  | 72.2  | 64.4  | 53.7  | 41.9 | 32.6  |
| -62.5° | 98.8   | 91.9   | 86.4  | 80.0  | 73.9  | 69.4  | 65.7  | 56.7  | 46.4  | 36.7 | 28.3  |
| -65°   | 82.7   | 78.5   | 74.1  | 68.3  | 63.8  | 60.8  | 57.4  | 49.1  | 39.7  | 31.2 | 23.9  |
| -67.5° | 68.0   | 64.4   | 59.8  | 55.8  | 54.4  | 52.2  | 48.9  | 41.1  | 32.8  | 25.4 | 19.9  |
| -70°   | 53.7   | 50.1   | 47.7  | 47.2  | 46.1  | 43.7  | 39.3  | 32.7  | 25.7  | 20.7 | 15.7  |
| -72.5° | 40.0   | 39.0   | 39.3  | 39.5  | 37.3  | 34.1  | 29.7  | 24.6  | 20.3  | 16.0 | 11.6  |
| -75°   | 26.4   | 28.8   | 30.6  | 30.6  | 28.1  | 24.7  | 21.7  | 18.6  | 14.9  | 11.2 | 8.8   |
| -77.5° | 19.3   | 21.1   | 22.3  | 21.8  | 19.4  | 17.1  | 14.9  | 12.6  | 10.1  | 8.3  | 6.5   |
| -80°   | 12.7   | 13.4   | 13.3  | 12.5  | 11.0  | 9.5   | 9.2   | 8.5   | 7.0   | 5.5  | 4.2   |
| -82.5° | 6.1    | 6.2    | 6.2   | 6.1   | 6.0   | 5.8   | 5.5   | 4.9   | 3.8   | 2.8  | 2.3   |
| -85°   | 3.2    | 3.1    | 2.9   | 2.6   | 2.4   | 2.2   | 2.2   | 2.2   | 2.0   | 1.8  | 1.6   |
| -87.5° | 1.1    | 1.1    | 1.0   | 1.0   | 1.0   | 1.1   | 1.1   | 1.1   | 1.0   | 0.9  | 0.8   |
| -90°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   |



REPORT NUMBER: P558683 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: GFLD-SA2C-940-U-WR-XX

**CANDELA DISTRIBUTION (continued):**

|        | 75°  | 77.5° | 80°  | 82.5° | 85° | 87.5° | 90° |
|--------|------|-------|------|-------|-----|-------|-----|
| 90°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0 | 0.0   | 0.0 |
| 87.5°  | 0.7  | 0.6   | 0.5  | 0.3   | 0.2 | 0.1   | 0.0 |
| 85°    | 1.3  | 1.1   | 0.9  | 0.7   | 0.5 | 0.2   | 0.0 |
| 82.5°  | 2.0  | 1.7   | 1.4  | 1.0   | 0.7 | 0.3   | 0.0 |
| 80°    | 2.8  | 2.2   | 1.8  | 1.4   | 0.9 | 0.5   | 0.0 |
| 77.5°  | 4.7  | 3.1   | 2.2  | 1.7   | 1.1 | 0.6   | 0.0 |
| 75°    | 6.6  | 4.4   | 2.8  | 2.0   | 1.3 | 0.7   | 0.0 |
| 72.5°  | 8.4  | 5.7   | 3.7  | 2.3   | 1.6 | 0.8   | 0.0 |
| 70°    | 10.4 | 7.0   | 4.5  | 2.7   | 1.8 | 0.9   | 0.0 |
| 67.5°  | 13.5 | 8.2   | 5.3  | 3.2   | 2.0 | 1.0   | 0.0 |
| 65°    | 16.5 | 9.8   | 6.1  | 3.7   | 2.2 | 1.1   | 0.0 |
| 62.5°  | 19.3 | 11.8  | 6.9  | 4.2   | 2.4 | 1.2   | 0.0 |
| 60°    | 21.8 | 13.6  | 7.5  | 4.6   | 2.6 | 1.3   | 0.0 |
| 57.5°  | 24.4 | 15.2  | 8.6  | 5.0   | 2.9 | 1.4   | 0.0 |
| 55°    | 26.6 | 16.6  | 9.6  | 5.4   | 3.1 | 1.5   | 0.0 |
| 52.5°  | 28.5 | 17.9  | 10.4 | 5.7   | 3.3 | 1.6   | 0.0 |
| 50°    | 30.2 | 19.1  | 11.2 | 6.0   | 3.6 | 1.7   | 0.0 |
| 47.5°  | 31.7 | 20.0  | 11.8 | 6.3   | 3.8 | 1.8   | 0.0 |
| 45°    | 34.2 | 20.7  | 12.2 | 6.7   | 4.0 | 1.8   | 0.0 |
| 42.5°  | 36.4 | 21.2  | 12.6 | 7.0   | 4.2 | 1.9   | 0.0 |
| 40°    | 38.1 | 21.4  | 12.8 | 7.3   | 4.4 | 2.0   | 0.0 |
| 37.5°  | 39.4 | 21.4  | 12.9 | 7.6   | 4.6 | 2.1   | 0.0 |
| 35°    | 40.2 | 21.9  | 12.9 | 8.0   | 4.8 | 2.1   | 0.0 |
| 32.5°  | 40.4 | 22.5  | 12.7 | 8.3   | 4.9 | 2.2   | 0.0 |
| 30°    | 39.7 | 22.8  | 12.4 | 8.6   | 5.1 | 2.3   | 0.0 |
| 27.5°  | 38.6 | 22.8  | 12.7 | 8.8   | 5.2 | 2.3   | 0.0 |
| 25°    | 37.2 | 22.6  | 13.1 | 9.1   | 5.4 | 2.4   | 0.0 |
| 22.5°  | 35.5 | 22.6  | 13.4 | 9.3   | 5.5 | 2.4   | 0.0 |
| 20°    | 33.5 | 23.7  | 13.8 | 9.5   | 5.6 | 2.4   | 0.0 |
| 17.5°  | 33.2 | 24.6  | 14.1 | 9.7   | 5.7 | 2.5   | 0.0 |
| 15°    | 33.8 | 25.4  | 14.4 | 9.9   | 5.8 | 2.5   | 0.0 |
| 12.5°  | 34.4 | 26.1  | 14.6 | 10.0  | 5.8 | 2.5   | 0.0 |
| 10°    | 35.0 | 26.6  | 14.9 | 10.1  | 5.9 | 2.6   | 0.0 |
| 7.5°   | 35.4 | 27.1  | 15.1 | 10.2  | 5.9 | 2.6   | 0.0 |
| 5°     | 35.8 | 27.4  | 15.3 | 10.3  | 6.0 | 2.6   | 0.0 |
| 2.5°   | 36.0 | 27.5  | 15.4 | 10.3  | 6.0 | 2.6   | 0.0 |
| 0°     | 36.2 | 27.6  | 15.5 | 10.3  | 6.0 | 2.6   | 0.0 |
| -2.5°  | 36.0 | 27.5  | 15.4 | 10.3  | 6.0 | 2.6   | 0.0 |
| -5°    | 35.8 | 27.4  | 15.3 | 10.3  | 6.0 | 2.6   | 0.0 |
| -7.5°  | 35.4 | 27.1  | 15.1 | 10.2  | 5.9 | 2.6   | 0.0 |
| -10°   | 35.0 | 26.6  | 14.9 | 10.1  | 5.9 | 2.6   | 0.0 |
| -12.5° | 34.4 | 26.1  | 14.6 | 10.0  | 5.8 | 2.5   | 0.0 |
| -15°   | 33.8 | 25.4  | 14.4 | 9.9   | 5.8 | 2.5   | 0.0 |
| -17.5° | 33.2 | 24.6  | 14.1 | 9.7   | 5.7 | 2.5   | 0.0 |
| -20°   | 33.5 | 23.7  | 13.8 | 9.5   | 5.6 | 2.4   | 0.0 |



REPORT NUMBER: P558683 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: GFLD-SA2C-940-U-WR-XX

**CANDELA DISTRIBUTION (continued):**

|        | 75°  | 77.5° | 80°  | 82.5° | 85° | 87.5° | 90° |
|--------|------|-------|------|-------|-----|-------|-----|
| -22.5° | 35.5 | 22.6  | 13.4 | 9.3   | 5.5 | 2.4   | 0.0 |
| -25°   | 37.2 | 22.6  | 13.1 | 9.1   | 5.4 | 2.4   | 0.0 |
| -27.5° | 38.6 | 22.8  | 12.7 | 8.8   | 5.2 | 2.3   | 0.0 |
| -30°   | 39.7 | 22.8  | 12.4 | 8.6   | 5.1 | 2.3   | 0.0 |
| -32.5° | 40.4 | 22.5  | 12.7 | 8.3   | 4.9 | 2.2   | 0.0 |
| -35°   | 40.2 | 21.9  | 12.9 | 8.0   | 4.8 | 2.1   | 0.0 |
| -37.5° | 39.4 | 21.4  | 12.9 | 7.6   | 4.6 | 2.1   | 0.0 |
| -40°   | 38.1 | 21.4  | 12.8 | 7.3   | 4.4 | 2.0   | 0.0 |
| -42.5° | 36.4 | 21.2  | 12.6 | 7.0   | 4.2 | 1.9   | 0.0 |
| -45°   | 34.2 | 20.7  | 12.2 | 6.7   | 4.0 | 1.8   | 0.0 |
| -47.5° | 31.7 | 20.0  | 11.8 | 6.3   | 3.8 | 1.8   | 0.0 |
| -50°   | 30.2 | 19.1  | 11.2 | 6.0   | 3.6 | 1.7   | 0.0 |
| -52.5° | 28.5 | 17.9  | 10.4 | 5.7   | 3.3 | 1.6   | 0.0 |
| -55°   | 26.6 | 16.6  | 9.6  | 5.4   | 3.1 | 1.5   | 0.0 |
| -57.5° | 24.4 | 15.2  | 8.6  | 5.0   | 2.9 | 1.4   | 0.0 |
| -60°   | 21.8 | 13.6  | 7.5  | 4.6   | 2.6 | 1.3   | 0.0 |
| -62.5° | 19.3 | 11.8  | 6.9  | 4.2   | 2.4 | 1.2   | 0.0 |
| -65°   | 16.5 | 9.8   | 6.1  | 3.7   | 2.2 | 1.1   | 0.0 |
| -67.5° | 13.5 | 8.2   | 5.3  | 3.2   | 2.0 | 1.0   | 0.0 |
| -70°   | 10.4 | 7.0   | 4.5  | 2.7   | 1.8 | 0.9   | 0.0 |
| -72.5° | 8.4  | 5.7   | 3.7  | 2.3   | 1.6 | 0.8   | 0.0 |
| -75°   | 6.6  | 4.4   | 2.8  | 2.0   | 1.3 | 0.7   | 0.0 |
| -77.5° | 4.7  | 3.1   | 2.2  | 1.7   | 1.1 | 0.6   | 0.0 |
| -80°   | 2.8  | 2.2   | 1.8  | 1.4   | 0.9 | 0.5   | 0.0 |
| -82.5° | 2.0  | 1.7   | 1.4  | 1.0   | 0.7 | 0.3   | 0.0 |
| -85°   | 1.3  | 1.1   | 0.9  | 0.7   | 0.5 | 0.2   | 0.0 |
| -87.5° | 0.7  | 0.6   | 0.5  | 0.3   | 0.2 | 0.1   | 0.0 |
| -90°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0 | 0.0   | 0.0 |

(END OF REPORT)