

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P821132

Luminaire Tested: **TT-D2-830-24VDC-T4-PM-HSS**

Issue Date: 12/2/2020



**Test Information**

Test Method: LM-79-08  
Report Number: P821132  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2010-017-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 12/2/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TT-D2-830-24VDC-T4-PM-HSS  
Description: TOPTIER LED SITE LUMINAIRE  
3000K, 80 CRI LEDS AND DRIVE LANE DISTRIBUTION WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3512.9 lumens  
Efficiency: N/A  
Efficacy: 92.4 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U1 - G3

Input Watts (W): 38  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

REPORT NUMBER: P821132  
 CATALOG NUMBER: TT-D2-830-24VDC-T4-PM-HSS

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 1.4 fc  
 Type IV - Short - N/A

REPORT NUMBER: P821132  
CATALOG NUMBER: TT-D2-830-24VDC-T4-PM-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral    - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P821132  
 CATALOG NUMBER: TT-D2-830-24VDC-T4-PM-HSS


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	638.3	0.7	639.0
	% Fixture	18.2	0.0	18.2
<b>Street Side</b>	Lumens	2866.2	7.8	2873.9
	% Fixture	81.6	0.2	81.8
<b>Total</b>	Lumens	3504.4	8.5	3512.9
	% Fixture	99.8	0.2	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	9.9	0.3
10°-20°	36.9	1.1
20°-30°	85.2	2.4
30°-40°	181.8	5.2
40°-50°	380.4	10.8
50°-60°	721.7	20.5
60°-70°	982.2	28.0
70°-80°	844.4	24.0
80°-90°	261.8	7.5
90°-100°	5.5	0.2
100°-110°	1.6	0.0
110°-120°	0.4	0.0
120°-130°	0.3	0.0
130°-140°	0.2	0.0
140°-150°	0.2	0.0
150°-160°	0.1	0.0
160°-170°	0.1	0.0
170°-180°	0.0	0.0
0°-90°	3504.4	99.8
0°-180°	3512.9	100.0




REPORT NUMBER: P821132  
 CATALOG NUMBER: TT-D2-830-24VDC-T4-PM-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	80.1	2.3			
FM (30°-60°)	965.5	27.5			
FH (60°-80°)	1590.9	45.3			G1/1800
FVH (80°-90°)	229.8	6.5			G3/500
BL (0°-30°)	52.0	1.5	B0/110		
BM (30°-60°)	318.4	9.1	B1/1000		
BH (60°-80°)	235.8	6.7	B1/500		G1/500
BVH (80°-90°)	32.1	0.9			G1/100
UL (90°-100°)	5.5	0.2		U1/10	
UH (100°-180°)	2.9	0.1		U1/10	

**BUG Rating: B1-U1-G3**  
 Type IV Short





REPORT NUMBER: P821132

CATALOG NUMBER: TT-D2-830-24VDC-T4-PM-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	41°	45°	55°	65°	75°	85°
0°	96.1	96.1	96.1	96.1	96.1	96.1	96.1	96.1	96.1	96.1	96.1
2.5°	104.3	103.6	103.6	102.8	102.8	101.3	101.3	100.6	99.8	99.1	97.6
5°	111.8	111.0	111.0	110.3	109.5	108.0	107.3	105.8	104.3	102.8	101.3
7.5°	120.7	120.0	120.0	119.2	117.7	115.5	114.8	112.5	110.3	108.0	105.8
10°	131.9	131.1	131.1	129.7	128.2	125.9	124.4	121.5	119.2	115.5	111.8
12.5°	143.8	143.1	143.1	141.6	138.6	137.1	135.6	131.9	128.2	123.7	119.2
15°	157.2	157.2	157.2	156.5	153.5	150.5	149.0	144.6	140.1	133.4	127.4
17.5°	174.4	173.6	173.6	172.1	168.4	166.9	164.7	159.5	152.8	145.3	137.9
20°	195.2	194.5	193.0	192.2	188.5	187.0	184.1	178.1	169.1	159.5	149.0
22.5°	216.1	216.1	215.3	216.1	213.1	211.6	207.9	199.7	189.3	175.1	162.4
25°	239.9	240.7	242.2	244.4	240.7	239.2	236.2	225.8	213.1	195.2	177.3
27.5°	269.7	269.7	273.5	277.2	274.2	273.5	269.0	257.8	239.9	218.3	197.5
30°	301.8	302.5	308.5	315.2	313.7	313.7	310.0	297.3	275.7	250.4	221.3
32.5°	339.0	342.0	348.0	355.4	360.6	360.6	359.2	345.7	320.4	286.1	250.4
35°	388.2	383.0	394.2	405.4	416.5	418.8	419.5	406.8	377.8	334.6	286.1
37.5°	430.7	429.9	447.1	466.5	485.1	492.5	494.8	482.9	445.6	389.0	324.9
40°	479.9	484.3	507.4	536.5	567.8	580.5	586.4	573.0	526.8	453.8	369.6
42.5°	531.3	544.7	573.8	617.7	665.4	684.0	690.7	678.1	623.7	535.0	426.2
45°	591.6	610.3	649.0	711.6	774.2	801.8	816.7	812.2	756.3	646.0	499.2
47.5°	666.2	679.6	732.5	816.7	905.3	950.8	971.7	984.3	904.6	760.8	563.3
50°	750.4	752.6	825.6	932.2	1061.8	1122.2	1158.7	1152.7	1058.1	892.7	644.5
52.5°	835.3	833.1	928.4	1073.0	1242.9	1321.9	1346.5	1371.1	1277.9	1093.9	774.9
55°	932.2	927.7	1047.7	1231.0	1441.9	1546.2	1615.5	1649.7	1503.0	1226.5	831.6
57.5°	1012.6	1026.8	1177.3	1397.9	1692.2	1823.4	1868.8	1850.2	1626.6	1293.6	859.1
60°	1114.7	1135.6	1307.0	1616.2	1909.1	2006.7	2048.4	1963.5	1705.6	1344.2	878.5
62.5°	1210.9	1237.7	1449.3	1793.6	2044.7	2134.1	2144.5	2052.1	1816.7	1444.1	935.2
65°	1301.0	1331.6	1590.9	1898.6	2163.1	2237.7	2255.5	2182.5	1934.4	1503.0	957.5
67.5°	1383.7	1415.8	1663.9	1982.8	2216.1	2273.4	2277.2	2166.1	1897.9	1472.4	921.7
70°	1447.1	1461.2	1698.9	1980.6	2153.5	2175.8	2160.9	2049.1	1812.2	1409.8	870.3
72.5°	1459.7	1470.2	1650.5	1870.3	1979.8	2000.7	1988.8	1890.4	1677.3	1298.0	786.9
75°	1395.7	1397.9	1520.1	1672.1	1751.8	1777.2	1761.5	1670.6	1474.6	1140.1	677.3
77.5°	1228.0	1232.5	1306.2	1408.3	1475.4	1497.0	1485.1	1401.6	1235.4	957.5	560.3
80°	973.2	982.1	1035.0	1105.8	1166.9	1189.2	1175.1	1108.0	972.4	752.6	437.4
82.5°	663.2	674.4	722.8	781.7	835.3	856.9	845.0	802.5	701.2	542.5	312.2
85°	335.3	347.2	397.2	452.3	499.2	522.3	518.6	500.7	431.4	334.6	188.5
87.5°	52.9	58.1	79.0	105.1	134.1	155.7	142.3	140.8	111.8	89.4	45.5
90°	21.6	21.6	20.9	20.1	17.9	16.4	15.6	12.7	9.7	6.0	2.2
92.5°	19.4	19.4	18.6	17.1	15.6	14.9	13.4	11.2	8.2	5.2	2.2
95°	15.6	15.6	14.9	14.2	12.7	11.9	10.4	8.9	6.7	4.5	2.2
97.5°	11.9	11.9	11.2	10.4	9.7	8.2	8.2	6.7	4.5	3.0	1.5
100°	8.9	8.9	8.2	7.5	6.7	6.0	6.0	4.5	3.0	2.2	1.5
102.5°	6.0	6.0	6.0	5.2	4.5	4.5	3.7	3.0	2.2	1.5	1.5
105°	3.7	3.7	3.7	3.7	3.0	2.2	2.2	1.5	1.5	1.5	1.5
107.5°	2.2	2.2	2.2	2.2	1.5	1.5	1.5	1.5	1.5	1.5	1.5
110°	1.5	1.5	1.5	0.7	0.7	0.7	0.7	0.7	0.7	1.5	0.7



REPORT NUMBER: P821132  
 CATALOG NUMBER: TT-D2-830-24VDC-T4-PM-HSS

**CANDELA DISTRIBUTION (continued):**

	0°	5°	15°	25°	35°	41°	45°	55°	65°	75°	85°
112.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
115°	0.0	0.0	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
117.5°	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7	0.7
120°	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7	0.7
122.5°	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7	0.7
125°	0.0	0.0	0.0	0.7	0.0	0.7	0.7	0.7	0.7	0.7	0.7
127.5°	0.0	0.0	0.0	0.7	0.0	0.0	0.7	0.7	0.7	0.7	0.7
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7
142.5°	0.7	0.7	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7
145°	0.7	0.7	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7
147.5°	0.7	0.7	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7
175°	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7	0.7
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P821132

CATALOG NUMBER: TT-D2-830-24VDC-T4-PM-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	96.1	96.1	96.1	96.1	96.1	96.1	96.1	96.1	96.1	96.1	96.1
2.5°	97.6	96.9	95.4	94.6	93.1	93.1	92.4	91.7	91.7	91.7	91.7
5°	99.8	99.1	97.6	96.1	94.6	93.1	92.4	91.7	91.7	91.7	90.9
7.5°	104.3	102.8	100.6	98.4	96.1	94.6	93.9	93.1	92.4	92.4	92.4
10°	109.5	108.0	104.3	102.1	99.1	96.9	96.1	95.4	94.6	94.6	94.6
12.5°	116.2	114.0	109.5	105.8	102.8	100.6	99.1	98.4	98.4	97.6	98.4
15°	124.4	121.5	115.5	111.0	107.3	105.1	103.6	102.8	102.8	102.8	102.1
17.5°	133.4	129.7	122.2	117.0	112.5	110.3	108.8	108.0	108.0	108.0	108.0
20°	143.8	138.6	130.4	123.7	119.2	116.2	114.8	114.8	114.0	114.8	114.8
22.5°	155.0	149.0	138.6	131.1	125.2	122.2	120.7	120.7	120.7	121.5	122.2
25°	168.4	161.0	148.3	138.6	131.9	128.9	127.4	128.2	128.2	128.9	128.9
27.5°	186.3	175.1	159.5	147.5	140.1	136.4	134.9	135.6	136.4	136.4	136.4
30°	206.4	193.0	171.4	158.7	149.8	145.3	143.8	144.6	145.3	146.8	146.0
32.5°	231.0	214.6	189.3	171.4	161.7	156.5	155.0	154.2	155.7	157.2	157.2
35°	260.8	239.9	210.1	189.3	175.1	168.4	166.9	166.2	166.9	168.4	169.9
37.5°	292.8	267.5	231.0	209.4	193.7	186.3	182.6	179.6	180.3	181.1	183.3
40°	329.4	298.1	254.8	228.8	214.6	205.7	200.4	196.0	197.5	197.5	198.2
42.5°	375.6	336.1	284.6	251.9	237.0	227.3	219.1	213.9	210.9	211.6	208.6
45°	435.9	386.7	321.9	284.6	263.8	248.9	239.2	228.8	221.3	222.8	218.3
47.5°	485.8	427.0	356.9	315.9	293.6	275.0	254.8	239.9	229.5	228.0	225.0
50°	546.9	476.1	397.2	350.2	326.4	298.1	274.2	248.9	231.7	227.3	228.0
52.5°	649.8	562.6	454.5	396.4	354.7	321.2	284.6	249.6	226.5	219.8	222.1
55°	687.0	591.6	484.3	434.4	393.4	341.3	289.1	241.4	211.6	205.7	206.4
57.5°	695.2	591.6	486.6	446.3	412.1	357.7	286.9	222.8	183.3	178.1	177.3
60°	699.7	587.9	478.4	437.4	400.1	342.0	257.8	179.6	140.8	137.1	134.9
62.5°	741.4	619.2	486.6	430.7	377.8	300.3	196.0	114.8	78.2	77.5	76.0
65°	754.1	630.4	497.0	435.2	353.2	233.2	116.2	38.7	8.2	8.9	7.5
67.5°	722.8	605.1	482.1	428.5	345.7	227.3	111.8	32.8	0.0	0.0	0.0
70°	679.6	568.5	456.0	405.4	330.1	218.3	109.5	32.8	0.0	0.0	0.0
72.5°	611.0	516.4	414.3	374.1	303.3	200.4	102.1	31.3	0.0	0.0	0.0
75°	530.5	449.3	362.9	331.6	269.0	175.9	91.7	28.3	0.0	0.0	0.0
77.5°	444.1	374.8	303.3	279.4	227.3	149.8	77.5	23.8	0.0	0.0	0.0
80°	348.7	296.6	239.2	222.8	179.6	119.2	61.8	18.6	0.0	0.0	0.0
82.5°	251.1	215.3	176.6	163.2	131.9	86.4	44.7	12.7	0.0	0.0	0.0
85°	155.0	134.9	114.0	105.8	83.5	53.7	26.8	6.7	0.0	0.0	0.0
87.5°	46.2	44.7	40.2	39.5	28.3	16.4	6.0	0.7	0.0	0.0	0.0
90°	0.7	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.7	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.7	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P821132  
 CATALOG NUMBER: TT-D2-830-24VDC-T4-PM-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
112.5°	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)