

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P400572

Luminaire Tested: **TT-D4-830-U-DL**

Issue Date: 5/19/2020

Test Information

Test Method: LM-79-08
Report Number: P400572
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1908-473-26)
Test Lab: INNOVATION CENTER
Issue Date: 5/19/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TT-D4-830-U-DL
Description: TOPTIER LED PARKING GARAGE LUMINAIRE
3000K, 80 CRI LEDS AND DRIVE LANE DISTRIBUTION
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5622 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Luminous Opening: Circular (Dia: 1.12' x H: 0')
IES Classification: Type IV - Short - Non-Cutoff
BUG Rating: B2 - U0 - G3


Input Watts (W): 59.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



REPORT NUMBER: P400572
 CATALOG NUMBER: TT-D4-830-U-DL

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 4.3 fc
 Type IV - Short - Non-Cutoff

REPORT NUMBER: P400572
CATALOG NUMBER: TT-D4-830-U-DL

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P400572

CATALOG NUMBER: TT-D4-830-U-DL


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 1638.3 | 0.0 | 1638.3 |
| | % Fixture | 29.1 | 0.0 | 29.1 |
| Street Side | Lumens | 3983.7 | 0.0 | 3983.7 |
| | % Fixture | 70.9 | 0.0 | 70.9 |
| Total | Lumens | 5622.0 | 0.0 | 5622.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

Coefficient of Utilization

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 12.5 | 0.2 |
| 10°-20° | 46.6 | 0.8 |
| 20°-30° | 110.3 | 2.0 |
| 30°-40° | 249.6 | 4.4 |
| 40°-50° | 556.5 | 9.9 |
| 50°-60° | 1118.7 | 19.9 |
| 60°-70° | 1643.1 | 29.2 |
| 70°-80° | 1444.8 | 25.7 |
| 80°-90° | 439.9 | 7.8 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 5622.0 | 100.0 |
| 0°-180° | 5622.0 | 100.0 |



REPORT NUMBER: P400572


CATALOG NUMBER: TT-D4-830-U-DL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|------|-------------|--------|-----------|-------------------------|------|---------|
| | | | | B | U | G |
| FL | (0°-30°) | 98.2 | 1.7 | | | |
| FM | (30°-60°) | 1316.6 | 23.4 | | | |
| FH | (60°-80°) | 2243.1 | 39.9 | | | G2/5000 |
| FVH | (80°-90°) | 325.9 | 5.8 | | | G3/500 |
| BL | (0°-30°) | 71.3 | 1.3 | B0/110 | | |
| BM | (30°-60°) | 608.2 | 10.8 | B1/1000 | | |
| BH | (60°-80°) | 844.8 | 15.0 | B2/1000 | | G2/1000 |
| BVH | (80°-90°) | 113.9 | 2.0 | | | G2/225 |
| UL | (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH | (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G3

Type IV Short





REPORT NUMBER: P400572

CATALOG NUMBER: TT-D4-830-U-DL

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 42.5° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 121.9 | 121.9 | 121.9 | 121.9 | 121.9 | 121.9 | 121.9 | 121.9 | 121.9 | 121.9 | 121.9 |
| 2.5° | 127.2 | 126.2 | 126.2 | 126.2 | 125.1 | 125.1 | 125.1 | 125.1 | 124.0 | 124.0 | 124.0 |
| 5° | 134.6 | 133.5 | 134.6 | 132.5 | 131.4 | 131.4 | 130.4 | 130.4 | 129.3 | 128.3 | 127.2 |
| 7.5° | 145.1 | 144.0 | 144.0 | 141.9 | 140.9 | 139.8 | 139.8 | 137.7 | 136.7 | 134.6 | 132.5 |
| 10° | 156.6 | 156.6 | 155.6 | 154.5 | 152.4 | 150.3 | 150.3 | 147.2 | 146.1 | 143.0 | 139.8 |
| 12.5° | 170.3 | 170.3 | 170.3 | 168.2 | 166.1 | 165.0 | 162.9 | 160.8 | 157.7 | 152.4 | 149.3 |
| 15° | 187.1 | 187.1 | 187.1 | 185.0 | 182.9 | 180.8 | 179.8 | 175.6 | 170.3 | 165.0 | 158.7 |
| 17.5° | 208.1 | 206.0 | 206.0 | 203.9 | 201.8 | 200.8 | 198.7 | 194.5 | 187.1 | 180.8 | 172.4 |
| 20° | 231.3 | 230.2 | 229.2 | 229.2 | 227.1 | 225.0 | 223.9 | 217.6 | 209.2 | 197.6 | 187.1 |
| 22.5° | 257.6 | 256.5 | 256.5 | 258.6 | 257.6 | 254.4 | 254.4 | 244.9 | 233.4 | 219.7 | 203.9 |
| 25° | 290.1 | 289.1 | 291.2 | 295.4 | 295.4 | 293.3 | 290.1 | 280.7 | 263.9 | 244.9 | 226.0 |
| 27.5° | 325.9 | 324.8 | 329.0 | 336.4 | 338.5 | 335.4 | 333.2 | 322.7 | 303.8 | 278.6 | 251.3 |
| 30° | 369.0 | 370.0 | 381.6 | 390.0 | 395.3 | 393.2 | 392.1 | 380.6 | 350.1 | 320.6 | 284.9 |
| 32.5° | 421.6 | 418.4 | 433.1 | 446.8 | 456.2 | 461.5 | 458.4 | 444.7 | 418.4 | 372.1 | 326.9 |
| 35° | 477.3 | 478.3 | 496.2 | 516.2 | 538.2 | 540.3 | 546.7 | 533.0 | 497.2 | 442.6 | 379.5 |
| 37.5° | 549.8 | 541.4 | 564.5 | 602.4 | 628.7 | 651.8 | 647.6 | 639.2 | 597.1 | 524.6 | 438.4 |
| 40° | 615.0 | 612.9 | 645.5 | 698.0 | 746.4 | 780.0 | 784.2 | 773.7 | 718.0 | 615.0 | 501.5 |
| 42.5° | 689.6 | 695.9 | 741.1 | 813.7 | 887.3 | 935.6 | 924.1 | 918.8 | 853.6 | 722.2 | 587.7 |
| 45° | 765.3 | 786.3 | 844.2 | 949.3 | 1035.5 | 1104.9 | 1124.9 | 1107.0 | 1027.1 | 891.5 | 697.0 |
| 47.5° | 856.8 | 885.2 | 956.6 | 1098.6 | 1239.4 | 1320.4 | 1324.6 | 1378.2 | 1257.3 | 1054.4 | 810.5 |
| 50° | 977.7 | 990.3 | 1090.2 | 1263.6 | 1457.0 | 1570.6 | 1603.2 | 1604.2 | 1483.3 | 1218.4 | 938.8 |
| 52.5° | 1096.5 | 1105.9 | 1237.3 | 1461.3 | 1724.1 | 1853.4 | 1860.7 | 1901.7 | 1736.7 | 1483.3 | 1122.7 |
| 55° | 1239.4 | 1235.2 | 1416.0 | 1685.2 | 1995.3 | 2183.5 | 2238.1 | 2293.9 | 2083.6 | 1692.5 | 1227.9 |
| 57.5° | 1378.2 | 1371.9 | 1589.5 | 1942.7 | 2366.4 | 2553.5 | 2598.7 | 2558.8 | 2246.5 | 1779.8 | 1279.4 |
| 60° | 1506.5 | 1528.5 | 1793.5 | 2227.6 | 2653.4 | 2832.1 | 2862.6 | 2754.3 | 2351.7 | 1847.1 | 1312.0 |
| 62.5° | 1640.0 | 1684.1 | 2004.8 | 2465.2 | 2873.1 | 3001.4 | 3003.5 | 2876.3 | 2527.2 | 1977.4 | 1418.2 |
| 65° | 1765.1 | 1835.5 | 2168.8 | 2668.1 | 3026.6 | 3154.8 | 3169.6 | 3055.0 | 2699.6 | 2091.0 | 1436.0 |
| 67.5° | 1875.5 | 1969.0 | 2282.3 | 2777.4 | 3130.7 | 3213.7 | 3221.1 | 3056.0 | 2658.6 | 2044.7 | 1386.6 |
| 70° | 1964.8 | 2040.5 | 2352.7 | 2779.5 | 3058.1 | 3081.2 | 3076.0 | 2900.4 | 2545.1 | 1953.2 | 1303.6 |
| 72.5° | 1999.5 | 2061.5 | 2319.1 | 2649.2 | 2844.7 | 2839.5 | 2835.3 | 2673.4 | 2358.0 | 1800.8 | 1183.7 |
| 75° | 1950.1 | 1968.0 | 2135.1 | 2370.6 | 2494.6 | 2524.1 | 2528.3 | 2382.2 | 2068.9 | 1574.8 | 1015.5 |
| 77.5° | 1746.1 | 1736.7 | 1864.9 | 2020.5 | 2114.1 | 2135.1 | 2130.9 | 2009.0 | 1734.6 | 1308.8 | 851.5 |
| 80° | 1384.5 | 1404.5 | 1484.4 | 1587.4 | 1681.0 | 1704.1 | 1689.4 | 1596.9 | 1349.8 | 1020.8 | 653.9 |
| 82.5° | 968.2 | 992.4 | 1059.7 | 1137.5 | 1207.9 | 1207.9 | 1221.6 | 1132.2 | 956.6 | 732.7 | 457.3 |
| 85° | 522.5 | 508.8 | 582.4 | 670.7 | 721.2 | 730.6 | 735.9 | 706.4 | 591.9 | 442.6 | 271.2 |
| 87.5° | 86.2 | 92.5 | 114.6 | 175.6 | 199.7 | 231.3 | 246.0 | 192.4 | 116.7 | 74.6 | 54.7 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P400572

CATALOG NUMBER: TT-D4-830-U-DL

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 121.9 | 121.9 | 121.9 | 121.9 | 121.9 | 121.9 | 121.9 | 121.9 | 121.9 | 121.9 | 121.9 |
| 2.5° | 124.0 | 123.0 | 121.9 | 120.9 | 120.9 | 119.8 | 119.8 | 119.8 | 120.9 | 120.9 | 120.9 |
| 5° | 127.2 | 126.2 | 125.1 | 124.0 | 121.9 | 121.9 | 121.9 | 121.9 | 121.9 | 121.9 | 121.9 |
| 7.5° | 132.5 | 130.4 | 129.3 | 127.2 | 125.1 | 125.1 | 124.0 | 124.0 | 124.0 | 125.1 | 124.0 |
| 10° | 138.8 | 136.7 | 134.6 | 131.4 | 130.4 | 129.3 | 128.3 | 128.3 | 129.3 | 129.3 | 128.3 |
| 12.5° | 146.1 | 145.1 | 140.9 | 137.7 | 135.6 | 134.6 | 133.5 | 134.6 | 133.5 | 134.6 | 134.6 |
| 15° | 156.6 | 153.5 | 148.2 | 145.1 | 141.9 | 140.9 | 139.8 | 140.9 | 140.9 | 141.9 | 140.9 |
| 17.5° | 168.2 | 164.0 | 158.7 | 153.5 | 149.3 | 148.2 | 148.2 | 148.2 | 149.3 | 150.3 | 149.3 |
| 20° | 181.9 | 176.6 | 169.3 | 162.9 | 158.7 | 157.7 | 157.7 | 158.7 | 159.8 | 160.8 | 160.8 |
| 22.5° | 195.5 | 191.3 | 180.8 | 172.4 | 170.3 | 169.3 | 168.2 | 170.3 | 172.4 | 173.5 | 174.5 |
| 25° | 216.6 | 208.1 | 195.5 | 186.1 | 181.9 | 181.9 | 182.9 | 185.0 | 186.1 | 188.2 | 187.1 |
| 27.5° | 238.6 | 229.2 | 213.4 | 200.8 | 197.6 | 196.6 | 198.7 | 200.8 | 205.0 | 205.0 | 203.9 |
| 30° | 269.1 | 253.4 | 233.4 | 221.8 | 213.4 | 214.5 | 217.6 | 220.8 | 225.0 | 227.1 | 227.1 |
| 32.5° | 303.8 | 287.0 | 259.7 | 241.8 | 237.6 | 238.6 | 239.7 | 244.9 | 249.1 | 253.4 | 250.2 |
| 35° | 349.0 | 328.0 | 294.4 | 274.4 | 263.9 | 262.8 | 267.0 | 273.3 | 277.5 | 279.6 | 279.6 |
| 37.5° | 398.4 | 371.1 | 329.0 | 312.2 | 299.6 | 298.6 | 299.6 | 304.9 | 310.1 | 312.2 | 316.4 |
| 40° | 458.4 | 424.7 | 375.3 | 348.0 | 338.5 | 336.4 | 340.6 | 348.0 | 348.0 | 351.1 | 352.2 |
| 42.5° | 531.9 | 488.8 | 434.2 | 398.4 | 386.9 | 386.9 | 385.8 | 392.1 | 392.1 | 392.1 | 390.0 |
| 45° | 625.5 | 577.1 | 505.7 | 468.9 | 448.9 | 438.4 | 441.5 | 437.3 | 436.3 | 439.4 | 430.0 |
| 47.5° | 715.9 | 654.9 | 570.8 | 530.9 | 510.9 | 504.6 | 493.0 | 489.9 | 484.6 | 484.6 | 471.0 |
| 50° | 821.0 | 745.3 | 664.4 | 607.6 | 588.7 | 570.8 | 561.4 | 546.7 | 530.9 | 527.7 | 522.5 |
| 52.5° | 996.6 | 902.0 | 774.8 | 713.8 | 665.4 | 647.6 | 625.5 | 606.6 | 587.7 | 572.9 | 581.3 |
| 55° | 1068.1 | 971.4 | 850.5 | 791.6 | 758.0 | 741.1 | 700.1 | 674.9 | 646.5 | 625.5 | 637.1 |
| 57.5° | 1103.8 | 998.7 | 886.2 | 842.1 | 832.6 | 816.8 | 786.3 | 743.2 | 710.7 | 684.4 | 686.5 |
| 60° | 1123.8 | 1013.4 | 905.1 | 865.2 | 859.9 | 870.4 | 854.7 | 825.2 | 774.8 | 748.5 | 745.3 |
| 62.5° | 1200.5 | 1084.9 | 958.8 | 902.0 | 890.4 | 897.8 | 902.0 | 884.1 | 842.1 | 807.4 | 797.9 |
| 65° | 1216.3 | 1093.3 | 969.3 | 932.5 | 933.5 | 935.6 | 938.8 | 919.9 | 898.8 | 855.7 | 847.3 |
| 67.5° | 1169.0 | 1048.1 | 937.7 | 907.2 | 909.3 | 933.5 | 952.4 | 951.4 | 928.3 | 891.5 | 888.3 |
| 70° | 1097.5 | 979.8 | 877.8 | 850.5 | 855.7 | 877.8 | 918.8 | 939.8 | 935.6 | 911.4 | 916.7 |
| 72.5° | 986.1 | 881.0 | 791.6 | 770.6 | 783.2 | 804.2 | 843.1 | 881.0 | 903.0 | 908.3 | 919.9 |
| 75° | 855.7 | 771.6 | 687.5 | 674.9 | 684.4 | 708.6 | 744.3 | 788.4 | 836.8 | 863.1 | 870.4 |
| 77.5° | 706.4 | 629.7 | 567.7 | 559.3 | 572.9 | 595.0 | 630.8 | 665.4 | 720.1 | 766.4 | 776.9 |
| 80° | 553.0 | 486.7 | 442.6 | 435.2 | 443.6 | 462.6 | 489.9 | 518.3 | 570.8 | 606.6 | 611.8 |
| 82.5° | 383.7 | 343.8 | 315.4 | 311.2 | 316.4 | 323.8 | 345.9 | 372.1 | 401.6 | 430.0 | 433.1 |
| 85° | 222.9 | 197.6 | 190.3 | 184.0 | 195.5 | 195.5 | 200.8 | 215.5 | 230.2 | 232.3 | 238.6 |
| 87.5° | 41.0 | 38.9 | 39.9 | 29.4 | 36.8 | 26.3 | 26.3 | 33.6 | 25.2 | 29.4 | 24.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

McGRAW-EDISON

Report Number: SP1-2006-844-5

Luminaire Tested: TT-D5-830-U-MQ

Test Date: 09/30/2020

Data applicable to product families TT-x-830 and TTN-x-830

Test Information


Test Method: LM-79-08
 Report Number: SP1-2006-844-5
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 09/30/2020
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: MCGRAW-EDISON
 Catalog Number: **TT-D5-830-U-MQ**
 Description: MCGRAW EDISON

DISTRIBUTION

Spectral Parameters

CCT (K): 2996
 CIE u': 0.2496
 CIE v': 0.5255
 Duv: 0.0029
 CIE x: 0.4414
 CIE y: 0.4130
 CIE z: 0.1455
 Peak Wavelength (nm): 601
 Dominant Wavelength (nm): 581
 Purity: 56.8
 Rf: 85.7
 Rg: 94.5

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 81.6 | | |
| R1: | 79.1 | R9: | -0.6 |
| R2: | 89.7 | R10: | 77.8 |
| R3: | 96.7 | R11: | 80.1 |
| R4: | 80.2 | R12: | 72.7 |
| R5: | 79.8 | R13: | 81.5 |
| R6: | 88.4 | R14: | 98.5 |
| R7: | 82.6 | | |
| R8: | 56.3 | | |



Test Conditions


Stabilization Time: 55M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.5/43%
 Sphere Temperature (°C): 25.9

REPORT NUMBER: SP1-2006-844-5


| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 7/29/2020 | 1/29/2021 |
| Power Meter | IN0071 | 12/3/2019 | 12/3/2020 |
| AC Power Source | IN0063 | 12/3/2019 | 12/3/2020 |
| DC Power Source | IN0208 | 12/3/2019 | 12/3/2020 |
| Sphere Thermometer | IN0085 | 12/3/2019 | 12/3/2020 |
| Room Thermometer | IN0046 | 12/3/2019 | 12/3/2020 |

REPORT NUMBER: SP1-2006-844-5

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2996K
 CIE x = 0.4414
 CIE y = 0.4130
 Duv = 0.0029

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2006-844-5

Photopic Flux vs. Wavelength




#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2265 | 0.0 | 490 | 45874 | 6.5 | 620 | 162337 | 42.2 | 750 | 6976 | 0.0 | 880 | 2976 | 0.0 |
| 365 | 2167 | 0.0 | 495 | 55189 | 10.0 | 625 | 153641 | 33.9 | 755 | 6666 | 0.0 | 885 | 2283 | 0.0 |
| 370 | 2505 | 0.0 | 500 | 64204 | 14.2 | 630 | 143151 | 25.9 | 760 | 5969 | 0.0 | 890 | 2506 | 0.0 |
| 375 | 2720 | 0.0 | 505 | 71441 | 20.0 | 635 | 133763 | 20.1 | 765 | 5281 | 0.0 | 895 | 3132 | 0.0 |
| 380 | 2601 | 0.0 | 510 | 76219 | 26.2 | 640 | 123759 | 14.8 | 770 | 4732 | 0.0 | 900 | 2539 | 0.0 |
| 385 | 2461 | 0.0 | 515 | 79949 | 33.1 | 645 | 112859 | 10.9 | 775 | 3998 | 0.0 | 905 | 1252 | 0.0 |
| 390 | 2308 | 0.0 | 520 | 83077 | 40.3 | 650 | 102080 | 7.5 | 780 | 4027 | 0.0 | 910 | 1938 | 0.0 |
| 395 | 2104 | 0.0 | 525 | 86267 | 46.3 | 655 | 91102 | 5.2 | 785 | 4088 | 0.0 | 915 | 2171 | 0.0 |
| 400 | 1900 | 0.0 | 530 | 89871 | 52.9 | 660 | 79928 | 3.3 | 790 | 3700 | 0.0 | 920 | 2123 | 0.0 |
| 405 | 1945 | 0.0 | 535 | 93544 | 58.0 | 665 | 70694 | 2.2 | 795 | 3213 | 0.0 | 925 | 1954 | 0.0 |
| 410 | 2378 | 0.0 | 540 | 97371 | 63.4 | 670 | 61201 | 1.3 | 800 | 3403 | 0.0 | 930 | 2800 | 0.0 |
| 415 | 3437 | 0.0 | 545 | 103011 | 68.6 | 675 | 53092 | 0.9 | 805 | 3079 | 0.0 | 935 | 3314 | 0.0 |
| 420 | 6173 | 0.0 | 550 | 108560 | 73.8 | 680 | 45718 | 0.5 | 810 | 2921 | 0.0 | 940 | 553 | 0.0 |
| 425 | 11052 | 0.1 | 555 | 114473 | 78.2 | 685 | 39372 | 0.3 | 815 | 2705 | 0.0 | 945 | 2793 | 0.0 |
| 430 | 18756 | 0.1 | 560 | 121896 | 82.8 | 690 | 34120 | 0.2 | 820 | 2685 | 0.0 | 950 | 2629 | 0.0 |
| 435 | 29750 | 0.4 | 565 | 130192 | 86.6 | 695 | 29427 | 0.1 | 825 | 3246 | 0.0 | 955 | 2418 | 0.0 |
| 440 | 43697 | 0.7 | 570 | 139595 | 90.8 | 700 | 25380 | 0.1 | 830 | 2813 | 0.0 | 960 | 2857 | 0.0 |
| 445 | 61462 | 1.3 | 575 | 149225 | 92.8 | 705 | 22079 | 0.0 | 835 | 2097 | 0.0 | 965 | 1052 | 0.0 |
| 450 | 76648 | 2.0 | 580 | 158344 | 94.1 | 710 | 18938 | 0.0 | 840 | 1606 | 0.0 | 970 | 4009 | 0.0 |
| 455 | 65529 | 2.2 | 585 | 165704 | 92.1 | 715 | 16322 | 0.0 | 845 | 2347 | 0.0 | 975 | 2341 | 0.0 |
| 460 | 46753 | 1.9 | 590 | 172269 | 89.1 | 720 | 14132 | 0.0 | 850 | 2273 | 0.0 | 980 | 2439 | 0.0 |
| 465 | 38422 | 2.0 | 595 | 177895 | 84.3 | 725 | 12072 | 0.0 | 855 | 1971 | 0.0 | 985 | 2098 | 0.0 |
| 470 | 32450 | 2.0 | 600 | 180887 | 78.0 | 730 | 10271 | 0.0 | 860 | 1962 | 0.0 | 990 | 1159 | 0.0 |
| 475 | 29284 | 2.3 | 605 | 178880 | 69.3 | 735 | 9202 | 0.0 | 865 | 2989 | 0.0 | 995 | 2146 | 0.0 |
| 480 | 31922 | 3.0 | 610 | 175843 | 60.4 | 740 | 8451 | 0.0 | 870 | 2921 | 0.0 | 1000 | 1904 | 0.0 |
| 485 | 37800 | 4.5 | 615 | 170321 | 51.4 | 745 | 7632 | 0.0 | 875 | 3581 | 0.0 | | | |

REPORT NUMBER: SP1-2006-844-5

Scotopic Flux vs. Wavelength



Scotopic Lumens: 4357.3

S/P: 0.5

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2265 | 0.0 | 490 | 45874 | 70.6 | 620 | 162337 | 2.0 | 750 | 6976 | 0.0 | 880 | 2976 | 0.0 |
| 365 | 2167 | 0.0 | 495 | 55189 | 89.2 | 625 | 153641 | 1.3 | 755 | 6666 | 0.0 | 885 | 2283 | 0.0 |
| 370 | 2505 | 0.0 | 500 | 64204 | 107.4 | 630 | 143151 | 0.8 | 760 | 5969 | 0.0 | 890 | 2506 | 0.0 |
| 375 | 2720 | 0.0 | 505 | 71441 | 121.4 | 635 | 133763 | 0.5 | 765 | 5281 | 0.0 | 895 | 3132 | 0.0 |
| 380 | 2601 | 0.0 | 510 | 76219 | 129.2 | 640 | 123759 | 0.3 | 770 | 4732 | 0.0 | 900 | 2539 | 0.0 |
| 385 | 2461 | 0.0 | 515 | 79949 | 132.5 | 645 | 112859 | 0.2 | 775 | 3998 | 0.0 | 905 | 1252 | 0.0 |
| 390 | 2308 | 0.0 | 520 | 83077 | 132.1 | 650 | 102080 | 0.1 | 780 | 4027 | 0.0 | 910 | 1938 | 0.0 |
| 395 | 2104 | 0.0 | 525 | 86267 | 129.1 | 655 | 91102 | 0.1 | 785 | 4088 | 0.0 | 915 | 2171 | 0.0 |
| 400 | 1900 | 0.0 | 530 | 89871 | 123.9 | 660 | 79928 | 0.0 | 790 | 3700 | 0.0 | 920 | 2123 | 0.0 |
| 405 | 1945 | 0.1 | 535 | 93544 | 116.6 | 665 | 70694 | 0.0 | 795 | 3213 | 0.0 | 925 | 1954 | 0.0 |
| 410 | 2378 | 0.1 | 540 | 97371 | 107.6 | 670 | 61201 | 0.0 | 800 | 3403 | 0.0 | 930 | 2800 | 0.0 |
| 415 | 3437 | 0.4 | 545 | 103011 | 98.8 | 675 | 53092 | 0.0 | 805 | 3079 | 0.0 | 935 | 3314 | 0.0 |
| 420 | 6173 | 1.0 | 550 | 108560 | 88.8 | 680 | 45718 | 0.0 | 810 | 2921 | 0.0 | 940 | 553 | 0.0 |
| 425 | 11052 | 2.7 | 555 | 114473 | 78.2 | 685 | 39372 | 0.0 | 815 | 2705 | 0.0 | 945 | 2793 | 0.0 |
| 430 | 18756 | 6.4 | 560 | 121896 | 68.1 | 690 | 34120 | 0.0 | 820 | 2685 | 0.0 | 950 | 2629 | 0.0 |
| 435 | 29750 | 13.3 | 565 | 130192 | 58.4 | 695 | 29427 | 0.0 | 825 | 3246 | 0.0 | 955 | 2418 | 0.0 |
| 440 | 43697 | 24.4 | 570 | 139595 | 49.3 | 700 | 25380 | 0.0 | 830 | 2813 | 0.0 | 960 | 2857 | 0.0 |
| 445 | 61462 | 41.2 | 575 | 149225 | 40.6 | 705 | 22079 | 0.0 | 835 | 2097 | 0.0 | 965 | 1052 | 0.0 |
| 450 | 76648 | 59.4 | 580 | 158344 | 32.6 | 710 | 18938 | 0.0 | 840 | 1606 | 0.0 | 970 | 4009 | 0.0 |
| 455 | 65529 | 57.3 | 585 | 165704 | 25.3 | 715 | 16322 | 0.0 | 845 | 2347 | 0.0 | 975 | 2341 | 0.0 |
| 460 | 46753 | 45.2 | 590 | 172269 | 19.2 | 720 | 14132 | 0.0 | 850 | 2273 | 0.0 | 980 | 2439 | 0.0 |
| 465 | 38422 | 40.6 | 595 | 177895 | 14.2 | 725 | 12072 | 0.0 | 855 | 1971 | 0.0 | 985 | 2098 | 0.0 |
| 470 | 32450 | 37.4 | 600 | 180887 | 10.2 | 730 | 10271 | 0.0 | 860 | 1962 | 0.0 | 990 | 1159 | 0.0 |
| 475 | 29284 | 36.6 | 605 | 178880 | 7.0 | 735 | 9202 | 0.0 | 865 | 2989 | 0.0 | 995 | 2146 | 0.0 |
| 480 | 31922 | 43.1 | 610 | 175843 | 4.8 | 740 | 8451 | 0.0 | 870 | 2921 | 0.0 | 1000 | 1904 | 0.0 |
| 485 | 37800 | 54.8 | 615 | 170321 | 3.2 | 745 | 7632 | 0.0 | 875 | 3581 | 0.0 | | | |

REPORT NUMBER: SP1-2006-844-5

Melanopic Flux vs. Wavelength




Melanopic Lumens: 11640.4 S/P: 1.33





| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2265 | 0.0 | 490 | 45874 | 38.2 | 620 | 162337 | 0.1 | 750 | 6976 | 0.0 | 880 | 2976 | 0.0 |
| 365 | 2167 | 0.0 | 495 | 55189 | 45.6 | 625 | 153641 | 0.1 | 755 | 6666 | 0.0 | 885 | 2283 | 0.0 |
| 370 | 2505 | 0.0 | 500 | 64204 | 51.6 | 630 | 143151 | 0.0 | 760 | 5969 | 0.0 | 890 | 2506 | 0.0 |
| 375 | 2720 | 0.0 | 505 | 71441 | 54.8 | 635 | 133763 | 0.0 | 765 | 5281 | 0.0 | 895 | 3132 | 0.0 |
| 380 | 2601 | 0.0 | 510 | 76219 | 54.7 | 640 | 123759 | 0.0 | 770 | 4732 | 0.0 | 900 | 2539 | 0.0 |
| 385 | 2461 | 0.0 | 515 | 79949 | 52.2 | 645 | 112859 | 0.0 | 775 | 3998 | 0.0 | 905 | 1252 | 0.0 |
| 390 | 2308 | 0.0 | 520 | 83077 | 48.4 | 650 | 102080 | 0.0 | 780 | 4027 | 0.0 | 910 | 1938 | 0.0 |
| 395 | 2104 | 0.0 | 525 | 86267 | 43.7 | 655 | 91102 | 0.0 | 785 | 4088 | 0.0 | 915 | 2171 | 0.0 |
| 400 | 1900 | 0.0 | 530 | 89871 | 38.8 | 660 | 79928 | 0.0 | 790 | 3700 | 0.0 | 920 | 2123 | 0.0 |
| 405 | 1945 | 0.0 | 535 | 93544 | 33.7 | 665 | 70694 | 0.0 | 795 | 3213 | 0.0 | 925 | 1954 | 0.0 |
| 410 | 2378 | 0.1 | 540 | 97371 | 28.5 | 670 | 61201 | 0.0 | 800 | 3403 | 0.0 | 930 | 2800 | 0.0 |
| 415 | 3437 | 0.2 | 545 | 103011 | 23.9 | 675 | 53092 | 0.0 | 805 | 3079 | 0.0 | 935 | 3314 | 0.0 |
| 420 | 6173 | 0.7 | 550 | 108560 | 19.5 | 680 | 45718 | 0.0 | 810 | 2921 | 0.0 | 940 | 553 | 0.0 |
| 425 | 11052 | 1.7 | 555 | 114473 | 15.4 | 685 | 39372 | 0.0 | 815 | 2705 | 0.0 | 945 | 2793 | 0.0 |
| 430 | 18756 | 4.0 | 560 | 121896 | 12.0 | 690 | 34120 | 0.0 | 820 | 2685 | 0.0 | 950 | 2629 | 0.0 |
| 435 | 29750 | 7.9 | 565 | 130192 | 9.1 | 695 | 29427 | 0.0 | 825 | 3246 | 0.0 | 955 | 2418 | 0.0 |
| 440 | 43697 | 14.6 | 570 | 139595 | 6.8 | 700 | 25380 | 0.0 | 830 | 2813 | 0.0 | 960 | 2857 | 0.0 |
| 445 | 61462 | 24.2 | 575 | 149225 | 5.0 | 705 | 22079 | 0.0 | 835 | 2097 | 0.0 | 965 | 1052 | 0.0 |
| 450 | 76648 | 35.3 | 580 | 158344 | 3.5 | 710 | 18938 | 0.0 | 840 | 1606 | 0.0 | 970 | 4009 | 0.0 |
| 455 | 65529 | 34.3 | 585 | 165704 | 2.5 | 715 | 16322 | 0.0 | 845 | 2347 | 0.0 | 975 | 2341 | 0.0 |
| 460 | 46753 | 27.5 | 590 | 172269 | 1.7 | 720 | 14132 | 0.0 | 850 | 2273 | 0.0 | 980 | 2439 | 0.0 |
| 465 | 38422 | 25.1 | 595 | 177895 | 1.1 | 725 | 12072 | 0.0 | 855 | 1971 | 0.0 | 985 | 2098 | 0.0 |
| 470 | 32450 | 23.2 | 600 | 180887 | 0.8 | 730 | 10271 | 0.0 | 860 | 1962 | 0.0 | 990 | 1159 | 0.0 |
| 475 | 29284 | 22.4 | 605 | 178880 | 0.5 | 735 | 9202 | 0.0 | 865 | 2989 | 0.0 | 995 | 2146 | 0.0 |
| 480 | 31922 | 25.6 | 610 | 175843 | 0.3 | 740 | 8451 | 0.0 | 870 | 2921 | 0.0 | 1000 | 1904 | 0.0 |
| 485 | 37800 | 31.2 | 615 | 170321 | 0.2 | 745 | 7632 | 0.0 | 875 | 3581 | 0.0 | | | |

Summary

$R_f = 85.7$
 $R_g = 94.5$
 CIE $R_a = 81.6$
 $R_g = -0.6$




Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)



| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 85 | CES51 = 95 | CES76 = 83 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 86 |
| CES03 = 31 | CES28 = 95 | CES53 = 90 | CES78 = 82 |
| CES04 = 70 | CES29 = 88 | CES54 = 91 | CES79 = 91 |
| CES05 = 50 | CES30 = 94 | CES55 = 91 | CES80 = 90 |
| CES06 = 51 | CES31 = 90 | CES56 = 87 | CES81 = 72 |
| CES07 = 42 | CES32 = 84 | CES57 = 86 | CES82 = 96 |
| CES08 = 41 | CES33 = 92 | CES58 = 87 | CES83 = 94 |
| CES09 = 29 | CES34 = 93 | CES59 = 91 | CES84 = 92 |
| CES10 = 76 | CES35 = 96 | CES60 = 94 | CES85 = 78 |
| CES11 = 59 | CES36 = 91 | CES61 = 90 | CES86 = 67 |
| CES12 = 65 | CES37 = 96 | CES62 = 95 | CES87 = 85 |
| CES13 = 43 | CES38 = 99 | CES63 = 88 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 84 | CES89 = 75 |
| CES15 = 72 | CES40 = 95 | CES65 = 79 | CES90 = 87 |
| CES16 = 47 | CES41 = 97 | CES66 = 83 | CES91 = 83 |
| CES17 = 50 | CES42 = 98 | CES67 = 82 | CES92 = 65 |
| CES18 = 56 | CES43 = 93 | CES68 = 84 | CES93 = 79 |
| CES19 = 72 | CES44 = 99 | CES69 = 89 | CES94 = 61 |
| CES20 = 67 | CES45 = 94 | CES70 = 81 | CES95 = 75 |
| CES21 = 87 | CES46 = 90 | CES71 = 80 | CES96 = 83 |
| CES22 = 79 | CES47 = 93 | CES72 = 93 | CES97 = 89 |
| CES23 = 92 | CES48 = 83 | CES73 = 77 | CES98 = 84 |
| CES24 = 91 | CES49 = 91 | CES74 = 93 | CES99 = 75 |
| CES25 = 72 | CES50 = 95 | CES75 = 82 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)