

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P821301

Luminaire Tested: **TT-D3-740-24VDC-RW-HSS**

Issue Date: 12/2/2020



**Test Information**

Test Method: LM-79-08  
Report Number: P821301  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2010-017-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 12/2/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TT-D3-740-24VDC-RW-HSS  
Description: TOPTIER LED PARKING GARAGE LUMINAIRE  
4000K, 70 CRI LEDS AND RECTANGULAR DISTRIBUTION WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4013.1 lumens  
Efficiency: N/A  
Efficacy: 87.2 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B2 - U2 - G3

Input Watts (W): 46  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

REPORT NUMBER: P821301  
 CATALOG NUMBER: TT-D3-740-24VDC-RW-HSS

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 1.4 fc  
 Type IV - Short - N/A

REPORT NUMBER: P821301  
CATALOG NUMBER: TT-D3-740-24VDC-RW-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 79-Deg Lateral      - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P821301  
 CATALOG NUMBER: TT-D3-740-24VDC-RW-HSS


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1267.3	1.6	1268.9
	% Fixture	31.6	0.0	31.6
<b>Street Side</b>	Lumens	2726.5	17.7	2744.2
	% Fixture	67.9	0.4	68.4
<b>Total</b>	Lumens	3993.8	19.3	4013.1
	% Fixture	99.5	0.5	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	11.4	0.3
10°-20°	43.2	1.1
20°-30°	99.7	2.5
30°-40°	213.6	5.3
40°-50°	457.5	11.4
50°-60°	864.1	21.5
60°-70°	1073.9	26.8
70°-80°	919.3	22.9
80°-90°	311.0	7.7
90°-100°	13.4	0.3
100°-110°	3.9	0.1
110°-120°	0.8	0.0
120°-130°	0.5	0.0
130°-140°	0.3	0.0
140°-150°	0.2	0.0
150°-160°	0.1	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3993.8	99.5
0°-180°	4013.1	100.0




REPORT NUMBER: P821301  
 CATALOG NUMBER: TT-D3-740-24VDC-RW-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	82.1	2.0			
FM (30°-60°)	918.4	22.9			
FH (60°-80°)	1485.5	37.0			G1/1800
FVH (80°-90°)	240.6	6.0			G3/500
BL (0°-30°)	72.3	1.8	B0/110		
BM (30°-60°)	616.9	15.4	B1/1000		
BH (60°-80°)	507.7	12.7	B2/1000		G2/1000
BVH (80°-90°)	70.4	1.8			G1/100
UL (90°-100°)	13.4	0.3		U2/50	
UH (100°-180°)	5.9	0.1		U1/10	

**BUG Rating: B2-U2-G3**  
 Type IV Short





REPORT NUMBER: P821301

CATALOG NUMBER: TT-D3-740-24VDC-RW-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	79°	85°
0°	109.0	109.0	109.0	109.0	109.0	109.0	109.0	109.0	109.0	109.0	109.0
2.5°	115.0	115.0	115.0	114.0	114.0	114.0	113.0	112.0	111.0	111.0	111.0
5°	121.0	121.0	121.0	121.0	120.0	119.0	118.0	117.0	116.0	116.0	115.0
7.5°	129.0	128.0	129.0	128.0	128.0	127.0	126.0	125.0	123.0	123.0	122.0
10°	137.0	137.0	137.0	137.0	137.0	136.0	135.0	134.0	133.0	132.0	131.0
12.5°	147.0	147.0	147.0	146.0	147.0	146.0	145.0	145.0	144.0	142.0	142.0
15°	157.0	157.0	157.0	157.0	158.0	158.0	158.0	157.0	157.0	156.0	155.0
17.5°	169.0	168.0	169.0	169.0	170.0	171.0	172.0	173.0	173.0	172.0	172.0
20°	182.0	181.0	182.0	182.0	184.0	186.0	189.0	191.0	192.0	190.0	190.0
22.5°	196.0	195.0	197.0	197.0	200.0	203.0	208.0	210.0	213.0	212.0	212.0
25°	213.0	212.0	213.0	214.0	218.0	223.0	229.0	234.0	237.0	237.0	238.0
27.5°	232.0	232.0	233.0	234.0	238.0	246.0	255.0	264.0	271.0	270.0	271.0
30°	258.0	258.0	260.0	261.0	266.0	275.0	287.0	299.0	309.0	309.0	311.0
32.5°	287.0	286.0	289.0	290.0	295.0	307.0	324.0	343.0	356.0	356.0	358.0
35°	322.0	321.0	324.0	324.0	330.0	347.0	369.0	395.0	417.0	418.0	421.0
37.5°	366.0	364.0	364.0	367.0	374.0	396.0	426.0	462.0	485.0	487.0	492.0
40°	418.0	417.0	419.0	418.0	427.0	454.0	492.0	534.0	561.0	566.0	572.0
42.5°	482.0	484.0	481.0	481.0	492.0	523.0	568.0	617.0	666.0	672.0	675.0
45°	560.0	564.0	560.0	559.0	569.0	605.0	667.0	753.0	810.0	830.0	836.0
47.5°	654.0	656.0	651.0	649.0	660.0	706.0	786.0	882.0	949.0	964.0	980.0
50°	759.0	756.0	752.0	749.0	770.0	827.0	920.0	1019.0	1134.0	1136.0	1142.0
52.5°	867.0	858.0	859.0	858.0	887.0	949.0	1073.0	1241.0	1416.0	1451.9	1455.9
55°	975.0	964.0	963.0	973.0	1014.0	1103.0	1259.0	1476.9	1618.9	1640.9	1637.9
57.5°	1083.0	1078.0	1076.0	1085.0	1145.0	1251.0	1427.0	1610.9	1731.9	1729.9	1708.9
60°	1195.0	1199.0	1192.0	1209.0	1271.0	1377.0	1504.9	1683.9	1795.9	1786.9	1765.9
62.5°	1310.0	1320.0	1313.0	1315.0	1355.0	1432.9	1558.9	1766.9	1921.9	1934.9	1910.9
65°	1424.0	1431.0	1420.0	1389.0	1411.0	1483.9	1663.9	1863.9	1981.9	1993.9	1975.9
67.5°	1519.9	1526.9	1488.9	1439.9	1442.9	1495.9	1653.9	1844.9	1949.9	1941.9	1912.9
70°	1601.9	1588.9	1526.9	1442.9	1408.0	1432.9	1581.9	1750.9	1857.9	1853.9	1819.9
72.5°	1628.9	1611.9	1506.9	1377.0	1308.0	1317.0	1461.9	1612.9	1699.9	1706.9	1665.9
75°	1585.9	1556.9	1413.0	1250.0	1161.0	1167.0	1291.0	1430.0	1499.9	1491.9	1459.9
77.5°	1431.0	1402.0	1246.0	1072.0	985.0	994.0	1092.0	1201.0	1259.0	1256.0	1234.0
80°	1188.0	1162.0	1025.0	863.0	784.0	789.0	864.0	950.0	995.0	1005.0	993.0
82.5°	878.0	860.0	763.0	632.0	568.0	567.0	624.0	690.0	734.0	755.0	747.0
85°	543.0	534.0	480.0	395.0	350.0	349.0	383.0	432.0	472.0	500.0	482.0
87.5°	216.0	213.0	197.0	159.0	139.0	132.0	124.0	155.0	158.0	187.0	186.0
90°	53.0	52.0	51.0	48.0	43.0	37.0	30.0	22.0	14.0	11.0	6.0
92.5°	47.0	47.0	46.0	43.0	39.0	33.0	27.0	20.0	13.0	10.0	5.0
95°	38.0	38.0	37.0	35.0	31.0	27.0	21.0	16.0	10.0	8.0	4.0
97.5°	29.0	28.0	28.0	26.0	24.0	20.0	16.0	12.0	8.0	6.0	3.0
100°	21.0	21.0	20.0	19.0	17.0	15.0	12.0	9.0	5.0	4.0	2.0
102.5°	15.0	14.0	14.0	14.0	12.0	10.0	8.0	6.0	4.0	3.0	1.0
105°	10.0	9.0	9.0	9.0	8.0	7.0	5.0	4.0	2.0	2.0	1.0
107.5°	6.0	6.0	6.0	6.0	5.0	4.0	3.0	2.0	1.0	1.0	1.0
110°	3.0	3.0	3.0	4.0	3.0	3.0	2.0	1.0	1.0	1.0	1.0



REPORT NUMBER: P821301  
 CATALOG NUMBER: TT-D3-740-24VDC-RW-HSS

**CANDELA DISTRIBUTION (continued):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	79°	85°
112.5°	2.0	2.0	2.0	2.0	2.0	2.0	1.0	1.0	1.0	1.0	1.0
115°	1.0	1.0	1.0	2.0	2.0	1.0	1.0	0.0	0.0	1.0	1.0
117.5°	0.0	0.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	1.0
120°	0.0	0.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	1.0
122.5°	0.0	0.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	1.0
125°	0.0	0.0	0.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	1.0
127.5°	0.0	0.0	0.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	1.0
130°	0.0	0.0	0.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	1.0
132.5°	0.0	0.0	0.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	1.0
135°	0.0	0.0	0.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	1.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	1.0	0.0	1.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P821301  
 CATALOG NUMBER: TT-D3-740-24VDC-RW-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	109.0	109.0	109.0	109.0	109.0	109.0	109.0	109.0	109.0	109.0	109.0
2.5°	110.0	110.0	110.0	109.0	109.0	109.0	108.0	108.0	107.0	107.0	107.0
5°	114.0	114.0	113.0	113.0	112.0	111.0	111.0	110.0	110.0	109.0	109.0
7.5°	121.0	121.0	120.0	119.0	117.0	116.0	115.0	114.0	114.0	113.0	113.0
10°	130.0	130.0	128.0	126.0	124.0	122.0	121.0	119.0	118.0	118.0	118.0
12.5°	141.0	140.0	138.0	135.0	133.0	130.0	128.0	126.0	124.0	124.0	124.0
15°	154.0	154.0	150.0	147.0	143.0	139.0	136.0	133.0	131.0	130.0	130.0
17.5°	170.0	170.0	165.0	160.0	155.0	150.0	146.0	142.0	140.0	139.0	139.0
20°	188.0	188.0	183.0	177.0	170.0	163.0	157.0	152.0	149.0	148.0	148.0
22.5°	210.0	210.0	203.0	195.0	186.0	176.0	168.0	162.0	159.0	157.0	157.0
25°	235.0	233.0	226.0	216.0	203.0	191.0	180.0	174.0	170.0	167.0	168.0
27.5°	269.0	266.0	257.0	240.0	224.0	208.0	195.0	187.0	182.0	180.0	181.0
30°	308.0	305.0	292.0	273.0	249.0	228.0	212.0	203.0	198.0	195.0	196.0
32.5°	355.0	351.0	335.0	309.0	281.0	251.0	231.0	220.0	215.0	212.0	211.0
35°	417.0	412.0	392.0	356.0	317.0	281.0	253.0	239.0	234.0	231.0	232.0
37.5°	487.0	480.0	453.0	409.0	360.0	314.0	282.0	264.0	258.0	253.0	253.0
40°	567.0	559.0	524.0	466.0	407.0	350.0	309.0	289.0	282.0	282.0	282.0
42.5°	667.0	659.0	619.0	534.0	456.0	389.0	340.0	317.0	310.0	312.0	312.0
45°	822.0	811.0	747.0	635.0	520.0	429.0	372.0	346.0	341.0	346.0	346.0
47.5°	964.0	950.0	856.0	729.0	583.0	469.0	404.0	374.0	372.0	383.0	383.0
50°	1123.0	1105.0	1006.0	805.0	634.0	513.0	433.0	397.0	398.0	414.0	419.0
52.5°	1431.0	1412.0	1241.0	943.0	689.0	529.0	445.0	402.0	402.0	420.0	427.0
55°	1613.9	1574.9	1352.0	1033.0	712.0	548.0	440.0	382.0	380.0	400.0	406.0
57.5°	1673.9	1633.9	1375.0	1007.0	697.0	524.0	411.0	328.0	324.0	350.0	348.0
60°	1722.9	1669.9	1338.0	920.0	612.0	473.0	355.0	244.0	227.0	250.0	249.0
62.5°	1860.9	1803.9	1340.0	818.0	512.0	395.0	267.0	137.0	102.0	120.0	112.0
65°	1929.9	1873.9	1361.0	770.0	461.0	327.0	191.0	56.0	4.0	4.0	2.0
67.5°	1870.9	1820.9	1334.0	758.0	454.0	325.0	194.0	55.0	0.0	0.0	0.0
70°	1784.9	1736.9	1272.0	716.0	431.0	313.0	190.0	55.0	0.0	0.0	0.0
72.5°	1633.9	1584.9	1165.0	656.0	396.0	287.0	176.0	52.0	0.0	0.0	0.0
75°	1434.9	1398.0	1029.0	578.0	349.0	253.0	156.0	46.0	0.0	0.0	0.0
77.5°	1215.0	1171.0	863.0	481.0	292.0	210.0	132.0	38.0	0.0	0.0	0.0
80°	975.0	943.0	680.0	377.0	226.0	164.0	103.0	29.0	0.0	0.0	0.0
82.5°	725.0	698.0	503.0	270.0	161.0	114.0	71.0	19.0	0.0	0.0	0.0
85°	476.0	469.0	323.0	164.0	96.0	63.0	38.0	9.0	0.0	0.0	0.0
87.5°	172.0	178.0	118.0	47.0	26.0	11.0	5.0	1.0	0.0	0.0	0.0
90°	1.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0
92.5°	1.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0
95°	1.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0
97.5°	1.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0
100°	1.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0
102.5°	1.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0
105°	1.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0
107.5°	1.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0
110°	1.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P821301  
 CATALOG NUMBER: TT-D3-740-24VDC-RW-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
112.5°	1.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0
115°	1.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0
117.5°	1.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0
120°	1.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0
122.5°	1.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0
125°	1.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0
127.5°	1.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0
130°	1.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0
132.5°	1.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0
135°	1.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	1.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)