

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P832956

Luminaire Tested: **TTN-D0-830-U-DL-CG-UPL3**

Issue Date: 5/15/2024

Test Information

Test Method: LM-79-08
Report Number: P832956
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G3-2308-121-4) AND
Test Lab: INNOVATION CENTER
Issue Date: 5/15/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: TTN-D0-830-U-DL-CG-UPL3
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE WITH UPLIGHT
3000K, 80 CRI LEDS AND DRIVE LANE DISTRIBUTION WITH CLEAR GLASS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1764.7 lumens
Efficiency: N/A
Efficacy: 99.7 lumens/watt
Luminous Opening: Vertical Cylinder (Dia: 0.71' x H: 0.1')
IES Classification: Type IV - Short
BUG Rating: B0 - U4 - G1


Input Watts (W): 17.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P832956
 CATALOG NUMBER: TTN-D0-830-U-DL-CG-UPL3

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.3 fc
 Type IV - Short - N/A

REPORT NUMBER: P832956
CATALOG NUMBER: TTN-D0-830-U-DL-CG-UPL3

Luminous Intensity Polar Plot



— Vertical Plane Through 33-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P832956
 CATALOG NUMBER: TTN-D0-830-U-DL-CG-UPL3


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	226.2	370.3	596.6
	% Fixture	12.8	21.0	33.8
Street Side	Lumens	797.8	370.3	1168.1
	% Fixture	45.2	21.0	66.2
Total	Lumens	1024.0	740.7	1764.7
	% Fixture	58.0	42.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	9.2	0.5
10°-20°	29.7	1.7
20°-30°	62.7	3.6
30°-40°	113.9	6.5
40°-50°	180.0	10.2
50°-60°	239.1	13.5
60°-70°	230.1	13.0
70°-80°	135.1	7.7
80°-90°	24.2	1.4
90°-100°	16.5	0.9
100°-110°	168.0	9.5
110°-120°	245.6	13.9
120°-130°	142.5	8.1
130°-140°	75.5	4.3
140°-150°	44.8	2.5
150°-160°	27.6	1.6
160°-170°	15.1	0.9
170°-180°	4.9	0.3
0°-90°	1024.0	58.0
0°-180°	1764.7	100.0

Coefficient of Utilization



REPORT NUMBER: P832956


CATALOG NUMBER: TTN-D0-830-U-DL-CG-UPL3

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	68.4	3.9			
FM (30°-60°)	413.9	23.5			
FH (60°-80°)	295.4	16.7			G0/660
FVH (80°-90°)	20.1	1.1			G1/100
BL (0°-30°)	33.2	1.9	B0/110		
BM (30°-60°)	119.1	6.7	B0/220		
BH (60°-80°)	69.8	4.0	B0/110		G0/110
BVH (80°-90°)	4.1	0.2			G0/10
UL (90°-100°)	16.5	0.9		U2/50	
UH (100°-180°)	724.1	41.0		U4/1000	

BUG Rating: B0-U4-G1

Type IV Short





REPORT NUMBER: P832956

CATALOG NUMBER: TTN-D0-830-U-DL-CG-UPL3

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	33°	35°	45°	55°	65°	75°	85°
0°	95.9	95.9	95.9	95.9	95.9	95.9	95.9	95.9	95.9	95.9	95.9
2.5°	102.2	103.0	102.2	102.2	101.3	101.3	100.4	99.5	98.6	97.7	95.9
5°	113.8	113.8	112.9	111.1	110.2	109.3	107.5	104.8	103.0	100.4	97.7
7.5°	119.2	119.2	118.3	116.5	114.7	113.8	111.1	107.5	104.8	101.3	97.7
10°	126.3	127.2	125.5	123.7	121.9	121.0	117.4	112.9	108.4	103.9	98.6
12.5°	134.4	135.3	134.4	131.7	129.0	128.1	124.6	119.2	113.8	107.5	101.3
15°	145.2	147.0	144.3	142.5	139.8	138.9	134.4	128.1	121.9	113.8	105.7
17.5°	157.7	158.6	156.8	154.1	152.3	151.4	147.0	139.8	130.8	121.9	112.0
20°	172.0	172.9	172.0	168.5	166.7	165.8	161.3	153.2	142.5	132.6	120.1
22.5°	189.1	190.9	188.2	185.5	183.7	183.7	178.3	169.4	156.8	144.3	129.9
25°	208.8	211.5	207.9	206.1	204.3	203.4	198.9	188.2	173.8	158.6	140.7
27.5°	233.0	234.8	232.1	231.2	227.6	227.6	220.4	207.9	192.7	174.7	154.1
30°	254.5	256.3	254.5	254.5	251.8	250.9	243.7	231.2	212.4	190.9	165.8
32.5°	275.1	276.9	276.0	276.9	276.0	275.1	266.1	252.7	233.9	206.1	177.4
35°	295.7	298.4	297.5	300.2	299.3	298.4	291.2	275.1	252.7	224.9	190.0
37.5°	317.2	319.9	319.9	322.6	323.5	323.5	315.4	298.4	273.3	241.9	204.3
40°	340.5	343.2	343.2	347.7	349.5	349.5	340.5	323.5	295.7	260.8	219.5
42.5°	362.9	365.6	366.5	371.0	373.7	374.6	367.4	347.7	315.4	279.6	233.9
45°	384.4	387.1	389.8	398.8	403.2	402.3	397.0	376.4	340.5	299.3	249.1
47.5°	405.0	408.6	413.1	424.7	431.0	430.1	426.5	403.2	363.8	318.1	262.5
50°	421.2	423.8	432.8	445.3	453.4	454.3	448.9	426.5	383.5	332.4	272.4
52.5°	433.7	437.3	448.0	466.0	472.2	474.9	468.6	446.2	403.2	345.0	280.5
55°	442.7	442.7	458.8	479.4	488.4	490.2	490.2	462.4	414.9	353.1	285.0
57.5°	438.2	438.2	456.1	478.5	492.8	491.9	490.2	463.3	416.7	351.3	282.3
60°	425.6	428.3	445.3	467.8	482.1	481.2	475.8	451.6	407.7	344.1	276.9
62.5°	408.6	413.1	431.0	448.0	464.2	466.9	459.7	438.2	392.5	333.3	267.0
65°	376.4	382.6	405.0	423.8	436.4	441.8	432.8	413.1	371.9	312.7	246.4
67.5°	340.5	345.0	363.8	390.7	397.9	403.2	398.8	378.1	343.2	279.6	223.1
70°	299.3	306.5	319.0	345.9	353.9	359.3	359.3	338.7	305.6	245.5	195.3
72.5°	250.9	259.0	274.2	293.9	304.7	308.2	307.4	290.3	260.8	207.9	164.9
75°	198.0	204.3	222.2	236.6	248.2	250.9	250.0	235.7	208.8	167.6	130.8
77.5°	146.1	152.3	165.8	176.5	187.3	185.5	185.5	174.7	157.7	124.6	99.5
80°	95.9	101.3	112.9	116.5	128.1	127.2	127.2	119.2	107.5	83.3	66.3
82.5°	52.9	57.3	65.4	69.0	76.2	74.4	75.3	69.9	62.7	46.6	37.6
85°	18.8	22.4	26.9	29.6	33.2	33.2	33.2	28.7	26.9	17.9	15.2
87.5°	0.9	1.8	3.6	3.6	5.4	5.4	5.4	3.6	3.6	0.9	0.9
90°	6.3	6.3	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	6.3
92.5°	6.3	6.3	6.3	8.9	9.9	10.1	8.9	10.1	7.6	7.6	6.3
95°	7.6	7.6	8.9	11.4	13.4	13.9	15.2	15.2	8.9	8.9	7.6
97.5°	10.1	11.4	11.4	13.9	21.0	22.8	41.8	25.3	12.7	12.7	11.4
100°	16.5	17.7	17.7	31.7	60.1	67.2	90.0	64.6	32.9	24.1	17.7
102.5°	53.2	55.8	68.4	102.6	142.2	152.1	138.1	116.6	110.2	76.0	60.8
105°	135.6	134.3	144.5	171.1	204.5	212.9	209.1	192.6	174.9	150.8	139.4
107.5°	178.7	178.7	187.5	210.4	235.7	242.0	282.6	286.4	226.8	198.9	186.3
110°	201.5	201.5	209.1	228.1	261.5	269.9	326.9	324.4	280.0	245.8	229.4



REPORT NUMBER: P832956
 CATALOG NUMBER: TTN-D0-830-U-DL-CG-UPL3

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	33°	35°	45°	55°	65°	75°	85°
112.5°	206.5	207.8	218.0	247.1	283.6	292.7	318.1	306.7	288.9	273.7	261.0
115°	214.2	214.2	225.6	253.4	273.7	278.8	288.9	276.2	262.3	252.2	247.1
117.5°	211.6	215.4	218.0	233.2	246.3	249.6	257.2	250.9	231.9	224.3	221.8
120°	196.4	196.4	198.9	206.5	213.6	215.4	219.2	216.7	204.0	197.7	196.4
122.5°	174.9	176.1	174.9	178.7	183.7	185.0	188.8	186.3	176.1	173.6	173.6
125°	153.3	153.3	152.1	154.6	157.6	158.4	157.1	158.4	153.3	152.1	152.1
127.5°	138.1	136.9	134.3	135.6	136.6	136.9	136.9	138.1	133.1	134.3	135.6
130°	122.9	122.9	120.4	120.4	120.4	120.4	117.8	120.4	117.8	119.1	120.4
132.5°	109.0	109.0	105.2	103.9	103.9	103.9	103.9	105.2	103.9	106.4	109.0
135°	97.6	97.6	93.8	95.0	95.0	95.0	93.8	95.0	93.8	96.3	97.6
137.5°	88.7	88.7	86.2	86.2	86.2	86.2	84.9	86.2	86.2	87.4	90.0
140°	81.1	81.1	79.8	79.8	78.8	78.6	79.8	79.8	79.8	81.1	82.4
142.5°	77.3	76.0	74.8	73.5	74.5	74.8	74.8	74.8	73.5	74.8	77.3
145°	71.0	71.0	69.7	69.7	69.7	69.7	71.0	69.7	69.7	71.0	71.0
147.5°	67.2	67.2	65.9	67.2	67.2	67.2	67.2	67.2	65.9	67.2	67.2
150°	65.9	64.6	63.4	64.6	64.6	64.6	63.4	63.4	63.4	63.4	64.6
152.5°	62.1	62.1	60.8	62.1	61.1	60.8	60.8	60.8	60.8	60.8	62.1
155°	59.6	59.6	58.3	59.6	59.6	59.6	59.6	59.6	59.6	59.6	59.6
157.5°	57.0	58.3	57.0	57.0	57.0	57.0	57.0	57.0	57.0	57.0	58.3
160°	55.8	55.8	55.8	55.8	54.8	54.5	54.5	54.5	55.8	55.8	55.8
162.5°	54.5	54.5	54.5	54.5	53.5	53.2	53.2	53.2	53.2	54.5	54.5
165°	54.5	53.2	53.2	53.2	52.2	52.0	52.0	52.0	52.0	53.2	54.5
167.5°	52.0	52.0	52.0	52.0	52.0	52.0	50.7	50.7	52.0	52.0	52.0
170°	52.0	52.0	50.7	50.7	50.7	50.7	50.7	50.7	50.7	50.7	50.7
172.5°	52.0	52.0	52.0	52.0	51.0	50.7	50.7	50.7	50.7	50.7	52.0
175°	52.0	52.0	52.0	52.0	51.0	50.7	50.7	50.7	52.0	52.0	52.0
177.5°	52.0	52.0	52.0	52.0	51.0	50.7	52.0	52.0	52.0	52.0	52.0
180°	52.0	52.0	52.0	52.0	52.0	52.0	52.0	52.0	52.0	52.0	52.0



REPORT NUMBER: P832956

CATALOG NUMBER: TTN-D0-830-U-DL-CG-UPL3

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	95.9	95.9	95.9	95.9	95.9	95.9	95.9	95.9	95.9	95.9	95.9
2.5°	95.0	94.1	93.2	91.4	90.5	89.6	88.7	87.8	87.8	87.8	87.8
5°	95.9	95.0	92.3	89.6	86.9	84.2	82.4	81.5	80.6	79.8	79.8
7.5°	95.9	94.1	90.5	86.9	84.2	80.6	78.0	75.3	73.5	72.6	72.6
10°	96.8	94.1	89.6	86.0	81.5	77.1	73.5	69.9	68.1	66.3	66.3
12.5°	98.6	95.9	89.6	85.1	79.8	74.4	69.9	66.3	63.6	61.8	61.8
15°	102.2	98.6	91.4	85.1	78.9	72.6	68.1	63.6	60.9	59.1	59.1
17.5°	107.5	103.0	94.1	85.1	78.0	71.7	66.3	61.8	58.2	56.5	56.5
20°	113.8	108.4	97.7	86.9	78.0	70.8	65.4	60.0	56.5	54.7	54.7
22.5°	122.8	114.7	102.2	89.6	79.8	71.7	64.5	59.1	55.6	53.8	53.8
25°	132.6	123.7	107.5	93.2	81.5	71.7	64.5	59.1	55.6	53.8	52.9
27.5°	143.4	133.5	113.8	96.8	83.3	73.5	65.4	59.1	55.6	53.8	53.8
30°	153.2	141.6	120.1	101.3	86.0	74.4	66.3	60.0	55.6	53.8	53.8
32.5°	164.0	150.5	126.3	105.7	88.7	76.2	67.2	60.9	56.5	54.7	53.8
35°	174.7	159.5	132.6	109.3	91.4	78.0	68.1	61.8	57.3	55.6	55.6
37.5°	186.4	169.4	138.9	113.8	94.1	79.8	69.9	62.7	58.2	56.5	56.5
40°	198.9	179.2	145.2	117.4	96.8	81.5	71.7	64.5	60.0	58.2	58.2
42.5°	211.5	190.0	152.3	121.9	99.5	83.3	72.6	66.3	61.8	60.0	60.0
45°	224.0	198.9	158.6	126.3	102.2	86.0	75.3	68.1	63.6	61.8	61.8
47.5°	235.7	208.8	164.0	129.0	104.8	87.8	76.2	69.9	65.4	64.5	63.6
50°	243.7	215.1	167.6	131.7	105.7	88.7	78.0	70.8	67.2	65.4	65.4
52.5°	250.0	221.3	170.3	133.5	106.6	89.6	78.9	72.6	69.0	67.2	66.3
55°	253.6	222.2	170.3	131.7	105.7	89.6	78.9	72.6	69.0	67.2	67.2
57.5°	250.0	217.7	166.7	128.1	103.0	86.9	76.2	70.8	67.2	66.3	65.4
60°	242.8	210.6	159.5	122.8	98.6	82.4	72.6	68.1	65.4	64.5	63.6
62.5°	233.0	201.6	152.3	115.6	92.3	77.1	69.9	64.5	62.7	61.8	60.9
65°	213.3	184.6	140.7	106.6	84.2	70.8	63.6	60.0	58.2	56.5	55.6
67.5°	191.8	165.8	124.6	95.9	74.4	63.6	57.3	53.8	51.1	51.1	50.2
70°	168.5	146.1	107.5	81.5	64.5	55.6	49.3	46.6	44.8	44.8	43.9
72.5°	140.7	122.8	89.6	66.3	52.9	45.7	41.2	38.5	37.6	37.6	36.7
75°	112.9	96.8	70.8	52.0	41.2	35.8	32.3	30.5	29.6	29.6	28.7
77.5°	83.3	70.8	51.1	37.6	29.6	26.0	23.3	22.4	21.5	21.5	20.6
80°	55.6	46.6	33.2	24.2	17.9	16.1	14.3	14.3	13.4	14.3	13.4
82.5°	30.5	25.1	17.9	12.5	9.0	8.1	7.2	7.2	8.1	8.1	7.2
85°	11.6	9.0	6.3	3.6	2.7	2.7	2.7	2.7	2.7	2.7	1.8
87.5°	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	6.3	6.3	7.6	7.6	7.6	7.6	7.6	7.6	7.6	6.3	6.3
92.5°	6.3	6.3	7.6	7.6	10.1	8.9	10.1	8.9	6.3	6.3	6.3
95°	7.6	7.6	8.9	8.9	15.2	15.2	13.9	11.4	8.9	7.6	7.6
97.5°	10.1	11.4	12.7	12.7	25.3	41.8	22.8	13.9	11.4	11.4	10.1
100°	17.7	17.7	24.1	32.9	64.6	90.0	67.2	31.7	17.7	17.7	16.5
102.5°	58.3	60.8	76.0	110.2	116.6	138.1	152.1	102.6	68.4	55.8	53.2
105°	139.4	139.4	150.8	174.9	192.6	209.1	212.9	171.1	144.5	134.3	135.6
107.5°	185.0	186.3	198.9	226.8	286.4	282.6	242.0	210.4	187.5	178.7	178.7
110°	226.8	229.4	245.8	280.0	324.4	326.9	269.9	228.1	209.1	201.5	201.5



REPORT NUMBER: P832956
 CATALOG NUMBER: TTN-D0-830-U-DL-CG-UPL3

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
112.5°	258.5	261.0	273.7	288.9	306.7	318.1	292.7	247.1	218.0	207.8	206.5
115°	249.6	247.1	252.2	262.3	276.2	288.9	278.8	253.4	225.6	214.2	214.2
117.5°	218.0	221.8	224.3	231.9	250.9	257.2	249.6	233.2	218.0	215.4	211.6
120°	193.9	196.4	197.7	204.0	216.7	219.2	215.4	206.5	198.9	196.4	196.4
122.5°	171.1	173.6	173.6	176.1	186.3	188.8	185.0	178.7	174.9	176.1	174.9
125°	150.8	152.1	152.1	153.3	158.4	157.1	158.4	154.6	152.1	153.3	153.3
127.5°	134.3	135.6	134.3	133.1	138.1	136.9	136.9	135.6	134.3	136.9	138.1
130°	121.6	120.4	119.1	117.8	120.4	117.8	120.4	120.4	120.4	122.9	122.9
132.5°	109.0	109.0	106.4	103.9	105.2	103.9	103.9	103.9	105.2	109.0	109.0
135°	97.6	97.6	96.3	93.8	95.0	93.8	95.0	95.0	93.8	97.6	97.6
137.5°	91.2	90.0	87.4	86.2	86.2	84.9	86.2	86.2	86.2	88.7	88.7
140°	82.4	82.4	81.1	79.8	79.8	79.8	78.6	79.8	79.8	81.1	81.1
142.5°	77.3	77.3	74.8	73.5	74.8	74.8	74.8	73.5	74.8	76.0	77.3
145°	72.2	71.0	71.0	69.7	69.7	71.0	69.7	69.7	69.7	71.0	71.0
147.5°	68.4	67.2	67.2	65.9	67.2	67.2	67.2	67.2	65.9	67.2	67.2
150°	64.6	64.6	63.4	63.4	63.4	63.4	64.6	64.6	63.4	64.6	65.9
152.5°	63.4	62.1	60.8	60.8	60.8	60.8	60.8	62.1	60.8	62.1	62.1
155°	59.6	59.6	59.6	59.6	59.6	59.6	59.6	59.6	58.3	59.6	59.6
157.5°	58.3	58.3	57.0	57.0	57.0	57.0	57.0	57.0	57.0	58.3	57.0
160°	57.0	55.8	55.8	55.8	54.5	54.5	54.5	55.8	55.8	55.8	55.8
162.5°	55.8	54.5	54.5	53.2	53.2	53.2	53.2	54.5	54.5	54.5	54.5
165°	53.2	54.5	53.2	52.0	52.0	52.0	52.0	53.2	53.2	53.2	54.5
167.5°	53.2	52.0	52.0	52.0	50.7	50.7	52.0	52.0	52.0	52.0	52.0
170°	52.0	50.7	50.7	50.7	50.7	50.7	50.7	50.7	50.7	52.0	52.0
172.5°	52.0	52.0	50.7	50.7	50.7	50.7	50.7	52.0	52.0	52.0	52.0
175°	50.7	52.0	52.0	52.0	50.7	50.7	50.7	52.0	52.0	52.0	52.0
177.5°	52.0	52.0	52.0	52.0	52.0	52.0	50.7	52.0	52.0	52.0	52.0
180°	52.0	52.0	52.0	52.0	52.0	52.0	52.0	52.0	52.0	52.0	52.0

(END OF REPORT)