

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P832958

Luminaire Tested: **TTN-D0-830-U-DL-UPL2**

Issue Date: 5/15/2024

Test Information

Test Method: LM-79-08
Report Number: P832958
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G3-2308-121-4) AND
Test Lab: INNOVATION CENTER
Issue Date: 5/15/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: TTN-D0-830-U-DL-UPL2
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE WITH UPLIGHT
3000K, 80 CRI LEDS AND DRIVE LANE DISTRIBUTION
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1566.8 lumens
Efficiency: N/A
Efficacy: 103.1 lumens/watt
Luminous Opening: Vertical Cylinder (Dia: 0.71' x H: 0.1')
IES Classification: Type IV - Short
BUG Rating: B0 - U4 - G1


Input Watts (W): 15.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P832958
 CATALOG NUMBER: TTN-D0-830-U-DL-UPL2

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.2 fc
 Type IV - Short - N/A

REPORT NUMBER: P832958
CATALOG NUMBER: TTN-D0-830-U-DL-UPL2

Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P832958

CATALOG NUMBER: TTN-D0-830-U-DL-UPL2


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	220.1	267.0	487.2
	% Fixture	14.1	17.0	31.1
Street Side	Lumens	812.6	267.0	1079.6
	% Fixture	51.9	17.0	68.9
Total	Lumens	1032.7	534.0	1566.8
	% Fixture	65.9	34.1	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	8.2	0.5
10°-20°	26.2	1.7
20°-30°	55.3	3.5
30°-40°	101.0	6.4
40°-50°	164.1	10.5
50°-60°	228.1	14.6
60°-70°	236.5	15.1
70°-80°	169.5	10.8
80°-90°	43.9	2.8
90°-100°	11.9	0.8
100°-110°	121.1	7.7
110°-120°	177.1	11.3
120°-130°	102.8	6.6
130°-140°	54.4	3.5
140°-150°	32.3	2.1
150°-160°	19.9	1.3
160°-170°	10.9	0.7
170°-180°	3.5	0.2
0°-90°	1032.7	65.9
0°-180°	1566.8	100.0

Coefficient of Utilization



REPORT NUMBER: P832958


CATALOG NUMBER: TTN-D0-830-U-DL-UPL2

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	60.4	3.9			
FM (30°-60°)	385.3	24.6			
FH (60°-80°)	330.5	21.1			G0/660
FVH (80°-90°)	36.4	2.3			G1/100
BL (0°-30°)	29.2	1.9	B0/110		
BM (30°-60°)	107.9	6.9	B0/220		
BH (60°-80°)	75.4	4.8	B0/110		G0/110
BVH (80°-90°)	7.6	0.5			G0/10
UL (90°-100°)	11.9	0.8		U2/50	
UH (100°-180°)	522.1	33.3		U4/1000	

BUG Rating: B0-U4-G1

Type IV Short





REPORT NUMBER: P832958
 CATALOG NUMBER: TTN-D0-830-U-DL-UPL2

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	40°	45°	55°	65°	75°	85°
0°	86.9	86.9	86.9	86.9	86.9	86.9	86.9	86.9	86.9	86.9	86.9
2.5°	93.2	93.2	93.2	93.2	92.3	92.3	91.4	90.5	89.6	88.7	86.9
5°	101.3	101.3	100.4	99.5	97.7	96.8	95.9	94.1	92.3	90.5	87.8
7.5°	104.8	104.8	104.8	103.9	101.3	100.4	98.6	95.9	93.2	90.5	86.9
10°	111.1	111.1	110.2	109.3	106.6	105.7	103.9	100.4	95.9	91.4	86.9
12.5°	119.2	118.3	117.4	116.5	113.8	112.0	109.3	105.7	100.4	95.0	89.6
15°	129.0	127.2	127.2	125.4	122.8	120.1	118.3	112.9	107.5	100.4	93.2
17.5°	139.8	138.9	138.0	136.2	133.5	131.7	129.0	122.8	115.6	106.6	98.6
20°	153.2	151.4	152.3	149.6	147.0	146.1	141.6	134.4	125.4	115.6	105.7
22.5°	169.4	167.6	167.6	164.9	163.1	161.3	156.8	148.7	137.1	126.3	113.8
25°	187.3	185.5	185.5	183.7	181.9	180.1	174.7	165.8	152.3	138.9	124.6
27.5°	207.0	205.2	205.2	204.3	199.8	197.1	192.7	182.8	169.4	152.3	135.3
30°	227.6	225.8	227.6	225.8	223.1	217.7	212.4	201.6	186.4	167.6	147.0
32.5°	243.7	243.7	244.6	246.4	244.6	240.1	233.9	224.9	204.3	181.0	157.7
35°	262.5	262.5	264.3	267.0	266.1	261.6	255.4	245.5	224.0	196.2	169.4
37.5°	283.2	283.2	284.9	289.4	287.6	284.9	280.5	267.9	243.7	211.5	181.9
40°	305.6	304.7	306.5	312.7	313.6	310.0	304.7	292.1	264.3	231.2	195.3
42.5°	328.0	327.1	330.6	336.9	337.8	336.9	331.5	317.2	285.8	250.9	208.8
45°	350.4	350.4	355.7	365.6	370.1	368.3	363.8	345.9	312.7	271.5	226.7
47.5°	373.7	373.7	380.8	393.4	398.7	397.8	396.1	374.6	338.7	293.0	241.9
50°	391.6	391.6	403.2	417.6	426.5	430.1	421.1	401.4	361.1	311.8	254.5
52.5°	409.5	409.5	421.1	443.5	452.5	457.9	446.2	425.6	386.2	328.9	266.1
55°	418.5	420.2	436.4	457.9	472.2	469.5	474.0	446.2	402.3	341.4	273.3
57.5°	419.4	422.0	440.0	462.4	478.5	477.6	478.5	453.4	408.6	344.1	274.2
60°	414.9	419.4	435.5	457.9	473.1	480.3	471.3	448.9	405.0	341.4	273.3
62.5°	404.1	413.1	430.1	447.1	469.5	472.2	465.1	446.2	395.2	338.7	268.8
65°	379.9	389.8	414.0	433.7	451.6	455.2	447.1	431.0	385.3	326.2	254.5
67.5°	355.7	362.0	382.6	413.1	425.6	429.2	426.5	407.7	368.3	301.1	237.5
70°	328.0	336.0	352.1	383.5	396.1	395.2	403.2	381.7	342.3	279.6	219.5
72.5°	290.3	302.0	318.1	344.1	359.3	353.9	366.5	348.6	308.2	252.7	195.3
75°	246.4	256.3	276.9	297.5	314.5	308.2	318.1	305.6	268.8	220.4	167.6
77.5°	197.1	208.8	227.6	246.4	258.1	258.1	262.5	251.8	223.1	181.0	137.1
80°	146.1	156.8	173.8	187.3	198.0	198.9	203.4	198.0	172.0	140.7	104.8
82.5°	96.8	102.2	117.4	128.1	138.9	138.0	145.2	141.6	120.1	96.8	69.9
85°	41.2	44.8	57.3	66.3	76.2	72.6	82.4	81.5	64.5	46.6	31.4
87.5°	1.8	2.7	2.7	1.8	2.7	0.9	2.7	3.6	2.7	1.8	1.8
90°	4.6	4.6	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	4.6
92.5°	4.6	4.6	4.6	6.4	7.3	6.8	6.4	7.3	5.5	5.5	4.6
95°	5.5	5.5	6.4	8.2	10.1	10.6	11.0	11.0	6.4	6.4	5.5
97.5°	7.3	8.2	8.2	10.1	16.4	23.3	30.2	18.3	9.1	9.1	8.2
100°	11.9	12.8	12.8	22.8	48.4	56.6	64.9	46.6	23.8	17.4	12.8
102.5°	38.4	40.2	49.3	74.0	109.6	104.6	99.6	84.1	79.5	54.8	43.9
105°	97.8	96.8	104.2	123.3	153.5	152.2	150.8	138.9	126.1	108.7	100.5
107.5°	128.8	128.8	135.2	151.7	174.5	189.1	203.7	206.5	163.5	143.4	134.3
110°	145.3	145.3	150.8	164.5	194.6	215.2	235.7	233.9	201.9	177.3	165.4



REPORT NUMBER: P832958
 CATALOG NUMBER: TTN-D0-830-U-DL-UPL2

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	40°	45°	55°	65°	75°	85°
112.5°	148.9	149.8	157.1	178.2	211.1	220.2	229.3	221.1	208.3	197.4	188.2
115°	154.4	154.4	162.6	182.7	201.0	204.6	208.3	199.2	189.1	181.8	178.2
117.5°	152.6	155.3	157.1	168.1	180.0	182.8	185.5	180.9	167.2	161.7	159.9
120°	141.6	141.6	143.4	148.9	155.3	156.7	158.1	156.2	147.1	142.5	141.6
122.5°	126.1	127.0	126.1	128.8	133.4	134.8	136.1	134.3	127.0	125.2	125.2
125°	110.6	110.6	109.6	111.5	114.2	113.8	113.3	114.2	110.6	109.6	109.6
127.5°	99.6	98.7	96.8	97.8	98.7	98.7	98.7	99.6	95.9	96.8	97.8
130°	88.6	88.6	86.8	86.8	86.8	85.9	85.0	86.8	85.0	85.9	86.8
132.5°	78.6	78.6	75.8	74.9	74.9	74.9	74.9	75.8	74.9	76.7	78.6
135°	70.4	70.4	67.6	68.5	68.5	68.0	67.6	68.5	67.6	69.4	70.4
137.5°	64.0	64.0	62.1	62.1	62.1	61.6	61.2	62.1	62.1	63.0	64.9
140°	58.5	58.5	57.6	57.6	56.6	57.1	57.6	57.6	57.6	58.5	59.4
142.5°	55.7	54.8	53.9	53.0	53.9	53.9	53.9	53.9	53.0	53.9	55.7
145°	51.2	51.2	50.3	50.3	50.3	50.8	51.2	50.3	50.3	51.2	51.2
147.5°	48.4	48.4	47.5	48.4	48.4	48.4	48.4	48.4	47.5	48.4	48.4
150°	47.5	46.6	45.7	46.6	46.6	46.2	45.7	45.7	45.7	45.7	46.6
152.5°	44.8	44.8	43.9	44.8	43.9	43.9	43.9	43.9	43.9	43.9	44.8
155°	42.9	42.9	42.0	42.9	42.9	42.9	42.9	42.9	42.9	42.9	42.9
157.5°	41.1	42.0	41.1	41.1	41.1	41.1	41.1	41.1	41.1	41.1	42.0
160°	40.2	40.2	40.2	40.2	39.3	39.3	39.3	39.3	40.2	40.2	40.2
162.5°	39.3	39.3	39.3	39.3	38.4	38.4	38.4	38.4	38.4	39.3	39.3
165°	39.3	38.4	38.4	38.4	37.5	37.5	37.5	37.5	37.5	38.4	39.3
167.5°	37.5	37.5	37.5	37.5	37.5	37.0	36.5	36.5	37.5	37.5	37.5
170°	37.5	37.5	36.5	36.5	36.5	36.5	36.5	36.5	36.5	36.5	36.5
172.5°	37.5	37.5	37.5	37.5	36.5	36.5	36.5	36.5	36.5	36.5	37.5
175°	37.5	37.5	37.5	37.5	36.5	36.5	36.5	36.5	37.5	37.5	37.5
177.5°	37.5	37.5	37.5	37.5	36.5	37.0	37.5	37.5	37.5	37.5	37.5
180°	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5



REPORT NUMBER: P832958
 CATALOG NUMBER: TTN-D0-830-U-DL-UPL2

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	86.9	86.9	86.9	86.9	86.9	86.9	86.9	86.9	86.9	86.9	86.9
2.5°	86.9	86.0	84.2	83.3	82.4	80.6	80.6	79.7	79.7	79.7	78.9
5°	86.9	85.1	83.3	80.6	78.9	77.1	75.3	73.5	72.6	72.6	71.7
7.5°	85.1	83.3	80.6	78.0	75.3	71.7	69.9	66.3	65.4	64.5	64.5
10°	85.1	83.3	78.9	75.3	71.7	68.1	65.4	61.8	59.1	58.2	58.2
12.5°	86.0	83.3	78.9	74.4	69.9	65.4	61.8	58.2	55.6	53.8	53.8
15°	89.6	86.0	80.6	74.4	69.0	63.6	60.0	55.6	52.9	51.1	51.1
17.5°	94.1	90.5	82.4	75.3	69.0	62.7	58.2	53.8	51.1	49.3	48.4
20°	100.4	95.0	86.0	76.2	69.0	62.7	57.3	52.9	49.3	47.5	47.5
22.5°	107.5	101.3	89.6	78.0	69.9	62.7	57.3	52.0	48.4	46.6	46.6
25°	116.5	108.4	95.0	81.5	71.7	63.6	57.3	52.0	48.4	46.6	46.6
27.5°	126.3	117.4	100.4	85.1	73.5	64.5	57.3	52.0	48.4	46.6	46.6
30°	135.3	125.4	105.7	88.7	76.2	65.4	58.2	52.9	49.3	47.5	46.6
32.5°	145.2	132.6	111.1	92.3	78.0	67.2	59.1	53.8	49.3	47.5	47.5
35°	155.0	141.6	116.5	96.8	80.6	69.0	60.0	54.7	50.2	48.4	48.4
37.5°	165.8	151.4	122.8	100.4	83.3	70.8	61.8	55.6	51.1	49.3	49.3
40°	178.3	161.3	129.0	104.8	86.0	72.6	62.7	57.3	52.9	51.1	51.1
42.5°	190.0	170.3	135.3	108.4	88.7	74.4	64.5	58.2	54.7	52.9	52.9
45°	201.6	181.0	141.6	112.9	91.4	77.1	66.3	60.9	56.5	54.7	54.7
47.5°	215.1	190.9	148.7	116.5	94.1	78.9	68.1	62.7	58.2	57.3	56.5
50°	225.8	198.0	153.2	120.1	95.9	80.6	69.9	63.6	60.0	58.2	58.2
52.5°	235.7	205.2	156.8	121.9	96.8	81.5	71.7	65.4	61.8	60.0	60.0
55°	241.0	207.9	159.5	121.9	97.7	82.4	71.7	65.4	61.8	60.9	60.0
57.5°	241.0	207.9	157.7	120.1	95.9	80.6	70.8	64.5	61.8	60.0	60.0
60°	237.5	205.2	153.2	116.5	93.2	78.0	69.0	62.7	60.0	59.1	59.1
62.5°	232.1	200.7	149.6	112.0	89.6	74.4	66.3	60.0	58.2	58.2	57.3
65°	217.7	187.3	141.6	105.7	84.2	69.9	62.7	57.3	55.6	54.7	53.8
67.5°	202.5	174.7	129.0	98.6	77.1	65.4	58.2	53.8	51.1	51.1	50.2
70°	187.3	161.3	117.4	88.7	69.0	60.0	52.9	48.4	46.6	46.6	46.6
72.5°	166.7	144.3	103.9	78.0	60.9	52.9	47.5	43.0	42.1	42.1	41.2
75°	142.5	122.8	87.8	66.3	51.1	44.8	40.3	35.8	35.8	35.8	35.8
77.5°	116.5	99.5	69.9	52.9	40.3	35.8	33.2	29.6	29.6	29.6	29.6
80°	87.8	73.5	51.1	38.5	29.6	26.0	24.2	22.4	23.3	23.3	22.4
82.5°	57.3	48.4	32.3	24.2	18.8	17.0	17.0	15.2	16.1	16.1	16.1
85°	25.1	21.5	13.4	10.8	9.0	9.0	9.0	8.1	9.0	9.0	9.0
87.5°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	0.0	0.9	1.8	0.9
90°	4.6	4.6	5.5	5.5	5.5	5.5	5.5	5.5	5.5	4.6	4.6
92.5°	4.6	4.6	5.5	5.5	7.3	6.4	7.3	6.4	4.6	4.6	4.6
95°	5.5	5.5	6.4	6.4	11.0	11.0	10.1	8.2	6.4	5.5	5.5
97.5°	7.3	8.2	9.1	9.1	18.3	30.2	16.4	10.1	8.2	8.2	7.3
100°	12.8	12.8	17.4	23.8	46.6	64.9	48.4	22.8	12.8	12.8	11.9
102.5°	42.0	43.9	54.8	79.5	84.1	99.6	109.6	74.0	49.3	40.2	38.4
105°	100.5	100.5	108.7	126.1	138.9	150.8	153.5	123.3	104.2	96.8	97.8
107.5°	133.4	134.3	143.4	163.5	206.5	203.7	174.5	151.7	135.2	128.8	128.8
110°	163.5	165.4	177.3	201.9	233.9	235.7	194.6	164.5	150.8	145.3	145.3



REPORT NUMBER: P832958
 CATALOG NUMBER: TTN-D0-830-U-DL-UPL2

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
112.5°	186.4	188.2	197.4	208.3	221.1	229.3	211.1	178.2	157.1	149.8	148.9
115°	180.0	178.2	181.8	189.1	199.2	208.3	201.0	182.7	162.6	154.4	154.4
117.5°	157.1	159.9	161.7	167.2	180.9	185.5	180.0	168.1	157.1	155.3	152.6
120°	139.8	141.6	142.5	147.1	156.2	158.1	155.3	148.9	143.4	141.6	141.6
122.5°	123.3	125.2	125.2	127.0	134.3	136.1	133.4	128.8	126.1	127.0	126.1
125°	108.7	109.6	109.6	110.6	114.2	113.3	114.2	111.5	109.6	110.6	110.6
127.5°	96.8	97.8	96.8	95.9	99.6	98.7	98.7	97.8	96.8	98.7	99.6
130°	87.7	86.8	85.9	85.0	86.8	85.0	86.8	86.8	86.8	88.6	88.6
132.5°	78.6	78.6	76.7	74.9	75.8	74.9	74.9	74.9	75.8	78.6	78.6
135°	70.4	70.4	69.4	67.6	68.5	67.6	68.5	68.5	67.6	70.4	70.4
137.5°	65.8	64.9	63.0	62.1	62.1	61.2	62.1	62.1	62.1	64.0	64.0
140°	59.4	59.4	58.5	57.6	57.6	57.6	56.6	57.6	57.6	58.5	58.5
142.5°	55.7	55.7	53.9	53.0	53.9	53.9	53.9	53.0	53.9	54.8	55.7
145°	52.1	51.2	51.2	50.3	50.3	51.2	50.3	50.3	50.3	51.2	51.2
147.5°	49.3	48.4	48.4	47.5	48.4	48.4	48.4	48.4	47.5	48.4	48.4
150°	46.6	46.6	45.7	45.7	45.7	45.7	46.6	46.6	45.7	46.6	47.5
152.5°	45.7	44.8	43.9	43.9	43.9	43.9	43.9	44.8	43.9	44.8	44.8
155°	42.9	42.9	42.9	42.9	42.9	42.9	42.9	42.9	42.0	42.9	42.9
157.5°	42.0	42.0	41.1	41.1	41.1	41.1	41.1	41.1	41.1	42.0	41.1
160°	41.1	40.2	40.2	40.2	39.3	39.3	39.3	40.2	40.2	40.2	40.2
162.5°	40.2	39.3	39.3	38.4	38.4	38.4	38.4	39.3	39.3	39.3	39.3
165°	38.4	39.3	38.4	37.5	37.5	37.5	37.5	38.4	38.4	38.4	39.3
167.5°	38.4	37.5	37.5	37.5	36.5	36.5	37.5	37.5	37.5	37.5	37.5
170°	37.5	36.5	36.5	36.5	36.5	36.5	36.5	36.5	36.5	37.5	37.5
172.5°	37.5	37.5	36.5	36.5	36.5	36.5	36.5	37.5	37.5	37.5	37.5
175°	36.5	37.5	37.5	37.5	36.5	36.5	36.5	37.5	37.5	37.5	37.5
177.5°	37.5	37.5	37.5	37.5	37.5	37.5	36.5	37.5	37.5	37.5	37.5
180°	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5

(END OF REPORT)