

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P832527

Luminaire Tested: **TTN-D0-830-U-MQ-CG**

Issue Date: 5/14/2024

Test Information

Test Method: LM-79-08
Report Number: P832527
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2312-254-13)
Test Lab: INNOVATION CENTER
Issue Date: 5/14/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TTN-D0-830-U-MQ-CG
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE
3000K, 80 CRI LEDS AND MEDIUM DISTRIBUTION WITH CLEAR GLASS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1104 lumens
Efficiency: N/A
Efficacy: 103.2 lumens/watt
Luminous Opening: Circular (Dia: 0.71' x H: 0')
IES Classification: Type V - Short
BUG Rating: B1 - U0 - G1


Input Watts (W): 10.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P832527
 CATALOG NUMBER: TTN-D0-830-U-MQ-CG

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.4 fc
 Type V - Short - N/A

REPORT NUMBER: P832527
CATALOG NUMBER: TTN-D0-830-U-MQ-CG

Luminous Intensity Polar Plot



REPORT NUMBER: P832527

CATALOG NUMBER: TTN-D0-830-U-MQ-CG


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	552.0	0.0	552.0
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	552.0	0.0	552.0
	% Fixture	50.0	0.0	50.0
Total	Lumens	1104.0	0.0	1104.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.7	2.2
10°-20°	71.4	6.5
20°-30°	114.8	10.4
30°-40°	153.3	13.9
40°-50°	186.3	16.9
50°-60°	216.5	19.6
60°-70°	199.7	18.1
70°-80°	116.9	10.6
80°-90°	20.5	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	1104.0	100.0
0°-180°	1104.0	100.0

Coefficient of Utilization



REPORT NUMBER: P832527


CATALOG NUMBER: TTN-D0-830-U-MQ-CG

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	105.4	9.5			
FM (30°-60°)	278.0	25.2			
FH (60°-80°)	158.3	14.3			G0/660
FVH (80°-90°)	10.2	0.9			G1/100
BL (0°-30°)	105.4	9.5	B0/110		
BM (30°-60°)	278.0	25.2	B1/1000		
BH (60°-80°)	158.3	14.3	B1/500		G0/660
BVH (80°-90°)	10.2	0.9			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type V Short





REPORT NUMBER: P832527
 CATALOG NUMBER: TTN-D0-830-U-MQ-CG

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	262.6	262.6	262.6	262.6	262.6	262.6	262.6	262.6	262.6	262.6	262.6
2.5°	260.0	260.8	260.0	260.0	260.0	260.0	260.0	260.0	260.0	260.0	260.8
5°	260.8	260.8	260.8	260.8	260.0	260.0	260.0	260.0	260.0	260.8	260.8
7.5°	258.2	258.2	258.2	258.2	258.2	257.3	258.2	258.2	258.2	258.2	258.2
10°	255.5	255.5	255.5	255.5	255.5	255.5	255.5	255.5	255.5	255.5	255.5
12.5°	253.7	253.7	253.7	253.7	253.7	253.7	253.7	253.7	253.7	252.8	252.8
15°	251.9	251.9	251.9	251.9	252.8	252.8	251.9	251.9	251.9	251.9	251.9
17.5°	250.1	250.1	250.1	250.1	251.0	251.0	251.0	250.1	250.1	250.1	250.1
20°	248.3	248.3	248.3	248.3	249.2	249.2	249.2	249.2	249.2	248.3	248.3
22.5°	247.4	247.4	247.4	247.4	248.3	248.3	248.3	248.3	247.4	247.4	247.4
25°	246.5	247.4	247.4	247.4	248.3	249.2	249.2	248.3	247.4	246.5	246.5
27.5°	247.4	247.4	247.4	248.3	248.3	249.2	249.2	248.3	247.4	247.4	247.4
30°	246.5	246.5	246.5	247.4	248.3	249.2	248.3	248.3	247.4	246.5	246.5
32.5°	244.7	244.7	245.6	246.5	247.4	247.4	247.4	246.5	245.6	244.7	244.7
35°	242.9	242.9	242.9	243.8	245.6	245.6	245.6	244.7	243.8	242.9	242.0
37.5°	240.2	241.1	241.1	242.9	243.8	244.7	243.8	242.9	241.1	240.2	240.2
40°	238.4	238.4	239.3	241.1	242.9	242.9	242.0	241.1	239.3	238.4	238.4
42.5°	235.7	235.7	237.5	239.3	242.0	242.0	241.1	239.3	237.5	235.7	235.7
45°	235.7	235.7	237.5	241.1	242.9	244.7	242.9	241.1	237.5	235.7	234.9
47.5°	236.6	236.6	238.4	242.9	246.5	248.3	245.6	242.0	238.4	236.6	235.7
50°	234.9	235.7	239.3	243.8	248.3	249.2	248.3	242.9	239.3	234.9	234.9
52.5°	235.7	235.7	240.2	247.4	251.9	253.7	251.9	247.4	239.3	234.9	234.9
55°	234.0	233.1	239.3	247.4	254.6	258.2	254.6	247.4	238.4	233.1	232.2
57.5°	225.9	225.9	234.0	242.0	251.0	252.8	250.1	242.0	233.1	225.9	224.1
60°	215.1	216.0	224.1	233.1	241.1	242.0	240.2	233.1	224.1	216.0	213.3
62.5°	203.5	205.3	213.3	222.3	232.2	234.0	231.3	222.3	211.5	206.2	201.7
65°	186.4	189.1	198.1	208.0	218.7	217.8	217.8	207.1	199.0	190.0	185.6
67.5°	167.6	170.3	176.6	190.0	199.0	198.1	197.2	190.0	176.6	170.3	167.6
70°	147.0	148.8	155.1	168.5	176.6	177.5	174.8	167.6	155.1	150.6	146.1
72.5°	122.8	123.7	132.7	143.4	151.5	150.6	149.7	143.4	131.8	127.3	121.9
75°	96.8	97.7	105.8	115.6	121.9	121.0	120.1	115.6	105.8	100.4	95.9
77.5°	72.6	71.7	79.8	86.9	90.5	91.4	89.6	86.1	78.9	74.4	71.7
80°	47.5	46.6	53.8	59.2	61.9	61.9	61.0	58.3	52.9	49.3	47.5
82.5°	26.9	26.0	30.5	34.1	36.8	35.9	35.0	33.2	30.5	27.8	26.0
85°	9.9	9.9	12.5	14.3	16.1	16.1	15.2	14.3	11.7	10.8	9.9
87.5°	0.9	0.9	1.8	2.7	2.7	2.7	1.8	1.8	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)