

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P558483 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **GFLD-SA1A-935-U-WR-XX**

Issue Date: 7/20/2021

Test Information

Test Method: LM-79-08
Report Number: P558483 (CONVERTED FROM TYPE C PHOTOMETRY)
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2101-125-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/20/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GFLD-SA1A-935-U-WR-XX
Description: GALLEON FLOOD, ONE LIGHT SQAURE, WIDE SYMMETRICAL ROUND N6
Light Source: (16) 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


| | | | |
|-------------------|--|----------------------|-----------------|
| Lumens per Lamp: | N/A | NEMA Type: | 6H x 6V |
| Luminaire Lumens: | 2136.1 lumens | Max Intensity: | 1578.3 candela |
| Efficiency: | N/A | Max Intensity Angle: | 0°H x 2.5°V |
| Efficacy: | 118.7 lumens/watt | | |
| Luminous Opening: | Rectangular (W 0.5' x L: 0.5' x H: 0') | | |
| Beam Angle (50%): | 68°H x 68.7°V | Field Angle (10%): | 114°H x 113.4°V |
| Beam Lumens: | 1280.7 lumens | Field Lumens: | 2040.5 lumens |
| Beam Efficiency: | 60.0% | Field Efficiency: | 95.5% |

Input Watts (W): 18
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



REPORT NUMBER: P558483 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: GFLD-SA1A-935-U-WR-XX

Iso-Candela Plot






REPORT NUMBER: P558483 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: GFLD-SA1A-935-U-WR-XX

Lumen Table

| | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|------|------|------|------|------|------|------|------|-----|-----|-----|-----|----|----|----|
| 90 | | | | | | | | | | | | | | | | | | | |
| 80 | 0.0 | 0.2 | 0.5 | 0.9 | 0.6 | 0.9 | 0.5 | 0.2 | 0.0 | | | | | | | | | | |
| 70 | | | | | | | | | | | | | | | | | | | |
| 60 | 0.1 | 0.1 | 0.3 | 0.5 | 0.7 | 0.9 | 1.1 | 1.2 | 1.2 | 1.1 | 0.9 | 0.7 | 0.5 | 0.3 | 0.1 | 0.1 | | | |
| 50 | | 0.2 | 0.5 | 0.9 | 1.7 | 3.2 | 4.8 | 5.8 | 5.8 | 4.8 | 3.2 | 1.7 | 0.9 | 0.5 | 0.2 | | | | |
| 40 | 0.2 | 0.3 | 0.7 | 2.0 | 5.4 | 9.0 | 11.9 | 13.6 | 13.6 | 11.9 | 9.0 | 5.4 | 2.0 | 0.7 | 0.3 | 0.2 | | | |
| 30 | | 0.4 | 1.2 | 4.7 | 9.7 | 15.1 | 20.0 | 22.9 | 22.9 | 20.0 | 15.1 | 9.7 | 4.7 | 1.2 | 0.4 | | | | |
| 20 | 0.2 | 0.5 | 2.2 | 7.1 | 13.7 | 21.5 | 28.7 | 33.2 | 33.2 | 28.7 | 21.5 | 13.7 | 7.1 | 2.2 | 0.5 | 0.2 | | | |
| 10 | | 0.5 | 3.1 | 8.9 | 16.9 | 26.8 | 36.5 | 42.7 | 42.7 | 36.5 | 26.8 | 16.9 | 8.9 | 3.1 | 0.5 | | | | |
| 0 | 0.2 | 0.6 | 3.6 | 9.8 | 18.7 | 30.0 | 41.0 | 46.9 | 46.9 | 41.0 | 30.0 | 18.7 | 9.8 | 3.6 | 0.6 | 0.2 | | | |
| -10 | | 0.6 | 3.6 | 9.8 | 18.7 | 30.0 | 41.0 | 46.9 | 46.9 | 41.0 | 30.0 | 18.7 | 9.8 | 3.6 | 0.6 | | | | |
| -20 | 0.2 | 0.5 | 3.1 | 8.9 | 16.9 | 26.8 | 36.5 | 42.7 | 42.7 | 36.5 | 26.8 | 16.9 | 8.9 | 3.1 | 0.5 | 0.2 | | | |
| -30 | | 0.5 | 2.2 | 7.1 | 13.7 | 21.5 | 28.7 | 33.2 | 33.2 | 28.7 | 21.5 | 13.7 | 7.1 | 2.2 | 0.5 | | | | |
| -40 | 0.2 | 0.4 | 1.2 | 4.7 | 9.7 | 15.1 | 20.0 | 22.9 | 22.9 | 20.0 | 15.1 | 9.7 | 4.7 | 1.2 | 0.4 | 0.2 | | | |
| -50 | | 0.3 | 0.7 | 2.0 | 5.4 | 9.0 | 11.9 | 13.6 | 13.6 | 11.9 | 9.0 | 5.4 | 2.0 | 0.7 | 0.3 | | | | |
| -60 | 0.1 | 0.2 | 0.5 | 0.9 | 1.7 | 3.2 | 4.8 | 5.8 | 5.8 | 4.8 | 3.2 | 1.7 | 0.9 | 0.5 | 0.2 | 0.1 | | | |
| -70 | | 0.1 | 0.3 | 0.5 | 0.7 | 0.9 | 1.1 | 1.2 | 1.2 | 1.1 | 0.9 | 0.7 | 0.5 | 0.3 | 0.1 | | | | |
| -80 | 0.0 | 0.2 | 0.5 | 0.9 | 0.6 | 0.9 | 0.5 | 0.2 | 0.0 | | | | | | | | | | |
| -90 | | | | | | | | | | | | | | | | | | | |
| | -90 | -80 | -70 | -60 | -50 | -40 | -30 | -20 | -10 | 0 | 10 | 20 | 30 | 40 | 50 | 60 | 70 | 80 | 90 |

REPORT NUMBER: P558483 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: GFLD-SA1A-935-U-WR-XX


Luminous Intensity Polar Plot



— Vertical Distribution Through 0-Deg - - - Horizontal Distribution Through 2.5-Deg

REPORT NUMBER: P558483 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: GFLD-SA1A-935-U-WR-XX

Luminous Intensity Plot



Beam:
H Angle: 68°
V Angle: 68.7°
Lumens: 1280.7
Efficiency: 60.0%

Field:
H Angle: 114°
V Angle: 113.4°
Lumens: 2040.5
Efficiency: 95.5%

Spill:
Lumens: 95.5
Efficiency: 4.5%

- Vertical Distribution through 0-Deg
- - Horizontal Distribution through 2.5-Deg



REPORT NUMBER: P558483 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: GFLD-SA1A-935-U-WR-XX

FIELD
 BEAM

CANDELA DISTRIBUTION:

| | -90° | -87.5° | -85° | -82.5° | -80° | -77.5° | -75° | -72.5° | -70° | -67.5° | -65° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.1 | 0.1 | 0.1 | 0.1 | 0.2 | 0.2 | 0.2 | 0.2 | 0.3 |
| 85° | 0.0 | 0.1 | 0.1 | 0.2 | 0.2 | 0.3 | 0.3 | 0.4 | 0.4 | 0.5 | 0.5 |
| 82.5° | 0.0 | 0.1 | 0.2 | 0.2 | 0.3 | 0.4 | 0.5 | 0.5 | 0.6 | 0.9 | 1.1 |
| 80° | 0.0 | 0.1 | 0.2 | 0.3 | 0.4 | 0.5 | 0.7 | 1.0 | 1.3 | 1.6 | 2.0 |
| 77.5° | 0.0 | 0.1 | 0.3 | 0.4 | 0.5 | 0.7 | 1.1 | 1.5 | 1.9 | 2.3 | 2.9 |
| 75° | 0.0 | 0.2 | 0.3 | 0.5 | 0.6 | 1.0 | 1.5 | 2.0 | 2.6 | 3.5 | 4.4 |
| 72.5° | 0.0 | 0.2 | 0.4 | 0.5 | 0.8 | 1.3 | 2.0 | 2.7 | 3.7 | 4.8 | 5.8 |
| 70° | 0.0 | 0.2 | 0.4 | 0.6 | 1.0 | 1.6 | 2.4 | 3.7 | 4.9 | 6.1 | 7.7 |
| 67.5° | 0.0 | 0.2 | 0.5 | 0.7 | 1.2 | 1.9 | 3.2 | 4.7 | 6.0 | 7.7 | 9.7 |
| 65° | 0.0 | 0.3 | 0.5 | 0.9 | 1.4 | 2.3 | 3.9 | 5.6 | 7.4 | 9.4 | 11.6 |
| 62.5° | 0.0 | 0.3 | 0.6 | 1.0 | 1.6 | 2.8 | 4.5 | 6.7 | 8.6 | 10.9 | 13.4 |
| 60° | 0.0 | 0.3 | 0.6 | 1.1 | 1.8 | 3.2 | 5.1 | 7.7 | 9.9 | 12.6 | 15.2 |
| 57.5° | 0.0 | 0.3 | 0.7 | 1.2 | 2.0 | 3.6 | 5.7 | 8.6 | 11.4 | 14.3 | 16.7 |
| 55° | 0.0 | 0.3 | 0.7 | 1.3 | 2.2 | 3.9 | 6.3 | 9.3 | 12.9 | 16.0 | 18.1 |
| 52.5° | 0.0 | 0.4 | 0.8 | 1.3 | 2.4 | 4.2 | 6.7 | 10.3 | 14.5 | 17.2 | 19.4 |
| 50° | 0.0 | 0.4 | 0.8 | 1.4 | 2.6 | 4.5 | 7.1 | 11.3 | 16.0 | 18.5 | 20.9 |
| 47.5° | 0.0 | 0.4 | 0.9 | 1.5 | 2.8 | 4.7 | 7.4 | 12.2 | 17.1 | 19.8 | 22.2 |
| 45° | 0.0 | 0.4 | 0.9 | 1.6 | 2.9 | 4.9 | 8.0 | 12.9 | 17.6 | 20.9 | 23.5 |
| 42.5° | 0.0 | 0.4 | 1.0 | 1.6 | 2.9 | 5.0 | 8.5 | 13.3 | 17.9 | 21.9 | 24.9 |
| 40° | 0.0 | 0.5 | 1.0 | 1.7 | 3.0 | 5.0 | 9.0 | 13.5 | 18.1 | 22.8 | 26.3 |
| 37.5° | 0.0 | 0.5 | 1.1 | 1.8 | 3.0 | 5.0 | 9.3 | 13.5 | 18.3 | 23.1 | 27.6 |
| 35° | 0.0 | 0.5 | 1.1 | 1.9 | 3.0 | 5.1 | 9.5 | 13.5 | 18.4 | 24.0 | 28.9 |
| 32.5° | 0.0 | 0.5 | 1.1 | 1.9 | 3.0 | 5.3 | 9.5 | 13.3 | 18.6 | 25.1 | 30.3 |
| 30° | 0.0 | 0.5 | 1.2 | 2.0 | 2.9 | 5.4 | 9.3 | 13.1 | 18.8 | 26.4 | 31.5 |
| 27.5° | 0.0 | 0.5 | 1.2 | 2.1 | 3.0 | 5.4 | 9.1 | 13.1 | 19.3 | 27.9 | 32.7 |
| 25° | 0.0 | 0.5 | 1.2 | 2.1 | 3.0 | 5.3 | 8.8 | 13.1 | 20.3 | 29.0 | 33.8 |
| 22.5° | 0.0 | 0.6 | 1.3 | 2.2 | 3.1 | 5.3 | 8.4 | 13.1 | 21.3 | 29.9 | 35.3 |
| 20° | 0.0 | 0.6 | 1.3 | 2.2 | 3.2 | 5.6 | 7.9 | 13.0 | 22.4 | 30.7 | 36.5 |
| 17.5° | 0.0 | 0.6 | 1.3 | 2.3 | 3.3 | 5.8 | 7.8 | 12.9 | 23.5 | 31.5 | 37.6 |
| 15° | 0.0 | 0.6 | 1.3 | 2.3 | 3.4 | 6.0 | 8.0 | 12.8 | 24.6 | 32.1 | 38.6 |
| 12.5° | 0.0 | 0.6 | 1.4 | 2.3 | 3.5 | 6.1 | 8.1 | 12.7 | 25.5 | 32.7 | 39.4 |
| 10° | 0.0 | 0.6 | 1.4 | 2.4 | 3.5 | 6.3 | 8.2 | 12.5 | 26.3 | 33.1 | 40.0 |
| 7.5° | 0.0 | 0.6 | 1.4 | 2.4 | 3.6 | 6.4 | 8.3 | 12.1 | 26.9 | 33.4 | 40.3 |
| 5° | 0.0 | 0.6 | 1.4 | 2.4 | 3.6 | 6.4 | 8.4 | 11.6 | 27.4 | 33.7 | 40.5 |
| 2.5° | 0.0 | 0.6 | 1.4 | 2.4 | 3.7 | 6.5 | 8.5 | 11.0 | 27.6 | 33.8 | 40.5 |
| 0° | 0.0 | 0.6 | 1.4 | 2.4 | 3.7 | 6.5 | 8.5 | 10.3 | 27.6 | 33.9 | 40.4 |
| -2.5° | 0.0 | 0.6 | 1.4 | 2.4 | 3.7 | 6.5 | 8.5 | 11.0 | 27.6 | 33.8 | 40.5 |
| -5° | 0.0 | 0.6 | 1.4 | 2.4 | 3.6 | 6.4 | 8.4 | 11.6 | 27.4 | 33.7 | 40.5 |
| -7.5° | 0.0 | 0.6 | 1.4 | 2.4 | 3.6 | 6.4 | 8.3 | 12.1 | 26.9 | 33.4 | 40.3 |
| -10° | 0.0 | 0.6 | 1.4 | 2.4 | 3.5 | 6.3 | 8.2 | 12.5 | 26.3 | 33.1 | 40.0 |
| -12.5° | 0.0 | 0.6 | 1.4 | 2.3 | 3.5 | 6.1 | 8.1 | 12.7 | 25.5 | 32.7 | 39.4 |
| -15° | 0.0 | 0.6 | 1.3 | 2.3 | 3.4 | 6.0 | 8.0 | 12.8 | 24.6 | 32.1 | 38.6 |
| -17.5° | 0.0 | 0.6 | 1.3 | 2.3 | 3.3 | 5.8 | 7.8 | 12.9 | 23.5 | 31.5 | 37.6 |
| -20° | 0.0 | 0.6 | 1.3 | 2.2 | 3.2 | 5.6 | 7.9 | 13.0 | 22.4 | 30.7 | 36.5 |



REPORT NUMBER: P558483 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: GFLD-SA1A-935-U-WR-XX

CANDELA DISTRIBUTION (continued):

| | -90° | -87.5° | -85° | -82.5° | -80° | -77.5° | -75° | -72.5° | -70° | -67.5° | -65° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| -22.5° | 0.0 | 0.6 | 1.3 | 2.2 | 3.1 | 5.3 | 8.4 | 13.1 | 21.3 | 29.9 | 35.3 |
| -25° | 0.0 | 0.5 | 1.2 | 2.1 | 3.0 | 5.3 | 8.8 | 13.1 | 20.3 | 29.0 | 33.8 |
| -27.5° | 0.0 | 0.5 | 1.2 | 2.1 | 3.0 | 5.4 | 9.1 | 13.1 | 19.3 | 27.9 | 32.7 |
| -30° | 0.0 | 0.5 | 1.2 | 2.0 | 2.9 | 5.4 | 9.3 | 13.1 | 18.8 | 26.4 | 31.5 |
| -32.5° | 0.0 | 0.5 | 1.1 | 1.9 | 3.0 | 5.3 | 9.5 | 13.3 | 18.6 | 25.1 | 30.3 |
| -35° | 0.0 | 0.5 | 1.1 | 1.9 | 3.0 | 5.1 | 9.5 | 13.5 | 18.4 | 24.0 | 28.9 |
| -37.5° | 0.0 | 0.5 | 1.1 | 1.8 | 3.0 | 5.0 | 9.3 | 13.5 | 18.3 | 23.1 | 27.6 |
| -40° | 0.0 | 0.5 | 1.0 | 1.7 | 3.0 | 5.0 | 9.0 | 13.5 | 18.1 | 22.8 | 26.3 |
| -42.5° | 0.0 | 0.4 | 1.0 | 1.6 | 2.9 | 5.0 | 8.5 | 13.3 | 17.9 | 21.9 | 24.9 |
| -45° | 0.0 | 0.4 | 0.9 | 1.6 | 2.9 | 4.9 | 8.0 | 12.9 | 17.6 | 20.9 | 23.5 |
| -47.5° | 0.0 | 0.4 | 0.9 | 1.5 | 2.8 | 4.7 | 7.4 | 12.2 | 17.1 | 19.8 | 22.2 |
| -50° | 0.0 | 0.4 | 0.8 | 1.4 | 2.6 | 4.5 | 7.1 | 11.3 | 16.0 | 18.5 | 20.9 |
| -52.5° | 0.0 | 0.4 | 0.8 | 1.3 | 2.4 | 4.2 | 6.7 | 10.3 | 14.5 | 17.2 | 19.4 |
| -55° | 0.0 | 0.3 | 0.7 | 1.3 | 2.2 | 3.9 | 6.3 | 9.3 | 12.9 | 16.0 | 18.1 |
| -57.5° | 0.0 | 0.3 | 0.7 | 1.2 | 2.0 | 3.6 | 5.7 | 8.6 | 11.4 | 14.3 | 16.7 |
| -60° | 0.0 | 0.3 | 0.6 | 1.1 | 1.8 | 3.2 | 5.1 | 7.7 | 9.9 | 12.6 | 15.2 |
| -62.5° | 0.0 | 0.3 | 0.6 | 1.0 | 1.6 | 2.8 | 4.5 | 6.7 | 8.6 | 10.9 | 13.4 |
| -65° | 0.0 | 0.3 | 0.5 | 0.9 | 1.4 | 2.3 | 3.9 | 5.6 | 7.4 | 9.4 | 11.6 |
| -67.5° | 0.0 | 0.2 | 0.5 | 0.7 | 1.2 | 1.9 | 3.2 | 4.7 | 6.0 | 7.7 | 9.7 |
| -70° | 0.0 | 0.2 | 0.4 | 0.6 | 1.0 | 1.6 | 2.4 | 3.7 | 4.9 | 6.1 | 7.7 |
| -72.5° | 0.0 | 0.2 | 0.4 | 0.5 | 0.8 | 1.3 | 2.0 | 2.7 | 3.7 | 4.8 | 5.8 |
| -75° | 0.0 | 0.2 | 0.3 | 0.5 | 0.6 | 1.0 | 1.5 | 2.0 | 2.6 | 3.5 | 4.4 |
| -77.5° | 0.0 | 0.1 | 0.3 | 0.4 | 0.5 | 0.7 | 1.1 | 1.5 | 1.9 | 2.3 | 2.9 |
| -80° | 0.0 | 0.1 | 0.2 | 0.3 | 0.4 | 0.5 | 0.7 | 1.0 | 1.3 | 1.6 | 2.0 |
| -82.5° | 0.0 | 0.1 | 0.2 | 0.2 | 0.3 | 0.4 | 0.5 | 0.5 | 0.6 | 0.9 | 1.1 |
| -85° | 0.0 | 0.1 | 0.1 | 0.2 | 0.2 | 0.3 | 0.3 | 0.4 | 0.4 | 0.5 | 0.5 |
| -87.5° | 0.0 | 0.0 | 0.1 | 0.1 | 0.1 | 0.1 | 0.2 | 0.2 | 0.2 | 0.2 | 0.3 |
| -90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P558483 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: GFLD-SA1A-935-U-WR-XX

CANDELA DISTRIBUTION (continued):

| | -62.5° | -60° | -57.5° | -55° | -52.5° | -50° | -47.5° | -45° | -42.5° | -40° | -37.5° |
|--------|--------|------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.3 | 0.3 | 0.2 | 0.2 | 0.2 | 0.3 | 0.3 | 0.3 | 0.3 | 0.2 | 0.2 |
| 85° | 0.5 | 0.5 | 0.6 | 0.6 | 0.7 | 0.7 | 0.7 | 0.7 | 0.8 | 0.9 | 1.1 |
| 82.5° | 1.3 | 1.4 | 1.4 | 1.4 | 1.4 | 1.4 | 1.4 | 1.4 | 1.7 | 2.2 | 2.7 |
| 80° | 2.1 | 2.2 | 2.6 | 2.9 | 3.1 | 3.1 | 3.0 | 2.6 | 3.1 | 3.9 | 4.9 |
| 77.5° | 3.5 | 4.0 | 4.6 | 5.2 | 5.3 | 5.0 | 4.5 | 3.9 | 4.7 | 6.1 | 7.6 |
| 75° | 5.1 | 5.8 | 6.6 | 7.2 | 7.2 | 6.8 | 6.2 | 6.1 | 7.3 | 9.0 | 10.4 |
| 72.5° | 7.0 | 8.0 | 8.8 | 9.3 | 9.3 | 9.2 | 9.4 | 9.9 | 10.9 | 12.1 | 13.2 |
| 70° | 9.3 | 10.3 | 10.9 | 11.1 | 11.2 | 11.8 | 12.6 | 13.3 | 13.9 | 15.2 | 16.3 |
| 67.5° | 11.5 | 12.3 | 12.8 | 13.2 | 14.1 | 15.2 | 16.0 | 16.8 | 17.6 | 18.9 | 19.9 |
| 65° | 13.5 | 14.3 | 15.0 | 16.1 | 17.5 | 18.5 | 19.5 | 20.5 | 22.0 | 23.4 | 24.3 |
| 62.5° | 15.5 | 16.3 | 17.4 | 18.9 | 20.4 | 21.6 | 23.3 | 25.1 | 27.1 | 28.5 | 30.1 |
| 60° | 17.0 | 18.2 | 19.8 | 21.5 | 23.2 | 25.4 | 27.5 | 29.6 | 31.6 | 33.5 | 35.9 |
| 57.5° | 18.5 | 20.2 | 22.1 | 24.1 | 26.5 | 29.1 | 31.7 | 34.0 | 36.5 | 39.2 | 41.9 |
| 55° | 20.0 | 22.3 | 24.4 | 26.8 | 29.7 | 33.1 | 35.9 | 38.7 | 41.7 | 46.1 | 50.1 |
| 52.5° | 21.8 | 24.3 | 26.7 | 29.6 | 33.2 | 36.8 | 40.0 | 43.9 | 48.8 | 55.5 | 66.4 |
| 50° | 23.4 | 26.1 | 28.9 | 32.7 | 36.6 | 40.4 | 45.0 | 50.4 | 60.3 | 72.8 | 94.7 |
| 47.5° | 25.0 | 27.9 | 31.6 | 35.7 | 39.9 | 44.9 | 50.8 | 62.6 | 76.2 | 107.2 | 138.2 |
| 45° | 26.6 | 30.1 | 34.2 | 38.8 | 43.8 | 50.1 | 62.4 | 76.9 | 113.8 | 149.5 | 186.7 |
| 42.5° | 28.2 | 32.3 | 37.0 | 41.9 | 48.4 | 59.8 | 75.6 | 114.0 | 153.9 | 194.9 | 230.7 |
| 40° | 30.0 | 34.3 | 39.7 | 45.9 | 54.6 | 71.9 | 107.5 | 150.6 | 195.6 | 234.4 | 269.2 |
| 37.5° | 31.7 | 36.8 | 42.6 | 49.9 | 65.5 | 94.3 | 140.1 | 188.0 | 231.6 | 269.5 | 306.6 |
| 35° | 33.3 | 39.2 | 46.1 | 57.0 | 76.2 | 123.6 | 173.3 | 222.0 | 263.7 | 304.1 | 344.7 |
| 32.5° | 35.1 | 41.5 | 49.5 | 66.5 | 100.7 | 151.9 | 204.8 | 251.2 | 294.8 | 337.9 | 384.3 |
| 30° | 37.1 | 44.3 | 54.2 | 75.6 | 124.9 | 179.4 | 231.8 | 279.2 | 324.4 | 372.3 | 422.0 |
| 27.5° | 39.0 | 47.1 | 62.0 | 93.1 | 147.7 | 205.0 | 256.4 | 305.1 | 353.7 | 404.7 | 458.1 |
| 25° | 40.7 | 49.7 | 69.4 | 112.3 | 169.7 | 227.0 | 279.0 | 328.6 | 381.0 | 436.4 | 492.7 |
| 22.5° | 42.5 | 52.3 | 76.0 | 129.8 | 189.9 | 246.5 | 298.9 | 351.5 | 407.0 | 465.8 | 524.5 |
| 20° | 44.5 | 57.7 | 86.8 | 145.9 | 208.2 | 264.2 | 316.8 | 372.8 | 431.4 | 492.2 | 554.2 |
| 17.5° | 46.4 | 62.6 | 99.8 | 161.3 | 223.5 | 279.6 | 333.0 | 392.2 | 452.5 | 516.2 | 581.4 |
| 15° | 48.0 | 66.8 | 111.2 | 174.8 | 236.6 | 292.7 | 348.7 | 409.3 | 471.3 | 537.6 | 605.4 |
| 12.5° | 49.5 | 70.3 | 121.0 | 186.5 | 247.6 | 303.9 | 361.9 | 423.8 | 488.1 | 556.4 | 627.1 |
| 10° | 50.7 | 73.2 | 129.2 | 196.3 | 256.6 | 313.1 | 372.5 | 435.8 | 501.5 | 571.5 | 644.5 |
| 7.5° | 51.5 | 75.6 | 135.7 | 204.2 | 263.5 | 320.3 | 380.5 | 445.3 | 511.3 | 583.3 | 657.7 |
| 5° | 51.9 | 77.5 | 140.4 | 210.0 | 268.5 | 325.8 | 386.3 | 452.1 | 517.5 | 591.5 | 666.5 |
| 2.5° | 52.1 | 78.8 | 143.2 | 213.7 | 271.7 | 329.6 | 391.1 | 458.1 | 524.1 | 597.4 | 673.4 |
| 0° | 52.1 | 79.5 | 144.3 | 215.3 | 272.9 | 331.3 | 393.4 | 461.2 | 528.3 | 599.9 | 678.1 |
| -2.5° | 52.1 | 78.8 | 143.2 | 213.7 | 271.7 | 329.6 | 391.1 | 458.1 | 524.1 | 597.4 | 673.4 |
| -5° | 51.9 | 77.5 | 140.4 | 210.0 | 268.5 | 325.8 | 386.3 | 452.1 | 517.5 | 591.5 | 666.5 |
| -7.5° | 51.5 | 75.6 | 135.7 | 204.2 | 263.5 | 320.3 | 380.5 | 445.3 | 511.3 | 583.3 | 657.7 |
| -10° | 50.7 | 73.2 | 129.2 | 196.3 | 256.6 | 313.1 | 372.5 | 435.8 | 501.5 | 571.5 | 644.5 |
| -12.5° | 49.5 | 70.3 | 121.0 | 186.5 | 247.6 | 303.9 | 361.9 | 423.8 | 488.1 | 556.4 | 627.1 |
| -15° | 48.0 | 66.8 | 111.2 | 174.8 | 236.6 | 292.7 | 348.7 | 409.3 | 471.3 | 537.6 | 605.4 |
| -17.5° | 46.4 | 62.6 | 99.8 | 161.3 | 223.5 | 279.6 | 333.0 | 392.2 | 452.5 | 516.2 | 581.4 |
| -20° | 44.5 | 57.7 | 86.8 | 145.9 | 208.2 | 264.2 | 316.8 | 372.8 | 431.4 | 492.2 | 554.2 |



REPORT NUMBER: P558483 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: GFLD-SA1A-935-U-WR-XX

CANDELA DISTRIBUTION (continued):

| | -62.5° | -60° | -57.5° | -55° | -52.5° | -50° | -47.5° | -45° | -42.5° | -40° | -37.5° |
|--------|--------|------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| -22.5° | 42.5 | 52.3 | 76.0 | 129.8 | 189.9 | 246.5 | 298.9 | 351.5 | 407.0 | 465.8 | 524.5 |
| -25° | 40.7 | 49.7 | 69.4 | 112.3 | 169.7 | 227.0 | 279.0 | 328.6 | 381.0 | 436.4 | 492.7 |
| -27.5° | 39.0 | 47.1 | 62.0 | 93.1 | 147.7 | 205.0 | 256.4 | 305.1 | 353.7 | 404.7 | 458.1 |
| -30° | 37.1 | 44.3 | 54.2 | 75.6 | 124.9 | 179.4 | 231.8 | 279.2 | 324.4 | 372.3 | 422.0 |
| -32.5° | 35.1 | 41.5 | 49.5 | 66.5 | 100.7 | 151.9 | 204.8 | 251.2 | 294.8 | 337.9 | 384.3 |
| -35° | 33.3 | 39.2 | 46.1 | 57.0 | 76.2 | 123.6 | 173.3 | 222.0 | 263.7 | 304.1 | 344.7 |
| -37.5° | 31.7 | 36.8 | 42.6 | 49.9 | 65.5 | 94.3 | 140.1 | 188.0 | 231.6 | 269.5 | 306.6 |
| -40° | 30.0 | 34.3 | 39.7 | 45.9 | 54.6 | 71.9 | 107.5 | 150.6 | 195.6 | 234.4 | 269.2 |
| -42.5° | 28.2 | 32.3 | 37.0 | 41.9 | 48.4 | 59.8 | 75.6 | 114.0 | 153.9 | 194.9 | 230.7 |
| -45° | 26.6 | 30.1 | 34.2 | 38.8 | 43.8 | 50.1 | 62.4 | 76.9 | 113.8 | 149.5 | 186.7 |
| -47.5° | 25.0 | 27.9 | 31.6 | 35.7 | 39.9 | 44.9 | 50.8 | 62.6 | 76.2 | 107.2 | 138.2 |
| -50° | 23.4 | 26.1 | 28.9 | 32.7 | 36.6 | 40.4 | 45.0 | 50.4 | 60.3 | 72.8 | 94.7 |
| -52.5° | 21.8 | 24.3 | 26.7 | 29.6 | 33.2 | 36.8 | 40.0 | 43.9 | 48.8 | 55.5 | 66.4 |
| -55° | 20.0 | 22.3 | 24.4 | 26.8 | 29.7 | 33.1 | 35.9 | 38.7 | 41.7 | 46.1 | 50.1 |
| -57.5° | 18.5 | 20.2 | 22.1 | 24.1 | 26.5 | 29.1 | 31.7 | 34.0 | 36.5 | 39.2 | 41.9 |
| -60° | 17.0 | 18.2 | 19.8 | 21.5 | 23.2 | 25.4 | 27.5 | 29.6 | 31.6 | 33.5 | 35.9 |
| -62.5° | 15.5 | 16.3 | 17.4 | 18.9 | 20.4 | 21.6 | 23.3 | 25.1 | 27.1 | 28.5 | 30.1 |
| -65° | 13.5 | 14.3 | 15.0 | 16.1 | 17.5 | 18.5 | 19.5 | 20.5 | 22.0 | 23.4 | 24.3 |
| -67.5° | 11.5 | 12.3 | 12.8 | 13.2 | 14.1 | 15.2 | 16.0 | 16.8 | 17.6 | 18.9 | 19.9 |
| -70° | 9.3 | 10.3 | 10.9 | 11.1 | 11.2 | 11.8 | 12.6 | 13.3 | 13.9 | 15.2 | 16.3 |
| -72.5° | 7.0 | 8.0 | 8.8 | 9.3 | 9.3 | 9.2 | 9.4 | 9.9 | 10.9 | 12.1 | 13.2 |
| -75° | 5.1 | 5.8 | 6.6 | 7.2 | 7.2 | 6.8 | 6.2 | 6.1 | 7.3 | 9.0 | 10.4 |
| -77.5° | 3.5 | 4.0 | 4.6 | 5.2 | 5.3 | 5.0 | 4.5 | 3.9 | 4.7 | 6.1 | 7.6 |
| -80° | 2.1 | 2.2 | 2.6 | 2.9 | 3.1 | 3.1 | 3.0 | 2.6 | 3.1 | 3.9 | 4.9 |
| -82.5° | 1.3 | 1.4 | 1.4 | 1.4 | 1.4 | 1.4 | 1.4 | 1.4 | 1.7 | 2.2 | 2.7 |
| -85° | 0.5 | 0.5 | 0.6 | 0.6 | 0.7 | 0.7 | 0.7 | 0.7 | 0.8 | 0.9 | 1.1 |
| -87.5° | 0.3 | 0.3 | 0.2 | 0.2 | 0.2 | 0.3 | 0.3 | 0.3 | 0.3 | 0.2 | 0.2 |
| -90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P558483 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: GFLD-SA1A-935-U-WR-XX

CANDELA DISTRIBUTION (continued):

| | -35° | -32.5° | -30° | -27.5° | -25° | -22.5° | -20° | -17.5° | -15° | -12.5° | -10° |
|--------|-------|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 |
| 85° | 1.2 | 1.2 | 1.2 | 1.1 | 1.0 | 1.0 | 1.1 | 1.1 | 1.1 | 1.1 | 1.0 |
| 82.5° | 3.2 | 3.4 | 3.6 | 3.9 | 4.1 | 4.1 | 4.0 | 3.8 | 3.6 | 3.2 | 2.8 |
| 80° | 6.0 | 6.5 | 6.9 | 7.2 | 7.4 | 7.2 | 6.9 | 6.5 | 6.0 | 5.3 | 4.6 |
| 77.5° | 9.2 | 9.8 | 10.1 | 10.5 | 10.8 | 10.9 | 11.0 | 11.0 | 11.1 | 9.8 | 8.2 |
| 75° | 11.5 | 12.3 | 12.9 | 13.4 | 13.9 | 14.1 | 14.3 | 14.4 | 14.5 | 12.9 | 10.7 |
| 72.5° | 14.1 | 14.8 | 15.4 | 16.0 | 16.5 | 16.9 | 17.3 | 17.5 | 17.7 | 16.4 | 14.5 |
| 70° | 17.2 | 17.9 | 18.6 | 19.2 | 19.8 | 20.3 | 20.8 | 21.3 | 21.7 | 21.7 | 21.8 |
| 67.5° | 20.7 | 21.1 | 21.9 | 22.7 | 23.6 | 24.2 | 25.0 | 25.7 | 26.3 | 26.9 | 27.3 |
| 65° | 25.0 | 26.5 | 28.1 | 28.9 | 28.9 | 29.9 | 31.4 | 32.2 | 32.5 | 32.7 | 33.2 |
| 62.5° | 32.3 | 34.2 | 35.3 | 36.6 | 38.5 | 40.5 | 41.3 | 42.4 | 43.8 | 45.3 | 46.7 |
| 60° | 38.0 | 39.7 | 42.2 | 44.7 | 47.0 | 49.1 | 54.0 | 58.5 | 62.3 | 65.6 | 68.7 |
| 57.5° | 45.1 | 47.9 | 51.7 | 58.6 | 65.0 | 70.6 | 80.4 | 92.4 | 103.0 | 112.3 | 120.5 |
| 55° | 56.4 | 64.6 | 71.9 | 88.2 | 105.6 | 120.7 | 134.9 | 150.0 | 162.3 | 171.9 | 180.8 |
| 52.5° | 75.8 | 98.1 | 120.6 | 141.8 | 162.7 | 181.7 | 198.7 | 212.1 | 222.5 | 230.4 | 237.8 |
| 50° | 121.4 | 148.2 | 175.7 | 201.0 | 221.4 | 240.1 | 257.8 | 271.1 | 282.3 | 291.8 | 300.3 |
| 47.5° | 171.1 | 202.5 | 228.4 | 251.7 | 273.8 | 294.5 | 313.9 | 330.1 | 343.8 | 356.5 | 367.0 |
| 45° | 220.5 | 248.6 | 275.2 | 300.2 | 324.2 | 347.5 | 368.3 | 386.7 | 404.8 | 419.9 | 431.7 |
| 42.5° | 262.4 | 292.1 | 320.4 | 349.0 | 375.8 | 401.9 | 427.1 | 449.4 | 468.7 | 485.1 | 498.3 |
| 40° | 302.5 | 334.5 | 368.1 | 399.9 | 431.8 | 461.5 | 489.4 | 515.0 | 536.9 | 556.3 | 572.7 |
| 37.5° | 343.3 | 380.7 | 417.6 | 453.8 | 489.0 | 521.4 | 553.4 | 582.9 | 608.6 | 631.2 | 650.3 |
| 35° | 386.4 | 427.6 | 467.8 | 508.6 | 546.9 | 584.4 | 619.8 | 652.3 | 680.7 | 707.5 | 730.4 |
| 32.5° | 429.6 | 474.2 | 519.4 | 563.6 | 606.1 | 648.1 | 686.9 | 723.5 | 757.1 | 786.7 | 811.2 |
| 30° | 471.6 | 520.8 | 569.2 | 617.3 | 665.7 | 711.5 | 754.5 | 794.7 | 831.2 | 863.4 | 891.3 |
| 27.5° | 511.9 | 564.8 | 616.7 | 671.7 | 724.4 | 774.2 | 820.9 | 864.1 | 904.9 | 941.5 | 973.1 |
| 25° | 549.3 | 605.4 | 665.9 | 723.6 | 780.0 | 835.2 | 886.4 | 933.3 | 979.9 | 1020.2 | 1054.5 |
| 22.5° | 584.5 | 647.2 | 710.9 | 771.4 | 833.7 | 894.3 | 951.6 | 1006.0 | 1055.7 | 1098.0 | 1134.6 |
| 20° | 618.0 | 685.5 | 751.1 | 818.2 | 885.5 | 950.9 | 1014.1 | 1072.2 | 1124.7 | 1170.8 | 1212.1 |
| 17.5° | 649.7 | 719.5 | 789.3 | 860.8 | 933.6 | 1002.4 | 1069.3 | 1132.5 | 1189.8 | 1240.9 | 1287.5 |
| 15° | 677.1 | 749.2 | 823.9 | 900.0 | 976.1 | 1049.2 | 1120.2 | 1189.0 | 1253.6 | 1309.2 | 1356.1 |
| 12.5° | 700.4 | 775.5 | 854.5 | 934.3 | 1014.6 | 1091.2 | 1166.5 | 1240.2 | 1308.8 | 1368.5 | 1416.7 |
| 10° | 719.7 | 798.4 | 880.9 | 964.1 | 1046.3 | 1126.0 | 1204.2 | 1280.5 | 1354.2 | 1416.1 | 1465.7 |
| 7.5° | 735.8 | 817.5 | 902.0 | 987.6 | 1070.6 | 1153.4 | 1234.9 | 1312.0 | 1384.6 | 1449.9 | 1500.8 |
| 5° | 747.8 | 830.9 | 917.1 | 1004.9 | 1089.2 | 1174.9 | 1258.9 | 1337.8 | 1409.7 | 1468.8 | 1510.3 |
| 2.5° | 756.8 | 839.2 | 926.9 | 1015.3 | 1100.7 | 1189.5 | 1275.3 | 1354.3 | 1427.8 | 1483.8 | 1519.8 |
| 0° | 762.9 | 843.8 | 935.9 | 1022.6 | 1109.4 | 1200.5 | 1285.3 | 1365.0 | 1438.9 | 1493.7 | 1530.8 |
| -2.5° | 756.8 | 839.2 | 926.9 | 1015.3 | 1100.7 | 1189.5 | 1275.3 | 1354.3 | 1427.8 | 1483.8 | 1519.8 |
| -5° | 747.8 | 830.9 | 917.1 | 1004.9 | 1089.2 | 1174.9 | 1258.9 | 1337.8 | 1409.7 | 1468.8 | 1510.3 |
| -7.5° | 735.8 | 817.5 | 902.0 | 987.6 | 1070.6 | 1153.4 | 1234.9 | 1312.0 | 1384.6 | 1449.9 | 1500.8 |
| -10° | 719.7 | 798.4 | 880.9 | 964.1 | 1046.3 | 1126.0 | 1204.2 | 1280.5 | 1354.2 | 1416.1 | 1465.7 |
| -12.5° | 700.4 | 775.5 | 854.5 | 934.3 | 1014.6 | 1091.2 | 1166.5 | 1240.2 | 1308.8 | 1368.5 | 1416.7 |
| -15° | 677.1 | 749.2 | 823.9 | 900.0 | 976.1 | 1049.2 | 1120.2 | 1189.0 | 1253.6 | 1309.2 | 1356.1 |
| -17.5° | 649.7 | 719.5 | 789.3 | 860.8 | 933.6 | 1002.4 | 1069.3 | 1132.5 | 1189.8 | 1240.9 | 1287.5 |
| -20° | 618.0 | 685.5 | 751.1 | 818.2 | 885.5 | 950.9 | 1014.1 | 1072.2 | 1124.7 | 1170.8 | 1212.1 |



REPORT NUMBER: P558483 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: GFLD-SA1A-935-U-WR-XX

CANDELA DISTRIBUTION (continued):

| | -35° | -32.5° | -30° | -27.5° | -25° | -22.5° | -20° | -17.5° | -15° | -12.5° | -10° |
|--------|-------|--------|-------|--------|-------|--------|-------|--------|--------|--------|--------|
| -22.5° | 584.5 | 647.2 | 710.9 | 771.4 | 833.7 | 894.3 | 951.6 | 1006.0 | 1055.7 | 1098.0 | 1134.6 |
| -25° | 549.3 | 605.4 | 665.9 | 723.6 | 780.0 | 835.2 | 886.4 | 933.3 | 979.9 | 1020.2 | 1054.5 |
| -27.5° | 511.9 | 564.8 | 616.7 | 671.7 | 724.4 | 774.2 | 820.9 | 864.1 | 904.9 | 941.5 | 973.1 |
| -30° | 471.6 | 520.8 | 569.2 | 617.3 | 665.7 | 711.5 | 754.5 | 794.7 | 831.2 | 863.4 | 891.3 |
| -32.5° | 429.6 | 474.2 | 519.4 | 563.6 | 606.1 | 648.1 | 686.9 | 723.5 | 757.1 | 786.7 | 811.2 |
| -35° | 386.4 | 427.6 | 467.8 | 508.6 | 546.9 | 584.4 | 619.8 | 652.3 | 680.7 | 707.5 | 730.4 |
| -37.5° | 343.3 | 380.7 | 417.6 | 453.8 | 489.0 | 521.4 | 553.4 | 582.9 | 608.6 | 631.2 | 650.3 |
| -40° | 302.5 | 334.5 | 368.1 | 399.9 | 431.8 | 461.5 | 489.4 | 515.0 | 536.9 | 556.3 | 572.7 |
| -42.5° | 262.4 | 292.1 | 320.4 | 349.0 | 375.8 | 401.9 | 427.1 | 449.4 | 468.7 | 485.1 | 498.3 |
| -45° | 220.5 | 248.6 | 275.2 | 300.2 | 324.2 | 347.5 | 368.3 | 386.7 | 404.8 | 419.9 | 431.7 |
| -47.5° | 171.1 | 202.5 | 228.4 | 251.7 | 273.8 | 294.5 | 313.9 | 330.1 | 343.8 | 356.5 | 367.0 |
| -50° | 121.4 | 148.2 | 175.7 | 201.0 | 221.4 | 240.1 | 257.8 | 271.1 | 282.3 | 291.8 | 300.3 |
| -52.5° | 75.8 | 98.1 | 120.6 | 141.8 | 162.7 | 181.7 | 198.7 | 212.1 | 222.5 | 230.4 | 237.8 |
| -55° | 56.4 | 64.6 | 71.9 | 88.2 | 105.6 | 120.7 | 134.9 | 150.0 | 162.3 | 171.9 | 180.8 |
| -57.5° | 45.1 | 47.9 | 51.7 | 58.6 | 65.0 | 70.6 | 80.4 | 92.4 | 103.0 | 112.3 | 120.5 |
| -60° | 38.0 | 39.7 | 42.2 | 44.7 | 47.0 | 49.1 | 54.0 | 58.5 | 62.3 | 65.6 | 68.7 |
| -62.5° | 32.3 | 34.2 | 35.3 | 36.6 | 38.5 | 40.5 | 41.3 | 42.4 | 43.8 | 45.3 | 46.7 |
| -65° | 25.0 | 26.5 | 28.1 | 28.9 | 28.9 | 29.9 | 31.4 | 32.2 | 32.5 | 32.7 | 33.2 |
| -67.5° | 20.7 | 21.1 | 21.9 | 22.7 | 23.6 | 24.2 | 25.0 | 25.7 | 26.3 | 26.9 | 27.3 |
| -70° | 17.2 | 17.9 | 18.6 | 19.2 | 19.8 | 20.3 | 20.8 | 21.3 | 21.7 | 21.7 | 21.8 |
| -72.5° | 14.1 | 14.8 | 15.4 | 16.0 | 16.5 | 16.9 | 17.3 | 17.5 | 17.7 | 16.4 | 14.5 |
| -75° | 11.5 | 12.3 | 12.9 | 13.4 | 13.9 | 14.1 | 14.3 | 14.4 | 14.5 | 12.9 | 10.7 |
| -77.5° | 9.2 | 9.8 | 10.1 | 10.5 | 10.8 | 10.9 | 11.0 | 11.0 | 11.1 | 9.8 | 8.2 |
| -80° | 6.0 | 6.5 | 6.9 | 7.2 | 7.4 | 7.2 | 6.9 | 6.5 | 6.0 | 5.3 | 4.6 |
| -82.5° | 3.2 | 3.4 | 3.6 | 3.9 | 4.1 | 4.1 | 4.0 | 3.8 | 3.6 | 3.2 | 2.8 |
| -85° | 1.2 | 1.2 | 1.2 | 1.1 | 1.0 | 1.0 | 1.1 | 1.1 | 1.1 | 1.1 | 1.0 |
| -87.5° | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 |
| -90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P558483 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: GFLD-SA1A-935-U-WR-XX

CANDELA DISTRIBUTION (continued):

| | -7.5° | -5° | -2.5° | 0° | 2.5° | 5° | 7.5° | 10° | 12.5° | 15° | 17.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 |
| 85° | 0.9 | 0.8 | 0.8 | 0.8 | 0.8 | 0.8 | 0.9 | 1.0 | 1.1 | 1.1 | 1.1 |
| 82.5° | 2.3 | 1.8 | 1.9 | 2.0 | 1.9 | 1.8 | 2.3 | 2.8 | 3.2 | 3.6 | 3.8 |
| 80° | 3.8 | 3.0 | 3.1 | 3.2 | 3.1 | 3.0 | 3.8 | 4.6 | 5.3 | 6.0 | 6.5 |
| 77.5° | 6.5 | 4.8 | 4.6 | 4.5 | 4.6 | 4.8 | 6.5 | 8.2 | 9.8 | 11.1 | 11.0 |
| 75° | 8.5 | 6.2 | 6.1 | 6.1 | 6.1 | 6.2 | 8.5 | 10.7 | 12.9 | 14.5 | 14.4 |
| 72.5° | 12.6 | 10.7 | 9.3 | 7.9 | 9.3 | 10.7 | 12.6 | 14.5 | 16.4 | 17.7 | 17.5 |
| 70° | 22.1 | 22.3 | 22.2 | 21.9 | 22.2 | 22.3 | 22.1 | 21.8 | 21.7 | 21.7 | 21.3 |
| 67.5° | 27.7 | 28.0 | 28.1 | 28.0 | 28.1 | 28.0 | 27.7 | 27.3 | 26.9 | 26.3 | 25.7 |
| 65° | 33.5 | 33.7 | 33.8 | 33.9 | 33.8 | 33.7 | 33.5 | 33.2 | 32.7 | 32.5 | 32.2 |
| 62.5° | 47.7 | 48.4 | 49.2 | 49.7 | 49.2 | 48.4 | 47.7 | 46.7 | 45.3 | 43.8 | 42.4 |
| 60° | 71.5 | 73.8 | 74.8 | 74.9 | 74.8 | 73.8 | 71.5 | 68.7 | 65.6 | 62.3 | 58.5 |
| 57.5° | 127.0 | 131.9 | 136.3 | 139.6 | 136.3 | 131.9 | 127.0 | 120.5 | 112.3 | 103.0 | 92.4 |
| 55° | 187.9 | 193.1 | 196.0 | 196.8 | 196.0 | 193.1 | 187.9 | 180.8 | 171.9 | 162.3 | 150.0 |
| 52.5° | 243.4 | 246.9 | 250.2 | 253.0 | 250.2 | 246.9 | 243.4 | 237.8 | 230.4 | 222.5 | 212.1 |
| 50° | 306.7 | 310.6 | 313.8 | 316.3 | 313.8 | 310.6 | 306.7 | 300.3 | 291.8 | 282.3 | 271.1 |
| 47.5° | 374.4 | 379.1 | 382.6 | 384.9 | 382.6 | 379.1 | 374.4 | 367.0 | 356.5 | 343.8 | 330.1 |
| 45° | 441.8 | 449.9 | 454.8 | 455.7 | 454.8 | 449.9 | 441.8 | 431.7 | 419.9 | 404.8 | 386.7 |
| 42.5° | 509.7 | 517.4 | 522.7 | 526.5 | 522.7 | 517.4 | 509.7 | 498.3 | 485.1 | 468.7 | 449.4 |
| 40° | 586.4 | 596.1 | 600.6 | 597.7 | 600.6 | 596.1 | 586.4 | 572.7 | 556.3 | 536.9 | 515.0 |
| 37.5° | 664.9 | 674.9 | 680.1 | 679.9 | 680.1 | 674.9 | 664.9 | 650.3 | 631.2 | 608.6 | 582.9 |
| 35° | 748.3 | 760.7 | 767.4 | 765.7 | 767.4 | 760.7 | 748.3 | 730.4 | 707.5 | 680.7 | 652.3 |
| 32.5° | 830.8 | 845.8 | 855.5 | 857.0 | 855.5 | 845.8 | 830.8 | 811.2 | 786.7 | 757.1 | 723.5 |
| 30° | 913.6 | 929.8 | 939.4 | 940.4 | 939.4 | 929.8 | 913.6 | 891.3 | 863.4 | 831.2 | 794.7 |
| 27.5° | 999.6 | 1017.8 | 1027.9 | 1030.3 | 1027.9 | 1017.8 | 999.6 | 973.1 | 941.5 | 904.9 | 864.1 |
| 25° | 1083.8 | 1103.9 | 1115.5 | 1120.0 | 1115.5 | 1103.9 | 1083.8 | 1054.5 | 1020.2 | 979.9 | 933.3 |
| 22.5° | 1165.0 | 1187.0 | 1202.1 | 1206.0 | 1202.1 | 1187.0 | 1165.0 | 1134.6 | 1098.0 | 1055.7 | 1006.0 |
| 20° | 1246.4 | 1272.4 | 1291.7 | 1293.6 | 1291.7 | 1272.4 | 1246.4 | 1212.1 | 1170.8 | 1124.7 | 1072.2 |
| 17.5° | 1324.8 | 1353.0 | 1373.6 | 1378.6 | 1373.6 | 1353.0 | 1324.8 | 1287.5 | 1240.9 | 1189.8 | 1132.5 |
| 15° | 1394.9 | 1424.5 | 1444.5 | 1448.8 | 1444.5 | 1424.5 | 1394.9 | 1356.1 | 1309.2 | 1253.6 | 1189.0 |
| 12.5° | 1455.5 | 1482.7 | 1501.4 | 1508.5 | 1501.4 | 1482.7 | 1455.5 | 1416.7 | 1368.5 | 1308.8 | 1240.2 |
| 10° | 1504.2 | 1525.3 | 1541.9 | 1549.5 | 1541.9 | 1525.3 | 1504.2 | 1465.7 | 1416.1 | 1354.2 | 1280.5 |
| 7.5° | 1531.4 | 1548.8 | 1560.3 | 1564.5 | 1560.3 | 1548.8 | 1531.4 | 1500.8 | 1449.9 | 1384.6 | 1312.0 |
| 5° | 1542.3 | 1558.9 | 1565.1 | 1568.7 | 1565.1 | 1558.9 | 1542.3 | 1510.3 | 1468.8 | 1409.7 | 1337.8 |
| 2.5° | 1543.7 | 1557.0 | 1569.8 | 1578.3 | 1569.8 | 1557.0 | 1543.7 | 1519.8 | 1483.8 | 1427.8 | 1354.3 |
| 0° | 1552.3 | 1565.3 | 1572.4 | 1576.5 | 1572.4 | 1565.3 | 1552.3 | 1530.8 | 1493.7 | 1438.9 | 1365.0 |
| -2.5° | 1543.7 | 1557.0 | 1569.8 | 1578.3 | 1569.8 | 1557.0 | 1543.7 | 1519.8 | 1483.8 | 1427.8 | 1354.3 |
| -5° | 1542.3 | 1558.9 | 1565.1 | 1568.7 | 1565.1 | 1558.9 | 1542.3 | 1510.3 | 1468.8 | 1409.7 | 1337.8 |
| -7.5° | 1531.4 | 1548.8 | 1560.3 | 1564.5 | 1560.3 | 1548.8 | 1531.4 | 1500.8 | 1449.9 | 1384.6 | 1312.0 |
| -10° | 1504.2 | 1525.3 | 1541.9 | 1549.5 | 1541.9 | 1525.3 | 1504.2 | 1465.7 | 1416.1 | 1354.2 | 1280.5 |
| -12.5° | 1455.5 | 1482.7 | 1501.4 | 1508.5 | 1501.4 | 1482.7 | 1455.5 | 1416.7 | 1368.5 | 1308.8 | 1240.2 |
| -15° | 1394.9 | 1424.5 | 1444.5 | 1448.8 | 1444.5 | 1424.5 | 1394.9 | 1356.1 | 1309.2 | 1253.6 | 1189.0 |
| -17.5° | 1324.8 | 1353.0 | 1373.6 | 1378.6 | 1373.6 | 1353.0 | 1324.8 | 1287.5 | 1240.9 | 1189.8 | 1132.5 |
| -20° | 1246.4 | 1272.4 | 1291.7 | 1293.6 | 1291.7 | 1272.4 | 1246.4 | 1212.1 | 1170.8 | 1124.7 | 1072.2 |



REPORT NUMBER: P558483 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: GFLD-SA1A-935-U-WR-XX

CANDELA DISTRIBUTION (continued):

| | -7.5° | -5° | -2.5° | 0° | 2.5° | 5° | 7.5° | 10° | 12.5° | 15° | 17.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| -22.5° | 1165.0 | 1187.0 | 1202.1 | 1206.0 | 1202.1 | 1187.0 | 1165.0 | 1134.6 | 1098.0 | 1055.7 | 1006.0 |
| -25° | 1083.8 | 1103.9 | 1115.5 | 1120.0 | 1115.5 | 1103.9 | 1083.8 | 1054.5 | 1020.2 | 979.9 | 933.3 |
| -27.5° | 999.6 | 1017.8 | 1027.9 | 1030.3 | 1027.9 | 1017.8 | 999.6 | 973.1 | 941.5 | 904.9 | 864.1 |
| -30° | 913.6 | 929.8 | 939.4 | 940.4 | 939.4 | 929.8 | 913.6 | 891.3 | 863.4 | 831.2 | 794.7 |
| -32.5° | 830.8 | 845.8 | 855.5 | 857.0 | 855.5 | 845.8 | 830.8 | 811.2 | 786.7 | 757.1 | 723.5 |
| -35° | 748.3 | 760.7 | 767.4 | 765.7 | 767.4 | 760.7 | 748.3 | 730.4 | 707.5 | 680.7 | 652.3 |
| -37.5° | 664.9 | 674.9 | 680.1 | 679.9 | 680.1 | 674.9 | 664.9 | 650.3 | 631.2 | 608.6 | 582.9 |
| -40° | 586.4 | 596.1 | 600.6 | 597.7 | 600.6 | 596.1 | 586.4 | 572.7 | 556.3 | 536.9 | 515.0 |
| -42.5° | 509.7 | 517.4 | 522.7 | 526.5 | 522.7 | 517.4 | 509.7 | 498.3 | 485.1 | 468.7 | 449.4 |
| -45° | 441.8 | 449.9 | 454.8 | 455.7 | 454.8 | 449.9 | 441.8 | 431.7 | 419.9 | 404.8 | 386.7 |
| -47.5° | 374.4 | 379.1 | 382.6 | 384.9 | 382.6 | 379.1 | 374.4 | 367.0 | 356.5 | 343.8 | 330.1 |
| -50° | 306.7 | 310.6 | 313.8 | 316.3 | 313.8 | 310.6 | 306.7 | 300.3 | 291.8 | 282.3 | 271.1 |
| -52.5° | 243.4 | 246.9 | 250.2 | 253.0 | 250.2 | 246.9 | 243.4 | 237.8 | 230.4 | 222.5 | 212.1 |
| -55° | 187.9 | 193.1 | 196.0 | 196.8 | 196.0 | 193.1 | 187.9 | 180.8 | 171.9 | 162.3 | 150.0 |
| -57.5° | 127.0 | 131.9 | 136.3 | 139.6 | 136.3 | 131.9 | 127.0 | 120.5 | 112.3 | 103.0 | 92.4 |
| -60° | 71.5 | 73.8 | 74.8 | 74.9 | 74.8 | 73.8 | 71.5 | 68.7 | 65.6 | 62.3 | 58.5 |
| -62.5° | 47.7 | 48.4 | 49.2 | 49.7 | 49.2 | 48.4 | 47.7 | 46.7 | 45.3 | 43.8 | 42.4 |
| -65° | 33.5 | 33.7 | 33.8 | 33.9 | 33.8 | 33.7 | 33.5 | 33.2 | 32.7 | 32.5 | 32.2 |
| -67.5° | 27.7 | 28.0 | 28.1 | 28.0 | 28.1 | 28.0 | 27.7 | 27.3 | 26.9 | 26.3 | 25.7 |
| -70° | 22.1 | 22.3 | 22.2 | 21.9 | 22.2 | 22.3 | 22.1 | 21.8 | 21.7 | 21.7 | 21.3 |
| -72.5° | 12.6 | 10.7 | 9.3 | 7.9 | 9.3 | 10.7 | 12.6 | 14.5 | 16.4 | 17.7 | 17.5 |
| -75° | 8.5 | 6.2 | 6.1 | 6.1 | 6.1 | 6.2 | 8.5 | 10.7 | 12.9 | 14.5 | 14.4 |
| -77.5° | 6.5 | 4.8 | 4.6 | 4.5 | 4.6 | 4.8 | 6.5 | 8.2 | 9.8 | 11.1 | 11.0 |
| -80° | 3.8 | 3.0 | 3.1 | 3.2 | 3.1 | 3.0 | 3.8 | 4.6 | 5.3 | 6.0 | 6.5 |
| -82.5° | 2.3 | 1.8 | 1.9 | 2.0 | 1.9 | 1.8 | 2.3 | 2.8 | 3.2 | 3.6 | 3.8 |
| -85° | 0.9 | 0.8 | 0.8 | 0.8 | 0.8 | 0.8 | 0.9 | 1.0 | 1.1 | 1.1 | 1.1 |
| -87.5° | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 |
| -90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P558483 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: GFLD-SA1A-935-U-WR-XX

CANDELA DISTRIBUTION (continued):

| | 20° | 22.5° | 25° | 27.5° | 30° | 32.5° | 35° | 37.5° | 40° | 42.5° | 45° |
|--------|--------|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.3 | 0.3 |
| 85° | 1.1 | 1.0 | 1.0 | 1.1 | 1.2 | 1.2 | 1.2 | 1.1 | 0.9 | 0.8 | 0.7 |
| 82.5° | 4.0 | 4.1 | 4.1 | 3.9 | 3.6 | 3.4 | 3.2 | 2.7 | 2.2 | 1.7 | 1.4 |
| 80° | 6.9 | 7.2 | 7.4 | 7.2 | 6.9 | 6.5 | 6.0 | 4.9 | 3.9 | 3.1 | 2.6 |
| 77.5° | 11.0 | 10.9 | 10.8 | 10.5 | 10.1 | 9.8 | 9.2 | 7.6 | 6.1 | 4.7 | 3.9 |
| 75° | 14.3 | 14.1 | 13.9 | 13.4 | 12.9 | 12.3 | 11.5 | 10.4 | 9.0 | 7.3 | 6.1 |
| 72.5° | 17.3 | 16.9 | 16.5 | 16.0 | 15.4 | 14.8 | 14.1 | 13.2 | 12.1 | 10.9 | 9.9 |
| 70° | 20.8 | 20.3 | 19.8 | 19.2 | 18.6 | 17.9 | 17.2 | 16.3 | 15.2 | 13.9 | 13.3 |
| 67.5° | 25.0 | 24.2 | 23.6 | 22.7 | 21.9 | 21.1 | 20.7 | 19.9 | 18.9 | 17.6 | 16.8 |
| 65° | 31.4 | 29.9 | 28.9 | 28.9 | 28.1 | 26.5 | 25.0 | 24.3 | 23.4 | 22.0 | 20.5 |
| 62.5° | 41.3 | 40.5 | 38.5 | 36.6 | 35.3 | 34.2 | 32.3 | 30.1 | 28.5 | 27.1 | 25.1 |
| 60° | 54.0 | 49.1 | 47.0 | 44.7 | 42.2 | 39.7 | 38.0 | 35.9 | 33.5 | 31.6 | 29.6 |
| 57.5° | 80.4 | 70.6 | 65.0 | 58.6 | 51.7 | 47.9 | 45.1 | 41.9 | 39.2 | 36.5 | 34.0 |
| 55° | 134.9 | 120.7 | 105.6 | 88.2 | 71.9 | 64.6 | 56.4 | 50.1 | 46.1 | 41.7 | 38.7 |
| 52.5° | 198.7 | 181.7 | 162.7 | 141.8 | 120.6 | 98.1 | 75.8 | 66.4 | 55.5 | 48.8 | 43.9 |
| 50° | 257.8 | 240.1 | 221.4 | 201.0 | 175.7 | 148.2 | 121.4 | 94.7 | 72.8 | 60.3 | 50.4 |
| 47.5° | 313.9 | 294.5 | 273.8 | 251.7 | 228.4 | 202.5 | 171.1 | 138.2 | 107.2 | 76.2 | 62.6 |
| 45° | 368.3 | 347.5 | 324.2 | 300.2 | 275.2 | 248.6 | 220.5 | 186.7 | 149.5 | 113.8 | 76.9 |
| 42.5° | 427.1 | 401.9 | 375.8 | 349.0 | 320.4 | 292.1 | 262.4 | 230.7 | 194.9 | 153.9 | 114.0 |
| 40° | 489.4 | 461.5 | 431.8 | 399.9 | 368.1 | 334.5 | 302.5 | 269.2 | 234.4 | 195.6 | 150.6 |
| 37.5° | 553.4 | 521.4 | 489.0 | 453.8 | 417.6 | 380.7 | 343.3 | 306.6 | 269.5 | 231.6 | 188.0 |
| 35° | 619.8 | 584.4 | 546.9 | 508.6 | 467.8 | 427.6 | 386.4 | 344.7 | 304.1 | 263.7 | 222.0 |
| 32.5° | 686.9 | 648.1 | 606.1 | 563.6 | 519.4 | 474.2 | 429.6 | 384.3 | 337.9 | 294.8 | 251.2 |
| 30° | 754.5 | 711.5 | 665.7 | 617.3 | 569.2 | 520.8 | 471.6 | 422.0 | 372.3 | 324.4 | 279.2 |
| 27.5° | 820.9 | 774.2 | 724.4 | 671.7 | 616.7 | 564.8 | 511.9 | 458.1 | 404.7 | 353.7 | 305.1 |
| 25° | 886.4 | 835.2 | 780.0 | 723.6 | 665.9 | 605.4 | 549.3 | 492.7 | 436.4 | 381.0 | 328.6 |
| 22.5° | 951.6 | 894.3 | 833.7 | 771.4 | 710.9 | 647.2 | 584.5 | 524.5 | 465.8 | 407.0 | 351.5 |
| 20° | 1014.1 | 950.9 | 885.5 | 818.2 | 751.1 | 685.5 | 618.0 | 554.2 | 492.2 | 431.4 | 372.8 |
| 17.5° | 1069.3 | 1002.4 | 933.6 | 860.8 | 789.3 | 719.5 | 649.7 | 581.4 | 516.2 | 452.5 | 392.2 |
| 15° | 1120.2 | 1049.2 | 976.1 | 900.0 | 823.9 | 749.2 | 677.1 | 605.4 | 537.6 | 471.3 | 409.3 |
| 12.5° | 1166.5 | 1091.2 | 1014.6 | 934.3 | 854.5 | 775.5 | 700.4 | 627.1 | 556.4 | 488.1 | 423.8 |
| 10° | 1204.2 | 1126.0 | 1046.3 | 964.1 | 880.9 | 798.4 | 719.7 | 644.5 | 571.5 | 501.5 | 435.8 |
| 7.5° | 1234.9 | 1153.4 | 1070.6 | 987.6 | 902.0 | 817.5 | 735.8 | 657.7 | 583.3 | 511.3 | 445.3 |
| 5° | 1258.9 | 1174.9 | 1089.2 | 1004.9 | 917.1 | 830.9 | 747.8 | 666.5 | 591.5 | 517.5 | 452.1 |
| 2.5° | 1275.3 | 1189.5 | 1100.7 | 1015.3 | 926.9 | 839.2 | 756.8 | 673.4 | 597.4 | 524.1 | 458.1 |
| 0° | 1285.3 | 1200.5 | 1109.4 | 1022.6 | 935.9 | 843.8 | 762.9 | 678.1 | 599.9 | 528.3 | 461.2 |
| -2.5° | 1275.3 | 1189.5 | 1100.7 | 1015.3 | 926.9 | 839.2 | 756.8 | 673.4 | 597.4 | 524.1 | 458.1 |
| -5° | 1258.9 | 1174.9 | 1089.2 | 1004.9 | 917.1 | 830.9 | 747.8 | 666.5 | 591.5 | 517.5 | 452.1 |
| -7.5° | 1234.9 | 1153.4 | 1070.6 | 987.6 | 902.0 | 817.5 | 735.8 | 657.7 | 583.3 | 511.3 | 445.3 |
| -10° | 1204.2 | 1126.0 | 1046.3 | 964.1 | 880.9 | 798.4 | 719.7 | 644.5 | 571.5 | 501.5 | 435.8 |
| -12.5° | 1166.5 | 1091.2 | 1014.6 | 934.3 | 854.5 | 775.5 | 700.4 | 627.1 | 556.4 | 488.1 | 423.8 |
| -15° | 1120.2 | 1049.2 | 976.1 | 900.0 | 823.9 | 749.2 | 677.1 | 605.4 | 537.6 | 471.3 | 409.3 |
| -17.5° | 1069.3 | 1002.4 | 933.6 | 860.8 | 789.3 | 719.5 | 649.7 | 581.4 | 516.2 | 452.5 | 392.2 |
| -20° | 1014.1 | 950.9 | 885.5 | 818.2 | 751.1 | 685.5 | 618.0 | 554.2 | 492.2 | 431.4 | 372.8 |



REPORT NUMBER: P558483 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: GFLD-SA1A-935-U-WR-XX

CANDELA DISTRIBUTION (continued):

| | 20° | 22.5° | 25° | 27.5° | 30° | 32.5° | 35° | 37.5° | 40° | 42.5° | 45° |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| -22.5° | 951.6 | 894.3 | 833.7 | 771.4 | 710.9 | 647.2 | 584.5 | 524.5 | 465.8 | 407.0 | 351.5 |
| -25° | 886.4 | 835.2 | 780.0 | 723.6 | 665.9 | 605.4 | 549.3 | 492.7 | 436.4 | 381.0 | 328.6 |
| -27.5° | 820.9 | 774.2 | 724.4 | 671.7 | 616.7 | 564.8 | 511.9 | 458.1 | 404.7 | 353.7 | 305.1 |
| -30° | 754.5 | 711.5 | 665.7 | 617.3 | 569.2 | 520.8 | 471.6 | 422.0 | 372.3 | 324.4 | 279.2 |
| -32.5° | 686.9 | 648.1 | 606.1 | 563.6 | 519.4 | 474.2 | 429.6 | 384.3 | 337.9 | 294.8 | 251.2 |
| -35° | 619.8 | 584.4 | 546.9 | 508.6 | 467.8 | 427.6 | 386.4 | 344.7 | 304.1 | 263.7 | 222.0 |
| -37.5° | 553.4 | 521.4 | 489.0 | 453.8 | 417.6 | 380.7 | 343.3 | 306.6 | 269.5 | 231.6 | 188.0 |
| -40° | 489.4 | 461.5 | 431.8 | 399.9 | 368.1 | 334.5 | 302.5 | 269.2 | 234.4 | 195.6 | 150.6 |
| -42.5° | 427.1 | 401.9 | 375.8 | 349.0 | 320.4 | 292.1 | 262.4 | 230.7 | 194.9 | 153.9 | 114.0 |
| -45° | 368.3 | 347.5 | 324.2 | 300.2 | 275.2 | 248.6 | 220.5 | 186.7 | 149.5 | 113.8 | 76.9 |
| -47.5° | 313.9 | 294.5 | 273.8 | 251.7 | 228.4 | 202.5 | 171.1 | 138.2 | 107.2 | 76.2 | 62.6 |
| -50° | 257.8 | 240.1 | 221.4 | 201.0 | 175.7 | 148.2 | 121.4 | 94.7 | 72.8 | 60.3 | 50.4 |
| -52.5° | 198.7 | 181.7 | 162.7 | 141.8 | 120.6 | 98.1 | 75.8 | 66.4 | 55.5 | 48.8 | 43.9 |
| -55° | 134.9 | 120.7 | 105.6 | 88.2 | 71.9 | 64.6 | 56.4 | 50.1 | 46.1 | 41.7 | 38.7 |
| -57.5° | 80.4 | 70.6 | 65.0 | 58.6 | 51.7 | 47.9 | 45.1 | 41.9 | 39.2 | 36.5 | 34.0 |
| -60° | 54.0 | 49.1 | 47.0 | 44.7 | 42.2 | 39.7 | 38.0 | 35.9 | 33.5 | 31.6 | 29.6 |
| -62.5° | 41.3 | 40.5 | 38.5 | 36.6 | 35.3 | 34.2 | 32.3 | 30.1 | 28.5 | 27.1 | 25.1 |
| -65° | 31.4 | 29.9 | 28.9 | 28.9 | 28.1 | 26.5 | 25.0 | 24.3 | 23.4 | 22.0 | 20.5 |
| -67.5° | 25.0 | 24.2 | 23.6 | 22.7 | 21.9 | 21.1 | 20.7 | 19.9 | 18.9 | 17.6 | 16.8 |
| -70° | 20.8 | 20.3 | 19.8 | 19.2 | 18.6 | 17.9 | 17.2 | 16.3 | 15.2 | 13.9 | 13.3 |
| -72.5° | 17.3 | 16.9 | 16.5 | 16.0 | 15.4 | 14.8 | 14.1 | 13.2 | 12.1 | 10.9 | 9.9 |
| -75° | 14.3 | 14.1 | 13.9 | 13.4 | 12.9 | 12.3 | 11.5 | 10.4 | 9.0 | 7.3 | 6.1 |
| -77.5° | 11.0 | 10.9 | 10.8 | 10.5 | 10.1 | 9.8 | 9.2 | 7.6 | 6.1 | 4.7 | 3.9 |
| -80° | 6.9 | 7.2 | 7.4 | 7.2 | 6.9 | 6.5 | 6.0 | 4.9 | 3.9 | 3.1 | 2.6 |
| -82.5° | 4.0 | 4.1 | 4.1 | 3.9 | 3.6 | 3.4 | 3.2 | 2.7 | 2.2 | 1.7 | 1.4 |
| -85° | 1.1 | 1.0 | 1.0 | 1.1 | 1.2 | 1.2 | 1.2 | 1.1 | 0.9 | 0.8 | 0.7 |
| -87.5° | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.3 | 0.3 |
| -90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P558483 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: GFLD-SA1A-935-U-WR-XX

CANDELA DISTRIBUTION (continued):

| | 47.5° | 50° | 52.5° | 55° | 57.5° | 60° | 62.5° | 65° | 67.5° | 70° | 72.5° |
|--------|-------|-------|-------|-------|-------|------|-------|------|-------|------|-------|
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.3 | 0.3 | 0.2 | 0.2 | 0.2 | 0.3 | 0.3 | 0.3 | 0.2 | 0.2 | 0.2 |
| 85° | 0.7 | 0.7 | 0.7 | 0.6 | 0.6 | 0.5 | 0.5 | 0.5 | 0.5 | 0.4 | 0.4 |
| 82.5° | 1.4 | 1.4 | 1.4 | 1.4 | 1.4 | 1.4 | 1.3 | 1.1 | 0.9 | 0.6 | 0.5 |
| 80° | 3.0 | 3.1 | 3.1 | 2.9 | 2.6 | 2.2 | 2.1 | 2.0 | 1.6 | 1.3 | 1.0 |
| 77.5° | 4.5 | 5.0 | 5.3 | 5.2 | 4.6 | 4.0 | 3.5 | 2.9 | 2.3 | 1.9 | 1.5 |
| 75° | 6.2 | 6.8 | 7.2 | 7.2 | 6.6 | 5.8 | 5.1 | 4.4 | 3.5 | 2.6 | 2.0 |
| 72.5° | 9.4 | 9.2 | 9.3 | 9.3 | 8.8 | 8.0 | 7.0 | 5.8 | 4.8 | 3.7 | 2.7 |
| 70° | 12.6 | 11.8 | 11.2 | 11.1 | 10.9 | 10.3 | 9.3 | 7.7 | 6.1 | 4.9 | 3.7 |
| 67.5° | 16.0 | 15.2 | 14.1 | 13.2 | 12.8 | 12.3 | 11.5 | 9.7 | 7.7 | 6.0 | 4.7 |
| 65° | 19.5 | 18.5 | 17.5 | 16.1 | 15.0 | 14.3 | 13.5 | 11.6 | 9.4 | 7.4 | 5.6 |
| 62.5° | 23.3 | 21.6 | 20.4 | 18.9 | 17.4 | 16.3 | 15.5 | 13.4 | 10.9 | 8.6 | 6.7 |
| 60° | 27.5 | 25.4 | 23.2 | 21.5 | 19.8 | 18.2 | 17.0 | 15.2 | 12.6 | 9.9 | 7.7 |
| 57.5° | 31.7 | 29.1 | 26.5 | 24.1 | 22.1 | 20.2 | 18.5 | 16.7 | 14.3 | 11.4 | 8.6 |
| 55° | 35.9 | 33.1 | 29.7 | 26.8 | 24.4 | 22.3 | 20.0 | 18.1 | 16.0 | 12.9 | 9.3 |
| 52.5° | 40.0 | 36.8 | 33.2 | 29.6 | 26.7 | 24.3 | 21.8 | 19.4 | 17.2 | 14.5 | 10.3 |
| 50° | 45.0 | 40.4 | 36.6 | 32.7 | 28.9 | 26.1 | 23.4 | 20.9 | 18.5 | 16.0 | 11.3 |
| 47.5° | 50.8 | 44.9 | 39.9 | 35.7 | 31.6 | 27.9 | 25.0 | 22.2 | 19.8 | 17.1 | 12.2 |
| 45° | 62.4 | 50.1 | 43.8 | 38.8 | 34.2 | 30.1 | 26.6 | 23.5 | 20.9 | 17.6 | 12.9 |
| 42.5° | 75.6 | 59.8 | 48.4 | 41.9 | 37.0 | 32.3 | 28.2 | 24.9 | 21.9 | 17.9 | 13.3 |
| 40° | 107.5 | 71.9 | 54.6 | 45.9 | 39.7 | 34.3 | 30.0 | 26.3 | 22.8 | 18.1 | 13.5 |
| 37.5° | 140.1 | 94.3 | 65.5 | 49.9 | 42.6 | 36.8 | 31.7 | 27.6 | 23.1 | 18.3 | 13.5 |
| 35° | 173.3 | 123.6 | 76.2 | 57.0 | 46.1 | 39.2 | 33.3 | 28.9 | 24.0 | 18.4 | 13.5 |
| 32.5° | 204.8 | 151.9 | 100.7 | 66.5 | 49.5 | 41.5 | 35.1 | 30.3 | 25.1 | 18.6 | 13.3 |
| 30° | 231.8 | 179.4 | 124.9 | 75.6 | 54.2 | 44.3 | 37.1 | 31.5 | 26.4 | 18.8 | 13.1 |
| 27.5° | 256.4 | 205.0 | 147.7 | 93.1 | 62.0 | 47.1 | 39.0 | 32.7 | 27.9 | 19.3 | 13.1 |
| 25° | 279.0 | 227.0 | 169.7 | 112.3 | 69.4 | 49.7 | 40.7 | 33.8 | 29.0 | 20.3 | 13.1 |
| 22.5° | 298.9 | 246.5 | 189.9 | 129.8 | 76.0 | 52.3 | 42.5 | 35.3 | 29.9 | 21.3 | 13.1 |
| 20° | 316.8 | 264.2 | 208.2 | 145.9 | 86.8 | 57.7 | 44.5 | 36.5 | 30.7 | 22.4 | 13.0 |
| 17.5° | 333.0 | 279.6 | 223.5 | 161.3 | 99.8 | 62.6 | 46.4 | 37.6 | 31.5 | 23.5 | 12.9 |
| 15° | 348.7 | 292.7 | 236.6 | 174.8 | 111.2 | 66.8 | 48.0 | 38.6 | 32.1 | 24.6 | 12.8 |
| 12.5° | 361.9 | 303.9 | 247.6 | 186.5 | 121.0 | 70.3 | 49.5 | 39.4 | 32.7 | 25.5 | 12.7 |
| 10° | 372.5 | 313.1 | 256.6 | 196.3 | 129.2 | 73.2 | 50.7 | 40.0 | 33.1 | 26.3 | 12.5 |
| 7.5° | 380.5 | 320.3 | 263.5 | 204.2 | 135.7 | 75.6 | 51.5 | 40.3 | 33.4 | 26.9 | 12.1 |
| 5° | 386.3 | 325.8 | 268.5 | 210.0 | 140.4 | 77.5 | 51.9 | 40.5 | 33.7 | 27.4 | 11.6 |
| 2.5° | 391.1 | 329.6 | 271.7 | 213.7 | 143.2 | 78.8 | 52.1 | 40.5 | 33.8 | 27.6 | 11.0 |
| 0° | 393.4 | 331.3 | 272.9 | 215.3 | 144.3 | 79.5 | 52.1 | 40.4 | 33.9 | 27.6 | 10.3 |
| -2.5° | 391.1 | 329.6 | 271.7 | 213.7 | 143.2 | 78.8 | 52.1 | 40.5 | 33.8 | 27.6 | 11.0 |
| -5° | 386.3 | 325.8 | 268.5 | 210.0 | 140.4 | 77.5 | 51.9 | 40.5 | 33.7 | 27.4 | 11.6 |
| -7.5° | 380.5 | 320.3 | 263.5 | 204.2 | 135.7 | 75.6 | 51.5 | 40.3 | 33.4 | 26.9 | 12.1 |
| -10° | 372.5 | 313.1 | 256.6 | 196.3 | 129.2 | 73.2 | 50.7 | 40.0 | 33.1 | 26.3 | 12.5 |
| -12.5° | 361.9 | 303.9 | 247.6 | 186.5 | 121.0 | 70.3 | 49.5 | 39.4 | 32.7 | 25.5 | 12.7 |
| -15° | 348.7 | 292.7 | 236.6 | 174.8 | 111.2 | 66.8 | 48.0 | 38.6 | 32.1 | 24.6 | 12.8 |
| -17.5° | 333.0 | 279.6 | 223.5 | 161.3 | 99.8 | 62.6 | 46.4 | 37.6 | 31.5 | 23.5 | 12.9 |
| -20° | 316.8 | 264.2 | 208.2 | 145.9 | 86.8 | 57.7 | 44.5 | 36.5 | 30.7 | 22.4 | 13.0 |



REPORT NUMBER: P558483 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: GFLD-SA1A-935-U-WR-XX

CANDELA DISTRIBUTION (continued):

| | 47.5° | 50° | 52.5° | 55° | 57.5° | 60° | 62.5° | 65° | 67.5° | 70° | 72.5° |
|--------|-------|-------|-------|-------|-------|------|-------|------|-------|------|-------|
| -22.5° | 298.9 | 246.5 | 189.9 | 129.8 | 76.0 | 52.3 | 42.5 | 35.3 | 29.9 | 21.3 | 13.1 |
| -25° | 279.0 | 227.0 | 169.7 | 112.3 | 69.4 | 49.7 | 40.7 | 33.8 | 29.0 | 20.3 | 13.1 |
| -27.5° | 256.4 | 205.0 | 147.7 | 93.1 | 62.0 | 47.1 | 39.0 | 32.7 | 27.9 | 19.3 | 13.1 |
| -30° | 231.8 | 179.4 | 124.9 | 75.6 | 54.2 | 44.3 | 37.1 | 31.5 | 26.4 | 18.8 | 13.1 |
| -32.5° | 204.8 | 151.9 | 100.7 | 66.5 | 49.5 | 41.5 | 35.1 | 30.3 | 25.1 | 18.6 | 13.3 |
| -35° | 173.3 | 123.6 | 76.2 | 57.0 | 46.1 | 39.2 | 33.3 | 28.9 | 24.0 | 18.4 | 13.5 |
| -37.5° | 140.1 | 94.3 | 65.5 | 49.9 | 42.6 | 36.8 | 31.7 | 27.6 | 23.1 | 18.3 | 13.5 |
| -40° | 107.5 | 71.9 | 54.6 | 45.9 | 39.7 | 34.3 | 30.0 | 26.3 | 22.8 | 18.1 | 13.5 |
| -42.5° | 75.6 | 59.8 | 48.4 | 41.9 | 37.0 | 32.3 | 28.2 | 24.9 | 21.9 | 17.9 | 13.3 |
| -45° | 62.4 | 50.1 | 43.8 | 38.8 | 34.2 | 30.1 | 26.6 | 23.5 | 20.9 | 17.6 | 12.9 |
| -47.5° | 50.8 | 44.9 | 39.9 | 35.7 | 31.6 | 27.9 | 25.0 | 22.2 | 19.8 | 17.1 | 12.2 |
| -50° | 45.0 | 40.4 | 36.6 | 32.7 | 28.9 | 26.1 | 23.4 | 20.9 | 18.5 | 16.0 | 11.3 |
| -52.5° | 40.0 | 36.8 | 33.2 | 29.6 | 26.7 | 24.3 | 21.8 | 19.4 | 17.2 | 14.5 | 10.3 |
| -55° | 35.9 | 33.1 | 29.7 | 26.8 | 24.4 | 22.3 | 20.0 | 18.1 | 16.0 | 12.9 | 9.3 |
| -57.5° | 31.7 | 29.1 | 26.5 | 24.1 | 22.1 | 20.2 | 18.5 | 16.7 | 14.3 | 11.4 | 8.6 |
| -60° | 27.5 | 25.4 | 23.2 | 21.5 | 19.8 | 18.2 | 17.0 | 15.2 | 12.6 | 9.9 | 7.7 |
| -62.5° | 23.3 | 21.6 | 20.4 | 18.9 | 17.4 | 16.3 | 15.5 | 13.4 | 10.9 | 8.6 | 6.7 |
| -65° | 19.5 | 18.5 | 17.5 | 16.1 | 15.0 | 14.3 | 13.5 | 11.6 | 9.4 | 7.4 | 5.6 |
| -67.5° | 16.0 | 15.2 | 14.1 | 13.2 | 12.8 | 12.3 | 11.5 | 9.7 | 7.7 | 6.0 | 4.7 |
| -70° | 12.6 | 11.8 | 11.2 | 11.1 | 10.9 | 10.3 | 9.3 | 7.7 | 6.1 | 4.9 | 3.7 |
| -72.5° | 9.4 | 9.2 | 9.3 | 9.3 | 8.8 | 8.0 | 7.0 | 5.8 | 4.8 | 3.7 | 2.7 |
| -75° | 6.2 | 6.8 | 7.2 | 7.2 | 6.6 | 5.8 | 5.1 | 4.4 | 3.5 | 2.6 | 2.0 |
| -77.5° | 4.5 | 5.0 | 5.3 | 5.2 | 4.6 | 4.0 | 3.5 | 2.9 | 2.3 | 1.9 | 1.5 |
| -80° | 3.0 | 3.1 | 3.1 | 2.9 | 2.6 | 2.2 | 2.1 | 2.0 | 1.6 | 1.3 | 1.0 |
| -82.5° | 1.4 | 1.4 | 1.4 | 1.4 | 1.4 | 1.4 | 1.3 | 1.1 | 0.9 | 0.6 | 0.5 |
| -85° | 0.7 | 0.7 | 0.7 | 0.6 | 0.6 | 0.5 | 0.5 | 0.5 | 0.5 | 0.4 | 0.4 |
| -87.5° | 0.3 | 0.3 | 0.2 | 0.2 | 0.2 | 0.3 | 0.3 | 0.3 | 0.2 | 0.2 | 0.2 |
| -90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P558483 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: GFLD-SA1A-935-U-WR-XX

CANDELA DISTRIBUTION (continued):

| | 75° | 77.5° | 80° | 82.5° | 85° | 87.5° | 90° |
|--------|-----|-------|-----|-------|-----|-------|-----|
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.2 | 0.1 | 0.1 | 0.1 | 0.1 | 0.0 | 0.0 |
| 85° | 0.3 | 0.3 | 0.2 | 0.2 | 0.1 | 0.1 | 0.0 |
| 82.5° | 0.5 | 0.4 | 0.3 | 0.2 | 0.2 | 0.1 | 0.0 |
| 80° | 0.7 | 0.5 | 0.4 | 0.3 | 0.2 | 0.1 | 0.0 |
| 77.5° | 1.1 | 0.7 | 0.5 | 0.4 | 0.3 | 0.1 | 0.0 |
| 75° | 1.5 | 1.0 | 0.6 | 0.5 | 0.3 | 0.2 | 0.0 |
| 72.5° | 2.0 | 1.3 | 0.8 | 0.5 | 0.4 | 0.2 | 0.0 |
| 70° | 2.4 | 1.6 | 1.0 | 0.6 | 0.4 | 0.2 | 0.0 |
| 67.5° | 3.2 | 1.9 | 1.2 | 0.7 | 0.5 | 0.2 | 0.0 |
| 65° | 3.9 | 2.3 | 1.4 | 0.9 | 0.5 | 0.3 | 0.0 |
| 62.5° | 4.5 | 2.8 | 1.6 | 1.0 | 0.6 | 0.3 | 0.0 |
| 60° | 5.1 | 3.2 | 1.8 | 1.1 | 0.6 | 0.3 | 0.0 |
| 57.5° | 5.7 | 3.6 | 2.0 | 1.2 | 0.7 | 0.3 | 0.0 |
| 55° | 6.3 | 3.9 | 2.2 | 1.3 | 0.7 | 0.3 | 0.0 |
| 52.5° | 6.7 | 4.2 | 2.4 | 1.3 | 0.8 | 0.4 | 0.0 |
| 50° | 7.1 | 4.5 | 2.6 | 1.4 | 0.8 | 0.4 | 0.0 |
| 47.5° | 7.4 | 4.7 | 2.8 | 1.5 | 0.9 | 0.4 | 0.0 |
| 45° | 8.0 | 4.9 | 2.9 | 1.6 | 0.9 | 0.4 | 0.0 |
| 42.5° | 8.5 | 5.0 | 2.9 | 1.6 | 1.0 | 0.4 | 0.0 |
| 40° | 9.0 | 5.0 | 3.0 | 1.7 | 1.0 | 0.5 | 0.0 |
| 37.5° | 9.3 | 5.0 | 3.0 | 1.8 | 1.1 | 0.5 | 0.0 |
| 35° | 9.5 | 5.1 | 3.0 | 1.9 | 1.1 | 0.5 | 0.0 |
| 32.5° | 9.5 | 5.3 | 3.0 | 1.9 | 1.1 | 0.5 | 0.0 |
| 30° | 9.3 | 5.4 | 2.9 | 2.0 | 1.2 | 0.5 | 0.0 |
| 27.5° | 9.1 | 5.4 | 3.0 | 2.1 | 1.2 | 0.5 | 0.0 |
| 25° | 8.8 | 5.3 | 3.0 | 2.1 | 1.2 | 0.5 | 0.0 |
| 22.5° | 8.4 | 5.3 | 3.1 | 2.2 | 1.3 | 0.6 | 0.0 |
| 20° | 7.9 | 5.6 | 3.2 | 2.2 | 1.3 | 0.6 | 0.0 |
| 17.5° | 7.8 | 5.8 | 3.3 | 2.3 | 1.3 | 0.6 | 0.0 |
| 15° | 8.0 | 6.0 | 3.4 | 2.3 | 1.3 | 0.6 | 0.0 |
| 12.5° | 8.1 | 6.1 | 3.5 | 2.3 | 1.4 | 0.6 | 0.0 |
| 10° | 8.2 | 6.3 | 3.5 | 2.4 | 1.4 | 0.6 | 0.0 |
| 7.5° | 8.3 | 6.4 | 3.6 | 2.4 | 1.4 | 0.6 | 0.0 |
| 5° | 8.4 | 6.4 | 3.6 | 2.4 | 1.4 | 0.6 | 0.0 |
| 2.5° | 8.5 | 6.5 | 3.7 | 2.4 | 1.4 | 0.6 | 0.0 |
| 0° | 8.5 | 6.5 | 3.7 | 2.4 | 1.4 | 0.6 | 0.0 |
| -2.5° | 8.5 | 6.5 | 3.7 | 2.4 | 1.4 | 0.6 | 0.0 |
| -5° | 8.4 | 6.4 | 3.6 | 2.4 | 1.4 | 0.6 | 0.0 |
| -7.5° | 8.3 | 6.4 | 3.6 | 2.4 | 1.4 | 0.6 | 0.0 |
| -10° | 8.2 | 6.3 | 3.5 | 2.4 | 1.4 | 0.6 | 0.0 |
| -12.5° | 8.1 | 6.1 | 3.5 | 2.3 | 1.4 | 0.6 | 0.0 |
| -15° | 8.0 | 6.0 | 3.4 | 2.3 | 1.3 | 0.6 | 0.0 |
| -17.5° | 7.8 | 5.8 | 3.3 | 2.3 | 1.3 | 0.6 | 0.0 |
| -20° | 7.9 | 5.6 | 3.2 | 2.2 | 1.3 | 0.6 | 0.0 |



REPORT NUMBER: P558483 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: GFLD-SA1A-935-U-WR-XX

CANDELA DISTRIBUTION (continued):

| | 75° | 77.5° | 80° | 82.5° | 85° | 87.5° | 90° |
|--------|-----|-------|-----|-------|-----|-------|-----|
| -22.5° | 8.4 | 5.3 | 3.1 | 2.2 | 1.3 | 0.6 | 0.0 |
| -25° | 8.8 | 5.3 | 3.0 | 2.1 | 1.2 | 0.5 | 0.0 |
| -27.5° | 9.1 | 5.4 | 3.0 | 2.1 | 1.2 | 0.5 | 0.0 |
| -30° | 9.3 | 5.4 | 2.9 | 2.0 | 1.2 | 0.5 | 0.0 |
| -32.5° | 9.5 | 5.3 | 3.0 | 1.9 | 1.1 | 0.5 | 0.0 |
| -35° | 9.5 | 5.1 | 3.0 | 1.9 | 1.1 | 0.5 | 0.0 |
| -37.5° | 9.3 | 5.0 | 3.0 | 1.8 | 1.1 | 0.5 | 0.0 |
| -40° | 9.0 | 5.0 | 3.0 | 1.7 | 1.0 | 0.5 | 0.0 |
| -42.5° | 8.5 | 5.0 | 2.9 | 1.6 | 1.0 | 0.4 | 0.0 |
| -45° | 8.0 | 4.9 | 2.9 | 1.6 | 0.9 | 0.4 | 0.0 |
| -47.5° | 7.4 | 4.7 | 2.8 | 1.5 | 0.9 | 0.4 | 0.0 |
| -50° | 7.1 | 4.5 | 2.6 | 1.4 | 0.8 | 0.4 | 0.0 |
| -52.5° | 6.7 | 4.2 | 2.4 | 1.3 | 0.8 | 0.4 | 0.0 |
| -55° | 6.3 | 3.9 | 2.2 | 1.3 | 0.7 | 0.3 | 0.0 |
| -57.5° | 5.7 | 3.6 | 2.0 | 1.2 | 0.7 | 0.3 | 0.0 |
| -60° | 5.1 | 3.2 | 1.8 | 1.1 | 0.6 | 0.3 | 0.0 |
| -62.5° | 4.5 | 2.8 | 1.6 | 1.0 | 0.6 | 0.3 | 0.0 |
| -65° | 3.9 | 2.3 | 1.4 | 0.9 | 0.5 | 0.3 | 0.0 |
| -67.5° | 3.2 | 1.9 | 1.2 | 0.7 | 0.5 | 0.2 | 0.0 |
| -70° | 2.4 | 1.6 | 1.0 | 0.6 | 0.4 | 0.2 | 0.0 |
| -72.5° | 2.0 | 1.3 | 0.8 | 0.5 | 0.4 | 0.2 | 0.0 |
| -75° | 1.5 | 1.0 | 0.6 | 0.5 | 0.3 | 0.2 | 0.0 |
| -77.5° | 1.1 | 0.7 | 0.5 | 0.4 | 0.3 | 0.1 | 0.0 |
| -80° | 0.7 | 0.5 | 0.4 | 0.3 | 0.2 | 0.1 | 0.0 |
| -82.5° | 0.5 | 0.4 | 0.3 | 0.2 | 0.2 | 0.1 | 0.0 |
| -85° | 0.3 | 0.3 | 0.2 | 0.2 | 0.1 | 0.1 | 0.0 |
| -87.5° | 0.2 | 0.1 | 0.1 | 0.1 | 0.1 | 0.0 | 0.0 |
| -90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

(END OF REPORT)