

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P832586

Luminaire Tested: **TTN-D1-830-U-DL-CG**

Issue Date: 5/14/2024

Test Information

Test Method: LM-79-08
Report Number: P832586
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2312-254-15)
Test Lab: INNOVATION CENTER
Issue Date: 5/14/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TTN-D1-830-U-DL-CG
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE
3000K, 80 CRI LEDS AND DRIVE LANE DISTRIBUTION WITH CLEAR GLASS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2831 lumens
Efficiency: N/A
Efficacy: 107.2 lumens/watt
Luminous Opening: Circular (Dia: 0.71' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G1


Input Watts (W): 26.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P832586
 CATALOG NUMBER: TTN-D1-830-U-DL-CG

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.7 fc
 Type IV - Short - N/A

REPORT NUMBER: P832586
CATALOG NUMBER: TTN-D1-830-U-DL-CG

Luminous Intensity Polar Plot



— Vertical Plane Through 33-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P832586
 CATALOG NUMBER: TTN-D1-830-U-DL-CG


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	624.7	0.0	624.7
	% Fixture	22.1	0.0	22.1
Street Side	Lumens	2206.3	0.0	2206.3
	% Fixture	77.9	0.0	77.9
Total	Lumens	2831.0	0.0	2831.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.4	0.9
10°-20°	82.3	2.9
20°-30°	173.6	6.1
30°-40°	315.3	11.1
40°-50°	498.2	17.6
50°-60°	661.6	23.4
60°-70°	636.8	22.5
70°-80°	373.8	13.2
80°-90°	64.2	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2831.0	100.0
0°-180°	2831.0	100.0

Coefficient of Utilization



REPORT NUMBER: P832586


CATALOG NUMBER: TTN-D1-830-U-DL-CG

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	189.4	6.7			
FM (30°-60°)	1145.3	40.5			
FH (60°-80°)	817.4	28.9			G1/1800
FVH (80°-90°)	54.2	1.9			G1/100
BL (0°-30°)	91.9	3.2	B0/110		
BM (30°-60°)	329.6	11.6	B1/1000		
BH (60°-80°)	193.2	6.8	B1/500		G1/500
BVH (80°-90°)	10.0	0.4			G0/10
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type IV Short





REPORT NUMBER: P832586
 CATALOG NUMBER: TTN-D1-830-U-DL-CG

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	33°	35°	45°	55°	65°	75°	85°
0°	265.3	265.3	265.3	265.3	265.3	265.3	265.3	265.3	265.3	265.3	265.3
2.5°	282.7	285.2	282.7	282.7	280.2	280.2	277.7	275.3	272.8	270.3	265.3
5°	314.9	314.9	312.4	307.5	305.0	302.5	297.6	290.1	285.2	277.7	270.3
7.5°	329.8	329.8	327.3	322.4	317.4	314.9	307.5	297.6	290.1	280.2	270.3
10°	349.6	352.1	347.2	342.2	337.2	334.8	324.8	312.4	300.0	287.7	272.8
12.5°	372.0	374.4	372.0	364.5	357.1	354.6	344.7	329.8	314.9	297.6	280.2
15°	401.7	406.7	399.2	394.3	386.8	384.4	372.0	354.6	337.2	314.9	292.6
17.5°	436.4	438.9	434.0	426.5	421.6	419.1	406.7	386.8	362.0	337.2	310.0
20°	476.1	478.6	476.1	466.2	461.2	458.8	446.4	424.0	394.3	367.0	332.3
22.5°	523.2	528.2	520.7	513.3	508.3	508.3	493.5	468.7	434.0	399.2	359.6
25°	577.8	585.2	575.3	570.3	565.4	562.9	550.5	520.7	481.1	438.9	389.3
27.5°	644.7	649.7	642.3	639.8	629.9	629.9	610.0	575.3	533.1	483.6	426.5
30°	704.2	709.2	704.2	704.2	696.8	694.3	674.5	639.8	587.7	528.2	458.8
32.5°	761.3	766.2	763.8	766.2	763.8	761.3	736.5	699.3	647.2	570.3	491.0
35°	818.3	825.8	823.3	830.7	828.2	825.8	805.9	761.3	699.3	622.4	525.7
37.5°	877.8	885.3	885.3	892.7	895.2	895.2	872.9	825.8	756.3	669.5	565.4
40°	942.3	949.7	949.7	962.1	967.1	967.1	942.3	895.2	818.3	721.6	607.5
42.5°	1004.3	1011.7	1014.2	1026.6	1034.1	1036.5	1016.7	962.1	872.9	773.7	647.2
45°	1063.8	1071.3	1078.7	1103.5	1115.9	1113.4	1098.5	1041.5	942.3	828.2	689.4
47.5°	1120.8	1130.8	1143.2	1175.4	1192.8	1190.3	1180.4	1115.9	1006.8	880.3	726.6
50°	1165.5	1172.9	1197.7	1232.4	1254.8	1257.2	1242.4	1180.4	1061.3	920.0	753.8
52.5°	1200.2	1210.1	1239.9	1289.5	1306.8	1314.3	1296.9	1234.9	1115.9	954.7	776.2
55°	1225.0	1225.0	1269.6	1326.7	1351.5	1356.4	1356.4	1279.6	1148.1	977.0	788.6
57.5°	1212.6	1212.6	1262.2	1324.2	1363.9	1361.4	1356.4	1282.0	1153.1	972.1	781.1
60°	1177.9	1185.3	1232.4	1294.4	1334.1	1331.6	1316.7	1249.8	1128.3	952.2	766.2
62.5°	1130.8	1143.2	1192.8	1239.9	1284.5	1291.9	1272.1	1212.6	1086.1	922.5	739.0
65°	1041.5	1058.9	1120.8	1172.9	1207.6	1222.5	1197.7	1143.2	1029.1	865.4	681.9
67.5°	942.3	954.7	1006.8	1081.2	1101.0	1115.9	1103.5	1046.5	949.7	773.7	617.5
70°	828.2	848.1	882.8	957.2	979.5	994.4	994.4	937.3	845.6	679.5	540.6
72.5°	694.3	716.6	758.8	813.4	843.1	853.0	850.6	803.4	721.6	575.3	456.3
75°	548.0	565.4	615.0	654.7	686.9	694.3	691.9	652.2	577.8	463.7	362.0
77.5°	404.2	421.6	458.8	488.5	518.3	513.3	513.3	483.6	436.4	344.7	275.3
80°	265.3	280.2	312.4	322.4	354.6	352.1	352.1	329.8	297.6	230.6	183.5
82.5°	146.3	158.7	181.0	190.9	210.8	205.8	208.3	193.4	173.6	128.9	104.1
85°	52.1	62.0	74.4	81.8	91.8	91.8	91.8	79.4	74.4	49.6	42.2
87.5°	2.5	5.0	9.9	9.9	14.9	14.9	14.9	9.9	9.9	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P832586
 CATALOG NUMBER: TTN-D1-830-U-DL-CG

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	265.3	265.3	265.3	265.3	265.3	265.3	265.3	265.3	265.3	265.3	265.3
2.5°	262.9	260.4	257.9	252.9	250.5	248.0	245.5	243.0	243.0	243.0	243.0
5°	265.3	262.9	255.4	248.0	240.5	233.1	228.1	225.7	223.2	220.7	220.7
7.5°	265.3	260.4	250.5	240.5	233.1	223.2	215.7	208.3	203.3	200.9	200.9
10°	267.8	260.4	248.0	238.1	225.7	213.3	203.3	193.4	188.5	183.5	183.5
12.5°	272.8	265.3	248.0	235.6	220.7	205.8	193.4	183.5	176.1	171.1	171.1
15°	282.7	272.8	252.9	235.6	218.2	200.9	188.5	176.1	168.6	163.7	163.7
17.5°	297.6	285.2	260.4	235.6	215.7	198.4	183.5	171.1	161.2	156.2	156.2
20°	314.9	300.0	270.3	240.5	215.7	195.9	181.0	166.1	156.2	151.3	151.3
22.5°	339.7	317.4	282.7	248.0	220.7	198.4	178.5	163.7	153.7	148.8	148.8
25°	367.0	342.2	297.6	257.9	225.7	198.4	178.5	163.7	153.7	148.8	146.3
27.5°	396.8	369.5	314.9	267.8	230.6	203.3	181.0	163.7	153.7	148.8	148.8
30°	424.0	391.8	332.3	280.2	238.1	205.8	183.5	166.1	153.7	148.8	148.8
32.5°	453.8	416.6	349.6	292.6	245.5	210.8	186.0	168.6	156.2	151.3	148.8
35°	483.6	441.4	367.0	302.5	252.9	215.7	188.5	171.1	158.7	153.7	153.7
37.5°	515.8	468.7	384.4	314.9	260.4	220.7	193.4	173.6	161.2	156.2	156.2
40°	550.5	496.0	401.7	324.8	267.8	225.7	198.4	178.5	166.1	161.2	161.2
42.5°	585.2	525.7	421.6	337.2	275.3	230.6	200.9	183.5	171.1	166.1	166.1
45°	619.9	550.5	438.9	349.6	282.7	238.1	208.3	188.5	176.1	171.1	171.1
47.5°	652.2	577.8	453.8	357.1	290.1	243.0	210.8	193.4	181.0	178.5	176.1
50°	674.5	595.1	463.7	364.5	292.6	245.5	215.7	195.9	186.0	181.0	181.0
52.5°	691.9	612.5	471.2	369.5	295.1	248.0	218.2	200.9	190.9	186.0	183.5
55°	701.8	615.0	471.2	364.5	292.6	248.0	218.2	200.9	190.9	186.0	186.0
57.5°	691.9	602.6	461.2	354.6	285.2	240.5	210.8	195.9	186.0	183.5	181.0
60°	672.0	582.7	441.4	339.7	272.8	228.1	200.9	188.5	181.0	178.5	176.1
62.5°	644.7	557.9	421.6	319.9	255.4	213.3	193.4	178.5	173.6	171.1	168.6
65°	590.2	510.8	389.3	295.1	233.1	195.9	176.1	166.1	161.2	156.2	153.7
67.5°	530.7	458.8	344.7	265.3	205.8	176.1	158.7	148.8	141.3	141.3	138.9
70°	466.2	404.2	297.6	225.7	178.5	153.7	136.4	128.9	124.0	124.0	121.5
72.5°	389.3	339.7	248.0	183.5	146.3	126.5	114.1	106.6	104.1	104.1	101.7
75°	312.4	267.8	195.9	143.8	114.1	99.2	89.3	84.3	81.8	81.8	79.4
77.5°	230.6	195.9	141.3	104.1	81.8	71.9	64.5	62.0	59.5	59.5	57.0
80°	153.7	128.9	91.8	67.0	49.6	44.6	39.7	39.7	37.2	39.7	37.2
82.5°	84.3	69.4	49.6	34.7	24.8	22.3	19.8	19.8	22.3	22.3	19.8
85°	32.2	24.8	17.4	9.9	7.4	7.4	7.4	7.4	7.4	7.4	5.0
87.5°	2.5	2.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)