

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P833677

Luminaire Tested: **TTN-D2-830-U-DL-UPL1**

Issue Date: 5/15/2024

Test Information

Test Method: LM-79-08
Report Number: P833677
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G3-2308-121-4) AND
Test Lab: INNOVATION CENTER
Issue Date: 5/15/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: TTN-D2-830-U-DL-UPL1
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE WITH UPLIGHT
3000K, 80 CRI LEDS AND DRIVE LANE DISTRIBUTION
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4786.9 lumens
Efficiency: N/A
Efficacy: 106.1 lumens/watt
Luminous Opening: Vertical Cylinder (Dia: 0.71' x H: 0.1')
IES Classification: Type IV - Short
BUG Rating: B1 - U3 - G2


Input Watts (W): 45.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P833677
 CATALOG NUMBER: TTN-D2-830-U-DL-UPL1

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1 fc
 Type IV - Short - N/A

REPORT NUMBER: P833677
CATALOG NUMBER: TTN-D2-830-U-DL-UPL1

Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P833677

CATALOG NUMBER: TTN-D2-830-U-DL-UPL1


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	956.6	147.7	1104.3
	% Fixture	20.0	3.1	23.1
Street Side	Lumens	3534.8	147.7	3682.6
	% Fixture	73.8	3.1	76.9
Total	Lumens	4491.4	295.5	4786.9
	% Fixture	93.8	6.2	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.7	0.7
10°-20°	113.8	2.4
20°-30°	240.5	5.0
30°-40°	439.5	9.2
40°-50°	714.2	14.9
50°-60°	992.7	20.7
60°-70°	1029.1	21.5
70°-80°	737.4	15.4
80°-90°	188.4	3.9
90°-100°	6.6	0.1
100°-110°	67.0	1.4
110°-120°	98.0	2.0
120°-130°	56.9	1.2
130°-140°	30.1	0.6
140°-150°	17.9	0.4
150°-160°	11.0	0.2
160°-170°	6.0	0.1
170°-180°	2.0	0.0
0°-90°	4491.4	93.8
0°-180°	4786.9	100.0

Coefficient of Utilization




REPORT NUMBER: P833677
 CATALOG NUMBER: TTN-D2-830-U-DL-UPL1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	262.8	5.5			
FM (30°-60°)	1676.9	35.0			
FH (60°-80°)	1438.3	30.0			G1/1800
FVH (80°-90°)	156.8	3.3			G2/225
BL (0°-30°)	127.2	2.7	B1/500		
BM (30°-60°)	469.5	9.8	B1/1000		
BH (60°-80°)	328.3	6.9	B1/500		G1/500
BVH (80°-90°)	31.6	0.7			G1/100
UL (90°-100°)	6.6	0.1		U1/10	
UH (100°-180°)	288.9	6.0		U3/500	

BUG Rating: B1-U3-G2
 Type IV Short





REPORT NUMBER: P833677

CATALOG NUMBER: TTN-D2-830-U-DL-UPL1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	40°	45°	55°	65°	75°	85°
0°	378.2	378.2	378.2	378.2	378.2	378.2	378.2	378.2	378.2	378.2	378.2
2.5°	405.5	405.5	405.5	405.5	401.6	401.6	397.7	393.8	389.9	386.0	378.2
5°	440.6	440.6	436.7	432.8	425.0	421.1	417.2	409.4	401.6	393.8	382.1
7.5°	456.2	456.2	456.2	452.3	440.6	436.7	428.9	417.2	405.5	393.8	378.2
10°	483.5	483.5	479.6	475.7	464.0	460.1	452.3	436.7	417.2	397.7	378.2
12.5°	518.6	514.7	510.8	506.9	495.2	487.4	475.7	460.1	436.7	413.3	389.9
15°	561.5	553.7	553.7	545.9	534.2	522.5	514.7	491.3	467.9	436.7	405.5
17.5°	608.3	604.4	600.5	592.7	581.0	573.2	561.5	534.2	503.0	464.0	428.9
20°	666.8	659.0	662.9	651.2	639.5	635.6	616.1	584.9	545.9	503.0	460.1
22.5°	737.0	729.2	729.2	717.5	709.7	701.9	682.4	647.3	596.6	549.8	495.2
25°	815.0	807.2	807.2	799.4	791.6	783.8	760.4	721.4	662.9	604.4	542.0
27.5°	900.8	893.0	893.0	889.1	869.6	857.9	838.4	795.5	737.0	662.9	588.8
30°	990.4	982.6	990.4	982.6	970.9	947.6	924.2	877.4	811.1	729.2	639.5
32.5°	1060.6	1060.6	1064.5	1072.3	1064.5	1045.0	1017.7	978.7	889.1	787.7	686.3
35°	1142.5	1142.5	1150.3	1162.0	1158.1	1138.6	1111.3	1068.4	974.8	854.0	737.0
37.5°	1232.2	1232.2	1240.0	1259.5	1251.7	1240.0	1220.5	1165.9	1060.6	920.3	791.6
40°	1329.7	1325.8	1333.6	1360.9	1364.8	1349.2	1325.8	1271.2	1150.3	1006.0	850.1
42.5°	1427.2	1423.3	1438.9	1466.2	1470.1	1466.2	1442.8	1380.4	1243.9	1091.8	908.6
45°	1524.7	1524.7	1548.1	1591.0	1610.4	1602.7	1583.2	1505.2	1360.9	1181.5	986.5
47.5°	1626.0	1626.0	1657.2	1711.8	1735.2	1731.3	1723.5	1629.9	1474.0	1275.1	1052.8
50°	1704.0	1704.0	1754.7	1817.1	1856.1	1871.7	1832.7	1746.9	1571.5	1357.0	1107.4
52.5°	1782.0	1782.0	1832.7	1930.2	1969.2	1992.6	1941.9	1852.2	1680.6	1431.1	1158.1
55°	1821.0	1828.8	1899.0	1992.6	2055.0	2043.3	2062.8	1941.9	1750.8	1485.7	1189.3
57.5°	1824.9	1836.6	1914.6	2012.1	2082.3	2078.4	2082.3	1973.1	1778.1	1497.4	1193.2
60°	1805.4	1824.9	1895.1	1992.6	2058.9	2090.1	2051.1	1953.6	1762.5	1485.7	1189.3
62.5°	1758.6	1797.6	1871.7	1945.8	2043.3	2055.0	2023.8	1941.9	1719.6	1474.0	1169.8
65°	1653.3	1696.2	1801.5	1887.3	1965.3	1980.9	1945.8	1875.6	1676.7	1419.4	1107.4
67.5°	1548.1	1575.4	1665.0	1797.6	1852.2	1867.8	1856.1	1774.2	1602.7	1310.2	1033.3
70°	1427.2	1462.3	1532.5	1668.9	1723.5	1719.6	1754.7	1661.1	1489.6	1216.6	955.4
72.5°	1263.4	1314.1	1384.3	1497.4	1563.7	1540.3	1594.9	1516.9	1341.4	1099.6	850.1
75°	1072.3	1115.2	1204.9	1294.6	1368.7	1341.4	1384.3	1329.7	1169.8	959.3	729.2
77.5°	857.9	908.6	990.4	1072.3	1123.0	1123.0	1142.5	1095.7	970.9	787.7	596.6
80°	635.6	682.4	756.5	815.0	861.8	865.7	885.2	861.8	748.7	612.2	456.2
82.5°	421.1	444.5	510.8	557.6	604.4	600.5	631.7	616.1	522.5	421.1	304.2
85°	179.4	195.0	249.6	288.6	331.4	315.9	358.7	354.8	280.8	202.8	136.5
87.5°	7.8	11.7	11.7	7.8	11.7	3.9	11.7	15.6	11.7	7.8	7.8
90°	2.5	2.5	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	2.5
92.5°	2.5	2.5	2.5	3.5	4.0	3.8	3.5	4.0	3.0	3.0	2.5
95°	3.0	3.0	3.5	4.5	5.6	5.8	6.1	6.1	3.5	3.5	3.0
97.5°	4.0	4.5	4.5	5.6	9.1	12.9	16.7	10.1	5.1	5.1	4.5
100°	6.6	7.1	7.1	12.6	26.8	31.4	35.9	25.8	13.1	9.6	7.1
102.5°	21.2	22.2	27.3	40.9	60.7	57.9	55.1	46.5	44.0	30.3	24.3
105°	54.1	53.6	57.6	68.2	84.9	84.2	83.4	76.8	69.8	60.2	55.6
107.5°	71.3	71.3	74.8	83.9	96.6	104.6	112.7	114.2	90.5	79.4	74.3
110°	80.4	80.4	83.4	91.0	107.7	119.0	130.4	129.4	111.7	98.1	91.5



REPORT NUMBER: P833677
 CATALOG NUMBER: TTN-D2-830-U-DL-UPL1

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	40°	45°	55°	65°	75°	85°
112.5°	82.4	82.9	86.9	98.6	116.8	121.8	126.9	122.3	115.3	109.2	104.1
115°	85.4	85.4	90.0	101.1	111.2	113.2	115.3	110.2	104.6	100.6	98.6
117.5°	84.4	85.9	86.9	93.0	99.6	101.1	102.6	100.1	92.5	89.5	88.5
120°	78.4	78.4	79.4	82.4	85.9	86.7	87.5	86.4	81.4	78.9	78.4
122.5°	69.8	70.3	69.8	71.3	73.8	74.6	75.3	74.3	70.3	69.3	69.3
125°	61.2	61.2	60.7	61.7	63.2	63.0	62.7	63.2	61.2	60.7	60.7
127.5°	55.1	54.6	53.6	54.1	54.6	54.6	54.6	55.1	53.1	53.6	54.1
130°	49.0	49.0	48.0	48.0	48.0	47.5	47.0	48.0	47.0	47.5	48.0
132.5°	43.5	43.5	42.0	41.5	41.5	41.5	41.5	42.0	41.5	42.5	43.5
135°	38.9	38.9	37.4	37.9	37.9	37.6	37.4	37.9	37.4	38.4	38.9
137.5°	35.4	35.4	34.4	34.4	34.4	34.2	33.9	34.4	34.4	34.9	35.9
140°	32.4	32.4	31.8	31.8	31.3	31.6	31.8	31.8	31.8	32.4	32.9
142.5°	30.8	30.3	29.8	29.3	29.8	29.8	29.8	29.8	29.3	29.8	30.8
145°	28.3	28.3	27.8	27.8	27.8	28.0	28.3	27.8	27.8	28.3	28.3
147.5°	26.8	26.8	26.3	26.8	26.8	26.8	26.8	26.8	26.3	26.8	26.8
150°	26.3	25.8	25.3	25.8	25.8	25.6	25.3	25.3	25.3	25.3	25.8
152.5°	24.8	24.8	24.3	24.8	24.3	24.3	24.3	24.3	24.3	24.3	24.8
155°	23.8	23.8	23.3	23.8	23.8	23.8	23.8	23.8	23.8	23.8	23.8
157.5°	22.7	23.3	22.7	22.7	22.7	22.7	22.7	22.7	22.7	22.7	23.3
160°	22.2	22.2	22.2	22.2	21.7	21.7	21.7	21.7	22.2	22.2	22.2
162.5°	21.7	21.7	21.7	21.7	21.2	21.2	21.2	21.2	21.2	21.7	21.7
165°	21.7	21.2	21.2	21.2	20.7	20.7	20.7	20.7	20.7	21.2	21.7
167.5°	20.7	20.7	20.7	20.7	20.7	20.4	20.2	20.2	20.7	20.7	20.7
170°	20.7	20.7	20.2	20.2	20.2	20.2	20.2	20.2	20.2	20.2	20.2
172.5°	20.7	20.7	20.7	20.7	20.2	20.2	20.2	20.2	20.2	20.2	20.7
175°	20.7	20.7	20.7	20.7	20.2	20.2	20.2	20.2	20.7	20.7	20.7
177.5°	20.7	20.7	20.7	20.7	20.2	20.4	20.7	20.7	20.7	20.7	20.7
180°	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7



REPORT NUMBER: P833677

CATALOG NUMBER: TTN-D2-830-U-DL-UPL1

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	378.2	378.2	378.2	378.2	378.2	378.2	378.2	378.2	378.2	378.2	378.2
2.5°	378.2	374.3	366.5	362.6	358.7	350.9	350.9	347.0	347.0	347.0	343.1
5°	378.2	370.4	362.6	350.9	343.1	335.3	327.5	319.8	315.9	315.9	312.0
7.5°	370.4	362.6	350.9	339.2	327.5	312.0	304.2	288.6	284.7	280.8	280.8
10°	370.4	362.6	343.1	327.5	312.0	296.4	284.7	269.1	257.4	253.5	253.5
12.5°	374.3	362.6	343.1	323.6	304.2	284.7	269.1	253.5	241.8	234.0	234.0
15°	389.9	374.3	350.9	323.6	300.3	276.9	261.3	241.8	230.1	222.3	222.3
17.5°	409.4	393.8	358.7	327.5	300.3	273.0	253.5	234.0	222.3	214.5	210.6
20°	436.7	413.3	374.3	331.4	300.3	273.0	249.6	230.1	214.5	206.7	206.7
22.5°	467.9	440.6	389.9	339.2	304.2	273.0	249.6	226.2	210.6	202.8	202.8
25°	506.9	471.8	413.3	354.8	312.0	276.9	249.6	226.2	210.6	202.8	202.8
27.5°	549.8	510.8	436.7	370.4	319.8	280.8	249.6	226.2	210.6	202.8	202.8
30°	588.8	545.9	460.1	386.0	331.4	284.7	253.5	230.1	214.5	206.7	202.8
32.5°	631.7	577.1	483.5	401.6	339.2	292.5	257.4	234.0	214.5	206.7	206.7
35°	674.6	616.1	506.9	421.1	350.9	300.3	261.3	237.9	218.4	210.6	210.6
37.5°	721.4	659.0	534.2	436.7	362.6	308.1	269.1	241.8	222.3	214.5	214.5
40°	776.0	701.9	561.5	456.2	374.3	315.9	273.0	249.6	230.1	222.3	222.3
42.5°	826.7	740.9	588.8	471.8	386.0	323.6	280.8	253.5	237.9	230.1	230.1
45°	877.4	787.7	616.1	491.3	397.7	335.3	288.6	265.2	245.7	237.9	237.9
47.5°	935.9	830.6	647.3	506.9	409.4	343.1	296.4	273.0	253.5	249.6	245.7
50°	982.6	861.8	666.8	522.5	417.2	350.9	304.2	276.9	261.3	253.5	253.5
52.5°	1025.5	893.0	682.4	530.3	421.1	354.8	312.0	284.7	269.1	261.3	261.3
55°	1048.9	904.7	694.1	530.3	425.0	358.7	312.0	284.7	269.1	265.2	261.3
57.5°	1048.9	904.7	686.3	522.5	417.2	350.9	308.1	280.8	269.1	261.3	261.3
60°	1033.3	893.0	666.8	506.9	405.5	339.2	300.3	273.0	261.3	257.4	257.4
62.5°	1009.9	873.5	651.2	487.4	389.9	323.6	288.6	261.3	253.5	253.5	249.6
65°	947.6	815.0	616.1	460.1	366.5	304.2	273.0	249.6	241.8	237.9	234.0
67.5°	881.3	760.4	561.5	428.9	335.3	284.7	253.5	234.0	222.3	222.3	218.4
70°	815.0	701.9	510.8	386.0	300.3	261.3	230.1	210.6	202.8	202.8	202.8
72.5°	725.3	627.8	452.3	339.2	265.2	230.1	206.7	187.2	183.3	183.3	179.4
75°	620.0	534.2	382.1	288.6	222.3	195.0	175.5	156.0	156.0	156.0	156.0
77.5°	506.9	432.8	304.2	230.1	175.5	156.0	144.3	128.7	128.7	128.7	128.7
80°	382.1	319.8	222.3	167.7	128.7	113.1	105.3	97.5	101.4	101.4	97.5
82.5°	249.6	210.6	140.4	105.3	81.9	74.1	74.1	66.3	70.2	70.2	70.2
85°	109.2	93.6	58.5	46.8	39.0	39.0	39.0	35.1	39.0	39.0	39.0
87.5°	7.8	7.8	7.8	7.8	7.8	7.8	7.8	0.0	3.9	7.8	3.9
90°	2.5	2.5	3.0	3.0	3.0	3.0	3.0	3.0	3.0	2.5	2.5
92.5°	2.5	2.5	3.0	3.0	4.0	3.5	4.0	3.5	2.5	2.5	2.5
95°	3.0	3.0	3.5	3.5	6.1	6.1	5.6	4.5	3.5	3.0	3.0
97.5°	4.0	4.5	5.1	5.1	10.1	16.7	9.1	5.6	4.5	4.5	4.0
100°	7.1	7.1	9.6	13.1	25.8	35.9	26.8	12.6	7.1	7.1	6.6
102.5°	23.3	24.3	30.3	44.0	46.5	55.1	60.7	40.9	27.3	22.2	21.2
105°	55.6	55.6	60.2	69.8	76.8	83.4	84.9	68.2	57.6	53.6	54.1
107.5°	73.8	74.3	79.4	90.5	114.2	112.7	96.6	83.9	74.8	71.3	71.3
110°	90.5	91.5	98.1	111.7	129.4	130.4	107.7	91.0	83.4	80.4	80.4



REPORT NUMBER: P833677
 CATALOG NUMBER: TTN-D2-830-U-DL-UPL1

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
112.5°	103.1	104.1	109.2	115.3	122.3	126.9	116.8	98.6	86.9	82.9	82.4
115°	99.6	98.6	100.6	104.6	110.2	115.3	111.2	101.1	90.0	85.4	85.4
117.5°	86.9	88.5	89.5	92.5	100.1	102.6	99.6	93.0	86.9	85.9	84.4
120°	77.3	78.4	78.9	81.4	86.4	87.5	85.9	82.4	79.4	78.4	78.4
122.5°	68.2	69.3	69.3	70.3	74.3	75.3	73.8	71.3	69.8	70.3	69.8
125°	60.2	60.7	60.7	61.2	63.2	62.7	63.2	61.7	60.7	61.2	61.2
127.5°	53.6	54.1	53.6	53.1	55.1	54.6	54.6	54.1	53.6	54.6	55.1
130°	48.5	48.0	47.5	47.0	48.0	47.0	48.0	48.0	48.0	49.0	49.0
132.5°	43.5	43.5	42.5	41.5	42.0	41.5	41.5	41.5	42.0	43.5	43.5
135°	38.9	38.9	38.4	37.4	37.9	37.4	37.9	37.9	37.4	38.9	38.9
137.5°	36.4	35.9	34.9	34.4	34.4	33.9	34.4	34.4	34.4	35.4	35.4
140°	32.9	32.9	32.4	31.8	31.8	31.8	31.3	31.8	31.8	32.4	32.4
142.5°	30.8	30.8	29.8	29.3	29.8	29.8	29.8	29.3	29.8	30.3	30.8
145°	28.8	28.3	28.3	27.8	27.8	28.3	27.8	27.8	27.8	28.3	28.3
147.5°	27.3	26.8	26.8	26.3	26.8	26.8	26.8	26.8	26.3	26.8	26.8
150°	25.8	25.8	25.3	25.3	25.3	25.3	25.8	25.8	25.3	25.8	26.3
152.5°	25.3	24.8	24.3	24.3	24.3	24.3	24.3	24.8	24.3	24.8	24.8
155°	23.8	23.8	23.8	23.8	23.8	23.8	23.8	23.8	23.3	23.8	23.8
157.5°	23.3	23.3	22.7	22.7	22.7	22.7	22.7	22.7	22.7	23.3	22.7
160°	22.7	22.2	22.2	22.2	21.7	21.7	21.7	22.2	22.2	22.2	22.2
162.5°	22.2	21.7	21.7	21.2	21.2	21.2	21.2	21.7	21.7	21.7	21.7
165°	21.2	21.7	21.2	20.7	20.7	20.7	20.7	21.2	21.2	21.2	21.7
167.5°	21.2	20.7	20.7	20.7	20.2	20.2	20.7	20.7	20.7	20.7	20.7
170°	20.7	20.2	20.2	20.2	20.2	20.2	20.2	20.2	20.2	20.7	20.7
172.5°	20.7	20.7	20.2	20.2	20.2	20.2	20.2	20.7	20.7	20.7	20.7
175°	20.2	20.7	20.7	20.7	20.2	20.2	20.2	20.7	20.7	20.7	20.7
177.5°	20.7	20.7	20.7	20.7	20.7	20.7	20.2	20.7	20.7	20.7	20.7
180°	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7

(END OF REPORT)