

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P833679

Luminaire Tested: **TTN-D2-830-U-DL-UPL3**

Issue Date: 5/15/2024

Test Information

Test Method: LM-79-08
Report Number: P833679
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G3-2308-121-4) AND
Test Lab: INNOVATION CENTER
Issue Date: 5/15/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: TTN-D2-830-U-DL-UPL3
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE WITH UPLIGHT
3000K, 80 CRI LEDS AND DRIVE LANE DISTRIBUTION
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5232.7 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Luminous Opening: Vertical Cylinder (Dia: 0.71' x H: 0.1')
IES Classification: Type IV - Short
BUG Rating: B1 - U4 - G2


Input Watts (W): 49.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P833679
 CATALOG NUMBER: TTN-D2-830-U-DL-UPL3

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1 fc
 Type IV - Short - N/A

REPORT NUMBER: P833679
CATALOG NUMBER: TTN-D2-830-U-DL-UPL3

Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P833679
 CATALOG NUMBER: TTN-D2-830-U-DL-UPL3


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	956.9	370.3	1327.2
	% Fixture	18.3	7.1	25.4
Street Side	Lumens	3535.1	370.3	3905.5
	% Fixture	67.6	7.1	74.6
Total	Lumens	4492.0	740.7	5232.7
	% Fixture	85.8	14.2	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.7	0.7
10°-20°	113.8	2.2
20°-30°	240.5	4.6
30°-40°	439.5	8.4
40°-50°	714.2	13.6
50°-60°	992.7	19.0
60°-70°	1029.1	19.7
70°-80°	737.4	14.1
80°-90°	189.0	3.6
90°-100°	16.5	0.3
100°-110°	168.0	3.2
110°-120°	245.6	4.7
120°-130°	142.5	2.7
130°-140°	75.5	1.4
140°-150°	44.9	0.9
150°-160°	27.6	0.5
160°-170°	15.1	0.3
170°-180°	4.9	0.1
0°-90°	4492.0	85.8
0°-180°	5232.7	100.0

Coefficient of Utilization



REPORT NUMBER: P833679


CATALOG NUMBER: TTN-D2-830-U-DL-UPL3

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	262.8	5.0			
FM (30°-60°)	1676.9	32.0			
FH (60°-80°)	1438.3	27.5			G1/1800
FVH (80°-90°)	157.1	3.0			G2/225
BL (0°-30°)	127.2	2.4	B1/500		
BM (30°-60°)	469.5	9.0	B1/1000		
BH (60°-80°)	328.3	6.3	B1/500		G1/500
BVH (80°-90°)	31.9	0.6			G1/100
UL (90°-100°)	16.5	0.3		U2/50	
UH (100°-180°)	724.2	13.8		U4/1000	

BUG Rating: B1-U4-G2

Type IV Short





REPORT NUMBER: P833679

CATALOG NUMBER: TTN-D2-830-U-DL-UPL3

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	40°	45°	55°	65°	75°	85°
0°	378.2	378.2	378.2	378.2	378.2	378.2	378.2	378.2	378.2	378.2	378.2
2.5°	405.5	405.5	405.5	405.5	401.6	401.6	397.7	393.8	389.9	386.0	378.2
5°	440.6	440.6	436.7	432.8	425.0	421.1	417.2	409.4	401.6	393.8	382.1
7.5°	456.2	456.2	456.2	452.3	440.6	436.7	428.9	417.2	405.5	393.8	378.2
10°	483.5	483.5	479.6	475.7	464.0	460.1	452.3	436.7	417.2	397.7	378.2
12.5°	518.6	514.7	510.8	506.9	495.2	487.4	475.7	460.1	436.7	413.3	389.9
15°	561.5	553.7	553.7	545.9	534.2	522.5	514.7	491.3	467.9	436.7	405.5
17.5°	608.3	604.4	600.5	592.7	581.0	573.2	561.5	534.2	503.0	464.0	428.9
20°	666.8	659.0	662.9	651.2	639.5	635.6	616.1	584.9	545.9	503.0	460.1
22.5°	737.0	729.2	729.2	717.5	709.7	701.9	682.4	647.3	596.6	549.8	495.2
25°	815.0	807.2	807.2	799.4	791.6	783.8	760.4	721.4	662.9	604.4	542.0
27.5°	900.8	893.0	893.0	889.1	869.6	857.9	838.4	795.5	737.0	662.9	588.8
30°	990.4	982.6	990.4	982.6	970.9	947.6	924.2	877.4	811.1	729.2	639.5
32.5°	1060.6	1060.6	1064.5	1072.3	1064.5	1045.0	1017.7	978.7	889.1	787.7	686.3
35°	1142.5	1142.5	1150.3	1162.0	1158.1	1138.6	1111.3	1068.4	974.8	854.0	737.0
37.5°	1232.2	1232.2	1240.0	1259.5	1251.7	1240.0	1220.5	1165.9	1060.6	920.3	791.6
40°	1329.7	1325.8	1333.6	1360.9	1364.8	1349.2	1325.8	1271.2	1150.3	1006.0	850.1
42.5°	1427.2	1423.3	1438.9	1466.2	1470.1	1466.2	1442.8	1380.4	1243.9	1091.8	908.6
45°	1524.7	1524.7	1548.1	1591.0	1610.4	1602.7	1583.2	1505.2	1360.9	1181.5	986.5
47.5°	1626.0	1626.0	1657.2	1711.8	1735.2	1731.3	1723.5	1629.9	1474.0	1275.1	1052.8
50°	1704.0	1704.0	1754.7	1817.1	1856.1	1871.7	1832.7	1746.9	1571.5	1357.0	1107.4
52.5°	1782.0	1782.0	1832.7	1930.2	1969.2	1992.6	1941.9	1852.2	1680.6	1431.1	1158.1
55°	1821.0	1828.8	1899.0	1992.6	2055.0	2043.3	2062.8	1941.9	1750.8	1485.7	1189.3
57.5°	1824.9	1836.6	1914.6	2012.1	2082.3	2078.4	2082.3	1973.1	1778.1	1497.4	1193.2
60°	1805.4	1824.9	1895.1	1992.6	2058.9	2090.1	2051.1	1953.6	1762.5	1485.7	1189.3
62.5°	1758.6	1797.6	1871.7	1945.8	2043.3	2055.0	2023.8	1941.9	1719.6	1474.0	1169.8
65°	1653.3	1696.2	1801.5	1887.3	1965.3	1980.9	1945.8	1875.6	1676.7	1419.4	1107.4
67.5°	1548.1	1575.4	1665.0	1797.6	1852.2	1867.8	1856.1	1774.2	1602.7	1310.2	1033.3
70°	1427.2	1462.3	1532.5	1668.9	1723.5	1719.6	1754.7	1661.1	1489.6	1216.6	955.4
72.5°	1263.4	1314.1	1384.3	1497.4	1563.7	1540.3	1594.9	1516.9	1341.4	1099.6	850.1
75°	1072.3	1115.2	1204.9	1294.6	1368.7	1341.4	1384.3	1329.7	1169.8	959.3	729.2
77.5°	857.9	908.6	990.4	1072.3	1123.0	1123.0	1142.5	1095.7	970.9	787.7	596.6
80°	635.6	682.4	756.5	815.0	861.8	865.7	885.2	861.8	748.7	612.2	456.2
82.5°	421.1	444.5	510.8	557.6	604.4	600.5	631.7	616.1	522.5	421.1	304.2
85°	179.4	195.0	249.6	288.6	331.4	315.9	358.7	354.8	280.8	202.8	136.5
87.5°	7.8	11.7	11.7	7.8	11.7	3.9	11.7	15.6	11.7	7.8	7.8
90°	6.3	6.3	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	6.3
92.5°	6.3	6.3	6.3	8.9	10.1	9.5	8.9	10.1	7.6	7.6	6.3
95°	7.6	7.6	8.9	11.4	13.9	14.6	15.2	15.2	8.9	8.9	7.6
97.5°	10.1	11.4	11.4	13.9	22.8	32.3	41.8	25.3	12.7	12.7	11.4
100°	16.5	17.7	17.7	31.7	67.2	78.6	90.0	64.6	32.9	24.1	17.7
102.5°	53.2	55.8	68.4	102.6	152.1	145.1	138.1	116.6	110.2	76.0	60.8
105°	135.6	134.3	144.5	171.1	212.9	211.0	209.1	192.6	174.9	150.8	139.4
107.5°	178.7	178.7	187.5	210.4	242.0	262.3	282.6	286.4	226.8	198.9	186.3
110°	201.5	201.5	209.1	228.1	269.9	298.4	326.9	324.4	280.0	245.8	229.4



REPORT NUMBER: P833679
 CATALOG NUMBER: TTN-D2-830-U-DL-UPL3

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	40°	45°	55°	65°	75°	85°
112.5°	206.5	207.8	218.0	247.1	292.7	305.4	318.1	306.7	288.9	273.7	261.0
115°	214.2	214.2	225.6	253.4	278.8	283.8	288.9	276.2	262.3	252.2	247.1
117.5°	211.6	215.4	218.0	233.2	249.6	253.4	257.2	250.9	231.9	224.3	221.8
120°	196.4	196.4	198.9	206.5	215.4	217.3	219.2	216.7	204.0	197.7	196.4
122.5°	174.9	176.1	174.9	178.7	185.0	186.9	188.8	186.3	176.1	173.6	173.6
125°	153.3	153.3	152.1	154.6	158.4	157.8	157.1	158.4	153.3	152.1	152.1
127.5°	138.1	136.9	134.3	135.6	136.9	136.9	136.9	138.1	133.1	134.3	135.6
130°	122.9	122.9	120.4	120.4	120.4	119.1	117.8	120.4	117.8	119.1	120.4
132.5°	109.0	109.0	105.2	103.9	103.9	103.9	103.9	105.2	103.9	106.4	109.0
135°	97.6	97.6	93.8	95.0	95.0	94.4	93.8	95.0	93.8	96.3	97.6
137.5°	88.7	88.7	86.2	86.2	86.2	85.6	84.9	86.2	86.2	87.4	90.0
140°	81.1	81.1	79.8	79.8	78.6	79.2	79.8	79.8	79.8	81.1	82.4
142.5°	77.3	76.0	74.8	73.5	74.8	74.8	74.8	74.8	73.5	74.8	77.3
145°	71.0	71.0	69.7	69.7	69.7	70.4	71.0	69.7	69.7	71.0	71.0
147.5°	67.2	67.2	65.9	67.2	67.2	67.2	67.2	67.2	65.9	67.2	67.2
150°	65.9	64.6	63.4	64.6	64.6	64.0	63.4	63.4	63.4	63.4	64.6
152.5°	62.1	62.1	60.8	62.1	60.8	60.8	60.8	60.8	60.8	60.8	62.1
155°	59.6	59.6	58.3	59.6	59.6	59.6	59.6	59.6	59.6	59.6	59.6
157.5°	57.0	58.3	57.0	57.0	57.0	57.0	57.0	57.0	57.0	57.0	58.3
160°	55.8	55.8	55.8	55.8	54.5	54.5	54.5	54.5	55.8	55.8	55.8
162.5°	54.5	54.5	54.5	54.5	53.2	53.2	53.2	53.2	53.2	54.5	54.5
165°	54.5	53.2	53.2	53.2	52.0	52.0	52.0	52.0	52.0	53.2	54.5
167.5°	52.0	52.0	52.0	52.0	52.0	51.4	50.7	50.7	52.0	52.0	52.0
170°	52.0	52.0	50.7	50.7	50.7	50.7	50.7	50.7	50.7	50.7	50.7
172.5°	52.0	52.0	52.0	52.0	50.7	50.7	50.7	50.7	50.7	50.7	52.0
175°	52.0	52.0	52.0	52.0	50.7	50.7	50.7	50.7	52.0	52.0	52.0
177.5°	52.0	52.0	52.0	52.0	50.7	51.4	52.0	52.0	52.0	52.0	52.0
180°	52.0	52.0	52.0	52.0	52.0	52.0	52.0	52.0	52.0	52.0	52.0



REPORT NUMBER: P833679

CATALOG NUMBER: TTN-D2-830-U-DL-UPL3

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	378.2	378.2	378.2	378.2	378.2	378.2	378.2	378.2	378.2	378.2	378.2
2.5°	378.2	374.3	366.5	362.6	358.7	350.9	350.9	347.0	347.0	347.0	343.1
5°	378.2	370.4	362.6	350.9	343.1	335.3	327.5	319.8	315.9	315.9	312.0
7.5°	370.4	362.6	350.9	339.2	327.5	312.0	304.2	288.6	284.7	280.8	280.8
10°	370.4	362.6	343.1	327.5	312.0	296.4	284.7	269.1	257.4	253.5	253.5
12.5°	374.3	362.6	343.1	323.6	304.2	284.7	269.1	253.5	241.8	234.0	234.0
15°	389.9	374.3	350.9	323.6	300.3	276.9	261.3	241.8	230.1	222.3	222.3
17.5°	409.4	393.8	358.7	327.5	300.3	273.0	253.5	234.0	222.3	214.5	210.6
20°	436.7	413.3	374.3	331.4	300.3	273.0	249.6	230.1	214.5	206.7	206.7
22.5°	467.9	440.6	389.9	339.2	304.2	273.0	249.6	226.2	210.6	202.8	202.8
25°	506.9	471.8	413.3	354.8	312.0	276.9	249.6	226.2	210.6	202.8	202.8
27.5°	549.8	510.8	436.7	370.4	319.8	280.8	249.6	226.2	210.6	202.8	202.8
30°	588.8	545.9	460.1	386.0	331.4	284.7	253.5	230.1	214.5	206.7	202.8
32.5°	631.7	577.1	483.5	401.6	339.2	292.5	257.4	234.0	214.5	206.7	206.7
35°	674.6	616.1	506.9	421.1	350.9	300.3	261.3	237.9	218.4	210.6	210.6
37.5°	721.4	659.0	534.2	436.7	362.6	308.1	269.1	241.8	222.3	214.5	214.5
40°	776.0	701.9	561.5	456.2	374.3	315.9	273.0	249.6	230.1	222.3	222.3
42.5°	826.7	740.9	588.8	471.8	386.0	323.6	280.8	253.5	237.9	230.1	230.1
45°	877.4	787.7	616.1	491.3	397.7	335.3	288.6	265.2	245.7	237.9	237.9
47.5°	935.9	830.6	647.3	506.9	409.4	343.1	296.4	273.0	253.5	249.6	245.7
50°	982.6	861.8	666.8	522.5	417.2	350.9	304.2	276.9	261.3	253.5	253.5
52.5°	1025.5	893.0	682.4	530.3	421.1	354.8	312.0	284.7	269.1	261.3	261.3
55°	1048.9	904.7	694.1	530.3	425.0	358.7	312.0	284.7	269.1	265.2	261.3
57.5°	1048.9	904.7	686.3	522.5	417.2	350.9	308.1	280.8	269.1	261.3	261.3
60°	1033.3	893.0	666.8	506.9	405.5	339.2	300.3	273.0	261.3	257.4	257.4
62.5°	1009.9	873.5	651.2	487.4	389.9	323.6	288.6	261.3	253.5	253.5	249.6
65°	947.6	815.0	616.1	460.1	366.5	304.2	273.0	249.6	241.8	237.9	234.0
67.5°	881.3	760.4	561.5	428.9	335.3	284.7	253.5	234.0	222.3	222.3	218.4
70°	815.0	701.9	510.8	386.0	300.3	261.3	230.1	210.6	202.8	202.8	202.8
72.5°	725.3	627.8	452.3	339.2	265.2	230.1	206.7	187.2	183.3	183.3	179.4
75°	620.0	534.2	382.1	288.6	222.3	195.0	175.5	156.0	156.0	156.0	156.0
77.5°	506.9	432.8	304.2	230.1	175.5	156.0	144.3	128.7	128.7	128.7	128.7
80°	382.1	319.8	222.3	167.7	128.7	113.1	105.3	97.5	101.4	101.4	97.5
82.5°	249.6	210.6	140.4	105.3	81.9	74.1	74.1	66.3	70.2	70.2	70.2
85°	109.2	93.6	58.5	46.8	39.0	39.0	39.0	35.1	39.0	39.0	39.0
87.5°	7.8	7.8	7.8	7.8	7.8	7.8	7.8	0.0	3.9	7.8	3.9
90°	6.3	6.3	7.6	7.6	7.6	7.6	7.6	7.6	7.6	6.3	6.3
92.5°	6.3	6.3	7.6	7.6	10.1	8.9	10.1	8.9	6.3	6.3	6.3
95°	7.6	7.6	8.9	8.9	15.2	15.2	13.9	11.4	8.9	7.6	7.6
97.5°	10.1	11.4	12.7	12.7	25.3	41.8	22.8	13.9	11.4	11.4	10.1
100°	17.7	17.7	24.1	32.9	64.6	90.0	67.2	31.7	17.7	17.7	16.5
102.5°	58.3	60.8	76.0	110.2	116.6	138.1	152.1	102.6	68.4	55.8	53.2
105°	139.4	139.4	150.8	174.9	192.6	209.1	212.9	171.1	144.5	134.3	135.6
107.5°	185.0	186.3	198.9	226.8	286.4	282.6	242.0	210.4	187.5	178.7	178.7
110°	226.8	229.4	245.8	280.0	324.4	326.9	269.9	228.1	209.1	201.5	201.5



REPORT NUMBER: P833679
 CATALOG NUMBER: TTN-D2-830-U-DL-UPL3

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
112.5°	258.5	261.0	273.7	288.9	306.7	318.1	292.7	247.1	218.0	207.8	206.5
115°	249.6	247.1	252.2	262.3	276.2	288.9	278.8	253.4	225.6	214.2	214.2
117.5°	218.0	221.8	224.3	231.9	250.9	257.2	249.6	233.2	218.0	215.4	211.6
120°	193.9	196.4	197.7	204.0	216.7	219.2	215.4	206.5	198.9	196.4	196.4
122.5°	171.1	173.6	173.6	176.1	186.3	188.8	185.0	178.7	174.9	176.1	174.9
125°	150.8	152.1	152.1	153.3	158.4	157.1	158.4	154.6	152.1	153.3	153.3
127.5°	134.3	135.6	134.3	133.1	138.1	136.9	136.9	135.6	134.3	136.9	138.1
130°	121.6	120.4	119.1	117.8	120.4	117.8	120.4	120.4	120.4	122.9	122.9
132.5°	109.0	109.0	106.4	103.9	105.2	103.9	103.9	103.9	105.2	109.0	109.0
135°	97.6	97.6	96.3	93.8	95.0	93.8	95.0	95.0	93.8	97.6	97.6
137.5°	91.2	90.0	87.4	86.2	86.2	84.9	86.2	86.2	86.2	88.7	88.7
140°	82.4	82.4	81.1	79.8	79.8	79.8	78.6	79.8	79.8	81.1	81.1
142.5°	77.3	77.3	74.8	73.5	74.8	74.8	74.8	73.5	74.8	76.0	77.3
145°	72.2	71.0	71.0	69.7	69.7	71.0	69.7	69.7	69.7	71.0	71.0
147.5°	68.4	67.2	67.2	65.9	67.2	67.2	67.2	67.2	65.9	67.2	67.2
150°	64.6	64.6	63.4	63.4	63.4	63.4	64.6	64.6	63.4	64.6	65.9
152.5°	63.4	62.1	60.8	60.8	60.8	60.8	60.8	62.1	60.8	62.1	62.1
155°	59.6	59.6	59.6	59.6	59.6	59.6	59.6	59.6	58.3	59.6	59.6
157.5°	58.3	58.3	57.0	57.0	57.0	57.0	57.0	57.0	57.0	58.3	57.0
160°	57.0	55.8	55.8	55.8	54.5	54.5	54.5	55.8	55.8	55.8	55.8
162.5°	55.8	54.5	54.5	53.2	53.2	53.2	53.2	54.5	54.5	54.5	54.5
165°	53.2	54.5	53.2	52.0	52.0	52.0	52.0	53.2	53.2	53.2	54.5
167.5°	53.2	52.0	52.0	52.0	50.7	50.7	52.0	52.0	52.0	52.0	52.0
170°	52.0	50.7	50.7	50.7	50.7	50.7	50.7	50.7	50.7	52.0	52.0
172.5°	52.0	52.0	50.7	50.7	50.7	50.7	50.7	52.0	52.0	52.0	52.0
175°	50.7	52.0	52.0	52.0	50.7	50.7	50.7	52.0	52.0	52.0	52.0
177.5°	52.0	52.0	52.0	52.0	52.0	52.0	50.7	52.0	52.0	52.0	52.0
180°	52.0	52.0	52.0	52.0	52.0	52.0	52.0	52.0	52.0	52.0	52.0

(END OF REPORT)