

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P833171

Luminaire Tested: **TTN-D1-735-U-MQ-CG-UPL2**

Issue Date: 5/15/2024

**Test Information**

Test Method: LM-79-08  
Report Number: P833171  
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G3-2308-121-4) AND  
Test Lab: INNOVATION CENTER  
Issue Date: 5/15/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: TTN-D1-735-U-MQ-CG-UPL2  
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE WITH UPLIGHT  
3500K, 70 CRI LEDS AND MEDIUM DISTRIBUTION WITH CLEAR GLASS  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3774.8 lumens  
Efficiency: N/A  
Efficacy: 122.2 lumens/watt  
Luminous Opening: Vertical Cylinder (Dia: 0.71' x H: 0.1')  
IES Classification: Type V - Short  
BUG Rating: B1 - U4 - G1  
  
Input Watts (W): 30.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P833171  
 CATALOG NUMBER: TTN-D1-735-U-MQ-CG-UPL2

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1.2 fc  
 Type V - Short - N/A

REPORT NUMBER: P833171  
CATALOG NUMBER: TTN-D1-735-U-MQ-CG-UPL2

### Luminous Intensity Polar Plot



REPORT NUMBER: P833171  
 CATALOG NUMBER: TTN-D1-735-U-MQ-CG-UPL2


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1615.9	271.5	1887.4
	% Fixture	42.8	7.2	50.0
<b>Street Side</b>	Lumens	1615.9	271.5	1887.4
	% Fixture	42.8	7.2	50.0
<b>Total</b>	Lumens	3231.7	543.0	3774.8
	% Fixture	85.6	14.4	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.2	1.9
10°-20°	208.8	5.5
20°-30°	335.9	8.9
30°-40°	448.8	11.9
40°-50°	545.2	14.4
50°-60°	633.5	16.8
60°-70°	584.5	15.5
70°-80°	342.1	9.1
80°-90°	60.7	1.6
90°-100°	12.1	0.3
100°-110°	123.2	3.3
110°-120°	180.1	4.8
120°-130°	104.5	2.8
130°-140°	55.4	1.5
140°-150°	32.9	0.9
150°-160°	20.2	0.5
160°-170°	11.0	0.3
170°-180°	3.6	0.1
0°-90°	3231.7	85.6
0°-180°	3774.8	100.0




REPORT NUMBER: P833171  
 CATALOG NUMBER: TTN-D1-735-U-MQ-CG-UPL2

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	308.5	8.2			
FM (30°-60°)	813.7	21.6			
FH (60°-80°)	463.3	12.3			G0/660
FVH (80°-90°)	30.3	0.8			G1/100
BL (0°-30°)	308.5	8.2	B1/500		
BM (30°-60°)	813.7	21.6	B1/1000		
BH (60°-80°)	463.3	12.3	B1/500		G0/660
BVH (80°-90°)	30.3	0.8			G1/100
UL (90°-100°)	12.1	0.3		U2/50	
UH (100°-180°)	530.9	14.1		U4/1000	

**BUG Rating: B1-U4-G1**  
 Type V Short





REPORT NUMBER: P833171

CATALOG NUMBER: TTN-D1-735-U-MQ-CG-UPL2

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	768.6	768.6	768.6	768.6	768.6	768.6	768.6	768.6	768.6	768.6	768.6
2.5°	760.8	763.4	760.8	760.8	760.8	760.8	760.8	760.8	760.8	760.8	763.4
5°	763.4	763.4	763.4	763.4	760.8	760.8	760.8	760.8	760.8	763.4	763.4
7.5°	755.5	755.5	755.5	755.5	755.5	752.9	755.5	755.5	755.5	755.5	755.5
10°	747.7	747.7	747.7	747.7	747.7	747.7	747.7	747.7	747.7	747.7	747.7
12.5°	742.4	742.4	742.4	742.4	742.4	742.4	742.4	742.4	742.4	739.8	739.8
15°	737.2	737.2	737.2	737.2	739.8	739.8	737.2	737.2	737.2	737.2	737.2
17.5°	731.9	731.9	731.9	731.9	734.5	734.5	734.5	731.9	731.9	731.9	731.9
20°	726.7	726.7	726.7	726.7	729.3	729.3	729.3	729.3	729.3	726.7	726.7
22.5°	724.1	724.1	724.1	724.1	726.7	726.7	726.7	726.7	724.1	724.1	724.1
25°	721.4	724.1	724.1	724.1	726.7	729.3	729.3	726.7	724.1	721.4	721.4
27.5°	724.1	724.1	724.1	726.7	726.7	729.3	729.3	726.7	724.1	724.1	724.1
30°	721.4	721.4	721.4	724.1	726.7	729.3	726.7	726.7	724.1	721.4	721.4
32.5°	716.2	716.2	718.8	721.4	724.1	724.1	724.1	721.4	718.8	716.2	716.2
35°	710.9	710.9	710.9	713.6	718.8	718.8	718.8	716.2	713.6	710.9	708.3
37.5°	703.1	705.7	705.7	710.9	713.6	716.2	713.6	710.9	705.7	703.1	703.1
40°	697.8	697.8	700.4	705.7	710.9	710.9	708.3	705.7	700.4	697.8	697.8
42.5°	689.9	689.9	695.2	700.4	708.3	708.3	705.7	700.4	695.2	689.9	689.9
45°	689.9	689.9	695.2	705.7	710.9	716.2	710.9	705.7	695.2	689.9	687.3
47.5°	692.6	692.6	697.8	710.9	721.4	726.7	718.8	708.3	697.8	692.6	689.9
50°	687.3	689.9	700.4	713.6	726.7	729.3	726.7	710.9	700.4	687.3	687.3
52.5°	689.9	689.9	703.1	724.1	737.2	742.4	737.2	724.1	700.4	687.3	687.3
55°	684.7	682.1	700.4	724.1	745.0	755.5	745.0	724.1	697.8	682.1	679.5
57.5°	661.1	661.1	684.7	708.3	734.5	739.8	731.9	708.3	682.1	661.1	655.8
60°	629.6	632.2	655.8	682.1	705.7	708.3	703.1	682.1	655.8	632.2	624.4
62.5°	595.5	600.8	624.4	650.6	679.5	684.7	676.8	650.6	619.1	603.4	590.3
65°	545.7	553.5	579.8	608.6	640.1	637.5	637.5	606.0	582.4	556.2	543.0
67.5°	490.6	498.4	516.8	556.2	582.4	579.8	577.1	556.2	516.8	498.4	490.6
70°	430.2	435.5	453.8	493.2	516.8	519.4	511.6	490.6	453.8	440.7	427.6
72.5°	359.4	362.0	388.3	419.7	443.4	440.7	438.1	419.7	385.6	372.5	356.8
75°	283.3	285.9	309.6	338.4	356.8	354.2	351.5	338.4	309.6	293.8	280.7
77.5°	212.5	209.9	233.5	254.5	265.0	267.6	262.3	251.8	230.9	217.7	209.9
80°	139.0	136.4	157.4	173.1	181.0	181.0	178.4	170.5	154.8	144.3	139.0
82.5°	78.7	76.1	89.2	99.7	107.6	104.9	102.3	97.1	89.2	81.3	76.1
85°	28.9	28.9	36.7	42.0	47.2	47.2	44.6	42.0	34.1	31.5	28.9
87.5°	2.6	2.6	5.2	7.9	7.9	7.9	5.2	5.2	2.6	2.6	2.6
90°	4.6	4.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	4.6	4.6
92.5°	4.6	4.6	4.6	6.5	7.4	6.5	7.4	5.6	5.6	4.6	4.6
95°	5.6	5.6	6.5	8.4	10.2	11.1	11.1	6.5	6.5	5.6	5.6
97.5°	7.4	8.4	8.4	10.2	16.7	30.7	18.6	9.3	9.3	8.4	7.4
100°	12.1	13.0	13.0	23.2	49.2	66.0	47.4	24.2	17.7	13.0	13.0
102.5°	39.0	40.9	50.2	75.3	111.5	101.3	85.5	80.8	55.7	44.6	42.7
105°	99.4	98.5	105.9	125.4	156.1	153.3	141.2	128.2	110.6	102.2	102.2
107.5°	131.0	131.0	137.5	154.2	177.4	207.2	210.0	166.3	145.9	136.6	135.6
110°	147.7	147.7	153.3	167.2	197.9	239.7	237.8	205.3	180.2	168.2	166.3



REPORT NUMBER: P833171  
 CATALOG NUMBER: TTN-D1-735-U-MQ-CG-UPL2

**CANDELA DISTRIBUTION (continued):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	151.4	152.4	159.8	181.2	214.6	233.2	224.8	211.8	200.7	191.4	189.5
115°	157.0	157.0	165.4	185.8	204.4	211.8	202.5	192.3	184.9	181.2	183.0
117.5°	155.1	157.9	159.8	170.9	183.0	188.6	183.9	170.0	164.4	162.6	159.8
120°	144.0	144.0	145.9	151.4	157.9	160.7	158.9	149.6	144.9	144.0	142.1
122.5°	128.2	129.1	128.2	131.0	135.6	138.4	136.6	129.1	127.3	127.3	125.4
125°	112.4	112.4	111.5	113.3	116.1	115.2	116.1	112.4	111.5	111.5	110.6
127.5°	101.3	100.3	98.5	99.4	100.3	100.3	101.3	97.5	98.5	99.4	98.5
130°	90.1	90.1	88.3	88.3	88.3	86.4	88.3	86.4	87.3	88.3	89.2
132.5°	79.9	79.9	77.1	76.2	76.2	76.2	77.1	76.2	78.0	79.9	79.9
135°	71.5	71.5	68.7	69.7	69.7	68.7	69.7	68.7	70.6	71.5	71.5
137.5°	65.0	65.0	63.2	63.2	63.2	62.2	63.2	63.2	64.1	66.0	66.9
140°	59.5	59.5	58.5	58.5	57.6	58.5	58.5	58.5	59.5	60.4	60.4
142.5°	56.7	55.7	54.8	53.9	54.8	54.8	54.8	53.9	54.8	56.7	56.7
145°	52.0	52.0	51.1	51.1	51.1	52.0	51.1	51.1	52.0	52.0	53.0
147.5°	49.2	49.2	48.3	49.2	49.2	49.2	49.2	48.3	49.2	49.2	50.2
150°	48.3	47.4	46.5	47.4	47.4	46.5	46.5	46.5	46.5	47.4	47.4
152.5°	45.5	45.5	44.6	45.5	44.6	44.6	44.6	44.6	44.6	45.5	46.5
155°	43.7	43.7	42.7	43.7	43.7	43.7	43.7	43.7	43.7	43.7	43.7
157.5°	41.8	42.7	41.8	41.8	41.8	41.8	41.8	41.8	41.8	42.7	42.7
160°	40.9	40.9	40.9	40.9	39.9	39.9	39.9	40.9	40.9	40.9	41.8
162.5°	39.9	39.9	39.9	39.9	39.0	39.0	39.0	39.0	39.9	39.9	40.9
165°	39.9	39.0	39.0	39.0	38.1	38.1	38.1	38.1	39.0	39.9	39.0
167.5°	38.1	38.1	38.1	38.1	38.1	37.2	37.2	38.1	38.1	38.1	39.0
170°	38.1	38.1	37.2	37.2	37.2	37.2	37.2	37.2	37.2	37.2	38.1
172.5°	38.1	38.1	38.1	38.1	37.2	37.2	37.2	37.2	37.2	38.1	38.1
175°	38.1	38.1	38.1	38.1	37.2	37.2	37.2	38.1	38.1	38.1	37.2
177.5°	38.1	38.1	38.1	38.1	37.2	38.1	38.1	38.1	38.1	38.1	38.1
180°	38.1	38.1	38.1	38.1	38.1	38.1	38.1	38.1	38.1	38.1	38.1

(END OF REPORT)