

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P833536

Luminaire Tested: **TTN-D2-735-U-RW-CG-UPL1**

Issue Date: 5/15/2024

Test Information

Test Method: LM-79-08
Report Number: P833536
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G3-2308-121-4) AND
Test Lab: INNOVATION CENTER
Issue Date: 5/15/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: TTN-D2-735-U-RW-CG-UPL1
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE WITH UPLIGHT
3500K, 70 CRI LEDS AND RECTANGULAR DISTRIBUTION WITH CLEAR GLASS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4882.9 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Luminous Opening: Vertical Cylinder (Dia: 0.71' x H: 0.1')
IES Classification: Type II - Short
BUG Rating: B2 - U3 - G2


Input Watts (W): 45.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P833536
 CATALOG NUMBER: TTN-D2-735-U-RW-CG-UPL1

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1 fc
 Type II - Short - N/A

REPORT NUMBER: P833536
CATALOG NUMBER: TTN-D2-735-U-RW-CG-UPL1

Luminous Intensity Polar Plot



— Vertical Plane Through 90-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P833536
 CATALOG NUMBER: TTN-D2-735-U-RW-CG-UPL1


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2291.2	150.2	2441.4
	% Fixture	46.9	3.1	50.0
Street Side	Lumens	2291.2	150.2	2441.4
	% Fixture	46.9	3.1	50.0
Total	Lumens	4582.4	300.5	4882.9
	% Fixture	93.8	6.2	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.3	0.8
10°-20°	126.6	2.6
20°-30°	269.5	5.5
30°-40°	496.6	10.2
40°-50°	799.6	16.4
50°-60°	1082.3	22.2
60°-70°	1052.3	21.6
70°-80°	612.3	12.5
80°-90°	103.9	2.1
90°-100°	6.7	0.1
100°-110°	68.2	1.4
110°-120°	99.6	2.0
120°-130°	57.8	1.2
130°-140°	30.6	0.6
140°-150°	18.2	0.4
150°-160°	11.2	0.2
160°-170°	6.1	0.1
170°-180°	2.0	0.0
0°-90°	4582.4	93.8
0°-180°	4882.9	100.0

Coefficient of Utilization




REPORT NUMBER: P833536
 CATALOG NUMBER: TTN-D2-735-U-RW-CG-UPL1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	217.7	4.5			
FM (30°-60°)	1189.3	24.4			
FH (60°-80°)	832.3	17.0			G1/1800
FVH (80°-90°)	52.0	1.1			G1/100
BL (0°-30°)	217.7	4.5	B1/500		
BM (30°-60°)	1189.3	24.4	B2/2500		
BH (60°-80°)	832.3	17.0	B2/1000		G2/1000
BVH (80°-90°)	52.0	1.1			G1/100
UL (90°-100°)	6.7	0.1		U1/10	
UH (100°-180°)	293.8	6.0		U3/500	

BUG Rating: B2-U3-G2
 Type II Short





REPORT NUMBER: P833536

CATALOG NUMBER: TTN-D2-735-U-RW-CG-UPL1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	412.3	412.3	412.3	412.3	412.3	412.3	412.3	412.3	412.3	412.3	412.3
2.5°	412.3	412.3	412.3	412.3	408.1	408.1	408.1	404.0	404.0	404.0	404.0
5°	412.3	412.3	412.3	416.4	416.4	416.4	412.3	412.3	412.3	412.3	412.3
7.5°	412.3	416.4	416.4	412.3	412.3	408.1	408.1	408.1	404.0	404.0	404.0
10°	412.3	412.3	412.3	412.3	408.1	408.1	412.3	412.3	416.4	416.4	416.4
12.5°	408.1	408.1	412.3	412.3	412.3	416.4	424.6	428.8	432.9	437.0	437.0
15°	412.3	412.3	416.4	420.5	424.6	432.9	445.2	457.6	465.9	470.0	465.9
17.5°	412.3	416.4	420.5	428.8	441.1	453.5	474.1	490.6	507.1	511.2	515.3
20°	420.5	420.5	424.6	441.1	461.7	482.3	511.2	540.1	560.7	568.9	568.9
22.5°	424.6	428.8	432.9	453.5	486.5	519.5	560.7	593.7	622.5	639.0	643.1
25°	437.0	437.0	445.2	474.1	515.3	564.8	618.4	667.9	705.0	725.6	729.7
27.5°	445.2	449.4	461.7	498.8	552.4	614.3	688.5	746.2	791.5	816.3	820.4
30°	453.5	457.6	482.3	523.6	589.5	663.7	750.3	824.5	882.2	911.1	915.2
32.5°	465.9	470.0	498.8	544.2	622.5	713.2	812.2	902.9	985.3	1010.0	1014.2
35°	478.2	482.3	515.3	568.9	659.6	762.7	878.1	985.3	1084.3	1117.2	1125.5
37.5°	490.6	494.7	527.7	593.7	696.7	816.3	952.3	1080.1	1187.3	1232.7	1245.0
40°	503.0	507.1	544.2	618.4	733.8	874.0	1030.7	1170.8	1294.5	1348.1	1356.3
42.5°	511.2	515.3	556.6	639.0	770.9	927.6	1113.1	1269.8	1401.7	1471.8	1480.0
45°	523.6	527.7	573.0	667.9	803.9	989.4	1191.4	1381.1	1533.6	1611.9	1620.2
47.5°	531.8	535.9	585.4	684.4	841.0	1047.1	1273.9	1480.0	1661.4	1743.9	1768.6
50°	535.9	540.1	593.7	700.8	865.8	1088.4	1339.9	1579.0	1772.7	1875.8	1888.2
52.5°	535.9	544.2	597.8	713.2	882.2	1125.5	1393.4	1661.4	1879.9	1995.4	1999.5
55°	531.8	535.9	593.7	709.1	890.5	1142.0	1430.6	1710.9	1954.1	2065.4	2102.5
57.5°	515.3	519.5	577.2	696.7	874.0	1133.7	1422.3	1723.3	1970.6	2077.8	2123.2
60°	490.6	498.8	552.4	667.9	849.3	1104.9	1397.6	1698.5	1945.9	2077.8	2081.9
62.5°	461.7	465.9	519.5	630.8	812.2	1059.5	1352.2	1649.0	1888.2	2024.2	2020.1
65°	420.5	424.6	470.0	585.4	746.2	972.9	1261.5	1570.7	1776.9	1921.1	1908.8
67.5°	375.2	379.3	420.5	523.6	667.9	878.1	1137.8	1438.8	1620.2	1768.6	1760.4
70°	325.7	325.7	362.8	449.4	585.4	770.9	1001.8	1265.6	1447.0	1570.7	1574.8
72.5°	268.0	268.0	301.0	375.2	490.6	647.3	845.1	1080.1	1228.5	1335.7	1344.0
75°	210.3	206.1	235.0	296.8	387.5	515.3	667.9	869.9	985.3	1088.4	1084.3
77.5°	148.4	148.4	164.9	214.4	280.3	383.4	494.7	655.5	733.8	820.4	803.9
80°	94.8	94.8	103.1	140.2	185.5	255.6	325.7	445.2	498.8	564.8	544.2
82.5°	49.5	45.3	53.6	74.2	98.9	140.2	181.4	259.7	284.5	333.9	317.4
85°	16.5	16.5	16.5	24.7	37.1	53.6	70.1	111.3	115.4	148.4	136.0
87.5°	4.1	0.0	0.0	4.1	4.1	4.1	4.1	12.4	12.4	24.7	16.5
90°	2.6	2.6	3.1	3.1	3.1	3.1	3.1	3.1	3.1	2.6	2.6
92.5°	2.6	2.6	2.6	3.6	4.1	3.6	4.1	3.1	3.1	2.6	2.6
95°	3.1	3.1	3.6	4.6	5.7	6.2	6.2	3.6	3.6	3.1	3.1
97.5°	4.1	4.6	4.6	5.7	9.3	17.0	10.3	5.1	5.1	4.6	4.1
100°	6.7	7.2	7.2	12.9	27.2	36.5	26.2	13.4	9.8	7.2	7.2
102.5°	21.6	22.6	27.8	41.6	61.7	56.0	47.3	44.7	30.8	24.7	23.6
105°	55.0	54.5	58.6	69.4	86.4	84.8	78.1	70.9	61.2	56.5	56.5
107.5°	72.5	72.5	76.1	85.3	98.2	114.6	116.2	92.0	80.7	75.6	75.0
110°	81.7	81.7	84.8	92.5	109.5	132.6	131.6	113.6	99.7	93.0	92.0



REPORT NUMBER: P833536
 CATALOG NUMBER: TTN-D2-735-U-RW-CG-UPL1

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	83.8	84.3	88.4	100.2	118.7	129.0	124.4	117.2	111.0	105.9	104.9
115°	86.9	86.9	91.5	102.8	113.1	117.2	112.1	106.4	102.3	100.2	101.3
117.5°	85.8	87.4	88.4	94.6	101.3	104.4	101.8	94.1	91.0	90.0	88.4
120°	79.7	79.7	80.7	83.8	87.4	88.9	87.9	82.8	80.2	79.7	78.6
122.5°	70.9	71.5	70.9	72.5	75.0	76.6	75.6	71.5	70.4	70.4	69.4
125°	62.2	62.2	61.7	62.7	64.3	63.7	64.3	62.2	61.7	61.7	61.2
127.5°	56.0	55.5	54.5	55.0	55.5	55.5	56.0	54.0	54.5	55.0	54.5
130°	49.9	49.9	48.8	48.8	48.8	47.8	48.8	47.8	48.3	48.8	49.3
132.5°	44.2	44.2	42.7	42.2	42.2	42.2	42.7	42.2	43.2	44.2	44.2
135°	39.6	39.6	38.0	38.6	38.6	38.0	38.6	38.0	39.1	39.6	39.6
137.5°	36.0	36.0	35.0	35.0	35.0	34.4	35.0	35.0	35.5	36.5	37.0
140°	32.9	32.9	32.4	32.4	31.9	32.4	32.4	32.4	32.9	33.4	33.4
142.5°	31.4	30.8	30.3	29.8	30.3	30.3	30.3	29.8	30.3	31.4	31.4
145°	28.8	28.8	28.3	28.3	28.3	28.8	28.3	28.3	28.8	28.8	29.3
147.5°	27.2	27.2	26.7	27.2	27.2	27.2	27.2	26.7	27.2	27.2	27.8
150°	26.7	26.2	25.7	26.2	26.2	25.7	25.7	25.7	25.7	26.2	26.2
152.5°	25.2	25.2	24.7	25.2	24.7	24.7	24.7	24.7	24.7	25.2	25.7
155°	24.2	24.2	23.6	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2
157.5°	23.1	23.6	23.1	23.1	23.1	23.1	23.1	23.1	23.1	23.6	23.6
160°	22.6	22.6	22.6	22.6	22.1	22.1	22.1	22.6	22.6	22.6	23.1
162.5°	22.1	22.1	22.1	22.1	21.6	21.6	21.6	21.6	22.1	22.1	22.6
165°	22.1	21.6	21.6	21.6	21.1	21.1	21.1	21.1	21.6	22.1	21.6
167.5°	21.1	21.1	21.1	21.1	21.1	20.6	20.6	21.1	21.1	21.1	21.6
170°	21.1	21.1	20.6	20.6	20.6	20.6	20.6	20.6	20.6	20.6	21.1
172.5°	21.1	21.1	21.1	21.1	20.6	20.6	20.6	20.6	20.6	21.1	21.1
175°	21.1	21.1	21.1	21.1	20.6	20.6	20.6	21.1	21.1	21.1	20.6
177.5°	21.1	21.1	21.1	21.1	20.6	21.1	21.1	21.1	21.1	21.1	21.1
180°	21.1	21.1	21.1	21.1	21.1	21.1	21.1	21.1	21.1	21.1	21.1

(END OF REPORT)