

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P833540

Luminaire Tested: **TTN-D2-735-U-RW-UPL2**

Issue Date: 5/15/2024

**Test Information**

Test Method: LM-79-08  
Report Number: P833540  
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G3-2308-121-4) AND  
Test Lab: INNOVATION CENTER  
Issue Date: 5/15/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TTN-D2-735-U-RW-UPL2  
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE WITH UPLIGHT  
3500K, 70 CRI LEDS AND RECTANGULAR DISTRIBUTION  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5430.8 lumens  
Efficiency: N/A  
Efficacy: 115.5 lumens/watt  
Luminous Opening: Vertical Cylinder (Dia: 0.71' x H: 0.1')  
IES Classification: Type II - Short  
BUG Rating: B2 - U4 - G2  
  
Input Watts (W): 47  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P833540  
 CATALOG NUMBER: TTN-D2-735-U-RW-UPL2

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1 fc  
 Type II - Short - N/A

REPORT NUMBER: P833540  
CATALOG NUMBER: TTN-D2-735-U-RW-UPL2

### Luminous Intensity Polar Plot



— Vertical Plane Through 90-Deg Lateral    - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P833540

CATALOG NUMBER: TTN-D2-735-U-RW-UPL2


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	2443.9	271.5	2715.4
	% Fixture	45.0	5.0	50.0
<b>Street Side</b>	Lumens	2443.9	271.5	2715.4
	% Fixture	45.0	5.0	50.0
<b>Total</b>	Lumens	4887.7	543.0	5430.8
	% Fixture	90.0	10.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	41.0	0.8
10°-20°	131.1	2.4
20°-30°	273.4	5.0
30°-40°	490.4	9.0
40°-50°	783.6	14.4
50°-60°	1072.7	19.8
60°-70°	1106.5	20.4
70°-80°	786.9	14.5
80°-90°	202.2	3.7
90°-100°	12.1	0.2
100°-110°	123.2	2.3
110°-120°	180.1	3.3
120°-130°	104.5	1.9
130°-140°	55.4	1.0
140°-150°	32.9	0.6
150°-160°	20.2	0.4
160°-170°	11.0	0.2
170°-180°	3.6	0.1
0°-90°	4887.7	90.0
0°-180°	5430.8	100.0

**Coefficient of Utilization**




REPORT NUMBER: P833540  
 CATALOG NUMBER: TTN-D2-735-U-RW-UPL2

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	222.7	4.1			
FM (30°-60°)	1173.3	21.6			
FH (60°-80°)	946.7	17.4			G1/1800
FVH (80°-90°)	101.1	1.9			G2/225
BL (0°-30°)	222.7	4.1	B1/500		
BM (30°-60°)	1173.3	21.6	B2/2500		
BH (60°-80°)	946.7	17.4	B2/1000		G2/1000
BVH (80°-90°)	101.1	1.9			G2/225
UL (90°-100°)	12.1	0.2		U2/50	
UH (100°-180°)	530.9	9.8		U4/1000	

**BUG Rating: B2-U4-G2**  
 Type II Short





REPORT NUMBER: P833540

CATALOG NUMBER: TTN-D2-735-U-RW-UPL2

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	437.2	437.2	437.2	437.2	437.2	437.2	437.2	437.2	437.2	437.2	437.2
2.5°	437.2	437.2	433.0	433.0	433.0	428.9	428.9	428.9	428.9	424.8	428.9
5°	437.2	437.2	437.2	437.2	433.0	428.9	428.9	428.9	424.8	424.8	424.8
7.5°	433.0	433.0	433.0	433.0	428.9	424.8	424.8	424.8	420.7	420.7	420.7
10°	428.9	433.0	428.9	428.9	424.8	424.8	428.9	428.9	433.0	433.0	433.0
12.5°	424.8	424.8	424.8	428.9	428.9	433.0	441.3	449.5	453.7	457.8	457.8
15°	424.8	424.8	428.9	433.0	441.3	449.5	461.9	474.3	482.5	490.8	490.8
17.5°	424.8	424.8	428.9	441.3	453.7	470.2	490.8	507.3	523.8	536.1	540.3
20°	424.8	424.8	433.0	449.5	474.3	499.0	527.9	552.6	577.4	598.0	598.0
22.5°	428.9	433.0	441.3	461.9	499.0	536.1	573.3	610.4	639.2	664.0	664.0
25°	437.2	437.2	449.5	482.5	527.9	577.4	631.0	676.4	713.5	746.5	746.5
27.5°	441.3	445.4	461.9	503.1	560.9	622.7	697.0	750.6	800.1	829.0	833.1
30°	449.5	453.7	478.4	519.6	589.8	668.1	754.7	829.0	882.6	911.4	919.7
32.5°	453.7	457.8	490.8	540.3	618.6	709.4	808.3	903.2	977.4	1010.4	1022.8
35°	466.0	470.2	503.1	560.9	651.6	754.7	870.2	981.6	1068.2	1109.4	1117.6
37.5°	478.4	482.5	515.5	581.5	684.6	804.2	936.2	1064.0	1163.0	1212.5	1229.0
40°	486.7	490.8	527.9	606.3	721.7	857.8	1010.4	1150.6	1262.0	1323.9	1336.2
42.5°	499.0	503.1	544.4	626.9	754.7	911.4	1088.8	1245.5	1365.1	1435.2	1451.7
45°	511.4	515.5	560.9	651.6	791.8	969.2	1167.1	1356.8	1492.9	1575.4	1591.9
47.5°	523.8	527.9	577.4	676.4	829.0	1026.9	1249.6	1455.8	1620.8	1699.2	1732.1
50°	527.9	536.1	585.6	692.9	853.7	1076.4	1319.7	1554.8	1728.0	1831.1	1839.4
52.5°	532.0	540.3	593.9	705.2	874.3	1113.5	1377.5	1637.3	1839.4	1963.1	1954.9
55°	536.1	536.1	593.9	705.2	882.6	1138.3	1418.7	1690.9	1913.6	2012.6	2070.3
57.5°	519.6	523.8	585.6	697.0	878.4	1134.1	1418.7	1711.5	1942.5	2049.7	2091.0
60°	499.0	507.3	565.0	676.4	862.0	1121.8	1410.5	1703.3	1954.9	2070.3	2058.0
62.5°	470.2	486.7	536.1	647.5	837.2	1092.9	1398.1	1682.7	1926.0	2045.6	2033.2
65°	437.2	453.7	499.0	618.6	783.6	1022.8	1332.1	1641.4	1847.6	1983.7	1959.0
67.5°	404.2	416.5	461.9	569.1	721.7	948.6	1245.5	1550.7	1736.3	1884.7	1872.4
70°	367.1	371.2	416.5	511.4	659.9	874.3	1163.0	1422.8	1637.3	1748.6	1773.4
72.5°	321.7	321.7	367.1	449.5	585.6	775.3	1051.7	1278.5	1480.6	1575.4	1612.5
75°	263.9	268.1	305.2	379.4	490.8	664.0	894.9	1125.9	1295.0	1394.0	1406.3
77.5°	206.2	210.3	239.2	301.1	395.9	536.1	738.2	919.7	1080.5	1167.1	1142.4
80°	148.5	152.6	173.2	218.6	292.8	400.0	569.1	730.0	845.5	915.6	882.6
82.5°	90.7	94.9	107.2	136.1	185.6	259.8	387.7	507.3	598.0	655.7	643.4
85°	45.4	45.4	53.6	61.9	78.4	115.5	185.6	255.7	325.8	367.1	354.7
87.5°	8.2	12.4	12.4	12.4	12.4	8.2	12.4	12.4	12.4	20.6	8.2
90°	4.6	4.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	4.6	4.6
92.5°	4.6	4.6	4.6	6.5	7.4	6.5	7.4	5.6	5.6	4.6	4.6
95°	5.6	5.6	6.5	8.4	10.2	11.1	11.1	6.5	6.5	5.6	5.6
97.5°	7.4	8.4	8.4	10.2	16.7	30.7	18.6	9.3	9.3	8.4	7.4
100°	12.1	13.0	13.0	23.2	49.2	66.0	47.4	24.2	17.7	13.0	13.0
102.5°	39.0	40.9	50.2	75.3	111.5	101.3	85.5	80.8	55.7	44.6	42.7
105°	99.4	98.5	105.9	125.4	156.1	153.3	141.2	128.2	110.6	102.2	102.2
107.5°	131.0	131.0	137.5	154.2	177.4	207.2	210.0	166.3	145.9	136.6	135.6
110°	147.7	147.7	153.3	167.2	197.9	239.7	237.8	205.3	180.2	168.2	166.3



REPORT NUMBER: P833540  
 CATALOG NUMBER: TTN-D2-735-U-RW-UPL2

**CANDELA DISTRIBUTION (continued):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	151.4	152.4	159.8	181.2	214.6	233.2	224.8	211.8	200.7	191.4	189.5
115°	157.0	157.0	165.4	185.8	204.4	211.8	202.5	192.3	184.9	181.2	183.0
117.5°	155.1	157.9	159.8	170.9	183.0	188.6	183.9	170.0	164.4	162.6	159.8
120°	144.0	144.0	145.9	151.4	157.9	160.7	158.9	149.6	144.9	144.0	142.1
122.5°	128.2	129.1	128.2	131.0	135.6	138.4	136.6	129.1	127.3	127.3	125.4
125°	112.4	112.4	111.5	113.3	116.1	115.2	116.1	112.4	111.5	111.5	110.6
127.5°	101.3	100.3	98.5	99.4	100.3	100.3	101.3	97.5	98.5	99.4	98.5
130°	90.1	90.1	88.3	88.3	88.3	86.4	88.3	86.4	87.3	88.3	89.2
132.5°	79.9	79.9	77.1	76.2	76.2	76.2	77.1	76.2	78.0	79.9	79.9
135°	71.5	71.5	68.7	69.7	69.7	68.7	69.7	68.7	70.6	71.5	71.5
137.5°	65.0	65.0	63.2	63.2	63.2	62.2	63.2	63.2	64.1	66.0	66.9
140°	59.5	59.5	58.5	58.5	57.6	58.5	58.5	58.5	59.5	60.4	60.4
142.5°	56.7	55.7	54.8	53.9	54.8	54.8	54.8	53.9	54.8	56.7	56.7
145°	52.0	52.0	51.1	51.1	51.1	52.0	51.1	51.1	52.0	52.0	53.0
147.5°	49.2	49.2	48.3	49.2	49.2	49.2	49.2	48.3	49.2	49.2	50.2
150°	48.3	47.4	46.5	47.4	47.4	46.5	46.5	46.5	46.5	47.4	47.4
152.5°	45.5	45.5	44.6	45.5	44.6	44.6	44.6	44.6	44.6	45.5	46.5
155°	43.7	43.7	42.7	43.7	43.7	43.7	43.7	43.7	43.7	43.7	43.7
157.5°	41.8	42.7	41.8	41.8	41.8	41.8	41.8	41.8	41.8	42.7	42.7
160°	40.9	40.9	40.9	40.9	39.9	39.9	39.9	40.9	40.9	40.9	41.8
162.5°	39.9	39.9	39.9	39.9	39.0	39.0	39.0	39.0	39.9	39.9	40.9
165°	39.9	39.0	39.0	39.0	38.1	38.1	38.1	38.1	39.0	39.9	39.0
167.5°	38.1	38.1	38.1	38.1	38.1	37.2	37.2	38.1	38.1	38.1	39.0
170°	38.1	38.1	37.2	37.2	37.2	37.2	37.2	37.2	37.2	37.2	38.1
172.5°	38.1	38.1	38.1	38.1	37.2	37.2	37.2	37.2	37.2	38.1	38.1
175°	38.1	38.1	38.1	38.1	37.2	37.2	37.2	38.1	38.1	38.1	37.2
177.5°	38.1	38.1	38.1	38.1	37.2	38.1	38.1	38.1	38.1	38.1	38.1
180°	38.1	38.1	38.1	38.1	38.1	38.1	38.1	38.1	38.1	38.1	38.1

(END OF REPORT)