

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P832832

Luminaire Tested: **TTN-D0-740-U-CQ-UPL2**

Issue Date: 5/15/2024

Test Information

Test Method: LM-79-08
Report Number: P832832
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G3-2308-121-4) AND
Test Lab: INNOVATION CENTER
Issue Date: 5/15/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: TTN-D0-740-U-CQ-UPL2
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE WITH UPLIGHT
4000K, 70 CRI LEDS AND CONCENTRATED DISTRIBUTION
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1807.7 lumens
Efficiency: N/A
Efficacy: 118.9 lumens/watt
Luminous Opening: Vertical Cylinder (Dia: 0.71' x H: 0.1')
IES Classification: Type V - Short
BUG Rating: B1 - U4 - G1


Input Watts (W): 15.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P832832
 CATALOG NUMBER: TTN-D0-740-U-CQ-UPL2

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.5 fc
 Type V - Short - N/A

REPORT NUMBER: P832832
CATALOG NUMBER: TTN-D0-740-U-CQ-UPL2

Luminous Intensity Polar Plot



REPORT NUMBER: P832832

CATALOG NUMBER: TTN-D0-740-U-CQ-UPL2


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	611.4	292.5	903.8
	% Fixture	33.8	16.2	50.0
Street Side	Lumens	611.4	292.5	903.8
	% Fixture	33.8	16.2	50.0
Total	Lumens	1222.8	584.9	1807.7
	% Fixture	67.6	32.4	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.1	1.6
10°-20°	84.6	4.7
20°-30°	136.2	7.5
30°-40°	183.2	10.1
40°-50°	226.1	12.5
50°-60°	242.5	13.4
60°-70°	196.7	10.9
70°-80°	104.2	5.8
80°-90°	20.1	1.1
90°-100°	13.1	0.7
100°-110°	132.7	7.3
110°-120°	194.0	10.7
120°-130°	112.6	6.2
130°-140°	59.7	3.3
140°-150°	35.4	2.0
150°-160°	21.8	1.2
160°-170°	11.9	0.7
170°-180°	3.9	0.2
0°-90°	1222.8	67.6
0°-180°	1807.7	100.0

Coefficient of Utilization



REPORT NUMBER: P832832


CATALOG NUMBER: TTN-D0-740-U-CQ-UPL2

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	125.0	6.9			
FM (30°-60°)	325.9	18.0			
FH (60°-80°)	150.5	8.3			G0/660
FVH (80°-90°)	10.0	0.6			G1/100
BL (0°-30°)	125.0	6.9	B1/500		
BM (30°-60°)	325.9	18.0	B1/1000		
BH (60°-80°)	150.5	8.3	B1/500		G0/660
BVH (80°-90°)	10.0	0.6			G1/100
UL (90°-100°)	13.1	0.7		U2/50	
UH (100°-180°)	571.8	31.6		U4/1000	

BUG Rating: B1-U4-G1

Type V Short





REPORT NUMBER: P832832
 CATALOG NUMBER: TTN-D0-740-U-CQ-UPL2

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	309.0	309.0	309.0	309.0	309.0	309.0	309.0	309.0	309.0	309.0	309.0
2.5°	307.0	307.0	307.0	307.0	307.0	307.0	307.0	307.0	307.0	307.0	308.0
5°	307.0	307.0	307.0	307.0	306.0	307.0	307.0	307.0	307.0	307.0	307.0
7.5°	305.0	305.0	305.0	305.0	305.0	305.0	305.0	305.0	305.0	305.0	305.0
10°	302.0	302.0	302.0	302.0	302.0	302.0	302.0	302.0	302.0	302.0	302.0
12.5°	300.0	300.0	300.0	300.0	300.0	300.0	300.0	300.0	300.0	300.0	300.0
15°	299.0	299.0	299.0	299.0	299.0	299.0	299.0	299.0	299.0	298.0	298.0
17.5°	297.0	297.0	297.0	297.0	298.0	298.0	298.0	297.0	297.0	297.0	297.0
20°	295.0	295.0	295.0	296.0	296.0	296.0	296.0	296.0	295.0	295.0	295.0
22.5°	294.0	294.0	294.0	294.0	295.0	295.0	295.0	295.0	294.0	294.0	294.0
25°	293.0	293.0	294.0	294.0	295.0	295.0	295.0	294.0	294.0	293.0	293.0
27.5°	293.0	293.0	294.0	294.0	295.0	295.0	295.0	295.0	294.0	293.0	293.0
30°	292.0	293.0	293.0	294.0	295.0	295.0	295.0	294.0	293.0	292.0	292.0
32.5°	291.0	291.0	292.0	293.0	294.0	294.0	294.0	293.0	292.0	291.0	290.0
35°	290.0	290.0	290.0	292.0	293.0	293.0	293.0	292.0	290.0	289.0	289.0
37.5°	288.0	289.0	290.0	291.0	293.0	293.0	293.0	291.0	289.0	288.0	287.0
40°	288.0	288.0	290.0	291.0	294.0	294.0	293.0	291.0	289.0	287.0	286.0
42.5°	287.0	288.0	290.0	293.0	296.0	296.0	295.0	292.0	289.0	287.0	286.0
45°	287.0	287.0	290.0	294.0	298.0	299.0	297.0	294.0	290.0	286.0	286.0
47.5°	285.0	285.0	289.0	294.0	299.0	300.0	299.0	294.0	289.0	286.0	285.0
50°	280.0	280.0	285.0	291.0	297.0	299.0	297.0	293.0	286.0	282.0	281.0
52.5°	272.0	272.0	277.0	285.0	291.0	294.0	292.0	287.0	280.0	274.0	273.0
55°	260.0	261.0	266.0	275.0	282.0	285.0	283.0	277.0	269.0	263.0	261.0
57.5°	246.0	246.0	253.0	262.0	269.0	272.0	270.0	264.0	255.0	249.0	247.0
60°	227.0	228.0	234.0	246.0	253.0	256.0	254.0	247.0	237.0	230.0	228.0
62.5°	208.0	209.0	215.0	225.0	233.0	235.0	233.0	226.0	217.0	210.0	208.0
65°	186.0	187.0	194.0	203.0	209.0	212.0	209.0	203.0	195.0	188.0	187.0
67.5°	163.0	164.0	171.0	179.0	185.0	187.0	184.0	179.0	171.0	165.0	163.0
70°	139.0	140.0	146.0	153.0	158.0	160.0	158.0	152.0	146.0	140.0	139.0
72.5°	114.0	115.0	121.0	127.0	131.0	133.0	130.0	126.0	120.0	115.0	114.0
75°	90.0	90.0	95.0	100.0	104.0	105.0	103.0	100.0	95.0	91.0	89.0
77.5°	67.0	67.0	72.0	75.0	77.0	79.0	77.0	74.0	71.0	67.0	67.0
80°	45.0	45.0	49.0	51.0	53.0	54.0	53.0	51.0	49.0	46.0	45.0
82.5°	27.0	27.0	29.0	31.0	31.0	32.0	32.0	31.0	29.0	27.0	27.0
85°	12.0	11.0	13.0	14.0	14.0	15.0	15.0	14.0	13.0	12.0	12.0
87.5°	1.0	2.0	2.0	3.0	3.0	3.0	3.0	3.0	2.0	2.0	2.0
90°	5.0	5.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	5.0	5.0
92.5°	5.0	5.0	5.0	7.0	8.0	7.0	8.0	6.0	6.0	5.0	5.0
95°	6.0	6.0	7.0	9.0	11.0	12.0	12.0	7.0	7.0	6.0	6.0
97.5°	8.0	9.0	9.0	11.0	18.0	33.0	20.0	10.0	10.0	9.0	8.0
100°	13.0	14.0	14.0	25.0	53.0	71.1	51.0	26.0	19.0	14.0	14.0
102.5°	42.0	44.0	54.0	81.1	120.1	109.1	92.1	87.1	60.0	48.0	46.0
105°	107.1	106.1	114.1	135.1	168.1	165.1	152.1	138.1	119.1	110.1	110.1
107.5°	141.1	141.1	148.1	166.1	191.1	223.2	226.2	179.1	157.1	147.1	146.1
110°	159.1	159.1	165.1	180.1	213.2	258.2	256.2	221.2	194.1	181.1	179.1



REPORT NUMBER: P832832
 CATALOG NUMBER: TTN-D0-740-U-CQ-UPL2

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	163.1	164.1	172.1	195.1	231.2	251.2	242.2	228.2	216.2	206.2	204.2
115°	169.1	169.1	178.1	200.2	220.2	228.2	218.2	207.2	199.2	195.1	197.1
117.5°	167.1	170.1	172.1	184.1	197.1	203.2	198.1	183.1	177.1	175.1	172.1
120°	155.1	155.1	157.1	163.1	170.1	173.1	171.1	161.1	156.1	155.1	153.1
122.5°	138.1	139.1	138.1	141.1	146.1	149.1	147.1	139.1	137.1	137.1	135.1
125°	121.1	121.1	120.1	122.1	125.1	124.1	125.1	121.1	120.1	120.1	119.1
127.5°	109.1	108.1	106.1	107.1	108.1	108.1	109.1	105.1	106.1	107.1	106.1
130°	97.1	97.1	95.1	95.1	95.1	93.1	95.1	93.1	94.1	95.1	96.1
132.5°	86.1	86.1	83.1	82.1	82.1	82.1	83.1	82.1	84.1	86.1	86.1
135°	77.1	77.1	74.1	75.1	75.1	74.1	75.1	74.1	76.1	77.1	77.1
137.5°	70.1	70.1	68.1	68.1	68.1	67.1	68.1	68.1	69.1	71.1	72.1
140°	64.0	64.0	63.0	63.0	62.0	63.0	63.0	63.0	64.0	65.0	65.0
142.5°	61.0	60.0	59.0	58.0	59.0	59.0	59.0	58.0	59.0	61.0	61.0
145°	56.0	56.0	55.0	55.0	55.0	56.0	55.0	55.0	56.0	56.0	57.0
147.5°	53.0	53.0	52.0	53.0	53.0	53.0	53.0	52.0	53.0	53.0	54.0
150°	52.0	51.0	50.0	51.0	51.0	50.0	50.0	50.0	50.0	51.0	51.0
152.5°	49.0	49.0	48.0	49.0	48.0	48.0	48.0	48.0	48.0	49.0	50.0
155°	47.0	47.0	46.0	47.0	47.0	47.0	47.0	47.0	47.0	47.0	47.0
157.5°	45.0	46.0	45.0	45.0	45.0	45.0	45.0	45.0	45.0	46.0	46.0
160°	44.0	44.0	44.0	44.0	43.0	43.0	43.0	44.0	44.0	44.0	45.0
162.5°	43.0	43.0	43.0	43.0	42.0	42.0	42.0	42.0	43.0	43.0	44.0
165°	43.0	42.0	42.0	42.0	41.0	41.0	41.0	41.0	42.0	43.0	42.0
167.5°	41.0	41.0	41.0	41.0	41.0	40.0	40.0	41.0	41.0	41.0	42.0
170°	41.0	41.0	40.0	40.0	40.0	40.0	40.0	40.0	40.0	40.0	41.0
172.5°	41.0	41.0	41.0	41.0	40.0	40.0	40.0	40.0	40.0	41.0	41.0
175°	41.0	41.0	41.0	41.0	40.0	40.0	40.0	41.0	41.0	41.0	40.0
177.5°	41.0	41.0	41.0	41.0	40.0	41.0	41.0	41.0	41.0	41.0	41.0
180°	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0

(END OF REPORT)