

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P832851

Luminaire Tested: **TTN-D0-740-U-RW-UPL3**

Issue Date: 5/15/2024

Test Information

Test Method: LM-79-08
Report Number: P832851
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G3-2308-121-4) AND
Test Lab: INNOVATION CENTER
Issue Date: 5/15/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TTN-D0-740-U-RW-UPL3
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE WITH UPLIGHT
4000K, 70 CRI LEDS AND RECTANGULAR DISTRIBUTION
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1997.6 lumens
Efficiency: N/A
Efficacy: 112.9 lumens/watt
Luminous Opening: Vertical Cylinder (Dia: 0.71' x H: 0.1')
IES Classification: Type II - Short
BUG Rating: B1 - U4 - G1


Input Watts (W): 17.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P832851
 CATALOG NUMBER: TTN-D0-740-U-RW-UPL3

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.2 fc
 Type II - Short - N/A

REPORT NUMBER: P832851
CATALOG NUMBER: TTN-D0-740-U-RW-UPL3

Luminous Intensity Polar Plot



— Vertical Plane Through 90-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P832851
 CATALOG NUMBER: TTN-D0-740-U-RW-UPL3


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	593.0	405.8	998.8
	% Fixture	29.7	20.3	50.0
Street Side	Lumens	593.0	405.8	998.8
	% Fixture	29.7	20.3	50.0
Total	Lumens	1186.1	811.5	1997.6
	% Fixture	59.4	40.6	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	9.9	0.5
10°-20°	31.8	1.6
20°-30°	66.3	3.3
30°-40°	118.9	6.0
40°-50°	190.0	9.5
50°-60°	260.1	13.0
60°-70°	268.3	13.4
70°-80°	190.8	9.6
80°-90°	49.9	2.5
90°-100°	18.1	0.9
100°-110°	184.1	9.2
110°-120°	269.1	13.5
120°-130°	156.2	7.8
130°-140°	82.7	4.1
140°-150°	49.1	2.5
150°-160°	30.3	1.5
160°-170°	16.5	0.8
170°-180°	5.4	0.3
0°-90°	1186.1	59.4
0°-180°	1997.6	100.0

Coefficient of Utilization



REPORT NUMBER: P832851


CATALOG NUMBER: TTN-D0-740-U-RW-UPL3

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	54.0	2.7			
FM (30°-60°)	284.5	14.2			
FH (60°-80°)	229.6	11.5			G0/660
FVH (80°-90°)	25.0	1.2			G1/100
BL (0°-30°)	54.0	2.7	B0/110		
BM (30°-60°)	284.5	14.2	B1/1000		
BH (60°-80°)	229.6	11.5	B1/500		G1/500
BVH (80°-90°)	25.0	1.2			G1/100
UL (90°-100°)	18.1	0.9		U2/50	
UH (100°-180°)	793.4	39.7		U4/1000	

BUG Rating: B1-U4-G1

Type II Short





REPORT NUMBER: P832851
 CATALOG NUMBER: TTN-D0-740-U-RW-UPL3

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	106.0	106.0	106.0	106.0	106.0	106.0	106.0	106.0	106.0	106.0	106.0
2.5°	106.0	106.0	105.0	105.0	105.0	104.0	104.0	104.0	104.0	103.0	104.0
5°	106.0	106.0	106.0	106.0	105.0	104.0	104.0	104.0	103.0	103.0	103.0
7.5°	105.0	105.0	105.0	105.0	104.0	103.0	103.0	103.0	102.0	102.0	102.0
10°	104.0	105.0	104.0	104.0	103.0	103.0	104.0	104.0	105.0	105.0	105.0
12.5°	103.0	103.0	103.0	104.0	104.0	105.0	107.0	109.0	110.0	111.0	111.0
15°	103.0	103.0	104.0	105.0	107.0	109.0	112.0	115.0	117.0	119.0	119.0
17.5°	103.0	103.0	104.0	107.0	110.0	114.0	119.0	123.0	127.0	130.0	131.0
20°	103.0	103.0	105.0	109.0	115.0	121.0	128.0	134.0	140.0	145.0	145.0
22.5°	104.0	105.0	107.0	112.0	121.0	130.0	139.0	148.0	155.0	161.0	161.0
25°	106.0	106.0	109.0	117.0	128.0	140.0	153.0	164.0	173.0	181.0	181.0
27.5°	107.0	108.0	112.0	122.0	136.0	151.0	169.0	182.0	194.0	201.0	202.0
30°	109.0	110.0	116.0	126.0	143.0	162.0	183.0	201.0	214.0	221.0	223.0
32.5°	110.0	111.0	119.0	131.0	150.0	172.0	196.0	219.0	237.0	245.0	248.0
35°	113.0	114.0	122.0	136.0	158.0	183.0	211.0	238.0	259.0	269.0	271.0
37.5°	116.0	117.0	125.0	141.0	166.0	195.0	227.0	258.0	282.0	294.0	298.0
40°	118.0	119.0	128.0	147.0	175.0	208.0	245.0	279.0	306.0	321.0	324.0
42.5°	121.0	122.0	132.0	152.0	183.0	221.0	264.0	302.0	331.0	348.0	352.0
45°	124.0	125.0	136.0	158.0	192.0	235.0	283.0	329.0	362.0	382.0	386.0
47.5°	127.0	128.0	140.0	164.0	201.0	249.0	303.0	353.0	393.0	412.0	420.0
50°	128.0	130.0	142.0	168.0	207.0	261.0	320.0	377.0	419.0	444.0	446.0
52.5°	129.0	131.0	144.0	171.0	212.0	270.0	334.0	397.0	446.0	476.0	474.0
55°	130.0	130.0	144.0	171.0	214.0	276.0	344.0	410.0	464.0	488.0	502.0
57.5°	126.0	127.0	142.0	169.0	213.0	275.0	344.0	415.0	471.0	497.0	507.0
60°	121.0	123.0	137.0	164.0	209.0	272.0	342.0	413.0	474.0	502.0	499.0
62.5°	114.0	118.0	130.0	157.0	203.0	265.0	339.0	408.0	467.0	496.0	493.0
65°	106.0	110.0	121.0	150.0	190.0	248.0	323.0	398.0	448.0	481.0	475.0
67.5°	98.0	101.0	112.0	138.0	175.0	230.0	302.0	376.0	421.0	457.0	454.0
70°	89.0	90.0	101.0	124.0	160.0	212.0	282.0	345.0	397.0	424.0	430.0
72.5°	78.0	78.0	89.0	109.0	142.0	188.0	255.0	310.0	359.0	382.0	391.0
75°	64.0	65.0	74.0	92.0	119.0	161.0	217.0	273.0	314.0	338.0	341.0
77.5°	50.0	51.0	58.0	73.0	96.0	130.0	179.0	223.0	262.0	283.0	277.0
80°	36.0	37.0	42.0	53.0	71.0	97.0	138.0	177.0	205.0	222.0	214.0
82.5°	22.0	23.0	26.0	33.0	45.0	63.0	94.0	123.0	145.0	159.0	156.0
85°	11.0	11.0	13.0	15.0	19.0	28.0	45.0	62.0	79.0	89.0	86.0
87.5°	2.0	3.0	3.0	3.0	3.0	2.0	3.0	3.0	3.0	5.0	2.0
90°	6.9	6.9	8.3	8.3	8.3	8.3	8.3	8.3	8.3	6.9	6.9
92.5°	6.9	6.9	6.9	9.7	11.1	9.7	11.1	8.3	8.3	6.9	6.9
95°	8.3	8.3	9.7	12.5	15.3	16.7	16.7	9.7	9.7	8.3	8.3
97.5°	11.1	12.5	12.5	15.3	25.0	45.8	27.8	13.9	13.9	12.5	11.1
100°	18.0	19.4	19.4	34.7	73.6	98.6	70.8	36.1	26.4	19.4	19.4
102.5°	58.3	61.1	75.0	112.5	166.6	151.3	127.7	120.8	83.3	66.6	63.9
105°	148.6	147.2	158.3	187.4	233.3	229.1	211.0	191.6	165.2	152.7	152.7
107.5°	195.8	195.8	205.5	230.5	265.2	309.6	313.8	248.5	218.0	204.1	202.7
110°	220.8	220.8	229.1	249.9	295.7	358.2	355.4	306.8	269.4	251.3	248.5



REPORT NUMBER: P832851
 CATALOG NUMBER: TTN-D0-740-U-RW-UPL3

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	226.3	227.7	238.8	270.7	320.7	348.5	336.0	316.6	299.9	286.0	283.2
115°	234.6	234.6	247.1	277.7	305.5	316.6	302.7	287.4	276.3	270.7	273.5
117.5°	231.9	236.0	238.8	255.5	273.5	281.8	274.9	254.1	245.8	243.0	238.8
120°	215.2	215.2	218.0	226.3	236.0	240.2	237.4	223.5	216.6	215.2	212.4
122.5°	191.6	193.0	191.6	195.8	202.7	206.9	204.1	193.0	190.2	190.2	187.4
125°	168.0	168.0	166.6	169.4	173.6	172.2	173.6	168.0	166.6	166.6	165.2
127.5°	151.3	149.9	147.2	148.6	149.9	149.9	151.3	145.8	147.2	148.6	147.2
130°	134.7	134.7	131.9	131.9	131.9	129.1	131.9	129.1	130.5	131.9	133.3
132.5°	119.4	119.4	115.2	113.9	113.9	113.9	115.2	113.9	116.6	119.4	119.4
135°	106.9	106.9	102.7	104.1	104.1	102.7	104.1	102.7	105.5	106.9	106.9
137.5°	97.2	97.2	94.4	94.4	94.4	93.0	94.4	94.4	95.8	98.6	100.0
140°	88.9	88.9	87.5	87.5	86.1	87.5	87.5	87.5	88.9	90.2	90.2
142.5°	84.7	83.3	81.9	80.5	81.9	81.9	81.9	80.5	81.9	84.7	84.7
145°	77.8	77.8	76.4	76.4	76.4	77.8	76.4	76.4	77.8	77.8	79.1
147.5°	73.6	73.6	72.2	73.6	73.6	73.6	73.6	72.2	73.6	73.6	75.0
150°	72.2	70.8	69.4	70.8	70.8	69.4	69.4	69.4	69.4	70.8	70.8
152.5°	68.0	68.0	66.6	68.0	66.6	66.6	66.6	66.6	66.6	68.0	69.4
155°	65.3	65.3	63.9	65.3	65.3	65.3	65.3	65.3	65.3	65.3	65.3
157.5°	62.5	63.9	62.5	62.5	62.5	62.5	62.5	62.5	62.5	63.9	63.9
160°	61.1	61.1	61.1	61.1	59.7	59.7	59.7	61.1	61.1	61.1	62.5
162.5°	59.7	59.7	59.7	59.7	58.3	58.3	58.3	58.3	59.7	59.7	61.1
165°	59.7	58.3	58.3	58.3	56.9	56.9	56.9	56.9	58.3	59.7	58.3
167.5°	56.9	56.9	56.9	56.9	56.9	55.5	55.5	56.9	56.9	56.9	58.3
170°	56.9	56.9	55.5	55.5	55.5	55.5	55.5	55.5	55.5	55.5	56.9
172.5°	56.9	56.9	56.9	56.9	55.5	55.5	55.5	55.5	55.5	56.9	56.9
175°	56.9	56.9	56.9	56.9	55.5	55.5	55.5	56.9	56.9	56.9	55.5
177.5°	56.9	56.9	56.9	56.9	55.5	56.9	56.9	56.9	56.9	56.9	56.9
180°	56.9	56.9	56.9	56.9	56.9	56.9	56.9	56.9	56.9	56.9	56.9

(END OF REPORT)