

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P832855

Luminaire Tested: **TTN-D0-740-U-WQ-SG-UPL1**

Issue Date: 5/15/2024

Test Information

Test Method: LM-79-08
Report Number: P832855
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G3-2308-121-4) AND
Test Lab: INNOVATION CENTER
Issue Date: 5/15/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: TTN-D0-740-U-WQ-SG-UPL1
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE WITH UPLIGHT
4000K, 70 CRI LEDS AND WIDE DISTRIBUTION WITH SOLITE GLASS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1455 lumens
Efficiency: N/A
Efficacy: 109.4 lumens/watt
Luminous Opening: Vertical Cylinder (Dia: 0.71' x H: 0.1')
IES Classification: Type V - Short
BUG Rating: B1 - U3 - G1


Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P832855
 CATALOG NUMBER: TTN-D0-740-U-WQ-SG-UPL1

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.2 fc
 Type V - Short - N/A

REPORT NUMBER: P832855
CATALOG NUMBER: TTN-D0-740-U-WQ-SG-UPL1

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 52.5-Deg Vertical

REPORT NUMBER: P832855
 CATALOG NUMBER: TTN-D0-740-U-WQ-SG-UPL1


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	565.8	161.7	727.5
	% Fixture	38.9	11.1	50.0
Street Side	Lumens	565.8	161.7	727.5
	% Fixture	38.9	11.1	50.0
Total	Lumens	1131.6	323.4	1455.0
	% Fixture	77.8	22.2	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	11.1	0.8
10°-20°	36.5	2.5
20°-30°	77.0	5.3
30°-40°	140.7	9.7
40°-50°	224.0	15.4
50°-60°	270.9	18.6
60°-70°	227.8	15.7
70°-80°	120.7	8.3
80°-90°	22.8	1.6
90°-100°	7.2	0.5
100°-110°	73.4	5.0
110°-120°	107.3	7.4
120°-130°	62.3	4.3
130°-140°	33.0	2.3
140°-150°	19.6	1.3
150°-160°	12.1	0.8
160°-170°	6.6	0.5
170°-180°	2.1	0.1
0°-90°	1131.6	77.8
0°-180°	1455.0	100.0

Coefficient of Utilization




REPORT NUMBER: P832855
 CATALOG NUMBER: TTN-D0-740-U-WQ-SG-UPL1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	62.3	4.3			
FM (30°-60°)	317.8	21.8			
FH (60°-80°)	174.3	12.0			G0/660
FVH (80°-90°)	11.4	0.8			G1/100
BL (0°-30°)	62.3	4.3	B0/110		
BM (30°-60°)	317.8	21.8	B1/1000		
BH (60°-80°)	174.3	12.0	B1/500		G0/660
BVH (80°-90°)	11.4	0.8			G1/100
UL (90°-100°)	7.2	0.5		U1/10	
UH (100°-180°)	316.2	21.7		U3/500	

BUG Rating: B1-U3-G1
 Type V Short





REPORT NUMBER: P832855

CATALOG NUMBER: TTN-D0-740-U-WQ-SG-UPL1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	115.0	115.0	115.0	115.0	115.0	115.0	115.0	115.0	115.0	115.0	115.0
2.5°	115.0	115.0	115.0	115.0	115.0	115.0	115.0	115.0	115.0	115.0	115.0
5°	116.0	116.0	115.0	116.0	116.0	116.0	116.0	116.0	116.0	116.0	116.0
7.5°	116.0	116.0	116.0	117.0	117.0	117.0	117.0	116.0	116.0	116.0	116.0
10°	118.0	118.0	118.0	118.0	118.0	118.0	118.0	118.0	118.0	118.0	118.0
12.5°	121.0	121.0	121.0	121.0	121.0	121.0	121.0	121.0	121.0	121.0	121.0
15°	126.0	126.0	126.0	126.0	127.0	127.0	127.0	126.0	126.0	126.0	126.0
17.5°	132.0	132.0	133.0	133.0	134.0	134.0	134.0	133.0	132.0	133.0	132.0
20°	141.0	141.0	141.0	142.0	143.0	143.0	143.0	141.0	141.0	141.0	141.0
22.5°	151.0	151.0	151.0	152.0	153.0	153.0	153.0	151.0	151.0	151.0	151.0
25°	163.0	163.0	163.0	164.0	165.0	166.0	166.0	164.0	163.0	163.0	162.0
27.5°	175.0	175.0	177.0	178.0	179.0	179.0	179.0	177.0	176.0	176.0	176.0
30°	189.0	189.0	191.0	192.0	194.0	194.0	194.0	191.0	190.0	189.0	189.0
32.5°	202.0	203.0	205.0	207.0	209.0	209.0	210.0	206.0	204.0	203.0	203.0
35°	216.0	217.0	219.0	222.0	224.0	225.0	226.0	222.0	219.0	218.0	218.0
37.5°	232.0	233.0	236.0	239.0	243.0	245.0	246.0	240.0	235.0	233.0	233.0
40°	250.0	251.0	254.0	258.0	262.0	264.0	265.0	259.0	254.0	252.0	251.0
42.5°	265.0	267.0	270.0	276.0	280.0	283.0	283.0	276.0	270.0	267.0	267.0
45°	279.0	281.0	286.0	292.0	298.0	301.0	300.0	293.0	286.0	282.0	281.0
47.5°	290.0	292.0	298.0	305.0	313.0	316.0	315.0	307.0	298.0	293.0	292.0
50°	296.0	297.0	304.0	314.0	322.0	325.0	323.0	315.0	305.0	298.0	297.0
52.5°	295.0	296.0	304.0	315.0	324.0	327.0	324.0	315.0	305.0	297.0	296.0
55°	289.0	290.0	298.0	310.0	319.0	322.0	319.0	310.0	299.0	291.0	290.0
57.5°	278.0	279.0	287.0	299.0	309.0	312.0	308.0	298.0	287.0	279.0	279.0
60°	262.0	263.0	271.0	284.0	293.0	296.0	291.0	283.0	272.0	263.0	262.0
62.5°	241.0	241.0	250.0	263.0	271.0	275.0	270.0	261.0	251.0	241.0	242.0
65°	216.0	215.0	224.0	236.0	245.0	248.0	243.0	235.0	225.0	216.0	216.0
67.5°	190.0	190.0	197.0	207.0	215.0	218.0	213.0	206.0	198.0	190.0	190.0
70°	162.0	162.0	167.0	177.0	184.0	186.0	183.0	176.0	169.0	162.0	162.0
72.5°	134.0	133.0	138.0	146.0	152.0	154.0	151.0	147.0	139.0	134.0	134.0
75°	106.0	105.0	108.0	115.0	120.0	122.0	119.0	116.0	110.0	106.0	106.0
77.5°	79.0	78.0	81.0	87.0	90.0	91.0	89.0	87.0	82.0	79.0	79.0
80°	54.0	53.0	55.0	59.0	62.0	62.0	61.0	60.0	56.0	54.0	55.0
82.5°	32.0	31.0	33.0	36.0	38.0	37.0	37.0	36.0	33.0	32.0	32.0
85°	14.0	13.0	14.0	16.0	18.0	17.0	17.0	17.0	15.0	14.0	14.0
87.5°	2.0	2.0	2.0	3.0	4.0	3.0	3.0	3.0	2.0	2.0	2.0
90°	2.8	2.8	3.3	3.3	3.3	3.3	3.3	3.3	3.3	2.8	2.8
92.5°	2.8	2.8	2.8	3.9	4.4	3.9	4.4	3.3	3.3	2.8	2.8
95°	3.3	3.3	3.9	5.0	6.1	6.6	6.6	3.9	3.9	3.3	3.3
97.5°	4.4	5.0	5.0	6.1	10.0	18.3	11.1	5.5	5.5	5.0	4.4
100°	7.2	7.7	7.7	13.8	29.3	39.3	28.2	14.4	10.5	7.7	7.7
102.5°	23.2	24.3	29.9	44.8	66.4	60.3	50.9	48.1	33.2	26.6	25.5
105°	59.2	58.7	63.1	74.7	93.0	91.3	84.1	76.4	65.8	60.9	60.9
107.5°	78.0	78.0	81.9	91.9	105.7	123.4	125.1	99.0	86.9	81.3	80.8
110°	88.0	88.0	91.3	99.6	117.9	142.8	141.6	122.3	107.3	100.2	99.0



REPORT NUMBER: P832855
 CATALOG NUMBER: TTN-D0-740-U-WQ-SG-UPL1

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	90.2	90.7	95.2	107.9	127.8	138.9	133.9	126.2	119.5	114.0	112.9
115°	93.5	93.5	98.5	110.7	121.7	126.2	120.6	114.5	110.1	107.9	109.0
117.5°	92.4	94.1	95.2	101.8	109.0	112.3	109.6	101.3	97.9	96.8	95.2
120°	85.8	85.8	86.9	90.2	94.1	95.7	94.6	89.1	86.3	85.8	84.7
122.5°	76.4	76.9	76.4	78.0	80.8	82.4	81.3	76.9	75.8	75.8	74.7
125°	67.0	67.0	66.4	67.5	69.2	68.6	69.2	67.0	66.4	66.4	65.8
127.5°	60.3	59.8	58.7	59.2	59.8	59.8	60.3	58.1	58.7	59.2	58.7
130°	53.7	53.7	52.6	52.6	52.6	51.5	52.6	51.5	52.0	52.6	53.1
132.5°	47.6	47.6	45.9	45.4	45.4	45.4	45.9	45.4	46.5	47.6	47.6
135°	42.6	42.6	40.9	41.5	41.5	40.9	41.5	40.9	42.1	42.6	42.6
137.5°	38.7	38.7	37.6	37.6	37.6	37.1	37.6	37.6	38.2	39.3	39.8
140°	35.4	35.4	34.9	34.9	34.3	34.9	34.9	34.9	35.4	36.0	36.0
142.5°	33.8	33.2	32.6	32.1	32.6	32.6	32.6	32.1	32.6	33.8	33.8
145°	31.0	31.0	30.4	30.4	30.4	31.0	30.4	30.4	31.0	31.0	31.5
147.5°	29.3	29.3	28.8	29.3	29.3	29.3	29.3	28.8	29.3	29.3	29.9
150°	28.8	28.2	27.7	28.2	28.2	27.7	27.7	27.7	27.7	28.2	28.2
152.5°	27.1	27.1	26.6	27.1	26.6	26.6	26.6	26.6	26.6	27.1	27.7
155°	26.0	26.0	25.5	26.0	26.0	26.0	26.0	26.0	26.0	26.0	26.0
157.5°	24.9	25.5	24.9	24.9	24.9	24.9	24.9	24.9	24.9	25.5	25.5
160°	24.3	24.3	24.3	24.3	23.8	23.8	23.8	24.3	24.3	24.3	24.9
162.5°	23.8	23.8	23.8	23.8	23.2	23.2	23.2	23.2	23.8	23.8	24.3
165°	23.8	23.2	23.2	23.2	22.7	22.7	22.7	22.7	23.2	23.8	23.2
167.5°	22.7	22.7	22.7	22.7	22.7	22.1	22.1	22.7	22.7	22.7	23.2
170°	22.7	22.7	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.7
172.5°	22.7	22.7	22.7	22.7	22.1	22.1	22.1	22.1	22.1	22.7	22.7
175°	22.7	22.7	22.7	22.7	22.1	22.1	22.1	22.7	22.7	22.7	22.1
177.5°	22.7	22.7	22.7	22.7	22.1	22.7	22.7	22.7	22.7	22.7	22.7
180°	22.7	22.7	22.7	22.7	22.7	22.7	22.7	22.7	22.7	22.7	22.7

(END OF REPORT)