

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P833551

Luminaire Tested: **TTN-D2-740-U-CQ-UPL1**

Issue Date: 5/15/2024

**Test Information**

Test Method: LM-79-08  
Report Number: P833551  
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G3-2308-121-4) AND  
Test Lab: INNOVATION CENTER  
Issue Date: 5/15/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: TTN-D2-740-U-CQ-UPL1  
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE WITH UPLIGHT  
4000K, 70 CRI LEDS AND CONCENTRATED DISTRIBUTION  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5639.9 lumens  
Efficiency: N/A  
Efficacy: 125.1 lumens/watt  
Luminous Opening: Vertical Cylinder (Dia: 0.71' x H: 0.1')  
IES Classification: Type V - Short  
BUG Rating: B2 - U3 - G1  
  
Input Watts (W): 45.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P833551  
 CATALOG NUMBER: TTN-D2-740-U-CQ-UPL1

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 2.2 fc  
 Type V - Short - N/A

REPORT NUMBER: P833551  
CATALOG NUMBER: TTN-D2-740-U-CQ-UPL1

### Luminous Intensity Polar Plot



REPORT NUMBER: P833551  
 CATALOG NUMBER: TTN-D2-740-U-CQ-UPL1


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	2658.2	161.7	2820.0
	% Fixture	47.1	2.9	50.0
<b>Street Side</b>	Lumens	2658.2	161.7	2820.0
	% Fixture	47.1	2.9	50.0
<b>Total</b>	Lumens	5316.5	323.4	5639.9
	% Fixture	94.3	5.7	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	126.7	2.2
10°-20°	368.0	6.5
20°-30°	592.6	10.5
30°-40°	797.1	14.1
40°-50°	983.4	17.4
50°-60°	1055.1	18.7
60°-70°	855.6	15.2
70°-80°	453.5	8.0
80°-90°	84.3	1.5
90°-100°	7.2	0.1
100°-110°	73.4	1.3
110°-120°	107.3	1.9
120°-130°	62.3	1.1
130°-140°	33.0	0.6
140°-150°	19.6	0.3
150°-160°	12.1	0.2
160°-170°	6.6	0.1
170°-180°	2.1	0.0
0°-90°	5316.5	94.3
0°-180°	5639.9	100.0

**Coefficient of Utilization**




REPORT NUMBER: P833551  
 CATALOG NUMBER: TTN-D2-740-U-CQ-UPL1

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	543.7	9.6			
FM (30°-60°)	1417.8	25.1			
FH (60°-80°)	654.6	11.6			G0/660
FVH (80°-90°)	42.2	0.7			G1/100
BL (0°-30°)	543.7	9.6	B2/1000		
BM (30°-60°)	1417.8	25.1	B2/2500		
BH (60°-80°)	654.6	11.6	B2/1000		G0/660
BVH (80°-90°)	42.2	0.7			G1/100
UL (90°-100°)	7.2	0.1		U1/10	
UH (100°-180°)	316.2	5.6		U3/500	

**BUG Rating: B2-U3-G1**  
 Type V Short





REPORT NUMBER: P833551  
 CATALOG NUMBER: TTN-D2-740-U-CQ-UPL1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	1344.2	1344.2	1344.2	1344.2	1344.2	1344.2	1344.2	1344.2	1344.2	1344.2	1344.2
2.5°	1335.5	1335.5	1335.5	1335.5	1335.5	1335.5	1335.5	1335.5	1335.5	1335.5	1339.9
5°	1335.5	1335.5	1335.5	1335.5	1331.2	1335.5	1335.5	1335.5	1335.5	1335.5	1335.5
7.5°	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8
10°	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8
12.5°	1305.1	1305.1	1305.1	1305.1	1305.1	1305.1	1305.1	1305.1	1305.1	1305.1	1305.1
15°	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1296.4	1296.4
17.5°	1292.0	1292.0	1292.0	1292.0	1296.4	1296.4	1296.4	1292.0	1292.0	1292.0	1292.0
20°	1283.3	1283.3	1283.3	1287.7	1287.7	1287.7	1287.7	1287.7	1283.3	1283.3	1283.3
22.5°	1279.0	1279.0	1279.0	1279.0	1283.3	1283.3	1283.3	1283.3	1279.0	1279.0	1279.0
25°	1274.6	1274.6	1279.0	1279.0	1283.3	1283.3	1283.3	1279.0	1279.0	1274.6	1274.6
27.5°	1274.6	1274.6	1279.0	1279.0	1283.3	1283.3	1283.3	1283.3	1279.0	1274.6	1274.6
30°	1270.3	1274.6	1274.6	1279.0	1283.3	1283.3	1283.3	1279.0	1274.6	1270.3	1270.3
32.5°	1265.9	1265.9	1270.3	1274.6	1279.0	1279.0	1279.0	1274.6	1270.3	1265.9	1261.6
35°	1261.6	1261.6	1261.6	1270.3	1274.6	1274.6	1274.6	1270.3	1261.6	1257.2	1257.2
37.5°	1252.9	1252.9	1261.6	1265.9	1274.6	1274.6	1274.6	1265.9	1257.2	1252.9	1248.5
40°	1252.9	1252.9	1261.6	1265.9	1279.0	1279.0	1274.6	1265.9	1257.2	1248.5	1244.2
42.5°	1248.5	1252.9	1261.6	1274.6	1287.7	1287.7	1283.3	1270.3	1257.2	1248.5	1244.2
45°	1248.5	1248.5	1261.6	1279.0	1296.4	1300.7	1292.0	1279.0	1261.6	1244.2	1244.2
47.5°	1239.8	1239.8	1257.2	1279.0	1300.7	1305.1	1300.7	1279.0	1257.2	1244.2	1239.8
50°	1218.1	1218.1	1239.8	1265.9	1292.0	1300.7	1292.0	1274.6	1244.2	1226.8	1222.4
52.5°	1183.3	1183.3	1205.0	1239.8	1265.9	1279.0	1270.3	1248.5	1218.1	1192.0	1187.6
55°	1131.1	1135.4	1157.2	1196.3	1226.8	1239.8	1231.1	1205.0	1170.2	1144.1	1135.4
57.5°	1070.2	1070.2	1100.6	1139.8	1170.2	1183.3	1174.6	1148.5	1109.3	1083.2	1074.5
60°	987.5	991.9	1018.0	1070.2	1100.6	1113.7	1105.0	1074.5	1031.0	1000.6	991.9
62.5°	904.9	909.2	935.3	978.8	1013.6	1022.3	1013.6	983.2	944.0	913.6	904.9
65°	809.1	813.5	843.9	883.1	909.2	922.3	909.2	883.1	848.3	817.8	813.5
67.5°	709.1	713.4	743.9	778.7	804.8	813.5	800.4	778.7	743.9	717.8	709.1
70°	604.7	609.0	635.1	665.6	687.3	696.0	687.3	661.2	635.1	609.0	604.7
72.5°	495.9	500.3	526.4	552.5	569.9	578.6	565.5	548.1	522.0	500.3	495.9
75°	391.5	391.5	413.3	435.0	452.4	456.8	448.1	435.0	413.3	395.9	387.2
77.5°	291.5	291.5	313.2	326.3	335.0	343.7	335.0	321.9	308.9	291.5	291.5
80°	195.8	195.8	213.2	221.9	230.6	234.9	230.6	221.9	213.2	200.1	195.8
82.5°	117.5	117.5	126.2	134.9	134.9	139.2	139.2	134.9	126.2	117.5	117.5
85°	52.2	47.9	56.6	60.9	60.9	65.3	65.3	60.9	56.6	52.2	52.2
87.5°	4.4	8.7	8.7	13.1	13.1	13.1	13.1	13.1	8.7	8.7	8.7
90°	2.8	2.8	3.3	3.3	3.3	3.3	3.3	3.3	3.3	2.8	2.8
92.5°	2.8	2.8	2.8	3.9	4.4	3.9	4.4	3.3	3.3	2.8	2.8
95°	3.3	3.3	3.9	5.0	6.1	6.6	6.6	3.9	3.9	3.3	3.3
97.5°	4.4	5.0	5.0	6.1	10.0	18.3	11.1	5.5	5.5	5.0	4.4
100°	7.2	7.7	7.7	13.8	29.3	39.3	28.2	14.4	10.5	7.7	7.7
102.5°	23.2	24.3	29.9	44.8	66.4	60.3	50.9	48.1	33.2	26.6	25.5
105°	59.2	58.7	63.1	74.7	93.0	91.3	84.1	76.4	65.8	60.9	60.9
107.5°	78.0	78.0	81.9	91.9	105.7	123.4	125.1	99.0	86.9	81.3	80.8
110°	88.0	88.0	91.3	99.6	117.9	142.8	141.6	122.3	107.3	100.2	99.0



REPORT NUMBER: P833551  
 CATALOG NUMBER: TTN-D2-740-U-CQ-UPL1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	90.2	90.7	95.2	107.9	127.8	138.9	133.9	126.2	119.5	114.0	112.9
115°	93.5	93.5	98.5	110.7	121.7	126.2	120.6	114.5	110.1	107.9	109.0
117.5°	92.4	94.1	95.2	101.8	109.0	112.3	109.6	101.3	97.9	96.8	95.2
120°	85.8	85.8	86.9	90.2	94.1	95.7	94.6	89.1	86.3	85.8	84.7
122.5°	76.4	76.9	76.4	78.0	80.8	82.4	81.3	76.9	75.8	75.8	74.7
125°	67.0	67.0	66.4	67.5	69.2	68.6	69.2	67.0	66.4	66.4	65.8
127.5°	60.3	59.8	58.7	59.2	59.8	59.8	60.3	58.1	58.7	59.2	58.7
130°	53.7	53.7	52.6	52.6	52.6	51.5	52.6	51.5	52.0	52.6	53.1
132.5°	47.6	47.6	45.9	45.4	45.4	45.4	45.9	45.4	46.5	47.6	47.6
135°	42.6	42.6	40.9	41.5	41.5	40.9	41.5	40.9	42.1	42.6	42.6
137.5°	38.7	38.7	37.6	37.6	37.6	37.1	37.6	37.6	38.2	39.3	39.8
140°	35.4	35.4	34.9	34.9	34.3	34.9	34.9	34.9	35.4	36.0	36.0
142.5°	33.8	33.2	32.6	32.1	32.6	32.6	32.6	32.1	32.6	33.8	33.8
145°	31.0	31.0	30.4	30.4	30.4	31.0	30.4	30.4	31.0	31.0	31.5
147.5°	29.3	29.3	28.8	29.3	29.3	29.3	29.3	28.8	29.3	29.3	29.9
150°	28.8	28.2	27.7	28.2	28.2	27.7	27.7	27.7	27.7	28.2	28.2
152.5°	27.1	27.1	26.6	27.1	26.6	26.6	26.6	26.6	26.6	27.1	27.7
155°	26.0	26.0	25.5	26.0	26.0	26.0	26.0	26.0	26.0	26.0	26.0
157.5°	24.9	25.5	24.9	24.9	24.9	24.9	24.9	24.9	24.9	25.5	25.5
160°	24.3	24.3	24.3	24.3	23.8	23.8	23.8	24.3	24.3	24.3	24.9
162.5°	23.8	23.8	23.8	23.8	23.2	23.2	23.2	23.2	23.8	23.8	24.3
165°	23.8	23.2	23.2	23.2	22.7	22.7	22.7	22.7	23.2	23.8	23.2
167.5°	22.7	22.7	22.7	22.7	22.7	22.1	22.1	22.7	22.7	22.7	23.2
170°	22.7	22.7	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.7
172.5°	22.7	22.7	22.7	22.7	22.1	22.1	22.1	22.1	22.1	22.7	22.7
175°	22.7	22.7	22.7	22.7	22.1	22.1	22.1	22.7	22.7	22.7	22.1
177.5°	22.7	22.7	22.7	22.7	22.1	22.7	22.7	22.7	22.7	22.7	22.7
180°	22.7	22.7	22.7	22.7	22.7	22.7	22.7	22.7	22.7	22.7	22.7

(END OF REPORT)