

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P832687

Luminaire Tested: **TTN-D3-740-U-MQ-CG**

Issue Date: 5/14/2024

Test Information

Test Method: LM-79-08
Report Number: P832687
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2312-254-13)
Test Lab: INNOVATION CENTER
Issue Date: 5/14/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TTN-D3-740-U-MQ-CG
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE
4000K, 70 CRI LEDS AND MEDIUM DISTRIBUTION WITH CLEAR GLASS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7133 lumens
Efficiency: N/A
Efficacy: 120.5 lumens/watt
Luminous Opening: Circular (Dia: 0.71' x H: 0')
IES Classification: Type V - Short
BUG Rating: B3 - U0 - G1


Input Watts (W): 59.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P832687
 CATALOG NUMBER: TTN-D3-740-U-MQ-CG

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 2.7 fc
 Type V - Short - N/A

REPORT NUMBER: P832687
CATALOG NUMBER: TTN-D3-740-U-MQ-CG

Luminous Intensity Polar Plot



REPORT NUMBER: P832687

CATALOG NUMBER: TTN-D3-740-U-MQ-CG


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3566.5	0.0	3566.5
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	3566.5	0.0	3566.5
	% Fixture	50.0	0.0	50.0
Total	Lumens	7133.0	0.0	7133.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.4	2.2
10°-20°	461.0	6.5
20°-30°	741.6	10.4
30°-40°	990.7	13.9
40°-50°	1203.7	16.9
50°-60°	1398.6	19.6
60°-70°	1290.3	18.1
70°-80°	755.4	10.6
80°-90°	132.3	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	7133.0	100.0
0°-180°	7133.0	100.0

Coefficient of Utilization




REPORT NUMBER: P832687
 CATALOG NUMBER: TTN-D3-740-U-MQ-CG

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	681.0	9.5			
FM (30°-60°)	1796.5	25.2			
FH (60°-80°)	1022.8	14.3			G1/1800
FVH (80°-90°)	66.2	0.9			G1/100
BL (0°-30°)	681.0	9.5	B2/1000		
BM (30°-60°)	1796.5	25.2	B2/2500		
BH (60°-80°)	1022.8	14.3	B3/2500		G1/1800
BVH (80°-90°)	66.2	0.9			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G1
 Type V Short





REPORT NUMBER: P832687

CATALOG NUMBER: TTN-D3-740-U-MQ-CG

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	1696.9	1696.9	1696.9	1696.9	1696.9	1696.9	1696.9	1696.9	1696.9	1696.9	1696.9
2.5°	1679.6	1685.3	1679.6	1679.6	1679.6	1679.6	1679.6	1679.6	1679.6	1679.6	1685.3
5°	1685.3	1685.3	1685.3	1685.3	1679.6	1679.6	1679.6	1679.6	1679.6	1685.3	1685.3
7.5°	1668.0	1668.0	1668.0	1668.0	1668.0	1662.2	1668.0	1668.0	1668.0	1668.0	1668.0
10°	1650.6	1650.6	1650.6	1650.6	1650.6	1650.6	1650.6	1650.6	1650.6	1650.6	1650.6
12.5°	1639.0	1639.0	1639.0	1639.0	1639.0	1639.0	1639.0	1639.0	1639.0	1633.2	1633.2
15°	1627.4	1627.4	1627.4	1627.4	1633.2	1633.2	1627.4	1627.4	1627.4	1627.4	1627.4
17.5°	1615.8	1615.8	1615.8	1615.8	1621.6	1621.6	1621.6	1615.8	1615.8	1615.8	1615.8
20°	1604.3	1604.3	1604.3	1604.3	1610.1	1610.1	1610.1	1610.1	1610.1	1604.3	1604.3
22.5°	1598.5	1598.5	1598.5	1598.5	1604.3	1604.3	1604.3	1604.3	1598.5	1598.5	1598.5
25°	1592.7	1598.5	1598.5	1598.5	1604.3	1610.1	1610.1	1604.3	1598.5	1592.7	1592.7
27.5°	1598.5	1598.5	1598.5	1604.3	1604.3	1610.1	1610.1	1604.3	1598.5	1598.5	1598.5
30°	1592.7	1592.7	1592.7	1598.5	1604.3	1610.1	1604.3	1604.3	1598.5	1592.7	1592.7
32.5°	1581.1	1581.1	1586.9	1592.7	1598.5	1598.5	1598.5	1592.7	1586.9	1581.1	1581.1
35°	1569.5	1569.5	1569.5	1575.3	1586.9	1586.9	1586.9	1581.1	1575.3	1569.5	1563.7
37.5°	1552.1	1557.9	1557.9	1569.5	1575.3	1581.1	1575.3	1569.5	1557.9	1552.1	1552.1
40°	1540.6	1540.6	1546.3	1557.9	1569.5	1569.5	1563.7	1557.9	1546.3	1540.6	1540.6
42.5°	1523.2	1523.2	1534.8	1546.3	1563.7	1563.7	1557.9	1546.3	1534.8	1523.2	1523.2
45°	1523.2	1523.2	1534.8	1557.9	1569.5	1581.1	1569.5	1557.9	1534.8	1523.2	1517.4
47.5°	1529.0	1529.0	1540.6	1569.5	1592.7	1604.3	1586.9	1563.7	1540.6	1529.0	1523.2
50°	1517.4	1523.2	1546.3	1575.3	1604.3	1610.1	1604.3	1569.5	1546.3	1517.4	1517.4
52.5°	1523.2	1523.2	1552.1	1598.5	1627.4	1639.0	1627.4	1598.5	1546.3	1517.4	1517.4
55°	1511.6	1505.8	1546.3	1598.5	1644.8	1668.0	1644.8	1598.5	1540.6	1505.8	1500.0
57.5°	1459.5	1459.5	1511.6	1563.7	1621.6	1633.2	1615.8	1563.7	1505.8	1459.5	1447.9
60°	1390.0	1395.8	1447.9	1505.8	1557.9	1563.7	1552.1	1505.8	1447.9	1395.8	1378.4
62.5°	1314.7	1326.3	1378.4	1436.3	1500.0	1511.6	1494.2	1436.3	1366.8	1332.1	1303.1
65°	1204.6	1222.0	1279.9	1343.6	1413.1	1407.3	1407.3	1337.9	1285.7	1227.8	1198.9
67.5°	1083.0	1100.4	1140.9	1227.8	1285.7	1279.9	1274.1	1227.8	1140.9	1100.4	1083.0
70°	949.8	961.4	1001.9	1088.8	1140.9	1146.7	1129.4	1083.0	1001.9	973.0	944.0
72.5°	793.4	799.2	857.2	926.6	978.8	973.0	967.2	926.6	851.4	822.4	787.7
75°	625.5	631.3	683.4	747.1	787.7	781.9	776.1	747.1	683.4	648.7	619.7
77.5°	469.1	463.3	515.4	561.8	584.9	590.7	579.2	556.0	509.7	480.7	463.3
80°	307.0	301.2	347.5	382.2	399.6	399.6	393.8	376.5	341.7	318.5	307.0
82.5°	173.7	168.0	196.9	220.1	237.5	231.7	225.9	214.3	196.9	179.5	168.0
85°	63.7	63.7	81.1	92.7	104.2	104.2	98.5	92.7	75.3	69.5	63.7
87.5°	5.8	5.8	11.6	17.4	17.4	17.4	11.6	11.6	5.8	5.8	5.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)