

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P832883

Luminaire Tested: **TTN-D0-750-U-WQ-CG-UPL2**

Issue Date: 5/15/2024

Test Information

Test Method: LM-79-08
Report Number: P832883
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G3-2308-121-4) AND
Test Lab: INNOVATION CENTER
Issue Date: 5/15/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: TTN-D0-750-U-WQ-CG-UPL2
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE WITH UPLIGHT
5000K, 70 CRI LEDS AND WIDE DISTRIBUTION WITH CLEAR GLASS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1739.5 lumens
Efficiency: N/A
Efficacy: 114.4 lumens/watt
Luminous Opening: Vertical Cylinder (Dia: 0.71' x H: 0.1')
IES Classification: Type V - Short
BUG Rating: B1 - U4 - G1


Input Watts (W): 15.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P832883
 CATALOG NUMBER: TTN-D0-750-U-WQ-CG-UPL2

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.2 fc
 Type V - Short - N/A

REPORT NUMBER: P832883
CATALOG NUMBER: TTN-D0-750-U-WQ-CG-UPL2

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P832883
 CATALOG NUMBER: TTN-D0-750-U-WQ-CG-UPL2


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	577.3	292.5	869.8
	% Fixture	33.2	16.8	50.0
Street Side	Lumens	577.3	292.5	869.8
	% Fixture	33.2	16.8	50.0
Total	Lumens	1154.6	584.9	1739.5
	% Fixture	66.4	33.6	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	10.4	0.6
10°-20°	33.6	1.9
20°-30°	70.7	4.1
30°-40°	127.5	7.3
40°-50°	202.6	11.6
50°-60°	270.4	15.5
60°-70°	261.2	15.0
70°-80°	151.4	8.7
80°-90°	26.9	1.5
90°-100°	13.1	0.8
100°-110°	132.7	7.6
110°-120°	194.0	11.2
120°-130°	112.6	6.5
130°-140°	59.7	3.4
140°-150°	35.4	2.0
150°-160°	21.8	1.3
160°-170°	11.9	0.7
170°-180°	3.9	0.2
0°-90°	1154.6	66.4
0°-180°	1739.5	100.0

Coefficient of Utilization




REPORT NUMBER: P832883
 CATALOG NUMBER: TTN-D0-750-U-WQ-CG-UPL2

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	57.4	3.3			
FM (30°-60°)	300.2	17.3			
FH (60°-80°)	206.3	11.9			G0/660
FVH (80°-90°)	13.4	0.8			G1/100
BL (0°-30°)	57.4	3.3	B0/110		
BM (30°-60°)	300.2	17.3	B1/1000		
BH (60°-80°)	206.3	11.9	B1/500		G0/660
BVH (80°-90°)	13.4	0.8			G1/100
UL (90°-100°)	13.1	0.8		U2/50	
UH (100°-180°)	571.8	32.9		U4/1000	

BUG Rating: B1-U4-G1
 Type V Short





REPORT NUMBER: P832883

CATALOG NUMBER: TTN-D0-750-U-WQ-CG-UPL2

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	109.0	109.0	109.0	109.0	109.0	109.0	109.0	109.0	109.0	109.0	109.0
2.5°	108.0	108.0	108.0	108.0	108.0	108.0	108.0	108.0	108.0	108.0	108.0
5°	109.0	109.0	109.0	109.0	109.0	109.0	109.0	109.0	109.0	109.0	109.0
7.5°	108.0	108.0	109.0	109.0	109.0	109.0	109.0	109.0	109.0	108.0	108.0
10°	109.0	109.0	109.0	110.0	110.0	110.0	110.0	110.0	109.0	109.0	109.0
12.5°	111.0	111.0	112.0	112.0	112.0	112.0	112.0	112.0	112.0	111.0	111.0
15°	116.0	116.0	116.0	117.0	117.0	117.0	117.0	117.0	116.0	116.0	116.0
17.5°	121.0	121.0	122.0	122.0	123.0	123.0	123.0	122.0	122.0	122.0	122.0
20°	128.0	128.0	129.0	129.0	130.0	131.0	131.0	130.0	129.0	129.0	129.0
22.5°	137.0	138.0	138.0	138.0	139.0	141.0	140.0	139.0	138.0	138.0	138.0
25°	148.0	149.0	150.0	150.0	151.0	153.0	153.0	150.0	150.0	150.0	150.0
27.5°	161.0	162.0	163.0	163.0	164.0	166.0	165.0	163.0	163.0	162.0	162.0
30°	173.0	174.0	175.0	176.0	177.0	178.0	178.0	176.0	175.0	174.0	173.0
32.5°	185.0	185.0	187.0	189.0	191.0	191.0	192.0	189.0	187.0	185.0	184.0
35°	197.0	198.0	199.0	202.0	205.0	206.0	205.0	202.0	199.0	197.0	197.0
37.5°	210.0	211.0	212.0	216.0	219.0	221.0	219.0	216.0	212.0	210.0	209.0
40°	224.0	225.0	226.0	231.0	234.0	236.0	233.0	230.0	226.0	224.0	223.0
42.5°	237.0	239.0	241.0	247.0	252.0	254.0	251.0	246.0	242.0	237.0	236.0
45°	253.0	255.0	258.0	264.0	269.0	272.0	268.0	263.0	257.0	253.0	252.0
47.5°	266.0	268.0	271.0	279.0	286.0	288.0	284.0	278.0	270.0	265.0	264.0
50°	276.0	278.0	284.0	293.0	301.0	303.0	299.0	291.0	282.0	275.0	274.0
52.5°	284.0	286.0	293.0	305.0	314.0	317.0	312.0	303.0	291.0	283.0	282.0
55°	288.0	289.0	298.0	311.0	320.0	324.0	319.0	309.0	296.0	287.0	286.0
57.5°	285.0	286.0	296.0	310.0	320.0	325.0	320.0	308.0	294.0	285.0	284.0
60°	279.0	279.0	288.0	304.0	316.0	319.0	314.0	302.0	287.0	278.0	277.0
62.5°	268.0	267.0	278.0	292.0	304.0	307.0	303.0	291.0	276.0	267.0	266.0
65°	247.0	245.0	261.0	274.0	285.0	288.0	285.0	274.0	260.0	246.0	244.0
67.5°	222.0	219.0	234.0	249.0	259.0	263.0	259.0	250.0	234.0	220.0	219.0
70°	196.0	193.0	205.0	218.0	229.0	231.0	227.0	218.0	203.0	194.0	194.0
72.5°	165.0	162.0	173.0	183.0	194.0	196.0	192.0	184.0	173.0	164.0	163.0
75°	131.0	128.0	138.0	146.0	157.0	158.0	156.0	147.0	138.0	129.0	129.0
77.5°	97.0	94.0	102.0	109.0	118.0	118.0	117.0	110.0	102.0	96.0	96.0
80°	64.0	62.0	69.0	72.0	80.0	80.0	79.0	74.0	68.0	64.0	63.0
82.5°	36.0	34.0	40.0	41.0	47.0	47.0	46.0	42.0	38.0	35.0	35.0
85°	14.0	12.0	16.0	17.0	20.0	20.0	19.0	18.0	15.0	13.0	13.0
87.5°	1.0	1.0	2.0	2.0	3.0	3.0	3.0	2.0	2.0	1.0	1.0
90°	5.0	5.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	5.0	5.0
92.5°	5.0	5.0	5.0	7.0	8.0	7.0	8.0	6.0	6.0	5.0	5.0
95°	6.0	6.0	7.0	9.0	11.0	12.0	12.0	7.0	7.0	6.0	6.0
97.5°	8.0	9.0	9.0	11.0	18.0	33.0	20.0	10.0	10.0	9.0	8.0
100°	13.0	14.0	14.0	25.0	53.0	71.1	51.0	26.0	19.0	14.0	14.0
102.5°	42.0	44.0	54.0	81.1	120.1	109.1	92.1	87.1	60.0	48.0	46.0
105°	107.1	106.1	114.1	135.1	168.1	165.1	152.1	138.1	119.1	110.1	110.1
107.5°	141.1	141.1	148.1	166.1	191.1	223.2	226.2	179.1	157.1	147.1	146.1
110°	159.1	159.1	165.1	180.1	213.2	258.2	256.2	221.2	194.1	181.1	179.1



REPORT NUMBER: P832883
 CATALOG NUMBER: TTN-D0-750-U-WQ-CG-UPL2

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	163.1	164.1	172.1	195.1	231.2	251.2	242.2	228.2	216.2	206.2	204.2
115°	169.1	169.1	178.1	200.2	220.2	228.2	218.2	207.2	199.2	195.1	197.1
117.5°	167.1	170.1	172.1	184.1	197.1	203.2	198.1	183.1	177.1	175.1	172.1
120°	155.1	155.1	157.1	163.1	170.1	173.1	171.1	161.1	156.1	155.1	153.1
122.5°	138.1	139.1	138.1	141.1	146.1	149.1	147.1	139.1	137.1	137.1	135.1
125°	121.1	121.1	120.1	122.1	125.1	124.1	125.1	121.1	120.1	120.1	119.1
127.5°	109.1	108.1	106.1	107.1	108.1	108.1	109.1	105.1	106.1	107.1	106.1
130°	97.1	97.1	95.1	95.1	95.1	93.1	95.1	93.1	94.1	95.1	96.1
132.5°	86.1	86.1	83.1	82.1	82.1	82.1	83.1	82.1	84.1	86.1	86.1
135°	77.1	77.1	74.1	75.1	75.1	74.1	75.1	74.1	76.1	77.1	77.1
137.5°	70.1	70.1	68.1	68.1	68.1	67.1	68.1	68.1	69.1	71.1	72.1
140°	64.0	64.0	63.0	63.0	62.0	63.0	63.0	63.0	64.0	65.0	65.0
142.5°	61.0	60.0	59.0	58.0	59.0	59.0	59.0	58.0	59.0	61.0	61.0
145°	56.0	56.0	55.0	55.0	55.0	56.0	55.0	55.0	56.0	56.0	57.0
147.5°	53.0	53.0	52.0	53.0	53.0	53.0	53.0	52.0	53.0	53.0	54.0
150°	52.0	51.0	50.0	51.0	51.0	50.0	50.0	50.0	50.0	51.0	51.0
152.5°	49.0	49.0	48.0	49.0	48.0	48.0	48.0	48.0	48.0	49.0	50.0
155°	47.0	47.0	46.0	47.0	47.0	47.0	47.0	47.0	47.0	47.0	47.0
157.5°	45.0	46.0	45.0	45.0	45.0	45.0	45.0	45.0	45.0	46.0	46.0
160°	44.0	44.0	44.0	44.0	43.0	43.0	43.0	44.0	44.0	44.0	45.0
162.5°	43.0	43.0	43.0	43.0	42.0	42.0	42.0	42.0	43.0	43.0	44.0
165°	43.0	42.0	42.0	42.0	41.0	41.0	41.0	41.0	42.0	43.0	42.0
167.5°	41.0	41.0	41.0	41.0	41.0	40.0	40.0	41.0	41.0	41.0	42.0
170°	41.0	41.0	40.0	40.0	40.0	40.0	40.0	40.0	40.0	40.0	41.0
172.5°	41.0	41.0	41.0	41.0	40.0	40.0	40.0	40.0	40.0	41.0	41.0
175°	41.0	41.0	41.0	41.0	40.0	40.0	40.0	41.0	41.0	41.0	40.0
177.5°	41.0	41.0	41.0	41.0	40.0	41.0	41.0	41.0	41.0	41.0	41.0
180°	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0

(END OF REPORT)