

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P833248

Luminaire Tested: **TTN-D1-750-U-WQ-UPL1**

Issue Date: 5/15/2024

**Test Information**

Test Method: LM-79-08  
Report Number: P833248  
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G3-2308-121-4) AND  
Test Lab: INNOVATION CENTER  
Issue Date: 5/15/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: TTN-D1-750-U-WQ-UPL1  
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE WITH UPLIGHT  
5000K, 70 CRI LEDS AND WIDE DISTRIBUTION  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3684.9 lumens  
Efficiency: N/A  
Efficacy: 127.1 lumens/watt  
Luminous Opening: Vertical Cylinder (Dia: 0.71' x H: 0.1')  
IES Classification: Type V - Short  
BUG Rating: B2 - U3 - G1


Input Watts (W): 29  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P833248  
 CATALOG NUMBER: TTN-D1-750-U-WQ-UPL1

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.5 fc  
 Type V - Short - N/A

REPORT NUMBER: P833248  
CATALOG NUMBER: TTN-D1-750-U-WQ-UPL1

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral    - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P833248

CATALOG NUMBER: TTN-D1-750-U-WQ-UPL1


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1680.7	161.7	1842.4
	% Fixture	45.6	4.4	50.0
<b>Street Side</b>	Lumens	1680.7	161.7	1842.4
	% Fixture	45.6	4.4	50.0
<b>Total</b>	Lumens	3361.4	323.4	3684.9
	% Fixture	91.2	8.8	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	26.8	0.7
10°-20°	85.5	2.3
20°-30°	179.3	4.9
30°-40°	325.3	8.8
40°-50°	530.3	14.4
50°-60°	742.2	20.1
60°-70°	774.9	21.0
70°-80°	553.6	15.0
80°-90°	143.7	3.9
90°-100°	7.2	0.2
100°-110°	73.4	2.0
110°-120°	107.3	2.9
120°-130°	62.3	1.7
130°-140°	33.0	0.9
140°-150°	19.6	0.5
150°-160°	12.1	0.3
160°-170°	6.6	0.2
170°-180°	2.1	0.1
0°-90°	3361.4	91.2
0°-180°	3684.9	100.0

**Coefficient of Utilization**



REPORT NUMBER: P833248


CATALOG NUMBER: TTN-D1-750-U-WQ-UPL1

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	145.8	4.0			
FM (30°-60°)	798.9	21.7			
FH (60°-80°)	664.2	18.0			G1/1800
FVH (80°-90°)	71.8	1.9			G1/100
BL (0°-30°)	145.8	4.0	B1/500		
BM (30°-60°)	798.9	21.7	B1/1000		
BH (60°-80°)	664.2	18.0	B2/1000		G1/1800
BVH (80°-90°)	71.8	1.9			G1/100
UL (90°-100°)	7.2	0.2		U1/10	
UH (100°-180°)	316.2	8.6		U3/500	

**BUG Rating: B2-U3-G1**

Type V Short





REPORT NUMBER: P833248  
 CATALOG NUMBER: TTN-D1-750-U-WQ-UPL1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	284.9	284.9	284.9	284.9	284.9	284.9	284.9	284.9	284.9	284.9	284.9
2.5°	282.1	282.1	282.1	282.1	282.1	282.1	282.1	282.1	282.1	282.1	282.1
5°	282.1	282.1	282.1	282.1	282.1	282.1	282.1	282.1	282.1	282.1	282.1
7.5°	276.6	276.6	279.4	279.4	279.4	279.4	279.4	279.4	279.4	279.4	279.4
10°	276.6	276.6	279.4	279.4	282.1	282.1	282.1	279.4	279.4	276.6	276.6
12.5°	282.1	282.1	282.1	284.9	287.7	287.7	287.7	284.9	284.9	282.1	282.1
15°	290.4	293.2	293.2	296.0	298.7	298.7	298.7	296.0	296.0	293.2	293.2
17.5°	307.0	307.0	307.0	309.8	312.6	315.3	315.3	309.8	309.8	307.0	309.8
20°	323.6	326.4	326.4	329.1	331.9	334.7	331.9	329.1	326.4	326.4	326.4
22.5°	348.5	348.5	351.3	351.3	356.8	356.8	356.8	351.3	351.3	351.3	351.3
25°	376.2	376.2	378.9	381.7	387.2	387.2	384.5	378.9	378.9	378.9	381.7
27.5°	409.4	409.4	412.1	412.1	417.7	417.7	414.9	412.1	412.1	412.1	414.9
30°	439.8	439.8	445.3	448.1	450.8	450.8	450.8	445.3	445.3	442.5	442.5
32.5°	467.4	470.2	473.0	481.3	486.8	484.0	486.8	481.3	475.7	473.0	473.0
35°	497.9	500.6	506.2	514.5	522.8	522.8	522.8	514.5	508.9	503.4	506.2
37.5°	533.8	533.8	542.1	550.4	561.5	564.2	561.5	553.2	544.9	539.4	539.4
40°	572.5	572.5	580.8	589.1	603.0	605.7	603.0	591.9	580.8	578.1	578.1
42.5°	611.3	611.3	622.3	630.6	647.2	652.8	647.2	633.4	622.3	614.0	616.8
45°	652.8	655.5	669.4	686.0	705.3	713.6	705.3	688.7	672.1	655.5	655.5
47.5°	699.8	699.8	716.4	735.7	757.9	766.2	755.1	738.5	716.4	702.5	702.5
50°	730.2	733.0	755.1	780.0	807.7	813.2	804.9	780.0	755.1	735.7	733.0
52.5°	760.6	763.4	788.3	824.2	851.9	860.2	849.1	824.2	788.3	763.4	763.4
55°	780.0	785.5	813.2	851.9	882.3	896.2	879.6	851.9	810.4	782.8	780.0
57.5°	782.8	788.3	815.9	863.0	893.4	910.0	896.2	860.2	815.9	785.5	782.8
60°	777.2	780.0	807.7	857.4	893.4	904.5	893.4	854.7	804.9	780.0	774.5
62.5°	763.4	768.9	796.6	838.1	879.6	887.9	876.8	835.3	793.8	763.4	757.9
65°	719.1	724.7	766.2	807.7	843.6	851.9	843.6	807.7	763.4	719.1	713.6
67.5°	669.4	672.1	713.6	763.4	796.6	810.4	796.6	766.2	710.8	669.4	663.8
70°	616.8	619.6	652.8	705.3	738.5	755.1	741.3	708.1	650.0	614.0	611.3
72.5°	556.0	556.0	589.1	630.6	663.8	680.4	669.4	627.9	583.6	547.7	542.1
75°	473.0	475.7	511.7	542.1	578.1	589.1	578.1	544.9	503.4	467.4	461.9
77.5°	387.2	390.0	420.4	445.3	478.5	486.8	478.5	450.8	412.1	381.7	378.9
80°	293.2	296.0	320.8	343.0	370.6	381.7	373.4	345.7	315.3	287.7	279.4
82.5°	190.8	193.6	218.5	235.1	260.0	268.3	262.8	237.9	213.0	185.3	182.6
85°	85.7	88.5	110.6	124.5	143.8	152.1	146.6	124.5	105.1	80.2	74.7
87.5°	8.3	8.3	8.3	8.3	8.3	11.1	11.1	8.3	8.3	8.3	8.3
90°	2.8	2.8	3.3	3.3	3.3	3.3	3.3	3.3	3.3	2.8	2.8
92.5°	2.8	2.8	2.8	3.9	4.4	3.9	4.4	3.3	3.3	2.8	2.8
95°	3.3	3.3	3.9	5.0	6.1	6.6	6.6	3.9	3.9	3.3	3.3
97.5°	4.4	5.0	5.0	6.1	10.0	18.3	11.1	5.5	5.5	5.0	4.4
100°	7.2	7.7	7.7	13.8	29.3	39.3	28.2	14.4	10.5	7.7	7.7
102.5°	23.2	24.3	29.9	44.8	66.4	60.3	50.9	48.1	33.2	26.6	25.5
105°	59.2	58.7	63.1	74.7	93.0	91.3	84.1	76.4	65.8	60.9	60.9
107.5°	78.0	78.0	81.9	91.9	105.7	123.4	125.1	99.0	86.9	81.3	80.8
110°	88.0	88.0	91.3	99.6	117.9	142.8	141.6	122.3	107.3	100.2	99.0



REPORT NUMBER: P833248  
 CATALOG NUMBER: TTN-D1-750-U-WQ-UPL1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	90.2	90.7	95.2	107.9	127.8	138.9	133.9	126.2	119.5	114.0	112.9
115°	93.5	93.5	98.5	110.7	121.7	126.2	120.6	114.5	110.1	107.9	109.0
117.5°	92.4	94.1	95.2	101.8	109.0	112.3	109.6	101.3	97.9	96.8	95.2
120°	85.8	85.8	86.9	90.2	94.1	95.7	94.6	89.1	86.3	85.8	84.7
122.5°	76.4	76.9	76.4	78.0	80.8	82.4	81.3	76.9	75.8	75.8	74.7
125°	67.0	67.0	66.4	67.5	69.2	68.6	69.2	67.0	66.4	66.4	65.8
127.5°	60.3	59.8	58.7	59.2	59.8	59.8	60.3	58.1	58.7	59.2	58.7
130°	53.7	53.7	52.6	52.6	52.6	51.5	52.6	51.5	52.0	52.6	53.1
132.5°	47.6	47.6	45.9	45.4	45.4	45.4	45.9	45.4	46.5	47.6	47.6
135°	42.6	42.6	40.9	41.5	41.5	40.9	41.5	40.9	42.1	42.6	42.6
137.5°	38.7	38.7	37.6	37.6	37.6	37.1	37.6	37.6	38.2	39.3	39.8
140°	35.4	35.4	34.9	34.9	34.3	34.9	34.9	34.9	35.4	36.0	36.0
142.5°	33.8	33.2	32.6	32.1	32.6	32.6	32.6	32.1	32.6	33.8	33.8
145°	31.0	31.0	30.4	30.4	30.4	31.0	30.4	30.4	31.0	31.0	31.5
147.5°	29.3	29.3	28.8	29.3	29.3	29.3	29.3	28.8	29.3	29.3	29.9
150°	28.8	28.2	27.7	28.2	28.2	27.7	27.7	27.7	27.7	28.2	28.2
152.5°	27.1	27.1	26.6	27.1	26.6	26.6	26.6	26.6	26.6	27.1	27.7
155°	26.0	26.0	25.5	26.0	26.0	26.0	26.0	26.0	26.0	26.0	26.0
157.5°	24.9	25.5	24.9	24.9	24.9	24.9	24.9	24.9	24.9	25.5	25.5
160°	24.3	24.3	24.3	24.3	23.8	23.8	23.8	24.3	24.3	24.3	24.9
162.5°	23.8	23.8	23.8	23.8	23.2	23.2	23.2	23.2	23.8	23.8	24.3
165°	23.8	23.2	23.2	23.2	22.7	22.7	22.7	22.7	23.2	23.8	23.2
167.5°	22.7	22.7	22.7	22.7	22.7	22.1	22.1	22.7	22.7	22.7	23.2
170°	22.7	22.7	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.7
172.5°	22.7	22.7	22.7	22.7	22.1	22.1	22.1	22.1	22.1	22.7	22.7
175°	22.7	22.7	22.7	22.7	22.1	22.1	22.1	22.7	22.7	22.7	22.1
177.5°	22.7	22.7	22.7	22.7	22.1	22.7	22.7	22.7	22.7	22.7	22.7
180°	22.7	22.7	22.7	22.7	22.7	22.7	22.7	22.7	22.7	22.7	22.7

(END OF REPORT)