

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P543185

Luminaire Tested: **TT-D8-830-U-MQ-UPL**

Issue Date: 5/10/2022

Test Information

Test Method: LM-79-08
Report Number: P543185
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G2-2002-677-2) AND
Test Lab: INNOVATION CENTER
Issue Date: 5/10/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: TT-D8-830-U-MQ-UPL
Description: TOPTIER LED PARKING GARAGE LUMINAIRE WITH UPLIGHT
3000K, 80 CRI LEDS AND MEDIUM DISTRIBUTION
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15888.7 lumens
Efficiency: N/A
Efficacy: 101.4 lumens/watt
Luminous Opening: Vertical Cylinder (Dia: 1.12' x H: 0.1')
IES Classification: Type V - Short
BUG Rating: B3 - U4 - G3


Input Watts (W): 156.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P543185
 CATALOG NUMBER: TT-D8-830-U-MQ-UPL

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 5 fc
 Type V - Short - N/A

REPORT NUMBER: P543185
CATALOG NUMBER: TT-D8-830-U-MQ-UPL

Luminous Intensity Polar Plot



REPORT NUMBER: P543185
 CATALOG NUMBER: TT-D8-830-U-MQ-UPL


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 7528.5 | 415.9 | 7944.4 |
| | % Fixture | 47.4 | 2.6 | 50.0 |
| Street Side | Lumens | 7528.5 | 415.9 | 7944.4 |
| | % Fixture | 47.4 | 2.6 | 50.0 |
| Total | Lumens | 15057.0 | 831.7 | 15888.7 |
| | % Fixture | 94.8 | 5.2 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 290.8 | 1.8 |
| 10°-20° | 835.2 | 5.3 |
| 20°-30° | 1345.8 | 8.5 |
| 30°-40° | 1823.7 | 11.5 |
| 40°-50° | 2311.9 | 14.6 |
| 50°-60° | 2844.2 | 17.9 |
| 60°-70° | 2864.8 | 18.0 |
| 70°-80° | 2096.6 | 13.2 |
| 80°-90° | 644.0 | 4.1 |
| 90°-100° | 42.6 | 0.3 |
| 100°-110° | 66.0 | 0.4 |
| 110°-120° | 91.9 | 0.6 |
| 120°-130° | 119.0 | 0.7 |
| 130°-140° | 138.7 | 0.9 |
| 140°-150° | 140.5 | 0.9 |
| 150°-160° | 121.9 | 0.8 |
| 160°-170° | 82.2 | 0.5 |
| 170°-180° | 28.9 | 0.2 |
| 0°-90° | 15057.0 | 94.8 |
| 0°-180° | 15888.7 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P543185
 CATALOG NUMBER: TT-D8-830-U-MQ-UPL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|---------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1235.9 | 7.8 | | | |
| FM (30°-60°) | 3489.9 | 22.0 | | | |
| FH (60°-80°) | 2480.7 | 15.6 | | | G2/5000 |
| FVH (80°-90°) | 322.0 | 2.0 | | | G3/500 |
| BL (0°-30°) | 1235.9 | 7.8 | B3/2500 | | |
| BM (30°-60°) | 3489.9 | 22.0 | B3/5000 | | |
| BH (60°-80°) | 2480.7 | 15.6 | B3/2500 | | G2/5000 |
| BVH (80°-90°) | 322.0 | 2.0 | | | G3/500 |
| UL (90°-100°) | 42.6 | 0.3 | | U2/50 | |
| UH (100°-180°) | 789.1 | 5.0 | | U4/1000 | |

BUG Rating: B3-U4-G3

Type V Short





REPORT NUMBER: P543185

CATALOG NUMBER: TT-D8-830-U-MQ-UPL

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° | 90° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3114.6 | 3114.6 | 3114.6 | 3114.6 | 3114.6 | 3114.6 | 3114.6 | 3114.6 | 3114.6 | 3114.6 | 3114.6 |
| 2.5° | 3100.7 | 3102.7 | 3102.1 | 3103.4 | 3103.4 | 3104.7 | 3103.4 | 3104.7 | 3102.7 | 3103.4 | 3103.4 |
| 5° | 3067.1 | 3069.8 | 3067.8 | 3071.1 | 3071.7 | 3072.4 | 3070.4 | 3070.4 | 3068.4 | 3068.4 | 3069.1 |
| 7.5° | 3030.9 | 3032.2 | 3032.2 | 3035.5 | 3037.5 | 3037.5 | 3035.5 | 3032.8 | 3031.5 | 3029.5 | 3029.5 |
| 10° | 2995.9 | 2997.9 | 2997.2 | 3000.5 | 3003.2 | 3003.8 | 3001.2 | 2996.6 | 2994.6 | 2993.3 | 2993.3 |
| 12.5° | 2965.6 | 2967.6 | 2968.9 | 2972.8 | 2976.8 | 2976.8 | 2975.5 | 2970.2 | 2966.9 | 2964.9 | 2964.3 |
| 15° | 2943.2 | 2945.1 | 2945.8 | 2951.7 | 2955.7 | 2957.7 | 2955.0 | 2949.8 | 2945.8 | 2943.2 | 2941.9 |
| 17.5° | 2920.8 | 2922.1 | 2925.4 | 2930.6 | 2934.6 | 2937.2 | 2934.6 | 2929.3 | 2924.1 | 2919.4 | 2918.1 |
| 20° | 2899.0 | 2899.7 | 2904.3 | 2911.5 | 2916.8 | 2919.4 | 2916.8 | 2908.9 | 2901.0 | 2897.0 | 2896.4 |
| 22.5° | 2889.1 | 2890.4 | 2896.4 | 2906.9 | 2914.2 | 2919.4 | 2912.8 | 2903.0 | 2893.7 | 2887.1 | 2886.5 |
| 25° | 2882.5 | 2883.2 | 2891.1 | 2905.6 | 2918.8 | 2922.7 | 2918.1 | 2904.3 | 2889.8 | 2881.2 | 2880.5 |
| 27.5° | 2888.4 | 2891.1 | 2901.6 | 2916.1 | 2933.3 | 2939.9 | 2935.3 | 2915.5 | 2899.7 | 2889.8 | 2887.8 |
| 30° | 2887.1 | 2889.1 | 2901.0 | 2917.5 | 2933.3 | 2946.5 | 2937.2 | 2916.1 | 2897.7 | 2887.8 | 2886.5 |
| 32.5° | 2883.2 | 2885.8 | 2896.4 | 2910.2 | 2932.6 | 2941.9 | 2933.3 | 2908.9 | 2893.1 | 2885.8 | 2883.2 |
| 35° | 2866.7 | 2871.3 | 2886.5 | 2906.9 | 2927.3 | 2936.6 | 2926.7 | 2906.2 | 2884.5 | 2872.6 | 2871.3 |
| 37.5° | 2860.1 | 2863.4 | 2878.6 | 2902.3 | 2929.3 | 2939.2 | 2926.0 | 2901.6 | 2877.2 | 2864.1 | 2860.8 |
| 40° | 2849.5 | 2854.8 | 2873.3 | 2901.0 | 2932.0 | 2941.2 | 2930.6 | 2902.3 | 2874.6 | 2852.8 | 2846.9 |
| 42.5° | 2849.5 | 2854.2 | 2879.9 | 2918.1 | 2952.4 | 2968.9 | 2952.4 | 2920.1 | 2881.2 | 2850.9 | 2846.3 |
| 45° | 2895.0 | 2901.0 | 2933.3 | 2990.0 | 3043.4 | 3063.2 | 3042.7 | 2993.3 | 2934.6 | 2899.7 | 2890.4 |
| 47.5° | 2933.9 | 2942.5 | 2991.3 | 3063.2 | 3129.8 | 3152.2 | 3127.8 | 3064.5 | 2992.0 | 2942.5 | 2933.9 |
| 50° | 2963.0 | 2972.8 | 3036.1 | 3127.1 | 3198.3 | 3228.7 | 3201.0 | 3129.1 | 3037.5 | 2974.2 | 2964.3 |
| 52.5° | 3015.0 | 3030.2 | 3105.4 | 3208.2 | 3307.8 | 3346.0 | 3307.8 | 3211.5 | 3105.4 | 3032.2 | 3015.0 |
| 55° | 3019.0 | 3028.9 | 3119.2 | 3246.5 | 3354.6 | 3392.2 | 3359.2 | 3247.1 | 3122.5 | 3033.5 | 3021.0 |
| 57.5° | 2973.5 | 2984.7 | 3080.3 | 3226.7 | 3334.1 | 3367.1 | 3334.8 | 3228.7 | 3088.9 | 2991.3 | 2980.1 |
| 60° | 2891.7 | 2903.0 | 3002.5 | 3154.8 | 3270.2 | 3320.3 | 3272.8 | 3158.1 | 3012.4 | 2910.9 | 2898.3 |
| 62.5° | 2802.7 | 2823.8 | 2938.6 | 3090.2 | 3204.9 | 3257.7 | 3210.2 | 3092.8 | 2945.1 | 2831.7 | 2812.6 |
| 65° | 2662.3 | 2671.5 | 2794.8 | 2959.0 | 3100.1 | 3138.3 | 3100.7 | 2963.6 | 2815.9 | 2679.4 | 2672.2 |
| 67.5° | 2519.9 | 2537.0 | 2639.2 | 2822.5 | 2959.0 | 2995.3 | 2958.3 | 2821.9 | 2652.4 | 2542.3 | 2529.8 |
| 70° | 2283.2 | 2303.0 | 2446.7 | 2604.3 | 2733.5 | 2796.8 | 2737.5 | 2606.3 | 2469.1 | 2310.9 | 2300.3 |
| 72.5° | 2064.3 | 2084.7 | 2183.6 | 2361.0 | 2492.2 | 2519.2 | 2500.8 | 2364.3 | 2204.1 | 2099.3 | 2084.7 |
| 75° | 1778.2 | 1785.4 | 1912.7 | 2063.0 | 2184.3 | 2213.3 | 2190.2 | 2061.0 | 1936.4 | 1801.9 | 1780.8 |
| 77.5° | 1480.8 | 1495.3 | 1585.0 | 1713.6 | 1818.4 | 1870.5 | 1817.1 | 1720.8 | 1594.2 | 1496.0 | 1481.5 |
| 80° | 1140.6 | 1156.4 | 1249.4 | 1366.1 | 1447.2 | 1488.7 | 1449.2 | 1362.8 | 1258.0 | 1157.8 | 1150.5 |
| 82.5° | 804.4 | 805.0 | 897.3 | 973.8 | 1054.9 | 1078.6 | 1056.2 | 989.6 | 903.9 | 812.3 | 813.6 |
| 85° | 455.6 | 460.2 | 523.5 | 593.4 | 640.2 | 671.8 | 646.8 | 597.3 | 530.1 | 466.1 | 460.2 |
| 87.5° | 103.5 | 102.9 | 135.8 | 176.0 | 228.1 | 227.5 | 222.8 | 182.0 | 139.8 | 101.5 | 100.2 |
| 90° | 30.1 | 29.1 | 29.1 | 29.1 | 29.1 | 29.1 | 29.1 | 29.1 | 29.1 | 29.1 | 29.1 |
| 92.5° | 34.8 | 34.2 | 34.2 | 33.8 | 33.8 | 33.8 | 33.8 | 33.8 | 33.8 | 33.8 | 33.8 |
| 95° | 39.4 | 39.4 | 39.4 | 38.5 | 38.5 | 38.5 | 38.5 | 38.5 | 38.5 | 38.5 | 38.5 |
| 97.5° | 44.6 | 44.6 | 44.6 | 44.2 | 44.2 | 44.2 | 44.2 | 44.2 | 44.2 | 44.2 | 44.2 |
| 100° | 49.8 | 49.8 | 49.8 | 49.8 | 49.8 | 49.8 | 49.8 | 49.8 | 49.8 | 49.8 | 49.8 |
| 102.5° | 55.9 | 55.9 | 55.9 | 55.9 | 55.9 | 55.9 | 55.9 | 56.4 | 55.9 | 55.9 | 55.9 |
| 105° | 62.0 | 62.0 | 62.0 | 62.0 | 62.0 | 62.0 | 62.0 | 62.9 | 62.0 | 62.0 | 62.0 |
| 107.5° | 68.6 | 68.6 | 69.0 | 69.0 | 69.0 | 69.0 | 69.0 | 69.5 | 69.0 | 69.0 | 69.0 |
| 110° | 75.1 | 75.1 | 76.1 | 76.1 | 76.1 | 76.1 | 76.1 | 76.1 | 76.1 | 76.1 | 76.1 |



REPORT NUMBER: P543185
 CATALOG NUMBER: TT-D8-830-U-MQ-UPL

CANDELA DISTRIBUTION (continued):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° | 90° |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 112.5° | 83.1 | 83.1 | 84.0 | 84.0 | 84.0 | 84.0 | 84.6 | 84.6 | 84.0 | 84.0 | 84.0 |
| 115° | 91.1 | 91.1 | 92.0 | 92.0 | 92.0 | 92.0 | 93.0 | 93.0 | 92.0 | 92.0 | 92.0 |
| 117.5° | 100.5 | 100.5 | 101.0 | 101.4 | 101.4 | 101.4 | 102.4 | 102.4 | 101.4 | 101.4 | 101.4 |
| 120° | 109.9 | 109.9 | 109.9 | 110.8 | 110.8 | 110.8 | 111.8 | 111.8 | 110.8 | 110.8 | 110.8 |
| 122.5° | 120.7 | 120.7 | 121.2 | 121.6 | 121.6 | 121.6 | 122.6 | 122.6 | 122.1 | 122.1 | 121.6 |
| 125° | 131.5 | 131.5 | 132.4 | 132.4 | 132.4 | 132.4 | 133.4 | 133.4 | 133.4 | 133.4 | 132.4 |
| 127.5° | 143.2 | 143.2 | 144.2 | 144.2 | 144.2 | 144.2 | 145.1 | 145.1 | 145.1 | 145.1 | 144.2 |
| 130° | 155.0 | 155.0 | 155.9 | 155.9 | 155.9 | 155.9 | 156.8 | 156.8 | 156.8 | 156.8 | 155.9 |
| 132.5° | 167.2 | 167.2 | 167.6 | 167.6 | 167.6 | 167.6 | 168.6 | 168.6 | 168.6 | 168.6 | 168.1 |
| 135° | 179.4 | 179.4 | 179.4 | 179.4 | 179.4 | 179.4 | 180.3 | 180.3 | 180.3 | 180.3 | 180.3 |
| 137.5° | 191.2 | 190.6 | 191.2 | 190.6 | 191.2 | 191.2 | 191.6 | 191.6 | 191.6 | 191.6 | 191.6 |
| 140° | 202.9 | 201.9 | 202.9 | 201.9 | 202.9 | 202.9 | 202.9 | 202.9 | 202.9 | 202.9 | 202.9 |
| 142.5° | 213.7 | 213.2 | 213.7 | 212.7 | 213.7 | 213.7 | 213.7 | 213.7 | 213.7 | 213.7 | 213.7 |
| 145° | 224.5 | 224.5 | 224.5 | 223.5 | 224.5 | 224.5 | 224.5 | 224.5 | 224.5 | 224.5 | 224.5 |
| 147.5° | 235.8 | 235.3 | 235.8 | 234.8 | 235.8 | 235.8 | 235.8 | 235.8 | 235.8 | 235.8 | 235.8 |
| 150° | 247.0 | 246.1 | 247.0 | 246.1 | 247.0 | 247.0 | 247.0 | 247.0 | 247.0 | 247.0 | 247.0 |
| 152.5° | 256.0 | 255.5 | 256.4 | 255.5 | 256.0 | 256.0 | 256.4 | 256.0 | 256.0 | 256.0 | 256.0 |
| 155° | 264.9 | 264.9 | 265.8 | 264.9 | 264.9 | 264.9 | 265.8 | 264.9 | 264.9 | 264.9 | 264.9 |
| 157.5° | 272.4 | 272.4 | 273.3 | 272.4 | 272.4 | 272.4 | 273.3 | 272.4 | 272.4 | 272.4 | 272.4 |
| 160° | 279.9 | 279.9 | 280.8 | 279.9 | 279.9 | 279.9 | 280.8 | 279.9 | 279.9 | 279.9 | 279.9 |
| 162.5° | 286.0 | 286.0 | 286.9 | 286.0 | 286.0 | 286.0 | 286.9 | 286.0 | 286.0 | 286.0 | 286.0 |
| 165° | 292.1 | 292.1 | 293.0 | 292.1 | 292.1 | 292.1 | 293.0 | 292.1 | 292.1 | 292.1 | 292.1 |
| 167.5° | 295.8 | 295.8 | 296.8 | 295.8 | 295.8 | 295.8 | 296.8 | 295.8 | 295.8 | 295.8 | 295.8 |
| 170° | 299.6 | 299.6 | 300.5 | 299.6 | 299.6 | 299.6 | 300.5 | 299.6 | 299.6 | 299.6 | 299.6 |
| 172.5° | 302.0 | 302.0 | 302.8 | 302.0 | 302.4 | 302.4 | 302.8 | 302.0 | 302.0 | 302.0 | 302.0 |
| 175° | 304.3 | 304.3 | 305.2 | 304.3 | 305.2 | 305.2 | 305.2 | 304.3 | 304.3 | 304.3 | 304.3 |
| 177.5° | 305.2 | 305.2 | 305.7 | 305.2 | 305.7 | 305.7 | 305.7 | 305.2 | 305.2 | 305.2 | 305.2 |
| 180° | 306.2 | 306.2 | 306.2 | 306.2 | 306.2 | 306.2 | 306.2 | 306.2 | 306.2 | 306.2 | 306.2 |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

McGRAW-EDISON

Report Number: SP1-2006-844-5

Luminaire Tested: TT-D5-830-U-MQ

Test Date: 09/30/2020

Data applicable to product families TT-x-830 and TTN-x-830

Test Information

Test Method: LM-79-08
 Report Number: SP1-2006-844-5
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 09/30/2020
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: MCGRAW-EDISON
 Catalog Number: **TT-D5-830-U-MQ**
 Description: MCGRAW EDISON

DISTRIBUTION

Spectral Parameters


CCT (K): 2996
 CIE u': 0.2496
 CIE v': 0.5255
 Duv: 0.0029
 CIE x: 0.4414
 CIE y: 0.4130
 CIE z: 0.1455
 Peak Wavelength (nm): 601
 Dominant Wavelength (nm): 581
 Purity: 56.8

 Rf: 85.7
 Rg: 94.5

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 81.6 | | |
| R1: | 79.1 | R9: | -0.6 |
| R2: | 89.7 | R10: | 77.8 |
| R3: | 96.7 | R11: | 80.1 |
| R4: | 80.2 | R12: | 72.7 |
| R5: | 79.8 | R13: | 81.5 |
| R6: | 88.4 | R14: | 98.5 |
| R7: | 82.6 | | |
| R8: | 56.3 | | |

Test Conditions

Stabilization Time: 55M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.5/43%
 Sphere Temperature (°C): 25.9



REPORT NUMBER: SP1-2006-844-5


| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 7/29/2020 | 1/29/2021 |
| Power Meter | IN0071 | 12/3/2019 | 12/3/2020 |
| AC Power Source | IN0063 | 12/3/2019 | 12/3/2020 |
| DC Power Source | IN0208 | 12/3/2019 | 12/3/2020 |
| Sphere Thermometer | IN0085 | 12/3/2019 | 12/3/2020 |
| Room Thermometer | IN0046 | 12/3/2019 | 12/3/2020 |

REPORT NUMBER: SP1-2006-844-5

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2006-844-5

Photopic Flux vs. Wavelength




#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2265 | 0.0 | 490 | 45874 | 6.5 | 620 | 162337 | 42.2 | 750 | 6976 | 0.0 | 880 | 2976 | 0.0 |
| 365 | 2167 | 0.0 | 495 | 55189 | 10.0 | 625 | 153641 | 33.9 | 755 | 6666 | 0.0 | 885 | 2283 | 0.0 |
| 370 | 2505 | 0.0 | 500 | 64204 | 14.2 | 630 | 143151 | 25.9 | 760 | 5969 | 0.0 | 890 | 2506 | 0.0 |
| 375 | 2720 | 0.0 | 505 | 71441 | 20.0 | 635 | 133763 | 20.1 | 765 | 5281 | 0.0 | 895 | 3132 | 0.0 |
| 380 | 2601 | 0.0 | 510 | 76219 | 26.2 | 640 | 123759 | 14.8 | 770 | 4732 | 0.0 | 900 | 2539 | 0.0 |
| 385 | 2461 | 0.0 | 515 | 79949 | 33.1 | 645 | 112859 | 10.9 | 775 | 3998 | 0.0 | 905 | 1252 | 0.0 |
| 390 | 2308 | 0.0 | 520 | 83077 | 40.3 | 650 | 102080 | 7.5 | 780 | 4027 | 0.0 | 910 | 1938 | 0.0 |
| 395 | 2104 | 0.0 | 525 | 86267 | 46.3 | 655 | 91102 | 5.2 | 785 | 4088 | 0.0 | 915 | 2171 | 0.0 |
| 400 | 1900 | 0.0 | 530 | 89871 | 52.9 | 660 | 79928 | 3.3 | 790 | 3700 | 0.0 | 920 | 2123 | 0.0 |
| 405 | 1945 | 0.0 | 535 | 93544 | 58.0 | 665 | 70694 | 2.2 | 795 | 3213 | 0.0 | 925 | 1954 | 0.0 |
| 410 | 2378 | 0.0 | 540 | 97371 | 63.4 | 670 | 61201 | 1.3 | 800 | 3403 | 0.0 | 930 | 2800 | 0.0 |
| 415 | 3437 | 0.0 | 545 | 103011 | 68.6 | 675 | 53092 | 0.9 | 805 | 3079 | 0.0 | 935 | 3314 | 0.0 |
| 420 | 6173 | 0.0 | 550 | 108560 | 73.8 | 680 | 45718 | 0.5 | 810 | 2921 | 0.0 | 940 | 553 | 0.0 |
| 425 | 11052 | 0.1 | 555 | 114473 | 78.2 | 685 | 39372 | 0.3 | 815 | 2705 | 0.0 | 945 | 2793 | 0.0 |
| 430 | 18756 | 0.1 | 560 | 121896 | 82.8 | 690 | 34120 | 0.2 | 820 | 2685 | 0.0 | 950 | 2629 | 0.0 |
| 435 | 29750 | 0.4 | 565 | 130192 | 86.6 | 695 | 29427 | 0.1 | 825 | 3246 | 0.0 | 955 | 2418 | 0.0 |
| 440 | 43697 | 0.7 | 570 | 139595 | 90.8 | 700 | 25380 | 0.1 | 830 | 2813 | 0.0 | 960 | 2857 | 0.0 |
| 445 | 61462 | 1.3 | 575 | 149225 | 92.8 | 705 | 22079 | 0.0 | 835 | 2097 | 0.0 | 965 | 1052 | 0.0 |
| 450 | 76648 | 2.0 | 580 | 158344 | 94.1 | 710 | 18938 | 0.0 | 840 | 1606 | 0.0 | 970 | 4009 | 0.0 |
| 455 | 65529 | 2.2 | 585 | 165704 | 92.1 | 715 | 16322 | 0.0 | 845 | 2347 | 0.0 | 975 | 2341 | 0.0 |
| 460 | 46753 | 1.9 | 590 | 172269 | 89.1 | 720 | 14132 | 0.0 | 850 | 2273 | 0.0 | 980 | 2439 | 0.0 |
| 465 | 38422 | 2.0 | 595 | 177895 | 84.3 | 725 | 12072 | 0.0 | 855 | 1971 | 0.0 | 985 | 2098 | 0.0 |
| 470 | 32450 | 2.0 | 600 | 180887 | 78.0 | 730 | 10271 | 0.0 | 860 | 1962 | 0.0 | 990 | 1159 | 0.0 |
| 475 | 29284 | 2.3 | 605 | 178880 | 69.3 | 735 | 9202 | 0.0 | 865 | 2989 | 0.0 | 995 | 2146 | 0.0 |
| 480 | 31922 | 3.0 | 610 | 175843 | 60.4 | 740 | 8451 | 0.0 | 870 | 2921 | 0.0 | 1000 | 1904 | 0.0 |
| 485 | 37800 | 4.5 | 615 | 170321 | 51.4 | 745 | 7632 | 0.0 | 875 | 3581 | 0.0 | | | |

REPORT NUMBER: SP1-2006-844-5

Scotopic Flux vs. Wavelength



Scotopic Lumens: 4357.3

S/P: 0.5

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2265 | 0.0 | 490 | 45874 | 70.6 | 620 | 162337 | 2.0 | 750 | 6976 | 0.0 | 880 | 2976 | 0.0 |
| 365 | 2167 | 0.0 | 495 | 55189 | 89.2 | 625 | 153641 | 1.3 | 755 | 6666 | 0.0 | 885 | 2283 | 0.0 |
| 370 | 2505 | 0.0 | 500 | 64204 | 107.4 | 630 | 143151 | 0.8 | 760 | 5969 | 0.0 | 890 | 2506 | 0.0 |
| 375 | 2720 | 0.0 | 505 | 71441 | 121.4 | 635 | 133763 | 0.5 | 765 | 5281 | 0.0 | 895 | 3132 | 0.0 |
| 380 | 2601 | 0.0 | 510 | 76219 | 129.2 | 640 | 123759 | 0.3 | 770 | 4732 | 0.0 | 900 | 2539 | 0.0 |
| 385 | 2461 | 0.0 | 515 | 79949 | 132.5 | 645 | 112859 | 0.2 | 775 | 3998 | 0.0 | 905 | 1252 | 0.0 |
| 390 | 2308 | 0.0 | 520 | 83077 | 132.1 | 650 | 102080 | 0.1 | 780 | 4027 | 0.0 | 910 | 1938 | 0.0 |
| 395 | 2104 | 0.0 | 525 | 86267 | 129.1 | 655 | 91102 | 0.1 | 785 | 4088 | 0.0 | 915 | 2171 | 0.0 |
| 400 | 1900 | 0.0 | 530 | 89871 | 123.9 | 660 | 79928 | 0.0 | 790 | 3700 | 0.0 | 920 | 2123 | 0.0 |
| 405 | 1945 | 0.1 | 535 | 93544 | 116.6 | 665 | 70694 | 0.0 | 795 | 3213 | 0.0 | 925 | 1954 | 0.0 |
| 410 | 2378 | 0.1 | 540 | 97371 | 107.6 | 670 | 61201 | 0.0 | 800 | 3403 | 0.0 | 930 | 2800 | 0.0 |
| 415 | 3437 | 0.4 | 545 | 103011 | 98.8 | 675 | 53092 | 0.0 | 805 | 3079 | 0.0 | 935 | 3314 | 0.0 |
| 420 | 6173 | 1.0 | 550 | 108560 | 88.8 | 680 | 45718 | 0.0 | 810 | 2921 | 0.0 | 940 | 553 | 0.0 |
| 425 | 11052 | 2.7 | 555 | 114473 | 78.2 | 685 | 39372 | 0.0 | 815 | 2705 | 0.0 | 945 | 2793 | 0.0 |
| 430 | 18756 | 6.4 | 560 | 121896 | 68.1 | 690 | 34120 | 0.0 | 820 | 2685 | 0.0 | 950 | 2629 | 0.0 |
| 435 | 29750 | 13.3 | 565 | 130192 | 58.4 | 695 | 29427 | 0.0 | 825 | 3246 | 0.0 | 955 | 2418 | 0.0 |
| 440 | 43697 | 24.4 | 570 | 139595 | 49.3 | 700 | 25380 | 0.0 | 830 | 2813 | 0.0 | 960 | 2857 | 0.0 |
| 445 | 61462 | 41.2 | 575 | 149225 | 40.6 | 705 | 22079 | 0.0 | 835 | 2097 | 0.0 | 965 | 1052 | 0.0 |
| 450 | 76648 | 59.4 | 580 | 158344 | 32.6 | 710 | 18938 | 0.0 | 840 | 1606 | 0.0 | 970 | 4009 | 0.0 |
| 455 | 65529 | 57.3 | 585 | 165704 | 25.3 | 715 | 16322 | 0.0 | 845 | 2347 | 0.0 | 975 | 2341 | 0.0 |
| 460 | 46753 | 45.2 | 590 | 172269 | 19.2 | 720 | 14132 | 0.0 | 850 | 2273 | 0.0 | 980 | 2439 | 0.0 |
| 465 | 38422 | 40.6 | 595 | 177895 | 14.2 | 725 | 12072 | 0.0 | 855 | 1971 | 0.0 | 985 | 2098 | 0.0 |
| 470 | 32450 | 37.4 | 600 | 180887 | 10.2 | 730 | 10271 | 0.0 | 860 | 1962 | 0.0 | 990 | 1159 | 0.0 |
| 475 | 29284 | 36.6 | 605 | 178880 | 7.0 | 735 | 9202 | 0.0 | 865 | 2989 | 0.0 | 995 | 2146 | 0.0 |
| 480 | 31922 | 43.1 | 610 | 175843 | 4.8 | 740 | 8451 | 0.0 | 870 | 2921 | 0.0 | 1000 | 1904 | 0.0 |
| 485 | 37800 | 54.8 | 615 | 170321 | 3.2 | 745 | 7632 | 0.0 | 875 | 3581 | 0.0 | | | |

REPORT NUMBER: SP1-2006-844-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: 11640.4 S/P: 1.33



| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2265 | 0.0 | 490 | 45874 | 38.2 | 620 | 162337 | 0.1 | 750 | 6976 | 0.0 | 880 | 2976 | 0.0 |
| 365 | 2167 | 0.0 | 495 | 55189 | 45.6 | 625 | 153641 | 0.1 | 755 | 6666 | 0.0 | 885 | 2283 | 0.0 |
| 370 | 2505 | 0.0 | 500 | 64204 | 51.6 | 630 | 143151 | 0.0 | 760 | 5969 | 0.0 | 890 | 2506 | 0.0 |
| 375 | 2720 | 0.0 | 505 | 71441 | 54.8 | 635 | 133763 | 0.0 | 765 | 5281 | 0.0 | 895 | 3132 | 0.0 |
| 380 | 2601 | 0.0 | 510 | 76219 | 54.7 | 640 | 123759 | 0.0 | 770 | 4732 | 0.0 | 900 | 2539 | 0.0 |
| 385 | 2461 | 0.0 | 515 | 79949 | 52.2 | 645 | 112859 | 0.0 | 775 | 3998 | 0.0 | 905 | 1252 | 0.0 |
| 390 | 2308 | 0.0 | 520 | 83077 | 48.4 | 650 | 102080 | 0.0 | 780 | 4027 | 0.0 | 910 | 1938 | 0.0 |
| 395 | 2104 | 0.0 | 525 | 86267 | 43.7 | 655 | 91102 | 0.0 | 785 | 4088 | 0.0 | 915 | 2171 | 0.0 |
| 400 | 1900 | 0.0 | 530 | 89871 | 38.8 | 660 | 79928 | 0.0 | 790 | 3700 | 0.0 | 920 | 2123 | 0.0 |
| 405 | 1945 | 0.0 | 535 | 93544 | 33.7 | 665 | 70694 | 0.0 | 795 | 3213 | 0.0 | 925 | 1954 | 0.0 |
| 410 | 2378 | 0.1 | 540 | 97371 | 28.5 | 670 | 61201 | 0.0 | 800 | 3403 | 0.0 | 930 | 2800 | 0.0 |
| 415 | 3437 | 0.2 | 545 | 103011 | 23.9 | 675 | 53092 | 0.0 | 805 | 3079 | 0.0 | 935 | 3314 | 0.0 |
| 420 | 6173 | 0.7 | 550 | 108560 | 19.5 | 680 | 45718 | 0.0 | 810 | 2921 | 0.0 | 940 | 553 | 0.0 |
| 425 | 11052 | 1.7 | 555 | 114473 | 15.4 | 685 | 39372 | 0.0 | 815 | 2705 | 0.0 | 945 | 2793 | 0.0 |
| 430 | 18756 | 4.0 | 560 | 121896 | 12.0 | 690 | 34120 | 0.0 | 820 | 2685 | 0.0 | 950 | 2629 | 0.0 |
| 435 | 29750 | 7.9 | 565 | 130192 | 9.1 | 695 | 29427 | 0.0 | 825 | 3246 | 0.0 | 955 | 2418 | 0.0 |
| 440 | 43697 | 14.6 | 570 | 139595 | 6.8 | 700 | 25380 | 0.0 | 830 | 2813 | 0.0 | 960 | 2857 | 0.0 |
| 445 | 61462 | 24.2 | 575 | 149225 | 5.0 | 705 | 22079 | 0.0 | 835 | 2097 | 0.0 | 965 | 1052 | 0.0 |
| 450 | 76648 | 35.3 | 580 | 158344 | 3.5 | 710 | 18938 | 0.0 | 840 | 1606 | 0.0 | 970 | 4009 | 0.0 |
| 455 | 65529 | 34.3 | 585 | 165704 | 2.5 | 715 | 16322 | 0.0 | 845 | 2347 | 0.0 | 975 | 2341 | 0.0 |
| 460 | 46753 | 27.5 | 590 | 172269 | 1.7 | 720 | 14132 | 0.0 | 850 | 2273 | 0.0 | 980 | 2439 | 0.0 |
| 465 | 38422 | 25.1 | 595 | 177895 | 1.1 | 725 | 12072 | 0.0 | 855 | 1971 | 0.0 | 985 | 2098 | 0.0 |
| 470 | 32450 | 23.2 | 600 | 180887 | 0.8 | 730 | 10271 | 0.0 | 860 | 1962 | 0.0 | 990 | 1159 | 0.0 |
| 475 | 29284 | 22.4 | 605 | 178880 | 0.5 | 735 | 9202 | 0.0 | 865 | 2989 | 0.0 | 995 | 2146 | 0.0 |
| 480 | 31922 | 25.6 | 610 | 175843 | 0.3 | 740 | 8451 | 0.0 | 870 | 2921 | 0.0 | 1000 | 1904 | 0.0 |
| 485 | 37800 | 31.2 | 615 | 170321 | 0.2 | 745 | 7632 | 0.0 | 875 | 3581 | 0.0 | | | |

Summary

$R_f = 85.7$
 $R_g = 94.5$
 CIE $R_a = 81.6$
 $R_g = -0.6$




Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)



| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 85 | CES51 = 95 | CES76 = 83 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 86 |
| CES03 = 31 | CES28 = 95 | CES53 = 90 | CES78 = 82 |
| CES04 = 70 | CES29 = 88 | CES54 = 91 | CES79 = 91 |
| CES05 = 50 | CES30 = 94 | CES55 = 91 | CES80 = 90 |
| CES06 = 51 | CES31 = 90 | CES56 = 87 | CES81 = 72 |
| CES07 = 42 | CES32 = 84 | CES57 = 86 | CES82 = 96 |
| CES08 = 41 | CES33 = 92 | CES58 = 87 | CES83 = 94 |
| CES09 = 29 | CES34 = 93 | CES59 = 91 | CES84 = 92 |
| CES10 = 76 | CES35 = 96 | CES60 = 94 | CES85 = 78 |
| CES11 = 59 | CES36 = 91 | CES61 = 90 | CES86 = 67 |
| CES12 = 65 | CES37 = 96 | CES62 = 95 | CES87 = 85 |
| CES13 = 43 | CES38 = 99 | CES63 = 88 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 84 | CES89 = 75 |
| CES15 = 72 | CES40 = 95 | CES65 = 79 | CES90 = 87 |
| CES16 = 47 | CES41 = 97 | CES66 = 83 | CES91 = 83 |
| CES17 = 50 | CES42 = 98 | CES67 = 82 | CES92 = 65 |
| CES18 = 56 | CES43 = 93 | CES68 = 84 | CES93 = 79 |
| CES19 = 72 | CES44 = 99 | CES69 = 89 | CES94 = 61 |
| CES20 = 67 | CES45 = 94 | CES70 = 81 | CES95 = 75 |
| CES21 = 87 | CES46 = 90 | CES71 = 80 | CES96 = 83 |
| CES22 = 79 | CES47 = 93 | CES72 = 93 | CES97 = 89 |
| CES23 = 92 | CES48 = 83 | CES73 = 77 | CES98 = 84 |
| CES24 = 91 | CES49 = 91 | CES74 = 93 | CES99 = 75 |
| CES25 = 72 | CES50 = 95 | CES75 = 82 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)